

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331288

Luminaire Tested: **S122DIP-S485D330U835-4F0-1E-UDD-D**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331288
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D330U835-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3276.6 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331288

CATALOG NUMBER: S122DIP-S485D330U835-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331288

CATALOG NUMBER: S122DIP-S485D330U835-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	97	92	87	83	89	85	81	78	72	69	67	61	58	56	50	48	47	42
2	88	79	72	67	81	73	67	62	62	58	54	52	49	46	43	40	38	34
3	80	69	61	55	73	64	57	51	55	49	45	46	42	38	37	34	32	28
4	73	61	52	46	67	57	49	43	48	42	38	40	36	32	33	30	27	23
5	66	54	45	39	61	50	42	37	43	37	32	36	31	28	30	26	23	20
6	61	48	40	34	56	45	37	32	39	32	28	32	28	24	27	23	20	17
7	56	44	35	29	52	41	33	28	35	29	24	29	25	21	24	21	18	15
8	52	39	31	26	48	37	29	24	32	26	22	27	22	19	22	19	16	14
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	14	12
10	45	33	25	21	42	31	24	19	27	21	17	23	18	15	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8320	8320	8320
5°	8361	8009	7978
10°	8308	7773	7685
15°	8193	7522	7376
20°	8049	7253	7078
25°	7906	6994	6809
30°	7704	6728	6536
35°	7501	6472	6346
40°	7287	6254	6154
45°	7084	6058	5992
50°	6865	5879	5830
55°	6634	5689	5666
60°	6355	5493	5493
65°	6063	5262	5287
70°	5738	5012	5065
75°	5319	4768	4860
80°	4657	4519	4652
85°	4025	4303	4491



TEST NUMBER: P331288

CATALOG NUMBER: S122DIP-S485D330U835-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	1.5
10°-20°	140.0	4.3
20°-30°	212.2	6.5
30°-40°	258.4	7.9
40°-50°	278.0	8.5
50°-60°	270.0	8.2
60°-70°	235.8	7.2
70°-80°	181.5	5.5
80°-90°	122.9	3.8
90°-100°	98.8	3.0
100°-110°	115.9	3.5
110°-120°	186.6	5.7
120°-130°	263.8	8.1
130°-140°	266.0	8.1
140°-150°	240.1	7.3
150°-160°	191.7	5.8
160°-170°	123.5	3.8
170°-180°	42.5	1.3
0°-30°	401.0	12.2
0°-40°	659.5	20.1
0°-60°	1207.5	36.9
0°-90°	1747.7	53.3
90°-120°	401.3	12.2
90°-150°	1171.2	35.7
90°-180°	1529.0	46.7
0°-180°	3276.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	515	515	515	515	515	
5°	517	514	510	514	514	49
15°	493	494	494	501	500	139
25°	448	453	460	469	471	206
35°	386	399	413	429	435	241
45°	317	337	363	385	394	244
55°	243	270	308	334	345	217
65°	166	203	246	276	287	165
75°	92	134	182	212	223	97
85°	27	73	121	151	163	29
90°	8	55	105	135	146	6
95°	27	53	98	127	137	30
105°	102	129	84	112	123	109
115°	189	204	244	123	102	186
125°	264	270	299	320	329	236
135°	326	331	342	360	366	252
145°	377	377	382	389	391	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	



TEST NUMBER: P331288

CATALOG NUMBER: S122DIP-S485D330U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3
2.5°	518.3	517.9	517.5	517.1	516.7	516.0	515.1	514.2	513.3	512.3	513.0
5°	516.8	516.3	515.8	515.3	514.8	514.1	513.1	512.1	511.1	510.1	511.1
7.5°	512.2	511.8	511.5	511.2	510.9	510.3	509.5	508.8	508.0	507.2	508.4
10°	508.6	508.3	507.9	507.6	507.3	506.9	506.4	505.9	505.4	504.9	506.2
12.5°	502.6	502.7	502.8	502.8	502.9	502.7	502.4	502.0	501.6	501.3	502.6
15°	492.9	493.2	493.6	493.9	494.2	494.4	494.4	494.4	494.4	494.4	495.9
17.5°	480.4	481.1	481.8	482.5	483.2	483.8	484.3	484.8	485.4	485.9	487.4
20°	472.0	472.8	473.7	474.5	475.3	476.1	476.7	477.4	478.1	478.7	480.5
22.5°	463.0	464.0	465.0	465.9	466.9	467.8	468.8	469.7	470.6	471.6	473.4
25°	448.1	449.3	450.4	451.6	452.7	454.1	455.6	457.1	458.6	460.0	462.0
27.5°	430.2	432.1	434.0	435.9	437.7	439.6	441.3	443.1	444.8	446.6	449.1
30°	418.2	420.4	422.5	424.7	426.9	429.0	431.2	433.3	435.5	437.6	440.3
32.5°	405.1	407.5	409.9	412.4	414.8	417.3	419.8	422.4	424.9	427.5	430.5
35°	386.1	388.9	391.8	394.6	397.4	400.4	403.5	406.7	409.8	413.0	416.6
37.5°	365.5	368.8	372.0	375.3	378.5	382.2	386.3	390.3	394.4	398.5	402.6
40°	351.8	355.4	359.1	362.7	366.4	370.4	374.9	379.4	383.9	388.4	392.7
42.5°	338.6	342.3	345.9	349.6	353.2	357.6	362.8	367.9	373.1	378.2	382.9
45°	316.7	321.1	325.6	330.1	334.6	339.7	345.5	351.3	357.2	363.0	368.1
47.5°	295.0	299.9	304.8	309.6	314.5	320.4	327.2	334.0	340.8	347.6	353.0
50°	280.1	285.2	290.4	295.5	300.6	306.9	314.4	321.9	329.4	336.8	342.5
52.5°	265.7	271.1	276.5	282.0	287.4	294.0	301.9	309.7	317.6	325.5	331.2
55°	242.7	248.7	254.7	260.6	266.6	273.9	282.6	291.2	299.8	308.4	314.4
57.5°	220.0	226.8	233.5	240.2	247.0	254.7	263.5	272.3	281.1	289.9	296.4
60°	203.9	211.0	218.2	225.3	232.4	240.7	250.2	259.6	269.1	278.6	284.9
62.5°	189.5	196.9	204.4	211.8	219.2	227.6	237.0	246.5	256.0	265.4	272.1
65°	165.8	173.9	182.1	190.2	198.3	207.3	217.1	226.9	236.7	246.5	253.3
67.5°	144.0	152.5	161.0	169.5	178.0	187.2	197.3	207.3	217.3	227.3	234.2
70°	128.5	137.1	145.7	154.3	163.0	172.4	182.7	193.0	203.3	213.6	220.7
72.5°	114.1	123.0	131.9	140.8	149.7	159.4	169.8	180.2	190.6	201.0	208.1
75°	91.9	101.2	110.4	119.7	129.0	139.0	149.6	160.2	170.9	181.5	188.6
77.5°	70.4	80.1	89.8	99.5	109.3	119.5	130.3	141.1	151.9	162.7	169.8
80°	56.0	66.1	76.3	86.4	96.5	107.0	117.8	128.5	139.3	150.1	157.1
82.5°	44.1	54.1	64.0	74.0	84.0	94.5	105.4	116.3	127.2	138.2	145.1
85°	26.9	37.2	47.5	57.8	68.0	78.5	89.1	99.7	110.4	121.0	128.0
87.5°	14.7	24.8	34.8	44.9	54.9	65.3	76.0	86.8	97.5	108.2	115.1
90°	7.8	18.2	28.6	39.0	49.5	60.3	71.5	82.7	93.9	105.0	112.0
92.5°	13.4	22.3	31.2	40.1	49.0	58.7	69.2	79.7	90.2	100.7	107.4
95°	27.0	32.4	37.8	43.3	48.7	56.7	67.1	77.6	88.0	98.5	105.2
97.5°	46.9	47.2	47.4	47.7	48.0	53.4	64.2	74.9	85.6	96.3	102.8
100°	62.5	58.8	55.1	51.3	47.6	51.1	61.6	72.1	82.6	93.1	99.8
102.5°	78.9	82.5	86.0	89.5	93.0	94.2	93.0	91.8	90.6	89.4	96.2
105°	102.0	109.0	116.0	122.9	129.9	127.9	116.9	105.9	94.9	84.0	90.5
107.5°	129.2	134.8	140.4	146.0	151.6	146.8	131.5	116.2	101.0	85.7	90.5
110°	146.2	151.1	155.9	160.7	165.5	161.6	149.0	136.4	123.7	111.1	109.2



TEST NUMBER: P331288

CATALOG NUMBER: S122DIP-S485D330U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	162.8	166.9	171.0	175.2	179.3	182.6	185.2	187.8	190.5	193.1	172.2
115°	188.9	191.9	195.0	198.0	201.1	207.2	216.5	225.8	235.0	244.3	216.0
117.5°	211.5	214.1	216.6	219.2	221.7	227.1	235.2	243.4	251.5	259.6	256.5
120°	228.6	230.3	232.1	233.8	235.5	240.4	248.3	256.2	264.2	272.1	277.6
122.5°	243.1	244.5	245.9	247.3	248.7	253.2	260.8	268.5	276.1	283.8	288.8
125°	264.4	265.3	266.2	267.2	268.1	271.9	278.6	285.3	291.9	298.6	303.6
127.5°	284.3	285.2	286.1	286.9	287.8	290.9	296.2	301.5	306.8	312.1	317.0
130°	297.0	298.0	299.0	300.0	301.0	303.6	307.9	312.1	316.4	320.7	325.5
132.5°	309.9	310.8	311.6	312.4	313.2	315.3	318.8	322.3	325.8	329.3	333.8
135°	326.0	327.2	328.3	329.5	330.6	332.3	334.6	337.0	339.3	341.6	345.8
137.5°	343.0	343.8	344.6	345.3	346.1	347.2	348.7	350.2	351.6	353.1	356.8
140°	354.1	354.6	355.0	355.4	355.8	356.5	357.7	358.8	359.9	361.0	364.3
142.5°	363.5	363.8	364.2	364.5	364.9	365.5	366.5	367.5	368.4	369.4	372.1
145°	377.3	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	384.0
147.5°	390.1	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.8
150°	398.3	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7
152.5°	405.3	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1
155°	415.5	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9
157.5°	423.4	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2
160°	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5
162.5°	432.2	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5
165°	437.8	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3
167.5°	441.9	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4
170°	444.3	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5
172.5°	445.8	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0
175°	447.8	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7
177.5°	448.1	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331288

CATALOG NUMBER: S122DIP-S485D330U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3
2.5°	513.7	514.3	515.0	515.2	514.9	514.7	514.4	514.1
5°	512.1	513.1	514.1	514.5	514.3	514.2	514.0	513.8
7.5°	509.6	510.8	512.0	512.5	512.4	512.2	512.0	511.9
10°	507.5	508.8	510.2	510.8	510.6	510.4	510.3	510.1
12.5°	503.9	505.3	506.6	507.2	507.0	506.8	506.7	506.5
15°	497.4	498.9	500.4	501.0	500.9	500.7	500.5	500.4
17.5°	489.0	490.6	492.1	492.9	492.9	492.9	492.9	492.9
20°	482.4	484.2	486.0	486.9	486.9	486.9	486.9	486.9
22.5°	475.2	477.0	478.9	479.9	480.2	480.4	480.7	481.0
25°	464.0	466.0	468.0	469.3	469.8	470.3	470.8	471.3
27.5°	451.7	454.2	456.7	458.1	458.5	458.9	459.2	459.6
30°	443.0	445.6	448.3	449.8	450.3	450.8	451.3	451.8
32.5°	433.6	436.6	439.7	441.7	442.6	443.5	444.4	445.3
35°	420.3	424.0	427.6	430.0	431.2	432.3	433.5	434.7
37.5°	406.6	410.7	414.7	417.3	418.6	419.8	421.0	422.3
40°	397.0	401.3	405.6	408.5	410.0	411.5	413.0	414.5
42.5°	387.6	392.3	397.0	400.2	401.6	403.1	404.6	406.1
45°	373.3	378.4	383.5	386.9	388.6	390.3	391.9	393.6
47.5°	358.3	363.7	369.1	372.7	374.5	376.3	378.2	380.0
50°	348.1	353.7	359.4	363.1	365.0	366.8	368.6	370.4
52.5°	337.0	342.8	348.6	352.4	354.4	356.4	358.3	360.3
55°	320.4	326.4	332.3	336.4	338.6	340.7	342.9	345.0
57.5°	302.8	309.2	315.7	320.0	322.2	324.4	326.6	328.8
60°	291.2	297.5	303.8	308.1	310.4	312.8	315.1	317.4
62.5°	278.8	285.5	292.2	296.7	298.9	301.1	303.3	305.5
65°	260.1	266.9	273.7	278.2	280.3	282.5	284.6	286.8
67.5°	241.1	247.9	254.8	259.4	261.6	263.9	266.2	268.4
70°	227.9	235.0	242.1	246.7	248.7	250.7	252.7	254.7
72.5°	215.1	222.1	229.1	233.8	236.1	238.5	240.9	243.3
75°	195.8	202.9	210.0	214.7	216.8	219.0	221.1	223.3
77.5°	176.9	184.0	191.1	195.8	198.1	200.4	202.8	205.1
80°	164.1	171.0	178.0	182.6	185.0	187.3	189.6	191.9
82.5°	152.1	159.1	166.0	170.6	172.8	175.0	177.2	179.4
85°	134.9	141.9	148.9	153.5	155.8	158.2	160.5	162.8
87.5°	121.9	128.8	135.6	140.1	142.3	144.4	146.6	148.7
90°	119.0	126.0	133.0	137.6	139.7	141.9	144.0	146.1
92.5°	114.1	120.8	127.5	131.9	133.9	136.0	138.1	140.2
95°	111.8	118.5	125.2	129.5	131.4	133.3	135.2	137.1
97.5°	109.2	115.6	122.1	126.3	128.3	130.4	132.4	134.5
100°	106.5	113.3	120.0	124.3	126.3	128.3	130.2	132.2
102.5°	103.0	109.7	116.5	120.9	122.9	124.9	126.9	129.0
105°	97.1	103.7	110.3	114.7	116.8	118.9	121.0	123.2
107.5°	95.3	100.0	104.8	108.2	110.4	112.5	114.6	116.7
110°	107.4	105.5	103.6	103.7	105.8	107.9	110.1	112.2



TEST NUMBER: P331288

CATALOG NUMBER: S122DIP-S485D330U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	151.3	130.4	109.5	100.0	102.1	104.1	106.2	108.3
115°	187.7	159.4	131.2	115.3	112.0	108.6	105.3	101.9
117.5°	253.4	250.2	247.1	237.9	222.6	207.3	192.0	176.7
120°	283.1	288.6	294.1	293.0	285.1	277.2	269.3	261.5
122.5°	293.8	298.9	303.9	306.3	305.9	305.6	305.3	305.0
125°	308.6	313.6	318.5	321.9	323.6	325.3	327.0	328.7
127.5°	321.8	326.7	331.5	334.7	336.2	337.7	339.2	340.7
130°	330.2	335.0	339.8	342.8	344.0	345.3	346.6	347.8
132.5°	338.3	342.8	347.4	350.2	351.5	352.8	354.0	355.3
135°	350.0	354.2	358.4	361.1	362.3	363.4	364.6	365.8
137.5°	360.6	364.4	368.1	370.4	371.3	372.2	373.1	374.0
140°	367.6	370.9	374.2	376.2	376.8	377.5	378.1	378.8
142.5°	374.8	377.6	380.3	381.9	382.4	382.9	383.4	383.9
145°	385.5	387.0	388.5	389.5	389.9	390.4	390.9	391.4
147.5°	395.3	395.8	396.3	396.6	396.7	396.8	396.9	397.0
150°	402.1	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	408.6	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.3	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	424.7	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.0	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	432.9	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	441.9	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.0	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	445.5	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.2	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.4	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)