

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331297

Luminaire Tested: **S122DIP-S485D530U835-4F0-1E-UDD-D**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331297
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D530U835-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4081.3 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331297

CATALOG NUMBER: S122DIP-S485D530U835-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331297

CATALOG NUMBER: S122DIP-S485D530U835-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	95	90	86	82	86	82	79	75	68	65	62	54	52	50	42	40	39	33
2	86	78	71	66	78	71	65	61	58	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	31	29	27	22
4	71	60	52	45	64	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	19	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15	12
8	51	39	31	25	46	36	28	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8320	8320	8320
5°	8361	8009	7978
10°	8308	7773	7685
15°	8193	7522	7376
20°	8049	7253	7078
25°	7906	6994	6809
30°	7704	6728	6536
35°	7501	6472	6346
40°	7287	6254	6154
45°	7084	6058	5992
50°	6865	5879	5830
55°	6634	5689	5666
60°	6355	5493	5493
65°	6063	5262	5287
70°	5738	5012	5065
75°	5319	4768	4860
80°	4657	4519	4652
85°	4025	4303	4491



TEST NUMBER: P331297

CATALOG NUMBER: S122DIP-S485D530U835-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	1.2
10°-20°	140.0	3.4
20°-30°	212.2	5.2
30°-40°	258.4	6.3
40°-50°	278.0	6.8
50°-60°	270.0	6.6
60°-70°	235.8	5.8
70°-80°	181.5	4.4
80°-90°	123.6	3.0
90°-100°	108.0	2.6
100°-110°	149.5	3.7
110°-120°	276.3	6.8
120°-130°	411.9	10.1
130°-140°	423.5	10.4
140°-150°	386.4	9.5
150°-160°	309.4	7.6
160°-170°	199.4	4.9
170°-180°	68.6	1.7
0°-30°	401.0	9.8
0°-40°	659.5	16.2
0°-60°	1207.5	29.6
0°-90°	1748.4	42.8
90°-120°	533.8	13.1
90°-150°	1755.6	43.0
90°-180°	2333.0	57.2
0°-180°	4081.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	515	515	515	515	515	
5°	517	514	510	514	514	49
15°	493	494	494	501	500	139
25°	448	453	460	469	471	206
35°	386	399	413	429	435	241
45°	317	337	363	385	394	244
55°	243	270	308	334	345	217
65°	166	203	246	276	287	165
75°	92	134	182	212	223	97
85°	27	73	121	151	163	29
90°	8	57	109	140	152	7
95°	40	60	106	136	146	46
105°	162	192	96	127	138	174
115°	303	322	367	158	118	298
125°	426	434	466	489	498	380
135°	526	534	546	566	572	406
145°	609	609	617	625	627	381
155°	671	666	672	675	671	309
165°	707	704	705	708	705	200
175°	723	719	720	723	719	69
180°	721	721	721	721	721	



TEST NUMBER: P331297

CATALOG NUMBER: S122DIP-S485D530U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3
2.5°	518.3	517.9	517.5	517.1	516.7	516.0	515.1	514.2	513.3	512.3	513.0
5°	516.8	516.3	515.8	515.3	514.8	514.1	513.1	512.1	511.1	510.1	511.1
7.5°	512.2	511.8	511.5	511.2	510.9	510.3	509.5	508.8	508.0	507.2	508.4
10°	508.6	508.3	507.9	507.6	507.3	506.9	506.4	505.9	505.4	504.9	506.2
12.5°	502.6	502.7	502.8	502.8	502.9	502.7	502.4	502.0	501.6	501.3	502.6
15°	492.9	493.2	493.6	493.9	494.2	494.4	494.4	494.4	494.4	494.4	495.9
17.5°	480.4	481.1	481.8	482.5	483.2	483.8	484.3	484.8	485.4	485.9	487.4
20°	472.0	472.8	473.7	474.5	475.3	476.1	476.7	477.4	478.1	478.7	480.5
22.5°	463.0	464.0	465.0	465.9	466.9	467.8	468.8	469.7	470.6	471.6	473.4
25°	448.1	449.3	450.4	451.6	452.7	454.1	455.6	457.1	458.6	460.0	462.0
27.5°	430.2	432.1	434.0	435.9	437.7	439.6	441.3	443.1	444.8	446.6	449.1
30°	418.2	420.4	422.5	424.7	426.9	429.0	431.2	433.3	435.5	437.6	440.3
32.5°	405.1	407.5	409.9	412.4	414.8	417.3	419.8	422.4	424.9	427.5	430.5
35°	386.1	388.9	391.8	394.6	397.4	400.4	403.5	406.7	409.8	413.0	416.6
37.5°	365.5	368.8	372.0	375.3	378.5	382.2	386.3	390.3	394.4	398.5	402.6
40°	351.8	355.4	359.1	362.7	366.4	370.4	374.9	379.4	383.9	388.4	392.7
42.5°	338.6	342.3	345.9	349.6	353.2	357.6	362.8	367.9	373.1	378.2	382.9
45°	316.7	321.1	325.6	330.1	334.6	339.7	345.5	351.3	357.2	363.0	368.1
47.5°	295.0	299.9	304.8	309.6	314.5	320.4	327.2	334.0	340.8	347.6	353.0
50°	280.1	285.2	290.4	295.5	300.6	306.9	314.4	321.9	329.4	336.8	342.5
52.5°	265.7	271.1	276.5	282.0	287.4	294.0	301.9	309.7	317.6	325.5	331.2
55°	242.7	248.7	254.7	260.6	266.6	273.9	282.6	291.2	299.8	308.4	314.4
57.5°	220.0	226.8	233.5	240.2	247.0	254.7	263.5	272.3	281.1	289.9	296.4
60°	203.9	211.0	218.2	225.3	232.4	240.7	250.2	259.6	269.1	278.6	284.9
62.5°	189.5	196.9	204.4	211.8	219.2	227.6	237.0	246.5	256.0	265.4	272.1
65°	165.8	173.9	182.1	190.2	198.3	207.3	217.1	226.9	236.7	246.5	253.3
67.5°	144.0	152.5	161.0	169.5	178.0	187.2	197.3	207.3	217.3	227.3	234.2
70°	128.5	137.1	145.7	154.3	163.0	172.4	182.7	193.0	203.3	213.6	220.7
72.5°	114.1	123.0	131.9	140.8	149.7	159.4	169.8	180.2	190.6	201.0	208.1
75°	91.9	101.2	110.4	119.7	129.0	139.0	149.6	160.2	170.9	181.5	188.6
77.5°	70.4	80.1	89.8	99.5	109.3	119.5	130.3	141.1	151.9	162.7	169.8
80°	56.0	66.1	76.3	86.4	96.5	107.0	117.8	128.5	139.3	150.1	157.1
82.5°	44.1	54.1	64.0	74.0	84.0	94.5	105.4	116.3	127.2	138.2	145.1
85°	26.9	37.2	47.5	57.8	68.0	78.5	89.1	99.7	110.4	121.0	128.0
87.5°	14.7	24.9	35.0	45.2	55.3	65.8	76.6	87.4	98.2	109.0	115.9
90°	8.0	18.9	29.8	40.7	51.6	62.8	74.4	85.9	97.5	109.0	116.2
92.5°	17.4	26.3	35.1	44.0	52.8	62.6	73.3	83.9	94.6	105.3	112.1
95°	39.9	43.9	47.8	51.8	55.8	63.2	73.9	84.7	95.5	106.2	113.1
97.5°	72.5	68.7	64.9	61.0	57.2	61.0	72.4	83.8	95.3	106.7	113.3
100°	97.6	87.9	78.1	68.4	58.6	59.4	70.6	81.9	93.2	104.4	111.5
102.5°	124.6	126.8	129.0	131.3	133.5	130.9	123.5	116.0	108.5	101.1	108.3
105°	162.4	170.7	179.0	187.3	195.6	188.2	165.2	142.1	119.1	96.1	103.1
107.5°	206.4	213.0	219.7	226.4	233.0	221.5	191.8	162.1	132.4	102.7	106.9
110°	234.2	239.9	245.7	251.4	257.2	247.4	222.0	196.6	171.2	145.8	139.6



TEST NUMBER: P331297

CATALOG NUMBER: S122DIP-S485D530U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.9	265.8	270.8	275.7	280.7	282.9	282.3	281.8	281.2	280.7	243.7
115°	303.1	306.9	310.7	314.5	318.3	325.3	335.7	346.1	356.4	366.8	318.1
117.5°	340.0	343.4	346.8	350.2	353.6	359.7	368.6	377.5	386.4	395.3	387.3
120°	367.5	370.0	372.4	374.8	377.2	382.7	391.5	400.2	408.9	417.6	423.7
122.5°	390.9	393.0	395.1	397.2	399.3	404.6	413.1	421.7	430.2	438.7	444.0
125°	425.8	427.3	428.8	430.3	431.8	436.3	443.8	451.3	458.9	466.4	471.7
127.5°	458.0	459.5	461.0	462.5	464.0	467.8	473.7	479.6	485.5	491.5	496.8
130°	478.5	480.2	481.9	483.6	485.2	488.5	493.2	498.0	502.7	507.5	512.8
132.5°	499.4	500.8	502.2	503.6	505.0	507.7	511.7	515.6	519.6	523.5	528.5
135°	525.7	527.6	529.5	531.3	533.2	535.4	538.2	540.9	543.6	546.3	550.9
137.5°	553.2	554.5	555.7	557.0	558.3	559.8	561.8	563.7	565.6	567.5	571.7
140°	571.2	571.9	572.7	573.4	574.2	575.4	577.0	578.6	580.2	581.8	585.5
142.5°	586.2	586.8	587.5	588.2	588.9	590.0	591.5	593.0	594.5	596.1	599.1
145°	609.0	608.9	608.8	608.7	608.6	609.5	611.5	613.4	615.4	617.4	619.2
147.5°	629.6	629.1	628.7	628.3	627.8	628.6	630.5	632.5	634.4	636.4	637.1
150°	642.9	642.1	641.3	640.5	639.7	640.2	642.1	643.9	645.8	647.6	648.3
152.5°	654.2	653.3	652.4	651.5	650.6	651.0	652.8	654.6	656.3	658.1	658.8
155°	670.6	669.6	668.5	667.5	666.4	666.6	668.0	669.4	670.8	672.2	672.9
157.5°	683.4	682.6	681.7	680.8	679.9	680.0	680.9	681.9	682.9	683.9	684.6
160°	691.0	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	691.7
162.5°	697.6	696.9	696.2	695.5	694.9	694.8	695.4	696.0	696.6	697.2	698.0
165°	706.6	705.9	705.2	704.5	703.8	703.7	704.0	704.3	704.7	705.0	705.9
167.5°	713.3	712.6	711.9	711.2	710.5	710.3	710.6	711.0	711.3	711.6	712.4
170°	717.0	716.4	715.7	715.0	714.3	714.0	714.3	714.5	714.7	715.0	715.8
172.5°	719.6	718.9	718.2	717.5	716.8	716.5	716.8	717.0	717.2	717.5	718.3
175°	722.8	722.0	721.2	720.4	719.5	719.3	719.5	719.7	719.9	720.2	721.0
177.5°	723.3	722.7	722.0	721.4	720.7	720.4	720.5	720.6	720.7	720.8	721.5
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331297

CATALOG NUMBER: S122DIP-S485D530U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	515.3	515.3	515.3	515.3	515.3	515.3	515.3	515.3
2.5°	513.7	514.3	515.0	515.2	514.9	514.7	514.4	514.1
5°	512.1	513.1	514.1	514.5	514.3	514.2	514.0	513.8
7.5°	509.6	510.8	512.0	512.5	512.4	512.2	512.0	511.9
10°	507.5	508.8	510.2	510.8	510.6	510.4	510.3	510.1
12.5°	503.9	505.3	506.6	507.2	507.0	506.8	506.7	506.5
15°	497.4	498.9	500.4	501.0	500.9	500.7	500.5	500.4
17.5°	489.0	490.6	492.1	492.9	492.9	492.9	492.9	492.9
20°	482.4	484.2	486.0	486.9	486.9	486.9	486.9	486.9
22.5°	475.2	477.0	478.9	479.9	480.2	480.4	480.7	481.0
25°	464.0	466.0	468.0	469.3	469.8	470.3	470.8	471.3
27.5°	451.7	454.2	456.7	458.1	458.5	458.9	459.2	459.6
30°	443.0	445.6	448.3	449.8	450.3	450.8	451.3	451.8
32.5°	433.6	436.6	439.7	441.7	442.6	443.5	444.4	445.3
35°	420.3	424.0	427.6	430.0	431.2	432.3	433.5	434.7
37.5°	406.6	410.7	414.7	417.3	418.6	419.8	421.0	422.3
40°	397.0	401.3	405.6	408.5	410.0	411.5	413.0	414.5
42.5°	387.6	392.3	397.0	400.2	401.6	403.1	404.6	406.1
45°	373.3	378.4	383.5	386.9	388.6	390.3	391.9	393.6
47.5°	358.3	363.7	369.1	372.7	374.5	376.3	378.2	380.0
50°	348.1	353.7	359.4	363.1	365.0	366.8	368.6	370.4
52.5°	337.0	342.8	348.6	352.4	354.4	356.4	358.3	360.3
55°	320.4	326.4	332.3	336.4	338.6	340.7	342.9	345.0
57.5°	302.8	309.2	315.7	320.0	322.2	324.4	326.6	328.8
60°	291.2	297.5	303.8	308.1	310.4	312.8	315.1	317.4
62.5°	278.8	285.5	292.2	296.7	298.9	301.1	303.3	305.5
65°	260.1	266.9	273.7	278.2	280.3	282.5	284.6	286.8
67.5°	241.1	247.9	254.8	259.4	261.6	263.9	266.2	268.4
70°	227.9	235.0	242.1	246.7	248.7	250.7	252.7	254.7
72.5°	215.1	222.1	229.1	233.8	236.1	238.5	240.9	243.3
75°	195.8	202.9	210.0	214.7	216.8	219.0	221.1	223.3
77.5°	176.9	184.0	191.1	195.8	198.1	200.4	202.8	205.1
80°	164.1	171.0	178.0	182.6	185.0	187.3	189.6	191.9
82.5°	152.1	159.1	166.0	170.6	172.8	175.0	177.2	179.4
85°	134.9	141.9	148.9	153.5	155.8	158.2	160.5	162.8
87.5°	122.8	129.7	136.6	141.1	143.3	145.5	147.6	149.8
90°	123.5	130.7	137.9	142.6	144.8	147.1	149.3	151.5
92.5°	118.9	125.7	132.5	137.0	139.1	141.3	143.4	145.5
95°	120.0	126.9	133.8	138.2	140.0	141.9	143.8	145.7
97.5°	119.9	126.5	133.1	137.5	139.6	141.7	143.8	145.9
100°	118.6	125.6	132.7	137.3	139.3	141.4	143.4	145.5
102.5°	115.5	122.7	129.9	134.6	136.8	138.9	141.1	143.2
105°	110.2	117.3	124.4	129.1	131.4	133.7	136.0	138.2
107.5°	111.2	115.5	119.8	123.1	125.4	127.6	129.9	132.2
110°	133.3	127.0	120.7	118.7	121.0	123.3	125.6	127.9



TEST NUMBER: P331297

CATALOG NUMBER: S122DIP-S485D530U835-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	206.7	169.7	132.7	115.3	117.5	119.7	121.9	124.1
115°	269.4	220.7	171.9	144.3	137.8	131.3	124.7	118.2
117.5°	379.2	371.1	363.0	346.1	320.4	294.6	268.9	243.1
120°	429.7	435.7	441.8	437.9	424.1	410.2	396.4	382.6
122.5°	449.4	454.7	460.1	462.0	460.5	459.1	457.6	456.1
125°	477.0	482.3	487.5	491.1	493.0	494.8	496.6	498.5
127.5°	502.1	507.4	512.7	516.1	517.6	519.1	520.7	522.2
130°	518.0	523.3	528.5	531.8	533.0	534.2	535.4	536.6
132.5°	533.4	538.4	543.3	546.4	547.6	548.8	550.0	551.2
135°	555.6	560.2	564.8	567.7	568.8	569.9	571.0	572.1
137.5°	575.9	580.1	584.3	586.7	587.5	588.2	588.9	589.7
140°	589.2	592.9	596.6	598.7	599.1	599.5	599.9	600.3
142.5°	602.2	605.3	608.4	610.0	610.3	610.6	610.9	611.2
145°	621.0	622.8	624.6	625.6	625.9	626.1	626.4	626.6
147.5°	637.8	638.6	639.3	639.6	639.5	639.5	639.4	639.3
150°	649.0	649.7	650.4	650.5	649.9	649.3	648.7	648.2
152.5°	659.5	660.2	660.9	660.8	660.1	659.3	658.5	657.8
155°	673.6	674.3	675.0	674.8	673.9	673.0	672.1	671.1
157.5°	685.4	686.2	687.0	687.0	686.0	685.1	684.2	683.3
160°	692.3	693.0	693.7	693.7	692.9	692.1	691.2	690.4
162.5°	698.8	699.6	700.4	700.3	699.3	698.3	697.3	696.3
165°	706.7	707.5	708.3	708.3	707.5	706.7	705.9	705.0
167.5°	713.2	714.1	714.9	714.8	713.7	712.7	711.6	710.6
170°	716.6	717.4	718.2	718.1	717.0	716.0	715.0	713.9
172.5°	719.1	719.9	720.7	720.6	719.6	718.5	717.5	716.4
175°	721.8	722.6	723.4	723.3	722.1	720.9	719.8	718.6
177.5°	722.1	722.8	723.4	723.3	722.5	721.6	720.8	720.0
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2

(END OF REPORT)