

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331944-927

Luminaire Tested: **S123DIP-S560D1025U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331944-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1025U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4628.4 lumens  
Efficiency: N/A  
Efficacy: 104.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331944-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331944-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	73	68	79	73	67	63	59	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	56	50	44	46	41	37	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	36	31	51	41	34	29	34	29	25	27	23	20	21	19	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7597	7597	7597
5°	7632	7527	7580
10°	7581	7462	7508
15°	7492	7377	7392
20°	7389	7257	7263
25°	7251	7114	7099
30°	7097	6954	6901
35°	6937	6786	6699
40°	6770	6600	6497
45°	6587	6428	6272
50°	6402	6219	6047
55°	6161	6001	5819
60°	5918	5748	5565
65°	5703	5471	5300
70°	5385	5155	4925
75°	4924	4745	4541
80°	4438	4252	4215
85°	3890	3742	3606



TEST NUMBER: P331944-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.5	1.4
10°-20°	187.7	4.1
20°-30°	277.3	6.0
30°-40°	323.9	7.0
40°-50°	325.6	7.0
50°-60°	286.0	6.2
60°-70°	213.1	4.6
70°-80°	121.4	2.6
80°-90°	37.8	0.8
90°-100°	65.6	1.4
100°-110°	196.3	4.2
110°-120°	333.8	7.2
120°-130°	439.1	9.5
130°-140°	493.6	10.7
140°-150°	485.2	10.5
150°-160°	408.4	8.8
160°-170°	271.9	5.9
170°-180°	95.2	2.1
0°-30°	531.5	11.5
0°-40°	855.4	18.5
0°-60°	1467.0	31.7
0°-90°	1839.4	39.7
90°-120°	595.7	12.9
90°-150°	2013.5	43.5
90°-180°	2789.0	60.3
0°-180°	4628.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	706	706	706	706	706	
5°	706	703	697	702	702	67
15°	672	670	662	666	663	189
25°	610	607	599	599	598	281
35°	528	524	516	513	510	330
45°	433	430	422	415	412	334
55°	328	327	320	313	310	294
65°	224	221	215	210	208	221
75°	118	116	114	111	109	127
85°	32	30	30	29	29	35
90°	1	9	19	22	24	5
95°	47	52	58	62	62	52
105°	178	180	187	187	188	191
115°	336	338	337	338	337	332
125°	492	494	493	489	486	438
135°	638	643	642	639	637	492
145°	774	776	778	777	774	483
155°	886	886	887	890	885	408
165°	966	963	963	967	962	272
175°	1004	1001	1001	1005	1000	95
180°	1007	1007	1007	1007	1007	



TEST NUMBER: P331944-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	708.1	707.7	707.3	706.9	706.5	705.6	704.4	703.2	702.1	700.9	702.0
5°	706.3	705.7	705.0	704.3	703.6	702.6	701.1	699.6	698.2	696.6	698.0
7.5°	699.4	698.8	698.1	697.4	696.7	695.6	694.1	692.5	691.0	689.5	690.7
10°	693.6	692.9	692.3	691.6	690.9	689.7	687.9	686.2	684.4	682.7	683.9
12.5°	685.9	685.2	684.7	684.1	683.6	682.5	680.8	679.1	677.6	675.9	676.8
15°	672.3	671.8	671.3	670.7	670.2	669.1	667.3	665.6	663.8	662.0	663.1
17.5°	656.7	656.0	655.3	654.6	653.9	652.7	650.9	649.2	647.5	645.6	646.4
20°	645.1	644.3	643.4	642.6	641.8	640.6	638.8	637.1	635.3	633.5	634.1
22.5°	631.9	631.1	630.3	629.5	628.7	627.4	625.7	623.9	622.2	620.4	620.8
25°	610.5	609.7	608.9	608.1	607.2	605.9	604.2	602.5	600.7	599.0	599.0
27.5°	587.6	586.8	586.0	585.2	584.4	583.0	581.1	579.3	577.4	575.5	575.6
30°	571.0	570.4	569.7	569.0	568.3	567.0	565.1	563.2	561.4	559.5	559.5
32.5°	554.5	553.7	552.7	551.8	551.0	549.8	548.3	546.8	545.4	544.0	543.2
35°	527.9	527.1	526.3	525.5	524.7	523.4	521.7	519.9	518.2	516.4	515.6
37.5°	500.7	499.7	498.7	497.6	496.6	495.3	493.5	491.7	489.9	488.1	487.2
40°	481.8	481.0	480.2	479.4	478.6	477.2	475.3	473.5	471.6	469.7	468.6
42.5°	462.9	462.0	461.1	460.1	459.2	457.8	455.9	454.1	452.2	450.3	449.2
45°	432.7	432.1	431.6	431.0	430.5	429.4	427.6	425.9	424.1	422.3	420.7
47.5°	402.7	401.9	401.2	400.4	399.6	398.3	396.7	395.1	393.4	391.7	390.1
50°	382.3	381.6	381.0	380.2	379.6	378.4	376.6	374.9	373.1	371.4	369.9
52.5°	360.9	360.4	360.0	359.6	359.1	357.9	356.1	354.3	352.4	350.5	349.3
55°	328.3	328.1	328.0	327.9	327.7	326.8	325.0	323.3	321.5	319.8	318.3
57.5°	297.2	296.8	296.3	295.9	295.4	294.5	293.0	291.7	290.3	288.8	287.6
60°	274.9	274.7	274.6	274.5	274.3	273.5	271.9	270.2	268.6	267.0	265.8
62.5°	255.0	254.6	254.3	254.0	253.6	252.6	251.0	249.4	247.7	246.1	244.9
65°	223.9	223.2	222.6	221.9	221.3	220.2	218.9	217.5	216.2	214.8	213.7
67.5°	191.0	190.4	189.8	189.3	188.6	187.8	186.8	185.8	184.7	183.8	182.8
70°	171.1	170.3	169.5	168.7	167.9	167.1	166.3	165.5	164.6	163.8	162.9
72.5°	150.3	149.6	149.1	148.5	147.9	147.1	146.2	145.3	144.3	143.5	142.6
75°	118.4	117.8	117.2	116.7	116.2	115.7	115.3	114.9	114.5	114.1	113.4
77.5°	90.1	89.8	89.4	89.2	88.9	88.5	88.0	87.5	87.0	86.5	86.1
80°	71.6	71.2	70.8	70.4	69.9	69.6	69.4	69.1	68.8	68.6	68.4
82.5°	53.6	53.6	53.5	53.4	53.3	53.2	53.2	53.2	53.1	53.1	52.8
85°	31.5	31.3	31.1	30.7	30.5	30.3	30.3	30.3	30.3	30.3	30.1
87.5°	12.8	12.8	12.8	12.8	12.9	13.1	13.5	13.8	14.1	14.5	14.5
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6
92.5°	19.2	20.4	21.5	22.7	23.9	25.2	26.5	27.7	29.1	30.3	30.9
95°	46.7	47.8	49.1	50.4	51.6	52.9	54.3	55.7	57.1	58.5	59.3
97.5°	82.9	83.8	84.7	85.6	86.5	87.5	88.5	89.5	90.5	91.6	92.4
100°	107.6	108.6	109.6	110.7	111.8	112.7	113.6	114.5	115.3	116.2	116.8
102.5°	136.0	136.7	137.3	137.9	138.6	139.4	140.6	141.7	142.9	144.1	144.6
105°	177.9	178.2	178.6	179.0	179.4	180.3	181.9	183.5	185.1	186.6	186.6
107.5°	226.6	226.9	227.0	227.3	227.5	227.9	228.5	229.2	229.8	230.4	231.0
110°	257.0	257.4	257.7	258.0	258.4	258.7	259.1	259.4	259.8	260.2	260.9



TEST NUMBER: P331944-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.6	288.8	289.1	289.2	289.5	289.6	289.7	289.8	289.9	289.9	290.7
115°	336.0	336.6	337.2	337.6	338.2	338.3	337.9	337.5	337.2	336.8	337.1
117.5°	383.8	384.2	384.5	384.9	385.2	385.2	384.8	384.3	383.8	383.3	383.3
120°	413.6	414.6	415.7	416.8	417.8	417.9	417.0	416.1	415.3	414.4	414.2
122.5°	444.6	445.4	446.1	446.9	447.7	447.8	447.3	446.9	446.5	446.0	445.5
125°	491.9	492.4	492.9	493.5	493.9	494.1	493.7	493.4	493.0	492.7	491.9
127.5°	535.5	536.6	537.7	538.8	540.0	540.3	540.0	539.6	539.2	538.8	537.8
130°	564.6	566.0	567.4	568.8	570.2	570.7	570.1	569.6	569.1	568.5	567.8
132.5°	593.7	595.1	596.5	597.9	599.4	599.8	599.4	599.0	598.7	598.3	597.5
135°	638.2	639.2	640.2	641.3	642.4	642.8	642.6	642.5	642.3	642.1	641.4
137.5°	679.3	680.2	681.0	681.9	682.8	683.4	683.9	684.4	684.8	685.2	684.5
140°	707.7	708.6	709.5	710.3	711.2	711.8	711.9	712.1	712.3	712.5	712.3
142.5°	733.6	734.5	735.5	736.3	737.2	737.8	738.1	738.4	738.7	739.0	738.9
145°	774.1	774.5	774.8	775.2	775.5	776.0	776.5	777.1	777.6	778.1	777.9
147.5°	809.6	810.2	810.9	811.5	812.1	812.7	813.2	813.7	814.1	814.7	814.7
150°	834.2	834.6	835.0	835.3	835.7	836.0	836.4	836.7	837.1	837.4	837.4
152.5°	854.5	855.0	855.5	856.0	856.4	856.8	857.1	857.2	857.5	857.7	857.9
155°	886.5	886.5	886.5	886.5	886.5	886.5	886.7	886.8	887.1	887.2	888.0
157.5°	913.6	913.5	913.2	913.0	912.8	912.8	912.9	913.1	913.2	913.3	914.1
160°	930.7	930.3	930.0	929.7	929.3	929.2	929.2	929.2	929.2	929.2	930.0
162.5°	945.9	945.4	944.9	944.4	944.0	943.8	943.9	944.0	944.2	944.4	945.2
165°	965.5	965.0	964.5	963.9	963.5	963.1	963.1	963.1	963.1	963.1	964.2
167.5°	981.2	980.5	979.8	979.1	978.3	978.1	978.3	978.3	978.5	978.7	979.8
170°	990.1	989.4	988.6	987.9	987.2	986.9	986.9	986.9	986.9	986.9	988.1
172.5°	997.0	996.3	995.6	994.9	994.2	993.8	993.8	993.8	993.8	993.8	994.9
175°	1004.2	1003.5	1002.8	1002.2	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2
177.5°	1007.3	1006.7	1006.2	1005.6	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331944-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	703.1	704.1	705.2	705.7	705.6	705.4	705.4	705.3
5°	699.3	700.7	702.0	702.6	702.3	702.0	701.8	701.5
7.5°	691.9	693.1	694.3	694.8	694.7	694.5	694.3	694.2
10°	685.1	686.3	687.5	688.0	687.8	687.5	687.2	686.9
12.5°	677.6	678.6	679.5	679.8	679.6	679.5	679.3	679.1
15°	664.2	665.3	666.4	666.5	665.7	664.9	664.1	663.3
17.5°	647.2	647.9	648.7	648.9	648.6	648.3	648.0	647.7
20°	634.6	635.2	635.6	635.7	635.3	634.9	634.5	634.1
22.5°	621.3	621.7	622.2	622.1	621.6	621.1	620.6	620.0
25°	599.2	599.4	599.4	599.4	599.0	598.6	598.1	597.7
27.5°	575.8	575.8	575.9	575.8	575.2	574.7	574.2	573.7
30°	559.5	559.5	559.5	559.0	558.1	557.1	556.2	555.2
32.5°	542.5	541.7	540.9	540.3	539.8	539.3	538.8	538.3
35°	514.8	514.0	513.2	512.5	511.7	511.1	510.4	509.8
37.5°	486.2	485.2	484.3	483.5	483.2	482.7	482.3	481.8
40°	467.5	466.4	465.4	464.5	464.0	463.5	463.0	462.4
42.5°	448.1	447.0	445.9	445.1	444.6	444.1	443.5	443.0
45°	419.1	417.5	415.9	414.7	414.1	413.4	412.7	412.0
47.5°	388.6	387.0	385.4	384.3	383.7	383.1	382.5	381.9
50°	368.4	366.9	365.4	364.3	363.5	362.7	361.9	361.1
52.5°	348.0	346.7	345.5	344.4	343.6	342.8	342.0	341.2
55°	316.8	315.4	313.9	312.8	312.1	311.4	310.8	310.1
57.5°	286.2	284.9	283.6	282.5	281.7	281.0	280.2	279.4
60°	264.6	263.4	262.1	261.2	260.5	259.8	259.2	258.5
62.5°	243.7	242.5	241.3	240.4	240.0	239.6	239.1	238.6
65°	212.6	211.6	210.5	209.8	209.4	209.0	208.6	208.1
67.5°	181.9	180.9	180.0	179.2	178.6	178.1	177.5	177.0
70°	161.9	161.1	160.1	159.2	158.6	157.9	157.2	156.5
72.5°	141.8	140.9	140.1	139.5	139.2	138.8	138.5	138.1
75°	112.7	112.1	111.4	110.8	110.4	110.0	109.6	109.2
77.5°	85.6	85.2	84.7	84.4	84.4	84.4	84.4	84.4
80°	68.3	68.1	68.0	68.0	68.0	68.0	68.0	68.0
82.5°	52.5	52.3	52.0	51.9	51.8	51.7	51.6	51.5
85°	29.8	29.5	29.2	29.2	29.2	29.2	29.2	29.2
87.5°	14.6	14.6	14.6	14.7	14.7	14.8	14.9	15.0
90°	20.4	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	31.5	32.1	32.6	32.8	32.6	32.4	32.2	31.9
95°	59.9	60.6	61.3	61.7	61.7	61.7	61.7	61.7
97.5°	93.2	94.0	94.8	95.1	95.1	95.1	95.0	94.9
100°	117.3	117.8	118.4	118.8	119.1	119.5	119.9	120.2
102.5°	145.1	145.7	146.2	146.4	146.3	146.2	146.2	146.2
105°	186.6	186.6	186.6	186.8	187.1	187.5	187.8	188.2
107.5°	231.6	232.1	232.7	232.8	232.7	232.4	232.2	232.0
110°	261.6	262.3	263.0	263.2	262.8	262.4	262.1	261.7





TEST NUMBER: P331944-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.6	292.4	293.3	293.7	293.6	293.5	293.4	293.3
115°	337.2	337.4	337.5	337.5	337.4	337.2	337.1	336.8
117.5°	383.3	383.3	383.3	382.9	382.5	382.0	381.5	381.0
120°	414.0	413.8	413.7	413.4	413.0	412.7	412.3	412.0
122.5°	445.0	444.7	444.2	443.7	443.2	442.7	442.2	441.7
125°	491.2	490.5	489.8	489.1	488.5	487.7	487.0	486.3
127.5°	536.9	535.9	534.9	534.0	533.2	532.3	531.6	530.8
130°	567.1	566.4	565.8	564.7	563.6	562.3	561.1	559.8
132.5°	596.6	595.8	594.9	594.1	593.1	592.2	591.2	590.3
135°	640.7	640.0	639.3	638.7	638.4	638.0	637.7	637.4
137.5°	683.8	683.1	682.3	681.6	681.0	680.2	679.6	679.0
140°	712.1	711.9	711.8	711.1	709.9	708.6	707.4	706.2
142.5°	738.7	738.6	738.3	737.8	736.8	735.9	734.9	734.0
145°	777.8	777.6	777.4	777.0	776.3	775.5	774.8	774.1
147.5°	814.7	814.7	814.7	814.1	813.1	812.0	811.0	809.9
150°	837.4	837.4	837.4	836.9	835.8	834.8	833.7	832.7
152.5°	858.3	858.5	858.8	858.5	857.5	856.7	855.7	854.8
155°	888.7	889.4	890.0	889.8	888.6	887.3	886.1	884.9
157.5°	914.8	915.5	916.3	916.2	915.2	914.2	913.2	912.2
160°	930.9	931.8	932.6	932.7	932.1	931.4	930.7	929.9
162.5°	946.1	947.0	947.8	947.7	946.6	945.5	944.4	943.3
165°	965.3	966.3	967.3	967.3	966.1	964.8	963.6	962.3
167.5°	980.8	981.9	983.0	983.0	981.9	980.8	979.8	978.7
170°	989.4	990.5	991.8	991.8	990.5	989.4	988.1	986.9
172.5°	996.0	997.1	998.1	998.1	996.9	995.7	994.4	993.2
175°	1003.2	1004.2	1005.4	1005.2	1004.0	1002.7	1001.6	1000.3
177.5°	1006.5	1007.3	1008.1	1008.1	1007.1	1006.1	1005.1	1004.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6

(END OF REPORT)