

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831464

Luminaire Tested: S123DIP-S560D1025U927-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831464
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U927-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4996.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	48	48	48	41	
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	41	41	41	36	
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	36	36	36	36	30	
3	81	72	65	59	73	66	60	55	54	50	47	44	41	39	35	33	31	31	31	31	26	
4	74	64	56	50	67	59	52	47	49	44	40	40	36	33	31	29	27	27	27	27	23	
5	68	57	49	44	62	52	46	41	44	39	35	36	32	29	28	26	24	24	24	24	21	
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	23	21	21	21	21	18	
7	58	47	39	34	53	43	36	32	36	31	27	30	26	23	24	21	19	19	19	19	17	
8	54	42	35	30	49	39	33	28	33	28	25	28	24	21	22	20	18	18	18	18	15	
9	51	39	32	27	46	36	30	25	31	26	22	25	22	19	21	18	16	16	16	16	14	
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	19	17	15	15	15	15	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	13764	13764	13764	13764	13764
5°	17407	16429	13887	11191	10283
10°	17575	18107	13795	8921	7795
15°	13238	16811	13700	7554	6593
20°	9223	13604	13526	6606	5987
25°	7033	10461	13227	6078	5616
30°	6084	8311	12751	5705	5317
35°	5645	7017	12202	5435	5106
40°	5344	6295	11431	5178	5036
45°	5167	5826	10450	4976	5004
50°	5077	5456	9291	4794	4978
55°	4889	5183	8150	4620	4999
60°	4712	4893	7025	4458	4917
65°	4429	4618	6059	4284	4821
70°	4088	4268	5155	3997	4538
75°	3701	3826	4417	3714	4146
80°	3050	3347	3496	3236	3496
85°	2421	2717	2569	2754	2779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 11931 cd/sqm



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	2.4
10°-20°	300.7	6.0
20°-30°	356.1	7.1
30°-40°	358.0	7.2
40°-50°	328.5	6.6
50°-60°	271.1	5.4
60°-70°	191.8	3.8
70°-80°	102.4	2.0
80°-90°	28.1	0.6
90°-100°	212.0	4.2
100°-110°	620.6	12.4
110°-120°	606.0	12.1
120°-130°	482.6	9.7
130°-140°	380.8	7.6
140°-150°	284.1	5.7
150°-160°	198.1	4.0
160°-170°	116.4	2.3
170°-180°	37.8	0.8
0°-30°	777.7	15.6
0°-40°	1135.7	22.7
0°-60°	1735.4	34.7
0°-90°	2057.7	41.2
90°-120°	1438.6	28.8
90°-150°	2586.1	51.8
90°-180°	2938.0	58.8
0°-180°	4996.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1279	1279	1279	1279	1279	
5°	1611	1520	1285	1036	952	153
15°	1188	1509	1229	678	592	328
25°	592	881	1114	512	473	279
35°	430	534	929	414	389	270
45°	339	383	686	327	329	263
55°	260	276	434	246	266	233
65°	174	181	238	168	189	173
75°	89	92	106	89	100	94
85°	20	22	21	22	22	22
90°	23	20	2	20	23	13
95°	92	469	27	469	92	149
105°	1006	636	92	636	1006	1003
115°	1223	486	162	486	1223	1193
125°	965	454	225	454	965	873
135°	782	448	264	448	782	607
145°	611	442	301	442	611	388
155°	507	428	342	428	507	236
165°	442	410	374	410	442	126
175°	398	393	390	393	398	39
180°	391	391	391	391	391	



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7
2.5°	1441.3	1439.8	1438.3	1430.9	1423.5	1419.9	1416.3	1405.7	1395.0	1383.1	1371.2
5°	1611.0	1615.1	1619.3	1614.5	1609.8	1595.2	1580.7	1561.4	1542.1	1520.5	1498.8
7.5°	1689.3	1691.6	1694.0	1691.1	1688.1	1684.2	1680.4	1663.2	1646.0	1623.7	1601.5
10°	1608.0	1613.3	1618.7	1630.2	1641.8	1654.9	1667.9	1665.5	1663.2	1656.6	1650.1
12.5°	1429.4	1435.9	1442.4	1465.6	1488.7	1518.4	1548.1	1573.6	1599.1	1616.9	1634.7
15°	1187.9	1206.0	1224.1	1245.2	1266.2	1309.8	1353.4	1407.1	1460.8	1508.6	1556.4
17.5°	978.4	985.3	992.1	1014.6	1037.2	1092.1	1147.0	1209.0	1271.0	1350.2	1429.4
20°	805.2	811.4	817.6	847.3	877.0	920.0	963.0	1032.7	1102.5	1187.6	1272.7
22.5°	676.4	686.2	696.0	712.6	729.2	770.5	811.7	873.7	935.7	1029.8	1123.8
25°	592.2	599.3	606.4	616.5	626.6	659.5	692.4	743.5	794.5	880.8	967.2
27.5°	534.6	537.6	540.5	550.6	560.7	582.1	603.4	647.3	691.3	764.5	837.8
30°	489.5	491.6	493.7	502.6	511.5	526.0	540.5	572.3	604.0	668.7	733.4
32.5°	458.1	459.6	461.0	467.9	474.7	485.1	495.4	518.6	541.7	595.1	648.5
35°	429.6	430.5	431.4	436.4	441.5	449.2	456.9	474.4	491.9	534.0	576.1
37.5°	404.7	405.9	407.0	410.0	413.0	419.8	426.6	440.6	454.5	486.8	519.2
40°	380.3	382.4	384.5	386.6	388.6	394.3	399.9	410.6	421.3	448.0	474.7
42.5°	359.6	361.6	363.7	364.6	365.5	368.8	372.0	381.8	391.6	411.5	431.4
45°	339.4	340.3	341.2	342.1	343.0	345.6	348.3	356.9	365.5	382.7	399.9
47.5°	321.0	321.0	321.0	321.6	322.2	324.6	326.9	333.2	339.4	352.7	366.1
50°	303.2	303.2	303.2	302.3	301.4	302.9	304.4	309.1	313.9	325.8	337.6
52.5°	281.8	281.8	281.8	282.1	282.4	282.4	282.4	286.6	290.7	301.4	312.1
55°	260.5	261.7	262.9	262.0	261.1	261.7	262.3	264.9	267.6	276.2	284.8
57.5°	239.1	239.7	240.3	240.0	239.7	240.0	240.3	242.7	245.1	251.6	258.1
60°	218.9	218.9	218.9	218.4	217.8	218.4	218.9	220.1	221.3	227.3	233.2
62.5°	196.4	196.7	197.0	197.3	197.6	197.0	196.4	197.9	199.4	203.8	208.3
65°	173.9	174.1	174.4	175.3	176.2	175.6	175.0	176.5	178.0	181.3	184.5
67.5°	153.7	153.1	152.5	152.8	153.1	154.0	154.9	155.2	155.5	159.0	162.6
70°	129.9	130.5	131.1	130.8	130.5	130.8	131.1	132.0	132.9	135.6	138.3
72.5°	108.6	108.9	109.2	109.2	109.2	109.8	110.4	111.3	112.1	113.6	115.1
75°	89.0	89.0	89.0	89.6	90.2	90.5	90.8	90.8	90.8	92.0	93.2
77.5°	67.6	69.1	70.6	70.3	70.0	70.6	71.2	72.1	73.0	73.6	74.2
80°	49.2	49.2	49.2	49.5	49.8	50.7	51.6	52.2	52.8	54.0	55.2
82.5°	31.4	31.7	32.0	32.9	33.8	34.4	35.0	35.9	36.8	36.8	36.8
85°	19.6	19.0	18.4	19.0	19.6	20.2	20.8	21.1	21.4	22.0	22.5
87.5°	9.5	9.5	9.5	9.5	9.5	9.8	10.1	10.1	10.1	10.1	10.1
90°	22.9	23.7	22.9	22.1	22.9	21.3	20.6	19.8	19.0	19.8	17.4
92.5°	41.9	43.5	42.7	45.9	47.4	53.0	60.9	78.3	109.9	147.1	162.9
95°	91.7	94.9	100.4	107.5	122.6	151.0	192.9	284.7	380.3	468.9	417.5
97.5°	188.2	196.9	215.9	245.9	298.9	389.0	493.4	653.9	745.7	721.2	538.5
100°	495.8	495.0	525.8	583.6	663.4	775.7	868.2	932.3	904.6	748.8	506.1
102.5°	785.2	808.1	832.6	875.3	933.1	994.0	1038.2	1024.8	912.5	697.4	458.6
105°	1005.8	1009.8	1035.1	1065.1	1101.5	1122.1	1107.0	1028.0	862.7	635.8	421.5
107.5°	1149.7	1158.4	1168.7	1182.9	1187.7	1166.3	1104.7	980.5	791.5	581.2	394.6
110°	1232.0	1233.6	1235.1	1228.8	1206.7	1151.3	1051.7	906.2	725.1	536.1	380.3



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1248.6	1247.8	1239.9	1216.9	1171.9	1096.8	982.1	832.6	667.4	506.1	372.4
115°	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4	623.1	486.3	371.6
117.5°	1167.9	1162.4	1138.7	1099.9	1038.2	948.9	842.1	720.4	593.8	472.9	372.4
120°	1095.2	1090.4	1071.5	1027.2	964.7	884.8	789.9	683.2	571.7	464.2	375.6
122.5°	1027.2	1020.8	999.5	960.7	907.0	834.2	748.0	653.9	553.5	458.6	381.1
125°	964.7	959.2	939.4	904.6	854.0	790.7	714.8	628.6	538.5	453.9	386.7
127.5°	910.9	906.2	888.0	858.0	812.1	753.6	684.0	605.7	524.3	451.5	393.0
130°	866.6	860.3	843.7	815.3	773.3	719.6	655.5	584.4	513.2	449.1	399.3
132.5°	823.2	819.2	805.0	776.5	737.8	687.2	628.6	564.6	502.9	448.3	404.1
135°	782.0	776.5	762.3	738.5	699.8	654.7	603.3	547.2	494.2	447.6	408.8
137.5°	738.5	733.8	721.9	697.4	664.2	623.9	578.0	530.6	486.3	446.0	412.0
140°	692.7	693.5	680.8	658.7	628.6	594.6	556.7	516.4	479.2	445.2	415.1
142.5°	650.0	650.8	639.7	620.7	596.2	567.8	536.1	502.9	472.9	443.6	417.5
145°	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.6	467.3	442.0	418.3
147.5°	578.0	577.2	570.9	559.1	543.2	526.6	505.3	483.9	461.8	439.7	418.3
150°	549.6	549.6	544.8	536.1	524.3	509.2	492.6	474.4	456.3	436.5	418.3
152.5°	525.8	525.8	523.5	515.6	506.9	495.0	480.8	465.7	449.9	432.5	415.9
155°	506.9	506.1	504.5	498.2	491.0	481.6	469.7	457.0	443.6	427.8	414.3
157.5°	488.7	488.7	487.1	482.4	476.0	468.1	458.6	447.6	436.5	423.8	412.0
160°	471.3	472.1	472.1	467.3	461.8	456.3	448.3	439.7	429.4	419.1	410.4
162.5°	455.5	456.3	456.3	452.3	449.1	444.4	437.3	430.2	422.3	414.3	407.2
165°	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.3	415.9	409.6	404.1
167.5°	428.6	428.6	429.4	427.0	425.4	422.3	419.1	415.1	409.6	404.9	400.9
170°	416.7	416.7	417.5	415.9	415.1	413.6	410.4	408.0	404.1	400.1	397.7
172.5°	405.6	406.4	408.0	406.4	406.4	405.6	403.3	401.7	398.5	396.2	395.4
175°	397.7	398.5	399.3	398.5	398.5	398.5	397.0	396.2	394.6	393.0	393.0
177.5°	392.2	392.2	393.8	393.0	393.8	393.8	393.0	392.2	391.4	390.6	391.4
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7
2.5°	1367.7	1364.1	1351.1	1338.0	1323.2	1308.3	1297.4	1286.4	1270.1	1253.8	1240.4
5°	1482.2	1465.6	1438.0	1410.4	1373.0	1335.6	1310.4	1285.2	1251.4	1217.6	1190.6
7.5°	1573.0	1544.5	1505.9	1467.4	1418.4	1369.5	1323.2	1276.9	1225.3	1173.7	1131.5
10°	1630.8	1611.5	1567.0	1522.5	1457.0	1391.4	1326.7	1262.1	1195.6	1129.2	1073.4
12.5°	1636.5	1638.2	1597.3	1556.4	1482.2	1408.0	1329.4	1250.8	1167.1	1083.5	1018.5
15°	1586.9	1617.5	1594.9	1572.4	1497.6	1422.9	1326.1	1229.4	1133.0	1036.6	961.5
17.5°	1495.0	1560.5	1563.8	1567.0	1492.3	1417.5	1310.4	1203.3	1094.1	985.0	906.1
20°	1369.5	1466.2	1499.4	1532.6	1471.8	1411.0	1295.9	1180.8	1058.5	936.3	853.5
22.5°	1241.3	1358.8	1419.6	1480.4	1435.3	1390.2	1267.7	1145.2	1016.1	887.1	803.1
25°	1095.3	1223.5	1316.9	1410.4	1382.8	1355.2	1234.5	1113.7	976.4	839.0	753.3
27.5°	968.1	1098.3	1211.0	1323.8	1317.8	1311.9	1192.0	1072.2	931.6	790.9	708.2
30°	854.7	976.1	1102.2	1228.2	1242.8	1257.3	1141.6	1025.9	885.0	744.1	664.3
32.5°	754.4	860.4	995.6	1130.9	1159.4	1187.9	1083.5	979.0	839.6	700.2	623.3
35°	672.3	768.4	903.7	1039.0	1074.6	1110.2	1019.4	928.6	792.7	656.8	583.6
37.5°	599.6	680.0	812.0	944.0	987.6	1031.2	950.0	868.7	741.4	614.1	546.8
40°	539.4	604.0	725.4	846.7	897.1	947.6	880.5	813.5	692.7	572.0	510.0
42.5°	488.9	546.5	656.5	766.6	815.0	863.3	806.7	750.0	642.6	535.2	478.5
45°	445.9	491.9	591.9	691.8	737.8	783.8	735.2	686.5	591.9	497.2	444.4
47.5°	405.6	445.0	530.5	615.9	656.8	697.8	659.8	621.8	541.7	461.6	413.9
50°	369.4	401.1	475.9	550.6	586.2	621.8	588.3	554.8	488.9	423.1	381.5
52.5°	337.9	363.7	426.3	488.9	519.5	550.0	521.3	492.5	440.3	388.1	351.9
55°	306.8	328.7	383.0	437.3	458.1	478.8	456.6	434.3	392.2	350.1	319.5
57.5°	277.7	297.3	341.8	386.3	402.3	418.3	398.1	378.0	346.2	314.5	289.0
60°	249.2	265.2	302.3	339.4	349.2	359.0	342.7	326.3	304.1	281.8	259.0
62.5°	222.8	237.3	264.9	292.5	299.0	305.6	293.1	280.7	263.7	246.8	229.0
65°	195.5	206.5	229.0	251.6	255.7	259.9	248.9	237.9	225.2	212.4	199.4
67.5°	170.3	178.0	196.4	214.8	215.1	215.4	206.5	197.6	190.5	183.3	173.0
70°	145.7	153.1	165.2	177.4	177.7	178.0	170.9	163.8	158.4	153.1	145.4
72.5°	120.5	125.8	135.0	144.2	143.6	143.0	138.5	134.1	129.9	125.8	120.2
75°	97.6	102.1	108.3	114.5	112.7	111.0	108.6	106.2	102.7	99.1	95.5
77.5°	76.8	79.5	83.1	86.6	85.4	84.3	82.2	80.1	77.4	74.8	73.3
80°	56.4	57.6	59.9	62.3	61.7	61.1	58.7	56.4	55.8	55.2	53.1
82.5°	38.3	39.8	40.3	40.9	40.6	40.3	38.6	36.8	36.2	35.6	35.3
85°	22.8	23.1	23.4	23.7	22.8	22.0	21.4	20.8	20.8	20.8	20.5
87.5°	10.4	10.7	10.7	10.7	10.4	10.1	9.5	8.9	9.2	9.5	9.5
90°	15.0	12.7	10.3	8.7	7.1	4.7	3.2	1.6	3.2	4.7	7.1
92.5°	121.8	79.9	54.6	40.3	32.4	25.3	17.4	11.9	17.4	25.3	32.4
95°	287.8	170.0	102.8	72.0	51.4	38.0	29.3	26.9	29.3	38.0	51.4
97.5°	320.2	183.5	117.0	83.0	62.5	50.6	43.5	42.7	43.5	50.6	62.5
100°	298.1	181.1	125.7	94.9	75.9	64.8	59.3	58.5	59.3	64.8	75.9
102.5°	279.1	184.2	136.0	108.3	91.7	81.4	76.7	75.1	76.7	81.4	91.7
105°	272.0	190.6	147.9	123.4	108.3	98.8	94.1	91.7	94.1	98.8	108.3
107.5°	270.4	200.8	162.9	140.0	125.7	116.2	111.5	109.1	111.5	116.2	125.7
110°	274.4	214.3	178.7	156.6	143.1	134.4	130.5	128.1	130.5	134.4	143.1



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	282.3	227.7	195.3	174.0	160.5	151.8	147.9	145.5	147.9	151.8	160.5
115°	291.0	242.8	212.7	191.4	177.9	170.0	165.3	162.1	165.3	170.0	177.9
117.5°	302.1	258.6	228.5	208.8	193.7	186.6	182.7	178.7	182.7	186.6	193.7
120°	314.7	273.6	245.1	225.4	210.3	202.4	198.5	196.1	198.5	202.4	210.3
122.5°	326.6	289.4	261.7	240.4	226.2	217.5	213.5	211.1	213.5	217.5	226.2
125°	339.2	304.4	276.8	255.4	240.4	231.7	226.9	225.4	226.9	231.7	240.4
127.5°	349.5	317.9	291.0	269.6	253.0	244.3	238.8	236.4	238.8	244.3	253.0
130°	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7	249.1	256.2	265.7
132.5°	369.3	340.0	314.7	294.2	277.5	265.7	257.8	254.6	257.8	265.7	277.5
135°	377.2	350.3	325.8	304.4	287.8	276.0	267.3	264.1	267.3	276.0	287.8
137.5°	383.5	357.4	333.7	313.9	297.3	284.7	276.0	272.8	276.0	284.7	297.3
140°	388.3	364.5	341.6	321.8	306.0	293.4	285.5	281.5	285.5	293.4	306.0
142.5°	393.0	370.1	347.9	329.7	313.9	302.9	294.2	291.0	294.2	302.9	313.9
145°	396.2	374.8	354.3	336.1	322.6	310.8	303.6	301.3	303.6	310.8	322.6
147.5°	398.5	378.8	359.8	344.0	330.5	320.2	313.1	311.6	313.1	320.2	330.5
150°	399.3	382.7	364.5	350.3	339.2	328.9	322.6	321.8	322.6	328.9	339.2
152.5°	400.9	385.1	370.1	356.6	347.1	338.4	332.1	332.1	332.1	338.4	347.1
155°	400.9	388.3	374.8	363.7	355.0	347.1	342.4	342.4	342.4	347.1	355.0
157.5°	401.7	389.8	378.8	370.1	362.2	355.0	351.1	350.3	351.1	355.0	362.2
160°	401.7	392.2	382.7	374.8	369.3	362.9	359.8	359.8	359.8	362.9	369.3
162.5°	400.9	393.0	385.1	378.8	374.0	369.3	366.9	366.9	366.9	369.3	374.0
165°	399.3	393.8	387.5	381.9	378.8	374.8	373.2	374.0	373.2	374.8	378.8
167.5°	398.5	393.8	389.0	385.1	382.7	379.6	378.8	379.6	378.8	379.6	382.7
170°	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3	382.7	383.5	385.9
172.5°	395.4	393.0	389.8	389.0	388.3	386.7	386.7	387.5	386.7	386.7	388.3
175°	393.8	392.2	390.6	389.8	389.8	388.3	389.0	389.8	389.0	388.3	389.8
177.5°	393.0	391.4	390.6	390.6	390.6	389.8	390.6	391.4	390.6	389.8	390.6
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7	1278.7
2.5°	1227.1	1215.5	1203.9	1195.0	1186.1	1171.0	1155.9	1152.3	1148.7	1143.7	1138.6
5°	1163.6	1135.1	1106.6	1081.1	1055.6	1035.7	1015.8	1002.8	989.7	980.2	970.7
7.5°	1089.4	1046.7	1004.0	973.7	943.4	914.7	885.9	876.7	867.5	855.0	842.6
10°	1017.6	970.4	923.3	883.8	844.3	816.2	788.0	776.7	765.4	749.7	734.0
12.5°	953.5	901.9	850.3	810.5	770.8	743.5	716.2	699.9	683.5	674.6	665.7
15°	886.5	831.3	776.1	739.3	702.5	677.9	653.3	639.0	624.8	616.2	607.6
17.5°	827.1	772.5	718.0	682.7	647.3	624.8	602.3	589.8	577.3	570.8	564.3
20°	770.8	717.4	664.0	629.5	595.1	576.7	558.3	550.3	542.3	537.0	531.6
22.5°	719.1	666.6	614.1	584.7	555.4	540.5	525.7	520.1	514.4	510.0	505.5
25°	667.5	620.6	573.8	548.9	523.9	511.8	499.6	494.0	488.3	483.9	479.4
27.5°	625.4	580.6	535.8	514.4	493.1	483.6	474.1	469.6	465.2	461.0	456.9
30°	584.5	544.4	504.4	486.0	467.6	459.0	450.4	445.9	441.5	437.6	433.7
32.5°	546.5	512.1	477.6	460.7	443.8	436.7	429.6	424.2	418.9	415.9	413.0
35°	510.3	479.4	448.6	434.6	420.7	413.6	406.4	402.0	397.5	395.2	392.8
37.5°	479.4	451.8	424.2	410.9	397.5	390.7	383.9	380.0	376.2	375.3	374.4
40°	448.0	424.2	400.5	387.5	374.4	368.5	362.5	360.2	357.8	357.2	356.6
42.5°	421.9	398.7	375.6	363.7	351.9	346.8	341.8	340.6	339.4	340.3	341.2
45°	391.6	372.3	353.0	342.1	331.1	326.9	322.8	321.9	321.0	322.8	324.6
47.5°	366.1	348.3	330.5	320.1	309.7	306.8	303.8	303.5	303.2	305.6	308.0
50°	340.0	322.8	305.6	297.3	289.0	286.3	283.6	284.5	285.4	289.3	293.1
52.5°	315.7	299.6	283.6	275.9	268.2	266.4	264.6	266.7	268.8	272.9	277.1
55°	289.0	274.4	259.9	254.0	248.0	246.2	244.5	248.6	252.8	256.6	260.5
57.5°	263.4	250.7	237.9	232.6	227.3	227.0	226.7	230.5	234.4	238.5	242.7
60°	236.2	225.5	214.8	210.6	206.5	207.1	207.7	212.1	216.6	219.8	223.1
62.5°	211.2	202.3	193.4	189.6	185.7	187.2	188.7	193.1	197.6	201.4	205.3
65°	186.3	178.9	171.5	168.8	166.1	168.2	170.3	174.1	178.0	180.7	183.3
67.5°	162.6	156.3	150.1	148.0	146.0	148.0	150.1	154.0	157.8	160.5	163.2
70°	137.7	132.6	127.6	126.1	124.6	127.0	129.4	132.6	135.9	138.5	141.2
72.5°	114.5	110.7	106.8	106.5	106.2	108.3	110.4	113.6	116.9	118.7	120.5
75°	92.0	89.9	87.8	87.5	87.2	89.3	91.4	93.2	94.9	96.4	97.9
77.5°	71.8	70.0	68.2	68.5	68.8	70.3	71.8	73.6	75.4	76.2	77.1
80°	51.0	50.4	49.8	50.4	51.0	52.2	53.4	54.6	55.8	56.4	57.0
82.5°	35.0	34.4	33.8	34.7	35.6	36.5	37.4	38.3	39.2	39.5	39.8
85°	20.2	21.1	22.0	22.0	22.0	22.3	22.5	22.8	23.1	22.8	22.5
87.5°	9.5	9.8	10.1	10.1	10.1	10.4	10.7	10.7	10.7	10.4	10.1
90°	8.7	10.3	12.7	15.0	17.4	19.8	19.0	19.8	20.6	21.3	22.9
92.5°	40.3	54.6	79.9	121.8	162.9	147.1	109.9	78.3	60.9	53.0	47.4
95°	72.0	102.8	170.0	287.8	417.5	468.9	380.3	284.7	192.9	151.0	122.6
97.5°	83.0	117.0	183.5	320.2	538.5	721.2	745.7	653.9	493.4	389.0	298.9
100°	94.9	125.7	181.1	298.1	506.1	748.8	904.6	932.3	868.2	775.7	663.4
102.5°	108.3	136.0	184.2	279.1	458.6	697.4	912.5	1024.8	1038.2	994.0	933.1
105°	123.4	147.9	190.6	272.0	421.5	635.8	862.7	1028.0	1107.0	1122.1	1101.5
107.5°	140.0	162.9	200.8	270.4	394.6	581.2	791.5	980.5	1104.7	1166.3	1187.7
110°	156.6	178.7	214.3	274.4	380.3	536.1	725.1	906.2	1051.7	1151.3	1206.7



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.0	195.3	227.7	282.3	372.4	506.1	667.4	832.6	982.1	1096.8	1171.9
115°	191.4	212.7	242.8	291.0	371.6	486.3	623.1	769.4	907.0	1023.2	1109.4
117.5°	208.8	228.5	258.6	302.1	372.4	472.9	593.8	720.4	842.1	948.9	1038.2
120°	225.4	245.1	273.6	314.7	375.6	464.2	571.7	683.2	789.9	884.8	964.7
122.5°	240.4	261.7	289.4	326.6	381.1	458.6	553.5	653.9	748.0	834.2	907.0
125°	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.6	714.8	790.7	854.0
127.5°	269.6	291.0	317.9	349.5	393.0	451.5	524.3	605.7	684.0	753.6	812.1
130°	282.3	303.6	329.7	359.8	399.3	449.1	513.2	584.4	655.5	719.6	773.3
132.5°	294.2	314.7	340.0	369.3	404.1	448.3	502.9	564.6	628.6	687.2	737.8
135°	304.4	325.8	350.3	377.2	408.8	447.6	494.2	547.2	603.3	654.7	699.8
137.5°	313.9	333.7	357.4	383.5	412.0	446.0	486.3	530.6	578.0	623.9	664.2
140°	321.8	341.6	364.5	388.3	415.1	445.2	479.2	516.4	556.7	594.6	628.6
142.5°	329.7	347.9	370.1	393.0	417.5	443.6	472.9	502.9	536.1	567.8	596.2
145°	336.1	354.3	374.8	396.2	418.3	442.0	467.3	492.6	518.7	544.0	567.0
147.5°	344.0	359.8	378.8	398.5	418.3	439.7	461.8	483.9	505.3	526.6	543.2
150°	350.3	364.5	382.7	399.3	418.3	436.5	456.3	474.4	492.6	509.2	524.3
152.5°	356.6	370.1	385.1	400.9	415.9	432.5	449.9	465.7	480.8	495.0	506.9
155°	363.7	374.8	388.3	400.9	414.3	427.8	443.6	457.0	469.7	481.6	491.0
157.5°	370.1	378.8	389.8	401.7	412.0	423.8	436.5	447.6	458.6	468.1	476.0
160°	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7	448.3	456.3	461.8
162.5°	378.8	385.1	393.0	400.9	407.2	414.3	422.3	430.2	437.3	444.4	449.1
165°	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.3	427.0	432.5	436.5
167.5°	385.1	389.0	393.8	398.5	400.9	404.9	409.6	415.1	419.1	422.3	425.4
170°	387.5	389.0	393.0	396.2	397.7	400.1	404.1	408.0	410.4	413.6	415.1
172.5°	389.0	389.8	393.0	395.4	395.4	396.2	398.5	401.7	403.3	405.6	406.4
175°	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2	397.0	398.5	398.5
177.5°	390.6	390.6	391.4	393.0	391.4	390.6	391.4	392.2	393.0	393.8	393.8
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1278.7	1278.7	1278.7	1278.7
2.5°	1136.6	1134.5	1126.2	1117.9
5°	963.6	956.5	954.1	951.7
7.5°	842.0	841.4	828.9	816.5
10°	734.9	735.8	724.5	713.2
12.5°	658.3	650.9	650.0	649.1
15°	600.8	593.9	592.8	591.6
17.5°	560.1	556.0	554.8	553.6
20°	529.3	526.9	524.8	522.7
22.5°	502.6	499.6	497.8	496.0
25°	476.8	474.1	473.5	472.9
27.5°	453.6	450.4	450.4	450.4
30°	431.7	429.6	428.7	427.8
32.5°	411.2	409.4	409.4	409.4
35°	391.9	391.0	389.8	388.6
37.5°	374.4	374.4	373.8	373.2
40°	357.5	358.4	358.4	358.4
42.5°	342.1	343.0	343.0	343.0
45°	326.0	327.5	328.1	328.7
47.5°	310.3	312.7	313.3	313.9
50°	294.9	296.7	297.0	297.3
52.5°	279.2	281.2	282.7	284.2
55°	262.6	264.6	265.5	266.4
57.5°	244.8	246.8	247.1	247.4
60°	225.2	227.3	227.8	228.4
62.5°	206.5	207.7	208.3	208.9
65°	185.1	186.9	188.1	189.3
67.5°	164.7	166.1	166.1	166.1
70°	141.8	142.4	143.3	144.2
72.5°	120.7	121.0	121.0	121.0
75°	98.5	99.1	99.4	99.7
77.5°	77.4	77.7	77.7	77.7
80°	56.7	56.4	56.4	56.4
82.5°	38.9	38.0	38.0	38.0
85°	22.3	22.0	22.3	22.5
87.5°	10.1	10.1	10.1	10.1
90°	22.1	22.9	23.7	22.9
92.5°	45.9	42.7	43.5	41.9
95°	107.5	100.4	94.9	91.7
97.5°	245.9	215.9	196.9	188.2
100°	583.6	525.8	495.0	495.8
102.5°	875.3	832.6	808.1	785.2
105°	1065.1	1035.1	1009.8	1005.8
107.5°	1182.9	1168.7	1158.4	1149.7
110°	1228.8	1235.1	1233.6	1232.0



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1216.9	1239.9	1247.8	1248.6
115°	1168.7	1203.5	1219.3	1223.3
117.5°	1099.9	1138.7	1162.4	1167.9
120°	1027.2	1071.5	1090.4	1095.2
122.5°	960.7	999.5	1020.8	1027.2
125°	904.6	939.4	959.2	964.7
127.5°	858.0	888.0	906.2	910.9
130°	815.3	843.7	860.3	866.6
132.5°	776.5	805.0	819.2	823.2
135°	738.5	762.3	776.5	782.0
137.5°	697.4	721.9	733.8	738.5
140°	658.7	680.8	693.5	692.7
142.5°	620.7	639.7	650.8	650.0
145°	586.7	603.3	609.7	611.2
147.5°	559.1	570.9	577.2	578.0
150°	536.1	544.8	549.6	549.6
152.5°	515.6	523.5	525.8	525.8
155°	498.2	504.5	506.1	506.9
157.5°	482.4	487.1	488.7	488.7
160°	467.3	472.1	472.1	471.3
162.5°	452.3	456.3	456.3	455.5
165°	439.7	442.8	442.0	442.0
167.5°	427.0	429.4	428.6	428.6
170°	415.9	417.5	416.7	416.7
172.5°	406.4	408.0	406.4	405.6
175°	398.5	399.3	398.5	397.7
177.5°	393.0	393.8	392.2	392.2
180°	390.6	390.6	390.6	390.6



TEST NUMBER: P831464

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.79	12.55	12.83	13.59	14.99	14.03	14.79	15.07	15.83	17.22
	3H	13.43	14.11	14.48	15.16	16.57	15.45	16.13	16.49	17.17	18.59
	4H	14.01	14.65	15.06	15.70	17.12	15.89	16.54	16.95	17.59	19.01
	6H	14.37	14.96	15.44	16.02	17.45	16.16	16.76	17.23	17.81	19.24
	8H	14.46	15.03	15.54	16.10	17.52	16.22	16.79	17.30	17.86	19.28
	12H	14.51	15.04	15.58	16.10	17.56	16.24	16.77	17.32	17.84	19.29
4H	2H	12.36	13.00	13.42	14.05	15.47	14.18	14.83	15.25	15.87	17.30
	3H	14.18	14.71	15.25	15.79	17.22	15.79	16.33	16.86	17.40	18.84
	4H	14.87	15.36	15.95	16.43	17.89	16.37	16.86	17.45	17.93	19.39
	6H	15.34	15.76	16.43	16.85	18.30	16.77	17.19	17.86	18.28	19.73
	8H	15.47	15.87	16.56	16.95	18.42	16.88	17.27	17.97	18.36	19.82
	12H	15.54	15.89	16.64	16.99	18.46	16.92	17.28	18.02	18.37	19.84
8H	4H	15.13	15.52	16.22	16.61	18.07	16.47	16.86	17.56	17.95	19.41
	6H	15.71	16.04	16.82	17.16	18.63	16.97	17.29	18.08	18.42	19.88
	8H	15.92	16.20	17.04	17.31	18.79	17.15	17.43	18.26	18.54	20.02
	12H	16.04	16.29	17.16	17.39	18.91	17.25	17.50	18.36	18.60	20.12
12H	4H	15.13	15.48	16.23	16.58	18.05	16.44	16.80	17.54	17.89	19.36
	6H	15.76	16.05	16.88	17.16	18.64	16.98	17.27	18.10	18.37	19.86
	8H	15.99	16.24	17.11	17.35	18.87	17.18	17.43	18.30	18.53	20.05