

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331312

Luminaire Tested: **S122DIP-S485D925U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331312  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D925U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5845.8 lumens  
Efficiency: N/A  
Efficacy: 131.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27				
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28	23				
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20				
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18				
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14				
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13				
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14	12				
10	46	34	27	23	42	32	26	21	26	22	18	22	18	16	17	14	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.5	1.6
10°-20°	269.0	4.6
20°-30°	390.5	6.7
30°-40°	412.0	7.0
40°-50°	364.8	6.2
50°-60°	291.1	5.0
60°-70°	197.9	3.4
70°-80°	101.5	1.7
80°-90°	27.6	0.5
90°-100°	42.1	0.7
100°-110°	154.4	2.6
110°-120°	412.7	7.1
120°-130°	681.3	11.7
130°-140°	724.5	12.4
140°-150°	673.4	11.5
150°-160°	541.4	9.3
160°-170°	348.9	6.0
170°-180°	120.1	2.1
0°-30°	752.0	12.9
0°-40°	1164.1	19.9
0°-60°	1820.1	31.1
0°-90°	2147.0	36.7
90°-120°	609.2	10.4
90°-150°	2688.4	46.0
90°-180°	3699.0	63.3
0°-180°	5845.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	25	1	25	1	25	12
95°	39	59	39	59	39	37
105°	69	278	69	278	69	72
115°	75	525	75	525	75	188
125°	781	742	781	742	781	676
135°	949	919	949	919	949	731
145°	1082	1066	1082	1066	1082	677
155°	1174	1174	1174	1174	1174	542
165°	1234	1237	1234	1237	1234	348
175°	1258	1265	1258	1265	1258	120
180°	1262	1262	1262	1262	1262	



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	12.7	12.6	12.8	12.5	12.4	12.5	12.3	11.8	11.9	12.0	12.0
90°	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3	19.3	18.3	16.6
92.5°	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2	21.7	21.2	20.4
95°	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6	36.6	35.6	34.2
97.5°	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3	48.5	47.7	44.4
100°	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3	53.7	52.1	48.6
102.5°	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7	55.6	53.5	48.4
105°	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2	57.9	55.7	48.6
107.5°	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4	75.7	78.0	144.4
110°	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2	139.5	159.8	218.5



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1	329.1	403.1	417.6
115°	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6	469.5	563.5	558.4
117.5°	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7	601.4	624.1	620.7
120°	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3	671.9	669.4	665.8
122.5°	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5	714.0	712.6	708.6
125°	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6	773.2	771.7	767.9
127.5°	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2	827.1	825.1	822.2
130°	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9	861.6	859.4	857.2
132.5°	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6	895.7	893.7	891.5
135°	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7	943.6	941.6	939.8
137.5°	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3	988.3	986.4	984.3
140°	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2	1017.4	1015.6	1013.4
142.5°	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9	1044.3	1042.6	1040.1
145°	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3	1081.8	1080.4	1077.0
147.5°	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8	1114.7	1113.7	1110.3
150°	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8	1134.6	1133.4	1130.2
152.5°	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1	1152.9	1151.7	1148.6
155°	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8	1177.5	1176.3	1173.9
157.5°	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5	1198.2	1196.8	1195.1
160°	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6	1210.4	1209.2	1208.0
162.5°	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9	1221.5	1220.2	1219.1
165°	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9	1233.3
167.5°	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2	1246.8	1245.4	1244.8
170°	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1	1252.6	1251.2	1250.8
172.5°	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4	1257.0	1255.6	1255.2
175°	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2	1261.8	1260.3	1259.9
177.5°	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7	1262.6	1261.4	1261.3
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	12.0	11.6	11.3	11.5	10.2	9.7	8.1	6.8	6.9	7.1	6.9
90°	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9	3.1	5.4	7.6
92.5°	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4	18.2	18.0	17.8
95°	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4	52.7	46.0	39.3
97.5°	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8	98.9	80.1	61.2
100°	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7	133.8	106.0	78.2
102.5°	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9	204.0	198.1	192.2
105°	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6	283.7	289.8	295.9
107.5°	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9	359.8	364.7	369.6
110°	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6	408.9	413.1	417.4





TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3	455.1	458.9	462.7
115°	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1	528.6	532.0	535.5
117.5°	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1	594.9	598.8	602.7
120°	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3	642.3	645.4	648.4
122.5°	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2	683.4	686.6	689.8
125°	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5	745.1	747.8	750.4
127.5°	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9	801.9	804.8	807.7
130°	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8	838.0	841.2	844.5
132.5°	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3	874.0	876.8	879.6
135°	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8	922.0	925.3	928.5
137.5°	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8	969.1	971.4	973.6
140°	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2	999.9	1001.5	1003.1
142.5°	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5	1026.0	1027.5	1028.9
145°	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8	1065.6	1065.4	1065.2
147.5°	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8	1101.0	1100.3	1099.5
150°	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2	1123.8	1122.3	1120.9
152.5°	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9	1143.3	1141.7	1140.2
155°	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6	1171.8	1169.9	1168.1
157.5°	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0	1194.5	1193.0	1191.4
160°	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1208.0	1206.8	1205.5
162.5°	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9	1219.7	1218.5	1217.2
165°	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6	1235.4	1234.2	1232.9
167.5°	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3	1247.1	1245.9	1244.6
170°	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9	1253.6	1252.4	1251.2
172.5°	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2	1258.0	1256.8	1255.6
175°	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9	1263.5	1262.1	1260.6
177.5°	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8	1264.7	1263.6	1262.4
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	7.0	7.1	7.2	7.5	7.5	7.5	7.4	7.6	7.8	7.5	7.6
90°	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3	21.3	22.3	23.0
92.5°	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2	22.8	23.3	23.7
95°	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6	38.7	39.7	40.1
97.5°	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3	50.1	50.9	51.4
100°	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3	56.9	58.6	59.6
102.5°	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7	59.9	62.0	63.3
105°	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2	62.4	64.6	66.2
107.5°	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4	71.2	68.9	68.2
110°	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2	98.9	78.6	68.9



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1	181.0	107.0	70.3
115°	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6	281.6	187.6	133.3
117.5°	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7	556.0	533.2	497.8
120°	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3	676.8	679.2	666.7
122.5°	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5	716.9	718.4	716.5
125°	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6	776.0	777.4	778.4
127.5°	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2	831.3	833.4	834.4
130°	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9	866.1	868.3	869.4
132.5°	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6	899.5	901.4	902.2
135°	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7	947.7	949.7	950.5
137.5°	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3	992.3	994.3	995.0
140°	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2	1021.1	1022.9	1023.3
142.5°	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9	1047.6	1049.3	1049.6
145°	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3	1084.7	1086.1	1086.3
147.5°	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8	1116.8	1117.9	1118.0
150°	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8	1137.1	1138.3	1138.4
152.5°	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1	1155.3	1156.5	1156.5
155°	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8	1180.0	1181.2	1181.0
157.5°	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5	1200.9	1202.3	1202.2
160°	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6	1212.9	1214.1	1214.0
162.5°	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9	1224.3	1225.7	1225.5
165°	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5
167.5°	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2	1249.6	1251.1	1250.8
170°	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1	1255.5	1256.9	1256.7
172.5°	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4	1259.9	1261.3	1261.1
175°	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2	1264.6	1266.0	1265.7
177.5°	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7	1264.9	1266.0	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	7.7	7.5	7.5	7.3	7.5	7.5	7.7	7.6	7.5	7.8	7.6
90°	23.4	23.8	24.3	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3
92.5°	23.9	24.2	24.4	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2
95°	39.9	39.7	39.5	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6
97.5°	51.7	51.9	52.2	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3
100°	60.0	60.4	60.8	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3
102.5°	63.9	64.4	65.0	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7
105°	67.0	67.8	68.6	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2
107.5°	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4
110°	69.7	70.5	71.3	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	70.9	71.6	72.2	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1
115°	118.7	104.1	89.5	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6
117.5°	449.8	401.8	353.8	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7
120°	639.3	611.9	584.5	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3
122.5°	711.2	705.8	700.5	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5
125°	779.0	779.6	780.3	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6
127.5°	834.6	834.7	834.8	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2
130°	869.2	868.9	868.7	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9
132.5°	902.0	901.8	901.6	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6
135°	950.1	949.7	949.3	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7
137.5°	994.3	993.6	992.9	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3
140°	1022.3	1021.3	1020.3	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2
142.5°	1048.6	1047.6	1046.6	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9
145°	1085.3	1084.3	1083.3	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3
147.5°	1117.1	1116.3	1115.4	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8
150°	1137.4	1136.3	1135.3	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8
152.5°	1155.1	1153.8	1152.5	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1
155°	1179.4	1177.7	1176.1	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8
157.5°	1200.6	1199.0	1197.4	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5
160°	1212.5	1211.1	1209.7	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6
162.5°	1223.8	1222.0	1220.3	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9
165°	1238.1	1236.7	1235.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7
167.5°	1249.0	1247.2	1245.4	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2
170°	1254.9	1253.0	1251.2	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1
172.5°	1259.2	1257.4	1255.6	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4
175°	1263.7	1261.7	1259.6	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2
177.5°	1264.4	1262.9	1261.4	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	7.4	7.5	7.5	7.5	7.2	7.1	7.0	6.9	7.1	6.9	6.8
90°	19.3	18.3	16.6	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9
92.5°	21.7	21.2	20.4	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4
95°	36.6	35.6	34.2	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4
97.5°	48.5	47.7	44.4	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8
100°	53.7	52.1	48.6	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7
102.5°	55.6	53.5	82.4	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9
105°	57.9	55.7	111.1	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6
107.5°	75.7	78.0	144.4	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9
110°	139.5	159.8	218.5	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	403.1	417.6	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3
115°	469.5	563.5	558.4	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1
117.5°	601.4	624.1	620.7	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1
120°	671.9	669.4	665.8	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3
122.5°	714.0	712.6	708.6	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2
125°	773.2	771.7	767.9	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5
127.5°	827.1	825.1	822.2	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9
130°	861.6	859.4	857.2	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8
132.5°	895.7	893.7	891.5	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3
135°	943.6	941.6	939.8	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8
137.5°	988.3	986.4	984.3	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8
140°	1017.4	1015.6	1013.4	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2
142.5°	1044.3	1042.6	1040.1	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5
145°	1081.8	1080.4	1077.0	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8
147.5°	1114.7	1113.7	1110.3	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8
150°	1134.6	1133.4	1130.2	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2
152.5°	1152.9	1151.7	1148.6	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9
155°	1177.5	1176.3	1173.9	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6
157.5°	1198.2	1196.8	1195.1	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0
160°	1210.4	1209.2	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2
162.5°	1221.5	1220.2	1219.1	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9
165°	1235.3	1233.9	1233.3	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6
167.5°	1246.8	1245.4	1244.8	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3
170°	1252.6	1251.2	1250.8	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9
172.5°	1257.0	1255.6	1255.2	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2
175°	1261.8	1260.3	1259.9	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9
177.5°	1262.6	1261.4	1261.3	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.1	9.7	10.2	11.5	11.3	11.6	12.0	12.0	12.0	11.9	11.8
90°	3.1	5.4	7.6	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3
92.5°	18.2	18.0	17.8	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2
95°	52.7	46.0	39.3	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6
97.5°	98.9	80.1	61.2	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3
100°	133.8	106.0	78.2	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3
102.5°	204.0	198.1	192.2	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7
105°	283.7	289.8	295.9	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2
107.5°	359.8	364.7	369.6	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4
110°	408.9	413.1	417.4	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2





TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.1	458.9	462.7	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1
115°	528.6	532.0	535.5	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6
117.5°	594.9	598.8	602.7	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7
120°	642.3	645.4	648.4	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3
122.5°	683.4	686.6	689.8	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5
125°	745.1	747.8	750.4	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6
127.5°	801.9	804.8	807.7	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2
130°	838.0	841.2	844.5	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9
132.5°	874.0	876.8	879.6	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6
135°	922.0	925.3	928.5	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7
137.5°	969.1	971.4	973.6	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3
140°	999.9	1001.5	1003.1	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2
142.5°	1026.0	1027.5	1028.9	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9
145°	1065.6	1065.4	1065.2	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3
147.5°	1101.0	1100.3	1099.5	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8
150°	1123.8	1122.3	1120.9	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8
152.5°	1143.3	1141.7	1140.2	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1
155°	1171.8	1169.9	1168.1	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8
157.5°	1194.5	1193.0	1191.4	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5
160°	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6
162.5°	1219.7	1218.5	1217.2	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9
165°	1235.4	1234.2	1232.9	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7
167.5°	1247.1	1245.9	1244.6	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2
170°	1253.6	1252.4	1251.2	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1
172.5°	1258.0	1256.8	1255.6	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4
175°	1263.5	1262.1	1260.6	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2
177.5°	1264.7	1263.6	1262.4	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	12.3	12.5	12.4	12.5	12.8	12.6	12.7
90°	21.3	22.3	23.0	23.4	23.8	24.3	24.7
92.5°	22.8	23.3	23.7	23.9	24.2	24.4	24.7
95°	38.7	39.7	40.1	39.9	39.7	39.5	39.3
97.5°	50.1	50.9	51.4	51.7	51.9	52.2	52.4
100°	56.9	58.6	59.6	60.0	60.4	60.8	61.2
102.5°	59.9	62.0	63.3	63.9	64.4	65.0	65.6
105°	62.4	64.6	66.2	67.0	67.8	68.6	69.4
107.5°	71.2	68.9	68.2	69.0	69.8	70.6	71.4
110°	98.9	78.6	68.9	69.7	70.5	71.3	72.2



TEST NUMBER: P331312

CATALOG NUMBER: S122DIP-S485D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.0	107.0	70.3	70.9	71.6	72.2	72.9
115°	281.6	187.6	133.3	118.7	104.1	89.5	74.9
117.5°	556.0	533.2	497.8	449.8	401.8	353.8	305.8
120°	676.8	679.2	666.7	639.3	611.9	584.5	557.1
122.5°	716.9	718.4	716.5	711.2	705.8	700.5	695.2
125°	776.0	777.4	778.4	779.0	779.6	780.3	780.9
127.5°	831.3	833.4	834.4	834.6	834.7	834.8	834.9
130°	866.1	868.3	869.4	869.2	868.9	868.7	868.5
132.5°	899.5	901.4	902.2	902.0	901.8	901.6	901.4
135°	947.7	949.7	950.5	950.1	949.7	949.3	948.9
137.5°	992.3	994.3	995.0	994.3	993.6	992.9	992.2
140°	1021.1	1022.9	1023.3	1022.3	1021.3	1020.3	1019.2
142.5°	1047.6	1049.3	1049.6	1048.6	1047.6	1046.6	1045.5
145°	1084.7	1086.1	1086.3	1085.3	1084.3	1083.3	1082.3
147.5°	1116.8	1117.9	1118.0	1117.1	1116.3	1115.4	1114.6
150°	1137.1	1138.3	1138.4	1137.4	1136.3	1135.3	1134.3
152.5°	1155.3	1156.5	1156.5	1155.1	1153.8	1152.5	1151.1
155°	1180.0	1181.2	1181.0	1179.4	1177.7	1176.1	1174.5
157.5°	1200.9	1202.3	1202.2	1200.6	1199.0	1197.4	1195.9
160°	1212.9	1214.1	1214.0	1212.5	1211.1	1209.7	1208.3
162.5°	1224.3	1225.7	1225.5	1223.8	1222.0	1220.3	1218.5
165°	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9
167.5°	1249.6	1251.1	1250.8	1249.0	1247.2	1245.4	1243.5
170°	1255.5	1256.9	1256.7	1254.9	1253.0	1251.2	1249.4
172.5°	1259.9	1261.3	1261.1	1259.2	1257.4	1255.6	1253.8
175°	1264.6	1266.0	1265.7	1263.7	1261.7	1259.6	1257.6
177.5°	1264.9	1266.0	1265.8	1264.4	1262.9	1261.4	1260.0
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2

(END OF REPORT)