

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331361

Luminaire Tested: **S122DIP-S675D925U835-4F0-1E-UDD-D1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331361
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D925U835-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5998.7 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331361

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331361

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	94	90	85	81	85	81	78	74	66	64	61	52	50	49	39	38	37	31
2	85	77	71	65	77	70	65	60	57	53	50	45	42	40	34	32	30	25
3	78	68	60	54	70	62	55	50	50	45	41	40	36	33	30	27	25	21
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	26	24	21	17
5	65	53	45	38	58	48	41	35	39	34	30	31	27	24	24	21	18	15
6	59	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	42	34	29	50	39	32	27	32	26	22	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	26	21	18	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11373	11373	11373
5°	11428	10947	10905
10°	11356	10624	10504
15°	11200	10282	10083
20°	11002	9915	9676
25°	10807	9560	9307
30°	10532	9197	8935
35°	10254	8846	8673
40°	9960	8547	8413
45°	9681	8279	8190
50°	9382	8037	7969
55°	9070	7777	7745
60°	8686	7508	7509
65°	8287	7191	7227
70°	7841	6852	6923
75°	7270	6518	6643
80°	6370	6177	6361
85°	5506	5882	6138



TEST NUMBER: P331361

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.1
10°-20°	191.4	3.2
20°-30°	290.0	4.8
30°-40°	353.3	5.9
40°-50°	380.0	6.3
50°-60°	369.1	6.2
60°-70°	322.3	5.4
70°-80°	248.1	4.1
80°-90°	171.2	2.9
90°-100°	189.6	3.2
100°-110°	316.5	5.3
110°-120°	453.2	7.6
120°-130°	554.0	9.2
130°-140°	600.1	10.0
140°-150°	578.0	9.6
150°-160°	482.9	8.1
160°-170°	320.3	5.3
170°-180°	111.9	1.9
0°-30°	548.2	9.1
0°-40°	901.4	15.0
0°-60°	1650.6	27.5
0°-90°	2392.1	39.9
90°-120°	959.3	16.0
90°-150°	2691.4	44.9
90°-180°	3607.0	60.1
0°-180°	5998.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	704	704	704	704	704	
5°	706	703	697	703	702	67
15°	674	676	676	684	684	190
25°	612	620	629	641	644	281
35°	528	545	564	586	594	330
45°	433	461	496	527	538	334
55°	332	369	422	457	472	297
65°	227	277	337	377	392	225
75°	126	183	248	290	305	133
85°	37	100	165	207	222	40
90°	11	83	170	207	222	10
95°	60	118	181	218	230	66
105°	220	254	307	344	356	232
115°	403	422	464	493	502	398
125°	583	593	622	645	654	521
135°	752	764	776	795	801	581
145°	912	919	925	932	933	570
155°	1043	1046	1049	1053	1051	480
165°	1135	1134	1134	1140	1136	320
175°	1181	1178	1176	1182	1177	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P331361

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	704.4	704.4	704.4	704.4	704.4	704.4	704.4	704.4	704.4	704.4	704.4
2.5°	708.5	707.9	707.4	706.8	706.3	705.4	704.1	702.8	701.6	700.3	701.2
5°	706.4	705.7	705.1	704.4	703.7	702.7	701.3	700.0	698.6	697.2	698.6
7.5°	700.1	699.6	699.2	698.7	698.3	697.5	696.5	695.4	694.4	693.4	695.0
10°	695.2	694.7	694.3	693.8	693.4	692.8	692.1	691.5	690.8	690.1	691.9
12.5°	687.0	687.1	687.2	687.3	687.4	687.2	686.7	686.2	685.7	685.2	687.0
15°	673.8	674.2	674.7	675.1	675.6	675.8	675.8	675.8	675.8	675.8	677.8
17.5°	656.6	657.6	658.5	659.5	660.4	661.3	662.0	662.7	663.4	664.2	666.3
20°	645.2	646.3	647.4	648.6	649.7	650.7	651.6	652.6	653.5	654.4	656.9
22.5°	632.9	634.2	635.6	636.9	638.2	639.5	640.8	642.0	643.3	644.6	647.1
25°	612.5	614.1	615.7	617.3	618.9	620.7	622.7	624.8	626.8	628.8	631.6
27.5°	588.0	590.6	593.2	595.8	598.4	600.9	603.3	605.7	608.1	610.5	613.9
30°	571.7	574.6	577.6	580.5	583.5	586.4	589.4	592.3	595.3	598.2	601.8
32.5°	553.7	557.0	560.3	563.6	567.0	570.4	573.9	577.3	580.8	584.3	588.5
35°	527.8	531.6	535.5	539.3	543.2	547.3	551.6	555.9	560.2	564.5	569.5
37.5°	499.6	504.1	508.5	512.9	517.4	522.4	528.0	533.6	539.1	544.7	550.3
40°	480.8	485.8	490.8	495.8	500.8	506.3	512.5	518.6	524.7	530.8	536.7
42.5°	462.9	467.8	472.8	477.8	482.8	488.8	495.9	502.9	509.9	517.0	523.4
45°	432.8	439.0	445.1	451.2	457.3	464.4	472.3	480.3	488.2	496.1	503.2
47.5°	403.2	409.9	416.6	423.2	429.9	437.9	447.2	456.5	465.8	475.1	482.5
50°	382.8	389.9	396.9	403.9	410.9	419.6	429.8	440.0	450.2	460.4	468.1
52.5°	363.2	370.6	378.0	385.4	392.8	401.9	412.6	423.4	434.1	444.9	452.8
55°	331.8	339.9	348.1	356.3	364.4	374.4	386.2	398.0	409.8	421.6	429.8
57.5°	300.7	310.0	319.2	328.4	337.6	348.2	360.2	372.2	384.3	396.3	405.1
60°	278.7	288.4	298.2	308.0	317.7	329.1	342.0	354.9	367.8	380.8	389.4
62.5°	259.1	269.2	279.3	289.4	299.6	311.1	324.0	336.9	349.9	362.8	372.0
65°	226.6	237.7	248.9	260.0	271.1	283.3	296.7	310.1	323.5	336.9	346.2
67.5°	196.8	208.4	220.1	231.7	243.3	255.9	269.6	283.3	297.0	310.7	320.1
70°	175.6	187.4	199.2	211.0	222.8	235.7	249.8	263.8	277.9	292.0	301.7
72.5°	156.0	168.1	180.3	192.5	204.6	217.8	232.1	246.3	260.6	274.8	284.4
75°	125.6	138.3	151.0	163.7	176.4	190.0	204.5	219.0	233.5	248.1	257.8
77.5°	96.2	109.5	122.8	136.0	149.3	163.4	178.1	192.9	207.6	222.3	232.1
80°	76.6	90.4	104.2	118.1	131.9	146.2	161.0	175.7	190.4	205.2	214.7
82.5°	60.2	73.9	87.5	101.2	114.9	129.1	144.1	159.0	173.9	188.9	198.4
85°	36.8	50.8	64.9	78.9	93.0	107.3	121.8	136.3	150.9	165.4	174.9
87.5°	20.2	34.3	48.3	62.4	76.4	91.2	106.7	122.2	137.7	153.2	162.3
90°	11.2	27.0	42.8	58.7	74.5	92.1	111.5	130.9	150.3	169.7	178.3
92.5°	27.2	41.4	55.6	69.8	84.0	98.6	113.8	128.9	144.0	159.1	168.1
95°	60.1	72.9	85.8	98.7	111.6	125.0	139.1	153.2	167.2	181.3	189.9
97.5°	102.0	113.4	124.8	136.3	147.7	160.4	174.3	188.2	202.1	216.0	224.4
100°	133.9	144.1	154.2	164.4	174.6	186.3	199.7	213.1	226.4	239.8	248.2
102.5°	166.6	175.7	184.8	193.9	202.9	214.1	227.3	240.5	253.6	266.8	275.2
105°	219.7	226.9	234.2	241.4	248.6	258.4	270.6	282.9	295.1	307.3	315.7
107.5°	274.1	280.4	286.6	292.9	299.1	307.9	319.2	330.5	341.8	353.1	360.9
110°	308.5	314.3	320.2	326.1	331.9	340.4	351.5	362.7	373.8	384.9	392.1



TEST NUMBER: P331361

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.8	351.9	357.1	362.2	367.3	375.1	385.5	395.9	406.3	416.7	423.4
115°	403.3	407.1	410.9	414.7	418.6	425.4	435.1	444.9	454.7	464.4	471.0
117.5°	458.5	461.9	465.3	468.8	472.2	478.0	486.2	494.4	502.5	510.7	516.9
120°	496.1	498.7	501.4	504.1	506.8	511.8	519.1	526.4	533.7	541.0	547.3
122.5°	530.4	532.9	535.4	537.9	540.3	545.2	552.5	559.8	567.1	574.4	580.0
125°	582.8	584.8	586.8	588.8	590.8	595.1	601.7	608.3	614.9	621.5	627.0
127.5°	634.9	637.2	639.5	641.8	644.1	647.8	652.9	657.9	663.0	668.0	672.9
130°	667.7	670.3	673.0	675.6	678.3	681.8	686.1	690.4	694.8	699.1	704.1
132.5°	704.4	706.5	708.6	710.8	712.9	715.8	719.6	723.4	727.1	730.9	735.2
135°	752.5	754.9	757.4	759.8	762.2	764.8	767.5	770.2	772.9	775.7	780.2
137.5°	804.2	806.1	808.1	810.0	812.0	813.7	815.3	816.9	818.5	820.0	824.0
140°	835.3	837.1	838.8	840.6	842.4	844.1	845.6	847.2	848.7	850.3	853.9
142.5°	867.2	869.0	870.8	872.6	874.3	875.6	876.5	877.3	878.2	879.0	882.1
145°	912.1	913.7	915.2	916.8	918.3	919.8	921.1	922.4	923.8	925.1	926.7
147.5°	953.0	954.9	956.8	958.6	960.5	961.9	962.8	963.6	964.5	965.4	966.1
150°	981.0	982.3	983.6	985.0	986.3	987.4	988.3	989.2	990.1	991.0	991.6
152.5°	1005.7	1007.1	1008.4	1009.7	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4
155°	1042.9	1043.5	1044.2	1044.9	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0
157.5°	1074.6	1075.0	1075.5	1075.9	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9
160°	1093.8	1094.2	1094.6	1095.1	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1
162.5°	1111.3	1111.4	1111.5	1111.6	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2
165°	1134.7	1134.5	1134.2	1134.0	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2
167.5°	1154.2	1153.6	1152.9	1152.2	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6
170°	1164.6	1163.9	1163.3	1162.6	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2
172.5°	1171.8	1171.1	1170.5	1169.8	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4
175°	1180.6	1179.9	1179.2	1178.6	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1
177.5°	1184.2	1183.6	1183.1	1182.6	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331361

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	704.4	704.4	704.4	704.4	704.4	704.4	704.4	704.4
2.5°	702.1	703.0	703.9	704.2	703.8	703.5	703.1	702.8
5°	700.0	701.3	702.7	703.3	703.0	702.8	702.6	702.3
7.5°	696.6	698.3	699.9	700.6	700.4	700.1	699.9	699.7
10°	693.7	695.5	697.4	698.1	697.9	697.7	697.5	697.2
12.5°	688.8	690.6	692.5	693.2	693.0	692.8	692.6	692.3
15°	679.9	681.9	684.0	684.9	684.7	684.4	684.2	684.0
17.5°	668.4	670.6	672.7	673.8	673.8	673.8	673.8	673.8
20°	659.4	661.9	664.3	665.6	665.6	665.6	665.6	665.6
22.5°	649.6	652.1	654.5	656.0	656.3	656.7	657.1	657.4
25°	634.3	637.0	639.7	641.4	642.1	642.8	643.5	644.2
27.5°	617.4	620.8	624.3	626.2	626.7	627.2	627.7	628.2
30°	605.5	609.1	612.7	614.9	615.6	616.3	616.9	617.6
32.5°	592.7	596.9	601.0	603.7	605.0	606.2	607.4	608.6
35°	574.5	579.5	584.5	587.8	589.4	591.0	592.5	594.1
37.5°	555.8	561.3	566.9	570.5	572.2	573.8	575.5	577.2
40°	542.6	548.5	554.4	558.4	560.4	562.5	564.5	566.6
42.5°	529.8	536.3	542.7	547.0	549.0	551.1	553.1	555.1
45°	510.2	517.2	524.3	528.9	531.2	533.5	535.7	538.0
47.5°	489.8	497.2	504.5	509.4	511.9	514.4	516.9	519.4
50°	475.8	483.5	491.3	496.4	498.9	501.4	503.8	506.3
52.5°	460.7	468.6	476.5	481.8	484.4	487.1	489.8	492.5
55°	437.9	446.1	454.3	459.8	462.8	465.7	468.7	471.6
57.5°	413.9	422.7	431.5	437.4	440.4	443.4	446.4	449.4
60°	398.0	406.6	415.3	421.2	424.3	427.5	430.7	433.9
62.5°	381.1	390.3	399.5	405.6	408.5	411.5	414.5	417.5
65°	355.5	364.8	374.1	380.2	383.2	386.1	389.1	392.0
67.5°	329.5	338.9	348.3	354.6	357.6	360.7	363.8	366.9
70°	311.5	321.2	331.0	337.2	339.9	342.7	345.4	348.1
72.5°	294.0	303.5	313.1	319.5	322.8	326.1	329.3	332.6
75°	267.6	277.3	287.1	293.4	296.4	299.3	302.3	305.2
77.5°	241.8	251.5	261.2	267.6	270.8	274.0	277.1	280.3
80°	224.2	233.8	243.3	249.7	252.8	256.0	259.2	262.4
82.5°	207.9	217.4	227.0	233.2	236.2	239.2	242.2	245.2
85°	184.4	194.0	203.5	209.8	213.0	216.2	219.4	222.5
87.5°	171.5	180.7	189.8	195.9	198.8	201.8	204.7	207.7
90°	186.9	195.6	204.2	210.0	212.9	215.9	218.8	221.8
92.5°	177.1	186.1	195.1	200.9	203.7	206.5	209.2	212.0
95°	198.5	207.1	215.7	221.2	223.5	225.8	228.0	230.3
97.5°	232.8	241.2	249.6	255.1	257.7	260.4	263.0	265.6
100°	256.6	265.0	273.4	278.7	281.0	283.3	285.5	287.8
102.5°	283.6	292.0	300.4	305.7	308.0	310.3	312.5	314.8
105°	324.1	332.5	340.9	346.3	348.8	351.3	353.8	356.3
107.5°	368.7	376.5	384.3	388.9	390.4	391.8	393.3	394.8
110°	399.4	406.7	413.9	418.5	420.3	422.1	424.0	425.8



TEST NUMBER: P331361

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	430.1	436.9	443.6	448.0	450.0	452.0	454.0	456.0
115°	477.6	484.2	490.8	495.0	496.8	498.6	500.5	502.3
117.5°	523.1	529.3	535.5	539.4	541.0	542.7	544.3	546.0
120°	553.7	560.0	566.4	570.5	572.3	574.1	576.0	577.8
122.5°	585.7	591.3	596.9	600.6	602.2	603.9	605.5	607.2
125°	632.4	637.9	643.3	647.0	648.8	650.6	652.4	654.3
127.5°	677.7	682.5	687.4	690.4	691.7	693.0	694.3	695.6
130°	709.1	714.1	719.1	722.0	723.0	723.9	724.8	725.7
132.5°	739.5	743.8	748.0	750.7	751.8	753.0	754.1	755.2
135°	784.7	789.3	793.8	796.7	797.8	799.0	800.1	801.3
137.5°	828.0	832.0	836.0	838.3	839.0	839.7	840.3	841.0
140°	857.6	861.2	864.8	866.9	867.3	867.8	868.3	868.8
142.5°	885.2	888.2	891.3	893.0	893.3	893.6	893.9	894.2
145°	928.3	929.9	931.4	932.3	932.6	932.8	933.1	933.3
147.5°	966.8	967.4	968.1	968.3	968.0	967.7	967.4	967.1
150°	992.3	993.0	993.6	993.6	993.0	992.3	991.6	991.0
152.5°	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5
155°	1051.1	1052.2	1053.3	1053.5	1052.8	1052.2	1051.5	1050.8
157.5°	1081.4	1082.9	1084.4	1084.6	1083.6	1082.5	1081.4	1080.4
160°	1099.4	1100.7	1102.1	1102.3	1101.4	1100.5	1099.6	1098.7
162.5°	1115.7	1117.2	1118.7	1119.0	1117.9	1116.8	1115.8	1114.7
165°	1136.8	1138.3	1139.9	1140.1	1139.0	1137.9	1136.8	1135.7
167.5°	1154.1	1155.7	1157.2	1157.4	1156.3	1155.1	1154.0	1152.8
170°	1163.7	1165.3	1166.8	1166.9	1165.6	1164.3	1162.9	1161.6
172.5°	1170.9	1172.5	1174.0	1174.1	1172.8	1171.5	1170.1	1168.8
175°	1178.7	1180.2	1181.8	1181.9	1180.6	1179.2	1177.9	1176.6
177.5°	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6

(END OF REPORT)