

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331989-927

Luminaire Tested: **S123DIP-S775D1025U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331989-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5302.2 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331989-927

CATALOG NUMBER: S123DIP-S775D1025U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331989-927

CATALOG NUMBER: S123DIP-S775D1025U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10384	10384	10384
5°	10432	10289	10361
10°	10363	10200	10263
15°	10242	10085	10104
20°	10100	9919	9929
25°	9911	9723	9704
30°	9701	9506	9434
35°	9483	9276	9155
40°	9254	9021	8882
45°	9003	8788	8573
50°	8751	8500	8264
55°	8422	8203	7955
60°	8088	7858	7608
65°	7796	7480	7246
70°	7361	7046	6735
75°	6729	6488	6209
80°	6069	5808	5759
85°	5323	5125	4915



TEST NUMBER: P331989-927

CATALOG NUMBER: S123DIP-S775D1025U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.7
10°-20°	256.6	4.8
20°-30°	379.0	7.1
30°-40°	442.7	8.4
40°-50°	445.1	8.4
50°-60°	391.0	7.4
60°-70°	291.3	5.5
70°-80°	166.0	3.1
80°-90°	50.6	1.0
90°-100°	65.6	1.2
100°-110°	196.3	3.7
110°-120°	333.8	6.3
120°-130°	439.1	8.3
130°-140°	493.6	9.3
140°-150°	485.2	9.1
150°-160°	408.4	7.7
160°-170°	271.9	5.1
170°-180°	95.2	1.8
0°-30°	726.5	13.7
0°-40°	1169.2	22.1
0°-60°	2005.3	37.8
0°-90°	2513.2	47.4
90°-120°	595.7	11.2
90°-150°	2013.5	38.0
90°-180°	2789.0	52.6
0°-180°	5302.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	965	965	965	965	965	
5°	966	961	952	960	959	91
15°	919	915	905	911	907	259
25°	834	829	819	819	817	384
35°	722	716	706	701	697	451
45°	591	588	577	568	563	456
55°	449	447	437	428	424	402
65°	306	302	294	287	284	302
75°	162	158	156	152	149	173
85°	43	42	42	40	40	47
90°	1	9	19	22	24	5
95°	47	52	58	62	62	52
105°	178	180	187	187	188	191
115°	336	338	337	338	337	332
125°	492	494	493	489	486	438
135°	638	643	642	639	637	492
145°	774	776	778	777	774	483
155°	886	886	887	890	885	408
165°	966	963	963	967	962	272
175°	1004	1001	1001	1005	1000	95
180°	1007	1007	1007	1007	1007	



TEST NUMBER: P331989-927

CATALOG NUMBER: S123DIP-S775D1025U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	968.0	967.4	966.9	966.2	965.7	964.6	962.9	961.3	959.6	958.1	959.5
5°	965.5	964.6	963.7	962.7	961.8	960.4	958.3	956.3	954.3	952.2	954.1
7.5°	956.1	955.1	954.2	953.3	952.4	950.9	948.7	946.7	944.5	942.5	944.1
10°	948.1	947.1	946.3	945.3	944.4	942.8	940.3	937.9	935.6	933.2	934.9
12.5°	937.5	936.7	936.0	935.2	934.4	932.9	930.7	928.4	926.1	923.8	925.1
15°	919.1	918.3	917.6	916.9	916.1	914.6	912.1	909.7	907.4	905.0	906.4
17.5°	897.6	896.7	895.7	894.8	893.8	892.2	889.8	887.3	884.9	882.6	883.6
20°	881.7	880.6	879.6	878.5	877.3	875.5	873.1	870.8	868.4	865.9	866.7
22.5°	863.8	862.7	861.6	860.5	859.4	857.6	855.2	852.9	850.5	848.0	848.7
25°	834.5	833.4	832.3	831.2	830.0	828.3	825.9	823.5	821.1	818.7	818.9
27.5°	803.1	802.0	801.0	799.9	798.8	797.0	794.4	791.9	789.3	786.6	786.8
30°	780.5	779.6	778.7	777.8	776.8	775.1	772.5	769.9	767.4	764.8	764.8
32.5°	758.0	756.8	755.5	754.3	753.1	751.5	749.5	747.5	745.5	743.5	742.5
35°	721.7	720.6	719.5	718.4	717.2	715.5	713.0	710.7	708.3	705.9	704.8
37.5°	684.4	683.1	681.7	680.2	678.9	677.0	674.5	672.1	669.6	667.3	665.9
40°	658.6	657.5	656.4	655.3	654.2	652.4	649.7	647.2	644.6	642.0	640.6
42.5°	632.7	631.4	630.2	629.0	627.7	625.8	623.2	620.6	618.1	615.4	614.0
45°	591.4	590.7	589.9	589.2	588.4	586.9	584.5	582.1	579.7	577.3	575.1
47.5°	550.4	549.4	548.3	547.2	546.1	544.5	542.2	540.0	537.7	535.5	533.3
50°	522.6	521.7	520.7	519.8	518.9	517.2	514.8	512.5	510.0	507.6	505.6
52.5°	493.4	492.7	492.1	491.5	490.8	489.3	486.7	484.2	481.6	479.1	477.4
55°	448.8	448.5	448.4	448.2	448.0	446.7	444.3	442.0	439.5	437.1	435.1
57.5°	406.3	405.7	405.0	404.4	403.8	402.5	400.6	398.6	396.7	394.8	393.0
60°	375.7	375.6	375.4	375.2	375.0	373.8	371.6	369.4	367.2	365.0	363.3
62.5°	348.6	348.1	347.6	347.1	346.7	345.3	343.1	340.9	338.7	336.4	334.8
65°	306.1	305.1	304.2	303.3	302.4	301.0	299.1	297.3	295.5	293.7	292.2
67.5°	261.1	260.3	259.5	258.6	257.9	256.7	255.4	254.0	252.5	251.2	249.9
70°	233.9	232.8	231.7	230.6	229.5	228.4	227.3	226.2	225.1	223.9	222.7
72.5°	205.4	204.5	203.7	203.0	202.2	201.1	199.9	198.6	197.3	196.1	195.0
75°	161.8	161.0	160.3	159.5	158.8	158.1	157.6	157.0	156.5	156.0	155.0
77.5°	123.1	122.7	122.3	121.9	121.4	121.0	120.3	119.6	119.0	118.3	117.6
80°	97.9	97.4	96.8	96.3	95.7	95.2	94.8	94.5	94.1	93.7	93.6
82.5°	73.4	73.2	73.1	73.0	72.9	72.8	72.7	72.6	72.6	72.5	72.2
85°	43.1	42.8	42.4	42.1	41.7	41.5	41.5	41.5	41.5	41.5	41.1
87.5°	17.4	17.3	17.2	17.1	17.0	17.2	17.4	17.7	18.1	18.4	18.4
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6
92.5°	19.2	20.4	21.5	22.7	23.9	25.2	26.5	27.7	29.1	30.3	30.9
95°	46.7	47.8	49.1	50.4	51.6	52.9	54.3	55.7	57.1	58.5	59.3
97.5°	82.9	83.8	84.7	85.6	86.5	87.5	88.5	89.5	90.5	91.6	92.4
100°	107.6	108.6	109.6	110.7	111.8	112.7	113.6	114.5	115.3	116.2	116.8
102.5°	136.0	136.7	137.3	137.9	138.6	139.4	140.6	141.7	142.9	144.1	144.6
105°	177.9	178.2	178.6	179.0	179.4	180.3	181.9	183.5	185.1	186.6	186.6
107.5°	226.6	226.9	227.0	227.3	227.5	227.9	228.5	229.2	229.8	230.4	231.0
110°	257.0	257.4	257.7	258.0	258.4	258.7	259.1	259.4	259.8	260.2	260.9



TEST NUMBER: P331989-927

CATALOG NUMBER: S123DIP-S775D1025U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.6	288.8	289.1	289.2	289.5	289.6	289.7	289.8	289.9	289.9	290.7
115°	336.0	336.6	337.2	337.6	338.2	338.3	337.9	337.5	337.2	336.8	337.1
117.5°	383.8	384.2	384.5	384.9	385.2	385.2	384.8	384.3	383.8	383.3	383.3
120°	413.6	414.6	415.7	416.8	417.8	417.9	417.0	416.1	415.3	414.4	414.2
122.5°	444.6	445.4	446.1	446.9	447.7	447.8	447.3	446.9	446.5	446.0	445.5
125°	491.9	492.4	492.9	493.5	493.9	494.1	493.7	493.4	493.0	492.7	491.9
127.5°	535.5	536.6	537.7	538.8	540.0	540.3	540.0	539.6	539.2	538.8	537.8
130°	564.6	566.0	567.4	568.8	570.2	570.7	570.1	569.6	569.1	568.5	567.8
132.5°	593.7	595.1	596.5	597.9	599.4	599.8	599.4	599.0	598.7	598.3	597.5
135°	638.2	639.2	640.2	641.3	642.4	642.8	642.6	642.5	642.3	642.1	641.4
137.5°	679.3	680.2	681.0	681.9	682.8	683.4	683.9	684.4	684.8	685.2	684.5
140°	707.7	708.6	709.5	710.3	711.2	711.8	711.9	712.1	712.3	712.5	712.3
142.5°	733.6	734.5	735.5	736.3	737.2	737.8	738.1	738.4	738.7	739.0	738.9
145°	774.1	774.5	774.8	775.2	775.5	776.0	776.5	777.1	777.6	778.1	777.9
147.5°	809.6	810.2	810.9	811.5	812.1	812.7	813.2	813.7	814.1	814.7	814.7
150°	834.2	834.6	835.0	835.3	835.7	836.0	836.4	836.7	837.1	837.4	837.4
152.5°	854.5	855.0	855.5	856.0	856.4	856.8	857.1	857.2	857.5	857.7	857.9
155°	886.5	886.5	886.5	886.5	886.5	886.5	886.7	886.8	887.1	887.2	888.0
157.5°	913.6	913.5	913.2	913.0	912.8	912.8	912.9	913.1	913.2	913.3	914.1
160°	930.7	930.3	930.0	929.7	929.3	929.2	929.2	929.2	929.2	929.2	930.0
162.5°	945.9	945.4	944.9	944.4	944.0	943.8	943.9	944.0	944.2	944.4	945.2
165°	965.5	965.0	964.5	963.9	963.5	963.1	963.1	963.1	963.1	963.1	964.2
167.5°	981.2	980.5	979.8	979.1	978.3	978.1	978.3	978.3	978.5	978.7	979.8
170°	990.1	989.4	988.6	987.9	987.2	986.9	986.9	986.9	986.9	986.9	988.1
172.5°	997.0	996.3	995.6	994.9	994.2	993.8	993.8	993.8	993.8	993.8	994.9
175°	1004.2	1003.5	1002.8	1002.2	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2
177.5°	1007.3	1006.7	1006.2	1005.6	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331989-927

CATALOG NUMBER: S123DIP-S775D1025U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	961.0	962.5	963.9	964.6	964.5	964.3	964.2	964.0
5°	955.9	957.7	959.6	960.4	960.0	959.6	959.3	958.9
7.5°	945.8	947.5	949.1	949.8	949.6	949.4	949.1	949.0
10°	936.5	938.1	939.8	940.5	940.1	939.7	939.4	939.0
12.5°	926.3	927.5	928.8	929.2	929.0	928.8	928.6	928.4
15°	907.9	909.3	910.9	911.0	909.9	908.8	907.8	906.7
17.5°	884.6	885.7	886.7	887.0	886.6	886.2	885.8	885.4
20°	867.4	868.2	868.9	869.0	868.5	867.9	867.4	866.8
22.5°	849.2	849.9	850.4	850.3	849.7	849.0	848.3	847.6
25°	819.0	819.3	819.4	819.3	818.7	818.2	817.6	817.1
27.5°	787.0	787.1	787.3	787.0	786.3	785.6	784.9	784.2
30°	764.8	764.8	764.8	764.1	762.9	761.5	760.3	759.0
32.5°	741.5	740.5	739.4	738.6	737.8	737.1	736.4	735.8
35°	703.7	702.6	701.5	700.4	699.5	698.6	697.7	696.7
37.5°	664.6	663.2	661.9	661.0	660.4	659.8	659.2	658.6
40°	639.1	637.6	636.1	635.0	634.3	633.5	632.8	632.1
42.5°	612.5	611.0	609.6	608.5	607.8	607.0	606.3	605.5
45°	572.9	570.7	568.5	566.9	566.0	565.1	564.1	563.2
47.5°	531.2	529.0	526.8	525.3	524.5	523.7	522.9	522.0
50°	503.6	501.5	499.6	498.0	496.9	495.7	494.6	493.5
52.5°	475.6	473.9	472.1	470.8	469.7	468.6	467.5	466.4
55°	433.1	431.0	429.0	427.5	426.6	425.7	424.8	423.9
57.5°	391.2	389.4	387.6	386.2	385.1	384.0	382.9	381.9
60°	361.6	360.0	358.3	357.0	356.1	355.2	354.3	353.4
62.5°	333.1	331.4	329.8	328.7	328.0	327.4	326.8	326.1
65°	290.7	289.2	287.7	286.7	286.1	285.6	285.0	284.5
67.5°	248.6	247.3	246.0	244.9	244.2	243.4	242.6	241.9
70°	221.4	220.1	218.8	217.7	216.7	215.9	214.9	214.0
72.5°	193.8	192.7	191.5	190.7	190.2	189.7	189.3	188.8
75°	154.1	153.2	152.3	151.5	151.0	150.4	149.9	149.3
77.5°	117.0	116.4	115.7	115.5	115.5	115.5	115.5	115.5
80°	93.4	93.2	93.0	92.9	92.9	92.9	92.9	92.9
82.5°	71.9	71.5	71.1	70.9	70.8	70.7	70.5	70.3
85°	40.7	40.4	40.0	39.8	39.8	39.8	39.8	39.8
87.5°	18.4	18.4	18.4	18.4	18.5	18.5	18.6	18.7
90°	20.4	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	31.5	32.1	32.6	32.8	32.6	32.4	32.2	31.9
95°	59.9	60.6	61.3	61.7	61.7	61.7	61.7	61.7
97.5°	93.2	94.0	94.8	95.1	95.1	95.1	95.0	94.9
100°	117.3	117.8	118.4	118.8	119.1	119.5	119.9	120.2
102.5°	145.1	145.7	146.2	146.4	146.3	146.2	146.2	146.2
105°	186.6	186.6	186.6	186.8	187.1	187.5	187.8	188.2
107.5°	231.6	232.1	232.7	232.8	232.7	232.4	232.2	232.0
110°	261.6	262.3	263.0	263.2	262.8	262.4	262.1	261.7



TEST NUMBER: P331989-927

CATALOG NUMBER: S123DIP-S775D1025U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.6	292.4	293.3	293.7	293.6	293.5	293.4	293.3
115°	337.2	337.4	337.5	337.5	337.4	337.2	337.1	336.8
117.5°	383.3	383.3	383.3	382.9	382.5	382.0	381.5	381.0
120°	414.0	413.8	413.7	413.4	413.0	412.7	412.3	412.0
122.5°	445.0	444.7	444.2	443.7	443.2	442.7	442.2	441.7
125°	491.2	490.5	489.8	489.1	488.5	487.7	487.0	486.3
127.5°	536.9	535.9	534.9	534.0	533.2	532.3	531.6	530.8
130°	567.1	566.4	565.8	564.7	563.6	562.3	561.1	559.8
132.5°	596.6	595.8	594.9	594.1	593.1	592.2	591.2	590.3
135°	640.7	640.0	639.3	638.7	638.4	638.0	637.7	637.4
137.5°	683.8	683.1	682.3	681.6	681.0	680.2	679.6	679.0
140°	712.1	711.9	711.8	711.1	709.9	708.6	707.4	706.2
142.5°	738.7	738.6	738.3	737.8	736.8	735.9	734.9	734.0
145°	777.8	777.6	777.4	777.0	776.3	775.5	774.8	774.1
147.5°	814.7	814.7	814.7	814.1	813.1	812.0	811.0	809.9
150°	837.4	837.4	837.4	836.9	835.8	834.8	833.7	832.7
152.5°	858.3	858.5	858.8	858.5	857.5	856.7	855.7	854.8
155°	888.7	889.4	890.0	889.8	888.6	887.3	886.1	884.9
157.5°	914.8	915.5	916.3	916.2	915.2	914.2	913.2	912.2
160°	930.9	931.8	932.6	932.7	932.1	931.4	930.7	929.9
162.5°	946.1	947.0	947.8	947.7	946.6	945.5	944.4	943.3
165°	965.3	966.3	967.3	967.3	966.1	964.8	963.6	962.3
167.5°	980.8	981.9	983.0	983.0	981.9	980.8	979.8	978.7
170°	989.4	990.5	991.8	991.8	990.5	989.4	988.1	986.9
172.5°	996.0	997.1	998.1	998.1	996.9	995.7	994.4	993.2
175°	1003.2	1004.2	1005.4	1005.2	1004.0	1002.7	1001.6	1000.3
177.5°	1006.5	1007.3	1008.1	1008.1	1007.1	1006.1	1005.1	1004.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6

(END OF REPORT)