

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331997-927

Luminaire Tested: **S123DIP-S775D1195U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331997-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6291.5 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331997-927

CATALOG NUMBER: S123DIP-S775D1195U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331997-927

CATALOG NUMBER: S123DIP-S775D1195U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	68	79	73	67	63	60	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10384	10384	10384
5°	10432	10289	10361
10°	10363	10200	10263
15°	10242	10085	10104
20°	10100	9919	9929
25°	9911	9723	9704
30°	9701	9506	9434
35°	9483	9276	9155
40°	9254	9021	8882
45°	9003	8788	8573
50°	8751	8500	8264
55°	8422	8203	7955
60°	8088	7858	7608
65°	7796	7480	7246
70°	7361	7046	6735
75°	6729	6488	6209
80°	6069	5808	5759
85°	5323	5125	4915



TEST NUMBER: P331997-927

CATALOG NUMBER: S123DIP-S775D1195U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.4
10°-20°	256.6	4.1
20°-30°	379.0	6.0
30°-40°	442.7	7.0
40°-50°	445.1	7.1
50°-60°	391.0	6.2
60°-70°	291.3	4.6
70°-80°	166.0	2.6
80°-90°	51.1	0.8
90°-100°	45.0	0.7
100°-110°	214.7	3.4
110°-120°	515.6	8.2
120°-130°	656.6	10.4
130°-140°	701.5	11.2
140°-150°	656.0	10.4
150°-160°	529.2	8.4
160°-170°	341.5	5.4
170°-180°	117.7	1.9
0°-30°	726.5	11.5
0°-40°	1169.2	18.6
0°-60°	2005.3	31.9
0°-90°	2513.7	40.0
90°-120°	775.3	12.3
90°-150°	2789.4	44.3
90°-180°	3778.0	60.0
0°-180°	6291.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	965	965	965	965	965	
5°	966	961	952	960	959	91
15°	919	915	905	911	907	259
25°	834	829	819	819	817	384
35°	722	716	706	701	697	451
45°	591	588	577	568	563	456
55°	449	447	437	428	424	402
65°	306	302	294	287	284	302
75°	162	158	156	152	149	173
85°	43	42	42	40	40	47
90°	1	10	22	26	28	5
95°	56	21	28	35	35	69
105°	274	279	202	48	40	291
115°	514	520	528	537	541	508
125°	725	732	736	738	740	647
135°	903	908	912	915	912	695
145°	1042	1048	1050	1052	1052	652
155°	1148	1146	1147	1151	1146	529
165°	1210	1208	1207	1213	1208	342
175°	1239	1234	1235	1241	1234	118
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P331997-927

CATALOG NUMBER: S123DIP-S775D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	968.0	967.4	966.9	966.2	965.7	964.6	962.9	961.3	959.6	958.1	959.5
5°	965.5	964.6	963.7	962.7	961.8	960.4	958.3	956.3	954.3	952.2	954.1
7.5°	956.1	955.1	954.2	953.3	952.4	950.9	948.7	946.7	944.5	942.5	944.1
10°	948.1	947.1	946.3	945.3	944.4	942.8	940.3	937.9	935.6	933.2	934.9
12.5°	937.5	936.7	936.0	935.2	934.4	932.9	930.7	928.4	926.1	923.8	925.1
15°	919.1	918.3	917.6	916.9	916.1	914.6	912.1	909.7	907.4	905.0	906.4
17.5°	897.6	896.7	895.7	894.8	893.8	892.2	889.8	887.3	884.9	882.6	883.6
20°	881.7	880.6	879.6	878.5	877.3	875.5	873.1	870.8	868.4	865.9	866.7
22.5°	863.8	862.7	861.6	860.5	859.4	857.6	855.2	852.9	850.5	848.0	848.7
25°	834.5	833.4	832.3	831.2	830.0	828.3	825.9	823.5	821.1	818.7	818.9
27.5°	803.1	802.0	801.0	799.9	798.8	797.0	794.4	791.9	789.3	786.6	786.8
30°	780.5	779.6	778.7	777.8	776.8	775.1	772.5	769.9	767.4	764.8	764.8
32.5°	758.0	756.8	755.5	754.3	753.1	751.5	749.5	747.5	745.5	743.5	742.5
35°	721.7	720.6	719.5	718.4	717.2	715.5	713.0	710.7	708.3	705.9	704.8
37.5°	684.4	683.1	681.7	680.2	678.9	677.0	674.5	672.1	669.6	667.3	665.9
40°	658.6	657.5	656.4	655.3	654.2	652.4	649.7	647.2	644.6	642.0	640.6
42.5°	632.7	631.4	630.2	629.0	627.7	625.8	623.2	620.6	618.1	615.4	614.0
45°	591.4	590.7	589.9	589.2	588.4	586.9	584.5	582.1	579.7	577.3	575.1
47.5°	550.4	549.4	548.3	547.2	546.1	544.5	542.2	540.0	537.7	535.5	533.3
50°	522.6	521.7	520.7	519.8	518.9	517.2	514.8	512.5	510.0	507.6	505.6
52.5°	493.4	492.7	492.1	491.5	490.8	489.3	486.7	484.2	481.6	479.1	477.4
55°	448.8	448.5	448.4	448.2	448.0	446.7	444.3	442.0	439.5	437.1	435.1
57.5°	406.3	405.7	405.0	404.4	403.8	402.5	400.6	398.6	396.7	394.8	393.0
60°	375.7	375.6	375.4	375.2	375.0	373.8	371.6	369.4	367.2	365.0	363.3
62.5°	348.6	348.1	347.6	347.1	346.7	345.3	343.1	340.9	338.7	336.4	334.8
65°	306.1	305.1	304.2	303.3	302.4	301.0	299.1	297.3	295.5	293.7	292.2
67.5°	261.1	260.3	259.5	258.6	257.9	256.7	255.4	254.0	252.5	251.2	249.9
70°	233.9	232.8	231.7	230.6	229.5	228.4	227.3	226.2	225.1	223.9	222.7
72.5°	205.4	204.5	203.7	203.0	202.2	201.1	199.9	198.6	197.3	196.1	195.0
75°	161.8	161.0	160.3	159.5	158.8	158.1	157.6	157.0	156.5	156.0	155.0
77.5°	123.1	122.7	122.3	121.9	121.4	121.0	120.3	119.6	119.0	118.3	117.6
80°	97.9	97.4	96.8	96.3	95.7	95.2	94.8	94.5	94.1	93.7	93.6
82.5°	73.4	73.2	73.1	73.0	72.9	72.8	72.7	72.6	72.6	72.5	72.2
85°	43.1	42.8	42.4	42.1	41.7	41.5	41.5	41.5	41.5	41.5	41.1
87.5°	17.4	17.4	17.3	17.3	17.3	17.5	17.8	18.2	18.6	19.0	19.0
90°	1.0	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9
92.5°	17.1	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9
95°	56.2	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9
97.5°	112.8	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3
100°	155.5	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0
102.5°	204.1	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5
105°	274.3	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3
107.5°	348.2	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9
110°	397.6	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4



TEST NUMBER: P331997-927

CATALOG NUMBER: S123DIP-S775D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	444.7	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6
115°	514.5	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4
117.5°	582.0	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7
120°	624.0	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7
122.5°	666.7	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2
125°	725.2	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7
127.5°	782.0	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4
130°	817.3	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2
132.5°	851.1	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3
135°	902.9	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7
137.5°	947.1	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0
140°	976.5	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6
142.5°	1003.8	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7
145°	1041.9	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5
147.5°	1077.8	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3
150°	1099.9	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9
152.5°	1119.7	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8
155°	1147.7	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8
157.5°	1169.4	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6
160°	1182.6	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1
162.5°	1195.2	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3
165°	1210.3	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2
167.5°	1222.1	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0
170°	1228.7	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6
172.5°	1233.1	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1
175°	1238.8	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6
177.5°	1240.3	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331997-927

CATALOG NUMBER: S123DIP-S775D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	961.0	962.5	963.9	964.6	964.5	964.3	964.2	964.0
5°	955.9	957.7	959.6	960.4	960.0	959.6	959.3	958.9
7.5°	945.8	947.5	949.1	949.8	949.6	949.4	949.1	949.0
10°	936.5	938.1	939.8	940.5	940.1	939.7	939.4	939.0
12.5°	926.3	927.5	928.8	929.2	929.0	928.8	928.6	928.4
15°	907.9	909.3	910.9	911.0	909.9	908.8	907.8	906.7
17.5°	884.6	885.7	886.7	887.0	886.6	886.2	885.8	885.4
20°	867.4	868.2	868.9	869.0	868.5	867.9	867.4	866.8
22.5°	849.2	849.9	850.4	850.3	849.7	849.0	848.3	847.6
25°	819.0	819.3	819.4	819.3	818.7	818.2	817.6	817.1
27.5°	787.0	787.1	787.3	787.0	786.3	785.6	784.9	784.2
30°	764.8	764.8	764.8	764.1	762.9	761.5	760.3	759.0
32.5°	741.5	740.5	739.4	738.6	737.8	737.1	736.4	735.8
35°	703.7	702.6	701.5	700.4	699.5	698.6	697.7	696.7
37.5°	664.6	663.2	661.9	661.0	660.4	659.8	659.2	658.6
40°	639.1	637.6	636.1	635.0	634.3	633.5	632.8	632.1
42.5°	612.5	611.0	609.6	608.5	607.8	607.0	606.3	605.5
45°	572.9	570.7	568.5	566.9	566.0	565.1	564.1	563.2
47.5°	531.2	529.0	526.8	525.3	524.5	523.7	522.9	522.0
50°	503.6	501.5	499.6	498.0	496.9	495.7	494.6	493.5
52.5°	475.6	473.9	472.1	470.8	469.7	468.6	467.5	466.4
55°	433.1	431.0	429.0	427.5	426.6	425.7	424.8	423.9
57.5°	391.2	389.4	387.6	386.2	385.1	384.0	382.9	381.9
60°	361.6	360.0	358.3	357.0	356.1	355.2	354.3	353.4
62.5°	333.1	331.4	329.8	328.7	328.0	327.4	326.8	326.1
65°	290.7	289.2	287.7	286.7	286.1	285.6	285.0	284.5
67.5°	248.6	247.3	246.0	244.9	244.2	243.4	242.6	241.9
70°	221.4	220.1	218.8	217.7	216.7	215.9	214.9	214.0
72.5°	193.8	192.7	191.5	190.7	190.2	189.7	189.3	188.8
75°	154.1	153.2	152.3	151.5	151.0	150.4	149.9	149.3
77.5°	117.0	116.4	115.7	115.5	115.5	115.5	115.5	115.5
80°	93.4	93.2	93.0	92.9	92.9	92.9	92.9	92.9
82.5°	71.9	71.5	71.1	70.9	70.8	70.7	70.5	70.3
85°	40.7	40.4	40.0	39.8	39.8	39.8	39.8	39.8
87.5°	19.0	19.1	19.1	19.1	19.3	19.3	19.4	19.5
90°	23.7	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	26.1	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	31.4	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	32.9	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	33.7	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	50.4	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	129.1	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	316.3	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	401.6	394.8	388.1	370.1	340.9	311.6	282.3	253.1



TEST NUMBER: P331997-927

CATALOG NUMBER: S123DIP-S775D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	461.7	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	532.3	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	596.4	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	638.3	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	679.3	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.1	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.0	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.0	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	863.1	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	958.1	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	986.4	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1013.4	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.0	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1084.7	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.3	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1123.6	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1148.8	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1170.8	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1183.3	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1194.7	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1209.9	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1232.7	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1238.0	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1239.9	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)