

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331963-927

Luminaire Tested: **S123DIP-S775D365U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331963-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D365U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3551.7 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331963-927

CATALOG NUMBER: S123DIP-S775D365U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331963-927

CATALOG NUMBER: S123DIP-S775D365U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63	59
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	56	53	50
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	52	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	42	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	37	32	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10384	10384	10384
5°	10432	10289	10361
10°	10363	10200	10263
15°	10242	10085	10104
20°	10100	9919	9929
25°	9911	9723	9704
30°	9701	9506	9434
35°	9483	9276	9155
40°	9254	9021	8882
45°	9003	8788	8573
50°	8751	8500	8264
55°	8422	8203	7955
60°	8088	7858	7608
65°	7796	7480	7246
70°	7361	7046	6735
75°	6729	6488	6209
80°	6069	5808	5759
85°	5323	5125	4915



TEST NUMBER: P331963-927

CATALOG NUMBER: S123DIP-S775D365U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	2.6
10°-20°	256.6	7.2
20°-30°	379.0	10.7
30°-40°	442.7	12.5
40°-50°	445.1	12.5
50°-60°	391.0	11.0
60°-70°	291.3	8.2
70°-80°	166.0	4.7
80°-90°	48.7	1.4
90°-100°	77.0	2.2
100°-110°	217.9	6.1
110°-120°	214.4	6.0
120°-130°	171.0	4.8
130°-140°	134.8	3.8
140°-150°	100.6	2.8
150°-160°	70.1	2.0
160°-170°	41.2	1.2
170°-180°	13.4	0.4
0°-30°	726.5	20.5
0°-40°	1169.2	32.9
0°-60°	2005.3	56.5
0°-90°	2511.3	70.7
90°-120°	509.3	14.3
90°-150°	915.7	25.8
90°-180°	1040.0	29.3
0°-180°	3551.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	965	965	965	965	965	
5°	966	961	952	960	959	91
15°	919	915	905	911	907	259
25°	834	829	819	819	817	384
35°	722	716	706	701	697	451
45°	591	588	577	568	563	456
55°	449	447	437	428	424	402
65°	306	302	294	287	284	302
75°	162	158	156	152	149	173
85°	43	42	42	40	40	47
90°	1	3	7	8	8	3
95°	10	31	166	48	32	10
105°	32	48	225	394	356	35
115°	57	72	172	378	433	57
125°	80	94	161	291	342	71
135°	94	112	158	240	277	72
145°	107	122	156	197	216	67
155°	121	131	152	172	179	56
165°	132	136	145	154	156	37
175°	138	138	139	141	141	13
180°	138	138	138	138	138	



TEST NUMBER: P331963-927

CATALOG NUMBER: S123DIP-S775D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	968.0	967.4	966.9	966.2	965.7	964.6	962.9	961.3	959.6	958.1	959.5
5°	965.5	964.6	963.7	962.7	961.8	960.4	958.3	956.3	954.3	952.2	954.1
7.5°	956.1	955.1	954.2	953.3	952.4	950.9	948.7	946.7	944.5	942.5	944.1
10°	948.1	947.1	946.3	945.3	944.4	942.8	940.3	937.9	935.6	933.2	934.9
12.5°	937.5	936.7	936.0	935.2	934.4	932.9	930.7	928.4	926.1	923.8	925.1
15°	919.1	918.3	917.6	916.9	916.1	914.6	912.1	909.7	907.4	905.0	906.4
17.5°	897.6	896.7	895.7	894.8	893.8	892.2	889.8	887.3	884.9	882.6	883.6
20°	881.7	880.6	879.6	878.5	877.3	875.5	873.1	870.8	868.4	865.9	866.7
22.5°	863.8	862.7	861.6	860.5	859.4	857.6	855.2	852.9	850.5	848.0	848.7
25°	834.5	833.4	832.3	831.2	830.0	828.3	825.9	823.5	821.1	818.7	818.9
27.5°	803.1	802.0	801.0	799.9	798.8	797.0	794.4	791.9	789.3	786.6	786.8
30°	780.5	779.6	778.7	777.8	776.8	775.1	772.5	769.9	767.4	764.8	764.8
32.5°	758.0	756.8	755.5	754.3	753.1	751.5	749.5	747.5	745.5	743.5	742.5
35°	721.7	720.6	719.5	718.4	717.2	715.5	713.0	710.7	708.3	705.9	704.8
37.5°	684.4	683.1	681.7	680.2	678.9	677.0	674.5	672.1	669.6	667.3	665.9
40°	658.6	657.5	656.4	655.3	654.2	652.4	649.7	647.2	644.6	642.0	640.6
42.5°	632.7	631.4	630.2	629.0	627.7	625.8	623.2	620.6	618.1	615.4	614.0
45°	591.4	590.7	589.9	589.2	588.4	586.9	584.5	582.1	579.7	577.3	575.1
47.5°	550.4	549.4	548.3	547.2	546.1	544.5	542.2	540.0	537.7	535.5	533.3
50°	522.6	521.7	520.7	519.8	518.9	517.2	514.8	512.5	510.0	507.6	505.6
52.5°	493.4	492.7	492.1	491.5	490.8	489.3	486.7	484.2	481.6	479.1	477.4
55°	448.8	448.5	448.4	448.2	448.0	446.7	444.3	442.0	439.5	437.1	435.1
57.5°	406.3	405.7	405.0	404.4	403.8	402.5	400.6	398.6	396.7	394.8	393.0
60°	375.7	375.6	375.4	375.2	375.0	373.8	371.6	369.4	367.2	365.0	363.3
62.5°	348.6	348.1	347.6	347.1	346.7	345.3	343.1	340.9	338.7	336.4	334.8
65°	306.1	305.1	304.2	303.3	302.4	301.0	299.1	297.3	295.5	293.7	292.2
67.5°	261.1	260.3	259.5	258.6	257.9	256.7	255.4	254.0	252.5	251.2	249.9
70°	233.9	232.8	231.7	230.6	229.5	228.4	227.3	226.2	225.1	223.9	222.7
72.5°	205.4	204.5	203.7	203.0	202.2	201.1	199.9	198.6	197.3	196.1	195.0
75°	161.8	161.0	160.3	159.5	158.8	158.1	157.6	157.0	156.5	156.0	155.0
77.5°	123.1	122.7	122.3	121.9	121.4	121.0	120.3	119.6	119.0	118.3	117.6
80°	97.9	97.4	96.8	96.3	95.7	95.2	94.8	94.5	94.1	93.7	93.6
82.5°	73.4	73.2	73.1	73.0	72.9	72.8	72.7	72.6	72.6	72.5	72.2
85°	43.1	42.8	42.4	42.1	41.7	41.5	41.5	41.5	41.5	41.5	41.1
87.5°	17.3	17.0	16.7	16.4	16.1	15.9	15.9	15.9	16.0	16.0	15.8
90°	0.6	1.1	1.7	2.5	3.1	3.6	4.5	5.3	6.2	7.0	6.7
92.5°	3.5	5.1	7.5	9.7	12.0	16.2	23.5	35.6	47.4	43.0	32.5
95°	9.5	10.4	13.5	18.2	25.5	36.4	60.2	101.9	147.8	166.0	134.7
97.5°	16.2	16.5	18.9	23.1	30.3	42.1	64.8	111.8	188.4	257.3	275.2
100°	20.8	21.0	23.0	26.9	33.6	44.5	64.1	105.5	179.2	265.1	320.3
102.5°	25.4	25.9	27.6	31.4	37.4	47.5	65.0	100.1	165.7	250.6	322.5
105°	32.5	33.4	35.0	38.3	43.6	52.4	67.5	96.3	149.2	225.1	305.4
107.5°	40.0	40.8	42.5	45.7	50.7	58.8	72.1	96.0	138.7	202.6	275.5
110°	45.3	46.2	47.6	50.7	55.5	63.3	75.9	97.1	134.7	189.8	256.7



TEST NUMBER: P331963-927

CATALOG NUMBER: S123DIP-S775D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.3	51.1	52.5	55.6	60.4	68.0	79.7	99.4	132.4	181.3	240.3
115°	57.4	58.5	60.2	63.0	67.7	75.3	86.0	103.0	131.6	172.1	220.6
117.5°	64.5	65.8	67.2	69.8	75.1	82.1	92.6	107.8	132.1	166.8	208.7
120°	69.4	70.3	71.7	74.5	79.8	86.7	96.9	111.4	133.0	164.3	202.4
122.5°	73.7	74.5	75.9	79.0	84.1	91.5	101.3	114.8	134.5	162.8	197.3
125°	79.8	80.3	82.0	85.1	90.4	98.0	107.8	120.1	136.9	160.7	190.7
127.5°	84.4	85.2	87.4	90.5	96.3	103.9	113.4	124.5	139.6	159.7	184.8
130°	87.4	88.2	90.7	94.0	100.0	107.5	116.8	127.4	141.4	159.0	181.6
132.5°	89.6	90.6	93.4	97.4	103.3	110.7	119.6	130.1	142.8	158.8	178.8
135°	93.5	94.6	97.7	101.9	107.8	115.3	124.0	133.6	144.7	158.4	175.0
137.5°	97.2	98.4	101.4	105.8	111.7	118.7	127.1	136.1	146.1	157.8	171.7
140°	99.7	101.1	103.9	108.4	113.9	121.0	129.0	137.4	146.9	157.6	169.6
142.5°	102.3	103.5	106.5	110.6	116.2	122.7	130.6	138.8	147.7	157.2	167.9
145°	106.6	107.5	110.0	114.2	119.0	125.4	132.7	140.2	148.1	156.5	165.4
147.5°	111.1	111.5	114.0	117.6	122.2	127.7	134.4	141.2	148.1	155.4	163.1
150°	113.9	114.2	116.5	120.1	124.0	129.0	135.5	141.4	148.1	154.6	161.5
152.5°	116.8	116.9	119.1	122.3	125.8	130.6	136.2	141.8	147.4	153.4	159.7
155°	121.2	121.2	122.9	125.7	128.8	132.7	137.4	142.0	146.7	151.5	157.0
157.5°	124.7	124.9	126.3	128.7	131.3	134.4	138.2	142.2	145.8	149.7	154.0
160°	127.4	127.4	128.5	130.7	132.7	135.5	138.9	142.2	145.3	148.4	152.0
162.5°	129.4	129.4	130.3	132.1	133.8	136.2	139.1	142.0	144.4	147.0	150.0
165°	132.4	132.1	132.7	134.1	135.2	137.2	139.4	141.4	143.1	145.0	147.3
167.5°	134.7	134.4	134.7	135.7	136.5	137.8	139.3	140.9	141.7	143.0	144.7
170°	136.0	135.5	135.8	136.6	137.2	137.8	139.1	140.2	140.9	141.6	143.1
172.5°	137.0	136.6	136.7	137.3	137.6	137.9	139.1	140.1	140.1	140.5	141.5
175°	138.0	137.8	137.4	138.0	138.0	138.3	138.9	139.4	139.1	139.1	139.7
177.5°	138.6	138.3	138.1	138.3	138.3	138.3	138.6	138.9	138.6	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P331963-927

CATALOG NUMBER: S123DIP-S775D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	961.0	962.5	963.9	964.6	964.5	964.3	964.2	964.0
5°	955.9	957.7	959.6	960.4	960.0	959.6	959.3	958.9
7.5°	945.8	947.5	949.1	949.8	949.6	949.4	949.1	949.0
10°	936.5	938.1	939.8	940.5	940.1	939.7	939.4	939.0
12.5°	926.3	927.5	928.8	929.2	929.0	928.8	928.6	928.4
15°	907.9	909.3	910.9	911.0	909.9	908.8	907.8	906.7
17.5°	884.6	885.7	886.7	887.0	886.6	886.2	885.8	885.4
20°	867.4	868.2	868.9	869.0	868.5	867.9	867.4	866.8
22.5°	849.2	849.9	850.4	850.3	849.7	849.0	848.3	847.6
25°	819.0	819.3	819.4	819.3	818.7	818.2	817.6	817.1
27.5°	787.0	787.1	787.3	787.0	786.3	785.6	784.9	784.2
30°	764.8	764.8	764.8	764.1	762.9	761.5	760.3	759.0
32.5°	741.5	740.5	739.4	738.6	737.8	737.1	736.4	735.8
35°	703.7	702.6	701.5	700.4	699.5	698.6	697.7	696.7
37.5°	664.6	663.2	661.9	661.0	660.4	659.8	659.2	658.6
40°	639.1	637.6	636.1	635.0	634.3	633.5	632.8	632.1
42.5°	612.5	611.0	609.6	608.5	607.8	607.0	606.3	605.5
45°	572.9	570.7	568.5	566.9	566.0	565.1	564.1	563.2
47.5°	531.2	529.0	526.8	525.3	524.5	523.7	522.9	522.0
50°	503.6	501.5	499.6	498.0	496.9	495.7	494.6	493.5
52.5°	475.6	473.9	472.1	470.8	469.7	468.6	467.5	466.4
55°	433.1	431.0	429.0	427.5	426.6	425.7	424.8	423.9
57.5°	391.2	389.4	387.6	386.2	385.1	384.0	382.9	381.9
60°	361.6	360.0	358.3	357.0	356.1	355.2	354.3	353.4
62.5°	333.1	331.4	329.8	328.7	328.0	327.4	326.8	326.1
65°	290.7	289.2	287.7	286.7	286.1	285.6	285.0	284.5
67.5°	248.6	247.3	246.0	244.9	244.2	243.4	242.6	241.9
70°	221.4	220.1	218.8	217.7	216.7	215.9	214.9	214.0
72.5°	193.8	192.7	191.5	190.7	190.2	189.7	189.3	188.8
75°	154.1	153.2	152.3	151.5	151.0	150.4	149.9	149.3
77.5°	117.0	116.4	115.7	115.5	115.5	115.5	115.5	115.5
80°	93.4	93.2	93.0	92.9	92.9	92.9	92.9	92.9
82.5°	71.9	71.5	71.1	70.9	70.8	70.7	70.5	70.3
85°	40.7	40.4	40.0	39.8	39.8	39.8	39.8	39.8
87.5°	15.7	15.6	15.5	15.5	15.5	15.5	15.6	15.5
90°	7.0	7.3	7.5	8.1	7.8	8.1	8.4	8.1
92.5°	23.6	18.7	16.5	15.1	14.6	13.7	14.0	13.5
95°	100.8	68.3	53.5	43.4	38.1	35.6	33.6	32.5
97.5°	251.2	201.2	165.1	131.7	111.0	98.4	90.8	88.4
100°	330.0	307.4	274.6	234.9	206.6	186.2	175.2	175.5
102.5°	356.2	355.5	336.4	311.2	289.2	273.1	264.0	257.5
105°	363.9	391.9	397.2	390.0	377.1	366.5	357.5	356.1
107.5°	341.8	387.3	411.9	421.8	422.1	418.4	415.4	412.9
110°	320.8	372.3	407.6	427.2	435.1	437.3	436.7	436.2



TEST NUMBER: P331963-927

CATALOG NUMBER: S123DIP-S775D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.0	352.6	392.1	417.3	431.7	438.6	440.8	440.8
115°	272.4	321.1	362.3	392.8	413.8	426.0	431.7	433.1
117.5°	252.4	294.5	331.4	362.3	384.3	398.4	406.4	408.3
120°	241.9	279.6	313.2	341.5	363.6	379.3	386.0	387.7
122.5°	233.6	267.8	298.9	325.2	344.8	358.9	366.3	368.4
125°	222.5	253.1	280.0	302.4	320.3	332.6	339.6	341.5
127.5°	212.9	240.1	264.4	284.8	300.7	311.2	317.6	319.3
130°	206.8	232.1	254.8	273.8	288.6	298.7	304.6	306.8
132.5°	201.3	224.4	245.6	263.7	277.7	287.7	292.9	294.5
135°	193.7	213.6	231.8	247.7	261.5	269.9	274.9	276.9
137.5°	186.8	203.1	218.8	232.7	244.2	252.7	256.9	258.3
140°	182.8	197.1	210.5	222.5	233.2	241.1	245.5	245.3
142.5°	179.0	191.2	202.9	213.3	222.4	229.4	233.4	233.1
145°	174.4	183.6	192.6	200.7	207.7	213.6	215.9	216.4
147.5°	170.6	178.0	185.2	191.0	196.3	200.3	202.4	202.6
150°	167.9	174.4	180.3	185.6	189.8	192.9	194.6	194.6
152.5°	165.5	171.0	176.3	180.7	183.9	186.8	187.8	187.8
155°	161.8	166.3	170.5	173.8	176.3	178.6	179.2	179.4
157.5°	157.9	161.6	164.9	167.5	169.7	171.3	171.8	171.7
160°	155.7	158.8	161.5	163.5	165.4	167.2	167.2	166.8
162.5°	153.0	155.6	158.2	159.9	161.2	162.6	162.6	162.4
165°	149.5	151.1	153.1	154.6	155.7	156.8	156.5	156.5
167.5°	146.5	147.7	148.9	149.9	150.4	151.1	150.9	150.9
170°	144.4	145.3	146.4	146.9	147.3	147.8	147.5	147.5
172.5°	142.7	143.3	144.2	144.5	144.6	145.1	144.7	144.4
175°	140.2	140.5	141.1	141.1	141.1	141.4	141.1	140.9
177.5°	138.7	138.9	139.2	139.2	138.9	139.2	138.7	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3

(END OF REPORT)