

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331741

Luminaire Tested: **S122RDIP-S1005D530U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331741
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S1005D530U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5926.8 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	60	56
2	94	87	81	76	88	82	77	73	73	69	66	64	61	59	57	54	53	49
3	86	77	70	65	81	73	67	62	65	60	56	58	54	51	51	48	46	43
4	80	69	62	56	75	66	59	54	59	53	49	52	48	45	46	43	41	38
5	74	62	55	49	69	59	52	47	53	48	43	48	43	40	43	39	36	33
6	68	57	49	43	64	54	47	42	49	43	39	44	39	36	39	35	33	30
7	64	52	44	39	60	49	42	37	45	39	35	40	36	32	36	32	30	27
8	59	47	40	35	56	45	38	34	41	35	31	37	32	29	33	30	27	25
9	56	44	36	31	52	42	35	30	38	32	28	34	30	27	31	27	25	23
10	52	40	33	29	49	39	32	28	35	30	26	32	28	24	29	25	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35608	35608	35608	35608
5°	39768	35832	31770	35832
10°	44124	35580	27539	35580
15°	46292	35059	21698	35059
20°	40132	34287	18777	34287
25°	26320	33228	16764	33228
30°	17715	31946	15172	31946
35°	14349	30328	13685	30328
40°	12760	28572	12663	28572
45°	11549	26510	11303	26510
50°	10510	24465	10472	24465
55°	9880	22196	9751	22196
60°	8263	20118	8167	20118
65°	6968	18269	7904	18269
70°	6439	16315	7454	16315
75°	6026	14198	6881	14198
80°	5560	11688	6127	11688
85°	5113	9226	5391	9226



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.1	3.5
10°-20°	582.5	9.8
20°-30°	750.7	12.7
30°-40°	713.4	12.0
40°-50°	611.1	10.3
50°-60°	465.4	7.9
60°-70°	294.2	5.0
70°-80°	146.9	2.5
80°-90°	40.0	0.7
90°-100°	24.1	0.4
100°-110°	88.2	1.5
110°-120°	235.8	4.0
120°-130°	389.3	6.6
130°-140°	414.0	7.0
140°-150°	384.8	6.5
150°-160°	309.4	5.2
160°-170°	199.4	3.4
170°-180°	68.6	1.2
0°-30°	1542.3	26.0
0°-40°	2255.7	38.1
0°-60°	3332.1	56.2
0°-90°	3813.3	64.3
90°-120°	348.1	5.9
90°-150°	1536.2	25.9
90°-180°	2114.0	35.7
0°-180°	5926.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2205	2205	2205	2205	2205	
5°	2454	2211	1960	2211	2454	242
15°	2769	2097	1298	2097	2769	747
25°	1477	1865	941	1865	1477	701
35°	728	1539	694	1539	728	466
45°	506	1161	495	1161	506	391
55°	351	788	346	788	351	308
65°	182	478	207	478	182	186
75°	97	228	110	228	97	102
85°	28	50	29	50	28	30
90°	14	0	14	0	14	8
95°	22	34	22	34	22	21
105°	40	159	40	159	40	41
115°	43	300	43	300	43	107
125°	446	424	446	424	446	386
135°	542	525	542	525	542	418
145°	618	609	618	609	618	387
155°	671	671	671	671	671	310
165°	705	707	705	707	705	199
175°	719	723	719	723	719	68
180°	721	721	721	721	721	



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2294.9	2296.8	2298.6	2294.3	2294.3	2290.6	2282.7	2276.5	2259.4	2256.9	2256.9
5°	2453.7	2452.2	2455.2	2445.3	2431.5	2428.4	2413.9	2394.7	2374.8	2352.6	2348.0
7.5°	2611.6	2609.3	2603.1	2601.5	2590.9	2567.7	2544.3	2519.3	2486.2	2453.9	2437.6
10°	2691.3	2716.6	2701.2	2674.4	2679.8	2643.8	2624.6	2591.7	2564.1	2515.8	2505.1
12.5°	2769.7	2779.7	2774.8	2759.6	2752.7	2727.7	2701.8	2673.2	2622.3	2578.9	2541.2
15°	2769.4	2784.0	2787.8	2783.2	2787.1	2785.5	2771.7	2748.0	2703.5	2656.0	2614.6
17.5°	2565.0	2575.1	2600.2	2617.2	2638.7	2684.1	2706.4	2715.2	2708.6	2681.5	2652.3
20°	2335.7	2318.8	2389.3	2425.4	2456.0	2532.6	2598.5	2623.8	2664.4	2663.7	2656.0
22.5°	2010.8	2014.8	2081.6	2124.4	2213.9	2290.5	2365.6	2460.8	2539.4	2591.3	2621.7
25°	1477.4	1506.6	1573.2	1631.5	1731.1	1873.6	2003.1	2153.3	2295.1	2407.0	2513.5
27.5°	1109.6	1111.8	1164.6	1218.4	1277.6	1394.4	1557.4	1736.8	1938.9	2105.7	2297.5
30°	950.2	945.6	967.8	1000.8	1051.4	1141.8	1264.4	1440.7	1642.2	1893.5	2117.3
32.5°	837.4	837.7	854.4	878.8	920.8	981.8	1065.8	1208.9	1399.4	1646.5	1908.9
35°	728.0	727.2	739.5	757.1	774.7	813.8	871.3	946.4	1077.4	1308.1	1576.3
37.5°	649.5	652.9	658.9	669.9	689.4	711.1	745.6	796.0	889.4	1025.8	1251.2
40°	605.4	606.9	615.3	624.5	636.0	652.9	681.2	721.9	790.1	898.9	1063.6
42.5°	564.9	566.5	572.4	581.0	590.1	606.9	630.4	665.5	720.8	805.7	941.6
45°	505.8	505.8	511.1	515.0	524.9	540.2	559.4	588.5	626.8	689.7	780.1
47.5°	450.3	450.4	454.0	460.6	466.8	478.8	497.6	521.4	549.3	597.9	675.1
50°	418.4	419.2	421.5	426.8	430.7	441.4	456.0	476.6	505.8	543.3	607.7
52.5°	392.7	392.2	395.1	397.4	400.0	407.7	418.6	436.8	462.8	495.5	548.8
55°	351.0	347.9	352.5	356.3	358.6	361.7	367.8	379.3	401.5	429.1	469.0
57.5°	298.9	297.6	300.9	304.4	311.6	319.9	325.1	332.4	343.9	363.7	403.2
60°	255.9	255.9	262.8	265.1	273.6	284.3	295.0	301.2	312.7	325.7	354.8
62.5°	217.9	218.6	221.8	224.1	228.8	242.0	257.0	270.5	281.4	293.8	313.1
65°	182.4	183.9	183.9	185.4	188.5	191.6	197.7	208.4	227.6	245.2	259.8
67.5°	154.8	155.3	155.7	157.2	158.0	161.4	163.8	168.6	173.0	189.7	207.8
70°	136.4	138.7	137.9	139.5	140.2	141.8	144.8	147.1	154.0	157.9	168.6
72.5°	119.2	120.9	120.8	121.7	123.7	124.0	126.4	128.7	133.2	136.4	142.2
75°	96.6	95.8	96.6	98.1	98.9	99.6	99.6	102.7	105.0	108.0	111.9
77.5°	74.5	75.3	75.1	75.3	75.4	76.8	76.6	78.0	80.3	81.8	83.7
80°	59.8	60.5	59.8	60.5	61.3	62.1	61.3	62.1	64.4	65.9	65.9
82.5°	46.3	46.4	46.9	47.1	47.2	47.4	48.4	48.6	50.3	50.0	50.6
85°	27.6	26.8	26.8	26.8	27.6	28.4	27.6	27.6	28.4	28.4	28.4
87.5°	12.6	13.2	13.1	13.1	13.1	13.0	12.9	13.4	12.6	13.1	12.3
90°	14.1	13.9	13.6	13.4	13.2	12.8	12.2	11.6	11.0	10.4	9.5
92.5°	14.1	14.0	13.8	13.7	13.5	13.3	13.0	12.7	12.4	12.1	11.6
95°	22.4	22.6	22.7	22.8	22.9	22.7	22.1	21.5	20.9	20.4	19.5
97.5°	30.0	29.8	29.7	29.5	29.4	29.1	28.6	28.2	27.7	27.2	25.4
100°	35.0	34.7	34.5	34.3	34.0	33.5	32.5	31.6	30.7	29.7	27.8
102.5°	37.5	37.1	36.8	36.5	36.2	35.4	34.2	33.0	31.8	30.6	47.1
105°	39.7	39.2	38.7	38.3	37.8	36.9	35.7	34.4	33.1	31.8	63.5
107.5°	40.8	40.3	39.9	39.4	39.0	39.4	40.7	42.0	43.3	44.6	82.5
110°	41.2	40.8	40.3	39.8	39.4	44.9	56.5	68.1	79.7	91.3	124.8



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	41.6	41.3	40.9	40.5	40.2	61.1	103.4	145.7	188.0	230.4	238.6
115°	42.8	51.1	59.5	67.8	76.2	107.2	160.9	214.6	268.3	322.0	319.1
117.5°	174.7	202.2	229.6	257.0	284.5	304.7	317.7	330.7	343.7	356.6	354.7
120°	318.3	334.0	349.7	365.3	381.0	388.1	386.7	385.3	383.9	382.5	380.4
122.5°	397.2	400.3	403.3	406.4	409.4	410.5	409.7	408.8	408.0	407.2	404.9
125°	446.2	445.9	445.5	445.2	444.8	444.2	443.4	442.6	441.8	441.0	438.8
127.5°	477.1	477.0	477.0	476.9	476.8	476.2	475.0	473.8	472.6	471.5	469.8
130°	496.3	496.4	496.5	496.6	496.8	496.2	494.9	493.6	492.4	491.1	489.8
132.5°	515.1	515.2	515.3	515.4	515.5	515.1	514.0	512.9	511.8	510.7	509.4
135°	542.2	542.5	542.7	542.9	543.2	542.7	541.5	540.4	539.2	538.0	537.0
137.5°	567.0	567.4	567.7	568.1	568.5	568.2	567.0	565.9	564.8	563.6	562.4
140°	582.4	583.0	583.6	584.1	584.7	584.5	583.4	582.4	581.4	580.3	579.0
142.5°	597.4	598.0	598.6	599.2	599.8	599.6	598.6	597.7	596.7	595.8	594.3
145°	618.4	619.0	619.6	620.2	620.7	620.6	619.8	619.0	618.2	617.4	615.4
147.5°	636.9	637.4	637.9	638.4	638.8	638.8	638.2	637.6	637.0	636.4	634.4
150°	648.2	648.7	649.3	649.9	650.5	650.4	649.7	649.0	648.3	647.6	645.8
152.5°	657.8	658.5	659.3	660.1	660.8	660.9	660.2	659.5	658.8	658.1	656.3
155°	671.1	672.1	673.0	673.9	674.8	675.0	674.3	673.6	672.9	672.2	670.8
157.5°	683.3	684.2	685.1	686.0	687.0	687.0	686.2	685.4	684.6	683.9	682.9
160°	690.4	691.2	692.1	692.9	693.7	693.7	693.0	692.3	691.7	691.0	690.3
162.5°	696.3	697.3	698.3	699.3	700.3	700.4	699.6	698.8	698.0	697.2	696.6
165°	705.0	705.9	706.7	707.5	708.3	708.3	707.5	706.7	705.9	705.0	704.7
167.5°	710.6	711.6	712.7	713.7	714.8	714.9	714.1	713.2	712.4	711.6	711.3
170°	713.9	715.0	716.0	717.0	718.1	718.2	717.4	716.6	715.8	715.0	714.7
172.5°	716.4	717.5	718.5	719.6	720.6	720.7	719.9	719.1	718.3	717.5	717.2
175°	718.6	719.8	720.9	722.1	723.3	723.4	722.6	721.8	721.0	720.2	719.9
177.5°	720.0	720.8	721.6	722.5	723.3	723.4	722.8	722.1	721.5	720.8	720.7
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2258.2	2253.2	2249.0	2237.9	2232.4	2220.1	2218.3	2217.7	2201.8	2186.4	2182.1
5°	2335.7	2323.4	2305.1	2283.6	2261.4	2238.4	2223.1	2210.8	2180.1	2151.0	2134.2
7.5°	2413.9	2387.5	2355.8	2315.2	2281.3	2243.3	2215.1	2189.8	2146.3	2104.6	2076.5
10°	2472.1	2429.2	2387.0	2331.1	2287.4	2244.5	2204.7	2170.2	2121.1	2066.0	2026.9
12.5°	2508.3	2461.1	2403.0	2348.3	2291.7	2237.2	2183.8	2139.5	2081.9	2024.9	1978.5
15°	2557.2	2506.6	2436.1	2357.9	2285.1	2213.9	2152.6	2097.4	2022.3	1954.1	1897.4
17.5°	2597.2	2527.6	2451.9	2361.5	2277.2	2186.6	2107.7	2037.2	1953.6	1871.3	1804.5
20°	2610.0	2541.1	2453.7	2363.3	2263.7	2157.2	2072.1	1995.5	1905.8	1816.1	1739.5
22.5°	2602.1	2548.4	2451.3	2343.1	2241.0	2129.6	2033.5	1944.6	1845.1	1753.6	1664.7
25°	2548.0	2529.6	2437.6	2319.6	2203.1	2073.6	1962.5	1865.2	1751.8	1653.7	1557.1
27.5°	2421.8	2461.5	2404.5	2278.8	2149.3	2010.5	1885.6	1774.8	1657.1	1546.7	1450.5
30°	2300.5	2391.6	2367.1	2250.6	2105.8	1969.4	1829.2	1713.5	1587.8	1474.4	1379.4
32.5°	2134.3	2285.0	2308.9	2211.4	2061.7	1911.8	1764.8	1649.7	1518.5	1399.0	1306.4
35°	1869.8	2095.1	2198.5	2136.5	1986.3	1824.6	1672.8	1538.7	1406.9	1288.9	1197.0
37.5°	1554.2	1861.1	2033.5	2037.9	1900.0	1731.9	1566.6	1433.5	1298.6	1182.7	1083.3
40°	1349.5	1682.0	1906.6	1956.4	1839.9	1658.3	1491.2	1355.6	1223.8	1110.4	996.2
42.5°	1165.6	1496.9	1772.9	1859.5	1767.0	1586.6	1418.9	1277.1	1149.0	1041.7	925.1
45°	942.6	1232.2	1536.4	1691.2	1639.9	1472.8	1295.8	1161.0	1040.6	947.9	836.0
47.5°	795.1	999.3	1293.7	1503.0	1502.1	1349.6	1175.5	1046.3	934.7	847.8	757.3
50°	711.1	888.9	1138.0	1375.5	1395.4	1267.5	1101.9	974.0	869.8	778.6	705.8
52.5°	635.7	782.2	1006.2	1233.9	1290.6	1179.8	1019.2	901.0	799.9	716.0	653.7
55°	537.2	650.6	820.7	1033.7	1119.6	1041.4	898.9	788.5	706.5	636.0	582.4
57.5°	454.4	539.5	676.0	847.5	947.5	898.3	780.7	691.1	620.9	557.1	514.8
60°	402.3	472.0	587.8	731.1	841.4	806.9	706.5	623.0	563.2	508.1	468.2
62.5°	353.3	413.2	512.4	628.7	729.8	715.6	633.6	563.5	511.1	460.9	427.1
65°	284.3	328.0	405.4	496.6	577.8	584.7	525.7	478.2	431.4	391.6	361.7
67.5°	226.4	254.9	309.4	386.2	447.1	468.8	432.8	396.5	359.4	328.6	302.7
70°	190.8	213.8	253.6	315.7	371.7	394.6	374.0	345.6	313.4	288.1	265.9
72.5°	154.6	177.0	206.4	252.0	299.9	324.8	317.6	297.2	271.1	250.1	229.1
75°	116.5	123.4	143.3	174.0	211.5	233.0	238.3	227.6	206.9	190.8	178.5
77.5°	86.1	90.3	99.8	115.9	140.4	159.5	167.4	166.1	151.9	142.5	131.0
80°	69.0	71.3	75.9	82.8	101.2	120.3	125.7	125.7	115.7	111.9	100.4
82.5°	52.4	54.1	56.9	60.7	69.3	86.0	92.0	93.2	86.9	81.8	72.8
85°	29.9	29.1	30.7	33.0	34.5	39.1	48.3	49.8	48.3	42.1	39.8
87.5°	12.1	12.6	12.4	11.5	11.9	12.3	15.1	17.9	15.7	14.1	13.1
90°	8.6	7.7	6.7	5.6	4.3	3.1	1.8	0.5	1.8	3.1	4.3
92.5°	11.2	10.7	10.3	10.1	10.2	10.3	10.4	10.5	10.4	10.3	10.2
95°	18.7	17.9	17.1	18.6	22.4	26.3	30.1	33.9	30.1	26.3	22.4
97.5°	23.5	21.6	19.7	24.2	35.0	45.8	56.5	67.3	56.5	45.8	35.0
100°	25.8	23.8	21.9	28.8	44.7	60.6	76.5	92.4	76.5	60.6	44.7
102.5°	63.6	80.1	96.5	106.5	109.8	113.2	116.6	119.9	116.6	113.2	109.8
105°	95.2	126.8	158.5	172.6	169.1	165.6	162.1	158.6	162.1	165.6	169.1
107.5°	120.5	158.5	196.4	214.0	211.2	208.4	205.6	202.8	205.6	208.4	211.2
110°	158.4	191.9	225.4	240.9	238.5	236.1	233.6	231.2	233.6	236.1	238.5



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.9	255.2	263.5	266.5	264.4	262.2	260.1	257.9	260.1	262.2	264.4
115°	316.2	313.3	310.4	308.0	306.0	304.0	302.0	300.1	302.0	304.0	306.0
117.5°	352.7	350.7	348.7	346.6	344.4	342.2	340.0	337.8	340.0	342.2	344.4
120°	378.4	376.3	374.2	372.3	370.5	368.8	367.0	365.3	367.0	368.8	370.5
122.5°	402.6	400.3	398.1	396.0	394.2	392.4	390.5	388.7	390.5	392.4	394.2
125°	436.6	434.4	432.2	430.3	428.8	427.3	425.8	424.3	425.8	427.3	428.8
127.5°	468.2	466.5	464.9	463.2	461.5	459.9	458.2	456.5	458.2	459.9	461.5
130°	488.5	487.3	486.0	484.4	482.6	480.7	478.8	477.0	478.8	480.7	482.6
132.5°	508.2	506.9	505.6	504.2	502.6	501.0	499.4	497.9	499.4	501.0	502.6
135°	536.0	534.9	533.9	532.4	530.6	528.7	526.9	525.0	526.9	528.7	530.6
137.5°	561.3	560.1	558.9	557.6	556.3	555.0	553.7	552.5	553.7	555.0	556.3
140°	577.8	576.5	575.2	574.1	573.2	572.3	571.3	570.4	571.3	572.3	573.2
142.5°	592.8	591.4	589.9	588.8	587.9	587.1	586.3	585.4	586.3	587.1	587.9
145°	613.4	611.5	609.5	608.6	608.7	608.8	608.9	609.0	608.9	608.8	608.7
147.5°	632.5	630.5	628.6	627.8	628.3	628.7	629.1	629.6	629.1	628.7	628.3
150°	643.9	642.1	640.2	639.7	640.5	641.3	642.1	642.9	642.1	641.3	640.5
152.5°	654.6	652.8	651.0	650.6	651.5	652.4	653.3	654.2	653.3	652.4	651.5
155°	669.4	668.0	666.6	666.4	667.5	668.5	669.6	670.6	669.6	668.5	667.5
157.5°	681.9	680.9	680.0	679.9	680.8	681.7	682.6	683.4	682.6	681.7	680.8
160°	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	690.3	689.6	688.9
162.5°	696.0	695.4	694.8	694.9	695.5	696.2	696.9	697.6	696.9	696.2	695.5
165°	704.3	704.0	703.7	703.8	704.5	705.2	705.9	706.6	705.9	705.2	704.5
167.5°	711.0	710.6	710.3	710.5	711.2	711.9	712.6	713.3	712.6	711.9	711.2
170°	714.5	714.3	714.0	714.3	715.0	715.7	716.4	717.0	716.4	715.7	715.0
172.5°	717.0	716.8	716.5	716.8	717.5	718.2	718.9	719.6	718.9	718.2	717.5
175°	719.7	719.5	719.3	719.5	720.4	721.2	722.0	722.8	722.0	721.2	720.4
177.5°	720.6	720.5	720.4	720.7	721.4	722.0	722.7	723.3	722.7	722.0	721.4
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2174.2	2169.9	2161.9	2149.6	2142.3	2129.4	2120.8	2125.7	2127.0	2125.7	2124.5
5°	2115.8	2099.7	2077.5	2056.0	2036.1	2014.6	2002.4	1997.0	1986.3	1980.1	1977.1
7.5°	2045.1	2017.4	1986.0	1948.6	1916.8	1883.6	1866.6	1858.1	1836.2	1824.3	1813.8
10°	1992.4	1948.7	1917.3	1868.3	1838.4	1794.7	1764.8	1765.6	1735.7	1718.8	1706.6
12.5°	1934.2	1886.2	1833.9	1789.8	1748.3	1713.2	1677.1	1662.6	1630.9	1614.6	1581.5
15°	1837.6	1781.7	1726.5	1666.7	1624.6	1570.2	1518.1	1454.5	1403.1	1358.7	1346.4
17.5°	1732.2	1662.9	1607.6	1537.4	1465.2	1373.7	1313.3	1276.4	1245.4	1222.0	1204.5
20°	1659.8	1589.3	1530.3	1424.6	1327.2	1265.2	1220.7	1192.4	1160.2	1134.9	1121.1
22.5°	1583.8	1510.2	1429.8	1311.8	1235.9	1186.1	1146.5	1113.9	1092.1	1072.4	1059.8
25°	1475.9	1395.4	1262.9	1181.6	1120.3	1068.2	1040.6	1020.7	997.7	970.9	958.7
27.5°	1361.9	1233.9	1138.7	1078.3	1019.8	985.9	961.1	931.4	910.8	898.7	886.0
30°	1276.7	1148.7	1074.4	1008.5	967.1	929.5	900.4	883.6	863.6	842.9	834.5
32.5°	1181.6	1079.4	1008.2	953.3	911.3	879.3	856.3	829.0	814.6	801.9	784.2
35°	1063.6	986.2	921.1	876.7	836.8	810.8	783.9	767.8	741.8	731.1	724.2
37.5°	963.7	896.6	848.0	801.1	769.5	740.7	724.3	698.7	687.4	672.5	658.0
40°	907.3	841.4	794.7	756.3	721.1	699.6	678.9	658.3	641.4	634.5	616.9
42.5°	849.7	796.0	749.3	707.3	683.7	661.0	634.8	619.6	602.2	591.0	580.1
45°	770.1	722.6	682.8	648.3	622.2	598.5	581.6	556.3	546.4	524.2	515.0
47.5°	700.3	656.1	618.1	585.3	559.9	544.4	519.7	499.9	484.0	470.4	458.6
50°	650.6	613.8	577.0	547.9	524.9	502.7	477.4	467.4	442.9	436.0	429.1
52.5°	605.2	570.3	536.6	508.1	485.1	463.5	441.2	428.2	411.7	404.8	399.7
55°	541.8	508.1	475.9	450.6	427.6	405.4	391.6	375.5	367.8	362.5	356.3
57.5°	478.0	447.7	423.0	397.4	374.3	356.6	340.7	331.0	323.1	316.0	308.7
60°	437.6	408.4	386.2	362.5	338.7	324.1	311.9	300.4	291.2	280.5	277.4
62.5°	394.6	369.2	348.8	325.7	305.0	291.7	280.0	269.1	258.1	242.5	238.2
65°	335.6	315.7	294.3	275.1	256.7	243.7	226.8	214.6	210.0	208.4	207.7
67.5°	282.3	263.5	245.1	225.4	208.7	196.6	188.1	186.2	183.0	182.1	179.9
70°	246.8	229.1	210.7	192.3	176.3	174.0	170.9	167.8	164.0	162.5	160.9
72.5°	214.9	196.6	178.2	163.5	156.6	153.7	150.7	147.6	145.0	143.5	142.5
75°	164.8	147.9	135.6	130.3	126.4	124.1	119.5	117.2	115.7	113.4	112.6
77.5°	118.6	109.1	103.5	100.1	96.1	93.6	91.0	88.7	87.1	86.6	85.4
80°	90.4	85.8	82.0	77.4	75.9	72.8	72.0	69.7	70.5	68.2	68.2
82.5°	70.2	64.4	61.2	59.0	57.5	55.0	54.3	53.2	53.3	51.6	51.6
85°	36.0	34.5	33.0	31.4	31.4	29.1	29.9	29.1	29.1	27.6	26.8
87.5°	12.8	12.4	11.3	11.5	11.7	11.3	11.4	10.9	11.0	11.1	10.6
90°	5.6	6.7	7.7	8.6	9.5	10.4	11.0	11.6	12.2	12.8	13.2
92.5°	10.1	10.3	10.7	11.2	11.6	12.1	12.4	12.7	13.0	13.3	13.5
95°	18.6	17.1	17.9	18.7	19.5	20.4	20.9	21.5	22.1	22.7	22.9
97.5°	24.2	19.7	21.6	23.5	25.4	27.2	27.7	28.2	28.6	29.1	29.4
100°	28.8	21.9	23.8	25.8	27.8	29.7	30.7	31.6	32.5	33.5	34.0
102.5°	106.5	96.5	80.1	63.6	47.1	30.6	31.8	33.0	34.2	35.4	36.2
105°	172.6	158.5	126.8	95.2	63.5	31.8	33.1	34.4	35.7	36.9	37.8
107.5°	214.0	196.4	158.5	120.5	82.5	44.6	43.3	42.0	40.7	39.4	39.0
110°	240.9	225.4	191.9	158.4	124.8	91.3	79.7	68.1	56.5	44.9	39.4



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	266.5	263.5	255.2	246.9	238.6	230.4	188.0	145.7	103.4	61.1	40.2
115°	308.0	310.4	313.3	316.2	319.1	322.0	268.3	214.6	160.9	107.2	76.2
117.5°	346.6	348.7	350.7	352.7	354.7	356.6	343.7	330.7	317.7	304.7	284.5
120°	372.3	374.2	376.3	378.4	380.4	382.5	383.9	385.3	386.7	388.1	381.0
122.5°	396.0	398.1	400.3	402.6	404.9	407.2	408.0	408.8	409.7	410.5	409.4
125°	430.3	432.2	434.4	436.6	438.8	441.0	441.8	442.6	443.4	444.2	444.8
127.5°	463.2	464.9	466.5	468.2	469.8	471.5	472.6	473.8	475.0	476.2	476.8
130°	484.4	486.0	487.3	488.5	489.8	491.1	492.4	493.6	494.9	496.2	496.8
132.5°	504.2	505.6	506.9	508.2	509.4	510.7	511.8	512.9	514.0	515.1	515.5
135°	532.4	533.9	534.9	536.0	537.0	538.0	539.2	540.4	541.5	542.7	543.2
137.5°	557.6	558.9	560.1	561.3	562.4	563.6	564.8	565.9	567.0	568.2	568.5
140°	574.1	575.2	576.5	577.8	579.0	580.3	581.4	582.4	583.4	584.5	584.7
142.5°	588.8	589.9	591.4	592.8	594.3	595.8	596.7	597.7	598.6	599.6	599.8
145°	608.6	609.5	611.5	613.4	615.4	617.4	618.2	619.0	619.8	620.6	620.7
147.5°	627.8	628.6	630.5	632.5	634.4	636.4	637.0	637.6	638.2	638.8	638.8
150°	639.7	640.2	642.1	643.9	645.8	647.6	648.3	649.0	649.7	650.4	650.5
152.5°	650.6	651.0	652.8	654.6	656.3	658.1	658.8	659.5	660.2	660.9	660.8
155°	666.4	666.6	668.0	669.4	670.8	672.2	672.9	673.6	674.3	675.0	674.8
157.5°	679.9	680.0	680.9	681.9	682.9	683.9	684.6	685.4	686.2	687.0	687.0
160°	688.2	688.2	688.9	689.6	690.3	691.0	691.7	692.3	693.0	693.7	693.7
162.5°	694.9	694.8	695.4	696.0	696.6	697.2	698.0	698.8	699.6	700.4	700.3
165°	703.8	703.7	704.0	704.3	704.7	705.0	705.9	706.7	707.5	708.3	708.3
167.5°	710.5	710.3	710.6	711.0	711.3	711.6	712.4	713.2	714.1	714.9	714.8
170°	714.3	714.0	714.3	714.5	714.7	715.0	715.8	716.6	717.4	718.2	718.1
172.5°	716.8	716.5	716.8	717.0	717.2	717.5	718.3	719.1	719.9	720.7	720.6
175°	719.5	719.3	719.5	719.7	719.9	720.2	721.0	721.8	722.6	723.4	723.3
177.5°	720.7	720.4	720.5	720.6	720.7	720.8	721.5	722.1	722.8	723.4	723.3
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2117.8	2119.0	2117.2	2118.4	2117.2	2119.0	2117.8	2124.5	2125.7	2127.0	2125.7
5°	1973.2	1964.0	1962.5	1960.2	1962.5	1964.0	1973.2	1977.1	1980.1	1986.3	1997.0
7.5°	1800.7	1799.3	1795.5	1790.1	1795.5	1799.3	1800.7	1813.8	1824.3	1836.2	1858.1
10°	1689.7	1685.9	1685.1	1679.7	1685.1	1685.9	1689.7	1706.6	1718.8	1735.7	1765.6
12.5°	1559.7	1535.1	1532.5	1519.1	1532.5	1535.1	1559.7	1581.5	1614.6	1630.9	1662.6
15°	1328.0	1323.4	1308.1	1298.1	1308.1	1323.4	1328.0	1346.4	1358.7	1403.1	1454.5
17.5°	1195.6	1180.6	1175.8	1173.7	1175.8	1180.6	1195.6	1204.5	1222.0	1245.4	1276.4
20°	1110.4	1096.6	1094.3	1092.8	1094.3	1096.6	1110.4	1121.1	1134.9	1160.2	1192.4
22.5°	1051.5	1037.1	1031.1	1026.5	1031.1	1037.1	1051.5	1059.8	1072.4	1092.1	1113.9
25°	951.0	945.6	942.6	941.0	942.6	945.6	951.0	958.7	970.9	997.7	1020.7
27.5°	872.4	860.6	858.3	854.3	858.3	860.6	872.4	886.0	898.7	910.8	931.4
30°	827.6	823.8	818.4	813.8	818.4	823.8	827.6	834.5	842.9	863.6	883.6
32.5°	774.9	771.7	766.9	764.8	766.9	771.7	774.9	784.2	801.9	814.6	829.0
35°	716.5	705.8	701.2	694.3	701.2	705.8	716.5	724.2	731.1	741.8	767.8
37.5°	654.7	649.1	642.6	644.9	642.6	649.1	654.7	658.0	672.5	687.4	698.7
40°	606.9	603.1	601.6	600.8	601.6	603.1	606.9	616.9	634.5	641.4	658.3
42.5°	568.9	558.3	554.3	554.2	554.3	558.3	568.9	580.1	591.0	602.2	619.6
45°	511.1	501.2	494.3	495.0	494.3	501.2	511.1	515.0	524.2	546.4	556.3
47.5°	452.0	451.7	447.4	448.7	447.4	451.7	452.0	458.6	470.4	484.0	499.9
50°	423.8	419.2	416.1	416.9	416.1	419.2	423.8	429.1	436.0	442.9	467.4
52.5°	396.8	392.8	390.4	393.6	390.4	392.8	396.8	399.7	404.8	411.7	428.2
55°	352.5	347.9	347.1	346.4	347.1	347.9	352.5	356.3	362.5	367.8	375.5
57.5°	303.0	299.9	295.3	293.3	295.3	299.9	303.0	308.7	316.0	323.1	331.0
60°	267.4	261.3	253.6	252.9	253.6	261.3	267.4	277.4	280.5	291.2	300.4
62.5°	234.9	233.7	232.2	232.0	232.2	233.7	234.9	238.2	242.5	258.1	269.1
65°	206.1	205.4	206.1	206.9	206.1	205.4	206.1	207.7	208.4	210.0	214.6
67.5°	179.6	178.2	176.9	177.5	176.9	178.2	179.6	179.9	182.1	183.0	186.2
70°	159.4	158.6	157.9	157.9	157.9	158.6	159.4	160.9	162.5	164.0	167.8
72.5°	139.8	139.6	138.9	138.2	138.9	139.6	139.8	142.5	143.5	145.0	147.6
75°	111.9	110.3	110.3	110.3	110.3	110.3	111.9	112.6	113.4	115.7	117.2
77.5°	85.2	84.4	83.7	83.1	83.7	84.4	85.2	85.4	86.6	87.1	88.7
80°	67.4	66.7	65.9	65.9	65.9	66.7	67.4	68.2	68.2	70.5	69.7
82.5°	51.5	50.7	50.6	50.0	50.6	50.7	51.5	51.6	51.6	53.3	53.2
85°	27.6	28.4	27.6	29.1	27.6	28.4	27.6	26.8	27.6	29.1	29.1
87.5°	10.6	10.1	10.7	10.2	10.7	10.1	10.6	10.6	11.1	11.0	10.9
90°	13.4	13.6	13.9	14.1	13.9	13.6	13.4	13.2	12.8	12.2	11.6
92.5°	13.7	13.8	14.0	14.1	14.0	13.8	13.7	13.5	13.3	13.0	12.7
95°	22.8	22.7	22.6	22.4	22.6	22.7	22.8	22.9	22.7	22.1	21.5
97.5°	29.5	29.7	29.8	30.0	29.8	29.7	29.5	29.4	29.1	28.6	28.2
100°	34.3	34.5	34.7	35.0	34.7	34.5	34.3	34.0	33.5	32.5	31.6
102.5°	36.5	36.8	37.1	37.5	37.1	36.8	36.5	36.2	35.4	34.2	33.0
105°	38.3	38.7	39.2	39.7	39.2	38.7	38.3	37.8	36.9	35.7	34.4
107.5°	39.4	39.9	40.3	40.8	40.3	39.9	39.4	39.0	39.4	40.7	42.0
110°	39.8	40.3	40.8	41.2	40.8	40.3	39.8	39.4	44.9	56.5	68.1



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	40.5	40.9	41.3	41.6	41.3	40.9	40.5	40.2	61.1	103.4	145.7
115°	67.8	59.5	51.1	42.8	51.1	59.5	67.8	76.2	107.2	160.9	214.6
117.5°	257.0	229.6	202.2	174.7	202.2	229.6	257.0	284.5	304.7	317.7	330.7
120°	365.3	349.7	334.0	318.3	334.0	349.7	365.3	381.0	388.1	386.7	385.3
122.5°	406.4	403.3	400.3	397.2	400.3	403.3	406.4	409.4	410.5	409.7	408.8
125°	445.2	445.5	445.9	446.2	445.9	445.5	445.2	444.8	444.2	443.4	442.6
127.5°	476.9	477.0	477.0	477.1	477.0	477.0	476.9	476.8	476.2	475.0	473.8
130°	496.6	496.5	496.4	496.3	496.4	496.5	496.6	496.8	496.2	494.9	493.6
132.5°	515.4	515.3	515.2	515.1	515.2	515.3	515.4	515.5	515.1	514.0	512.9
135°	542.9	542.7	542.5	542.2	542.5	542.7	542.9	543.2	542.7	541.5	540.4
137.5°	568.1	567.7	567.4	567.0	567.4	567.7	568.1	568.5	568.2	567.0	565.9
140°	584.1	583.6	583.0	582.4	583.0	583.6	584.1	584.7	584.5	583.4	582.4
142.5°	599.2	598.6	598.0	597.4	598.0	598.6	599.2	599.8	599.6	598.6	597.7
145°	620.2	619.6	619.0	618.4	619.0	619.6	620.2	620.7	620.6	619.8	619.0
147.5°	638.4	637.9	637.4	636.9	637.4	637.9	638.4	638.8	638.8	638.2	637.6
150°	649.9	649.3	648.7	648.2	648.7	649.3	649.9	650.5	650.4	649.7	649.0
152.5°	660.1	659.3	658.5	657.8	658.5	659.3	660.1	660.8	660.9	660.2	659.5
155°	673.9	673.0	672.1	671.1	672.1	673.0	673.9	674.8	675.0	674.3	673.6
157.5°	686.0	685.1	684.2	683.3	684.2	685.1	686.0	687.0	687.0	686.2	685.4
160°	692.9	692.1	691.2	690.4	691.2	692.1	692.9	693.7	693.7	693.0	692.3
162.5°	699.3	698.3	697.3	696.3	697.3	698.3	699.3	700.3	700.4	699.6	698.8
165°	707.5	706.7	705.9	705.0	705.9	706.7	707.5	708.3	708.3	707.5	706.7
167.5°	713.7	712.7	711.6	710.6	711.6	712.7	713.7	714.8	714.9	714.1	713.2
170°	717.0	716.0	715.0	713.9	715.0	716.0	717.0	718.1	718.2	717.4	716.6
172.5°	719.6	718.5	717.5	716.4	717.5	718.5	719.6	720.6	720.7	719.9	719.1
175°	722.1	720.9	719.8	718.6	719.8	720.9	722.1	723.3	723.4	722.6	721.8
177.5°	722.5	721.6	720.8	720.0	720.8	721.6	722.5	723.3	723.4	722.8	722.1
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2120.8	2129.4	2142.3	2149.6	2161.9	2169.9	2174.2	2182.1	2186.4	2201.8	2217.7
5°	2002.4	2014.6	2036.1	2056.0	2077.5	2099.7	2115.8	2134.2	2151.0	2180.1	2210.8
7.5°	1866.6	1883.6	1916.8	1948.6	1986.0	2017.4	2045.1	2076.5	2104.6	2146.3	2189.8
10°	1764.8	1794.7	1838.4	1868.3	1917.3	1948.7	1992.4	2026.9	2066.0	2121.1	2170.2
12.5°	1677.1	1713.2	1748.3	1789.8	1833.9	1886.2	1934.2	1978.5	2024.9	2081.9	2139.5
15°	1518.1	1570.2	1624.6	1666.7	1726.5	1781.7	1837.6	1897.4	1954.1	2022.3	2097.4
17.5°	1313.3	1373.7	1465.2	1537.4	1607.6	1662.9	1732.2	1804.5	1871.3	1953.6	2037.2
20°	1220.7	1265.2	1327.2	1424.6	1530.3	1589.3	1659.8	1739.5	1816.1	1905.8	1995.5
22.5°	1146.5	1186.1	1235.9	1311.8	1429.8	1510.2	1583.8	1664.7	1753.6	1845.1	1944.6
25°	1040.6	1068.2	1120.3	1181.6	1262.9	1395.4	1475.9	1557.1	1653.7	1751.8	1865.2
27.5°	961.1	985.9	1019.8	1078.3	1138.7	1233.9	1361.9	1450.5	1546.7	1657.1	1774.8
30°	900.4	929.5	967.1	1008.5	1074.4	1148.7	1276.7	1379.4	1474.4	1587.8	1713.5
32.5°	856.3	879.3	911.3	953.3	1008.2	1079.4	1181.6	1306.4	1399.0	1518.5	1649.7
35°	783.9	810.8	836.8	876.7	921.1	986.2	1063.6	1197.0	1288.9	1406.9	1538.7
37.5°	724.3	740.7	769.5	801.1	848.0	896.6	963.7	1083.3	1182.7	1298.6	1433.5
40°	678.9	699.6	721.1	756.3	794.7	841.4	907.3	996.2	1110.4	1223.8	1355.6
42.5°	634.8	661.0	683.7	707.3	749.3	796.0	849.7	925.1	1041.7	1149.0	1277.1
45°	581.6	598.5	622.2	648.3	682.8	722.6	770.1	836.0	947.9	1040.6	1161.0
47.5°	519.7	544.4	559.9	585.3	618.1	656.1	700.3	757.3	847.8	934.7	1046.3
50°	477.4	502.7	524.9	547.9	577.0	613.8	650.6	705.8	778.6	869.8	974.0
52.5°	441.2	463.5	485.1	508.1	536.6	570.3	605.2	653.7	716.0	799.9	901.0
55°	391.6	405.4	427.6	450.6	475.9	508.1	541.8	582.4	636.0	706.5	788.5
57.5°	340.7	356.6	374.3	397.4	423.0	447.7	478.0	514.8	557.1	620.9	691.1
60°	311.9	324.1	338.7	362.5	386.2	408.4	437.6	468.2	508.1	563.2	623.0
62.5°	280.0	291.7	305.0	325.7	348.8	369.2	394.6	427.1	460.9	511.1	563.5
65°	226.8	243.7	256.7	275.1	294.3	315.7	335.6	361.7	391.6	431.4	478.2
67.5°	188.1	196.6	208.7	225.4	245.1	263.5	282.3	302.7	328.6	359.4	396.5
70°	170.9	174.0	176.3	192.3	210.7	229.1	246.8	265.9	288.1	313.4	345.6
72.5°	150.7	153.7	156.6	163.5	178.2	196.6	214.9	229.1	250.1	271.1	297.2
75°	119.5	124.1	126.4	130.3	135.6	147.9	164.8	178.5	190.8	206.9	227.6
77.5°	91.0	93.6	96.1	100.1	103.5	109.1	118.6	131.0	142.5	151.9	166.1
80°	72.0	72.8	75.9	77.4	82.0	85.8	90.4	100.4	111.9	115.7	125.7
82.5°	54.3	55.0	57.5	59.0	61.2	64.4	70.2	72.8	81.8	86.9	93.2
85°	29.9	29.1	31.4	31.4	33.0	34.5	36.0	39.8	42.1	48.3	49.8
87.5°	11.4	11.3	11.7	11.5	11.3	12.4	12.8	13.1	14.1	15.7	17.9
90°	11.0	10.4	9.5	8.6	7.7	6.7	5.6	4.3	3.1	1.8	0.5
92.5°	12.4	12.1	11.6	11.2	10.7	10.3	10.1	10.2	10.3	10.4	10.5
95°	20.9	20.4	19.5	18.7	17.9	17.1	18.6	22.4	26.3	30.1	33.9
97.5°	27.7	27.2	25.4	23.5	21.6	19.7	24.2	35.0	45.8	56.5	67.3
100°	30.7	29.7	27.8	25.8	23.8	21.9	28.8	44.7	60.6	76.5	92.4
102.5°	31.8	30.6	47.1	63.6	80.1	96.5	106.5	109.8	113.2	116.6	119.9
105°	33.1	31.8	63.5	95.2	126.8	158.5	172.6	169.1	165.6	162.1	158.6
107.5°	43.3	44.6	82.5	120.5	158.5	196.4	214.0	211.2	208.4	205.6	202.8
110°	79.7	91.3	124.8	158.4	191.9	225.4	240.9	238.5	236.1	233.6	231.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	188.0	230.4	238.6	246.9	255.2	263.5	266.5	264.4	262.2	260.1	257.9
115°	268.3	322.0	319.1	316.2	313.3	310.4	308.0	306.0	304.0	302.0	300.1
117.5°	343.7	356.6	354.7	352.7	350.7	348.7	346.6	344.4	342.2	340.0	337.8
120°	383.9	382.5	380.4	378.4	376.3	374.2	372.3	370.5	368.8	367.0	365.3
122.5°	408.0	407.2	404.9	402.6	400.3	398.1	396.0	394.2	392.4	390.5	388.7
125°	441.8	441.0	438.8	436.6	434.4	432.2	430.3	428.8	427.3	425.8	424.3
127.5°	472.6	471.5	469.8	468.2	466.5	464.9	463.2	461.5	459.9	458.2	456.5
130°	492.4	491.1	489.8	488.5	487.3	486.0	484.4	482.6	480.7	478.8	477.0
132.5°	511.8	510.7	509.4	508.2	506.9	505.6	504.2	502.6	501.0	499.4	497.9
135°	539.2	538.0	537.0	536.0	534.9	533.9	532.4	530.6	528.7	526.9	525.0
137.5°	564.8	563.6	562.4	561.3	560.1	558.9	557.6	556.3	555.0	553.7	552.5
140°	581.4	580.3	579.0	577.8	576.5	575.2	574.1	573.2	572.3	571.3	570.4
142.5°	596.7	595.8	594.3	592.8	591.4	589.9	588.8	587.9	587.1	586.3	585.4
145°	618.2	617.4	615.4	613.4	611.5	609.5	608.6	608.7	608.8	608.9	609.0
147.5°	637.0	636.4	634.4	632.5	630.5	628.6	627.8	628.3	628.7	629.1	629.6
150°	648.3	647.6	645.8	643.9	642.1	640.2	639.7	640.5	641.3	642.1	642.9
152.5°	658.8	658.1	656.3	654.6	652.8	651.0	650.6	651.5	652.4	653.3	654.2
155°	672.9	672.2	670.8	669.4	668.0	666.6	666.4	667.5	668.5	669.6	670.6
157.5°	684.6	683.9	682.9	681.9	680.9	680.0	679.9	680.8	681.7	682.6	683.4
160°	691.7	691.0	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0
162.5°	698.0	697.2	696.6	696.0	695.4	694.8	694.9	695.5	696.2	696.9	697.6
165°	705.9	705.0	704.7	704.3	704.0	703.7	703.8	704.5	705.2	705.9	706.6
167.5°	712.4	711.6	711.3	711.0	710.6	710.3	710.5	711.2	711.9	712.6	713.3
170°	715.8	715.0	714.7	714.5	714.3	714.0	714.3	715.0	715.7	716.4	717.0
172.5°	718.3	717.5	717.2	717.0	716.8	716.5	716.8	717.5	718.2	718.9	719.6
175°	721.0	720.2	719.9	719.7	719.5	719.3	719.5	720.4	721.2	722.0	722.8
177.5°	721.5	720.8	720.7	720.6	720.5	720.4	720.7	721.4	722.0	722.7	723.3
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2218.3	2220.1	2232.4	2237.9	2249.0	2253.2	2258.2	2256.9	2256.9	2259.4	2276.5
5°	2223.1	2238.4	2261.4	2283.6	2305.1	2323.4	2335.7	2348.0	2352.6	2374.8	2394.7
7.5°	2215.1	2243.3	2281.3	2315.2	2355.8	2387.5	2413.9	2437.6	2453.9	2486.2	2519.3
10°	2204.7	2244.5	2287.4	2331.1	2387.0	2429.2	2472.1	2505.1	2515.8	2564.1	2591.7
12.5°	2183.8	2237.2	2291.7	2348.3	2403.0	2461.1	2508.3	2541.2	2578.9	2622.3	2673.2
15°	2152.6	2213.9	2285.1	2357.9	2436.1	2506.6	2557.2	2614.6	2656.0	2703.5	2748.0
17.5°	2107.7	2186.6	2277.2	2361.5	2451.9	2527.6	2597.2	2652.3	2681.5	2708.6	2715.2
20°	2072.1	2157.2	2263.7	2363.3	2453.7	2541.1	2610.0	2656.0	2663.7	2664.4	2623.8
22.5°	2033.5	2129.6	2241.0	2343.1	2451.3	2548.4	2602.1	2621.7	2591.3	2539.4	2460.8
25°	1962.5	2073.6	2203.1	2319.6	2437.6	2529.6	2548.0	2513.5	2407.0	2295.1	2153.3
27.5°	1885.6	2010.5	2149.3	2278.8	2404.5	2461.5	2421.8	2297.5	2105.7	1938.9	1736.8
30°	1829.2	1969.4	2105.8	2250.6	2367.1	2391.6	2300.5	2117.3	1893.5	1642.2	1440.7
32.5°	1764.8	1911.8	2061.7	2211.4	2308.9	2285.0	2134.3	1908.9	1646.5	1399.4	1208.9
35°	1672.8	1824.6	1986.3	2136.5	2198.5	2095.1	1869.8	1576.3	1308.1	1077.4	946.4
37.5°	1566.6	1731.9	1900.0	2037.9	2033.5	1861.1	1554.2	1251.2	1025.8	889.4	796.0
40°	1491.2	1658.3	1839.9	1956.4	1906.6	1682.0	1349.5	1063.6	898.9	790.1	721.9
42.5°	1418.9	1586.6	1767.0	1859.5	1772.9	1496.9	1165.6	941.6	805.7	720.8	665.5
45°	1295.8	1472.8	1639.9	1691.2	1536.4	1232.2	942.6	780.1	689.7	626.8	588.5
47.5°	1175.5	1349.6	1502.1	1503.0	1293.7	999.3	795.1	675.1	597.9	549.3	521.4
50°	1101.9	1267.5	1395.4	1375.5	1138.0	888.9	711.1	607.7	543.3	505.8	476.6
52.5°	1019.2	1179.8	1290.6	1233.9	1006.2	782.2	635.7	548.8	495.5	462.8	436.8
55°	898.9	1041.4	1119.6	1033.7	820.7	650.6	537.2	469.0	429.1	401.5	379.3
57.5°	780.7	898.3	947.5	847.5	676.0	539.5	454.4	403.2	363.7	343.9	332.4
60°	706.5	806.9	841.4	731.1	587.8	472.0	402.3	354.8	325.7	312.7	301.2
62.5°	633.6	715.6	729.8	628.7	512.4	413.2	353.3	313.1	293.8	281.4	270.5
65°	525.7	584.7	577.8	496.6	405.4	328.0	284.3	259.8	245.2	227.6	208.4
67.5°	432.8	468.8	447.1	386.2	309.4	254.9	226.4	207.8	189.7	173.0	168.6
70°	374.0	394.6	371.7	315.7	253.6	213.8	190.8	168.6	157.9	154.0	147.1
72.5°	317.6	324.8	299.9	252.0	206.4	177.0	154.6	142.2	136.4	133.2	128.7
75°	238.3	233.0	211.5	174.0	143.3	123.4	116.5	111.9	108.0	105.0	102.7
77.5°	167.4	159.5	140.4	115.9	99.8	90.3	86.1	83.7	81.8	80.3	78.0
80°	125.7	120.3	101.2	82.8	75.9	71.3	69.0	65.9	65.9	64.4	62.1
82.5°	92.0	86.0	69.3	60.7	56.9	54.1	52.4	50.6	50.0	50.3	48.6
85°	48.3	39.1	34.5	33.0	30.7	29.1	29.9	28.4	28.4	28.4	27.6
87.5°	15.1	12.3	11.9	11.5	12.4	12.6	12.1	12.3	13.1	12.6	13.4
90°	1.8	3.1	4.3	5.6	6.7	7.7	8.6	9.5	10.4	11.0	11.6
92.5°	10.4	10.3	10.2	10.1	10.3	10.7	11.2	11.6	12.1	12.4	12.7
95°	30.1	26.3	22.4	18.6	17.1	17.9	18.7	19.5	20.4	20.9	21.5
97.5°	56.5	45.8	35.0	24.2	19.7	21.6	23.5	25.4	27.2	27.7	28.2
100°	76.5	60.6	44.7	28.8	21.9	23.8	25.8	27.8	29.7	30.7	31.6
102.5°	116.6	113.2	109.8	106.5	96.5	80.1	63.6	47.1	30.6	31.8	33.0
105°	162.1	165.6	169.1	172.6	158.5	126.8	95.2	63.5	31.8	33.1	34.4
107.5°	205.6	208.4	211.2	214.0	196.4	158.5	120.5	82.5	44.6	43.3	42.0
110°	233.6	236.1	238.5	240.9	225.4	191.9	158.4	124.8	91.3	79.7	68.1



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	260.1	262.2	264.4	266.5	263.5	255.2	246.9	238.6	230.4	188.0	145.7
115°	302.0	304.0	306.0	308.0	310.4	313.3	316.2	319.1	322.0	268.3	214.6
117.5°	340.0	342.2	344.4	346.6	348.7	350.7	352.7	354.7	356.6	343.7	330.7
120°	367.0	368.8	370.5	372.3	374.2	376.3	378.4	380.4	382.5	383.9	385.3
122.5°	390.5	392.4	394.2	396.0	398.1	400.3	402.6	404.9	407.2	408.0	408.8
125°	425.8	427.3	428.8	430.3	432.2	434.4	436.6	438.8	441.0	441.8	442.6
127.5°	458.2	459.9	461.5	463.2	464.9	466.5	468.2	469.8	471.5	472.6	473.8
130°	478.8	480.7	482.6	484.4	486.0	487.3	488.5	489.8	491.1	492.4	493.6
132.5°	499.4	501.0	502.6	504.2	505.6	506.9	508.2	509.4	510.7	511.8	512.9
135°	526.9	528.7	530.6	532.4	533.9	534.9	536.0	537.0	538.0	539.2	540.4
137.5°	553.7	555.0	556.3	557.6	558.9	560.1	561.3	562.4	563.6	564.8	565.9
140°	571.3	572.3	573.2	574.1	575.2	576.5	577.8	579.0	580.3	581.4	582.4
142.5°	586.3	587.1	587.9	588.8	589.9	591.4	592.8	594.3	595.8	596.7	597.7
145°	608.9	608.8	608.7	608.6	609.5	611.5	613.4	615.4	617.4	618.2	619.0
147.5°	629.1	628.7	628.3	627.8	628.6	630.5	632.5	634.4	636.4	637.0	637.6
150°	642.1	641.3	640.5	639.7	640.2	642.1	643.9	645.8	647.6	648.3	649.0
152.5°	653.3	652.4	651.5	650.6	651.0	652.8	654.6	656.3	658.1	658.8	659.5
155°	669.6	668.5	667.5	666.4	666.6	668.0	669.4	670.8	672.2	672.9	673.6
157.5°	682.6	681.7	680.8	679.9	680.0	680.9	681.9	682.9	683.9	684.6	685.4
160°	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	691.7	692.3
162.5°	696.9	696.2	695.5	694.9	694.8	695.4	696.0	696.6	697.2	698.0	698.8
165°	705.9	705.2	704.5	703.8	703.7	704.0	704.3	704.7	705.0	705.9	706.7
167.5°	712.6	711.9	711.2	710.5	710.3	710.6	711.0	711.3	711.6	712.4	713.2
170°	716.4	715.7	715.0	714.3	714.0	714.3	714.5	714.7	715.0	715.8	716.6
172.5°	718.9	718.2	717.5	716.8	716.5	716.8	717.0	717.2	717.5	718.3	719.1
175°	722.0	721.2	720.4	719.5	719.3	719.5	719.7	719.9	720.2	721.0	721.8
177.5°	722.7	722.0	721.4	720.7	720.4	720.5	720.6	720.7	720.8	721.5	722.1
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2282.7	2290.6	2294.3	2294.3	2298.6	2296.8	2294.9
5°	2413.9	2428.4	2431.5	2445.3	2455.2	2452.2	2453.7
7.5°	2544.3	2567.7	2590.9	2601.5	2603.1	2609.3	2611.6
10°	2624.6	2643.8	2679.8	2674.4	2701.2	2716.6	2691.3
12.5°	2701.8	2727.7	2752.7	2759.6	2774.8	2779.7	2769.7
15°	2771.7	2785.5	2787.1	2783.2	2787.8	2784.0	2769.4
17.5°	2706.4	2684.1	2638.7	2617.2	2600.2	2575.1	2565.0
20°	2598.5	2532.6	2456.0	2425.4	2389.3	2318.8	2335.7
22.5°	2365.6	2290.5	2213.9	2124.4	2081.6	2014.8	2010.8
25°	2003.1	1873.6	1731.1	1631.5	1573.2	1506.6	1477.4
27.5°	1557.4	1394.4	1277.6	1218.4	1164.6	1111.8	1109.6
30°	1264.4	1141.8	1051.4	1000.8	967.8	945.6	950.2
32.5°	1065.8	981.8	920.8	878.8	854.4	837.7	837.4
35°	871.3	813.8	774.7	757.1	739.5	727.2	728.0
37.5°	745.6	711.1	689.4	669.9	658.9	652.9	649.5
40°	681.2	652.9	636.0	624.5	615.3	606.9	605.4
42.5°	630.4	606.9	590.1	581.0	572.4	566.5	564.9
45°	559.4	540.2	524.9	515.0	511.1	505.8	505.8
47.5°	497.6	478.8	466.8	460.6	454.0	450.4	450.3
50°	456.0	441.4	430.7	426.8	421.5	419.2	418.4
52.5°	418.6	407.7	400.0	397.4	395.1	392.2	392.7
55°	367.8	361.7	358.6	356.3	352.5	347.9	351.0
57.5°	325.1	319.9	311.6	304.4	300.9	297.6	298.9
60°	295.0	284.3	273.6	265.1	262.8	255.9	255.9
62.5°	257.0	242.0	228.8	224.1	221.8	218.6	217.9
65°	197.7	191.6	188.5	185.4	183.9	183.9	182.4
67.5°	163.8	161.4	158.0	157.2	155.7	155.3	154.8
70°	144.8	141.8	140.2	139.5	137.9	138.7	136.4
72.5°	126.4	124.0	123.7	121.7	120.8	120.9	119.2
75°	99.6	99.6	98.9	98.1	96.6	95.8	96.6
77.5°	76.6	76.8	75.4	75.3	75.1	75.3	74.5
80°	61.3	62.1	61.3	60.5	59.8	60.5	59.8
82.5°	48.4	47.4	47.2	47.1	46.9	46.4	46.3
85°	27.6	28.4	27.6	26.8	26.8	26.8	27.6
87.5°	12.9	13.0	13.1	13.1	13.1	13.2	12.6
90°	12.2	12.8	13.2	13.4	13.6	13.9	14.1
92.5°	13.0	13.3	13.5	13.7	13.8	14.0	14.1
95°	22.1	22.7	22.9	22.8	22.7	22.6	22.4
97.5°	28.6	29.1	29.4	29.5	29.7	29.8	30.0
100°	32.5	33.5	34.0	34.3	34.5	34.7	35.0
102.5°	34.2	35.4	36.2	36.5	36.8	37.1	37.5
105°	35.7	36.9	37.8	38.3	38.7	39.2	39.7
107.5°	40.7	39.4	39.0	39.4	39.9	40.3	40.8
110°	56.5	44.9	39.4	39.8	40.3	40.8	41.2



TEST NUMBER: P331741

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	103.4	61.1	40.2	40.5	40.9	41.3	41.6
115°	160.9	107.2	76.2	67.8	59.5	51.1	42.8
117.5°	317.7	304.7	284.5	257.0	229.6	202.2	174.7
120°	386.7	388.1	381.0	365.3	349.7	334.0	318.3
122.5°	409.7	410.5	409.4	406.4	403.3	400.3	397.2
125°	443.4	444.2	444.8	445.2	445.5	445.9	446.2
127.5°	475.0	476.2	476.8	476.9	477.0	477.0	477.1
130°	494.9	496.2	496.8	496.6	496.5	496.4	496.3
132.5°	514.0	515.1	515.5	515.4	515.3	515.2	515.1
135°	541.5	542.7	543.2	542.9	542.7	542.5	542.2
137.5°	567.0	568.2	568.5	568.1	567.7	567.4	567.0
140°	583.4	584.5	584.7	584.1	583.6	583.0	582.4
142.5°	598.6	599.6	599.8	599.2	598.6	598.0	597.4
145°	619.8	620.6	620.7	620.2	619.6	619.0	618.4
147.5°	638.2	638.8	638.8	638.4	637.9	637.4	636.9
150°	649.7	650.4	650.5	649.9	649.3	648.7	648.2
152.5°	660.2	660.9	660.8	660.1	659.3	658.5	657.8
155°	674.3	675.0	674.8	673.9	673.0	672.1	671.1
157.5°	686.2	687.0	687.0	686.0	685.1	684.2	683.3
160°	693.0	693.7	693.7	692.9	692.1	691.2	690.4
162.5°	699.6	700.4	700.3	699.3	698.3	697.3	696.3
165°	707.5	708.3	708.3	707.5	706.7	705.9	705.0
167.5°	714.1	714.9	714.8	713.7	712.7	711.6	710.6
170°	717.4	718.2	718.1	717.0	716.0	715.0	713.9
172.5°	719.9	720.7	720.6	719.6	718.5	717.5	716.4
175°	722.6	723.4	723.3	722.1	720.9	719.8	718.6
177.5°	722.8	723.4	723.3	722.5	721.6	720.8	720.0
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2

(END OF REPORT)