

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331619

Luminaire Tested: **S122RDIP-S290D330U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331619
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D330U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2204.7 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331619

CATALOG NUMBER: S122RDIP-S290D330U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331619

CATALOG NUMBER: S122RDIP-S290D330U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331619

CATALOG NUMBER: S122RDIP-S290D330U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	2.1
10°-20°	129.0	5.9
20°-30°	181.2	8.2
30°-40°	197.6	9.0
40°-50°	181.6	8.2
50°-60°	142.7	6.5
60°-70°	93.0	4.2
70°-80°	48.0	2.2
80°-90°	14.1	0.6
90°-100°	26.5	1.2
100°-110°	82.4	3.7
110°-120°	140.8	6.4
120°-130°	185.2	8.4
130°-140°	207.9	9.4
140°-150°	203.8	9.2
150°-160°	171.0	7.8
160°-170°	113.4	5.1
170°-180°	39.6	1.8
0°-30°	357.2	16.2
0°-40°	554.7	25.2
0°-60°	879.0	39.9
0°-90°	1034.1	46.9
90°-120°	249.8	11.3
90°-150°	846.7	38.4
90°-180°	1171.0	53.1
0°-180°	2204.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	0	5	12	12	12	2
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	143	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	205
145°	323	325	328	328	326	202
155°	369	370	371	373	372	170
165°	402	401	401	404	402	113
175°	418	417	416	418	416	40
180°	419	419	419	419	419	



TEST NUMBER: P331619

CATALOG NUMBER: S122RDIP-S290D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	5.9	5.4	5.0	4.5	4.1	4.0	4.3	4.7	5.0	5.4	5.3
90°	0.4	1.3	2.2	3.2	4.1	5.5	7.2	8.9	10.6	12.4	12.2
92.5°	6.3	7.0	7.7	8.4	9.1	9.6	10.0	10.4	10.8	11.2	11.3
95°	18.4	19.2	19.9	20.7	21.5	22.0	22.1	22.3	22.5	22.6	22.6
97.5°	33.6	34.3	34.9	35.6	36.3	36.8	37.1	37.4	37.7	38.0	38.0
100°	44.9	45.5	46.1	46.8	47.4	47.8	48.0	48.3	48.5	48.8	48.8
102.5°	56.7	57.2	57.7	58.2	58.7	59.2	59.4	59.7	60.0	60.3	60.4
105°	76.0	76.2	76.4	76.7	76.9	77.1	77.3	77.4	77.6	77.7	77.9
107.5°	95.3	95.7	96.0	96.4	96.7	96.9	96.9	96.9	96.9	96.9	96.9
110°	107.8	108.2	108.7	109.2	109.6	109.9	109.9	109.9	109.9	109.9	109.9



TEST NUMBER: P331619

CATALOG NUMBER: S122RDIP-S290D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.3	121.8	122.3	122.7	123.2	123.4	123.3	123.3	123.2	123.2	123.0
115°	141.3	141.8	142.3	142.7	143.2	143.4	143.2	143.0	142.9	142.7	142.7
117.5°	161.2	161.9	162.5	163.1	163.8	163.9	163.4	163.0	162.5	162.1	161.9
120°	174.5	175.2	175.8	176.4	177.0	177.0	176.4	175.8	175.2	174.5	174.5
122.5°	186.7	187.4	188.2	188.9	189.7	189.9	189.4	189.0	188.5	188.1	187.9
125°	205.6	206.3	207.0	207.7	208.4	208.7	208.4	208.2	208.0	207.7	207.5
127.5°	224.1	225.0	225.9	226.7	227.6	227.9	227.7	227.4	227.1	226.8	226.5
130°	235.7	236.7	237.7	238.7	239.7	240.2	240.0	239.9	239.7	239.5	239.4
132.5°	248.7	249.5	250.3	251.1	252.0	252.4	252.4	252.5	252.5	252.5	252.2
135°	266.0	266.9	267.8	268.6	269.5	270.0	270.2	270.3	270.5	270.6	270.5
137.5°	284.3	285.0	285.7	286.5	287.2	287.6	287.8	288.0	288.2	288.4	288.4
140°	295.4	296.1	296.8	297.5	298.2	298.7	299.1	299.5	299.9	300.3	300.3
142.5°	306.7	307.4	308.1	308.8	309.5	310.0	310.2	310.5	310.8	311.0	311.1
145°	322.9	323.5	324.0	324.6	325.1	325.6	326.1	326.6	327.0	327.5	327.6
147.5°	337.4	338.1	338.7	339.4	340.0	340.5	340.8	341.2	341.5	341.8	342.0
150°	347.3	347.8	348.2	348.7	349.2	349.6	349.9	350.2	350.5	350.8	351.1
152.5°	356.1	356.5	357.0	357.5	357.9	358.4	358.7	359.1	359.5	359.9	360.2
155°	369.2	369.4	369.7	369.9	370.1	370.4	370.6	370.8	371.1	371.3	371.7
157.5°	380.4	380.6	380.7	380.9	381.1	381.2	381.4	381.5	381.6	381.8	382.3
160°	387.2	387.4	387.5	387.7	387.8	388.0	388.0	388.1	388.2	388.3	388.7
162.5°	393.4	393.5	393.5	393.5	393.6	393.6	393.7	393.8	393.9	393.9	394.5
165°	401.7	401.6	401.5	401.5	401.4	401.3	401.3	401.3	401.3	401.3	401.9
167.5°	408.6	408.4	408.2	407.9	407.7	407.6	407.5	407.5	407.5	407.5	408.0
170°	412.3	412.1	411.8	411.6	411.4	411.2	411.1	411.0	411.0	410.9	411.4
172.5°	414.8	414.6	414.4	414.1	413.9	413.7	413.7	413.6	413.5	413.4	414.0
175°	418.0	417.7	417.5	417.2	417.0	416.8	416.7	416.5	416.3	416.2	416.7
177.5°	419.2	419.0	418.8	418.7	418.5	418.3	418.2	418.1	417.9	417.8	418.2
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7



TEST NUMBER: P331619

CATALOG NUMBER: S122RDIP-S290D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	5.2	5.0	4.9	4.9	4.9	4.9	4.9	4.9
90°	12.1	11.9	11.7	11.7	11.8	11.9	11.9	12.0
92.5°	11.3	11.3	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.6	22.6	22.6	22.5	22.4	22.2	22.1	21.9
97.5°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.9
100°	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.4
102.5°	60.5	60.5	60.6	60.6	60.5	60.4	60.4	60.3
105°	78.0	78.2	78.4	78.4	78.4	78.4	78.4	78.4
107.5°	97.0	97.1	97.1	97.0	96.6	96.3	95.9	95.5
110°	109.9	109.9	109.9	109.8	109.5	109.3	109.1	108.8



TEST NUMBER: P331619

CATALOG NUMBER: S122RDIP-S290D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	122.6	122.4	122.2	122.1	121.9	121.7	121.5
115°	142.6	142.5	142.4	142.3	142.0	141.8	141.6	141.3
117.5°	161.7	161.5	161.3	161.1	160.9	160.7	160.4	160.2
120°	174.5	174.5	174.5	174.4	174.2	173.9	173.7	173.5
122.5°	187.7	187.5	187.3	187.2	187.0	186.8	186.6	186.5
125°	207.3	207.0	206.8	206.6	206.6	206.5	206.4	206.3
127.5°	226.3	226.0	225.7	225.4	225.2	224.9	224.7	224.4
130°	239.2	239.1	238.9	238.7	238.4	238.0	237.7	237.4
132.5°	251.8	251.5	251.2	250.9	250.6	250.4	250.1	249.9
135°	270.5	270.4	270.3	270.2	269.9	269.7	269.5	269.2
137.5°	288.3	288.2	288.2	288.0	287.7	287.4	287.1	286.7
140°	300.3	300.3	300.3	300.1	299.8	299.5	299.2	298.9
142.5°	311.2	311.2	311.3	311.2	310.9	310.5	310.2	309.9
145°	327.7	327.7	327.8	327.7	327.4	327.1	326.8	326.4
147.5°	342.1	342.3	342.5	342.4	342.1	341.8	341.5	341.2
150°	351.3	351.5	351.8	351.8	351.5	351.3	351.1	350.8
152.5°	360.5	360.8	361.1	361.1	360.8	360.5	360.2	359.9
155°	372.1	372.5	372.9	373.0	372.7	372.5	372.3	372.0
157.5°	382.8	383.4	383.9	384.0	383.6	383.2	382.9	382.5
160°	389.2	389.7	390.2	390.2	389.9	389.6	389.3	389.0
162.5°	395.0	395.5	396.1	396.1	395.8	395.4	395.0	394.6
165°	402.4	403.0	403.5	403.6	403.2	402.8	402.4	402.1
167.5°	408.6	409.1	409.7	409.8	409.4	408.9	408.5	408.1
170°	412.0	412.5	413.1	413.1	412.7	412.2	411.7	411.2
172.5°	414.5	415.1	415.6	415.7	415.2	414.7	414.3	413.8
175°	417.3	417.8	418.4	418.4	418.0	417.5	417.0	416.5
177.5°	418.6	418.9	419.3	419.3	418.9	418.6	418.2	417.8
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7

(END OF REPORT)