

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331626

Luminaire Tested: **S122RDIP-S290D530U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331626
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D530U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3098.7 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331626

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331626

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331626

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.5
10°-20°	129.0	4.2
20°-30°	181.2	5.8
30°-40°	197.6	6.4
40°-50°	181.6	5.9
50°-60°	142.7	4.6
60°-70°	93.0	3.0
70°-80°	48.0	1.5
80°-90°	15.1	0.5
90°-100°	118.6	3.8
100°-110°	402.4	13.0
110°-120°	427.5	13.8
120°-130°	351.9	11.4
130°-140°	282.6	9.1
140°-150°	213.5	6.9
150°-160°	150.1	4.8
160°-170°	88.3	2.9
170°-180°	28.8	0.9
0°-30°	357.2	11.5
0°-40°	554.7	17.9
0°-60°	879.0	28.4
0°-90°	1035.1	33.4
90°-120°	948.4	30.6
90°-150°	1796.4	58.0
90°-180°	2064.0	66.6
0°-180°	3098.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	8	19	18	19	2
95°	20	49	224	84	65	21
105°	70	105	423	755	643	74
115°	123	155	354	730	846	122
125°	171	202	340	591	686	152
135°	201	240	336	497	569	155
145°	229	263	334	415	454	144
155°	261	281	324	367	382	120
165°	284	293	311	330	335	80
175°	296	296	299	303	302	28
180°	296	296	296	296	296	



TEST NUMBER: P331626

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	5.9	5.6	5.4	5.0	4.6	4.6	5.2	6.0	6.7	6.8	6.6
90°	0.6	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8
92.5°	7.0	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6
95°	20.0	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6
97.5°	32.5	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3
100°	43.9	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6
102.5°	54.4	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9
105°	69.6	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3
107.5°	86.0	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2
110°	96.9	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7



TEST NUMBER: P331626

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.0	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8
115°	122.6	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7
117.5°	138.8	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6
120°	148.8	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5
122.5°	158.4	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7
125°	171.1	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6
127.5°	181.1	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4
130°	187.1	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5
132.5°	192.5	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0
135°	200.7	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4
137.5°	208.5	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0
140°	214.4	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9
142.5°	220.4	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7
145°	229.3	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4
147.5°	238.8	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1
150°	245.2	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5
152.5°	251.6	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3
155°	260.6	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3
157.5°	268.1	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7
160°	273.2	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6
162.5°	278.2	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0
165°	284.0	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9
167.5°	288.8	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0
170°	292.0	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8
172.5°	293.8	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6
175°	296.0	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4
177.5°	297.0	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331626

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	6.4	6.1	6.2	6.3	6.3	6.3	6.3	6.3
90°	18.2	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	49.7	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	149.4	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	348.7	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	520.7	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	633.4	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	692.9	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	650.0	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	613.1	715.1	788.1	834.9	859.4	870.3	875.4	874.8



TEST NUMBER: P331626

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	579.3	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	537.8	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	506.5	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	491.0	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	478.7	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	460.8	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	443.1	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	431.7	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	420.8	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	405.5	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	393.3	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	385.5	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	379.1	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	370.1	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	363.2	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	358.1	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	353.1	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	346.2	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	338.1	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	333.0	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	328.0	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	320.5	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	313.3	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	309.7	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	305.6	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.1	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)