

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331981-927

Luminaire Tested: **S123DIP-S775D805U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331981-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4814.4 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331981-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331981-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52				
1	98	94	90	86	91	87	84	80	74	72	69	62	60	59	51	50	49	44				
2	89	82	76	70	82	76	71	66	65	61	57	55	52	49	45	43	41	37				
3	82	72	65	59	75	67	60	55	57	52	48	48	45	41	40	37	35	31				
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27				
5	68	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	16				
9	50	38	31	25	47	36	29	24	31	26	22	27	22	19	23	19	17	14				
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10384	10384	10384
5°	10432	10289	10361
10°	10363	10200	10263
15°	10242	10085	10104
20°	10100	9919	9929
25°	9911	9723	9704
30°	9701	9506	9434
35°	9483	9276	9155
40°	9254	9021	8882
45°	9003	8788	8573
50°	8751	8500	8264
55°	8422	8203	7955
60°	8088	7858	7608
65°	7796	7480	7246
70°	7361	7046	6735
75°	6729	6488	6209
80°	6069	5808	5759
85°	5323	5125	4915



TEST NUMBER: P331981-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.9
10°-20°	256.6	5.3
20°-30°	379.0	7.9
30°-40°	442.7	9.2
40°-50°	445.1	9.2
50°-60°	391.0	8.1
60°-70°	291.3	6.1
70°-80°	166.0	3.4
80°-90°	50.0	1.0
90°-100°	170.3	3.5
100°-110°	482.1	10.0
110°-120°	474.3	9.9
120°-130°	378.3	7.9
130°-140°	298.3	6.2
140°-150°	222.6	4.6
150°-160°	155.2	3.2
160°-170°	91.2	1.9
170°-180°	29.7	0.6
0°-30°	726.5	15.1
0°-40°	1169.2	24.3
0°-60°	2005.3	41.7
0°-90°	2512.6	52.2
90°-120°	1126.7	23.4
90°-150°	2025.9	42.1
90°-180°	2302.0	47.8
0°-180°	4814.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	965	965	965	965	965	
5°	966	961	952	960	959	91
15°	919	915	905	911	907	259
25°	834	829	819	819	817	384
35°	722	716	706	701	697	451
45°	591	588	577	568	563	456
55°	449	447	437	428	424	402
65°	306	302	294	287	284	302
75°	162	158	156	152	149	173
85°	43	42	42	40	40	47
90°	1	7	15	17	18	4
95°	21	68	367	107	72	23
105°	72	106	498	871	788	76
115°	127	158	381	835	958	126
125°	176	208	356	644	756	157
135°	207	247	350	530	612	160
145°	236	270	346	435	479	148
155°	268	289	335	381	397	123
165°	293	301	321	340	346	83
175°	305	306	308	312	312	29
180°	306	306	306	306	306	



TEST NUMBER: P331981-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	968.0	967.4	966.9	966.2	965.7	964.6	962.9	961.3	959.6	958.1	959.5
5°	965.5	964.6	963.7	962.7	961.8	960.4	958.3	956.3	954.3	952.2	954.1
7.5°	956.1	955.1	954.2	953.3	952.4	950.9	948.7	946.7	944.5	942.5	944.1
10°	948.1	947.1	946.3	945.3	944.4	942.8	940.3	937.9	935.6	933.2	934.9
12.5°	937.5	936.7	936.0	935.2	934.4	932.9	930.7	928.4	926.1	923.8	925.1
15°	919.1	918.3	917.6	916.9	916.1	914.6	912.1	909.7	907.4	905.0	906.4
17.5°	897.6	896.7	895.7	894.8	893.8	892.2	889.8	887.3	884.9	882.6	883.6
20°	881.7	880.6	879.6	878.5	877.3	875.5	873.1	870.8	868.4	865.9	866.7
22.5°	863.8	862.7	861.6	860.5	859.4	857.6	855.2	852.9	850.5	848.0	848.7
25°	834.5	833.4	832.3	831.2	830.0	828.3	825.9	823.5	821.1	818.7	818.9
27.5°	803.1	802.0	801.0	799.9	798.8	797.0	794.4	791.9	789.3	786.6	786.8
30°	780.5	779.6	778.7	777.8	776.8	775.1	772.5	769.9	767.4	764.8	764.8
32.5°	758.0	756.8	755.5	754.3	753.1	751.5	749.5	747.5	745.5	743.5	742.5
35°	721.7	720.6	719.5	718.4	717.2	715.5	713.0	710.7	708.3	705.9	704.8
37.5°	684.4	683.1	681.7	680.2	678.9	677.0	674.5	672.1	669.6	667.3	665.9
40°	658.6	657.5	656.4	655.3	654.2	652.4	649.7	647.2	644.6	642.0	640.6
42.5°	632.7	631.4	630.2	629.0	627.7	625.8	623.2	620.6	618.1	615.4	614.0
45°	591.4	590.7	589.9	589.2	588.4	586.9	584.5	582.1	579.7	577.3	575.1
47.5°	550.4	549.4	548.3	547.2	546.1	544.5	542.2	540.0	537.7	535.5	533.3
50°	522.6	521.7	520.7	519.8	518.9	517.2	514.8	512.5	510.0	507.6	505.6
52.5°	493.4	492.7	492.1	491.5	490.8	489.3	486.7	484.2	481.6	479.1	477.4
55°	448.8	448.5	448.4	448.2	448.0	446.7	444.3	442.0	439.5	437.1	435.1
57.5°	406.3	405.7	405.0	404.4	403.8	402.5	400.6	398.6	396.7	394.8	393.0
60°	375.7	375.6	375.4	375.2	375.0	373.8	371.6	369.4	367.2	365.0	363.3
62.5°	348.6	348.1	347.6	347.1	346.7	345.3	343.1	340.9	338.7	336.4	334.8
65°	306.1	305.1	304.2	303.3	302.4	301.0	299.1	297.3	295.5	293.7	292.2
67.5°	261.1	260.3	259.5	258.6	257.9	256.7	255.4	254.0	252.5	251.2	249.9
70°	233.9	232.8	231.7	230.6	229.5	228.4	227.3	226.2	225.1	223.9	222.7
72.5°	205.4	204.5	203.7	203.0	202.2	201.1	199.9	198.6	197.3	196.1	195.0
75°	161.8	161.0	160.3	159.5	158.8	158.1	157.6	157.0	156.5	156.0	155.0
77.5°	123.1	122.7	122.3	121.9	121.4	121.0	120.3	119.6	119.0	118.3	117.6
80°	97.9	97.4	96.8	96.3	95.7	95.2	94.8	94.5	94.1	93.7	93.6
82.5°	73.4	73.2	73.1	73.0	72.9	72.8	72.7	72.6	72.6	72.5	72.2
85°	43.1	42.8	42.4	42.1	41.7	41.5	41.5	41.5	41.5	41.5	41.1
87.5°	17.5	17.3	17.1	17.0	16.9	16.8	17.0	17.3	17.5	17.7	17.4
90°	1.3	2.5	3.7	5.5	6.8	8.1	9.9	11.8	13.6	15.4	14.9
92.5°	7.7	11.4	16.6	21.5	26.6	35.8	52.0	78.7	104.8	95.2	71.9
95°	21.1	22.9	29.7	40.2	56.3	80.5	133.2	225.5	327.0	367.3	297.9
97.5°	35.9	36.5	41.9	51.0	66.9	93.0	143.3	247.4	416.7	569.2	609.0
100°	45.9	46.4	50.8	59.5	74.3	98.5	141.8	233.5	396.4	586.5	708.5
102.5°	56.2	57.4	61.2	69.4	82.8	104.9	143.8	221.6	366.6	554.3	713.5
105°	71.9	73.7	77.4	84.8	96.6	115.8	149.2	213.0	330.1	498.0	675.7
107.5°	88.4	90.3	93.9	101.2	112.3	130.1	159.4	212.5	306.8	448.1	609.6
110°	100.4	102.2	105.3	112.1	122.6	140.0	167.9	214.9	297.9	419.9	567.9



TEST NUMBER: P331981-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.2	113.1	116.2	123.0	133.6	150.4	176.3	219.8	292.9	401.1	531.8
115°	127.0	129.4	133.2	139.3	149.9	166.6	190.1	227.9	291.1	380.9	488.1
117.5°	142.7	145.5	148.6	154.3	166.1	181.6	204.9	238.6	292.2	369.0	461.7
120°	153.6	155.4	158.5	164.8	176.5	192.0	214.3	246.5	294.2	363.5	447.8
122.5°	163.0	164.9	167.9	174.7	185.9	202.4	224.2	253.9	297.6	360.1	436.4
125°	176.5	177.8	181.5	188.3	200.0	216.7	238.4	265.7	302.9	355.5	421.8
127.5°	186.8	188.6	193.2	200.2	213.2	229.9	250.8	275.4	308.8	353.3	408.9
130°	193.2	195.1	200.7	208.1	221.1	237.8	258.3	281.8	312.8	351.8	402.0
132.5°	198.2	200.6	206.6	215.6	228.5	244.8	264.7	287.7	315.8	351.3	395.5
135°	206.8	209.4	216.2	225.5	238.4	255.2	274.3	295.4	320.2	350.5	387.1
137.5°	215.0	217.6	224.3	234.2	247.1	262.6	281.1	301.1	323.2	349.2	379.8
140°	220.5	223.6	229.8	239.7	252.1	267.5	285.5	304.1	325.2	348.7	375.3
142.5°	226.4	229.0	235.8	244.6	257.1	271.5	289.0	307.0	326.6	347.7	371.4
145°	236.0	237.8	243.4	252.7	263.2	277.5	293.6	310.3	327.6	346.2	366.1
147.5°	245.7	246.8	252.2	260.2	270.4	282.6	297.3	312.3	327.6	343.9	360.8
150°	252.1	252.7	257.6	265.7	274.3	285.5	299.8	312.8	327.6	341.9	357.4
152.5°	258.5	258.6	263.6	270.7	278.3	289.0	301.3	313.8	326.1	339.4	353.4
155°	268.2	268.2	271.9	278.1	284.9	293.6	304.1	314.0	324.6	335.1	347.5
157.5°	275.8	276.3	279.3	284.8	290.6	297.3	305.7	314.7	322.4	331.2	340.8
160°	281.8	281.8	284.3	289.2	293.6	299.8	307.2	314.7	321.5	328.3	336.3
162.5°	286.3	286.3	288.3	292.2	296.0	301.3	307.7	314.1	319.5	325.3	331.8
165°	292.9	292.3	293.6	296.7	299.1	303.5	308.4	312.8	316.5	320.8	325.7
167.5°	298.0	297.3	297.9	300.2	302.0	304.8	308.3	311.8	313.5	316.4	320.0
170°	301.0	299.8	300.4	302.2	303.5	304.8	307.8	310.3	311.6	313.4	316.5
172.5°	303.0	302.2	302.4	303.7	304.4	305.2	307.8	309.8	310.1	310.9	313.0
175°	305.3	304.8	304.1	305.3	305.3	305.9	307.2	308.4	307.8	307.8	309.0
177.5°	306.4	305.9	305.5	305.9	305.9	305.9	306.4	307.4	306.4	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P331981-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	961.0	962.5	963.9	964.6	964.5	964.3	964.2	964.0
5°	955.9	957.7	959.6	960.4	960.0	959.6	959.3	958.9
7.5°	945.8	947.5	949.1	949.8	949.6	949.4	949.1	949.0
10°	936.5	938.1	939.8	940.5	940.1	939.7	939.4	939.0
12.5°	926.3	927.5	928.8	929.2	929.0	928.8	928.6	928.4
15°	907.9	909.3	910.9	911.0	909.9	908.8	907.8	906.7
17.5°	884.6	885.7	886.7	887.0	886.6	886.2	885.8	885.4
20°	867.4	868.2	868.9	869.0	868.5	867.9	867.4	866.8
22.5°	849.2	849.9	850.4	850.3	849.7	849.0	848.3	847.6
25°	819.0	819.3	819.4	819.3	818.7	818.2	817.6	817.1
27.5°	787.0	787.1	787.3	787.0	786.3	785.6	784.9	784.2
30°	764.8	764.8	764.8	764.1	762.9	761.5	760.3	759.0
32.5°	741.5	740.5	739.4	738.6	737.8	737.1	736.4	735.8
35°	703.7	702.6	701.5	700.4	699.5	698.6	697.7	696.7
37.5°	664.6	663.2	661.9	661.0	660.4	659.8	659.2	658.6
40°	639.1	637.6	636.1	635.0	634.3	633.5	632.8	632.1
42.5°	612.5	611.0	609.6	608.5	607.8	607.0	606.3	605.5
45°	572.9	570.7	568.5	566.9	566.0	565.1	564.1	563.2
47.5°	531.2	529.0	526.8	525.3	524.5	523.7	522.9	522.0
50°	503.6	501.5	499.6	498.0	496.9	495.7	494.6	493.5
52.5°	475.6	473.9	472.1	470.8	469.7	468.6	467.5	466.4
55°	433.1	431.0	429.0	427.5	426.6	425.7	424.8	423.9
57.5°	391.2	389.4	387.6	386.2	385.1	384.0	382.9	381.9
60°	361.6	360.0	358.3	357.0	356.1	355.2	354.3	353.4
62.5°	333.1	331.4	329.8	328.7	328.0	327.4	326.8	326.1
65°	290.7	289.2	287.7	286.7	286.1	285.6	285.0	284.5
67.5°	248.6	247.3	246.0	244.9	244.2	243.4	242.6	241.9
70°	221.4	220.1	218.8	217.7	216.7	215.9	214.9	214.0
72.5°	193.8	192.7	191.5	190.7	190.2	189.7	189.3	188.8
75°	154.1	153.2	152.3	151.5	151.0	150.4	149.9	149.3
77.5°	117.0	116.4	115.7	115.5	115.5	115.5	115.5	115.5
80°	93.4	93.2	93.0	92.9	92.9	92.9	92.9	92.9
82.5°	71.9	71.5	71.1	70.9	70.8	70.7	70.5	70.3
85°	40.7	40.4	40.0	39.8	39.8	39.8	39.8	39.8
87.5°	17.4	17.3	17.3	17.5	17.4	17.5	17.7	17.5
90°	15.4	16.1	16.7	18.0	17.3	18.0	18.6	18.0
92.5°	52.1	41.4	36.5	33.4	32.2	30.3	31.0	29.9
95°	223.0	151.1	118.3	96.0	84.2	78.7	74.3	71.9
97.5°	555.8	445.2	365.3	291.2	245.5	217.6	200.9	195.6
100°	730.2	680.0	607.6	519.6	457.1	411.9	387.7	388.3
102.5°	788.1	786.6	744.3	688.6	639.9	604.1	583.9	569.7
105°	805.2	867.0	878.8	862.8	834.2	810.7	790.9	787.8
107.5°	756.4	856.9	911.2	933.2	933.7	925.8	919.1	913.4
110°	709.8	823.7	901.7	945.2	962.4	967.4	966.1	965.0



TEST NUMBER: P331981-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	663.7	780.1	867.6	923.3	955.1	970.4	975.1	975.3
115°	602.6	710.3	801.5	868.9	915.4	942.6	955.1	958.1
117.5°	558.4	651.4	733.2	801.7	850.1	881.3	899.1	903.4
120°	535.1	618.7	693.1	755.6	804.5	839.2	854.1	857.8
122.5°	516.8	592.5	661.3	719.5	762.9	794.1	810.5	815.2
125°	492.3	559.9	619.3	668.9	708.5	735.8	751.2	755.6
127.5°	471.1	531.2	584.9	630.0	665.3	688.6	702.6	706.5
130°	457.7	513.4	563.6	605.7	638.6	660.8	673.8	678.8
132.5°	445.3	496.6	543.3	583.4	614.3	636.6	648.1	651.6
135°	428.6	472.5	512.8	548.1	578.5	597.1	608.2	612.5
137.5°	413.4	449.4	484.1	514.7	540.2	559.0	568.5	571.3
140°	404.4	436.0	465.7	492.3	515.9	533.2	543.2	542.6
142.5°	396.0	423.1	448.9	472.1	492.1	507.5	516.4	515.8
145°	385.9	406.3	426.1	444.1	459.5	472.5	477.5	478.7
147.5°	377.6	393.8	409.8	422.6	434.3	443.1	447.8	448.3
150°	371.6	385.9	398.9	410.6	419.9	426.7	430.5	430.5
152.5°	366.1	378.4	389.9	399.7	407.0	413.4	415.6	415.6
155°	358.0	367.9	377.2	384.6	390.1	395.1	396.4	397.0
157.5°	349.3	357.6	364.8	370.6	375.4	379.1	380.2	380.0
160°	344.4	351.2	357.4	361.7	366.1	369.7	369.7	369.2
162.5°	338.4	344.2	349.9	353.8	356.6	359.8	359.8	359.3
165°	330.7	334.5	338.8	341.9	344.4	346.8	346.2	346.2
167.5°	324.0	326.9	329.4	331.6	332.7	334.5	333.8	333.8
170°	319.6	321.5	323.9	325.2	325.7	327.0	326.4	326.4
172.5°	315.6	317.0	318.9	319.7	319.8	321.1	320.0	319.5
175°	310.3	310.9	312.1	312.1	312.1	312.8	312.1	311.6
177.5°	307.0	307.4	307.9	307.9	307.4	307.9	307.0	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9

(END OF REPORT)