

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831705

Luminaire Tested: S123DIP-S775D805U927-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831705
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U927-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5352.6 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 46.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53								
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45								
2	91	83	78	73	84	78	72	68	66	63	59	56	54	51	47	45	43	39								
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34								
4	76	66	58	52	71	61	55	50	53	48	44	45	42	38	38	35	33	30								
5	70	59	51	46	65	55	48	43	48	43	38	41	37	34	35	32	29	26								
6	65	53	46	40	60	50	43	38	44	38	34	38	33	30	32	29	26	23								
7	60	49	41	35	56	46	39	34	40	34	30	34	30	27	29	26	24	21								
8	56	44	37	32	52	42	35	30	37	31	27	32	28	24	27	24	22	19								
9	53	41	33	29	49	38	32	27	34	28	25	29	25	22	25	22	20	18								
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	24	21	18	16								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	18813	18813	18813	18813	18813
5°	23793	22456	18982	15297	14056
10°	24024	24751	18855	12193	10656
15°	18094	22979	18727	10326	9011
20°	12607	18594	18488	9030	8184
25°	9613	14300	18081	8308	7677
30°	8316	11361	17429	7798	7269
35°	7716	9592	16679	7428	6980
40°	7305	8604	15625	7078	6884
45°	7062	7963	14285	6803	6839
50°	6941	7457	12698	6553	6804
55°	6683	7084	11142	6317	6835
60°	6443	6687	9604	6095	6723
65°	6052	6311	8283	5855	6589
70°	5589	5832	7046	5463	6203
75°	5061	5228	6039	5078	5669
80°	4172	4575	4779	4426	4779
85°	3310	3705	3507	3754	3804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 16309 cd/sqm



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.2	3.1
10°-20°	411.1	7.7
20°-30°	486.7	9.1
30°-40°	489.4	9.1
40°-50°	449.0	8.4
50°-60°	370.6	6.9
60°-70°	262.2	4.9
70°-80°	139.9	2.6
80°-90°	37.2	0.7
90°-100°	29.4	0.5
100°-110°	142.1	2.7
110°-120°	348.3	6.5
120°-130°	442.1	8.3
130°-140°	472.3	8.8
140°-150°	441.7	8.3
150°-160°	356.2	6.7
160°-170°	229.9	4.3
170°-180°	79.2	1.5
0°-30°	1063.1	19.9
0°-40°	1552.5	29.0
0°-60°	2372.1	44.3
0°-90°	2811.4	52.5
90°-120°	519.7	9.7
90°-150°	1875.8	35.0
90°-180°	2541.0	47.5
0°-180°	5352.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1748	1748	1748	1748	1748	
5°	2202	2078	1757	1416	1301	210
15°	1624	2062	1680	927	809	449
25°	809	1204	1522	700	646	382
35°	587	730	1269	565	531	369
45°	464	523	938	447	449	359
55°	356	378	594	337	364	319
65°	238	248	325	230	259	236
75°	122	126	145	122	136	128
85°	27	30	28	30	31	30
90°	19	15	1	15	19	10
95°	24	19	38	19	24	20
105°	27	136	185	136	27	57
115°	364	356	346	356	364	343
125°	498	496	488	496	498	445
135°	614	614	608	614	614	473
145°	708	707	701	707	708	442
155°	771	772	772	772	771	356
165°	813	812	814	812	813	230
175°	830	831	834	831	830	79
180°	834	834	834	834	834	



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8
2.5°	1970.1	1968.0	1966.0	1955.9	1945.7	1940.9	1936.0	1921.4	1906.8	1890.6	1874.4
5°	2202.0	2207.7	2213.4	2206.9	2200.4	2180.5	2160.7	2134.3	2107.9	2078.3	2048.7
7.5°	2309.1	2312.3	2315.6	2311.5	2307.5	2302.2	2296.9	2273.4	2249.9	2219.5	2189.0
10°	2198.0	2205.3	2212.6	2228.4	2244.2	2262.0	2279.9	2276.6	2273.4	2264.5	2255.6
12.5°	1953.8	1962.8	1971.7	2003.3	2034.9	2075.5	2116.1	2150.9	2185.8	2210.1	2234.5
15°	1623.7	1648.5	1673.2	1702.0	1730.8	1790.4	1850.0	1923.4	1996.8	2062.1	2127.4
17.5°	1337.4	1346.8	1356.1	1386.9	1417.7	1492.8	1567.8	1652.5	1737.3	1845.6	1953.8
20°	1100.6	1109.1	1117.6	1158.2	1198.7	1257.5	1316.3	1411.6	1506.9	1623.3	1739.7
22.5°	924.6	938.0	951.4	974.1	996.8	1053.2	1109.5	1194.3	1279.0	1407.6	1536.1
25°	809.4	819.2	828.9	842.7	856.5	901.5	946.5	1016.3	1086.0	1204.0	1322.0
27.5°	730.8	734.8	738.9	752.7	766.5	795.6	824.8	884.9	944.9	1045.0	1145.2
30°	669.1	672.0	674.8	687.0	699.1	719.0	738.9	782.3	825.7	914.1	1002.5
32.5°	626.1	628.2	630.2	639.5	648.8	663.0	677.2	708.9	740.5	813.5	886.5
35°	587.2	588.4	589.6	596.5	603.4	614.0	624.5	648.4	672.4	730.0	787.5
37.5°	553.1	554.8	556.4	560.4	564.5	573.8	583.2	602.2	621.3	665.5	709.7
40°	519.9	522.7	525.6	528.4	531.2	538.9	546.7	561.3	575.9	612.3	648.8
42.5°	491.5	494.3	497.2	498.4	499.6	504.1	508.5	521.9	535.3	562.5	589.6
45°	463.9	465.1	466.4	467.6	468.8	472.4	476.1	487.9	499.6	523.1	546.7
47.5°	438.8	438.8	438.8	439.6	440.4	443.6	446.9	455.4	463.9	482.2	500.4
50°	414.5	414.5	414.5	413.2	412.0	414.0	416.1	422.6	429.1	445.3	461.5
52.5°	385.3	385.3	385.3	385.7	386.1	386.1	386.1	391.7	397.4	412.0	426.6
55°	356.1	357.7	359.3	358.1	356.9	357.7	358.5	362.1	365.8	377.5	389.3
57.5°	326.9	327.7	328.5	328.1	327.7	328.1	328.5	331.7	335.0	343.9	352.8
60°	299.3	299.3	299.3	298.5	297.7	298.5	299.3	300.9	302.5	310.6	318.7
62.5°	268.5	268.9	269.3	269.7	270.1	269.3	268.5	270.5	272.5	278.6	284.7
65°	237.6	238.0	238.5	239.7	240.9	240.1	239.3	241.3	243.3	247.8	252.2
67.5°	210.1	209.3	208.4	208.8	209.3	210.5	211.7	212.1	212.5	217.4	222.2
70°	177.6	178.4	179.2	178.8	178.4	178.8	179.2	180.5	181.7	185.3	189.0
72.5°	148.4	148.8	149.2	149.2	149.2	150.0	150.9	152.1	153.3	155.3	157.3
75°	121.7	121.7	121.7	122.5	123.3	123.7	124.1	124.1	124.1	125.7	127.3
77.5°	92.5	94.5	96.5	96.1	95.7	96.5	97.3	98.5	99.8	100.6	101.4
80°	67.3	67.3	67.3	67.7	68.1	69.3	70.6	71.4	72.2	73.8	75.4
82.5°	43.0	43.4	43.8	45.0	46.2	47.0	47.9	49.1	50.3	50.3	50.3
85°	26.8	26.0	25.1	26.0	26.8	27.6	28.4	28.8	29.2	30.0	30.8
87.5°	13.0	13.0	13.0	13.0	13.0	13.4	13.8	13.8	13.8	13.8	13.8
90°	18.6	18.3	18.0	17.8	17.5	17.1	16.5	16.0	15.4	14.9	13.1
92.5°	21.1	20.9	20.8	20.6	20.5	20.0	19.0	18.0	17.1	16.1	14.9
95°	23.5	23.5	23.5	23.5	23.5	23.1	22.1	21.1	20.2	19.2	17.7
97.5°	25.4	25.3	25.1	25.0	24.8	24.2	23.1	22.0	20.9	19.8	26.8
100°	26.0	25.9	25.7	25.6	25.5	24.8	23.7	22.6	21.5	20.4	41.9
102.5°	26.6	26.4	26.1	25.8	25.5	27.7	32.2	36.7	41.3	45.8	69.8
105°	27.3	27.0	26.7	26.4	26.1	38.2	62.6	86.9	111.3	135.6	148.0
107.5°	64.4	82.4	100.5	118.5	136.5	156.1	177.3	198.5	219.7	240.9	238.9
110°	170.3	190.0	209.7	229.4	249.0	261.1	265.7	270.2	274.8	279.3	277.8



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	322.7	322.9	323.2	323.5	323.8	323.3	322.0	320.8	319.6	318.3	316.8
115°	364.2	363.6	363.1	362.5	362.0	361.0	359.6	358.2	356.9	355.5	354.3
117.5°	397.6	397.5	397.3	397.2	397.1	396.4	395.3	394.2	393.1	392.0	391.3
120°	432.3	432.3	432.3	432.3	432.3	431.7	430.6	429.5	428.4	427.3	426.9
122.5°	466.4	466.2	466.1	465.9	465.8	465.4	464.7	464.0	463.3	462.6	462.1
125°	497.9	497.7	497.4	497.1	496.8	496.6	496.3	496.0	495.7	495.5	494.9
127.5°	528.9	529.2	529.5	529.7	530.0	529.9	529.5	529.1	528.7	528.3	527.6
130°	558.6	558.9	559.2	559.5	559.7	559.6	559.0	558.5	557.9	557.4	556.8
132.5°	585.9	586.3	586.7	587.1	587.5	587.5	586.9	586.4	585.8	585.3	584.8
135°	613.7	614.2	614.6	615.0	615.4	615.4	615.0	614.6	614.2	613.7	613.2
137.5°	640.4	640.7	640.9	641.2	641.5	641.3	640.6	639.9	639.2	638.5	638.2
140°	663.9	664.2	664.5	664.7	665.0	664.9	664.3	663.8	663.2	662.7	662.3
142.5°	685.6	686.0	686.4	686.8	687.2	687.2	686.8	686.4	686.0	685.6	685.2
145°	707.9	707.9	707.9	707.9	707.9	707.7	707.5	707.2	706.9	706.6	706.4
147.5°	724.0	724.7	725.4	726.1	726.7	726.9	726.7	726.4	726.1	725.8	725.6
150°	742.6	743.0	743.4	743.8	744.2	744.3	744.0	743.7	743.5	743.2	742.9
152.5°	757.4	758.1	758.8	759.5	760.2	760.3	759.7	759.2	758.6	758.1	757.9
155°	771.1	771.9	772.7	773.5	774.4	774.4	773.7	773.1	772.4	771.7	771.5
157.5°	782.8	783.9	785.0	786.1	787.2	787.4	786.5	785.7	784.9	784.1	784.2
160°	794.0	794.9	795.9	796.9	797.8	797.9	797.1	796.2	795.4	794.6	794.7
162.5°	804.5	805.3	806.2	807.0	807.8	807.7	806.8	805.8	804.8	803.9	804.0
165°	812.6	813.5	814.5	815.4	816.4	816.3	815.2	814.1	813.0	811.9	812.1
167.5°	818.7	819.8	820.9	822.0	823.1	823.1	822.0	820.9	819.8	818.7	818.7
170°	824.3	825.4	826.5	827.6	828.7	828.7	827.6	826.5	825.4	824.3	824.3
172.5°	827.4	828.7	829.9	831.1	832.4	832.4	831.3	830.2	829.1	828.0	827.9
175°	830.5	831.6	832.7	833.8	834.9	835.0	834.0	833.1	832.1	831.1	831.0
177.5°	831.1	832.5	833.9	835.3	836.6	836.8	835.7	834.6	833.5	832.4	832.2
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8
2.5°	1869.5	1864.6	1846.8	1828.9	1808.7	1788.4	1773.4	1758.4	1736.1	1713.8	1695.5
5°	2026.0	2003.3	1965.6	1927.9	1876.8	1825.7	1791.2	1756.8	1710.5	1664.3	1627.4
7.5°	2150.1	2111.2	2058.5	2005.7	1938.8	1871.9	1808.7	1745.4	1674.8	1604.3	1546.7
10°	2229.2	2202.8	2142.0	2081.2	1991.6	1901.9	1813.5	1725.1	1634.3	1543.4	1467.2
12.5°	2236.9	2239.3	2183.4	2127.4	2026.0	1924.6	1817.2	1709.7	1595.4	1481.0	1392.2
15°	2169.2	2210.9	2180.1	2149.3	2047.1	1944.9	1812.7	1680.5	1548.7	1416.9	1314.3
17.5°	2043.5	2133.1	2137.5	2142.0	2039.8	1937.6	1791.2	1644.8	1495.6	1346.4	1238.5
20°	1871.9	2004.1	2049.5	2095.0	2011.8	1928.7	1771.4	1614.0	1446.9	1279.9	1166.7
22.5°	1696.7	1857.3	1940.5	2023.6	1962.0	1900.3	1732.8	1565.3	1388.9	1212.5	1097.8
25°	1497.2	1672.4	1800.1	1927.9	1890.2	1852.5	1687.4	1522.4	1334.6	1146.8	1029.6
27.5°	1323.2	1501.3	1655.4	1809.5	1801.4	1793.3	1629.4	1465.6	1273.4	1081.1	968.0
30°	1168.3	1334.2	1506.5	1678.9	1698.8	1718.6	1560.5	1402.3	1209.7	1017.1	908.0
32.5°	1031.3	1176.0	1361.0	1545.9	1584.8	1623.7	1481.0	1338.2	1147.6	957.0	852.0
35°	918.9	1050.3	1235.2	1420.2	1468.8	1517.5	1393.4	1269.3	1083.6	897.8	797.7
37.5°	819.6	929.5	1109.9	1290.4	1350.0	1409.6	1298.5	1187.4	1013.4	839.4	747.4
40°	737.3	825.7	991.5	1157.4	1226.3	1295.3	1203.6	1112.0	946.9	781.9	697.1
42.5°	668.3	747.0	897.4	1047.9	1114.0	1180.1	1102.6	1025.2	878.4	731.6	654.1
45°	609.5	672.4	809.0	945.7	1008.6	1071.4	1004.9	938.4	809.0	679.7	607.5
47.5°	554.4	608.3	725.1	841.9	897.8	953.8	901.9	850.0	740.5	631.0	565.7
50°	504.9	548.3	650.5	752.7	801.3	850.0	804.2	758.3	668.3	578.3	521.5
52.5°	461.9	497.2	582.7	668.3	710.1	751.9	712.5	673.2	601.8	530.4	481.0
55°	419.3	449.3	523.5	597.8	626.1	654.5	624.1	593.7	536.1	478.5	436.8
57.5°	379.6	406.3	467.2	528.0	549.9	571.8	544.2	516.6	473.3	429.9	395.0
60°	340.6	362.5	413.2	463.9	477.3	490.7	468.4	446.1	415.7	385.3	354.0
62.5°	304.6	324.4	362.1	399.9	408.8	417.7	400.7	383.6	360.5	337.4	313.1
65°	267.2	282.2	313.1	343.9	349.6	355.2	340.2	325.2	307.8	290.4	272.5
67.5°	232.8	243.3	268.5	293.6	294.0	294.4	282.2	270.1	260.3	250.6	236.4
70°	199.1	209.3	225.9	242.5	242.9	243.3	233.6	223.9	216.6	209.3	198.7
72.5°	164.6	171.9	184.5	197.1	196.3	195.5	189.4	183.3	177.6	171.9	164.2
75°	133.4	139.5	148.0	156.5	154.1	151.7	148.4	145.2	140.3	135.4	130.6
77.5°	105.0	108.7	113.5	118.4	116.8	115.2	112.3	109.5	105.8	102.2	100.2
80°	77.1	78.7	81.9	85.2	84.4	83.5	80.3	77.1	76.2	75.4	72.6
82.5°	52.3	54.3	55.2	56.0	55.6	55.2	52.7	50.3	49.5	48.7	48.3
85°	31.2	31.6	32.0	32.4	31.2	30.0	29.2	28.4	28.4	28.4	28.0
87.5°	14.2	14.6	14.6	14.6	14.2	13.8	13.0	12.2	12.6	13.0	13.0
90°	11.3	9.5	7.7	6.1	4.7	3.4	2.0	0.6	2.0	3.4	4.7
92.5°	13.6	12.4	11.1	10.9	11.8	12.6	13.4	14.2	13.4	12.6	11.8
95°	16.2	14.7	13.1	15.2	20.9	26.5	32.1	37.8	32.1	26.5	20.9
97.5°	33.9	40.9	47.9	53.3	57.2	61.0	64.9	68.7	64.9	61.0	57.2
100°	63.4	84.8	106.3	115.7	112.9	110.2	107.4	104.7	107.4	110.2	112.9
102.5°	93.7	117.7	141.6	152.7	150.9	149.1	147.3	145.5	147.3	149.1	150.9
105°	160.4	172.8	185.2	190.6	189.1	187.6	186.1	184.6	186.1	187.6	189.1
107.5°	236.8	234.7	232.7	231.0	229.8	228.5	227.3	226.1	227.3	228.5	229.8
110°	276.3	274.8	273.3	272.0	270.9	269.7	268.6	267.5	268.6	269.7	270.9



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	315.3	313.8	312.3	311.0	310.1	309.1	308.1	307.2	308.1	309.1	310.1
115°	353.0	351.8	350.5	349.5	348.7	347.9	347.0	346.2	347.0	347.9	348.7
117.5°	390.7	390.0	389.3	388.5	387.5	386.5	385.6	384.6	385.6	386.5	387.5
120°	426.5	426.1	425.7	424.9	423.6	422.4	421.1	419.9	421.1	422.4	423.6
122.5°	461.5	461.0	460.4	459.7	458.7	457.7	456.8	455.8	456.8	457.7	458.7
125°	494.4	493.8	493.3	492.4	491.3	490.2	489.1	488.0	489.1	490.2	491.3
127.5°	526.9	526.2	525.5	524.6	523.5	522.4	521.3	520.2	521.3	522.4	523.5
130°	556.3	555.7	555.2	554.4	553.3	552.2	551.1	550.0	551.1	552.2	553.3
132.5°	584.4	584.0	583.6	582.9	581.8	580.6	579.5	578.4	579.5	580.6	581.8
135°	612.6	612.1	611.5	610.9	610.0	609.2	608.4	607.6	608.4	609.2	610.0
137.5°	638.0	637.7	637.4	636.7	635.6	634.5	633.4	632.3	633.4	634.5	635.6
140°	661.8	661.4	661.0	660.4	659.6	658.8	657.9	657.1	657.9	658.8	659.6
142.5°	684.8	684.4	683.9	683.3	682.5	681.7	680.8	680.0	680.8	681.7	682.5
145°	706.1	705.8	705.5	704.9	704.0	703.0	702.0	701.1	702.0	703.0	704.0
147.5°	725.3	725.0	724.7	724.3	723.6	722.9	722.2	721.5	722.2	722.9	723.6
150°	742.6	742.4	742.1	741.7	741.3	740.9	740.5	740.1	740.5	740.9	741.3
152.5°	757.8	757.6	757.5	757.4	757.2	757.1	757.0	756.8	757.0	757.1	757.2
155°	771.4	771.3	771.1	771.2	771.5	771.7	772.0	772.3	772.0	771.7	771.5
157.5°	784.3	784.5	784.6	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7
160°	794.9	795.0	795.1	795.3	795.4	795.6	795.7	795.8	795.7	795.6	795.4
162.5°	804.2	804.3	804.4	804.7	805.1	805.5	805.9	806.4	805.9	805.5	805.1
165°	812.2	812.3	812.5	812.8	813.2	813.6	814.0	814.4	814.0	813.6	813.2
167.5°	818.7	818.7	818.7	819.0	819.6	820.1	820.7	821.2	820.7	820.1	819.6
170°	824.3	824.3	824.3	824.6	825.1	825.7	826.2	826.8	826.2	825.7	825.1
172.5°	827.8	827.6	827.5	827.8	828.4	829.1	829.8	830.5	829.8	829.1	828.4
175°	830.9	830.7	830.6	830.9	831.5	832.2	832.9	833.6	832.9	832.2	831.5
177.5°	832.1	832.0	831.8	832.1	832.8	833.5	834.2	834.8	834.2	833.5	832.8
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8
2.5°	1677.3	1661.5	1645.6	1633.5	1621.3	1600.6	1579.9	1575.1	1570.2	1563.3	1556.4
5°	1590.5	1551.6	1512.6	1477.7	1442.9	1415.7	1388.5	1370.7	1352.8	1339.9	1326.9
7.5°	1489.1	1430.7	1372.3	1330.9	1289.6	1250.2	1210.9	1198.3	1185.8	1168.7	1151.7
10°	1391.0	1326.5	1262.0	1208.1	1154.1	1115.6	1077.1	1061.7	1046.3	1024.8	1003.3
12.5°	1303.4	1232.8	1162.2	1107.9	1053.6	1016.3	978.9	956.6	934.3	922.2	910.0
15°	1211.7	1136.3	1060.9	1010.6	960.3	926.6	893.0	873.5	854.0	842.3	830.5
17.5°	1130.6	1056.0	981.4	933.1	884.9	854.0	823.2	806.2	789.2	780.2	771.3
20°	1053.6	980.6	907.6	860.5	813.5	788.3	763.2	752.3	741.3	734.0	726.7
22.5°	983.0	911.2	839.4	799.3	759.2	738.9	718.6	710.9	703.2	697.1	691.0
25°	912.4	848.4	784.3	750.2	716.2	699.5	682.9	675.2	667.5	661.4	655.3
27.5°	854.9	793.6	732.4	703.2	674.0	661.0	648.0	642.0	635.9	630.2	624.5
30°	798.9	744.1	689.4	664.3	639.1	627.4	615.6	609.5	603.4	598.2	592.9
32.5°	747.0	699.9	652.9	629.8	606.7	596.9	587.2	579.9	572.6	568.6	564.5
35°	697.5	655.3	613.2	594.1	575.0	565.3	555.6	549.5	543.4	540.2	536.9
37.5°	655.3	617.6	579.9	561.7	543.4	534.1	524.8	519.5	514.2	513.0	511.8
40°	612.3	579.9	547.5	529.6	511.8	503.7	495.6	492.3	489.1	488.3	487.4
42.5°	576.7	545.0	513.4	497.2	481.0	474.1	467.2	465.5	463.9	465.1	466.4
45°	535.3	508.9	482.6	467.6	452.6	446.9	441.2	440.0	438.8	441.2	443.6
47.5°	500.4	476.1	451.8	437.6	423.4	419.3	415.3	414.9	414.5	417.7	420.9
50°	464.7	441.2	417.7	406.3	395.0	391.3	387.7	388.9	390.1	395.4	400.7
52.5°	431.5	409.6	387.7	377.1	366.6	364.2	361.7	364.6	367.4	373.1	378.8
55°	395.0	375.1	355.2	347.1	339.0	336.6	334.2	339.8	345.5	350.8	356.1
57.5°	360.1	342.7	325.2	317.9	310.6	310.2	309.8	315.1	320.4	326.0	331.7
60°	322.8	308.2	293.6	287.9	282.2	283.1	283.9	290.0	296.0	300.5	305.0
62.5°	288.7	276.6	264.4	259.1	253.9	255.9	257.9	264.0	270.1	275.4	280.6
65°	254.7	244.5	234.4	230.7	227.1	229.9	232.8	238.0	243.3	247.0	250.6
67.5°	222.2	213.7	205.2	202.4	199.5	202.4	205.2	210.5	215.7	219.4	223.0
70°	188.2	181.3	174.4	172.3	170.3	173.6	176.8	181.3	185.7	189.4	193.0
72.5°	156.5	151.3	146.0	145.6	145.2	148.0	150.9	155.3	159.8	162.2	164.6
75°	125.7	122.9	120.0	119.6	119.2	122.1	124.9	127.3	129.8	131.8	133.8
77.5°	98.1	95.7	93.3	93.7	94.1	96.1	98.1	100.6	103.0	104.2	105.4
80°	69.8	68.9	68.1	68.9	69.8	71.4	73.0	74.6	76.2	77.1	77.9
82.5°	47.9	47.0	46.2	47.4	48.7	49.9	51.1	52.3	53.5	53.9	54.3
85°	27.6	28.8	30.0	30.0	30.0	30.4	30.8	31.2	31.6	31.2	30.8
87.5°	13.0	13.4	13.8	13.8	13.8	14.2	14.6	14.6	14.6	14.2	13.8
90°	6.1	7.7	9.5	11.3	13.1	14.9	15.4	16.0	16.5	17.1	17.5
92.5°	10.9	11.1	12.4	13.6	14.9	16.1	17.1	18.0	19.0	20.0	20.5
95°	15.2	13.1	14.7	16.2	17.7	19.2	20.2	21.1	22.1	23.1	23.5
97.5°	53.3	47.9	40.9	33.9	26.8	19.8	20.9	22.0	23.1	24.2	24.8
100°	115.7	106.3	84.8	63.4	41.9	20.4	21.5	22.6	23.7	24.8	25.5
102.5°	152.7	141.6	117.7	93.7	69.8	45.8	41.3	36.7	32.2	27.7	25.5
105°	190.6	185.2	172.8	160.4	148.0	135.6	111.3	86.9	62.6	38.2	26.1
107.5°	231.0	232.7	234.7	236.8	238.9	240.9	219.7	198.5	177.3	156.1	136.5
110°	272.0	273.3	274.8	276.3	277.8	279.3	274.8	270.2	265.7	261.1	249.0



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	311.0	312.3	313.8	315.3	316.8	318.3	319.6	320.8	322.0	323.3	323.8
115°	349.5	350.5	351.8	353.0	354.3	355.5	356.9	358.2	359.6	361.0	362.0
117.5°	388.5	389.3	390.0	390.7	391.3	392.0	393.1	394.2	395.3	396.4	397.1
120°	424.9	425.7	426.1	426.5	426.9	427.3	428.4	429.5	430.6	431.7	432.3
122.5°	459.7	460.4	461.0	461.5	462.1	462.6	463.3	464.0	464.7	465.4	465.8
125°	492.4	493.3	493.8	494.4	494.9	495.5	495.7	496.0	496.3	496.6	496.8
127.5°	524.6	525.5	526.2	526.9	527.6	528.3	528.7	529.1	529.5	529.9	530.0
130°	554.4	555.2	555.7	556.3	556.8	557.4	557.9	558.5	559.0	559.6	559.7
132.5°	582.9	583.6	584.0	584.4	584.8	585.3	585.8	586.4	586.9	587.5	587.5
135°	610.9	611.5	612.1	612.6	613.2	613.7	614.2	614.6	615.0	615.4	615.4
137.5°	636.7	637.4	637.7	638.0	638.2	638.5	639.2	639.9	640.6	641.3	641.5
140°	660.4	661.0	661.4	661.8	662.3	662.7	663.2	663.8	664.3	664.9	665.0
142.5°	683.3	683.9	684.4	684.8	685.2	685.6	686.0	686.4	686.8	687.2	687.2
145°	704.9	705.5	705.8	706.1	706.4	706.6	706.9	707.2	707.5	707.7	707.9
147.5°	724.3	724.7	725.0	725.3	725.6	725.8	726.1	726.4	726.7	726.9	726.7
150°	741.7	742.1	742.4	742.6	742.9	743.2	743.5	743.7	744.0	744.3	744.2
152.5°	757.4	757.5	757.6	757.8	757.9	758.1	758.6	759.2	759.7	760.3	760.2
155°	771.2	771.1	771.3	771.4	771.5	771.7	772.4	773.1	773.7	774.4	774.4
157.5°	784.7	784.6	784.5	784.3	784.2	784.1	784.9	785.7	786.5	787.4	787.2
160°	795.3	795.1	795.0	794.9	794.7	794.6	795.4	796.2	797.1	797.9	797.8
162.5°	804.7	804.4	804.3	804.2	804.0	803.9	804.8	805.8	806.8	807.7	807.8
165°	812.8	812.5	812.3	812.2	812.1	811.9	813.0	814.1	815.2	816.3	816.4
167.5°	819.0	818.7	818.7	818.7	818.7	818.7	819.8	820.9	822.0	823.1	823.1
170°	824.6	824.3	824.3	824.3	824.3	824.3	825.4	826.5	827.6	828.7	828.7
172.5°	827.8	827.5	827.6	827.8	827.9	828.0	829.1	830.2	831.3	832.4	832.4
175°	830.9	830.6	830.7	830.9	831.0	831.1	832.1	833.1	834.0	835.0	834.9
177.5°	832.1	831.8	832.0	832.1	832.2	832.4	833.5	834.6	835.7	836.8	836.6
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1747.8	1747.8	1747.8	1747.8
2.5°	1553.6	1550.7	1539.4	1528.0
5°	1317.2	1307.4	1304.2	1300.9
7.5°	1150.9	1150.1	1133.0	1116.0
10°	1004.5	1005.7	990.3	974.9
12.5°	899.9	889.7	888.5	887.3
15°	821.2	811.9	810.2	808.6
17.5°	765.6	760.0	758.3	756.7
20°	723.5	720.2	717.4	714.5
22.5°	687.0	682.9	680.5	678.0
25°	651.7	648.0	647.2	646.4
27.5°	620.1	615.6	615.6	615.6
30°	590.0	587.2	586.0	584.8
32.5°	562.1	559.6	559.6	559.6
35°	535.7	534.5	532.9	531.2
37.5°	511.8	511.8	511.0	510.2
40°	488.7	489.9	489.9	489.9
42.5°	467.6	468.8	468.8	468.8
45°	445.7	447.7	448.5	449.3
47.5°	424.2	427.4	428.2	429.1
50°	403.1	405.5	405.9	406.3
52.5°	381.6	384.4	386.5	388.5
55°	358.9	361.7	362.9	364.2
57.5°	334.6	337.4	337.8	338.2
60°	307.8	310.6	311.4	312.3
62.5°	282.2	283.9	284.7	285.5
65°	253.1	255.5	257.1	258.7
67.5°	225.1	227.1	227.1	227.1
70°	193.8	194.7	195.9	197.1
72.5°	165.1	165.5	165.5	165.5
75°	134.6	135.4	135.9	136.3
77.5°	105.8	106.2	106.2	106.2
80°	77.5	77.1	77.1	77.1
82.5°	53.1	51.9	51.9	51.9
85°	30.4	30.0	30.4	30.8
87.5°	13.8	13.8	13.8	13.8
90°	17.8	18.0	18.3	18.6
92.5°	20.6	20.8	20.9	21.1
95°	23.5	23.5	23.5	23.5
97.5°	25.0	25.1	25.3	25.4
100°	25.6	25.7	25.9	26.0
102.5°	25.8	26.1	26.4	26.6
105°	26.4	26.7	27.0	27.3
107.5°	118.5	100.5	82.4	64.4
110°	229.4	209.7	190.0	170.3



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	323.5	323.2	322.9	322.7
115°	362.5	363.1	363.6	364.2
117.5°	397.2	397.3	397.5	397.6
120°	432.3	432.3	432.3	432.3
122.5°	465.9	466.1	466.2	466.4
125°	497.1	497.4	497.7	497.9
127.5°	529.7	529.5	529.2	528.9
130°	559.5	559.2	558.9	558.6
132.5°	587.1	586.7	586.3	585.9
135°	615.0	614.6	614.2	613.7
137.5°	641.2	640.9	640.7	640.4
140°	664.7	664.5	664.2	663.9
142.5°	686.8	686.4	686.0	685.6
145°	707.9	707.9	707.9	707.9
147.5°	726.1	725.4	724.7	724.0
150°	743.8	743.4	743.0	742.6
152.5°	759.5	758.8	758.1	757.4
155°	773.5	772.7	771.9	771.1
157.5°	786.1	785.0	783.9	782.8
160°	796.9	795.9	794.9	794.0
162.5°	807.0	806.2	805.3	804.5
165°	815.4	814.5	813.5	812.6
167.5°	822.0	820.9	819.8	818.7
170°	827.6	826.5	825.4	824.3
172.5°	831.1	829.9	828.7	827.4
175°	833.8	832.7	831.6	830.5
177.5°	835.3	833.9	832.5	831.1
180°	833.6	833.6	833.6	833.6



TEST NUMBER: P831705

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.00	14.84	14.94	15.80	17.04	16.23	17.08	17.18	18.03	19.27
	3H	15.64	16.40	16.60	17.36	18.63	17.66	18.41	18.61	19.38	20.64
	4H	16.22	16.94	17.19	17.90	19.17	18.11	18.82	19.08	19.79	21.06
	6H	16.59	17.25	17.57	18.22	19.50	18.38	19.04	19.36	20.01	21.30
	8H	16.69	17.31	17.67	18.30	19.58	18.44	19.07	19.43	20.06	21.34
	12H	16.73	17.33	17.72	18.31	19.61	18.46	19.06	19.45	20.04	21.35
4H	2H	14.57	15.29	15.54	16.25	17.52	16.40	17.11	17.37	18.08	19.35
	3H	16.40	16.99	17.38	17.99	19.27	18.01	18.61	19.00	19.61	20.89
	4H	17.10	17.64	18.09	18.63	19.94	18.60	19.14	19.59	20.13	21.44
	6H	17.57	18.04	18.57	19.05	20.36	19.00	19.47	20.00	20.48	21.79
	8H	17.71	18.14	18.71	19.15	20.47	19.11	19.55	20.12	20.56	21.88
	12H	17.77	18.17	18.80	19.19	20.51	19.16	19.55	20.18	20.57	21.90
8H	4H	17.36	17.80	18.36	18.80	20.12	18.70	19.14	19.71	20.15	21.46
	6H	17.95	18.31	18.98	19.36	20.68	19.20	19.56	20.23	20.61	21.93
	8H	18.16	18.47	19.19	19.51	20.85	19.38	19.70	20.42	20.74	22.07
	12H	18.28	18.56	19.32	19.59	20.97	19.48	19.76	20.52	20.79	22.17
12H	4H	17.36	17.75	18.38	18.78	20.10	18.68	19.07	19.70	20.09	21.42
	6H	18.00	18.32	19.04	19.35	20.69	19.22	19.53	20.25	20.57	21.91
	8H	18.23	18.51	19.27	19.54	20.92	19.42	19.70	20.46	20.72	22.11