

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332353-927

Luminaire Tested: **S123RDIP-S1000D1025U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332353-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5945.1 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332353-927

CATALOG NUMBER: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332353-927

CATALOG NUMBER: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69		62	60	59		51	49	48	43
2	90	82	77	71	83	76	71	67	65	61	58		55	52	49		45	43	41	37
3	82	73	66	60	76	68	61	56	58	53	49		49	45	42		40	38	36	31
4	75	65	57	51	69	60	53	48	51	46	42		43	40	36		36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36		39	35	32		33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32		35	31	28		30	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28		32	28	25		27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25		30	25	22		25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23		27	23	20		23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20		25	21	18		21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332353-927

CATALOG NUMBER: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.8	2.1
10°-20°	347.3	5.8
20°-30°	500.2	8.4
30°-40°	563.4	9.5
40°-50°	539.0	9.1
50°-60°	441.4	7.4
60°-70°	297.8	5.0
70°-80°	149.8	2.5
80°-90°	42.7	0.7
90°-100°	217.4	3.7
100°-110°	615.6	10.4
110°-120°	605.5	10.2
120°-130°	483.0	8.1
130°-140°	380.8	6.4
140°-150°	284.2	4.8
150°-160°	198.1	3.3
160°-170°	116.4	2.0
170°-180°	37.9	0.6
0°-30°	972.3	16.4
0°-40°	1535.7	25.8
0°-60°	2516.0	42.3
0°-90°	3006.3	50.6
90°-120°	1438.5	24.2
90°-150°	2586.5	43.5
90°-180°	2939.0	49.4
0°-180°	5945.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	2	10	20	22	23	5
95°	27	87	469	137	92	29
105°	92	136	636	1112	1006	97
115°	162	202	486	1066	1223	160
125°	225	266	454	822	965	200
135°	264	315	448	677	782	204
145°	301	345	442	556	611	189
155°	342	369	428	486	507	157
165°	374	385	410	434	442	105
175°	390	390	393	398	398	37
180°	391	391	391	391	391	



TEST NUMBER: P332353-927

CATALOG NUMBER: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	21.0	19.3	17.4	15.8	14.0	13.3	13.7	14.2	14.7	15.1	14.8
90°	1.6	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0
92.5°	9.8	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7
95°	26.9	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3
97.5°	45.9	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4
100°	58.5	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6
102.5°	71.8	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9
105°	91.7	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7
107.5°	112.9	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2
110°	128.1	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1



TEST NUMBER: P332353-927

CATALOG NUMBER: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.0	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9
115°	162.1	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1
117.5°	182.2	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4
120°	196.1	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7
122.5°	208.1	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1
125°	225.4	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5
127.5°	238.5	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0
130°	246.7	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2
132.5°	253.0	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9
135°	264.1	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2
137.5°	274.6	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9
140°	281.5	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2
142.5°	289.1	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1
145°	301.3	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3
147.5°	313.6	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7
150°	321.9	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2
152.5°	330.0	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2
155°	342.4	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6
157.5°	352.2	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1
160°	359.8	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4
162.5°	365.5	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7
165°	374.0	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9
167.5°	380.5	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5
170°	384.3	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1
172.5°	386.8	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7
175°	389.8	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6
177.5°	391.3	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332353-927

CATALOG NUMBER: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	14.8	14.7	14.7	14.8	14.5	14.5	14.4	14.1
90°	19.8	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	66.5	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	284.6	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	709.6	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	932.3	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1006.3	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1027.9	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	965.7	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	906.2	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0





TEST NUMBER: P332353-927

CATALOG NUMBER: S123RDIP-S1000D1025U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	847.3	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	769.4	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	713.0	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	683.2	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	659.8	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	628.7	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	601.4	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	584.4	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	568.5	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	547.2	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	527.8	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	516.3	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	505.6	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	492.7	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	482.0	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	474.4	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	467.5	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	457.0	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	446.0	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	439.7	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	432.1	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	422.2	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	413.7	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	408.1	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	403.0	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	396.2	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	391.9	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)