

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332355-927

Luminaire Tested: **S123RDIP-S1000D1195U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332355-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6385.4 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43				
2	90	83	77	72	83	77	72	67	65	61	58	54	52	49	45	43	41	37				
3	82	73	66	61	76	68	62	57	58	53	50	49	45	43	40	38	36	32				
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	36	33	31	28				
5	70	58	51	45	64	54	47	42	47	41	37	39	35	32	33	30	28	24				
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	24	22				
7	59	48	40	34	55	44	38	33	38	33	29	33	29	25	27	24	22	19				
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17				
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16				
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13555	13555	13555	13555
5°	16159	13613	11988	13613
10°	20176	13535	10831	13535
15°	23682	13397	9877	13397
20°	26431	13190	9065	13190
25°	26008	12973	8568	12973
30°	18695	12771	8054	12771
35°	12482	12510	7721	12510
40°	9197	12197	7378	12197
45°	7715	11645	7042	11645
50°	6807	10923	6571	10923
55°	5970	10098	5928	10098
60°	5315	9309	5431	9309
65°	4669	8458	5053	8458
70°	3666	7704	4614	7704
75°	3227	6729	4213	6729
80°	2808	5715	4147	5715
85°	2260	4594	4397	4594



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	1.9
10°-20°	386.9	6.1
20°-30°	607.8	9.5
30°-40°	634.2	9.9
40°-50°	542.7	8.5
50°-60°	413.6	6.5
60°-70°	265.1	4.2
70°-80°	127.5	2.0
80°-90°	37.2	0.6
90°-100°	76.3	1.2
100°-110°	228.5	3.6
110°-120°	388.6	6.1
120°-130°	511.1	8.0
130°-140°	574.5	9.0
140°-150°	564.7	8.8
150°-160°	475.4	7.4
160°-170°	316.5	5.0
170°-180°	110.8	1.7
0°-30°	1118.6	17.5
0°-40°	1752.8	27.4
0°-60°	2709.1	42.4
0°-90°	3139.0	49.2
90°-120°	693.4	10.9
90°-150°	2343.7	36.7
90°-180°	3246.0	50.8
0°-180°	6385.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1259	1259	1259	1259	1259	
5°	1496	1260	1110	1260	1496	154
15°	2125	1202	886	1202	2125	603
25°	2190	1092	721	1092	2190	941
35°	950	952	588	952	950	623
45°	507	765	463	765	507	398
55°	318	538	316	538	318	288
65°	183	332	198	332	183	180
75°	78	162	101	162	78	83
85°	18	37	36	37	18	22
90°	28	1	28	1	28	14
95°	72	54	72	54	72	74
105°	219	207	219	207	219	232
115°	392	391	392	391	392	388
125°	566	572	566	572	566	506
135°	742	743	742	743	742	570
145°	901	901	901	901	901	562
155°	1030	1032	1030	1032	1030	474
165°	1120	1124	1120	1124	1120	316
175°	1164	1169	1164	1169	1164	111
180°	1172	1172	1172	1172	1172	



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1341.3	1343.0	1337.4	1336.6	1330.1	1328.3	1328.3	1319.3	1313.7	1306.4	1302.0
5°	1495.5	1504.1	1499.8	1490.1	1473.9	1470.1	1459.9	1443.8	1425.4	1402.7	1391.9
7.5°	1688.1	1699.8	1695.3	1680.3	1663.3	1649.6	1620.8	1593.9	1556.3	1523.3	1495.1
10°	1845.9	1833.5	1823.8	1809.3	1793.6	1768.2	1738.0	1696.5	1648.6	1610.8	1568.8
12.5°	1964.1	1962.0	1949.7	1934.7	1912.6	1888.6	1851.5	1800.9	1745.2	1690.7	1642.5
15°	2125.2	2128.4	2120.3	2104.7	2073.4	2030.8	1974.8	1953.8	1873.9	1814.7	1755.3
17.5°	2236.6	2236.0	2234.9	2213.3	2181.4	2151.0	2099.0	2043.8	1971.5	1887.9	1808.1
20°	2307.4	2302.0	2303.0	2278.8	2255.1	2220.0	2169.4	2089.1	2029.7	1933.2	1850.8
22.5°	2305.6	2304.5	2308.7	2300.3	2283.1	2256.3	2216.4	2148.6	2072.8	1975.5	1882.7
25°	2189.8	2185.6	2210.9	2217.9	2245.4	2250.2	2238.4	2201.2	2129.5	2029.2	1914.4
27.5°	1832.7	1830.3	1877.4	1936.3	2010.9	2068.9	2124.9	2152.0	2129.5	2057.7	1942.6
30°	1504.1	1554.8	1578.5	1663.7	1758.6	1871.8	1970.9	2065.3	2088.5	2057.2	1962.9
32.5°	1248.8	1293.0	1312.8	1385.9	1474.3	1606.9	1755.8	1889.4	1983.7	2007.6	1950.8
35°	949.9	950.5	995.7	1028.1	1110.0	1246.4	1390.9	1569.9	1747.8	1882.5	1896.6
37.5°	758.0	760.7	788.1	820.3	881.8	953.9	1081.1	1229.9	1435.4	1642.4	1763.6
40°	654.5	659.3	679.9	711.6	755.8	810.2	909.5	1049.6	1221.1	1451.3	1639.4
42.5°	588.0	596.0	606.5	631.0	658.4	709.3	789.6	897.9	1053.8	1271.5	1488.5
45°	506.8	511.0	519.2	530.4	555.2	590.9	644.8	717.6	846.9	1022.2	1239.4
47.5°	447.0	444.7	453.3	462.5	479.0	503.2	539.3	598.7	691.0	831.6	1015.9
50°	406.5	405.9	411.9	418.9	434.5	452.3	482.0	526.7	600.0	716.4	885.2
52.5°	368.5	370.6	374.8	383.5	394.8	409.2	435.8	468.0	531.0	631.5	772.2
55°	318.1	319.7	325.6	330.5	338.6	353.1	369.8	396.8	439.9	510.0	625.9
57.5°	275.4	274.6	280.4	281.5	290.7	302.5	315.4	336.4	367.7	419.8	497.8
60°	246.9	245.3	250.2	253.9	258.8	268.5	279.2	299.8	324.6	362.8	429.7
62.5°	221.0	220.3	223.9	227.6	231.6	240.4	249.5	265.2	284.9	317.1	370.2
65°	183.3	184.9	186.6	188.1	190.3	195.7	204.3	215.1	228.5	251.2	289.5
67.5°	144.0	145.7	146.2	149.6	154.2	157.6	162.8	172.4	181.8	200.9	222.7
70°	116.5	115.9	116.5	118.0	124.0	129.9	137.0	143.9	149.9	163.3	181.6
72.5°	100.1	99.1	100.5	100.8	103.7	105.4	109.8	116.4	124.0	133.2	146.3
75°	77.6	77.6	77.6	77.6	79.8	80.9	82.5	84.1	86.8	91.1	100.8
77.5°	57.4	57.4	58.2	58.8	59.2	59.8	60.8	62.4	63.4	65.7	69.9
80°	45.3	45.8	45.3	45.8	45.8	46.9	47.5	49.0	49.6	52.3	53.9
82.5°	34.1	33.7	34.1	34.6	34.6	35.7	35.8	37.0	37.1	38.5	40.1
85°	18.3	17.3	18.3	17.8	18.9	17.8	18.3	19.4	19.4	20.0	22.1
87.5°	9.8	10.6	9.7	10.1	9.9	10.2	10.1	9.9	10.6	10.1	9.9
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8	22.9	22.1	19.4
92.5°	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7	36.0	35.3	33.8
95°	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7	68.9	68.1	66.5
97.5°	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4	107.5	106.5	105.4
100°	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5	135.9	135.3	134.3
102.5°	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9	168.3	167.7	166.4
105°	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2	217.2	217.2	215.4
107.5°	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5	268.9	268.2	267.4
110°	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4	303.6	302.9	302.4



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4	338.4	337.4	337.3
115°	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5	392.3	392.1	392.5
117.5°	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2	446.2	446.2	446.8
120°	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9	482.1	482.3	483.3
122.5°	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1	518.6	519.1	519.7
125°	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8	572.6	573.5	573.9
127.5°	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9	626.1	627.2	627.6
130°	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1	661.0	661.8	662.4
132.5°	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4	695.4	696.4	696.8
135°	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8	746.6	747.3	747.6
137.5°	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9	796.8	797.6	797.1
140°	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9	829.1	829.3	829.1
142.5°	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8	860.0	860.2	859.8
145°	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3	905.5	905.7	905.1
147.5°	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7	974.7	974.7	974.3
152.5°	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9	998.6	998.3	998.1
155°	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4	1033.6	1032.7	1032.5
157.5°	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8	1064.0	1063.1	1063.0
160°	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5	1082.5	1081.5	1081.5
162.5°	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2	1100.2	1099.2	1099.0
165°	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6	1122.3	1121.1	1121.1
167.5°	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1	1138.9
170°	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7	1148.7
172.5°	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4	1158.1	1156.8	1156.8
175°	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7	1166.5	1165.2	1165.2
177.5°	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5	1170.4	1169.5	1169.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1300.3	1299.0	1293.0	1286.1	1277.0	1271.0	1266.2	1263.7	1255.9	1246.4	1239.9
5°	1380.6	1364.5	1347.3	1326.2	1306.8	1286.8	1274.5	1259.9	1242.1	1222.2	1208.2
7.5°	1466.7	1435.0	1400.8	1365.6	1330.7	1299.5	1271.8	1248.2	1219.9	1191.3	1171.2
10°	1532.7	1486.3	1438.4	1389.3	1344.5	1302.5	1270.1	1238.3	1204.4	1171.5	1146.7
12.5°	1592.6	1531.6	1476.3	1416.0	1358.8	1308.5	1261.9	1224.6	1183.7	1148.6	1120.4
15°	1668.5	1606.0	1539.1	1447.5	1371.5	1307.9	1251.3	1202.2	1152.6	1109.5	1082.0
17.5°	1739.5	1645.4	1555.5	1479.1	1380.3	1300.8	1231.8	1173.1	1118.6	1072.9	1039.1
20°	1768.8	1677.7	1580.1	1482.6	1385.5	1296.6	1216.2	1151.5	1095.0	1043.1	1011.9
22.5°	1786.5	1683.3	1580.6	1475.7	1372.5	1280.2	1200.7	1129.6	1068.2	1019.0	980.4
25°	1807.0	1684.2	1571.0	1467.4	1362.3	1262.0	1167.7	1092.3	1026.0	973.6	932.6
27.5°	1820.7	1676.1	1542.3	1427.2	1320.6	1220.8	1134.2	1054.2	987.0	931.7	887.7
30°	1823.3	1669.6	1520.3	1395.7	1287.4	1195.7	1104.1	1027.5	956.4	897.6	856.7
32.5°	1826.7	1653.7	1490.5	1358.2	1247.3	1156.5	1073.5	1000.4	927.5	869.6	827.8
35°	1812.5	1644.8	1445.3	1293.3	1182.3	1094.4	1019.5	952.0	880.4	824.3	781.7
37.5°	1751.2	1609.8	1398.5	1220.2	1104.1	1022.7	961.6	902.9	837.1	776.7	736.5
40°	1689.6	1575.3	1362.3	1175.8	1054.5	970.9	915.9	868.0	804.4	747.7	704.6
42.5°	1597.7	1528.3	1327.9	1129.2	998.4	917.9	871.5	826.6	770.7	713.2	672.7
45°	1429.2	1438.4	1257.2	1055.0	920.8	840.0	796.2	765.0	715.4	668.0	626.5
47.5°	1217.8	1303.5	1174.3	976.0	838.9	763.0	724.8	697.6	664.2	617.6	579.7
50°	1079.8	1202.2	1107.9	923.0	787.7	712.2	674.4	652.3	623.2	586.5	550.4
52.5°	952.6	1084.0	1027.6	863.9	732.0	663.0	626.1	607.9	584.8	550.3	517.6
55°	776.8	910.0	897.1	774.7	648.6	586.5	558.5	538.1	522.4	496.5	470.6
57.5°	628.4	754.6	761.3	675.5	575.0	513.7	489.6	474.2	464.0	444.4	420.5
60°	534.8	650.7	673.4	608.6	522.4	468.5	444.7	432.4	424.3	408.6	390.3
62.5°	457.2	555.8	581.5	534.9	471.9	421.4	402.9	390.9	385.5	372.0	355.8
65°	349.9	431.8	456.6	430.7	397.8	357.4	342.3	332.1	327.3	319.7	307.8
67.5°	263.1	322.8	350.0	331.8	319.9	294.4	284.8	279.2	275.0	269.7	259.8
70°	211.4	255.6	283.6	278.7	269.0	255.6	248.5	244.8	240.4	236.1	227.5
72.5°	169.9	200.3	226.6	229.1	221.2	218.5	212.3	210.7	208.1	203.0	198.2
75°	112.6	133.7	152.0	159.1	162.2	164.9	162.2	161.8	161.2	156.9	154.2
77.5°	73.8	85.2	96.7	108.7	113.8	117.4	118.3	120.3	118.8	116.5	115.3
80°	56.6	59.3	67.4	77.6	85.7	89.0	91.1	92.2	91.7	91.1	89.0
82.5°	41.1	43.3	47.1	54.3	61.2	66.5	67.8	67.6	68.8	69.1	67.4
85°	22.1	22.7	23.7	24.8	28.6	34.5	36.1	37.2	38.3	38.3	35.0
87.5°	10.2	9.3	9.6	9.2	10.1	10.1	12.2	14.0	14.8	13.5	13.9
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3	23.7	25.0	26.5
95°	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3	55.8	57.2	58.6
97.5°	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5	97.5	98.6	99.7
100°	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2	126.4	127.6	128.9
102.5°	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3	159.1	159.8	160.5
105°	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1	207.5	207.9	208.3
107.5°	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8	264.0	264.3	264.5
110°	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1	299.5	299.9	300.4



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0	336.2	336.4	336.7
115°	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2	391.8	392.4	393.0
117.5°	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8	447.2	447.6	448.0
120°	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4	482.6	483.9	485.1
122.5°	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5	518.3	519.3	520.1
125°	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5	573.1	573.7	574.3
127.5°	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3	624.6	625.9	627.2
130°	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2	658.8	660.4	662.1
132.5°	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0	692.7	694.3	695.9
135°	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8	744.0	745.2	746.5
137.5°	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7	791.6	792.7	793.7
140°	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8	824.8	825.9	826.9
142.5°	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0	855.0	856.0	857.1
145°	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1	901.5	901.9	902.3
147.5°	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3	943.1	943.8	944.5
150°	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1	971.5	971.8	972.2
152.5°	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6	995.2	995.8	996.3
155°	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4	1063.2	1063.0	1062.7
160°	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3	1082.9	1082.5	1082.1
162.5°	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0	1100.4	1099.9	1099.3
165°	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9	1123.2	1122.6	1122.0
167.5°	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1	1141.2	1140.4	1139.6
170°	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4	1151.5	1150.7	1149.9
172.5°	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5	1159.7	1158.8	1158.0
175°	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9	1168.2	1167.3	1166.5
177.5°	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4	1171.8	1171.2	1170.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1237.8	1232.2	1228.3	1219.6	1214.1	1208.0	1202.0	1205.9	1205.5	1205.0	1205.0
5°	1196.3	1183.8	1172.6	1158.0	1148.8	1137.5	1128.9	1127.8	1130.0	1122.4	1118.1
7.5°	1155.1	1138.1	1122.1	1106.0	1089.0	1075.4	1066.9	1062.9	1057.4	1052.7	1047.9
10°	1126.2	1106.3	1090.6	1070.6	1052.3	1036.2	1026.0	1018.9	1015.1	1011.4	1004.3
12.5°	1096.5	1076.9	1057.0	1034.4	1017.0	998.2	990.5	982.7	975.5	971.2	961.6
15°	1052.9	1027.5	1006.5	982.8	963.4	945.1	934.3	918.6	916.5	911.1	901.4
17.5°	1009.2	981.7	952.7	935.2	913.2	894.1	877.7	872.5	857.1	851.3	842.8
20°	974.7	949.4	927.2	904.1	872.3	854.4	841.5	834.6	822.1	814.6	809.2
22.5°	944.9	919.2	893.7	866.6	840.3	820.4	811.0	800.0	793.2	782.7	776.8
25°	902.5	874.4	843.7	814.6	795.7	780.6	765.6	755.8	746.2	741.2	730.5
27.5°	853.1	823.8	795.0	772.9	749.8	734.9	721.2	712.6	700.9	692.8	686.8
30°	825.9	791.4	766.6	746.6	717.0	703.0	692.8	682.0	673.4	664.7	658.8
32.5°	794.4	763.0	739.4	714.8	692.0	676.7	663.5	653.9	646.6	638.4	632.5
35°	745.0	718.7	694.3	669.6	652.8	637.2	621.6	613.5	606.5	599.0	593.6
37.5°	700.4	675.7	652.7	629.2	608.4	595.7	583.1	576.9	567.4	562.4	556.9
40°	672.8	648.6	623.8	601.1	579.6	569.8	558.5	549.4	540.7	536.9	531.0
42.5°	642.6	618.4	597.5	573.1	555.4	542.2	531.8	521.7	515.3	509.8	506.4
45°	597.9	576.3	555.8	531.6	514.8	503.5	491.6	482.5	476.6	472.8	466.8
47.5°	554.4	532.8	512.1	490.9	474.8	461.8	450.0	443.5	435.7	431.1	427.1
50°	522.9	503.5	481.4	462.0	445.8	432.9	423.2	415.1	408.1	402.2	399.5
52.5°	494.0	473.3	454.2	436.2	419.1	404.4	395.6	387.1	381.8	375.0	371.9
55°	446.4	426.4	410.3	392.4	375.7	363.4	352.6	345.0	339.6	332.1	327.8
57.5°	401.6	383.7	364.4	349.0	331.8	321.3	312.4	302.1	295.6	289.6	285.4
60°	371.5	350.9	334.2	319.7	304.6	291.1	283.0	275.0	267.9	262.0	258.3
62.5°	339.9	322.1	306.2	290.3	276.6	264.8	255.4	248.7	242.5	238.7	235.0
65°	291.7	277.7	261.5	248.5	235.6	227.0	219.4	213.5	209.1	206.4	203.3
67.5°	247.2	233.6	219.5	206.8	198.2	191.6	186.6	181.6	179.4	175.9	173.8
70°	218.3	204.3	191.9	182.2	173.6	168.7	165.5	161.8	159.5	155.3	153.1
72.5°	186.9	176.7	167.8	159.8	152.9	148.5	144.3	139.7	136.3	131.5	129.4
75°	147.2	138.0	131.0	125.6	121.3	115.3	109.4	104.6	103.0	101.3	100.8
77.5°	109.0	103.2	98.2	93.6	88.2	83.9	82.6	81.5	81.2	80.3	80.3
80°	85.7	80.3	76.5	71.1	67.9	67.9	67.9	66.9	67.4	67.4	67.4
82.5°	63.7	58.8	56.7	54.7	54.1	54.6	54.6	54.7	54.4	55.3	54.9
85°	32.9	33.4	34.5	34.0	34.5	34.5	35.6	35.0	35.6	34.5	35.6
87.5°	13.9	15.7	16.6	17.6	18.5	18.6	19.3	19.4	20.0	20.2	20.3
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8	24.6	25.3	26.0
92.5°	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7	37.3	37.9	38.2
95°	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7	70.6	71.4	71.8
97.5°	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4	109.4	110.4	110.7
100°	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5	137.1	137.8	138.2
102.5°	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9	169.5	170.2	170.4
105°	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2	217.2	217.2	217.5
107.5°	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5	270.2	270.8	271.0
110°	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4	305.3	306.1	306.3



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4	340.4	341.4	341.8
115°	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5	392.7	392.9	392.9
117.5°	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2	446.1	446.1	445.8
120°	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9	481.7	481.5	481.2
122.5°	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1	517.5	517.0	516.4
125°	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8	571.0	570.1	569.3
127.5°	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9	623.8	622.6	621.5
130°	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1	659.3	658.5	657.4
132.5°	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4	693.5	692.4	691.4
135°	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8	744.9	744.1	743.5
137.5°	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9	795.0	794.2	793.4
140°	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9	828.7	828.5	827.7
142.5°	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8	859.6	859.4	858.7
145°	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3	905.1	904.9	904.4
147.5°	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7	974.7	974.7	974.1
152.5°	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9	999.3	999.6	999.3
155°	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4	1035.1	1036.0	1035.7
157.5°	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8	1065.6	1066.5	1066.4
160°	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5	1084.6	1085.6	1085.7
162.5°	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2	1102.2	1103.3	1103.1
165°	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6	1124.7	1126.0	1125.8
167.5°	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1
170°	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4
172.5°	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4	1160.6	1161.9	1161.8
175°	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7	1168.9	1170.1	1170.1
177.5°	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5	1172.4	1173.4	1173.3
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1199.8	1199.4	1199.8	1198.1	1199.8	1199.4	1199.8	1205.0	1205.0	1205.5	1205.9
5°	1116.5	1115.9	1114.4	1109.5	1114.4	1115.9	1116.5	1118.1	1122.4	1130.0	1127.8
7.5°	1043.7	1043.0	1038.2	1038.3	1038.2	1043.0	1043.7	1047.9	1052.7	1057.4	1062.9
10°	1000.6	1001.1	994.7	990.9	994.7	1001.1	1000.6	1004.3	1011.4	1015.1	1018.9
12.5°	958.8	956.2	951.1	946.9	951.1	956.2	958.8	961.6	971.2	975.5	982.7
15°	903.6	898.2	885.2	886.3	885.2	898.2	903.6	901.4	911.1	916.5	918.6
17.5°	838.5	834.6	834.3	826.8	834.3	834.6	838.5	842.8	851.3	857.1	872.5
20°	800.6	797.9	798.9	791.4	798.9	797.9	800.6	809.2	814.6	822.1	834.6
22.5°	770.8	768.1	763.6	761.2	763.6	768.1	770.8	776.8	782.7	793.2	800.0
25°	727.2	722.9	718.7	721.4	718.7	722.9	727.2	730.5	741.2	746.2	755.8
27.5°	683.7	680.5	676.1	675.6	676.1	680.5	683.7	686.8	692.8	700.9	712.6
30°	656.1	652.8	650.7	648.0	650.7	652.8	656.1	658.8	664.7	673.4	682.0
32.5°	628.0	627.4	623.5	623.0	623.5	627.4	628.0	632.5	638.4	646.6	653.9
35°	591.4	588.2	587.1	587.6	587.1	588.2	591.4	593.6	599.0	606.5	613.5
37.5°	556.6	552.2	550.3	548.3	550.3	552.2	556.6	556.9	562.4	567.4	576.9
40°	531.6	527.3	526.2	525.1	526.2	527.3	531.6	531.0	536.9	540.7	549.4
42.5°	503.5	501.8	501.1	499.2	501.1	501.8	503.5	506.4	509.8	515.3	521.7
45°	465.2	464.7	461.4	462.6	461.4	464.7	465.2	466.8	472.8	476.6	482.5
47.5°	424.9	422.6	420.3	421.8	420.3	422.6	424.9	427.1	431.1	435.7	443.5
50°	397.4	396.2	391.4	392.4	391.4	396.2	397.4	399.5	402.2	408.1	415.1
52.5°	369.7	365.6	363.8	363.1	363.8	365.6	369.7	371.9	375.0	381.8	387.1
55°	324.0	319.2	317.0	315.9	317.0	319.2	324.0	327.8	332.1	339.6	345.0
57.5°	279.2	277.8	276.2	277.3	276.2	277.8	279.2	285.4	289.6	295.6	302.1
60°	252.9	252.9	252.9	252.3	252.9	252.9	252.9	258.3	262.0	267.9	275.0
62.5°	232.6	231.2	230.8	231.6	230.8	231.2	232.6	235.0	238.7	242.5	248.7
65°	201.6	201.1	198.9	198.4	198.9	201.1	201.6	203.3	206.4	209.1	213.5
67.5°	172.4	170.5	169.8	169.1	169.8	170.5	172.4	173.8	175.9	179.4	181.6
70°	150.4	149.3	146.1	146.6	146.1	149.3	150.4	153.1	155.3	159.5	161.8
72.5°	126.7	125.6	124.9	124.2	124.9	125.6	126.7	129.4	131.5	136.3	139.7
75°	100.3	99.7	99.2	101.3	99.2	99.7	100.3	100.8	101.3	103.0	104.6
77.5°	80.3	80.3	80.6	79.8	80.6	80.3	80.3	80.3	80.3	81.2	81.5
80°	67.4	67.4	66.9	66.9	66.9	67.4	67.4	67.4	67.4	67.4	66.9
82.5°	54.0	54.4	54.7	53.9	54.7	54.4	54.0	54.9	55.3	54.4	54.7
85°	35.6	35.0	36.1	35.6	36.1	35.0	35.6	35.6	34.5	35.6	35.0
87.5°	21.2	20.4	20.5	21.1	20.5	20.4	21.2	20.3	20.2	20.0	19.4
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8
92.5°	37.9	37.7	37.4	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7
95°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7
97.5°	110.7	110.6	110.5	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4
100°	138.7	139.1	139.5	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5
102.5°	170.3	170.2	170.2	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9
105°	217.9	218.2	218.6	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2
107.5°	270.8	270.5	270.3	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5
110°	305.9	305.5	305.1	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.7	341.7	341.6	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4
115°	392.7	392.5	392.3	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5
117.5°	445.2	444.6	444.0	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2
120°	480.8	480.4	480.0	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9
122.5°	515.9	515.3	514.7	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1
125°	568.5	567.7	566.9	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8
127.5°	620.6	619.6	618.7	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9
130°	655.9	654.5	653.1	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1
132.5°	690.3	689.2	688.1	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4
135°	743.1	742.7	742.3	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8
137.5°	792.6	791.9	791.1	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9
140°	826.2	824.8	823.4	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9
142.5°	857.6	856.5	855.5	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8
145°	903.6	902.7	901.9	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3
147.5°	946.3	945.2	943.9	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2
150°	972.9	971.7	970.4	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7
152.5°	998.1	997.1	996.0	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9
155°	1034.3	1032.8	1031.4	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4
157.5°	1065.2	1064.1	1063.0	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8
160°	1084.9	1084.0	1083.2	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5
162.5°	1101.8	1100.5	1099.2	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2
165°	1124.4	1123.0	1121.6	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6
167.5°	1142.9	1141.6	1140.3	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6
170°	1153.0	1151.5	1150.1	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5
172.5°	1160.3	1158.9	1157.5	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4
175°	1168.6	1167.2	1165.8	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7
177.5°	1172.2	1171.0	1169.9	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1202.0	1208.0	1214.1	1219.6	1228.3	1232.2	1237.8	1239.9	1246.4	1255.9	1263.7
5°	1128.9	1137.5	1148.8	1158.0	1172.6	1183.8	1196.3	1208.2	1222.2	1242.1	1259.9
7.5°	1066.9	1075.4	1089.0	1106.0	1122.1	1138.1	1155.1	1171.2	1191.3	1219.9	1248.2
10°	1026.0	1036.2	1052.3	1070.6	1090.6	1106.3	1126.2	1146.7	1171.5	1204.4	1238.3
12.5°	990.5	998.2	1017.0	1034.4	1057.0	1076.9	1096.5	1120.4	1148.6	1183.7	1224.6
15°	934.3	945.1	963.4	982.8	1006.5	1027.5	1052.9	1082.0	1109.5	1152.6	1202.2
17.5°	877.7	894.1	913.2	935.2	952.7	981.7	1009.2	1039.1	1072.9	1118.6	1173.1
20°	841.5	854.4	872.3	904.1	927.2	949.4	974.7	1011.9	1043.1	1095.0	1151.5
22.5°	811.0	820.4	840.3	866.6	893.7	919.2	944.9	980.4	1019.0	1068.2	1129.6
25°	765.6	780.6	795.7	814.6	843.7	874.4	902.5	932.6	973.6	1026.0	1092.3
27.5°	721.2	734.9	749.8	772.9	795.0	823.8	853.1	887.7	931.7	987.0	1054.2
30°	692.8	703.0	717.0	746.6	766.6	791.4	825.9	856.7	897.6	956.4	1027.5
32.5°	663.5	676.7	692.0	714.8	739.4	763.0	794.4	827.8	869.6	927.5	1000.4
35°	621.6	637.2	652.8	669.6	694.3	718.7	745.0	781.7	824.3	880.4	952.0
37.5°	583.1	595.7	608.4	629.2	652.7	675.7	700.4	736.5	776.7	837.1	902.9
40°	558.5	569.8	579.6	601.1	623.8	648.6	672.8	704.6	747.7	804.4	868.0
42.5°	531.8	542.2	555.4	573.1	597.5	618.4	642.6	672.7	713.2	770.7	826.6
45°	491.6	503.5	514.8	531.6	555.8	576.3	597.9	626.5	668.0	715.4	765.0
47.5°	450.0	461.8	474.8	490.9	512.1	532.8	554.4	579.7	617.6	664.2	697.6
50°	423.2	432.9	445.8	462.0	481.4	503.5	522.9	550.4	586.5	623.2	652.3
52.5°	395.6	404.4	419.1	436.2	454.2	473.3	494.0	517.6	550.3	584.8	607.9
55°	352.6	363.4	375.7	392.4	410.3	426.4	446.4	470.6	496.5	522.4	538.1
57.5°	312.4	321.3	331.8	349.0	364.4	383.7	401.6	420.5	444.4	464.0	474.2
60°	283.0	291.1	304.6	319.7	334.2	350.9	371.5	390.3	408.6	424.3	432.4
62.5°	255.4	264.8	276.6	290.3	306.2	322.1	339.9	355.8	372.0	385.5	390.9
65°	219.4	227.0	235.6	248.5	261.5	277.7	291.7	307.8	319.7	327.3	332.1
67.5°	186.6	191.6	198.2	206.8	219.5	233.6	247.2	259.8	269.7	275.0	279.2
70°	165.5	168.7	173.6	182.2	191.9	204.3	218.3	227.5	236.1	240.4	244.8
72.5°	144.3	148.5	152.9	159.8	167.8	176.7	186.9	198.2	203.0	208.1	210.7
75°	109.4	115.3	121.3	125.6	131.0	138.0	147.2	154.2	156.9	161.2	161.8
77.5°	82.6	83.9	88.2	93.6	98.2	103.2	109.0	115.3	116.5	118.8	120.3
80°	67.9	67.9	67.9	71.1	76.5	80.3	85.7	89.0	91.1	91.7	92.2
82.5°	54.6	54.6	54.1	54.7	56.7	58.8	63.7	67.4	69.1	68.8	67.6
85°	35.6	34.5	34.5	34.0	34.5	33.4	32.9	35.0	38.3	38.3	37.2
87.5°	19.3	18.6	18.5	17.6	16.6	15.7	13.9	13.9	13.5	14.8	14.0
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	36.0	35.3	33.8	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3
95°	68.9	68.1	66.5	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3
97.5°	107.5	106.5	105.4	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5
100°	135.9	135.3	134.3	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2
102.5°	168.3	167.7	166.4	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3
105°	217.2	217.2	215.4	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1
107.5°	268.9	268.2	267.4	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8
110°	303.6	302.9	302.4	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	338.4	337.4	337.3	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0
115°	392.3	392.1	392.5	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2
117.5°	446.2	446.2	446.8	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8
120°	482.1	482.3	483.3	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4
122.5°	518.6	519.1	519.7	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5
125°	572.6	573.5	573.9	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5
127.5°	626.1	627.2	627.6	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3
130°	661.0	661.8	662.4	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2
132.5°	695.4	696.4	696.8	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0
135°	746.6	747.3	747.6	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8
137.5°	796.8	797.6	797.1	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7
140°	829.1	829.3	829.1	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8
142.5°	860.0	860.2	859.8	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0
145°	905.5	905.7	905.1	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1
147.5°	948.2	948.2	947.6	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3
150°	974.7	974.7	974.3	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1
152.5°	998.6	998.3	998.1	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6
155°	1033.6	1032.7	1032.5	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1064.0	1063.1	1063.0	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4
160°	1082.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3
162.5°	1100.2	1099.2	1099.0	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0
165°	1122.3	1121.1	1121.1	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9
167.5°	1140.3	1139.1	1138.9	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1
170°	1150.1	1148.7	1148.7	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4
172.5°	1158.1	1156.8	1156.8	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5
175°	1166.5	1165.2	1165.2	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9
177.5°	1170.4	1169.5	1169.5	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1266.2	1271.0	1277.0	1286.1	1293.0	1299.0	1300.3	1302.0	1306.4	1313.7	1319.3
5°	1274.5	1286.8	1306.8	1326.2	1347.3	1364.5	1380.6	1391.9	1402.7	1425.4	1443.8
7.5°	1271.8	1299.5	1330.7	1365.6	1400.8	1435.0	1466.7	1495.1	1523.3	1556.3	1593.9
10°	1270.1	1302.5	1344.5	1389.3	1438.4	1486.3	1532.7	1568.8	1610.8	1648.6	1696.5
12.5°	1261.9	1308.5	1358.8	1416.0	1476.3	1531.6	1592.6	1642.5	1690.7	1745.2	1800.9
15°	1251.3	1307.9	1371.5	1447.5	1539.1	1606.0	1668.5	1755.3	1814.7	1873.9	1953.8
17.5°	1231.8	1300.8	1380.3	1479.1	1555.5	1645.4	1739.5	1808.1	1887.9	1971.5	2043.8
20°	1216.2	1296.6	1385.5	1482.6	1580.1	1677.7	1768.8	1850.8	1933.2	2029.7	2089.1
22.5°	1200.7	1280.2	1372.5	1475.7	1580.6	1683.3	1786.5	1882.7	1975.5	2072.8	2148.6
25°	1167.7	1262.0	1362.3	1467.4	1571.0	1684.2	1807.0	1914.4	2029.2	2129.5	2201.2
27.5°	1134.2	1220.8	1320.6	1427.2	1542.3	1676.1	1820.7	1942.6	2057.7	2129.5	2152.0
30°	1104.1	1195.7	1287.4	1395.7	1520.3	1669.6	1823.3	1962.9	2057.2	2088.5	2065.3
32.5°	1073.5	1156.5	1247.3	1358.2	1490.5	1653.7	1826.7	1950.8	2007.6	1983.7	1889.4
35°	1019.5	1094.4	1182.3	1293.3	1445.3	1644.8	1812.5	1896.6	1882.5	1747.8	1569.9
37.5°	961.6	1022.7	1104.1	1220.2	1398.5	1609.8	1751.2	1763.6	1642.4	1435.4	1229.9
40°	915.9	970.9	1054.5	1175.8	1362.3	1575.3	1689.6	1639.4	1451.3	1221.1	1049.6
42.5°	871.5	917.9	998.4	1129.2	1327.9	1528.3	1597.7	1488.5	1271.5	1053.8	897.9
45°	796.2	840.0	920.8	1055.0	1257.2	1438.4	1429.2	1239.4	1022.2	846.9	717.6
47.5°	724.8	763.0	838.9	976.0	1174.3	1303.5	1217.8	1015.9	831.6	691.0	598.7
50°	674.4	712.2	787.7	923.0	1107.9	1202.2	1079.8	885.2	716.4	600.0	526.7
52.5°	626.1	663.0	732.0	863.9	1027.6	1084.0	952.6	772.2	631.5	531.0	468.0
55°	558.5	586.5	648.6	774.7	897.1	910.0	776.8	625.9	510.0	439.9	396.8
57.5°	489.6	513.7	575.0	675.5	761.3	754.6	628.4	497.8	419.8	367.7	336.4
60°	444.7	468.5	522.4	608.6	673.4	650.7	534.8	429.7	362.8	324.6	299.8
62.5°	402.9	421.4	471.9	534.9	581.5	555.8	457.2	370.2	317.1	284.9	265.2
65°	342.3	357.4	397.8	430.7	456.6	431.8	349.9	289.5	251.2	228.5	215.1
67.5°	284.8	294.4	319.9	331.8	350.0	322.8	263.1	222.7	200.9	181.8	172.4
70°	248.5	255.6	269.0	278.7	283.6	255.6	211.4	181.6	163.3	149.9	143.9
72.5°	212.3	218.5	221.2	229.1	226.6	200.3	169.9	146.3	133.2	124.0	116.4
75°	162.2	164.9	162.2	159.1	152.0	133.7	112.6	100.8	91.1	86.8	84.1
77.5°	118.3	117.4	113.8	108.7	96.7	85.2	73.8	69.9	65.7	63.4	62.4
80°	91.1	89.0	85.7	77.6	67.4	59.3	56.6	53.9	52.3	49.6	49.0
82.5°	67.8	66.5	61.2	54.3	47.1	43.3	41.1	40.1	38.5	37.1	37.0
85°	36.1	34.5	28.6	24.8	23.7	22.7	22.1	22.1	20.0	19.4	19.4
87.5°	12.2	10.1	10.1	9.2	9.6	9.3	10.2	9.9	10.1	10.6	9.9
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8
92.5°	23.7	25.0	26.5	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7
95°	55.8	57.2	58.6	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7
97.5°	97.5	98.6	99.7	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4
100°	126.4	127.6	128.9	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5
102.5°	159.1	159.8	160.5	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9
105°	207.5	207.9	208.3	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2
107.5°	264.0	264.3	264.5	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5
110°	299.5	299.9	300.4	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	336.4	336.7	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4
115°	391.8	392.4	393.0	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5
117.5°	447.2	447.6	448.0	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2
120°	482.6	483.9	485.1	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9
122.5°	518.3	519.3	520.1	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1
125°	573.1	573.7	574.3	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8
127.5°	624.6	625.9	627.2	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9
130°	658.8	660.4	662.1	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1
132.5°	692.7	694.3	695.9	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4
135°	744.0	745.2	746.5	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8
137.5°	791.6	792.7	793.7	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9
140°	824.8	825.9	826.9	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9
142.5°	855.0	856.0	857.1	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8
145°	901.5	901.9	902.3	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3
147.5°	943.1	943.8	944.5	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2
150°	971.5	971.8	972.2	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7
152.5°	995.2	995.8	996.3	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9
155°	1031.8	1031.8	1031.8	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4
157.5°	1063.2	1063.0	1062.7	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8
160°	1082.9	1082.5	1082.1	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5
162.5°	1100.4	1099.9	1099.3	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2
165°	1123.2	1122.6	1122.0	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6
167.5°	1141.2	1140.4	1139.6	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6
170°	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5
172.5°	1159.7	1158.8	1158.0	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4
175°	1168.2	1167.3	1166.5	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7
177.5°	1171.8	1171.2	1170.4	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1328.3	1328.3	1330.1	1336.6	1337.4	1343.0	1341.3
5°	1459.9	1470.1	1473.9	1490.1	1499.8	1504.1	1495.5
7.5°	1620.8	1649.6	1663.3	1680.3	1695.3	1699.8	1688.1
10°	1738.0	1768.2	1793.6	1809.3	1823.8	1833.5	1845.9
12.5°	1851.5	1888.6	1912.6	1934.7	1949.7	1962.0	1964.1
15°	1974.8	2030.8	2073.4	2104.7	2120.3	2128.4	2125.2
17.5°	2099.0	2151.0	2181.4	2213.3	2234.9	2236.0	2236.6
20°	2169.4	2220.0	2255.1	2278.8	2303.0	2302.0	2307.4
22.5°	2216.4	2256.3	2283.1	2300.3	2308.7	2304.5	2305.6
25°	2238.4	2250.2	2245.4	2217.9	2210.9	2185.6	2189.8
27.5°	2124.9	2068.9	2010.9	1936.3	1877.4	1830.3	1832.7
30°	1970.9	1871.8	1758.6	1663.7	1578.5	1554.8	1504.1
32.5°	1755.8	1606.9	1474.3	1385.9	1312.8	1293.0	1248.8
35°	1390.9	1246.4	1110.0	1028.1	995.7	950.5	949.9
37.5°	1081.1	953.9	881.8	820.3	788.1	760.7	758.0
40°	909.5	810.2	755.8	711.6	679.9	659.3	654.5
42.5°	789.6	709.3	658.4	631.0	606.5	596.0	588.0
45°	644.8	590.9	555.2	530.4	519.2	511.0	506.8
47.5°	539.3	503.2	479.0	462.5	453.3	444.7	447.0
50°	482.0	452.3	434.5	418.9	411.9	405.9	406.5
52.5°	435.8	409.2	394.8	383.5	374.8	370.6	368.5
55°	369.8	353.1	338.6	330.5	325.6	319.7	318.1
57.5°	315.4	302.5	290.7	281.5	280.4	274.6	275.4
60°	279.2	268.5	258.8	253.9	250.2	245.3	246.9
62.5°	249.5	240.4	231.6	227.6	223.9	220.3	221.0
65°	204.3	195.7	190.3	188.1	186.6	184.9	183.3
67.5°	162.8	157.6	154.2	149.6	146.2	145.7	144.0
70°	137.0	129.9	124.0	118.0	116.5	115.9	116.5
72.5°	109.8	105.4	103.7	100.8	100.5	99.1	100.1
75°	82.5	80.9	79.8	77.6	77.6	77.6	77.6
77.5°	60.8	59.8	59.2	58.8	58.2	57.4	57.4
80°	47.5	46.9	45.8	45.8	45.3	45.8	45.3
82.5°	35.8	35.7	34.6	34.6	34.1	33.7	34.1
85°	18.3	17.8	18.9	17.8	18.3	17.3	18.3
87.5°	10.1	10.2	9.9	10.1	9.7	10.6	9.8
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	37.3	37.9	38.2	37.9	37.7	37.4	37.2
95°	70.6	71.4	71.8	71.8	71.8	71.8	71.8
97.5°	109.4	110.4	110.7	110.7	110.6	110.5	110.4
100°	137.1	137.8	138.2	138.7	139.1	139.5	139.9
102.5°	169.5	170.2	170.4	170.3	170.2	170.2	170.1
105°	217.2	217.2	217.5	217.9	218.2	218.6	219.0
107.5°	270.2	270.8	271.0	270.8	270.5	270.3	270.1
110°	305.3	306.1	306.3	305.9	305.5	305.1	304.7



TEST NUMBER: P332355-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	340.4	341.4	341.8	341.7	341.7	341.6	341.5
115°	392.7	392.9	392.9	392.7	392.5	392.3	392.1
117.5°	446.1	446.1	445.8	445.2	444.6	444.0	443.5
120°	481.7	481.5	481.2	480.8	480.4	480.0	479.5
122.5°	517.5	517.0	516.4	515.9	515.3	514.7	514.1
125°	571.0	570.1	569.3	568.5	567.7	566.9	566.1
127.5°	623.8	622.6	621.5	620.6	619.6	618.7	617.8
130°	659.3	658.5	657.4	655.9	654.5	653.1	651.6
132.5°	693.5	692.4	691.4	690.3	689.2	688.1	687.0
135°	744.9	744.1	743.5	743.1	742.7	742.3	741.9
137.5°	795.0	794.2	793.4	792.6	791.9	791.1	790.3
140°	828.7	828.5	827.7	826.2	824.8	823.4	822.0
142.5°	859.6	859.4	858.7	857.6	856.5	855.5	854.4
145°	905.1	904.9	904.4	903.6	902.7	901.9	901.1
147.5°	948.2	948.2	947.6	946.3	945.2	943.9	942.7
150°	974.7	974.7	974.1	972.9	971.7	970.4	969.2
152.5°	999.3	999.6	999.3	998.1	997.1	996.0	995.0
155°	1035.1	1036.0	1035.7	1034.3	1032.8	1031.4	1029.9
157.5°	1065.6	1066.5	1066.4	1065.2	1064.1	1063.0	1061.8
160°	1084.6	1085.6	1085.7	1084.9	1084.0	1083.2	1082.4
162.5°	1102.2	1103.3	1103.1	1101.8	1100.5	1099.2	1097.9
165°	1124.7	1126.0	1125.8	1124.4	1123.0	1121.6	1120.1
167.5°	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1
170°	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7
172.5°	1160.6	1161.9	1161.8	1160.3	1158.9	1157.5	1156.0
175°	1168.9	1170.1	1170.1	1168.6	1167.2	1165.8	1164.3
177.5°	1172.4	1173.4	1173.3	1172.2	1171.0	1169.9	1168.8
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7

(END OF REPORT)