

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331457-935

Luminaire Tested: **S122DIP-S1005D1080U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331457-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D1080U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7106.4 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.5	2.3
10°-20°	475.3	6.7
20°-30°	689.9	9.7
30°-40°	728.0	10.2
40°-50°	644.6	9.1
50°-60°	514.4	7.2
60°-70°	349.6	4.9
70°-80°	179.3	2.5
80°-90°	47.9	0.7
90°-100°	75.1	1.1
100°-110°	233.2	3.3
110°-120°	398.7	5.6
120°-130°	524.3	7.4
130°-140°	588.5	8.3
140°-150°	577.0	8.1
150°-160°	484.0	6.8
160°-170°	321.0	4.5
170°-180°	112.2	1.6
0°-30°	1328.7	18.7
0°-40°	2056.7	28.9
0°-60°	3215.7	45.3
0°-90°	3792.5	53.4
90°-120°	707.0	9.9
90°-150°	2396.8	33.7
90°-180°	3314.0	46.6
0°-180°	7106.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	40
90°	34	1	34	1	34	17
95°	62	52	62	52	62	69
105°	222	215	222	215	222	234
115°	400	400	400	400	400	395
125°	584	582	584	582	584	521
135°	762	753	762	753	762	587
145°	924	914	924	914	924	577
155°	1053	1045	1053	1045	1053	485
165°	1138	1137	1138	1137	1138	321
175°	1179	1183	1179	1183	1179	112
180°	1185	1185	1185	1185	1185	



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	20.5	20.5	20.9	20.4	20.3	20.9	21.0	20.6	21.2	21.8	21.4
90°	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1	34.5	35.0	30.1
92.5°	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9	31.9	31.8	30.7
95°	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0	64.0	64.0	63.5
97.5°	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6	107.6	107.6	106.8
100°	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0	138.0	138.0	137.3
102.5°	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2	171.0	170.8	170.0
105°	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9	220.5	220.0	219.6
107.5°	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6	274.4	274.2	274.2
110°	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6	348.1	348.6	348.8
115°	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6	403.8	404.1	404.5
117.5°	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8	458.3	458.8	460.1
120°	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0	494.0	494.0	495.8
122.5°	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4	531.9	532.4	533.7
125°	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8	587.4	588.1	588.8
127.5°	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5	641.3	642.0	642.9
130°	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2	677.6	678.1	678.6
132.5°	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9	713.9	714.9	714.8
135°	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7	765.9	766.1	765.7
137.5°	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1	816.3	816.5	815.9
140°	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1	850.1	850.1	849.0
142.5°	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9	880.7	880.5	879.8
145°	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6	927.3	927.1	925.7
147.5°	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5	968.0	967.5	966.6
150°	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5	993.8	993.2	992.2
152.5°	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7	1017.7
155°	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3	1052.2	1051.1	1050.5
157.5°	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7	1082.3	1080.7	1080.3
160°	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8	1100.4	1099.2	1098.9
162.5°	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2	1116.6	1115.2	1114.9
165°	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3	1137.7	1136.2	1136.2
167.5°	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7	1155.1	1153.6	1153.6
170°	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2	1164.7	1163.1	1163.4
172.5°	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5	1171.9	1170.4	1170.5
175°	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3	1179.7	1178.1	1178.6
177.5°	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8	1183.1
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	20.9	19.9	18.9	19.2	17.1	16.6	13.9	11.8	11.8	11.8	11.3
90°	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0	3.7	6.4	9.0
92.5°	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8	19.7	21.7	23.7
95°	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0	54.2	56.5	58.6
97.5°	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1	96.9	98.9	100.9
100°	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0	128.8	130.6	132.3
102.5°	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7	162.0	163.5	164.9
105°	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0	215.7	216.4	217.1
107.5°	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8	270.8	271.8	272.8
110°	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1	306.3	307.7	309.0





TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5	344.7	346.1	347.4
115°	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0	401.4	402.7	404.1
117.5°	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4	458.2	460.0	461.8
120°	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	495.8	497.7	499.4
122.5°	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5	530.6	532.7	534.9
125°	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0	584.1	586.1	588.1
127.5°	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3	636.8	639.4	641.9
130°	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1	669.9	672.9	675.7
132.5°	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9	706.3	708.6	710.9
135°	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1	755.5	758.0	760.4
137.5°	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9	806.9	808.9	810.9
140°	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1	838.1	840.1	842.1
142.5°	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1	870.1	872.1	874.1
145°	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1	915.7	917.2	918.8
147.5°	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1	957.0	958.8	960.7
150°	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1	984.5	985.8	987.1
152.5°	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9	1009.3	1010.6	1011.9
155°	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2	1045.8	1046.5	1047.1
157.5°	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9	1077.4	1077.8	1078.2
160°	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1	1096.6	1097.0	1097.4
162.5°	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7	1113.8	1113.9	1114.0
165°	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1	1137.0	1136.7	1136.4
167.5°	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8	1156.1	1155.4	1154.8
170°	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2	1166.5	1165.8	1165.1
172.5°	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3	1173.7	1173.0	1172.3
175°	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2	1182.5	1181.8	1181.1
177.5°	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7	1186.2	1185.7	1185.2
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	11.3	11.5	12.0	13.0	13.4	13.9	13.3	13.2	13.1	11.9	11.9
90°	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1	33.7	33.2	33.1
92.5°	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9	32.0	32.2	32.2
95°	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0	64.0	64.0	63.8
97.5°	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6	107.6	107.6	107.6
100°	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0	138.0	138.0	137.9
102.5°	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2	171.3	171.5	171.5
105°	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9	221.4	221.8	222.1
107.5°	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6	274.7	274.9	274.5
110°	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	310.7



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6	347.1	346.6	346.0
115°	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6	403.4	403.1	402.7
117.5°	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8	457.3	456.8	456.2
120°	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0	494.0	494.0	493.7
122.5°	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4	530.9	530.3	529.9
125°	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8	586.1	585.4	585.0
127.5°	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5	639.6	638.9	638.1
130°	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2	676.7	676.3	675.6
132.5°	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9	712.0	711.0	710.2
135°	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7	765.4	765.2	764.7
137.5°	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1	816.0	815.8	815.3
140°	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1	850.1	850.1	849.6
142.5°	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9	881.1	881.2	880.9
145°	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6	927.8	928.0	927.6
147.5°	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5	969.0	969.5	969.3
150°	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5	995.1	995.8	995.8
152.5°	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1
155°	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3	1054.5	1055.6	1055.8
157.5°	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7	1085.3	1086.8	1087.0
160°	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8	1103.1	1104.5	1104.7
162.5°	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2	1119.6	1121.2	1121.4
165°	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3	1140.8	1142.4	1142.5
167.5°	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7	1158.2	1159.8	1159.9
170°	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2	1167.8	1169.3	1169.5
172.5°	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5	1175.0	1176.6	1176.6
175°	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3	1182.8	1184.4	1184.5
177.5°	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	12.0	11.5	11.5	11.0	11.5	11.5	12.0	11.9	11.9	13.1	13.2
90°	33.3	33.6	33.8	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1
92.5°	32.3	32.3	32.4	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9
95°	63.4	62.9	62.4	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0
97.5°	107.5	107.5	107.5	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6
100°	137.7	137.5	137.2	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0
102.5°	171.3	171.1	170.8	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2
105°	222.1	222.1	222.1	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9
107.5°	273.5	272.5	271.5	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6
110°	310.0	309.4	308.7	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	345.5	345.0	344.6	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6
115°	402.1	401.4	400.7	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6
117.5°	455.5	454.8	454.1	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8
120°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0
122.5°	529.3	528.8	528.4	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4
125°	584.7	584.5	584.3	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8
127.5°	637.4	636.7	636.0	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5
130°	674.8	673.8	673.0	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2
132.5°	709.5	708.7	708.0	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9
135°	764.1	763.4	762.8	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7
137.5°	814.3	813.5	812.6	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1
140°	848.8	847.9	847.0	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1
142.5°	879.9	879.1	878.2	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9
145°	926.8	925.9	925.0	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6
147.5°	968.5	967.6	966.7	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5
150°	995.1	994.5	993.8	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5
152.5°	1021.2	1020.5	1019.6	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5
155°	1055.2	1054.5	1053.8	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3
157.5°	1085.9	1084.9	1083.8	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7
160°	1103.8	1102.9	1102.0	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8
162.5°	1120.3	1119.3	1118.2	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2
165°	1141.5	1140.4	1139.3	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3
167.5°	1158.8	1157.6	1156.5	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7
170°	1168.1	1166.8	1165.4	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2
172.5°	1175.4	1174.0	1172.7	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5
175°	1183.2	1181.8	1180.5	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3
177.5°	1185.9	1184.9	1183.8	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	13.3	13.9	13.4	13.0	12.0	11.5	11.3	11.3	11.8	11.8	11.8
90°	34.5	35.0	30.1	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0
92.5°	31.9	31.8	30.7	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8
95°	64.0	64.0	63.5	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0
97.5°	107.6	107.6	106.8	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1
100°	138.0	138.0	137.3	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0
102.5°	171.0	170.8	170.0	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7
105°	220.5	220.0	219.6	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0
107.5°	274.4	274.2	274.2	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8
110°	311.1	311.1	311.1	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.1	348.6	348.8	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5
115°	403.8	404.1	404.5	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0
117.5°	458.3	458.8	460.1	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4
120°	494.0	494.0	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0
122.5°	531.9	532.4	533.7	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5
125°	587.4	588.1	588.8	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0
127.5°	641.3	642.0	642.9	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3
130°	677.6	678.1	678.6	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1
132.5°	713.9	714.9	714.8	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9
135°	765.9	766.1	765.7	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1
137.5°	816.3	816.5	815.9	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9
140°	850.1	850.1	849.0	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1
142.5°	880.7	880.5	879.8	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1
145°	927.3	927.1	925.7	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1
147.5°	968.0	967.5	966.6	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1
150°	993.8	993.2	992.2	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1
152.5°	1019.6	1018.7	1017.7	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9
155°	1052.2	1051.1	1050.5	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2
157.5°	1082.3	1080.7	1080.3	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9
160°	1100.4	1099.2	1098.9	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1
162.5°	1116.6	1115.2	1114.9	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7
165°	1137.7	1136.2	1136.2	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1
167.5°	1155.1	1153.6	1153.6	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8
170°	1164.7	1163.1	1163.4	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2
172.5°	1171.9	1170.4	1170.5	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3
175°	1179.7	1178.1	1178.6	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2
177.5°	1183.8	1182.8	1183.1	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	13.9	16.6	17.1	19.2	18.9	19.9	20.9	21.4	21.8	21.2	20.6
90°	3.7	6.4	9.0	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1
92.5°	19.7	21.7	23.7	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9
95°	54.2	56.5	58.6	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0
97.5°	96.9	98.9	100.9	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6
100°	128.8	130.6	132.3	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0
102.5°	162.0	163.5	164.9	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2
105°	215.7	216.4	217.1	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9
107.5°	270.8	271.8	272.8	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6
110°	306.3	307.7	309.0	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1





TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.7	346.1	347.4	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6
115°	401.4	402.7	404.1	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6
117.5°	458.2	460.0	461.8	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8
120°	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0
122.5°	530.6	532.7	534.9	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4
125°	584.1	586.1	588.1	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8
127.5°	636.8	639.4	641.9	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5
130°	669.9	672.9	675.7	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2
132.5°	706.3	708.6	710.9	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9
135°	755.5	758.0	760.4	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7
137.5°	806.9	808.9	810.9	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1
140°	838.1	840.1	842.1	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1
142.5°	870.1	872.1	874.1	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9
145°	915.7	917.2	918.8	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6
147.5°	957.0	958.8	960.7	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5
150°	984.5	985.8	987.1	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5
152.5°	1009.3	1010.6	1011.9	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5
155°	1045.8	1046.5	1047.1	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3
157.5°	1077.4	1077.8	1078.2	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7
160°	1096.6	1097.0	1097.4	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8
162.5°	1113.8	1113.9	1114.0	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2
165°	1137.0	1136.7	1136.4	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3
167.5°	1156.1	1155.4	1154.8	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7
170°	1166.5	1165.8	1165.1	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2
172.5°	1173.7	1173.0	1172.3	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5
175°	1182.5	1181.8	1181.1	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3
177.5°	1186.2	1185.7	1185.2	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	21.0	20.9	20.3	20.4	20.9	20.5	20.5
90°	33.7	33.2	33.1	33.3	33.6	33.8	34.0
92.5°	32.0	32.2	32.2	32.3	32.3	32.4	32.4
95°	64.0	64.0	63.8	63.4	62.9	62.4	62.0
97.5°	107.6	107.6	107.6	107.5	107.5	107.5	107.5
100°	138.0	138.0	137.9	137.7	137.5	137.2	137.0
102.5°	171.3	171.5	171.5	171.3	171.1	170.8	170.7
105°	221.4	221.8	222.1	222.1	222.1	222.1	222.1
107.5°	274.7	274.9	274.5	273.5	272.5	271.5	270.4
110°	311.1	311.1	310.7	310.0	309.4	308.7	308.1



TEST NUMBER: P331457-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.1	346.6	346.0	345.5	345.0	344.6	344.1
115°	403.4	403.1	402.7	402.1	401.4	400.7	400.0
117.5°	457.3	456.8	456.2	455.5	454.8	454.1	453.5
120°	494.0	494.0	493.7	493.1	492.4	491.7	491.0
122.5°	530.9	530.3	529.9	529.3	528.8	528.4	527.9
125°	586.1	585.4	585.0	584.7	584.5	584.3	584.1
127.5°	639.6	638.9	638.1	637.4	636.7	636.0	635.2
130°	676.7	676.3	675.6	674.8	673.8	673.0	672.1
132.5°	712.0	711.0	710.2	709.5	708.7	708.0	707.3
135°	765.4	765.2	764.7	764.1	763.4	762.8	762.1
137.5°	816.0	815.8	815.3	814.3	813.5	812.6	811.7
140°	850.1	850.1	849.6	848.8	847.9	847.0	846.1
142.5°	881.1	881.2	880.9	879.9	879.1	878.2	877.3
145°	927.8	928.0	927.6	926.8	925.9	925.0	924.1
147.5°	969.0	969.5	969.3	968.5	967.6	966.7	966.0
150°	995.1	995.8	995.8	995.1	994.5	993.8	993.2
152.5°	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7
155°	1054.5	1055.6	1055.8	1055.2	1054.5	1053.8	1053.1
157.5°	1085.3	1086.8	1087.0	1085.9	1084.9	1083.8	1082.7
160°	1103.1	1104.5	1104.7	1103.8	1102.9	1102.0	1101.1
162.5°	1119.6	1121.2	1121.4	1120.3	1119.3	1118.2	1117.1
165°	1140.8	1142.4	1142.5	1141.5	1140.4	1139.3	1138.2
167.5°	1158.2	1159.8	1159.9	1158.8	1157.6	1156.5	1155.4
170°	1167.8	1169.3	1169.5	1168.1	1166.8	1165.4	1164.2
172.5°	1175.0	1176.6	1176.6	1175.4	1174.0	1172.7	1171.3
175°	1182.8	1184.4	1184.5	1183.2	1181.8	1180.5	1179.1
177.5°	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2

(END OF REPORT)