

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332340-927

Luminaire Tested: **S123RDIP-S1000D585U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332340-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4598.7 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332340-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332340-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56
2	93	86	79	74	87	81	75	71	72	68	64	63	60	58	56	53	51	47
3	85	76	68	62	80	71	65	60	64	59	54	56	52	49	50	47	44	41
4	78	67	59	53	73	64	57	51	57	51	47	51	46	42	45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31
6	66	54	46	40	62	51	44	39	46	40	36	41	37	33	37	33	30	27
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24	22
9	53	41	34	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332340-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.7
10°-20°	347.3	7.6
20°-30°	500.2	10.9
30°-40°	563.4	12.3
40°-50°	539.0	11.7
50°-60°	441.4	9.6
60°-70°	297.8	6.5
70°-80°	149.8	3.3
80°-90°	41.3	0.9
90°-100°	37.5	0.8
100°-110°	112.2	2.4
110°-120°	190.8	4.1
120°-130°	250.9	5.5
130°-140°	282.0	6.1
140°-150°	277.2	6.0
150°-160°	233.4	5.1
160°-170°	155.4	3.4
170°-180°	54.4	1.2
0°-30°	972.3	21.1
0°-40°	1535.7	33.4
0°-60°	2516.0	54.7
0°-90°	3005.0	65.3
90°-120°	340.4	7.4
90°-150°	1150.6	25.0
90°-180°	1594.0	34.7
0°-180°	4598.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	0	5	11	13	14	4
95°	27	30	33	35	35	30
105°	102	103	107	107	108	109
115°	192	193	192	193	192	190
125°	281	282	282	280	278	251
135°	365	367	367	365	364	281
145°	442	443	445	444	442	276
155°	506	507	507	508	506	233
165°	552	550	550	553	550	155
175°	574	572	572	574	572	54
180°	575	575	575	575	575	



TEST NUMBER: P332340-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.8	18.9	17.0	15.1	13.2	12.4	12.6	12.8	13.2	13.4	13.3
90°	0.5	1.4	2.5	3.5	4.4	5.6	6.9	8.2	9.5	10.9	11.2
92.5°	10.9	11.6	12.3	13.0	13.7	14.4	15.1	15.8	16.6	17.3	17.7
95°	26.7	27.3	28.0	28.8	29.5	30.3	31.1	31.8	32.6	33.4	33.8
97.5°	47.4	47.8	48.4	49.0	49.4	50.0	50.5	51.2	51.7	52.4	52.8
100°	61.5	62.0	62.7	63.3	63.8	64.4	64.9	65.4	65.9	66.4	66.7
102.5°	77.7	78.1	78.4	78.8	79.1	79.7	80.3	81.0	81.7	82.3	82.6
105°	101.6	101.9	102.0	102.3	102.5	103.0	103.9	104.8	105.8	106.6	106.6
107.5°	129.5	129.6	129.8	129.8	130.0	130.2	130.6	130.9	131.3	131.7	132.0
110°	146.9	147.0	147.3	147.4	147.7	147.8	148.1	148.3	148.5	148.7	149.1



TEST NUMBER: P332340-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	164.9	165.0	165.2	165.2	165.4	165.5	165.6	165.6	165.6	165.6	166.1
115°	192.0	192.3	192.7	193.0	193.2	193.3	193.1	192.9	192.7	192.5	192.6
117.5°	219.4	219.5	219.8	219.9	220.1	220.1	219.8	219.6	219.4	219.0	219.0
120°	236.3	236.9	237.5	238.1	238.8	238.8	238.3	237.8	237.3	236.8	236.7
122.5°	254.1	254.4	254.9	255.3	255.8	255.9	255.6	255.4	255.1	254.8	254.6
125°	281.1	281.4	281.6	281.9	282.3	282.3	282.1	281.9	281.7	281.5	281.1
127.5°	306.0	306.7	307.3	307.9	308.6	308.8	308.6	308.3	308.1	307.9	307.4
130°	322.7	323.4	324.2	325.0	325.8	326.1	325.8	325.5	325.2	324.9	324.5
132.5°	339.2	340.1	340.9	341.7	342.5	342.8	342.5	342.3	342.1	341.9	341.4
135°	364.6	365.3	365.8	366.5	367.0	367.3	367.2	367.1	367.0	366.9	366.5
137.5°	388.2	388.6	389.1	389.7	390.1	390.5	390.8	391.0	391.3	391.6	391.2
140°	404.4	404.9	405.4	405.9	406.4	406.7	406.8	406.9	407.0	407.1	407.0
142.5°	419.2	419.7	420.3	420.7	421.2	421.6	421.8	421.9	422.2	422.3	422.2
145°	442.4	442.6	442.8	443.0	443.1	443.4	443.7	444.0	444.3	444.7	444.5
147.5°	462.6	463.0	463.3	463.7	464.1	464.4	464.7	464.9	465.2	465.5	465.5
150°	476.7	476.9	477.1	477.3	477.5	477.7	477.9	478.1	478.3	478.5	478.5
152.5°	488.3	488.5	488.9	489.1	489.4	489.6	489.7	489.8	490.0	490.0	490.2
155°	506.5	506.5	506.5	506.5	506.5	506.6	506.7	506.8	506.9	507.0	507.4
157.5°	522.0	522.0	521.8	521.7	521.6	521.6	521.7	521.7	521.8	521.9	522.3
160°	531.8	531.6	531.4	531.2	531.0	530.9	530.9	530.9	530.9	530.9	531.4
162.5°	540.5	540.2	540.0	539.6	539.4	539.3	539.4	539.5	539.6	539.6	540.1
165°	551.7	551.4	551.1	550.8	550.5	550.3	550.3	550.3	550.3	550.3	551.0
167.5°	560.6	560.2	559.8	559.4	559.0	558.9	559.0	559.0	559.1	559.2	559.8
170°	565.7	565.3	564.9	564.5	564.1	563.9	563.9	563.9	563.9	563.9	564.6
172.5°	569.7	569.3	568.9	568.5	568.1	567.9	567.9	567.9	567.9	567.9	568.5
175°	573.9	573.5	573.1	572.7	572.3	572.0	572.0	572.0	572.0	572.0	572.7
177.5°	575.6	575.3	575.0	574.6	574.3	574.1	574.1	574.1	574.1	574.1	574.6
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P332340-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	13.2	13.1	12.9	12.8	12.7	12.5	12.4	12.2
90°	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	18.0	18.3	18.6	18.8	18.6	18.5	18.4	18.2
95°	34.2	34.6	35.0	35.3	35.3	35.3	35.3	35.3
97.5°	53.2	53.7	54.2	54.3	54.3	54.3	54.3	54.2
100°	67.0	67.3	67.7	67.9	68.0	68.3	68.4	68.7
102.5°	82.9	83.3	83.5	83.7	83.7	83.6	83.6	83.5
105°	106.6	106.6	106.6	106.7	106.9	107.1	107.3	107.6
107.5°	132.3	132.6	132.9	133.1	132.9	132.8	132.7	132.6
110°	149.5	149.9	150.3	150.4	150.2	150.0	149.8	149.6



TEST NUMBER: P332340-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	166.6	167.1	167.5	167.8	167.8	167.7	167.7	167.6
115°	192.7	192.8	192.9	192.9	192.8	192.7	192.6	192.5
117.5°	219.0	219.0	219.0	218.8	218.6	218.2	218.0	217.7
120°	236.5	236.5	236.4	236.2	236.0	235.8	235.6	235.4
122.5°	254.3	254.1	253.8	253.5	253.3	252.9	252.7	252.4
125°	280.7	280.3	279.9	279.5	279.1	278.7	278.3	277.9
127.5°	306.7	306.2	305.6	305.1	304.7	304.2	303.7	303.2
130°	324.1	323.7	323.3	322.7	322.0	321.3	320.6	319.9
132.5°	340.9	340.4	339.9	339.5	338.9	338.3	337.8	337.2
135°	366.1	365.7	365.3	365.0	364.8	364.6	364.4	364.2
137.5°	390.7	390.3	389.9	389.5	389.1	388.7	388.3	387.9
140°	406.9	406.8	406.7	406.3	405.6	404.9	404.2	403.5
142.5°	422.1	422.0	421.9	421.6	421.0	420.5	419.9	419.4
145°	444.4	444.3	444.3	443.9	443.5	443.1	442.8	442.4
147.5°	465.5	465.5	465.5	465.2	464.6	464.0	463.4	462.8
150°	478.5	478.5	478.5	478.2	477.6	477.0	476.4	475.8
152.5°	490.4	490.6	490.8	490.5	490.0	489.5	489.0	488.5
155°	507.8	508.2	508.6	508.4	507.7	507.0	506.4	505.6
157.5°	522.8	523.2	523.6	523.5	522.9	522.4	521.8	521.3
160°	532.0	532.4	532.9	533.0	532.6	532.2	531.8	531.4
162.5°	540.6	541.1	541.6	541.5	540.9	540.3	539.6	539.0
165°	551.6	552.2	552.8	552.7	552.0	551.3	550.6	549.9
167.5°	560.5	561.1	561.7	561.7	561.1	560.5	559.8	559.2
170°	565.3	566.0	566.7	566.7	566.0	565.3	564.6	563.9
172.5°	569.1	569.7	570.4	570.4	569.7	568.9	568.2	567.5
175°	573.2	573.9	574.5	574.4	573.7	573.0	572.3	571.6
177.5°	575.1	575.6	576.1	576.0	575.4	574.9	574.3	573.8
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2

(END OF REPORT)