

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332341-927

Luminaire Tested: **S123RDIP-S1000D585U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332341-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D585U927-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4684.3 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332341-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332341-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	58	47	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332341-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.8	2.7
10°-20°	347.3	7.4
20°-30°	500.2	10.7
30°-40°	563.4	12.0
40°-50°	539.0	11.5
50°-60°	441.4	9.4
60°-70°	297.8	6.4
70°-80°	149.8	3.2
80°-90°	41.4	0.9
90°-100°	124.2	2.7
100°-110°	351.7	7.5
110°-120°	346.0	7.4
120°-130°	276.0	5.9
130°-140°	217.6	4.6
140°-150°	162.4	3.5
150°-160°	113.2	2.4
160°-170°	66.5	1.4
170°-180°	21.6	0.5
0°-30°	972.3	20.8
0°-40°	1535.7	32.8
0°-60°	2516.0	53.7
0°-90°	3005.0	64.2
90°-120°	822.0	17.5
90°-150°	1478.0	31.6
90°-180°	1679.0	35.8
0°-180°	4684.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	1	5	11	13	13	4
95°	15	50	268	78	52	17
105°	52	78	363	635	575	56
115°	93	115	278	609	699	92
125°	129	152	259	470	551	114
135°	151	180	256	387	447	117
145°	172	197	252	317	349	108
155°	196	211	244	278	290	90
165°	214	220	234	248	252	60
175°	223	223	225	228	227	21
180°	223	223	223	223	223	



TEST NUMBER: P332341-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.9	18.9	17.0	15.2	13.2	12.4	12.7	12.9	13.2	13.5	13.2
90°	0.9	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9
92.5°	5.6	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4
95°	15.4	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3
97.5°	26.2	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3
100°	33.4	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9
102.5°	41.0	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5
105°	52.4	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0
107.5°	64.5	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7
110°	73.2	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3



TEST NUMBER: P332341-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.1	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9
115°	92.6	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1
117.5°	104.1	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8
120°	112.1	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7
122.5°	118.9	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4
125°	128.8	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7
127.5°	136.3	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3
130°	141.0	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3
132.5°	144.6	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5
135°	150.9	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4
137.5°	156.9	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1
140°	160.9	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8
142.5°	165.2	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9
145°	172.1	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0
147.5°	179.2	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2
150°	183.9	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7
152.5°	188.6	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9
155°	195.7	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5
157.5°	201.2	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6
160°	205.6	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3
162.5°	208.8	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1
165°	213.7	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7
167.5°	217.5	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5
170°	219.6	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9
172.5°	221.0	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4
175°	222.8	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5
177.5°	223.6	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332341-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	13.1	13.0	12.9	12.9	12.6	12.5	12.4	12.1
90°	11.3	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	38.0	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	162.6	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	405.5	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	532.7	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	575.0	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	587.4	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	551.8	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	517.8	600.9	657.9	689.5	702.2	705.8	704.9	703.9





TEST NUMBER: P332341-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	484.2	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	439.7	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	407.3	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	390.4	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	377.0	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	359.2	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	343.6	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	333.9	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	324.9	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	312.7	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	301.6	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	295.1	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	288.9	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	281.5	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	275.4	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	271.1	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	267.1	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	261.2	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	254.8	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	251.2	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	246.9	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	241.3	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	236.4	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	233.1	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	230.3	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.4	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	223.9	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)