

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331322-935

Luminaire Tested: **S122DIP-S485D1080U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331322-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D1080U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5164.5 lumens  
Efficiency: N/A  
Efficacy: 104.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36				
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26				
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23				
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20				
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17				
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15				
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	19	17	14				
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	13				
9	49	37	30	25	45	34	28	24	29	24	20	23	19	17	18	15	14	11				
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.7	1.5
10°-20°	231.6	4.5
20°-30°	336.2	6.5
30°-40°	354.8	6.9
40°-50°	314.1	6.1
50°-60°	250.7	4.9
60°-70°	170.4	3.3
70°-80°	87.4	1.7
80°-90°	25.8	0.5
90°-100°	75.1	1.5
100°-110°	233.2	4.5
110°-120°	398.7	7.7
120°-130°	524.3	10.2
130°-140°	588.5	11.4
140°-150°	577.0	11.2
150°-160°	484.0	9.4
160°-170°	321.0	6.2
170°-180°	112.2	2.2
0°-30°	647.5	12.5
0°-40°	1002.3	19.4
0°-60°	1567.1	30.3
0°-90°	1850.6	35.8
90°-120°	707.0	13.7
90°-150°	2396.8	46.4
90°-180°	3314.0	64.2
0°-180°	5164.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	20
90°	34	1	34	1	34	16
95°	62	52	62	52	62	69
105°	222	215	222	215	222	234
115°	400	400	400	400	400	395
125°	584	582	584	582	584	521
135°	762	753	762	753	762	587
145°	924	914	924	914	924	577
155°	1053	1045	1053	1045	1053	485
165°	1138	1137	1138	1137	1138	321
175°	1179	1183	1179	1183	1179	112
180°	1185	1185	1185	1185	1185	



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	13.5	13.4	13.7	13.3	13.3	13.6	13.7	13.5	13.9	14.2	13.5
90°	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1	34.5	35.0	30.1
92.5°	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9	31.9	31.8	30.7
95°	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0	64.0	64.0	63.5
97.5°	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6	107.6	107.6	106.8
100°	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0	138.0	138.0	137.3
102.5°	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2	171.0	170.8	170.0
105°	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9	220.5	220.0	219.6
107.5°	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6	274.4	274.2	274.2
110°	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6	348.1	348.6	348.8
115°	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6	403.8	404.1	404.5
117.5°	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8	458.3	458.8	460.1
120°	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0	494.0	494.0	495.8
122.5°	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4	531.9	532.4	533.7
125°	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8	587.4	588.1	588.8
127.5°	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5	641.3	642.0	642.9
130°	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2	677.6	678.1	678.6
132.5°	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9	713.9	714.9	714.8
135°	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7	765.9	766.1	765.7
137.5°	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1	816.3	816.5	815.9
140°	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1	850.1	850.1	849.0
142.5°	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9	880.7	880.5	879.8
145°	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6	927.3	927.1	925.7
147.5°	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5	968.0	967.5	966.6
150°	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5	993.8	993.2	992.2
152.5°	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7	1017.7
155°	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3	1052.2	1051.1	1050.5
157.5°	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7	1082.3	1080.7	1080.3
160°	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8	1100.4	1099.2	1098.9
162.5°	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2	1116.6	1115.2	1114.9
165°	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3	1137.7	1136.2	1136.2
167.5°	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7	1155.1	1153.6	1153.6
170°	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2	1164.7	1163.1	1163.4
172.5°	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5	1171.9	1170.4	1170.5
175°	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3	1179.7	1178.1	1178.6
177.5°	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8	1183.1
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	12.7	11.8	10.8	10.6	9.3	8.7	7.1	5.9	6.1	6.4	6.5
90°	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0	3.7	6.4	9.0
92.5°	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8	19.7	21.7	23.7
95°	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0	54.2	56.5	58.6
97.5°	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1	96.9	98.9	100.9
100°	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0	128.8	130.6	132.3
102.5°	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7	162.0	163.5	164.9
105°	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0	215.7	216.4	217.1
107.5°	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8	270.8	271.8	272.8
110°	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1	306.3	307.7	309.0





TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5	344.7	346.1	347.4
115°	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0	401.4	402.7	404.1
117.5°	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4	458.2	460.0	461.8
120°	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	495.8	497.7	499.4
122.5°	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5	530.6	532.7	534.9
125°	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0	584.1	586.1	588.1
127.5°	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3	636.8	639.4	641.9
130°	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1	669.9	672.9	675.7
132.5°	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9	706.3	708.6	710.9
135°	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1	755.5	758.0	760.4
137.5°	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9	806.9	808.9	810.9
140°	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1	838.1	840.1	842.1
142.5°	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1	870.1	872.1	874.1
145°	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1	915.7	917.2	918.8
147.5°	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1	957.0	958.8	960.7
150°	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1	984.5	985.8	987.1
152.5°	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9	1009.3	1010.6	1011.9
155°	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2	1045.8	1046.5	1047.1
157.5°	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9	1077.4	1077.8	1078.2
160°	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1	1096.6	1097.0	1097.4
162.5°	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7	1113.8	1113.9	1114.0
165°	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1	1137.0	1136.7	1136.4
167.5°	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8	1156.1	1155.4	1154.8
170°	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2	1166.5	1165.8	1165.1
172.5°	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3	1173.7	1173.0	1172.3
175°	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2	1182.5	1181.8	1181.1
177.5°	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7	1186.2	1185.7	1185.2
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	6.7	7.2	7.9	8.9	9.6	10.3	10.0	9.9	9.8	9.2	9.2
90°	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1	33.7	33.2	33.1
92.5°	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9	32.0	32.2	32.2
95°	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0	64.0	64.0	63.8
97.5°	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6	107.6	107.6	107.6
100°	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0	138.0	138.0	137.9
102.5°	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2	171.3	171.5	171.5
105°	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9	221.4	221.8	222.1
107.5°	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6	274.7	274.9	274.5
110°	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	310.7



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6	347.1	346.6	346.0
115°	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6	403.4	403.1	402.7
117.5°	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8	457.3	456.8	456.2
120°	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0	494.0	494.0	493.7
122.5°	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4	530.9	530.3	529.9
125°	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8	586.1	585.4	585.0
127.5°	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5	639.6	638.9	638.1
130°	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2	676.7	676.3	675.6
132.5°	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9	712.0	711.0	710.2
135°	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7	765.4	765.2	764.7
137.5°	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1	816.0	815.8	815.3
140°	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1	850.1	850.1	849.6
142.5°	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9	881.1	881.2	880.9
145°	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6	927.8	928.0	927.6
147.5°	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5	969.0	969.5	969.3
150°	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5	995.1	995.8	995.8
152.5°	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1
155°	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3	1054.5	1055.6	1055.8
157.5°	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7	1085.3	1086.8	1087.0
160°	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8	1103.1	1104.5	1104.7
162.5°	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2	1119.6	1121.2	1121.4
165°	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3	1140.8	1142.4	1142.5
167.5°	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7	1158.2	1159.8	1159.9
170°	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2	1167.8	1169.3	1169.5
172.5°	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5	1175.0	1176.6	1176.6
175°	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3	1182.8	1184.4	1184.5
177.5°	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	9.2	9.0	9.0	8.9	9.0	9.0	9.2	9.2	9.2	9.8	9.9
90°	33.3	33.6	33.8	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1
92.5°	32.3	32.3	32.4	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9
95°	63.4	62.9	62.4	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0
97.5°	107.5	107.5	107.5	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6
100°	137.7	137.5	137.2	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0
102.5°	171.3	171.1	170.8	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2
105°	222.1	222.1	222.1	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9
107.5°	273.5	272.5	271.5	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6
110°	310.0	309.4	308.7	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	345.5	345.0	344.6	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6
115°	402.1	401.4	400.7	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6
117.5°	455.5	454.8	454.1	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8
120°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0
122.5°	529.3	528.8	528.4	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4
125°	584.7	584.5	584.3	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8
127.5°	637.4	636.7	636.0	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5
130°	674.8	673.8	673.0	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2
132.5°	709.5	708.7	708.0	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9
135°	764.1	763.4	762.8	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7
137.5°	814.3	813.5	812.6	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1
140°	848.8	847.9	847.0	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1
142.5°	879.9	879.1	878.2	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9
145°	926.8	925.9	925.0	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6
147.5°	968.5	967.6	966.7	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5
150°	995.1	994.5	993.8	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5
152.5°	1021.2	1020.5	1019.6	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5
155°	1055.2	1054.5	1053.8	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3
157.5°	1085.9	1084.9	1083.8	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7
160°	1103.8	1102.9	1102.0	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8
162.5°	1120.3	1119.3	1118.2	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2
165°	1141.5	1140.4	1139.3	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3
167.5°	1158.8	1157.6	1156.5	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7
170°	1168.1	1166.8	1165.4	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2
172.5°	1175.4	1174.0	1172.7	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5
175°	1183.2	1181.8	1180.5	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3
177.5°	1185.9	1184.9	1183.8	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	10.0	10.3	9.6	8.9	7.9	7.2	6.7	6.5	6.4	6.1	5.9
90°	34.5	35.0	30.1	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0
92.5°	31.9	31.8	30.7	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8
95°	64.0	64.0	63.5	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0
97.5°	107.6	107.6	106.8	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1
100°	138.0	138.0	137.3	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0
102.5°	171.0	170.8	170.0	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7
105°	220.5	220.0	219.6	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0
107.5°	274.4	274.2	274.2	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8
110°	311.1	311.1	311.1	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.1	348.6	348.8	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5
115°	403.8	404.1	404.5	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0
117.5°	458.3	458.8	460.1	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4
120°	494.0	494.0	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0
122.5°	531.9	532.4	533.7	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5
125°	587.4	588.1	588.8	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0
127.5°	641.3	642.0	642.9	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3
130°	677.6	678.1	678.6	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1
132.5°	713.9	714.9	714.8	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9
135°	765.9	766.1	765.7	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1
137.5°	816.3	816.5	815.9	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9
140°	850.1	850.1	849.0	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1
142.5°	880.7	880.5	879.8	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1
145°	927.3	927.1	925.7	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1
147.5°	968.0	967.5	966.6	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1
150°	993.8	993.2	992.2	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1
152.5°	1019.6	1018.7	1017.7	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9
155°	1052.2	1051.1	1050.5	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2
157.5°	1082.3	1080.7	1080.3	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9
160°	1100.4	1099.2	1098.9	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1
162.5°	1116.6	1115.2	1114.9	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7
165°	1137.7	1136.2	1136.2	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1
167.5°	1155.1	1153.6	1153.6	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8
170°	1164.7	1163.1	1163.4	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2
172.5°	1171.9	1170.4	1170.5	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3
175°	1179.7	1178.1	1178.6	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2
177.5°	1183.8	1182.8	1183.1	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	7.1	8.7	9.3	10.6	10.8	11.8	12.7	13.5	14.2	13.9	13.5
90°	3.7	6.4	9.0	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1
92.5°	19.7	21.7	23.7	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9
95°	54.2	56.5	58.6	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0
97.5°	96.9	98.9	100.9	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6
100°	128.8	130.6	132.3	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0
102.5°	162.0	163.5	164.9	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2
105°	215.7	216.4	217.1	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9
107.5°	270.8	271.8	272.8	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6
110°	306.3	307.7	309.0	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1





TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.7	346.1	347.4	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6
115°	401.4	402.7	404.1	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6
117.5°	458.2	460.0	461.8	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8
120°	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0
122.5°	530.6	532.7	534.9	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4
125°	584.1	586.1	588.1	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8
127.5°	636.8	639.4	641.9	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5
130°	669.9	672.9	675.7	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2
132.5°	706.3	708.6	710.9	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9
135°	755.5	758.0	760.4	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7
137.5°	806.9	808.9	810.9	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1
140°	838.1	840.1	842.1	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1
142.5°	870.1	872.1	874.1	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9
145°	915.7	917.2	918.8	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6
147.5°	957.0	958.8	960.7	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5
150°	984.5	985.8	987.1	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5
152.5°	1009.3	1010.6	1011.9	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5
155°	1045.8	1046.5	1047.1	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3
157.5°	1077.4	1077.8	1078.2	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7
160°	1096.6	1097.0	1097.4	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8
162.5°	1113.8	1113.9	1114.0	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2
165°	1137.0	1136.7	1136.4	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3
167.5°	1156.1	1155.4	1154.8	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7
170°	1166.5	1165.8	1165.1	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2
172.5°	1173.7	1173.0	1172.3	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5
175°	1182.5	1181.8	1181.1	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3
177.5°	1186.2	1185.7	1185.2	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	13.7	13.6	13.3	13.3	13.7	13.4	13.5
90°	33.7	33.2	33.1	33.3	33.6	33.8	34.0
92.5°	32.0	32.2	32.2	32.3	32.3	32.4	32.4
95°	64.0	64.0	63.8	63.4	62.9	62.4	62.0
97.5°	107.6	107.6	107.6	107.5	107.5	107.5	107.5
100°	138.0	138.0	137.9	137.7	137.5	137.2	137.0
102.5°	171.3	171.5	171.5	171.3	171.1	170.8	170.7
105°	221.4	221.8	222.1	222.1	222.1	222.1	222.1
107.5°	274.7	274.9	274.5	273.5	272.5	271.5	270.4
110°	311.1	311.1	310.7	310.0	309.4	308.7	308.1



TEST NUMBER: P331322-935

CATALOG NUMBER: S122DIP-S485D1080U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.1	346.6	346.0	345.5	345.0	344.6	344.1
115°	403.4	403.1	402.7	402.1	401.4	400.7	400.0
117.5°	457.3	456.8	456.2	455.5	454.8	454.1	453.5
120°	494.0	494.0	493.7	493.1	492.4	491.7	491.0
122.5°	530.9	530.3	529.9	529.3	528.8	528.4	527.9
125°	586.1	585.4	585.0	584.7	584.5	584.3	584.1
127.5°	639.6	638.9	638.1	637.4	636.7	636.0	635.2
130°	676.7	676.3	675.6	674.8	673.8	673.0	672.1
132.5°	712.0	711.0	710.2	709.5	708.7	708.0	707.3
135°	765.4	765.2	764.7	764.1	763.4	762.8	762.1
137.5°	816.0	815.8	815.3	814.3	813.5	812.6	811.7
140°	850.1	850.1	849.6	848.8	847.9	847.0	846.1
142.5°	881.1	881.2	880.9	879.9	879.1	878.2	877.3
145°	927.8	928.0	927.6	926.8	925.9	925.0	924.1
147.5°	969.0	969.5	969.3	968.5	967.6	966.7	966.0
150°	995.1	995.8	995.8	995.1	994.5	993.8	993.2
152.5°	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7
155°	1054.5	1055.6	1055.8	1055.2	1054.5	1053.8	1053.1
157.5°	1085.3	1086.8	1087.0	1085.9	1084.9	1083.8	1082.7
160°	1103.1	1104.5	1104.7	1103.8	1102.9	1102.0	1101.1
162.5°	1119.6	1121.2	1121.4	1120.3	1119.3	1118.2	1117.1
165°	1140.8	1142.4	1142.5	1141.5	1140.4	1139.3	1138.2
167.5°	1158.2	1159.8	1159.9	1158.8	1157.6	1156.5	1155.4
170°	1167.8	1169.3	1169.5	1168.1	1166.8	1165.4	1164.2
172.5°	1175.0	1176.6	1176.6	1175.4	1174.0	1172.7	1171.3
175°	1182.8	1184.4	1184.5	1183.2	1181.8	1180.5	1179.1
177.5°	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2

(END OF REPORT)