

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332365-927

Luminaire Tested: **S123RDIP-S1165D365U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332365-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4510.1 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332365-927

CATALOG NUMBER: S123RDIP-S1165D365U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332365-927

CATALOG NUMBER: S123RDIP-S1165D365U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	114	114	114	114	108	108	108	108	98	98	98		89	89	89		81	81	81	77
1	104	100	96	93	99	96	92	89	87	84	82		79	77	76		72	71	69	66
2	95	88	82	77	91	84	79	74	77	73	69		70	67	64		64	62	59	56
3	87	78	70	64	83	75	68	62	68	63	58		63	58	55		57	54	51	48
4	80	69	61	55	76	66	59	53	61	55	50		56	51	47		52	48	44	42
5	74	62	54	48	70	60	52	46	55	49	44		51	45	41		47	42	39	36
6	68	56	48	42	65	54	46	41	50	43	39		46	41	37		43	38	35	32
7	64	51	43	37	60	49	42	36	45	39	34		42	37	33		39	34	31	29
8	59	47	39	33	56	45	37	32	42	35	31		39	33	29		36	31	28	26
9	55	43	35	30	53	41	34	29	38	32	28		36	30	27		33	29	25	23
10	52	39	32	27	49	38	31	26	36	30	25		33	28	24		31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332365-927

CATALOG NUMBER: S123RDIP-S1165D365U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	3.2
10°-20°	401.2	8.9
20°-30°	577.6	12.8
30°-40°	650.7	14.4
40°-50°	622.5	13.8
50°-60°	509.7	11.3
60°-70°	343.9	7.6
70°-80°	173.0	3.8
80°-90°	46.8	1.0
90°-100°	77.0	1.7
100°-110°	217.9	4.8
110°-120°	214.4	4.8
120°-130°	171.0	3.8
130°-140°	134.8	3.0
140°-150°	100.6	2.2
150°-160°	70.1	1.6
160°-170°	41.2	0.9
170°-180°	13.4	0.3
0°-30°	1123.0	24.9
0°-40°	1773.6	39.3
0°-60°	2905.8	64.4
0°-90°	3469.6	76.9
90°-120°	509.3	11.3
90°-150°	915.7	20.3
90°-180°	1040.0	23.1
0°-180°	4510.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	1	3	7	8	8	4
95°	10	31	166	48	32	10
105°	32	48	225	394	356	35
115°	57	72	172	378	433	57
125°	80	94	161	291	342	71
135°	94	112	158	240	277	72
145°	107	122	156	197	216	67
155°	121	131	152	172	179	56
165°	132	136	145	154	156	37
175°	138	138	139	141	141	13
180°	138	138	138	138	138	



TEST NUMBER: P332365-927

CATALOG NUMBER: S123RDIP-S1165D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.0	21.7	19.4	17.1	14.8	13.7	13.9	14.0	14.2	14.3	14.1
90°	0.6	1.1	1.7	2.5	3.1	3.6	4.5	5.3	6.2	7.0	6.7
92.5°	3.5	5.1	7.5	9.7	12.0	16.2	23.5	35.6	47.4	43.0	32.5
95°	9.5	10.4	13.5	18.2	25.5	36.4	60.2	101.9	147.8	166.0	134.7
97.5°	16.2	16.5	18.9	23.1	30.3	42.1	64.8	111.8	188.4	257.3	275.2
100°	20.8	21.0	23.0	26.9	33.6	44.5	64.1	105.5	179.2	265.1	320.3
102.5°	25.4	25.9	27.6	31.4	37.4	47.5	65.0	100.1	165.7	250.6	322.5
105°	32.5	33.4	35.0	38.3	43.6	52.4	67.5	96.3	149.2	225.1	305.4
107.5°	40.0	40.8	42.5	45.7	50.7	58.8	72.1	96.0	138.7	202.6	275.5
110°	45.3	46.2	47.6	50.7	55.5	63.3	75.9	97.1	134.7	189.8	256.7



TEST NUMBER: P332365-927

CATALOG NUMBER: S123RDIP-S1165D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.3	51.1	52.5	55.6	60.4	68.0	79.7	99.4	132.4	181.3	240.3
115°	57.4	58.5	60.2	63.0	67.7	75.3	86.0	103.0	131.6	172.1	220.6
117.5°	64.5	65.8	67.2	69.8	75.1	82.1	92.6	107.8	132.1	166.8	208.7
120°	69.4	70.3	71.7	74.5	79.8	86.7	96.9	111.4	133.0	164.3	202.4
122.5°	73.7	74.5	75.9	79.0	84.1	91.5	101.3	114.8	134.5	162.8	197.3
125°	79.8	80.3	82.0	85.1	90.4	98.0	107.8	120.1	136.9	160.7	190.7
127.5°	84.4	85.2	87.4	90.5	96.3	103.9	113.4	124.5	139.6	159.7	184.8
130°	87.4	88.2	90.7	94.0	100.0	107.5	116.8	127.4	141.4	159.0	181.6
132.5°	89.6	90.6	93.4	97.4	103.3	110.7	119.6	130.1	142.8	158.8	178.8
135°	93.5	94.6	97.7	101.9	107.8	115.3	124.0	133.6	144.7	158.4	175.0
137.5°	97.2	98.4	101.4	105.8	111.7	118.7	127.1	136.1	146.1	157.8	171.7
140°	99.7	101.1	103.9	108.4	113.9	121.0	129.0	137.4	146.9	157.6	169.6
142.5°	102.3	103.5	106.5	110.6	116.2	122.7	130.6	138.8	147.7	157.2	167.9
145°	106.6	107.5	110.0	114.2	119.0	125.4	132.7	140.2	148.1	156.5	165.4
147.5°	111.1	111.5	114.0	117.6	122.2	127.7	134.4	141.2	148.1	155.4	163.1
150°	113.9	114.2	116.5	120.1	124.0	129.0	135.5	141.4	148.1	154.6	161.5
152.5°	116.8	116.9	119.1	122.3	125.8	130.6	136.2	141.8	147.4	153.4	159.7
155°	121.2	121.2	122.9	125.7	128.8	132.7	137.4	142.0	146.7	151.5	157.0
157.5°	124.7	124.9	126.3	128.7	131.3	134.4	138.2	142.2	145.8	149.7	154.0
160°	127.4	127.4	128.5	130.7	132.7	135.5	138.9	142.2	145.3	148.4	152.0
162.5°	129.4	129.4	130.3	132.1	133.8	136.2	139.1	142.0	144.4	147.0	150.0
165°	132.4	132.1	132.7	134.1	135.2	137.2	139.4	141.4	143.1	145.0	147.3
167.5°	134.7	134.4	134.7	135.7	136.5	137.8	139.3	140.9	141.7	143.0	144.7
170°	136.0	135.5	135.8	136.6	137.2	137.8	139.1	140.2	140.9	141.6	143.1
172.5°	137.0	136.6	136.7	137.3	137.6	137.9	139.1	140.1	140.1	140.5	141.5
175°	138.0	137.8	137.4	138.0	138.0	138.3	138.9	139.4	139.1	139.1	139.7
177.5°	138.6	138.3	138.1	138.3	138.3	138.3	138.6	138.9	138.6	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332365-927

CATALOG NUMBER: S123RDIP-S1165D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	13.9	13.7	13.5	13.5	13.2	13.0	12.8	12.6
90°	7.0	7.3	7.5	8.1	7.8	8.1	8.4	8.1
92.5°	23.6	18.7	16.5	15.1	14.6	13.7	14.0	13.5
95°	100.8	68.3	53.5	43.4	38.1	35.6	33.6	32.5
97.5°	251.2	201.2	165.1	131.7	111.0	98.4	90.8	88.4
100°	330.0	307.4	274.6	234.9	206.6	186.2	175.2	175.5
102.5°	356.2	355.5	336.4	311.2	289.2	273.1	264.0	257.5
105°	363.9	391.9	397.2	390.0	377.1	366.5	357.5	356.1
107.5°	341.8	387.3	411.9	421.8	422.1	418.4	415.4	412.9
110°	320.8	372.3	407.6	427.2	435.1	437.3	436.7	436.2



TEST NUMBER: P332365-927

CATALOG NUMBER: S123RDIP-S1165D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.0	352.6	392.1	417.3	431.7	438.6	440.8	440.8
115°	272.4	321.1	362.3	392.8	413.8	426.0	431.7	433.1
117.5°	252.4	294.5	331.4	362.3	384.3	398.4	406.4	408.3
120°	241.9	279.6	313.2	341.5	363.6	379.3	386.0	387.7
122.5°	233.6	267.8	298.9	325.2	344.8	358.9	366.3	368.4
125°	222.5	253.1	280.0	302.4	320.3	332.6	339.6	341.5
127.5°	212.9	240.1	264.4	284.8	300.7	311.2	317.6	319.3
130°	206.8	232.1	254.8	273.8	288.6	298.7	304.6	306.8
132.5°	201.3	224.4	245.6	263.7	277.7	287.7	292.9	294.5
135°	193.7	213.6	231.8	247.7	261.5	269.9	274.9	276.9
137.5°	186.8	203.1	218.8	232.7	244.2	252.7	256.9	258.3
140°	182.8	197.1	210.5	222.5	233.2	241.1	245.5	245.3
142.5°	179.0	191.2	202.9	213.3	222.4	229.4	233.4	233.1
145°	174.4	183.6	192.6	200.7	207.7	213.6	215.9	216.4
147.5°	170.6	178.0	185.2	191.0	196.3	200.3	202.4	202.6
150°	167.9	174.4	180.3	185.6	189.8	192.9	194.6	194.6
152.5°	165.5	171.0	176.3	180.7	183.9	186.8	187.8	187.8
155°	161.8	166.3	170.5	173.8	176.3	178.6	179.2	179.4
157.5°	157.9	161.6	164.9	167.5	169.7	171.3	171.8	171.7
160°	155.7	158.8	161.5	163.5	165.4	167.2	167.2	166.8
162.5°	153.0	155.6	158.2	159.9	161.2	162.6	162.6	162.4
165°	149.5	151.1	153.1	154.6	155.7	156.8	156.5	156.5
167.5°	146.5	147.7	148.9	149.9	150.4	151.1	150.9	150.9
170°	144.4	145.3	146.4	146.9	147.3	147.8	147.5	147.5
172.5°	142.7	143.3	144.2	144.5	144.6	145.1	144.7	144.4
175°	140.2	140.5	141.1	141.1	141.1	141.4	141.1	140.9
177.5°	138.7	138.9	139.2	139.2	138.9	139.2	138.7	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3

(END OF REPORT)