

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832020

Luminaire Tested: S123RDIP-S1165D805U927-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832020
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U927-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6479.2 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	101	97	94	90	95	91	88	85	80	78	75	69	68	66	60	59	58	58	58	58	53	
2	93	86	80	75	87	81	76	72	71	67	64	62	59	57	54	52	50	50	50	50	46	
3	86	77	70	64	80	72	66	61	64	59	55	56	52	50	49	46	44	44	44	44	40	
4	79	69	61	56	74	65	58	53	58	52	48	51	47	44	44	41	39	39	39	39	36	
5	73	62	54	49	68	59	52	47	52	47	43	46	42	39	41	37	35	35	35	35	32	
6	68	56	48	43	63	53	46	41	48	42	38	42	38	35	37	34	31	31	31	31	29	
7	63	51	44	38	59	49	42	37	44	38	34	39	35	31	35	31	28	28	28	28	26	
8	59	47	40	35	55	45	38	33	40	35	31	36	32	28	32	29	26	26	26	26	24	
9	55	43	36	31	52	41	35	30	37	32	28	34	29	26	30	27	24	24	24	24	22	
10	52	40	33	29	49	38	32	28	35	29	26	31	27	24	28	25	22	22	22	22	20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	31957	31957	31957	31957	31957
5°	37945	36735	32158	25996	24135
10°	34379	37313	31997	20828	17868
15°	23670	31992	31660	17024	14135
20°	16467	24631	31024	14355	12424
25°	12549	18772	30100	12758	11450
30°	10924	15008	28942	11846	10606
35°	10029	12661	27304	11077	9837
40°	9150	11306	25160	10322	9133
45°	8264	10339	22847	9608	8432
50°	7502	9540	20118	8907	7562
55°	6784	8760	17498	8223	6488
60°	6079	7965	15199	7468	6131
65°	5611	7068	13084	6711	5797
70°	4560	6112	11415	6071	4711
75°	4001	4862	9669	5036	4151
80°	3620	4110	7922	4228	3924
85°	3310	3606	6015	3829	3606

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 24108 cd/sqm



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.6	4.2
10°-20°	626.2	9.7
20°-30°	718.5	11.1
30°-40°	708.2	10.9
40°-50°	624.5	9.6
50°-60°	480.5	7.4
60°-70°	315.9	4.9
70°-80°	153.4	2.4
80°-90°	40.3	0.6
90°-100°	29.4	0.5
100°-110°	142.1	2.2
110°-120°	348.3	5.4
120°-130°	442.1	6.8
130°-140°	472.3	7.3
140°-150°	441.7	6.8
150°-160°	356.2	5.5
160°-170°	229.9	3.5
170°-180°	79.2	1.2
0°-30°	1615.3	24.9
0°-40°	2323.4	35.9
0°-60°	3428.4	52.9
0°-90°	3938.0	60.8
90°-120°	519.7	8.0
90°-150°	1875.8	29.0
90°-180°	2541.0	39.2
0°-180°	6479.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2969	2969	2969	2969	2969	
5°	3512	3400	2976	2406	2234	321
15°	2124	2871	2841	1528	1268	600
25°	1057	1581	2534	1074	964	499
35°	763	964	2078	843	749	476
45°	543	679	1501	631	554	421
55°	362	467	932	438	346	324
65°	220	278	514	264	228	216
75°	96	117	232	121	100	104
85°	27	29	49	31	29	28
90°	19	15	1	15	19	10
95°	24	19	38	19	24	20
105°	27	136	185	136	27	57
115°	364	356	346	356	364	343
125°	498	496	488	496	498	445
135°	614	614	608	614	614	473
145°	708	707	701	707	708	442
155°	771	772	772	772	771	356
165°	813	812	814	812	813	230
175°	830	831	834	831	830	79
180°	834	834	834	834	834	



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9
2.5°	3290.3	3279.9	3269.6	3266.5	3263.5	3253.8	3244.0	3222.1	3200.2	3177.7	3155.2
5°	3511.8	3513.0	3514.3	3511.2	3508.2	3495.4	3482.6	3455.8	3429.0	3399.8	3370.6
7.5°	3443.7	3463.1	3482.6	3486.3	3489.9	3499.6	3509.4	3503.3	3497.2	3486.3	3475.3
10°	3145.4	3144.2	3143.0	3164.9	3186.8	3251.9	3317.1	3350.5	3384.0	3413.8	3443.7
12.5°	2658.5	2660.3	2662.2	2734.0	2805.8	2867.3	2928.7	3014.0	3099.2	3191.1	3283.0
15°	2124.1	2154.0	2183.8	2247.7	2311.6	2404.1	2496.6	2611.0	2725.5	2870.9	3016.4
17.5°	1744.3	1757.1	1769.9	1831.4	1892.9	1980.5	2068.1	2197.8	2327.4	2514.9	2702.3
20°	1437.6	1449.2	1460.7	1505.2	1549.6	1633.6	1717.6	1841.1	1964.7	2150.3	2335.9
22.5°	1200.2	1222.7	1245.3	1275.1	1304.9	1365.8	1426.6	1552.6	1678.6	1847.8	2017.0
25°	1056.6	1066.9	1077.3	1102.8	1128.4	1186.8	1245.3	1328.6	1412.0	1580.6	1749.2
27.5°	959.2	962.3	965.3	984.2	1003.0	1040.8	1078.5	1155.8	1233.1	1371.9	1510.6
30°	878.9	884.3	889.8	904.4	919.0	946.4	973.8	1028.6	1083.4	1207.5	1331.7
32.5°	816.8	819.8	822.9	835.0	847.2	867.3	887.4	930.6	973.8	1068.8	1163.7
35°	763.2	763.8	764.4	773.6	782.7	802.2	821.7	857.6	893.5	963.5	1033.5
37.5°	702.4	706.6	710.9	717.6	724.3	741.3	758.4	787.6	816.8	874.6	932.4
40°	651.2	654.9	658.5	666.5	674.4	687.8	701.1	727.9	754.7	804.6	854.5
42.5°	600.1	602.5	605.0	612.9	620.8	637.2	653.7	675.0	696.3	737.7	779.1
45°	542.9	549.0	555.1	563.6	572.1	586.1	600.1	622.0	643.9	679.2	714.5
47.5°	495.4	498.5	501.5	508.8	516.1	533.2	550.2	569.7	589.2	622.0	654.9
50°	448.0	449.2	450.4	457.1	463.8	479.0	494.2	516.7	539.3	569.7	600.1
52.5°	402.9	406.0	409.0	415.7	422.4	432.7	443.1	466.2	489.3	519.2	549.0
55°	361.5	363.4	365.2	370.0	374.9	387.1	399.3	419.3	439.4	466.8	494.2
57.5°	322.6	325.0	327.4	331.1	334.7	345.7	356.7	374.3	392.0	419.3	446.7
60°	282.4	285.4	288.5	292.8	297.0	305.5	314.1	329.9	345.7	370.0	394.4
62.5°	253.2	253.8	254.4	258.1	261.7	267.8	273.9	286.7	299.4	323.8	348.1
65°	220.3	222.2	224.0	225.8	227.6	232.5	237.4	248.3	259.3	277.5	295.8
67.5°	186.2	188.1	189.9	192.9	196.0	200.2	204.5	211.8	219.1	236.2	253.2
70°	144.9	144.9	144.9	149.7	154.6	161.9	169.2	174.7	180.2	194.2	208.2
72.5°	118.1	118.7	119.3	119.9	120.5	124.8	129.0	138.2	147.3	155.8	164.3
75°	96.2	96.8	97.4	98.0	98.6	99.8	101.0	104.1	107.1	116.9	126.6
77.5°	76.7	77.3	77.9	78.5	79.1	80.3	81.6	82.8	84.0	87.6	91.3
80°	58.4	59.0	59.6	60.3	60.9	61.5	62.1	63.3	64.5	66.3	68.2
82.5°	42.6	42.6	42.6	42.6	42.6	43.8	45.0	45.0	45.0	46.3	47.5
85°	26.8	26.8	26.8	27.4	28.0	28.0	28.0	28.6	29.2	29.2	29.2
87.5°	12.2	11.6	11.0	11.6	12.2	12.2	12.2	12.8	13.4	13.4	13.4
90°	18.6	18.3	18.0	17.8	17.5	17.1	16.5	16.0	15.4	14.9	13.1
92.5°	21.1	20.9	20.8	20.6	20.5	20.0	19.0	18.0	17.1	16.1	14.9
95°	23.5	23.5	23.5	23.5	23.5	23.1	22.1	21.1	20.2	19.2	17.7
97.5°	25.4	25.3	25.1	25.0	24.8	24.2	23.1	22.0	20.9	19.8	26.8
100°	26.0	25.9	25.7	25.6	25.5	24.8	23.7	22.6	21.5	20.4	41.9
102.5°	26.6	26.4	26.1	25.8	25.5	27.7	32.2	36.7	41.3	45.8	69.8
105°	27.3	27.0	26.7	26.4	26.1	38.2	62.6	86.9	111.3	135.6	148.0
107.5°	64.4	82.4	100.5	118.5	136.5	156.1	177.3	198.5	219.7	240.9	238.9
110°	170.3	190.0	209.7	229.4	249.0	261.1	265.7	270.2	274.8	279.3	277.8



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	322.7	322.9	323.2	323.5	323.8	323.3	322.0	320.8	319.6	318.3	316.8
115°	364.2	363.6	363.1	362.5	362.0	361.0	359.6	358.2	356.9	355.5	354.3
117.5°	397.6	397.5	397.3	397.2	397.1	396.4	395.3	394.2	393.1	392.0	391.3
120°	432.3	432.3	432.3	432.3	432.3	431.7	430.6	429.5	428.4	427.3	426.9
122.5°	466.4	466.2	466.1	465.9	465.8	465.4	464.7	464.0	463.3	462.6	462.1
125°	497.9	497.7	497.4	497.1	496.8	496.6	496.3	496.0	495.7	495.5	494.9
127.5°	528.9	529.2	529.5	529.7	530.0	529.9	529.5	529.1	528.7	528.3	527.6
130°	558.6	558.9	559.2	559.5	559.7	559.6	559.0	558.5	557.9	557.4	556.8
132.5°	585.9	586.3	586.7	587.1	587.5	587.5	586.9	586.4	585.8	585.3	584.8
135°	613.7	614.2	614.6	615.0	615.4	615.4	615.0	614.6	614.2	613.7	613.2
137.5°	640.4	640.7	640.9	641.2	641.5	641.3	640.6	639.9	639.2	638.5	638.2
140°	663.9	664.2	664.5	664.7	665.0	664.9	664.3	663.8	663.2	662.7	662.3
142.5°	685.6	686.0	686.4	686.8	687.2	687.2	686.8	686.4	686.0	685.6	685.2
145°	707.9	707.9	707.9	707.9	707.9	707.7	707.5	707.2	706.9	706.6	706.4
147.5°	724.0	724.7	725.4	726.1	726.7	726.9	726.7	726.4	726.1	725.8	725.6
150°	742.6	743.0	743.4	743.8	744.2	744.3	744.0	743.7	743.5	743.2	742.9
152.5°	757.4	758.1	758.8	759.5	760.2	760.3	759.7	759.2	758.6	758.1	757.9
155°	771.1	771.9	772.7	773.5	774.4	774.4	773.7	773.1	772.4	771.7	771.5
157.5°	782.8	783.9	785.0	786.1	787.2	787.4	786.5	785.7	784.9	784.1	784.2
160°	794.0	794.9	795.9	796.9	797.8	797.9	797.1	796.2	795.4	794.6	794.7
162.5°	804.5	805.3	806.2	807.0	807.8	807.7	806.8	805.8	804.8	803.9	804.0
165°	812.6	813.5	814.5	815.4	816.4	816.3	815.2	814.1	813.0	811.9	812.1
167.5°	818.7	819.8	820.9	822.0	823.1	823.1	822.0	820.9	819.8	818.7	818.7
170°	824.3	825.4	826.5	827.6	828.7	828.7	827.6	826.5	825.4	824.3	824.3
172.5°	827.4	828.7	829.9	831.1	832.4	832.4	831.3	830.2	829.1	828.0	827.9
175°	830.5	831.6	832.7	833.8	834.9	835.0	834.0	833.1	832.1	831.1	831.0
177.5°	831.1	832.5	833.9	835.3	836.6	836.8	835.7	834.6	833.5	832.4	832.2
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9
2.5°	3152.1	3149.1	3119.9	3090.6	3062.0	3033.4	3012.1	2990.8	2954.9	2919.0	2896.5
5°	3347.5	3324.4	3278.1	3231.8	3162.5	3093.1	3034.7	2976.2	2902.0	2827.7	2765.6
7.5°	3456.4	3437.6	3381.6	3325.6	3233.7	3141.8	3050.5	2959.2	2849.6	2740.1	2646.3
10°	3459.5	3475.3	3429.0	3382.8	3279.3	3175.9	3051.7	2927.5	2780.2	2633.0	2511.8
12.5°	3351.1	3419.3	3409.6	3399.8	3294.5	3189.2	3038.3	2887.4	2706.6	2525.8	2374.3
15°	3148.5	3280.5	3319.5	3358.4	3271.4	3184.4	3012.7	2841.1	2628.7	2416.3	2242.2
17.5°	2887.4	3072.4	3175.2	3278.1	3214.8	3151.5	2963.4	2775.4	2536.2	2297.0	2107.7
20°	2578.2	2820.4	2981.7	3143.0	3119.9	3096.7	2902.6	2708.4	2450.4	2192.3	1987.2
22.5°	2272.6	2528.3	2751.0	2973.8	2997.5	3021.3	2825.3	2629.3	2346.9	2064.5	1855.7
25°	2009.1	2269.0	2534.4	2799.7	2853.3	2906.8	2720.6	2534.4	2241.6	1948.8	1741.3
27.5°	1757.7	2004.8	2297.0	2589.1	2686.5	2783.9	2613.5	2443.1	2138.1	1833.2	1626.3
30°	1552.6	1773.6	2071.8	2370.0	2505.7	2641.5	2485.1	2328.6	2026.1	1723.7	1521.0
32.5°	1361.5	1559.3	1858.8	2158.2	2315.9	2473.5	2338.4	2203.3	1912.3	1621.4	1421.2
35°	1210.6	1387.7	1667.1	1946.4	2122.9	2299.4	2188.6	2077.9	1793.6	1509.4	1320.1
37.5°	1080.9	1229.4	1491.8	1754.1	1941.5	2129.0	2036.5	1944.0	1676.8	1409.6	1230.7
40°	973.8	1093.1	1337.2	1581.2	1765.0	1948.8	1869.7	1790.6	1551.4	1312.2	1144.8
42.5°	881.9	984.8	1203.9	1423.0	1591.6	1760.2	1707.8	1655.5	1438.8	1222.1	1066.9
45°	801.0	887.4	1080.3	1273.3	1428.5	1583.7	1542.3	1500.9	1314.0	1127.2	984.8
47.5°	729.1	803.4	975.6	1147.9	1287.3	1426.6	1388.3	1350.0	1195.4	1040.8	911.1
50°	663.4	726.7	870.3	1014.0	1139.4	1264.7	1233.1	1201.4	1073.6	945.8	833.8
52.5°	601.3	653.7	782.7	911.7	1012.8	1113.8	1089.5	1065.1	966.5	867.9	766.3
55°	542.3	590.4	699.3	808.3	894.7	981.1	956.8	932.4	855.7	779.1	689.6
57.5°	488.7	530.7	619.0	707.2	776.0	844.8	833.2	821.7	757.8	693.8	620.2
60°	432.1	469.9	545.9	622.0	677.4	732.8	719.4	706.0	660.4	614.7	551.4
62.5°	381.6	415.1	476.0	536.8	581.9	626.9	617.2	607.4	572.7	538.0	485.7
65°	328.7	361.5	410.8	460.1	495.4	530.7	522.2	513.7	487.5	461.3	419.3
67.5°	280.6	308.0	350.6	393.2	416.9	440.7	435.8	430.9	410.8	390.7	357.9
70°	231.9	255.6	290.9	326.2	342.7	359.1	360.9	362.7	344.5	326.2	301.9
72.5°	183.2	202.1	234.9	267.8	280.6	293.4	292.8	292.1	281.2	270.2	248.3
75°	140.6	154.6	180.2	205.7	216.7	227.6	230.1	232.5	222.2	211.8	199.6
77.5°	101.0	110.8	130.2	149.7	161.9	174.1	175.3	176.5	171.6	166.8	155.2
80°	71.2	74.3	86.4	98.6	111.4	124.2	126.0	127.8	122.9	118.1	110.8
82.5°	49.3	51.1	55.4	59.6	70.0	80.3	82.8	85.2	82.8	80.3	72.4
85°	29.8	30.4	32.3	34.1	39.0	43.8	46.3	48.7	47.5	46.3	42.0
87.5°	13.4	13.4	14.0	14.6	15.8	17.0	20.1	23.1	21.3	19.5	17.7
90°	11.3	9.5	7.7	6.1	4.7	3.4	2.0	0.6	2.0	3.4	4.7
92.5°	13.6	12.4	11.1	10.9	11.8	12.6	13.4	14.2	13.4	12.6	11.8
95°	16.2	14.7	13.1	15.2	20.9	26.5	32.1	37.8	32.1	26.5	20.9
97.5°	33.9	40.9	47.9	53.3	57.2	61.0	64.9	68.7	64.9	61.0	57.2
100°	63.4	84.8	106.3	115.7	112.9	110.2	107.4	104.7	107.4	110.2	112.9
102.5°	93.7	117.7	141.6	152.7	150.9	149.1	147.3	145.5	147.3	149.1	150.9
105°	160.4	172.8	185.2	190.6	189.1	187.6	186.1	184.6	186.1	187.6	189.1
107.5°	236.8	234.7	232.7	231.0	229.8	228.5	227.3	226.1	227.3	228.5	229.8
110°	276.3	274.8	273.3	272.0	270.9	269.7	268.6	267.5	268.6	269.7	270.9



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	315.3	313.8	312.3	311.0	310.1	309.1	308.1	307.2	308.1	309.1	310.1
115°	353.0	351.8	350.5	349.5	348.7	347.9	347.0	346.2	347.0	347.9	348.7
117.5°	390.7	390.0	389.3	388.5	387.5	386.5	385.6	384.6	385.6	386.5	387.5
120°	426.5	426.1	425.7	424.9	423.6	422.4	421.1	419.9	421.1	422.4	423.6
122.5°	461.5	461.0	460.4	459.7	458.7	457.7	456.8	455.8	456.8	457.7	458.7
125°	494.4	493.8	493.3	492.4	491.3	490.2	489.1	488.0	489.1	490.2	491.3
127.5°	526.9	526.2	525.5	524.6	523.5	522.4	521.3	520.2	521.3	522.4	523.5
130°	556.3	555.7	555.2	554.4	553.3	552.2	551.1	550.0	551.1	552.2	553.3
132.5°	584.4	584.0	583.6	582.9	581.8	580.6	579.5	578.4	579.5	580.6	581.8
135°	612.6	612.1	611.5	610.9	610.0	609.2	608.4	607.6	608.4	609.2	610.0
137.5°	638.0	637.7	637.4	636.7	635.6	634.5	633.4	632.3	633.4	634.5	635.6
140°	661.8	661.4	661.0	660.4	659.6	658.8	657.9	657.1	657.9	658.8	659.6
142.5°	684.8	684.4	683.9	683.3	682.5	681.7	680.8	680.0	680.8	681.7	682.5
145°	706.1	705.8	705.5	704.9	704.0	703.0	702.0	701.1	702.0	703.0	704.0
147.5°	725.3	725.0	724.7	724.3	723.6	722.9	722.2	721.5	722.2	722.9	723.6
150°	742.6	742.4	742.1	741.7	741.3	740.9	740.5	740.1	740.5	740.9	741.3
152.5°	757.8	757.6	757.5	757.4	757.2	757.1	757.0	756.8	757.0	757.1	757.2
155°	771.4	771.3	771.1	771.2	771.5	771.7	772.0	772.3	772.0	771.7	771.5
157.5°	784.3	784.5	784.6	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7
160°	794.9	795.0	795.1	795.3	795.4	795.6	795.7	795.8	795.7	795.6	795.4
162.5°	804.2	804.3	804.4	804.7	805.1	805.5	805.9	806.4	805.9	805.5	805.1
165°	812.2	812.3	812.5	812.8	813.2	813.6	814.0	814.4	814.0	813.6	813.2
167.5°	818.7	818.7	818.7	819.0	819.6	820.1	820.7	821.2	820.7	820.1	819.6
170°	824.3	824.3	824.3	824.6	825.1	825.7	826.2	826.8	826.2	825.7	825.1
172.5°	827.8	827.6	827.5	827.8	828.4	829.1	829.8	830.5	829.8	829.1	828.4
175°	830.9	830.7	830.6	830.9	831.5	832.2	832.9	833.6	832.9	832.2	831.5
177.5°	832.1	832.0	831.8	832.1	832.8	833.5	834.2	834.8	834.2	833.5	832.8
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9	2968.9
2.5°	2874.0	2839.3	2804.6	2779.6	2754.7	2723.6	2692.6	2691.4	2690.2	2667.0	2643.9
5°	2703.6	2643.3	2583.0	2524.0	2465.0	2405.9	2346.9	2333.5	2320.1	2300.0	2279.9
7.5°	2552.6	2456.4	2360.3	2284.8	2209.3	2150.3	2091.3	2051.1	2010.9	1979.9	1948.8
10°	2390.7	2271.4	2152.1	2060.8	1969.5	1905.6	1841.7	1795.5	1749.2	1727.3	1705.4
12.5°	2222.7	2093.1	1963.5	1874.0	1784.5	1707.8	1631.1	1589.1	1547.1	1516.7	1486.3
15°	2068.1	1928.8	1789.4	1694.4	1599.5	1527.7	1455.9	1413.9	1371.9	1341.4	1311.0
17.5°	1918.4	1777.8	1637.2	1541.1	1444.9	1379.8	1314.7	1273.9	1233.1	1214.2	1195.4
20°	1782.1	1640.3	1498.5	1407.8	1317.1	1253.2	1189.3	1167.4	1145.5	1127.8	1110.1
22.5°	1647.0	1510.6	1374.3	1287.3	1200.2	1154.0	1107.7	1090.1	1072.4	1059.0	1045.6
25°	1533.8	1398.0	1262.3	1186.2	1110.1	1074.2	1038.3	1026.8	1015.2	1001.8	988.4
27.5°	1419.3	1290.3	1161.3	1100.4	1039.5	1010.3	981.1	966.5	951.9	940.9	930.0
30°	1318.3	1199.0	1079.7	1029.2	978.7	953.1	927.6	911.7	895.9	885.6	875.2
32.5°	1220.9	1115.0	1009.1	965.9	922.7	897.7	872.8	857.6	842.4	830.2	818.0
35°	1130.8	1038.9	947.0	907.5	867.9	843.0	818.0	802.8	787.6	775.4	763.2
37.5°	1051.7	968.3	885.0	847.8	810.7	788.8	766.9	751.1	735.2	722.4	709.7
40°	977.5	903.8	830.2	794.3	758.4	734.6	710.9	696.9	682.9	671.3	659.8
42.5°	911.7	844.2	776.6	741.3	706.0	683.5	661.0	644.5	628.1	621.4	614.7
45°	842.4	782.7	723.1	689.0	654.9	631.2	607.4	593.4	579.4	573.3	567.2
47.5°	781.5	726.1	670.7	637.2	603.8	582.5	561.2	550.2	539.3	530.7	522.2
50°	721.8	668.3	614.7	582.5	550.2	531.9	513.7	500.3	486.9	480.8	474.7
52.5°	664.6	615.9	567.2	534.4	501.5	483.9	466.2	454.7	443.1	430.3	417.5
55°	600.1	557.5	514.9	485.7	456.5	438.2	420.0	406.6	393.2	379.8	366.4
57.5°	546.6	504.6	462.6	436.4	410.2	392.6	374.9	360.3	345.7	334.7	323.8
60°	488.1	451.6	415.1	389.5	364.0	346.9	329.9	315.9	301.9	296.4	290.9
62.5°	433.3	399.3	365.2	342.7	320.1	303.7	287.3	278.1	269.0	265.4	261.7
65°	377.4	348.1	318.9	298.2	277.5	263.5	249.5	245.3	241.0	238.0	234.9
67.5°	325.0	300.1	275.1	256.8	238.6	228.8	219.1	214.2	209.4	205.7	202.1
70°	277.5	255.6	233.7	217.9	202.1	192.9	183.8	179.5	175.3	168.6	161.9
72.5°	226.4	209.4	192.3	180.2	168.0	160.1	152.2	143.6	135.1	129.0	122.9
75°	187.5	170.4	153.4	141.8	130.2	121.1	112.0	108.9	105.9	104.1	102.3
77.5°	143.6	129.0	114.4	105.3	96.2	91.9	87.6	85.8	84.0	83.4	82.8
80°	103.5	91.3	79.1	74.3	69.4	68.2	66.9	65.7	64.5	63.9	63.3
82.5°	64.5	58.4	52.3	51.1	49.9	49.3	48.7	48.1	47.5	46.9	46.3
85°	37.7	35.3	32.9	32.3	31.6	31.0	30.4	30.4	30.4	30.4	30.4
87.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.2	14.6
90°	6.1	7.7	9.5	11.3	13.1	14.9	15.4	16.0	16.5	17.1	17.5
92.5°	10.9	11.1	12.4	13.6	14.9	16.1	17.1	18.0	19.0	20.0	20.5
95°	15.2	13.1	14.7	16.2	17.7	19.2	20.2	21.1	22.1	23.1	23.5
97.5°	53.3	47.9	40.9	33.9	26.8	19.8	20.9	22.0	23.1	24.2	24.8
100°	115.7	106.3	84.8	63.4	41.9	20.4	21.5	22.6	23.7	24.8	25.5
102.5°	152.7	141.6	117.7	93.7	69.8	45.8	41.3	36.7	32.2	27.7	25.5
105°	190.6	185.2	172.8	160.4	148.0	135.6	111.3	86.9	62.6	38.2	26.1
107.5°	231.0	232.7	234.7	236.8	238.9	240.9	219.7	198.5	177.3	156.1	136.5
110°	272.0	273.3	274.8	276.3	277.8	279.3	274.8	270.2	265.7	261.1	249.0



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	311.0	312.3	313.8	315.3	316.8	318.3	319.6	320.8	322.0	323.3	323.8
115°	349.5	350.5	351.8	353.0	354.3	355.5	356.9	358.2	359.6	361.0	362.0
117.5°	388.5	389.3	390.0	390.7	391.3	392.0	393.1	394.2	395.3	396.4	397.1
120°	424.9	425.7	426.1	426.5	426.9	427.3	428.4	429.5	430.6	431.7	432.3
122.5°	459.7	460.4	461.0	461.5	462.1	462.6	463.3	464.0	464.7	465.4	465.8
125°	492.4	493.3	493.8	494.4	494.9	495.5	495.7	496.0	496.3	496.6	496.8
127.5°	524.6	525.5	526.2	526.9	527.6	528.3	528.7	529.1	529.5	529.9	530.0
130°	554.4	555.2	555.7	556.3	556.8	557.4	557.9	558.5	559.0	559.6	559.7
132.5°	582.9	583.6	584.0	584.4	584.8	585.3	585.8	586.4	586.9	587.5	587.5
135°	610.9	611.5	612.1	612.6	613.2	613.7	614.2	614.6	615.0	615.4	615.4
137.5°	636.7	637.4	637.7	638.0	638.2	638.5	639.2	639.9	640.6	641.3	641.5
140°	660.4	661.0	661.4	661.8	662.3	662.7	663.2	663.8	664.3	664.9	665.0
142.5°	683.3	683.9	684.4	684.8	685.2	685.6	686.0	686.4	686.8	687.2	687.2
145°	704.9	705.5	705.8	706.1	706.4	706.6	706.9	707.2	707.5	707.7	707.9
147.5°	724.3	724.7	725.0	725.3	725.6	725.8	726.1	726.4	726.7	726.9	726.7
150°	741.7	742.1	742.4	742.6	742.9	743.2	743.5	743.7	744.0	744.3	744.2
152.5°	757.4	757.5	757.6	757.8	757.9	758.1	758.6	759.2	759.7	760.3	760.2
155°	771.2	771.1	771.3	771.4	771.5	771.7	772.4	773.1	773.7	774.4	774.4
157.5°	784.7	784.6	784.5	784.3	784.2	784.1	784.9	785.7	786.5	787.4	787.2
160°	795.3	795.1	795.0	794.9	794.7	794.6	795.4	796.2	797.1	797.9	797.8
162.5°	804.7	804.4	804.3	804.2	804.0	803.9	804.8	805.8	806.8	807.7	807.8
165°	812.8	812.5	812.3	812.2	812.1	811.9	813.0	814.1	815.2	816.3	816.4
167.5°	819.0	818.7	818.7	818.7	818.7	818.7	819.8	820.9	822.0	823.1	823.1
170°	824.6	824.3	824.3	824.3	824.3	824.3	825.4	826.5	827.6	828.7	828.7
172.5°	827.8	827.5	827.6	827.8	827.9	828.0	829.1	830.2	831.3	832.4	832.4
175°	830.9	830.6	830.7	830.9	831.0	831.1	832.1	833.1	834.0	835.0	834.9
177.5°	832.1	831.8	832.0	832.1	832.2	832.4	833.5	834.6	835.7	836.8	836.6
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2968.9	2968.9	2968.9	2968.9
2.5°	2637.8	2631.7	2629.3	2626.9
5°	2261.1	2242.2	2237.9	2233.7
7.5°	1940.9	1933.0	1906.9	1880.7
10°	1681.0	1656.7	1645.7	1634.8
12.5°	1463.8	1441.2	1437.6	1433.9
15°	1295.2	1279.3	1273.9	1268.4
17.5°	1184.4	1173.4	1166.8	1160.1
20°	1102.2	1094.3	1089.5	1084.6
22.5°	1039.5	1033.5	1029.8	1026.2
25°	979.3	970.2	967.1	964.1
27.5°	922.1	914.2	911.1	908.1
30°	868.5	861.8	857.6	853.3
32.5°	810.1	802.2	799.7	797.3
35°	758.4	753.5	751.1	748.6
37.5°	703.6	697.5	693.8	690.2
40°	656.7	653.7	651.8	650.0
42.5°	609.2	603.8	603.2	602.5
45°	561.8	556.3	555.1	553.9
47.5°	517.3	512.5	511.9	511.3
50°	468.0	461.3	456.5	451.6
52.5°	411.4	405.4	401.1	396.8
55°	359.7	353.0	349.4	345.7
57.5°	320.8	317.7	315.9	314.1
60°	289.1	287.3	286.1	284.8
62.5°	259.9	258.1	258.1	258.1
65°	233.1	231.3	229.5	227.6
67.5°	198.4	194.8	194.2	193.5
70°	156.4	150.9	150.3	149.7
72.5°	122.3	121.7	120.5	119.3
75°	101.0	99.8	99.8	99.8
77.5°	81.6	80.3	80.3	80.3
80°	62.7	62.1	62.7	63.3
82.5°	46.3	46.3	45.6	45.0
85°	29.8	29.2	29.2	29.2
87.5°	14.6	14.6	14.6	14.6
90°	17.8	18.0	18.3	18.6
92.5°	20.6	20.8	20.9	21.1
95°	23.5	23.5	23.5	23.5
97.5°	25.0	25.1	25.3	25.4
100°	25.6	25.7	25.9	26.0
102.5°	25.8	26.1	26.4	26.6
105°	26.4	26.7	27.0	27.3
107.5°	118.5	100.5	82.4	64.4
110°	229.4	209.7	190.0	170.3



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	323.5	323.2	322.9	322.7
115°	362.5	363.1	363.6	364.2
117.5°	397.2	397.3	397.5	397.6
120°	432.3	432.3	432.3	432.3
122.5°	465.9	466.1	466.2	466.4
125°	497.1	497.4	497.7	497.9
127.5°	529.7	529.5	529.2	528.9
130°	559.5	559.2	558.9	558.6
132.5°	587.1	586.7	586.3	585.9
135°	615.0	614.6	614.2	613.7
137.5°	641.2	640.9	640.7	640.4
140°	664.7	664.5	664.2	663.9
142.5°	686.8	686.4	686.0	685.6
145°	707.9	707.9	707.9	707.9
147.5°	726.1	725.4	724.7	724.0
150°	743.8	743.4	743.0	742.6
152.5°	759.5	758.8	758.1	757.4
155°	773.5	772.7	771.9	771.1
157.5°	786.1	785.0	783.9	782.8
160°	796.9	795.9	794.9	794.0
162.5°	807.0	806.2	805.3	804.5
165°	815.4	814.5	813.5	812.6
167.5°	822.0	820.9	819.8	818.7
170°	827.6	826.5	825.4	824.3
172.5°	831.1	829.9	828.7	827.4
175°	833.8	832.7	831.6	830.5
177.5°	835.3	833.9	832.5	831.1
180°	833.6	833.6	833.6	833.6



TEST NUMBER: P832020

CATALOG NUMBER: S123RDIP-S1165D805U927-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.74	14.64	14.61	15.52	16.64	18.41	19.30	19.28	20.19	21.30
	3H	14.97	15.77	15.85	16.66	17.80	19.91	20.71	20.79	21.60	22.74
	4H	15.35	16.11	16.25	17.01	18.16	20.40	21.16	21.30	22.06	23.21
	6H	15.64	16.33	16.55	17.24	18.40	20.72	21.41	21.63	22.32	23.48
	8H	15.73	16.39	16.65	17.31	18.47	20.80	21.46	21.72	22.38	23.54
	12H	15.78	16.41	16.70	17.33	18.51	20.83	21.46	21.76	22.38	23.56
4H	2H	14.47	15.23	15.38	16.13	17.28	18.41	19.16	19.31	20.06	21.21
	3H	15.85	16.47	16.76	17.41	18.57	20.07	20.70	20.99	21.63	22.79
	4H	16.31	16.88	17.23	17.80	18.99	20.68	21.25	21.61	22.18	23.37
	6H	16.68	17.17	17.62	18.12	19.31	21.12	21.61	22.06	22.56	23.76
	8H	16.80	17.26	17.74	18.21	19.41	21.26	21.71	22.20	22.66	23.86
	12H	16.88	17.29	17.84	18.26	19.46	21.32	21.73	22.28	22.69	23.90
8H	4H	16.62	17.08	17.57	18.03	19.23	20.65	21.11	21.59	22.06	23.26
	6H	17.09	17.47	18.06	18.45	19.66	21.15	21.53	22.12	22.52	23.72
	8H	17.28	17.62	18.26	18.59	19.81	21.34	21.67	22.31	22.65	23.87
	12H	17.43	17.72	18.40	18.69	19.96	21.46	21.75	22.43	22.72	23.99
12H	4H	16.64	17.05	17.60	18.01	19.22	20.61	21.02	21.57	21.98	23.19
	6H	17.15	17.48	18.13	18.46	19.68	21.13	21.46	22.10	22.44	23.66
	8H	17.37	17.66	18.35	18.63	19.90	21.32	21.62	22.30	22.58	23.85