

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331299-935

Luminaire Tested: **S122DIP-S485D530U935-4F0-1E-UDD-D4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331299-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D530U935-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3471.7 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331299-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331299-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	95	90	86	82	87	82	79	75	68	65	63	54	53	51	42	41	40	34
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	23
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	18	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7164	7164	7164
5°	7199	6896	6870
10°	7153	6692	6617
15°	7055	6477	6350
20°	6930	6245	6094
25°	6807	6022	5862
30°	6634	5793	5628
35°	6458	5572	5464
40°	6275	5384	5299
45°	6100	5215	5159
50°	5912	5062	5019
55°	5713	4898	4878
60°	5473	4730	4729
65°	5222	4530	4552
70°	4938	4315	4361
75°	4578	4106	4186
80°	4008	3889	4005
85°	3471	3705	3868



TEST NUMBER: P331299-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.0	1.2
10°-20°	120.6	3.5
20°-30°	182.7	5.3
30°-40°	222.5	6.4
40°-50°	239.4	6.9
50°-60°	232.5	6.7
60°-70°	203.0	5.8
70°-80°	156.3	4.5
80°-90°	107.2	3.1
90°-100°	174.3	5.0
100°-110°	399.2	11.5
110°-120°	402.9	11.6
120°-130°	322.4	9.3
130°-140°	251.5	7.2
140°-150°	185.3	5.3
150°-160°	129.2	3.7
160°-170°	76.1	2.2
170°-180°	24.8	0.7
0°-30°	345.3	9.9
0°-40°	567.8	16.4
0°-60°	1039.7	29.9
0°-90°	1506.1	43.4
90°-120°	976.4	28.1
90°-150°	1735.6	50.0
90°-180°	1966.0	56.6
0°-180°	3471.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	444	444	444	444	444	
5°	445	443	439	443	442	42
15°	424	426	426	431	431	119
25°	386	390	396	404	406	177
35°	332	343	356	369	374	208
45°	273	290	312	332	339	210
55°	209	233	266	288	297	187
65°	143	175	212	238	247	142
75°	79	115	156	183	192	84
85°	23	63	104	130	140	25
90°	7	51	102	126	134	5
95°	22	78	266	170	162	22
105°	63	113	419	727	638	67
115°	108	144	343	685	793	107
125°	149	177	314	548	636	132
135°	174	207	296	448	515	134
145°	197	227	288	361	398	124
155°	224	242	279	316	328	103
165°	244	252	268	284	288	69
175°	255	255	257	260	260	24
180°	255	255	255	255	255	



TEST NUMBER: P331299-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.3	445.9	445.6	445.2	444.9	444.3	443.5	442.7	442.0	441.1	441.7
5°	445.0	444.5	444.1	443.7	443.2	442.6	441.8	440.9	440.1	439.2	440.1
7.5°	441.0	440.7	440.4	440.1	439.9	439.4	438.7	438.1	437.4	436.7	437.7
10°	437.9	437.6	437.3	437.0	436.8	436.4	436.0	435.6	435.1	434.7	435.8
12.5°	432.7	432.8	432.9	432.9	433.0	432.8	432.6	432.2	431.9	431.6	432.7
15°	424.4	424.6	425.0	425.2	425.5	425.7	425.7	425.7	425.7	425.7	427.0
17.5°	413.6	414.2	414.8	415.4	416.0	416.6	417.0	417.4	417.9	418.4	419.7
20°	406.4	407.1	407.9	408.5	409.2	409.9	410.4	411.0	411.6	412.2	413.7
22.5°	398.6	399.5	400.4	401.1	402.0	402.8	403.6	404.4	405.2	406.0	407.6
25°	385.8	386.8	387.8	388.8	389.8	391.0	392.3	393.6	394.9	396.1	397.8
27.5°	370.4	372.0	373.7	375.3	376.9	378.5	380.0	381.5	383.0	384.5	386.7
30°	360.1	362.0	363.8	365.7	367.6	369.4	371.3	373.1	375.0	376.8	379.1
32.5°	348.8	350.9	352.9	355.1	357.1	359.3	361.4	363.7	365.8	368.1	370.7
35°	332.4	334.8	337.3	339.8	342.2	344.7	347.4	350.2	352.8	355.6	358.7
37.5°	314.7	317.5	320.3	323.1	325.9	329.1	332.6	336.0	339.6	343.1	346.6
40°	302.9	306.0	309.2	312.3	315.5	318.9	322.8	326.7	330.5	334.4	338.1
42.5°	291.5	294.7	297.8	301.0	304.1	307.9	312.4	316.8	321.2	325.6	329.7
45°	272.7	276.5	280.3	284.2	288.1	292.5	297.5	302.5	307.5	312.5	316.9
47.5°	254.0	258.2	262.4	266.6	270.8	275.9	281.7	287.6	293.4	299.3	303.9
50°	241.2	245.6	250.0	254.4	258.8	264.2	270.7	277.2	283.6	290.0	294.9
52.5°	228.8	233.4	238.1	242.8	247.5	253.1	259.9	266.7	273.5	280.3	285.2
55°	209.0	214.1	219.3	224.4	229.5	235.8	243.3	250.7	258.1	265.5	270.7
57.5°	189.4	195.3	201.0	206.8	212.7	219.3	226.9	234.5	242.0	249.6	255.2
60°	175.6	181.7	187.9	194.0	200.1	207.2	215.4	223.5	231.7	239.9	245.3
62.5°	163.2	169.5	176.0	182.4	188.7	196.0	204.1	212.2	220.4	228.5	234.3
65°	142.8	149.7	156.8	163.8	170.7	178.5	186.9	195.4	203.8	212.2	218.1
67.5°	124.0	131.3	138.6	145.9	153.3	161.2	169.9	178.5	187.1	195.7	201.6
70°	110.6	118.0	125.4	132.9	140.3	148.4	157.3	166.2	175.0	183.9	190.0
72.5°	98.2	105.9	113.6	121.2	128.9	137.2	146.2	155.2	164.1	173.1	179.2
75°	79.1	87.1	95.1	103.1	111.1	119.7	128.8	137.9	147.1	156.3	162.4
77.5°	60.6	69.0	77.3	85.7	94.1	102.9	112.2	121.5	130.8	140.1	146.2
80°	48.2	56.9	65.7	74.4	83.1	92.1	101.4	110.6	119.9	129.2	135.3
82.5°	38.0	46.6	55.1	63.7	72.3	81.4	90.7	100.1	109.5	119.0	124.9
85°	23.2	32.0	40.9	49.8	58.5	67.6	76.7	85.8	95.1	104.2	110.2
87.5°	12.7	21.5	30.4	39.2	47.9	57.0	66.6	76.5	86.2	95.4	101.2
90°	6.9	16.7	26.9	36.2	45.5	55.6	67.2	79.8	92.0	101.6	106.8
92.5°	11.9	22.3	33.5	43.4	54.4	67.3	87.2	111.7	134.4	144.0	139.7
95°	22.3	31.0	42.6	53.8	68.4	87.7	118.9	170.2	235.7	266.4	247.8
97.5°	32.5	41.2	52.3	64.9	80.0	100.4	137.0	204.7	307.6	397.0	418.4
100°	42.3	49.1	58.8	71.9	87.0	107.5	141.5	209.3	323.4	452.2	528.2
102.5°	50.8	56.7	66.0	78.7	93.7	113.7	145.6	206.6	312.5	450.6	566.9
105°	63.1	69.2	76.8	88.3	103.2	122.8	153.3	204.4	292.9	419.1	554.7
107.5°	77.1	82.1	88.7	98.8	112.8	131.8	161.4	206.6	280.7	386.0	506.2
110°	86.0	90.8	96.7	105.9	119.1	138.3	166.9	209.2	276.1	369.5	475.8



TEST NUMBER: P331299-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	94.7	99.0	104.8	113.2	125.5	144.6	172.1	212.2	273.3	357.3	453.3
115°	108.1	112.2	116.7	124.2	135.5	152.8	180.4	216.7	270.8	343.0	424.9
117.5°	121.4	124.4	128.4	134.7	145.1	162.3	187.8	221.9	269.5	333.1	404.8
120°	130.1	132.6	136.1	141.1	151.5	168.4	193.3	225.5	269.1	327.3	393.6
122.5°	138.4	140.2	143.3	148.4	158.4	175.3	198.7	228.6	269.1	322.6	383.7
125°	148.6	150.1	153.0	158.9	168.8	184.8	207.0	233.7	268.7	314.5	368.9
127.5°	157.2	159.0	163.1	169.4	178.7	194.6	215.4	238.9	269.1	308.2	355.2
130°	162.3	164.2	168.9	175.6	185.4	200.5	220.7	242.4	269.9	304.4	346.0
132.5°	167.0	169.3	174.4	181.6	191.7	206.5	225.2	245.7	270.6	300.8	338.1
135°	173.5	175.5	181.3	188.7	200.0	214.5	231.6	250.2	271.3	296.3	327.3
137.5°	180.1	182.4	188.4	196.1	207.3	220.4	236.5	253.2	271.7	292.5	318.6
140°	185.3	187.1	192.9	200.5	211.2	224.0	239.1	254.6	271.6	290.0	313.4
142.5°	190.4	191.8	197.2	204.8	215.2	227.0	241.5	256.3	271.9	289.0	309.2
145°	197.4	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	304.3
147.5°	205.6	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.8
150°	211.1	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6
152.5°	216.6	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9
155°	224.4	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7
157.5°	230.8	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9
160°	235.2	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3
162.5°	239.5	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2
165°	244.5	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0
167.5°	248.7	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9
170°	251.4	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2
172.5°	253.0	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4
175°	254.9	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8
177.5°	255.7	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331299-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	442.3	442.8	443.4	443.6	443.3	443.2	442.9	442.6
5°	440.9	441.8	442.6	443.0	442.8	442.7	442.6	442.4
7.5°	438.8	439.8	440.8	441.3	441.2	441.0	440.8	440.7
10°	437.0	438.1	439.3	439.8	439.6	439.5	439.4	439.2
12.5°	433.9	435.1	436.2	436.7	436.5	436.4	436.3	436.1
15°	428.3	429.6	430.8	431.4	431.3	431.1	430.9	430.8
17.5°	421.0	422.4	423.7	424.4	424.4	424.4	424.4	424.4
20°	415.3	416.9	418.4	419.2	419.2	419.2	419.2	419.2
22.5°	409.1	410.7	412.3	413.2	413.5	413.6	413.9	414.1
25°	399.5	401.2	402.9	404.1	404.5	404.9	405.4	405.8
27.5°	388.9	391.1	393.2	394.4	394.8	395.1	395.4	395.7
30°	381.4	383.7	386.0	387.3	387.7	388.1	388.6	389.0
32.5°	373.3	375.9	378.6	380.3	381.1	381.9	382.6	383.4
35°	361.9	365.1	368.2	370.2	371.3	372.2	373.2	374.3
37.5°	350.1	353.6	357.1	359.3	360.4	361.4	362.5	363.6
40°	341.8	345.5	349.2	351.7	353.0	354.3	355.6	356.9
42.5°	333.7	337.8	341.8	344.6	345.8	347.1	348.4	349.7
45°	321.4	325.8	330.2	333.1	334.6	336.0	337.4	338.9
47.5°	308.5	313.1	317.8	320.9	322.4	324.0	325.6	327.2
50°	299.7	304.5	309.4	312.6	314.3	315.8	317.4	318.9
52.5°	290.2	295.2	300.1	303.4	305.1	306.9	308.5	310.2
55°	275.9	281.0	286.1	289.6	291.5	293.3	295.2	297.0
57.5°	260.7	266.2	271.8	275.5	277.4	279.3	281.2	283.1
60°	250.7	256.1	261.6	265.3	267.3	269.3	271.3	273.3
62.5°	240.0	245.8	251.6	255.5	257.4	259.2	261.1	263.0
65°	223.9	229.8	235.7	239.5	241.3	243.2	245.0	246.9
67.5°	207.6	213.4	219.4	223.3	225.2	227.2	229.2	231.1
70°	196.2	202.3	208.4	212.4	214.1	215.9	217.6	219.3
72.5°	185.2	191.2	197.3	201.3	203.3	205.3	207.4	209.5
75°	168.6	174.7	180.8	184.9	186.7	188.6	190.4	192.3
77.5°	152.3	158.4	164.5	168.6	170.6	172.5	174.6	176.6
80°	141.3	147.2	153.3	157.2	159.3	161.3	163.2	165.2
82.5°	131.0	137.0	142.9	146.9	148.8	150.7	152.6	154.5
85°	116.1	122.2	128.2	132.2	134.1	136.2	138.2	140.2
87.5°	106.9	112.5	118.6	122.4	124.3	126.1	127.9	129.8
90°	112.0	116.8	123.5	127.7	129.4	131.1	132.8	134.5
92.5°	134.2	133.8	135.3	135.9	137.2	137.3	139.5	140.3
95°	213.4	188.9	173.7	166.5	161.9	159.6	159.9	162.0
97.5°	379.2	329.8	282.1	250.1	228.3	217.9	212.4	210.0
100°	523.1	467.6	405.6	349.7	310.4	290.8	278.2	271.0
102.5°	616.4	607.8	563.8	504.2	461.5	427.0	410.8	400.4
105°	661.9	722.4	733.7	720.8	692.0	663.1	643.6	638.3
107.5°	619.3	707.7	763.5	790.5	795.9	795.8	793.2	785.6
110°	583.9	676.4	743.8	787.1	809.9	820.7	826.7	827.9



TEST NUMBER: P331299-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	551.3	640.2	712.0	761.1	792.1	809.3	819.2	823.5
115°	510.1	590.1	658.7	712.2	748.6	772.8	787.1	793.2
117.5°	477.9	548.5	611.1	661.3	698.4	723.7	738.6	743.7
120°	461.0	525.9	581.9	629.4	665.4	690.0	705.8	712.3
122.5°	447.0	506.7	559.9	602.9	635.1	659.1	673.1	678.6
125°	426.3	480.8	527.8	567.2	597.0	616.9	630.5	635.7
127.5°	405.9	455.1	499.5	535.8	561.9	580.7	592.5	596.9
130°	392.7	438.3	480.6	515.3	540.4	558.4	569.3	574.4
132.5°	380.0	422.3	461.3	494.0	518.8	536.7	546.8	551.5
135°	362.2	397.6	433.0	462.6	484.8	502.1	512.1	515.3
137.5°	347.2	376.9	405.3	431.1	451.3	466.2	474.9	478.9
140°	337.8	363.6	388.5	411.7	428.3	441.9	450.1	453.9
142.5°	330.4	352.2	373.5	392.9	408.5	420.9	428.2	429.5
145°	320.4	337.4	353.5	368.5	381.1	390.1	395.7	398.0
147.5°	312.9	325.8	337.8	348.4	358.5	365.5	369.2	370.4
150°	308.3	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	304.0	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	298.1	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	291.1	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	286.7	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	282.4	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	276.0	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	269.8	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	266.7	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	263.1	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.2	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)