

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332269-927

Luminaire Tested: **S123RDIP-S340D1195U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332269-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4452.4 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332269-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332269-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332269-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.0
10°-20°	118.9	2.7
20°-30°	171.2	3.8
30°-40°	192.9	4.3
40°-50°	184.5	4.1
50°-60°	151.1	3.4
60°-70°	101.9	2.3
70°-80°	51.3	1.2
80°-90°	17.1	0.4
90°-100°	253.0	5.7
100°-110°	716.5	16.1
110°-120°	704.8	15.8
120°-130°	562.2	12.6
130°-140°	443.3	10.0
140°-150°	330.8	7.4
150°-160°	230.6	5.2
160°-170°	135.5	3.0
170°-180°	44.1	1.0
0°-30°	332.9	7.5
0°-40°	525.7	11.8
0°-60°	861.4	19.3
0°-90°	1031.7	23.2
90°-120°	1674.3	37.6
90°-150°	3010.6	67.6
90°-180°	3421.0	76.8
0°-180°	4452.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	2	11	23	26	27	3
95°	31	102	546	159	107	34
105°	107	158	740	1294	1171	113
115°	189	235	566	1241	1424	187
125°	262	310	528	957	1123	233
135°	307	367	521	788	910	237
145°	351	402	514	647	712	220
155°	398	430	498	566	590	183
165°	435	448	477	506	514	123
175°	454	454	457	464	463	43
180°	455	455	455	455	455	



TEST NUMBER: P332269-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.4	7.1	6.7	6.6	6.3	6.3	6.8	7.4	7.9	8.5	8.2
90°	1.8	3.6	5.5	8.3	10.1	12.0	14.7	17.5	20.3	23.0	22.1
92.5°	11.4	17.0	24.6	31.8	39.6	53.2	77.3	116.9	155.7	141.6	106.8
95°	31.3	34.1	44.2	59.8	83.7	119.6	197.9	335.0	486.0	545.8	442.7
97.5°	53.4	54.3	62.2	75.8	99.4	138.2	213.0	367.6	619.2	845.8	904.9
100°	68.1	69.0	75.5	88.3	110.4	146.3	210.8	347.0	589.1	871.6	1053.0
102.5°	83.6	85.2	90.9	103.1	122.9	155.9	213.7	329.3	544.9	823.8	1060.3
105°	106.8	109.6	115.0	126.1	143.5	172.1	221.8	316.6	490.6	740.0	1004.2
107.5°	131.4	134.2	139.5	150.4	166.8	193.3	236.9	315.7	456.0	666.0	905.9
110°	149.1	151.9	156.5	166.6	182.2	208.0	249.5	319.4	442.7	624.0	844.0



TEST NUMBER: P332269-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.3	168.1	172.7	182.8	198.4	223.5	262.0	326.8	435.4	596.0	790.3
115°	188.7	192.3	197.9	207.1	222.8	247.6	282.6	338.7	432.6	566.0	725.2
117.5°	212.1	216.3	220.9	229.3	246.8	269.9	304.4	354.5	434.3	548.3	686.0
120°	228.2	231.0	235.6	244.9	262.3	285.3	318.5	366.3	437.2	540.3	665.4
122.5°	242.2	245.0	249.6	259.5	276.3	300.8	333.2	377.4	442.4	535.1	648.5
125°	262.3	264.2	269.7	279.8	297.3	322.1	354.3	394.8	450.0	528.3	626.8
127.5°	277.6	280.4	287.2	297.5	316.8	341.7	372.7	409.2	458.9	525.0	607.7
130°	287.2	289.9	298.2	309.3	328.6	353.4	383.8	418.7	464.8	522.8	597.3
132.5°	294.5	298.0	307.0	320.3	339.6	363.8	393.4	427.6	469.2	522.0	587.8
135°	307.4	311.1	321.2	335.0	354.3	379.2	407.7	439.0	475.9	520.9	575.3
137.5°	319.6	323.4	333.4	348.1	367.3	390.2	417.6	447.5	480.3	518.9	564.4
140°	327.6	332.2	341.4	356.2	374.6	397.6	424.3	451.9	483.2	518.2	557.8
142.5°	336.5	340.4	350.3	363.5	382.0	403.5	429.4	456.3	485.4	516.7	551.8
145°	350.7	353.4	361.7	375.5	391.2	412.3	436.3	461.1	486.9	514.5	544.0
147.5°	365.0	366.7	374.8	386.7	401.9	419.9	441.8	464.1	486.9	511.0	536.2
150°	374.6	375.5	382.9	394.8	407.7	424.3	445.4	464.8	486.9	508.0	531.1
152.5°	384.2	384.4	391.7	402.2	413.6	429.4	447.7	466.3	484.7	504.4	525.2
155°	398.5	398.5	404.1	413.3	423.3	436.3	451.9	466.7	482.3	498.0	516.3
157.5°	410.0	410.7	415.1	423.2	431.8	441.8	454.3	467.5	479.2	492.3	506.4
160°	418.7	418.7	422.5	429.8	436.3	445.4	456.5	467.5	477.7	487.8	499.8
162.5°	425.4	425.4	428.3	434.3	440.0	447.7	457.2	466.8	474.8	483.4	493.1
165°	435.4	434.4	436.3	440.8	444.6	451.0	458.4	464.8	470.3	476.7	484.1
167.5°	442.9	441.8	442.7	446.2	448.8	452.8	458.2	463.3	465.9	470.2	475.5
170°	447.3	445.4	446.4	449.2	451.0	452.8	457.4	461.1	463.0	465.7	470.3
172.5°	450.3	449.2	449.3	451.4	452.5	453.6	457.4	460.4	460.7	462.0	465.2
175°	453.8	452.8	451.9	453.8	453.8	454.7	456.5	458.4	457.4	457.4	459.3
177.5°	455.4	454.7	453.9	454.7	454.7	454.7	455.4	456.9	455.4	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332269-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	8.3	8.4	8.6	8.9	8.6	8.7	8.9	8.6
90°	23.0	23.9	24.9	26.7	25.7	26.7	27.6	26.7
92.5°	77.5	61.5	54.3	49.5	47.8	45.1	46.0	44.4
95°	331.4	224.6	175.8	142.7	125.2	116.9	110.4	106.8
97.5°	825.9	661.6	542.9	432.8	364.9	323.4	298.6	290.7
100°	1085.1	1010.6	902.9	772.2	679.2	612.0	576.2	577.1
102.5°	1171.3	1168.9	1106.1	1023.3	950.9	897.8	867.8	846.6
105°	1196.5	1288.6	1306.1	1282.1	1239.8	1204.8	1175.4	1170.8
107.5°	1123.9	1273.4	1354.1	1386.9	1387.6	1375.8	1365.9	1357.4
110°	1054.8	1224.2	1340.1	1404.5	1430.3	1437.7	1435.8	1434.0



TEST NUMBER: P332269-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	986.3	1159.4	1289.3	1372.1	1419.3	1442.1	1449.1	1449.5
115°	895.6	1055.7	1191.0	1291.3	1360.3	1400.8	1419.3	1423.9
117.5°	829.8	968.0	1089.6	1191.4	1263.4	1309.7	1336.3	1342.5
120°	795.2	919.5	1029.9	1122.9	1195.6	1247.1	1269.2	1274.8
122.5°	767.9	880.4	982.8	1069.1	1133.8	1180.1	1204.4	1211.4
125°	731.7	832.0	920.4	994.0	1053.0	1093.4	1116.4	1122.9
127.5°	700.1	789.5	869.2	936.2	988.7	1023.3	1044.1	1050.0
130°	680.2	763.0	837.6	900.2	949.0	982.1	1001.4	1008.8
132.5°	661.8	738.0	807.4	867.0	912.8	945.9	963.1	968.3
135°	636.9	702.3	762.1	814.5	859.7	887.2	903.8	910.3
137.5°	614.3	667.8	719.4	764.9	802.8	830.8	844.7	849.0
140°	601.0	647.9	692.1	731.7	766.7	792.5	807.2	806.3
142.5°	588.5	628.8	667.1	701.6	731.3	754.2	767.4	766.5
145°	573.4	603.8	633.3	659.9	682.9	702.3	709.6	711.5
147.5°	561.1	585.2	609.0	627.9	645.4	658.5	665.4	666.1
150°	552.2	573.4	592.7	610.2	624.0	634.1	639.7	639.7
152.5°	544.2	562.4	579.5	594.1	604.9	614.3	617.6	617.6
155°	532.0	546.7	560.5	571.6	579.9	587.2	589.1	589.9
157.5°	519.1	531.5	542.1	550.7	557.9	563.5	564.9	564.7
160°	511.7	521.9	531.1	537.5	544.0	549.5	549.5	548.6
162.5°	502.9	511.6	520.0	525.7	530.0	534.7	534.7	533.9
165°	491.5	497.0	503.4	508.0	511.7	515.4	514.5	514.5
167.5°	481.6	485.8	489.5	492.8	494.4	497.0	496.1	496.1
170°	474.9	477.7	481.3	483.2	484.1	486.0	485.1	485.1
172.5°	469.1	471.0	474.0	475.1	475.3	477.1	475.5	474.8
175°	461.1	462.0	463.9	463.9	463.9	464.8	463.9	463.0
177.5°	456.1	456.9	457.6	457.6	456.9	457.6	456.1	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

(END OF REPORT)