

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332244-927

Luminaire Tested: **S123RDIP-S340D365U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332244-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D365U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2016.6 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332244-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332244-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	71	67	65	61	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	28
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	32	28	33	28	25	27	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	25	32	27	23	27	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332244-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	2.1
10°-20°	118.9	5.9
20°-30°	171.2	8.5
30°-40°	192.9	9.6
40°-50°	184.5	9.1
50°-60°	151.1	7.5
60°-70°	101.9	5.1
70°-80°	51.3	2.5
80°-90°	14.6	0.7
90°-100°	23.2	1.2
100°-110°	69.5	3.4
110°-120°	118.2	5.9
120°-130°	155.5	7.7
130°-140°	174.7	8.7
140°-150°	171.8	8.5
150°-160°	144.6	7.2
160°-170°	96.3	4.8
170°-180°	33.7	1.7
0°-30°	332.9	16.5
0°-40°	525.7	26.1
0°-60°	861.4	42.7
0°-90°	1029.2	51.0
90°-120°	210.9	10.5
90°-150°	712.8	35.3
90°-180°	987.0	48.9
0°-180°	2016.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	0	3	7	8	8	2
95°	17	18	21	22	22	19
105°	63	64	66	66	67	67
115°	119	120	119	120	119	118
125°	174	175	174	173	172	155
135°	226	228	227	226	226	174
145°	274	275	275	275	274	171
155°	314	314	314	315	313	144
165°	342	341	341	342	341	96
175°	356	354	354	356	354	34
180°	356	356	356	356	356	



TEST NUMBER: P332244-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.1	6.6	5.9	5.4	4.8	4.5	4.7	4.8	5.0	5.1	5.1
90°	0.3	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0
92.5°	6.8	7.2	7.6	8.1	8.5	8.9	9.3	9.8	10.3	10.8	10.9
95°	16.6	17.0	17.3	17.8	18.2	18.7	19.3	19.7	20.2	20.8	21.0
97.5°	29.3	29.6	30.0	30.3	30.7	31.0	31.4	31.7	32.1	32.4	32.7
100°	38.1	38.4	38.8	39.2	39.5	39.9	40.2	40.6	40.9	41.1	41.4
102.5°	48.2	48.4	48.6	48.8	49.0	49.4	49.7	50.2	50.6	51.0	51.2
105°	63.0	63.1	63.2	63.4	63.5	63.8	64.4	65.0	65.5	66.1	66.1
107.5°	80.2	80.3	80.4	80.5	80.6	80.6	80.9	81.1	81.4	81.6	81.8
110°	91.0	91.1	91.3	91.3	91.5	91.6	91.7	91.9	92.0	92.1	92.4



TEST NUMBER: P332244-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.2	102.3	102.3	102.4	102.5	102.5	102.6	102.6	102.6	102.7	102.9
115°	119.0	119.1	119.4	119.5	119.7	119.8	119.6	119.5	119.4	119.2	119.3
117.5°	135.9	136.0	136.2	136.3	136.4	136.3	136.2	136.0	135.9	135.7	135.7
120°	146.4	146.8	147.2	147.5	147.9	147.9	147.7	147.3	147.0	146.7	146.6
122.5°	157.4	157.6	158.0	158.2	158.5	158.5	158.4	158.2	158.0	157.9	157.7
125°	174.1	174.3	174.5	174.7	174.9	174.9	174.8	174.7	174.5	174.4	174.1
127.5°	189.6	190.0	190.4	190.8	191.2	191.3	191.2	191.0	190.9	190.8	190.4
130°	199.9	200.3	200.9	201.4	201.8	202.0	201.8	201.7	201.5	201.3	201.1
132.5°	210.2	210.7	211.2	211.7	212.1	212.4	212.2	212.1	211.9	211.8	211.5
135°	225.9	226.3	226.6	227.0	227.4	227.6	227.5	227.4	227.4	227.4	227.0
137.5°	240.5	240.8	241.1	241.4	241.7	241.9	242.1	242.2	242.4	242.6	242.3
140°	250.6	250.9	251.2	251.5	251.8	252.0	252.1	252.1	252.2	252.2	252.2
142.5°	259.8	260.1	260.4	260.7	260.9	261.2	261.3	261.4	261.5	261.7	261.6
145°	274.1	274.2	274.3	274.4	274.6	274.7	274.9	275.1	275.3	275.4	275.4
147.5°	286.6	286.8	287.1	287.3	287.5	287.7	287.9	288.0	288.2	288.4	288.4
150°	295.3	295.5	295.6	295.7	295.9	296.0	296.1	296.2	296.4	296.4	296.4
152.5°	302.5	302.7	302.9	303.0	303.2	303.3	303.4	303.5	303.6	303.6	303.7
155°	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9	314.0	314.1	314.3
157.5°	323.4	323.4	323.3	323.2	323.1	323.1	323.2	323.2	323.3	323.4	323.6
160°	329.5	329.4	329.2	329.2	329.0	328.9	328.9	328.9	328.9	328.9	329.2
162.5°	334.9	334.7	334.5	334.4	334.1	334.1	334.1	334.2	334.3	334.3	334.6
165°	341.8	341.7	341.4	341.3	341.0	341.0	341.0	341.0	341.0	341.0	341.4
167.5°	347.4	347.1	346.9	346.6	346.3	346.3	346.3	346.3	346.4	346.5	346.8
170°	350.5	350.2	350.0	349.7	349.5	349.4	349.4	349.4	349.4	349.4	349.8
172.5°	353.0	352.7	352.4	352.2	352.0	351.8	351.8	351.8	351.8	351.8	352.2
175°	355.5	355.3	355.1	354.8	354.6	354.4	354.4	354.4	354.4	354.4	354.8
177.5°	356.6	356.4	356.2	356.0	355.8	355.7	355.7	355.7	355.7	355.7	356.0
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332244-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	5.1	5.1	5.1	5.1	5.1	5.0	5.0	4.9
90°	7.2	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.2	11.3	11.6	11.6	11.6	11.5	11.4	11.3
95°	21.2	21.5	21.7	21.9	21.9	21.9	21.9	21.9
97.5°	33.0	33.3	33.6	33.7	33.7	33.7	33.6	33.6
100°	41.5	41.7	41.9	42.1	42.1	42.3	42.5	42.5
102.5°	51.4	51.6	51.7	51.8	51.8	51.8	51.7	51.7
105°	66.1	66.1	66.1	66.1	66.2	66.4	66.5	66.6
107.5°	82.0	82.1	82.4	82.5	82.4	82.3	82.2	82.1
110°	92.6	92.8	93.1	93.2	93.0	92.9	92.8	92.7





TEST NUMBER: P332244-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	103.2	103.5	103.9	103.9	103.9	103.9	103.9	103.9
115°	119.4	119.5	119.5	119.5	119.5	119.4	119.3	119.2
117.5°	135.7	135.7	135.7	135.5	135.4	135.2	135.1	134.9
120°	146.6	146.5	146.5	146.3	146.2	146.1	146.0	145.8
122.5°	157.6	157.4	157.2	157.1	156.9	156.7	156.5	156.4
125°	173.9	173.6	173.4	173.2	172.9	172.7	172.4	172.1
127.5°	190.0	189.7	189.3	189.0	188.8	188.5	188.2	187.9
130°	200.8	200.5	200.3	199.9	199.6	199.1	198.7	198.2
132.5°	211.2	210.9	210.6	210.3	209.9	209.6	209.3	209.0
135°	226.8	226.6	226.3	226.2	226.0	225.9	225.8	225.6
137.5°	242.1	241.9	241.5	241.3	241.1	240.8	240.6	240.3
140°	252.1	252.1	252.0	251.8	251.3	250.9	250.4	250.0
142.5°	261.5	261.4	261.4	261.2	260.9	260.5	260.2	259.8
145°	275.4	275.3	275.2	275.0	274.8	274.6	274.3	274.1
147.5°	288.4	288.4	288.4	288.2	287.9	287.5	287.1	286.7
150°	296.4	296.4	296.4	296.3	295.9	295.6	295.2	294.8
152.5°	303.8	304.0	304.0	303.9	303.6	303.2	302.9	302.6
155°	314.6	314.8	315.1	315.0	314.6	314.1	313.7	313.2
157.5°	323.8	324.2	324.4	324.3	324.0	323.7	323.3	323.0
160°	329.5	329.9	330.2	330.2	329.9	329.7	329.5	329.2
162.5°	334.9	335.3	335.6	335.5	335.1	334.7	334.3	333.9
165°	341.7	342.1	342.5	342.5	342.0	341.6	341.1	340.7
167.5°	347.2	347.6	348.0	348.0	347.6	347.2	346.8	346.5
170°	350.2	350.7	351.1	351.1	350.7	350.2	349.8	349.4
172.5°	352.6	353.0	353.4	353.4	352.9	352.5	352.0	351.6
175°	355.1	355.5	355.9	355.8	355.5	355.0	354.6	354.1
177.5°	356.3	356.6	356.9	356.9	356.6	356.2	355.8	355.5
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4

(END OF REPORT)