

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332250-927

Luminaire Tested: **S123RDIP-S340D585U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332250-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2623.5 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332250-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332250-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34
3	80	71	64	58	72	65	58	54	53	49	45	42	39	37	33	31	29
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	37	32	52	42	35	30	35	29	26	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332250-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.6
10°-20°	118.9	4.5
20°-30°	171.2	6.5
30°-40°	192.9	7.4
40°-50°	184.5	7.0
50°-60°	151.1	5.8
60°-70°	101.9	3.9
70°-80°	51.3	2.0
80°-90°	15.3	0.6
90°-100°	37.5	1.4
100°-110°	112.2	4.3
110°-120°	190.8	7.3
120°-130°	250.9	9.6
130°-140°	282.0	10.7
140°-150°	277.2	10.6
150°-160°	233.4	8.9
160°-170°	155.4	5.9
170°-180°	54.4	2.1
0°-30°	332.9	12.7
0°-40°	525.7	20.0
0°-60°	861.4	32.8
0°-90°	1029.9	39.3
90°-120°	340.4	13.0
90°-150°	1150.6	43.9
90°-180°	1594.0	60.8
0°-180°	2623.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	0	5	11	13	14	3
95°	27	30	33	35	35	30
105°	102	103	107	107	108	109
115°	192	193	192	193	192	190
125°	281	282	282	280	278	251
135°	365	367	367	365	364	281
145°	442	443	445	444	442	276
155°	506	507	507	508	506	233
165°	552	550	550	553	550	155
175°	574	572	572	574	572	54
180°	575	575	575	575	575	



TEST NUMBER: P332250-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.2	6.7	6.1	5.6	5.1	5.0	5.2	5.5	5.8	6.0	6.0
90°	0.5	1.4	2.5	3.5	4.4	5.6	6.9	8.2	9.5	10.9	11.2
92.5°	10.9	11.6	12.3	13.0	13.7	14.4	15.1	15.8	16.6	17.3	17.7
95°	26.7	27.3	28.0	28.8	29.5	30.3	31.1	31.8	32.6	33.4	33.8
97.5°	47.4	47.8	48.4	49.0	49.4	50.0	50.5	51.2	51.7	52.4	52.8
100°	61.5	62.0	62.7	63.3	63.8	64.4	64.9	65.4	65.9	66.4	66.7
102.5°	77.7	78.1	78.4	78.8	79.1	79.7	80.3	81.0	81.7	82.3	82.6
105°	101.6	101.9	102.0	102.3	102.5	103.0	103.9	104.8	105.8	106.6	106.6
107.5°	129.5	129.6	129.8	129.8	130.0	130.2	130.6	130.9	131.3	131.7	132.0
110°	146.9	147.0	147.3	147.4	147.7	147.8	148.1	148.3	148.5	148.7	149.1



TEST NUMBER: P332250-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	164.9	165.0	165.2	165.2	165.4	165.5	165.6	165.6	165.6	165.6	166.1
115°	192.0	192.3	192.7	193.0	193.2	193.3	193.1	192.9	192.7	192.5	192.6
117.5°	219.4	219.5	219.8	219.9	220.1	220.1	219.8	219.6	219.4	219.0	219.0
120°	236.3	236.9	237.5	238.1	238.8	238.8	238.3	237.8	237.3	236.8	236.7
122.5°	254.1	254.4	254.9	255.3	255.8	255.9	255.6	255.4	255.1	254.8	254.6
125°	281.1	281.4	281.6	281.9	282.3	282.3	282.1	281.9	281.7	281.5	281.1
127.5°	306.0	306.7	307.3	307.9	308.6	308.8	308.6	308.3	308.1	307.9	307.4
130°	322.7	323.4	324.2	325.0	325.8	326.1	325.8	325.5	325.2	324.9	324.5
132.5°	339.2	340.1	340.9	341.7	342.5	342.8	342.5	342.3	342.1	341.9	341.4
135°	364.6	365.3	365.8	366.5	367.0	367.3	367.2	367.1	367.0	366.9	366.5
137.5°	388.2	388.6	389.1	389.7	390.1	390.5	390.8	391.0	391.3	391.6	391.2
140°	404.4	404.9	405.4	405.9	406.4	406.7	406.8	406.9	407.0	407.1	407.0
142.5°	419.2	419.7	420.3	420.7	421.2	421.6	421.8	421.9	422.2	422.3	422.2
145°	442.4	442.6	442.8	443.0	443.1	443.4	443.7	444.0	444.3	444.7	444.5
147.5°	462.6	463.0	463.3	463.7	464.1	464.4	464.7	464.9	465.2	465.5	465.5
150°	476.7	476.9	477.1	477.3	477.5	477.7	477.9	478.1	478.3	478.5	478.5
152.5°	488.3	488.5	488.9	489.1	489.4	489.6	489.7	489.8	490.0	490.0	490.2
155°	506.5	506.5	506.5	506.5	506.5	506.6	506.7	506.8	506.9	507.0	507.4
157.5°	522.0	522.0	521.8	521.7	521.6	521.6	521.7	521.7	521.8	521.9	522.3
160°	531.8	531.6	531.4	531.2	531.0	530.9	530.9	530.9	530.9	530.9	531.4
162.5°	540.5	540.2	540.0	539.6	539.4	539.3	539.4	539.5	539.6	539.6	540.1
165°	551.7	551.4	551.1	550.8	550.5	550.3	550.3	550.3	550.3	550.3	551.0
167.5°	560.6	560.2	559.8	559.4	559.0	558.9	559.0	559.0	559.1	559.2	559.8
170°	565.7	565.3	564.9	564.5	564.1	563.9	563.9	563.9	563.9	563.9	564.6
172.5°	569.7	569.3	568.9	568.5	568.1	567.9	567.9	567.9	567.9	567.9	568.5
175°	573.9	573.5	573.1	572.7	572.3	572.0	572.0	572.0	572.0	572.0	572.7
177.5°	575.6	575.3	575.0	574.6	574.3	574.1	574.1	574.1	574.1	574.1	574.6
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P332250-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	6.0	6.0	6.1	6.1	6.0	6.0	6.0	5.9
90°	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	18.0	18.3	18.6	18.8	18.6	18.5	18.4	18.2
95°	34.2	34.6	35.0	35.3	35.3	35.3	35.3	35.3
97.5°	53.2	53.7	54.2	54.3	54.3	54.3	54.3	54.2
100°	67.0	67.3	67.7	67.9	68.0	68.3	68.4	68.7
102.5°	82.9	83.3	83.5	83.7	83.7	83.6	83.6	83.5
105°	106.6	106.6	106.6	106.7	106.9	107.1	107.3	107.6
107.5°	132.3	132.6	132.9	133.1	132.9	132.8	132.7	132.6
110°	149.5	149.9	150.3	150.4	150.2	150.0	149.8	149.6



TEST NUMBER: P332250-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	166.6	167.1	167.5	167.8	167.8	167.7	167.7	167.6
115°	192.7	192.8	192.9	192.9	192.8	192.7	192.6	192.5
117.5°	219.0	219.0	219.0	218.8	218.6	218.2	218.0	217.7
120°	236.5	236.5	236.4	236.2	236.0	235.8	235.6	235.4
122.5°	254.3	254.1	253.8	253.5	253.3	252.9	252.7	252.4
125°	280.7	280.3	279.9	279.5	279.1	278.7	278.3	277.9
127.5°	306.7	306.2	305.6	305.1	304.7	304.2	303.7	303.2
130°	324.1	323.7	323.3	322.7	322.0	321.3	320.6	319.9
132.5°	340.9	340.4	339.9	339.5	338.9	338.3	337.8	337.2
135°	366.1	365.7	365.3	365.0	364.8	364.6	364.4	364.2
137.5°	390.7	390.3	389.9	389.5	389.1	388.7	388.3	387.9
140°	406.9	406.8	406.7	406.3	405.6	404.9	404.2	403.5
142.5°	422.1	422.0	421.9	421.6	421.0	420.5	419.9	419.4
145°	444.4	444.3	444.3	443.9	443.5	443.1	442.8	442.4
147.5°	465.5	465.5	465.5	465.2	464.6	464.0	463.4	462.8
150°	478.5	478.5	478.5	478.2	477.6	477.0	476.4	475.8
152.5°	490.4	490.6	490.8	490.5	490.0	489.5	489.0	488.5
155°	507.8	508.2	508.6	508.4	507.7	507.0	506.4	505.6
157.5°	522.8	523.2	523.6	523.5	522.9	522.4	521.8	521.3
160°	532.0	532.4	532.9	533.0	532.6	532.2	531.8	531.4
162.5°	540.6	541.1	541.6	541.5	540.9	540.3	539.6	539.0
165°	551.6	552.2	552.8	552.7	552.0	551.3	550.6	549.9
167.5°	560.5	561.1	561.7	561.7	561.1	560.5	559.8	559.2
170°	565.3	566.0	566.7	566.7	566.0	565.3	564.6	563.9
172.5°	569.1	569.7	570.4	570.4	569.7	568.9	568.2	567.5
175°	573.2	573.9	574.5	574.4	573.7	573.0	572.3	571.6
177.5°	575.1	575.6	576.1	576.0	575.4	574.9	574.3	573.8
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2

(END OF REPORT)