

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332251-927

Luminaire Tested: **S123RDIP-S340D585U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332251-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U927-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2709.2 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332251-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332251-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332251-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	1.6
10°-20°	118.9	4.4
20°-30°	171.2	6.3
30°-40°	192.9	7.1
40°-50°	184.5	6.8
50°-60°	151.1	5.6
60°-70°	101.9	3.8
70°-80°	51.3	1.9
80°-90°	15.3	0.6
90°-100°	124.2	4.6
100°-110°	351.7	13.0
110°-120°	346.0	12.8
120°-130°	276.0	10.2
130°-140°	217.6	8.0
140°-150°	162.4	6.0
150°-160°	113.2	4.2
160°-170°	66.5	2.5
170°-180°	21.6	0.8
0°-30°	332.9	12.3
0°-40°	525.7	19.4
0°-60°	861.4	31.8
0°-90°	1029.9	38.0
90°-120°	822.0	30.3
90°-150°	1478.0	54.6
90°-180°	1679.0	62.0
0°-180°	2709.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	1	5	11	13	13	2
95°	15	50	268	78	52	17
105°	52	78	363	635	575	56
115°	93	115	278	609	699	92
125°	129	152	259	470	551	114
135°	151	180	256	387	447	117
145°	172	197	252	317	349	108
155°	196	211	244	278	290	90
165°	214	220	234	248	252	60
175°	223	223	225	228	227	21
180°	223	223	223	223	223	



TEST NUMBER: P332251-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.3	6.7	6.2	5.7	5.2	5.0	5.3	5.5	5.9	6.1	5.9
90°	0.9	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9
92.5°	5.6	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4
95°	15.4	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3
97.5°	26.2	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3
100°	33.4	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9
102.5°	41.0	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5
105°	52.4	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0
107.5°	64.5	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7
110°	73.2	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3



TEST NUMBER: P332251-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.1	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9
115°	92.6	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1
117.5°	104.1	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8
120°	112.1	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7
122.5°	118.9	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4
125°	128.8	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7
127.5°	136.3	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3
130°	141.0	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3
132.5°	144.6	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5
135°	150.9	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4
137.5°	156.9	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1
140°	160.9	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8
142.5°	165.2	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9
145°	172.1	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0
147.5°	179.2	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2
150°	183.9	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7
152.5°	188.6	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9
155°	195.7	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5
157.5°	201.2	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6
160°	205.6	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3
162.5°	208.8	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1
165°	213.7	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7
167.5°	217.5	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5
170°	219.6	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9
172.5°	221.0	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4
175°	222.8	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5
177.5°	223.6	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332251-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	5.9	6.0	6.0	6.1	5.9	6.0	6.0	5.9
90°	11.3	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	38.0	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	162.6	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	405.5	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	532.7	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	575.0	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	587.4	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	551.8	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	517.8	600.9	657.9	689.5	702.2	705.8	704.9	703.9





TEST NUMBER: P332251-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	484.2	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	439.7	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	407.3	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	390.4	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	377.0	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	359.2	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	343.6	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	333.9	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	324.9	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	312.7	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	301.6	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	295.1	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	288.9	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	281.5	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	275.4	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	271.1	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	267.1	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	261.2	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	254.8	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	251.2	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	246.9	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	241.3	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	236.4	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	233.1	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	230.3	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.4	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	223.9	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)