

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331361-935

Luminaire Tested: **S122DIP-S675D925U935-4F0-1E-UDD-D1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331361-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D925U935-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5164.9 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331361-935

CATALOG NUMBER: S122DIP-S675D925U935-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331361-935

CATALOG NUMBER: S122DIP-S675D925U935-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	94	90	85	81	85	81	78	74	66	64	61	52	50	49	39	38	37	31
2	85	77	71	65	77	70	65	60	57	53	50	45	42	40	34	32	30	25
3	78	68	60	54	70	62	55	50	50	45	41	40	36	33	30	27	25	21
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	26	24	21	17
5	65	53	45	38	58	48	41	35	39	34	30	31	27	24	24	21	18	15
6	59	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	42	34	29	50	39	32	27	32	26	22	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	26	21	18	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9792	9792	9792
5°	9839	9426	9390
10°	9778	9148	9044
15°	9643	8853	8681
20°	9473	8536	8331
25°	9305	8231	8014
30°	9067	7919	7694
35°	8828	7615	7468
40°	8576	7358	7243
45°	8334	7127	7051
50°	8078	6920	6861
55°	7810	6696	6668
60°	7480	6465	6465
65°	7135	6192	6222
70°	6751	5899	5960
75°	6257	5612	5720
80°	5488	5319	5476
85°	4743	5064	5286



TEST NUMBER: P331361-935

CATALOG NUMBER: S122DIP-S675D925U935-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	1.1
10°-20°	164.8	3.2
20°-30°	249.7	4.8
30°-40°	304.2	5.9
40°-50°	327.2	6.3
50°-60°	317.8	6.2
60°-70°	277.5	5.4
70°-80°	213.6	4.1
80°-90°	147.4	2.9
90°-100°	163.3	3.2
100°-110°	272.5	5.3
110°-120°	390.2	7.6
120°-130°	477.0	9.2
130°-140°	516.7	10.0
140°-150°	497.6	9.6
150°-160°	415.8	8.1
160°-170°	275.8	5.3
170°-180°	96.4	1.9
0°-30°	472.0	9.1
0°-40°	776.1	15.0
0°-60°	1421.1	27.5
0°-90°	2059.6	39.9
90°-120°	825.9	16.0
90°-150°	2317.3	44.9
90°-180°	3105.0	60.1
0°-180°	5164.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	606	606	606	606	606	
5°	608	605	600	605	605	58
15°	580	582	582	589	589	163
25°	527	534	541	552	555	242
35°	454	469	486	505	512	284
45°	373	397	427	453	463	288
55°	286	318	363	394	406	255
65°	195	239	290	325	338	194
75°	108	158	214	250	263	114
85°	32	86	142	178	192	34
90°	10	72	146	178	191	8
95°	52	102	156	188	198	57
105°	189	218	265	296	307	200
115°	347	363	400	424	432	343
125°	502	511	535	556	563	449
135°	648	657	668	685	690	501
145°	785	791	796	802	804	491
155°	898	900	903	907	905	413
165°	977	976	976	982	978	275
175°	1016	1014	1012	1018	1013	97
180°	1018	1018	1018	1018	1018	



TEST NUMBER: P331361-935

CATALOG NUMBER: S122DIP-S675D925U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5
2.5°	610.0	609.5	609.1	608.6	608.1	607.3	606.2	605.1	604.1	603.0	603.7
5°	608.2	607.6	607.1	606.5	605.9	605.0	603.8	602.7	601.5	600.3	601.5
7.5°	602.8	602.4	602.0	601.6	601.2	600.5	599.7	598.7	597.9	597.0	598.4
10°	598.6	598.1	597.8	597.4	597.0	596.5	595.9	595.4	594.8	594.2	595.7
12.5°	591.5	591.6	591.7	591.8	591.9	591.7	591.2	590.8	590.4	590.0	591.5
15°	580.1	580.5	580.9	581.3	581.7	581.9	581.9	581.9	581.9	581.9	583.6
17.5°	565.3	566.2	567.0	567.8	568.6	569.4	570.0	570.6	571.2	571.9	573.7
20°	555.5	556.5	557.4	558.4	559.4	560.3	561.0	561.9	562.7	563.4	565.6
22.5°	544.9	546.0	547.3	548.4	549.5	550.6	551.7	552.8	553.9	555.0	557.2
25°	527.4	528.7	530.1	531.5	532.9	534.4	536.1	538.0	539.7	541.4	543.8
27.5°	506.3	508.5	510.7	513.0	515.2	517.4	519.4	521.5	523.6	525.6	528.6
30°	492.2	494.7	497.3	499.8	502.4	504.9	507.5	510.0	512.6	515.1	518.1
32.5°	476.7	479.6	482.4	485.3	488.2	491.1	494.1	497.1	500.1	503.1	506.7
35°	454.4	457.7	461.1	464.3	467.7	471.2	474.9	478.6	482.3	486.0	490.3
37.5°	430.2	434.0	437.8	441.6	445.5	449.8	454.6	459.4	464.2	469.0	473.8
40°	414.0	418.3	422.6	426.9	431.2	435.9	441.3	446.5	451.8	457.0	462.1
42.5°	398.6	402.8	407.1	411.4	415.7	420.9	427.0	433.0	439.0	445.1	450.6
45°	372.6	378.0	383.2	388.5	393.7	399.8	406.7	413.5	420.3	427.1	433.3
47.5°	347.2	352.9	358.7	364.4	370.1	377.0	385.0	393.0	401.1	409.1	415.4
50°	329.6	335.7	341.7	347.8	353.8	361.3	370.1	378.8	387.6	396.4	403.0
52.5°	312.7	319.1	325.5	331.8	338.2	346.0	355.2	364.5	373.8	383.1	389.9
55°	285.7	292.7	299.7	306.8	313.7	322.4	332.5	342.7	352.8	363.0	370.1
57.5°	258.9	266.9	274.8	282.8	290.7	299.8	310.1	320.5	330.9	341.2	348.8
60°	240.0	248.3	256.8	265.2	273.5	283.4	294.5	305.6	316.7	327.9	335.3
62.5°	223.1	231.8	240.5	249.2	258.0	267.9	279.0	290.1	301.3	312.4	320.3
65°	195.1	204.7	214.3	223.9	233.4	243.9	255.5	267.0	278.5	290.1	298.1
67.5°	169.4	179.4	189.5	199.5	209.5	220.3	232.1	243.9	255.7	267.5	275.6
70°	151.2	161.4	171.5	181.7	191.8	202.9	215.1	227.1	239.3	251.4	259.8
72.5°	134.3	144.7	155.2	165.7	176.2	187.5	199.8	212.1	224.4	236.6	244.9
75°	108.1	119.1	130.0	140.9	151.9	163.6	176.1	188.6	201.0	213.6	222.0
77.5°	82.8	94.3	105.7	117.1	128.5	140.7	153.3	166.1	178.7	191.4	199.8
80°	66.0	77.8	89.7	101.7	113.6	125.9	138.6	151.3	163.9	176.7	184.9
82.5°	51.8	63.6	75.3	87.1	98.9	111.2	124.1	136.9	149.7	162.6	170.8
85°	31.7	43.7	55.9	67.9	80.1	92.4	104.9	117.4	129.9	142.4	150.6
87.5°	17.4	29.5	41.6	53.7	65.8	78.5	91.9	105.2	118.6	131.9	139.7
90°	9.6	23.2	36.9	50.5	64.1	79.3	96.0	112.7	129.4	146.1	153.5
92.5°	23.4	35.6	47.9	60.1	72.3	84.9	98.0	111.0	124.0	137.0	144.7
95°	51.7	62.8	73.9	85.0	96.1	107.6	119.8	131.9	144.0	156.1	163.5
97.5°	87.8	97.6	107.5	117.4	127.2	138.1	150.1	162.0	174.0	186.0	193.2
100°	115.3	124.1	132.8	141.5	150.3	160.4	171.9	183.5	194.9	206.5	213.7
102.5°	143.4	151.3	159.1	166.9	174.7	184.3	195.7	207.1	218.3	229.7	236.9
105°	189.2	195.4	201.6	207.8	214.0	222.5	233.0	243.6	254.1	264.6	271.8
107.5°	236.0	241.4	246.8	252.2	257.5	265.1	274.8	284.6	294.3	304.0	310.7
110°	265.6	270.6	275.7	280.8	285.8	293.1	302.6	312.3	321.8	331.4	337.6



TEST NUMBER: P331361-935

CATALOG NUMBER: S122DIP-S675D925U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	298.6	303.0	307.5	311.9	316.2	323.0	331.9	340.9	349.8	358.8	364.5
115°	347.2	350.5	353.8	357.1	360.4	366.3	374.6	383.1	391.5	399.8	405.5
117.5°	394.8	397.7	400.6	403.6	406.6	411.6	418.6	425.7	432.7	439.7	445.1
120°	427.1	429.4	431.7	434.0	436.4	440.7	446.9	453.2	459.5	465.8	471.2
122.5°	456.7	458.8	461.0	463.1	465.2	469.4	475.7	482.0	488.3	494.6	499.4
125°	501.8	503.5	505.2	507.0	508.7	512.4	518.1	523.7	529.4	535.1	539.8
127.5°	546.6	548.6	550.6	552.6	554.6	557.8	562.1	566.5	570.8	575.1	579.4
130°	574.9	577.1	579.5	581.7	584.0	587.0	590.7	594.4	598.2	601.9	606.2
132.5°	606.5	608.3	610.1	612.0	613.8	616.3	619.6	622.8	626.0	629.3	633.0
135°	647.9	650.0	652.1	654.2	656.3	658.5	660.8	663.1	665.5	667.9	671.8
137.5°	692.4	694.1	695.8	697.4	699.1	700.6	702.0	703.4	704.7	706.0	709.5
140°	719.2	720.7	722.2	723.8	725.3	726.8	728.1	729.4	730.7	732.1	735.2
142.5°	746.7	748.2	749.8	751.3	752.8	753.9	754.7	755.4	756.1	756.8	759.5
145°	785.3	786.7	788.0	789.4	790.7	791.9	793.1	794.2	795.4	796.5	797.9
147.5°	820.5	822.2	823.8	825.4	827.0	828.2	829.0	829.7	830.4	831.2	831.8
150°	844.6	845.8	846.9	848.1	849.2	850.2	850.9	851.7	852.5	853.3	853.8
152.5°	865.9	867.1	868.2	869.4	870.6	871.6	872.5	873.4	874.3	875.2	876.0
155°	897.9	898.5	899.1	899.7	900.2	900.8	901.4	901.9	902.5	903.0	904.0
157.5°	925.2	925.6	926.0	926.3	926.8	927.1	927.5	927.8	928.2	928.5	929.8
160°	941.8	942.1	942.5	942.9	943.2	943.6	943.7	943.9	944.1	944.3	945.5
162.5°	956.8	956.9	957.0	957.1	957.2	957.3	957.5	957.7	957.9	958.0	959.3
165°	977.0	976.8	976.5	976.4	976.2	976.1	976.1	976.1	976.1	976.1	977.4
167.5°	993.8	993.2	992.6	992.0	991.5	991.2	991.2	991.1	991.1	991.0	992.4
170°	1002.7	1002.1	1001.6	1001.0	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7
172.5°	1008.9	1008.3	1007.8	1007.2	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9
175°	1016.5	1015.9	1015.3	1014.8	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5
177.5°	1019.6	1019.1	1018.6	1018.2	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331361-935

CATALOG NUMBER: S122DIP-S675D925U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5
2.5°	604.5	605.3	606.1	606.3	606.0	605.7	605.4	605.1
5°	602.7	603.8	605.0	605.5	605.3	605.1	604.9	604.7
7.5°	599.8	601.2	602.6	603.2	603.0	602.8	602.6	602.4
10°	597.3	598.8	600.5	601.1	600.9	600.7	600.5	600.3
12.5°	593.1	594.6	596.2	596.8	596.7	596.5	596.3	596.1
15°	585.4	587.1	588.9	589.7	589.5	589.3	589.1	588.9
17.5°	575.5	577.4	579.2	580.1	580.1	580.1	580.1	580.1
20°	567.7	569.9	572.0	573.1	573.1	573.1	573.1	573.1
22.5°	559.3	561.5	563.5	564.8	565.1	565.4	565.8	566.0
25°	546.1	548.5	550.8	552.2	552.8	553.5	554.1	554.7
27.5°	531.6	534.5	537.5	539.2	539.6	540.0	540.4	540.9
30°	521.3	524.4	527.5	529.4	530.0	530.6	531.2	531.8
32.5°	510.3	513.9	517.5	519.8	520.9	521.9	523.0	524.0
35°	494.6	498.9	503.3	506.1	507.5	508.9	510.1	511.5
37.5°	478.5	483.3	488.1	491.2	492.7	494.0	495.5	497.0
40°	467.2	472.3	477.3	480.8	482.5	484.3	486.0	487.8
42.5°	456.2	461.8	467.3	471.0	472.7	474.5	476.2	477.9
45°	439.3	445.3	451.4	455.4	457.4	459.3	461.2	463.2
47.5°	421.7	428.1	434.4	438.6	440.7	442.9	445.1	447.2
50°	409.7	416.3	423.0	427.4	429.6	431.7	433.8	435.9
52.5°	396.7	403.5	410.3	414.8	417.1	419.4	421.7	424.0
55°	377.0	384.1	391.2	395.9	398.5	401.0	403.6	406.0
57.5°	356.4	363.9	371.5	376.6	379.2	381.8	384.4	386.9
60°	342.7	350.1	357.6	362.7	365.3	368.1	370.8	373.6
62.5°	328.1	336.0	344.0	349.2	351.7	354.3	356.9	359.5
65°	306.1	314.1	322.1	327.4	329.9	332.4	335.0	337.5
67.5°	283.7	291.8	299.9	305.3	307.9	310.6	313.2	315.9
70°	268.2	276.6	285.0	290.3	292.7	295.1	297.4	299.7
72.5°	253.1	261.3	269.6	275.1	277.9	280.8	283.5	286.4
75°	230.4	238.8	247.2	252.6	255.2	257.7	260.3	262.8
77.5°	208.2	216.5	224.9	230.4	233.2	235.9	238.6	241.3
80°	193.0	201.3	209.5	215.0	217.7	220.4	223.2	225.9
82.5°	179.0	187.2	195.4	200.8	203.4	206.0	208.5	211.1
85°	158.8	167.0	175.2	180.6	183.4	186.1	188.9	191.6
87.5°	147.7	155.6	163.4	168.7	171.2	173.7	176.2	178.8
90°	160.9	168.4	175.8	180.8	183.3	185.9	188.4	191.0
92.5°	152.5	160.2	168.0	173.0	175.4	177.8	180.1	182.5
95°	170.9	178.3	185.7	190.5	192.4	194.4	196.3	198.3
97.5°	200.4	207.7	214.9	219.6	221.9	224.2	226.4	228.7
100°	220.9	228.2	235.4	240.0	241.9	243.9	245.8	247.8
102.5°	244.2	251.4	258.6	263.2	265.2	267.2	269.1	271.0
105°	279.1	286.3	293.5	298.2	300.3	302.5	304.6	306.8
107.5°	317.5	324.2	330.9	334.8	336.1	337.3	338.6	339.9
110°	343.9	350.2	356.4	360.3	361.9	363.4	365.1	366.6



TEST NUMBER: P331361-935

CATALOG NUMBER: S122DIP-S675D925U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	370.3	376.2	381.9	385.7	387.4	389.2	390.9	392.6
115°	411.2	416.9	422.6	426.2	427.7	429.3	430.9	432.5
117.5°	450.4	455.7	461.1	464.4	465.8	467.3	468.6	470.1
120°	476.7	482.2	487.7	491.2	492.8	494.3	495.9	497.5
122.5°	504.3	509.1	513.9	517.1	518.5	520.0	521.3	522.8
125°	544.5	549.2	553.9	557.1	558.6	560.2	561.7	563.4
127.5°	583.5	587.6	591.9	594.4	595.6	596.7	597.8	598.9
130°	610.5	614.8	619.1	621.6	622.5	623.3	624.1	624.8
132.5°	636.7	640.4	644.0	646.4	647.3	648.3	649.3	650.2
135°	675.6	679.6	683.5	686.0	686.9	687.9	688.9	689.9
137.5°	712.9	716.4	719.8	721.8	722.4	723.0	723.5	724.1
140°	738.4	741.5	744.6	746.4	746.7	747.2	747.6	748.0
142.5°	762.2	764.7	767.4	768.9	769.1	769.4	769.6	769.9
145°	799.3	800.6	801.9	802.7	803.0	803.1	803.4	803.6
147.5°	832.4	832.9	833.5	833.7	833.4	833.2	832.9	832.7
150°	854.4	855.0	855.5	855.5	855.0	854.4	853.8	853.3
152.5°	876.7	877.4	878.1	878.1	877.4	876.7	876.0	875.2
155°	905.0	905.9	906.9	907.1	906.5	905.9	905.3	904.7
157.5°	931.1	932.4	933.7	933.8	933.0	932.0	931.1	930.2
160°	946.6	947.7	948.9	949.1	948.3	947.5	946.8	946.0
162.5°	960.6	961.9	963.2	963.5	962.5	961.6	960.7	959.8
165°	978.8	980.1	981.5	981.6	980.7	979.7	978.8	977.8
167.5°	993.7	995.1	996.3	996.5	995.6	994.5	993.6	992.6
170°	1001.9	1003.3	1004.6	1004.7	1003.6	1002.5	1001.3	1000.1
172.5°	1008.1	1009.5	1010.8	1010.9	1009.8	1008.7	1007.5	1006.3
175°	1014.9	1016.2	1017.5	1017.6	1016.5	1015.3	1014.2	1013.1
177.5°	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2

(END OF REPORT)