

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332288-927

Luminaire Tested: **S123RDIP-S560D1025U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332288-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5013.4 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32	26
3	79	70	64	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	46	46	42	38	37	33	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	16
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	13
9	49	37	30	25	45	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7629	7629	7629	7629
5°	9095	7662	6748	7662
10°	11355	7618	6096	7618
15°	13329	7540	5558	7540
20°	14875	7424	5102	7424
25°	14638	7301	4822	7301
30°	10521	7188	4533	7188
35°	7025	7041	4346	7041
40°	5176	6864	4154	6864
45°	4341	6555	3962	6555
50°	3831	6149	3699	6149
55°	3359	5684	3337	5684
60°	2990	5240	3057	5240
65°	2626	4760	2845	4760
70°	2061	4337	2596	4337
75°	1817	3785	2371	3785
80°	1581	3217	2331	3217
85°	1272	2581	2470	2581



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.7	1.4
10°-20°	217.8	4.3
20°-30°	342.1	6.8
30°-40°	356.9	7.1
40°-50°	305.5	6.1
50°-60°	232.8	4.6
60°-70°	149.2	3.0
70°-80°	71.8	1.4
80°-90°	22.0	0.4
90°-100°	38.7	0.8
100°-110°	184.4	3.7
110°-120°	443.0	8.8
120°-130°	564.1	11.3
130°-140°	602.7	12.0
140°-150°	563.6	11.2
150°-160°	454.6	9.1
160°-170°	293.4	5.9
170°-180°	101.1	2.0
0°-30°	629.6	12.6
0°-40°	986.5	19.7
0°-60°	1524.8	30.4
0°-90°	1767.7	35.3
90°-120°	666.1	13.3
90°-150°	2396.5	47.8
90°-180°	3246.0	64.7
0°-180°	5013.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	842	709	624	709	842	87
15°	1196	677	499	677	1196	339
25°	1232	615	406	615	1232	530
35°	535	536	331	536	535	351
45°	285	431	260	431	285	224
55°	179	303	178	303	179	162
65°	103	187	112	187	103	101
75°	44	91	57	91	44	47
85°	10	21	20	21	10	12
90°	24	1	24	1	24	11
95°	30	48	30	48	30	25
105°	35	236	35	236	35	79
115°	465	442	465	442	465	430
125°	636	623	636	623	636	568
135°	784	776	784	776	784	604
145°	904	895	904	895	904	564
155°	984	986	984	986	984	454
165°	1037	1040	1037	1040	1037	293
175°	1060	1064	1060	1064	1060	101
180°	1064	1064	1064	1064	1064	



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	754.9	755.9	752.7	752.3	748.6	747.7	747.7	742.5	739.3	735.2	732.8
5°	841.7	846.5	844.1	838.7	829.6	827.4	821.7	812.5	802.2	789.5	783.5
7.5°	950.1	956.7	954.1	945.7	936.2	928.4	912.2	897.1	875.9	857.4	841.5
10°	1038.9	1031.9	1026.5	1018.3	1009.5	995.2	978.3	954.9	927.9	906.7	883.0
12.5°	1105.4	1104.3	1097.3	1088.9	1076.5	1063.0	1042.0	1013.6	982.2	951.5	924.5
15°	1196.1	1197.9	1193.3	1184.6	1167.0	1143.0	1111.4	1099.6	1054.7	1021.3	987.9
17.5°	1258.9	1258.5	1257.8	1245.6	1227.7	1210.6	1181.4	1150.2	1109.6	1062.6	1017.6
20°	1298.6	1295.6	1296.2	1282.5	1269.2	1249.5	1221.0	1175.8	1142.4	1088.1	1041.6
22.5°	1297.7	1297.0	1299.3	1294.7	1285.0	1269.9	1247.4	1209.3	1166.6	1111.8	1059.6
25°	1232.5	1230.1	1244.4	1248.2	1263.8	1266.5	1259.8	1238.9	1198.5	1142.1	1077.4
27.5°	1031.5	1030.2	1056.6	1089.7	1131.8	1164.4	1196.0	1211.2	1198.5	1158.1	1093.4
30°	846.5	875.0	888.4	936.4	989.8	1053.4	1109.3	1162.4	1175.4	1157.9	1104.8
32.5°	702.8	727.7	738.9	780.1	829.8	904.4	988.2	1063.3	1116.5	1130.0	1098.0
35°	534.6	535.0	560.4	578.6	624.7	701.5	782.8	883.5	983.7	1059.5	1067.5
37.5°	426.6	428.1	443.5	461.7	496.3	536.9	608.5	692.2	807.9	924.3	992.6
40°	368.4	371.1	382.6	400.5	425.4	456.1	511.9	590.7	687.2	816.8	922.7
42.5°	331.0	335.4	341.4	355.1	370.5	399.3	444.4	505.3	593.0	715.6	837.7
45°	285.2	287.6	292.2	298.6	312.5	332.6	362.9	403.9	476.7	575.3	697.6
47.5°	251.6	250.3	255.1	260.3	269.6	283.2	303.6	337.0	389.0	468.0	571.8
50°	228.8	228.5	231.8	235.8	244.5	254.6	271.2	296.4	337.7	403.2	498.2
52.5°	207.4	208.6	211.0	215.9	222.2	230.3	245.3	263.4	298.9	355.5	434.6
55°	179.0	179.9	183.2	186.0	190.5	198.8	208.2	223.3	247.6	287.0	352.3
57.5°	155.0	154.6	157.8	158.4	163.6	170.2	177.5	189.3	206.9	236.2	280.2
60°	138.9	138.1	140.8	142.9	145.6	151.1	157.2	168.7	182.7	204.2	241.9
62.5°	124.4	124.0	126.0	128.1	130.3	135.3	140.5	149.2	160.3	178.5	208.3
65°	103.1	104.1	105.0	105.9	107.1	110.1	115.0	121.0	128.7	141.4	163.0
67.5°	81.0	82.0	82.3	84.1	86.7	88.6	91.7	97.0	102.3	113.0	125.3
70°	65.5	65.2	65.5	66.5	69.8	73.1	77.1	81.0	84.4	92.0	102.3
72.5°	56.3	55.8	56.6	56.7	58.4	59.3	61.8	65.5	69.8	74.9	82.4
75°	43.7	43.7	43.7	43.7	44.9	45.6	46.4	47.4	48.9	51.3	56.7
77.5°	32.3	32.3	32.8	33.0	33.4	33.7	34.2	35.2	35.6	37.0	39.3
80°	25.5	25.8	25.5	25.8	25.8	26.4	26.7	27.6	27.9	29.5	30.3
82.5°	19.2	19.0	19.2	19.5	19.5	20.1	20.1	20.8	20.9	21.6	22.6
85°	10.3	9.7	10.3	10.0	10.6	10.0	10.3	10.9	10.9	11.2	12.4
87.5°	7.2	7.6	7.1	7.2	7.1	7.3	7.1	7.0	7.4	7.0	6.7
90°	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4	19.6	19.0	16.7
92.5°	26.2	26.1	25.8	25.6	25.4	24.7	23.6	22.5	21.4	20.3	18.5
95°	30.0	30.0	30.0	30.0	30.0	29.5	28.2	26.9	25.7	24.5	22.6
97.5°	32.6	32.4	32.2	32.1	31.8	31.1	29.7	28.3	26.9	25.4	38.1
100°	33.2	33.0	32.9	32.7	32.5	31.7	30.3	28.9	27.5	26.1	53.5
102.5°	33.8	33.5	33.2	32.9	32.6	34.6	39.0	43.3	47.7	52.0	82.0
105°	34.8	34.5	34.1	33.7	33.4	48.8	79.9	111.0	142.0	173.2	189.0
107.5°	109.2	132.7	156.1	179.6	203.0	226.2	249.0	271.8	294.6	317.4	314.9
110°	217.5	242.6	267.7	292.8	318.0	333.4	339.2	345.0	350.8	356.6	354.7



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.0	378.3	383.7	389.0	394.3	396.9	396.8	396.6	396.6	396.5	394.5
115°	464.9	464.2	463.5	462.8	462.2	460.9	459.1	457.4	455.7	453.8	452.3
117.5°	516.5	516.3	516.2	516.1	515.9	515.2	513.7	512.4	511.0	509.5	508.7
120°	551.9	551.9	551.9	551.9	551.9	551.2	549.8	548.4	547.0	545.6	545.1
122.5°	586.7	586.5	586.5	586.3	586.1	585.6	584.6	583.6	582.7	581.6	581.0
125°	635.7	635.4	635.0	634.7	634.3	634.0	633.6	633.3	633.0	632.6	631.8
127.5°	682.9	683.2	683.6	683.9	684.3	684.1	683.6	683.0	682.5	681.9	681.0
130°	713.2	713.6	713.9	714.3	714.6	714.5	713.8	713.0	712.3	711.6	710.9
132.5°	741.1	741.6	742.0	742.5	743.0	742.9	742.2	741.5	740.8	740.1	739.6
135°	783.6	784.1	784.7	785.2	785.7	785.7	785.2	784.7	784.1	783.6	782.9
137.5°	823.6	823.9	824.3	824.7	825.0	824.7	823.9	823.1	822.2	821.4	821.0
140°	847.6	848.0	848.3	848.7	849.1	848.9	848.2	847.5	846.8	846.1	845.6
142.5°	869.8	870.3	870.8	871.2	871.7	871.7	871.2	870.6	870.1	869.5	868.9
145°	903.8	903.8	903.8	903.8	903.8	903.6	903.2	902.9	902.5	902.2	901.8
147.5°	929.1	929.9	930.7	931.5	932.3	932.6	932.2	931.8	931.5	931.1	930.8
150°	948.1	948.6	949.1	949.7	950.1	950.3	949.9	949.6	949.2	948.9	948.5
152.5°	963.2	964.1	964.9	965.7	966.5	966.5	965.9	965.3	964.6	964.0	963.8
155°	984.4	985.5	986.6	987.6	988.6	988.7	987.9	987.0	986.1	985.2	985.1
157.5°	1002.3	1003.7	1005.0	1006.4	1007.8	1008.0	1006.9	1005.8	1004.8	1003.7	1003.9
160°	1013.7	1014.9	1016.1	1017.4	1018.6	1018.7	1017.6	1016.6	1015.6	1014.5	1014.6
162.5°	1024.5	1025.6	1026.6	1027.7	1028.8	1028.7	1027.5	1026.4	1025.2	1024.0	1024.1
165°	1037.4	1038.6	1039.9	1041.1	1042.4	1042.3	1040.8	1039.4	1038.0	1036.6	1036.8
167.5°	1046.7	1048.1	1049.6	1051.0	1052.3	1052.3	1051.0	1049.6	1048.1	1046.7	1046.7
170°	1052.4	1053.8	1055.3	1056.7	1058.0	1058.0	1056.7	1055.3	1053.8	1052.4	1052.4
172.5°	1055.6	1057.2	1058.7	1060.3	1061.8	1061.8	1060.4	1059.1	1057.6	1056.2	1056.1
175°	1060.3	1061.8	1063.2	1064.5	1066.0	1066.0	1064.9	1063.6	1062.4	1061.1	1061.0
177.5°	1061.8	1063.2	1064.6	1066.0	1067.4	1067.5	1066.4	1065.2	1064.1	1063.0	1062.9
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	731.8	731.1	727.7	723.8	718.7	715.3	712.6	711.2	706.9	701.5	697.8
5°	777.1	767.9	758.3	746.4	735.5	724.3	717.3	709.1	699.1	687.9	679.9
7.5°	825.5	807.6	788.4	768.6	748.9	731.3	715.8	702.5	686.6	670.5	659.2
10°	862.6	836.5	809.5	781.9	756.7	733.1	714.9	697.0	677.9	659.3	645.4
12.5°	896.4	862.1	830.9	796.9	764.8	736.5	710.3	689.2	666.2	646.5	630.6
15°	939.1	903.9	866.3	814.7	771.9	736.1	704.3	676.6	648.7	624.5	609.0
17.5°	979.0	926.1	875.5	832.4	776.9	732.1	693.2	660.2	629.6	603.9	584.8
20°	995.5	944.3	889.3	834.4	779.8	729.8	684.5	648.1	616.2	587.1	569.5
22.5°	1005.4	947.4	889.5	830.5	772.5	720.5	675.8	635.7	601.2	573.5	551.8
25°	1017.1	947.8	884.2	825.9	766.8	710.3	657.2	614.7	577.4	548.0	524.9
27.5°	1024.7	943.3	868.0	803.3	743.2	687.1	638.4	593.3	555.5	524.3	499.6
30°	1026.2	939.7	855.6	785.5	724.5	673.0	621.4	578.3	538.3	505.2	482.1
32.5°	1028.1	930.7	838.9	764.5	702.0	650.9	604.2	563.0	522.0	489.4	465.9
35°	1020.1	925.7	813.5	727.9	665.4	615.9	573.8	535.8	495.5	463.9	440.0
37.5°	985.6	906.0	787.1	686.7	621.4	575.6	541.2	508.2	471.2	437.1	414.5
40°	950.9	886.6	766.8	661.8	593.5	546.4	515.5	488.5	452.7	420.8	396.6
42.5°	899.2	860.2	747.3	635.6	561.9	516.6	490.5	465.2	433.8	401.4	378.6
45°	804.4	809.5	707.6	593.8	518.2	472.7	448.1	430.6	402.7	376.0	352.6
47.5°	685.4	733.6	660.9	549.3	472.2	429.4	408.0	392.6	373.8	347.6	326.3
50°	607.8	676.6	623.5	519.4	443.3	400.8	379.6	367.2	350.8	330.1	309.8
52.5°	536.1	610.1	578.4	486.2	412.0	373.1	352.4	342.1	329.2	309.7	291.4
55°	437.2	512.1	504.9	436.0	365.0	330.1	314.3	302.9	294.0	279.5	264.9
57.5°	353.6	424.7	428.5	380.2	323.6	289.1	275.6	266.9	261.1	250.2	236.7
60°	301.0	366.2	379.0	342.5	294.0	263.6	250.3	243.4	238.8	230.0	219.7
62.5°	257.3	312.8	327.3	301.0	265.6	237.2	226.8	220.1	217.0	209.4	200.3
65°	196.9	243.0	257.0	242.4	223.9	201.1	192.7	186.9	184.2	179.9	173.3
67.5°	148.1	181.7	197.0	186.7	180.1	165.6	160.3	157.2	154.7	151.9	146.2
70°	118.9	143.9	159.6	156.9	151.4	143.9	139.9	137.8	135.3	132.9	128.0
72.5°	95.6	112.7	127.5	129.0	124.5	122.9	119.5	118.6	117.1	114.2	111.5
75°	63.5	75.3	85.6	89.5	91.3	92.8	91.3	91.0	90.7	88.3	86.7
77.5°	41.6	47.9	54.4	61.2	64.0	66.1	66.5	67.7	66.9	65.6	64.9
80°	31.8	33.4	37.9	43.7	48.2	50.1	51.3	51.9	51.6	51.3	50.1
82.5°	23.1	24.4	26.5	30.6	34.4	37.5	38.2	38.0	38.7	38.9	37.9
85°	12.4	12.8	13.4	13.9	16.1	19.4	20.4	20.9	21.5	21.5	19.7
87.5°	6.7	6.1	6.1	5.7	6.1	5.9	7.1	7.9	8.6	7.9	8.2
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	16.8	15.1	13.4	12.8	13.2	13.7	14.2	14.7	14.2	13.7	13.2
95°	20.7	18.7	16.8	19.4	26.6	33.8	41.0	48.2	41.0	33.8	26.6
97.5°	50.8	63.5	76.0	84.0	87.2	90.5	93.7	97.0	93.7	90.5	87.2
100°	80.9	108.3	135.7	147.7	144.2	140.7	137.1	133.6	137.1	140.7	144.2
102.5°	111.9	141.9	171.8	185.5	183.0	180.5	177.9	175.4	177.9	180.5	183.0
105°	204.8	220.6	236.4	243.4	241.5	239.5	237.6	235.6	237.6	239.5	241.5
107.5°	312.4	309.9	307.4	305.4	303.9	302.3	300.8	299.2	300.8	302.3	303.9
110°	352.8	350.8	348.9	347.2	345.8	344.4	343.0	341.6	343.0	344.4	345.8



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.6	390.7	388.7	387.1	385.9	384.6	383.3	382.1	383.3	384.6	385.9
115°	450.7	449.1	447.6	446.2	445.2	444.1	443.1	442.0	443.1	444.1	445.2
117.5°	507.9	507.1	506.3	505.3	504.0	502.6	501.4	500.0	501.4	502.6	504.0
120°	544.5	544.0	543.5	542.4	540.8	539.2	537.7	536.1	537.7	539.2	540.8
122.5°	580.4	579.6	579.0	578.0	576.7	575.4	574.1	572.8	574.1	575.4	576.7
125°	631.1	630.5	629.8	628.7	627.3	625.9	624.5	623.1	624.5	625.9	627.3
127.5°	680.2	679.4	678.5	677.4	676.0	674.6	673.2	671.8	673.2	674.6	676.0
130°	710.3	709.6	708.8	707.8	706.4	705.0	703.5	702.2	703.5	705.0	706.4
132.5°	738.9	738.4	737.8	736.9	735.5	734.0	732.7	731.3	732.7	734.0	735.5
135°	782.2	781.5	780.8	779.9	778.9	777.8	776.7	775.7	776.7	777.8	778.9
137.5°	820.6	820.2	819.8	819.0	817.7	816.3	815.0	813.7	815.0	816.3	817.7
140°	845.0	844.5	844.0	843.2	842.1	841.1	840.0	838.9	840.0	841.1	842.1
142.5°	868.4	867.9	867.4	866.6	865.5	864.4	863.4	862.4	863.4	864.4	865.5
145°	901.5	901.2	900.8	900.0	898.8	897.5	896.4	895.1	896.4	897.5	898.8
147.5°	930.4	930.1	929.7	929.2	928.4	927.6	926.8	925.9	926.8	927.6	928.4
150°	948.2	947.8	947.5	947.0	946.5	945.9	945.5	944.9	945.5	945.9	946.5
152.5°	963.6	963.4	963.2	963.0	962.7	962.5	962.3	961.9	962.3	962.5	962.7
155°	984.8	984.7	984.5	984.6	985.0	985.3	985.6	986.0	985.6	985.3	985.0
157.5°	1004.1	1004.2	1004.4	1004.6	1004.6	1004.6	1004.6	1004.6	1004.6	1004.6	1004.6
160°	1014.9	1015.0	1015.2	1015.3	1015.6	1015.7	1015.9	1016.1	1015.9	1015.7	1015.6
162.5°	1024.3	1024.5	1024.7	1025.0	1025.5	1025.9	1026.4	1026.8	1026.4	1025.9	1025.5
165°	1037.0	1037.1	1037.4	1037.7	1038.2	1038.7	1039.3	1039.8	1039.3	1038.7	1038.2
167.5°	1046.7	1046.7	1046.7	1047.1	1047.8	1048.5	1049.2	1049.9	1049.2	1048.5	1047.8
170°	1052.4	1052.4	1052.4	1052.8	1053.5	1054.2	1054.9	1055.6	1054.9	1054.2	1053.5
172.5°	1056.0	1055.8	1055.7	1056.1	1056.9	1057.7	1058.6	1059.4	1058.6	1057.7	1056.9
175°	1060.8	1060.6	1060.4	1060.8	1061.7	1062.6	1063.4	1064.3	1063.4	1062.6	1061.7
177.5°	1062.8	1062.6	1062.5	1062.8	1063.4	1064.1	1064.9	1065.6	1064.9	1064.1	1063.4
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	696.6	693.5	691.3	686.4	683.3	679.9	676.5	678.7	678.4	678.2	678.2
5°	673.3	666.3	660.0	651.7	646.6	640.2	635.3	634.8	636.0	631.7	629.3
7.5°	650.1	640.6	631.5	622.5	612.9	605.2	600.5	598.3	595.2	592.6	589.8
10°	633.8	622.7	613.8	602.6	592.3	583.2	577.4	573.5	571.3	569.2	565.3
12.5°	617.1	606.1	594.8	582.2	572.4	561.8	557.5	553.1	549.0	546.6	541.2
15°	592.6	578.3	566.5	553.1	542.2	531.9	525.9	517.1	515.8	512.8	507.3
17.5°	568.0	552.5	536.2	526.3	514.0	503.3	494.0	491.1	482.4	479.1	474.4
20°	548.6	534.3	521.9	508.8	490.9	480.9	473.6	469.7	462.7	458.4	455.4
22.5°	531.9	517.3	503.0	487.7	472.9	461.8	456.4	450.3	446.5	440.5	437.2
25°	507.9	492.2	474.8	458.4	447.8	439.3	430.9	425.4	419.9	417.2	411.1
27.5°	480.1	463.7	447.5	435.1	422.0	413.6	405.9	401.1	394.5	389.9	386.6
30°	464.9	445.4	431.5	420.3	403.5	395.7	389.9	383.8	379.0	374.1	370.7
32.5°	447.1	429.4	416.1	402.3	389.4	380.9	373.4	368.0	363.9	359.3	356.0
35°	419.3	404.5	390.8	376.8	367.4	358.6	349.8	345.3	341.4	337.1	334.1
37.5°	394.2	380.3	367.3	354.1	342.5	335.3	328.2	324.7	319.4	316.6	313.5
40°	378.7	365.0	351.1	338.3	326.1	320.8	314.3	309.2	304.4	302.2	298.9
42.5°	361.7	348.0	336.3	322.5	312.6	305.1	299.3	293.7	290.0	286.9	285.0
45°	336.5	324.3	312.8	299.2	289.8	283.4	276.7	271.6	268.2	266.1	262.8
47.5°	312.0	299.9	288.2	276.3	267.2	259.9	253.3	249.6	245.3	242.6	240.3
50°	294.3	283.4	270.9	260.0	251.0	243.7	238.2	233.6	229.7	226.3	224.8
52.5°	278.1	266.4	255.6	245.5	235.9	227.6	222.7	217.9	214.9	211.0	209.3
55°	251.2	240.0	230.9	220.9	211.5	204.5	198.4	194.2	191.2	186.9	184.5
57.5°	226.0	215.9	205.1	196.5	186.7	180.9	175.8	170.0	166.4	163.0	160.7
60°	209.1	197.5	188.1	179.9	171.4	163.8	159.3	154.7	150.8	147.4	145.4
62.5°	191.3	181.3	172.4	163.4	155.7	149.0	143.8	139.9	136.5	134.4	132.2
65°	164.1	156.3	147.2	139.9	132.6	127.8	123.5	120.2	117.7	116.2	114.4
67.5°	139.2	131.5	123.6	116.4	111.5	107.8	105.0	102.2	101.0	99.0	97.8
70°	122.9	115.0	108.1	102.6	97.7	95.0	93.2	91.0	89.8	87.4	86.2
72.5°	105.2	99.5	94.4	89.9	86.0	83.6	81.3	78.7	76.7	74.1	72.8
75°	82.9	77.7	73.8	70.7	68.3	65.0	61.6	58.9	58.0	57.0	56.7
77.5°	61.3	58.1	55.2	52.7	49.7	47.2	46.5	45.9	45.7	45.2	45.2
80°	48.2	45.2	43.1	40.1	38.3	38.3	38.3	37.6	37.9	37.9	37.9
82.5°	35.9	33.0	31.9	30.8	30.5	30.7	30.7	30.8	30.7	31.1	30.9
85°	18.5	18.8	19.4	19.1	19.4	19.4	20.0	19.7	20.0	19.4	20.0
87.5°	8.4	9.5	10.2	10.9	11.6	11.8	12.2	12.4	12.7	12.8	13.0
90°	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4	21.1	21.8	22.3
92.5°	12.8	13.4	15.1	16.8	18.5	20.3	21.4	22.5	23.6	24.7	25.4
95°	19.4	16.8	18.7	20.7	22.6	24.5	25.7	26.9	28.2	29.5	30.0
97.5°	84.0	76.0	63.5	50.8	38.1	25.4	26.9	28.3	29.7	31.1	31.8
100°	147.7	135.7	108.3	80.9	53.5	26.1	27.5	28.9	30.3	31.7	32.5
102.5°	185.5	171.8	141.9	111.9	82.0	52.0	47.7	43.3	39.0	34.6	32.6
105°	243.4	236.4	220.6	204.8	189.0	173.2	142.0	111.0	79.9	48.8	33.4
107.5°	305.4	307.4	309.9	312.4	314.9	317.4	294.6	271.8	249.0	226.2	203.0
110°	347.2	348.9	350.8	352.8	354.7	356.6	350.8	345.0	339.2	333.4	318.0



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	387.1	388.7	390.7	392.6	394.5	396.5	396.6	396.6	396.8	396.9	394.3
115°	446.2	447.6	449.1	450.7	452.3	453.8	455.7	457.4	459.1	460.9	462.2
117.5°	505.3	506.3	507.1	507.9	508.7	509.5	511.0	512.4	513.7	515.2	515.9
120°	542.4	543.5	544.0	544.5	545.1	545.6	547.0	548.4	549.8	551.2	551.9
122.5°	578.0	579.0	579.6	580.4	581.0	581.6	582.7	583.6	584.6	585.6	586.1
125°	628.7	629.8	630.5	631.1	631.8	632.6	633.0	633.3	633.6	634.0	634.3
127.5°	677.4	678.5	679.4	680.2	681.0	681.9	682.5	683.0	683.6	684.1	684.3
130°	707.8	708.8	709.6	710.3	710.9	711.6	712.3	713.0	713.8	714.5	714.6
132.5°	736.9	737.8	738.4	738.9	739.6	740.1	740.8	741.5	742.2	742.9	743.0
135°	779.9	780.8	781.5	782.2	782.9	783.6	784.1	784.7	785.2	785.7	785.7
137.5°	819.0	819.8	820.2	820.6	821.0	821.4	822.2	823.1	823.9	824.7	825.0
140°	843.2	844.0	844.5	845.0	845.6	846.1	846.8	847.5	848.2	848.9	849.1
142.5°	866.6	867.4	867.9	868.4	868.9	869.5	870.1	870.6	871.2	871.7	871.7
145°	900.0	900.8	901.2	901.5	901.8	902.2	902.5	902.9	903.2	903.6	903.8
147.5°	929.2	929.7	930.1	930.4	930.8	931.1	931.5	931.8	932.2	932.6	932.3
150°	947.0	947.5	947.8	948.2	948.5	948.9	949.2	949.6	949.9	950.3	950.1
152.5°	963.0	963.2	963.4	963.6	963.8	964.0	964.6	965.3	965.9	966.5	966.5
155°	984.6	984.5	984.7	984.8	985.1	985.2	986.1	987.0	987.9	988.7	988.6
157.5°	1004.6	1004.4	1004.2	1004.1	1003.9	1003.7	1004.8	1005.8	1006.9	1008.0	1007.8
160°	1015.3	1015.2	1015.0	1014.9	1014.6	1014.5	1015.6	1016.6	1017.6	1018.7	1018.6
162.5°	1025.0	1024.7	1024.5	1024.3	1024.1	1024.0	1025.2	1026.4	1027.5	1028.7	1028.8
165°	1037.7	1037.4	1037.1	1037.0	1036.8	1036.6	1038.0	1039.4	1040.8	1042.3	1042.4
167.5°	1047.1	1046.7	1046.7	1046.7	1046.7	1046.7	1048.1	1049.6	1051.0	1052.3	1052.3
170°	1052.8	1052.4	1052.4	1052.4	1052.4	1052.4	1053.8	1055.3	1056.7	1058.0	1058.0
172.5°	1056.1	1055.7	1055.8	1056.0	1056.1	1056.2	1057.6	1059.1	1060.4	1061.8	1061.8
175°	1060.8	1060.4	1060.6	1060.8	1061.0	1061.1	1062.4	1063.6	1064.9	1066.0	1066.0
177.5°	1062.8	1062.5	1062.6	1062.8	1062.9	1063.0	1064.1	1065.2	1066.4	1067.5	1067.4
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	675.3	675.0	675.3	674.3	675.3	675.0	675.3	678.2	678.2	678.4	678.7
5°	628.4	628.0	627.2	624.5	627.2	628.0	628.4	629.3	631.7	636.0	634.8
7.5°	587.4	587.0	584.3	584.4	584.3	587.0	587.4	589.8	592.6	595.2	598.3
10°	563.2	563.5	559.8	557.7	559.8	563.5	563.2	565.3	569.2	571.3	573.5
12.5°	539.6	538.2	535.3	532.9	535.3	538.2	539.6	541.2	546.6	549.0	553.1
15°	508.5	505.5	498.2	498.8	498.2	505.5	508.5	507.3	512.8	515.8	517.1
17.5°	471.9	469.7	469.6	465.3	469.6	469.7	471.9	474.4	479.1	482.4	491.1
20°	450.6	449.1	449.6	445.4	449.6	449.1	450.6	455.4	458.4	462.7	469.7
22.5°	433.8	432.3	429.8	428.4	429.8	432.3	433.8	437.2	440.5	446.5	450.3
25°	409.3	406.9	404.5	406.0	404.5	406.9	409.3	411.1	417.2	419.9	425.4
27.5°	384.8	382.9	380.6	380.2	380.6	382.9	384.8	386.6	389.9	394.5	401.1
30°	369.2	367.4	366.2	364.7	366.2	367.4	369.2	370.7	374.1	379.0	383.8
32.5°	353.5	353.2	350.9	350.6	350.9	353.2	353.5	356.0	359.3	363.9	368.0
35°	332.9	331.1	330.4	330.7	330.4	331.1	332.9	334.1	337.1	341.4	345.3
37.5°	313.2	310.9	309.7	308.6	309.7	310.9	313.2	313.5	316.6	319.4	324.7
40°	299.2	296.8	296.1	295.6	296.1	296.8	299.2	298.9	302.2	304.4	309.2
42.5°	283.4	282.4	282.1	281.0	282.1	282.4	283.4	285.0	286.9	290.0	293.7
45°	261.8	261.6	259.8	260.3	259.8	261.6	261.8	262.8	266.1	268.2	271.6
47.5°	239.2	237.8	236.5	237.4	236.5	237.8	239.2	240.3	242.6	245.3	249.6
50°	223.6	223.0	220.3	220.9	220.3	223.0	223.6	224.8	226.3	229.7	233.6
52.5°	208.1	205.8	204.8	204.4	204.8	205.8	208.1	209.3	211.0	214.9	217.9
55°	182.4	179.6	178.4	177.8	178.4	179.6	182.4	184.5	186.9	191.2	194.2
57.5°	157.1	156.4	155.4	156.1	155.4	156.4	157.1	160.7	163.0	166.4	170.0
60°	142.3	142.3	142.3	142.0	142.3	142.3	142.3	145.4	147.4	150.8	154.7
62.5°	130.9	130.2	129.9	130.3	129.9	130.2	130.9	132.2	134.4	136.5	139.9
65°	113.4	113.2	111.9	111.7	111.9	113.2	113.4	114.4	116.2	117.7	120.2
67.5°	97.0	95.9	95.6	95.1	95.6	95.9	97.0	97.8	99.0	101.0	102.2
70°	84.7	84.1	82.2	82.5	82.2	84.1	84.7	86.2	87.4	89.8	91.0
72.5°	71.3	70.7	70.3	69.9	70.3	70.7	71.3	72.8	74.1	76.7	78.7
75°	56.4	56.2	55.8	57.0	55.8	56.2	56.4	56.7	57.0	58.0	58.9
77.5°	45.2	45.2	45.4	44.9	45.4	45.2	45.2	45.2	45.2	45.7	45.9
80°	37.9	37.9	37.6	37.6	37.6	37.9	37.9	37.9	37.9	37.9	37.6
82.5°	30.4	30.7	30.8	30.3	30.8	30.7	30.4	30.9	31.1	30.7	30.8
85°	20.0	19.7	20.4	20.0	20.4	19.7	20.0	20.0	19.4	20.0	19.7
87.5°	13.5	13.1	13.2	13.5	13.2	13.1	13.5	13.0	12.8	12.7	12.4
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4
92.5°	25.6	25.8	26.1	26.2	26.1	25.8	25.6	25.4	24.7	23.6	22.5
95°	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	29.5	28.2	26.9
97.5°	32.1	32.2	32.4	32.6	32.4	32.2	32.1	31.8	31.1	29.7	28.3
100°	32.7	32.9	33.0	33.2	33.0	32.9	32.7	32.5	31.7	30.3	28.9
102.5°	32.9	33.2	33.5	33.8	33.5	33.2	32.9	32.6	34.6	39.0	43.3
105°	33.7	34.1	34.5	34.8	34.5	34.1	33.7	33.4	48.8	79.9	111.0
107.5°	179.6	156.1	132.7	109.2	132.7	156.1	179.6	203.0	226.2	249.0	271.8
110°	292.8	267.7	242.6	217.5	242.6	267.7	292.8	318.0	333.4	339.2	345.0



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	389.0	383.7	378.3	373.0	378.3	383.7	389.0	394.3	396.9	396.8	396.6
115°	462.8	463.5	464.2	464.9	464.2	463.5	462.8	462.2	460.9	459.1	457.4
117.5°	516.1	516.2	516.3	516.5	516.3	516.2	516.1	515.9	515.2	513.7	512.4
120°	551.9	551.9	551.9	551.9	551.9	551.9	551.9	551.9	551.2	549.8	548.4
122.5°	586.3	586.5	586.5	586.7	586.5	586.5	586.3	586.1	585.6	584.6	583.6
125°	634.7	635.0	635.4	635.7	635.4	635.0	634.7	634.3	634.0	633.6	633.3
127.5°	683.9	683.6	683.2	682.9	683.2	683.6	683.9	684.3	684.1	683.6	683.0
130°	714.3	713.9	713.6	713.2	713.6	713.9	714.3	714.6	714.5	713.8	713.0
132.5°	742.5	742.0	741.6	741.1	741.6	742.0	742.5	743.0	742.9	742.2	741.5
135°	785.2	784.7	784.1	783.6	784.1	784.7	785.2	785.7	785.7	785.2	784.7
137.5°	824.7	824.3	823.9	823.6	823.9	824.3	824.7	825.0	824.7	823.9	823.1
140°	848.7	848.3	848.0	847.6	848.0	848.3	848.7	849.1	848.9	848.2	847.5
142.5°	871.2	870.8	870.3	869.8	870.3	870.8	871.2	871.7	871.7	871.2	870.6
145°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.6	903.2	902.9
147.5°	931.5	930.7	929.9	929.1	929.9	930.7	931.5	932.3	932.6	932.2	931.8
150°	949.7	949.1	948.6	948.1	948.6	949.1	949.7	950.1	950.3	949.9	949.6
152.5°	965.7	964.9	964.1	963.2	964.1	964.9	965.7	966.5	966.5	965.9	965.3
155°	987.6	986.6	985.5	984.4	985.5	986.6	987.6	988.6	988.7	987.9	987.0
157.5°	1006.4	1005.0	1003.7	1002.3	1003.7	1005.0	1006.4	1007.8	1008.0	1006.9	1005.8
160°	1017.4	1016.1	1014.9	1013.7	1014.9	1016.1	1017.4	1018.6	1018.7	1017.6	1016.6
162.5°	1027.7	1026.6	1025.6	1024.5	1025.6	1026.6	1027.7	1028.8	1028.7	1027.5	1026.4
165°	1041.1	1039.9	1038.6	1037.4	1038.6	1039.9	1041.1	1042.4	1042.3	1040.8	1039.4
167.5°	1051.0	1049.6	1048.1	1046.7	1048.1	1049.6	1051.0	1052.3	1052.3	1051.0	1049.6
170°	1056.7	1055.3	1053.8	1052.4	1053.8	1055.3	1056.7	1058.0	1058.0	1056.7	1055.3
172.5°	1060.3	1058.7	1057.2	1055.6	1057.2	1058.7	1060.3	1061.8	1061.8	1060.4	1059.1
175°	1064.5	1063.2	1061.8	1060.3	1061.8	1063.2	1064.5	1066.0	1066.0	1064.9	1063.6
177.5°	1066.0	1064.6	1063.2	1061.8	1063.2	1064.6	1066.0	1067.4	1067.5	1066.4	1065.2
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	676.5	679.9	683.3	686.4	691.3	693.5	696.6	697.8	701.5	706.9	711.2
5°	635.3	640.2	646.6	651.7	660.0	666.3	673.3	679.9	687.9	699.1	709.1
7.5°	600.5	605.2	612.9	622.5	631.5	640.6	650.1	659.2	670.5	686.6	702.5
10°	577.4	583.2	592.3	602.6	613.8	622.7	633.8	645.4	659.3	677.9	697.0
12.5°	557.5	561.8	572.4	582.2	594.8	606.1	617.1	630.6	646.5	666.2	689.2
15°	525.9	531.9	542.2	553.1	566.5	578.3	592.6	609.0	624.5	648.7	676.6
17.5°	494.0	503.3	514.0	526.3	536.2	552.5	568.0	584.8	603.9	629.6	660.2
20°	473.6	480.9	490.9	508.8	521.9	534.3	548.6	569.5	587.1	616.2	648.1
22.5°	456.4	461.8	472.9	487.7	503.0	517.3	531.9	551.8	573.5	601.2	635.7
25°	430.9	439.3	447.8	458.4	474.8	492.2	507.9	524.9	548.0	577.4	614.7
27.5°	405.9	413.6	422.0	435.1	447.5	463.7	480.1	499.6	524.3	555.5	593.3
30°	389.9	395.7	403.5	420.3	431.5	445.4	464.9	482.1	505.2	538.3	578.3
32.5°	373.4	380.9	389.4	402.3	416.1	429.4	447.1	465.9	489.4	522.0	563.0
35°	349.8	358.6	367.4	376.8	390.8	404.5	419.3	440.0	463.9	495.5	535.8
37.5°	328.2	335.3	342.5	354.1	367.3	380.3	394.2	414.5	437.1	471.2	508.2
40°	314.3	320.8	326.1	338.3	351.1	365.0	378.7	396.6	420.8	452.7	488.5
42.5°	299.3	305.1	312.6	322.5	336.3	348.0	361.7	378.6	401.4	433.8	465.2
45°	276.7	283.4	289.8	299.2	312.8	324.3	336.5	352.6	376.0	402.7	430.6
47.5°	253.3	259.9	267.2	276.3	288.2	299.9	312.0	326.3	347.6	373.8	392.6
50°	238.2	243.7	251.0	260.0	270.9	283.4	294.3	309.8	330.1	350.8	367.2
52.5°	222.7	227.6	235.9	245.5	255.6	266.4	278.1	291.4	309.7	329.2	342.1
55°	198.4	204.5	211.5	220.9	230.9	240.0	251.2	264.9	279.5	294.0	302.9
57.5°	175.8	180.9	186.7	196.5	205.1	215.9	226.0	236.7	250.2	261.1	266.9
60°	159.3	163.8	171.4	179.9	188.1	197.5	209.1	219.7	230.0	238.8	243.4
62.5°	143.8	149.0	155.7	163.4	172.4	181.3	191.3	200.3	209.4	217.0	220.1
65°	123.5	127.8	132.6	139.9	147.2	156.3	164.1	173.3	179.9	184.2	186.9
67.5°	105.0	107.8	111.5	116.4	123.6	131.5	139.2	146.2	151.9	154.7	157.2
70°	93.2	95.0	97.7	102.6	108.1	115.0	122.9	128.0	132.9	135.3	137.8
72.5°	81.3	83.6	86.0	89.9	94.4	99.5	105.2	111.5	114.2	117.1	118.6
75°	61.6	65.0	68.3	70.7	73.8	77.7	82.9	86.7	88.3	90.7	91.0
77.5°	46.5	47.2	49.7	52.7	55.2	58.1	61.3	64.9	65.6	66.9	67.7
80°	38.3	38.3	38.3	40.1	43.1	45.2	48.2	50.1	51.3	51.6	51.9
82.5°	30.7	30.7	30.5	30.8	31.9	33.0	35.9	37.9	38.9	38.7	38.0
85°	20.0	19.4	19.4	19.1	19.4	18.8	18.5	19.7	21.5	21.5	20.9
87.5°	12.2	11.8	11.6	10.9	10.2	9.5	8.4	8.2	7.9	8.6	7.9
90°	19.6	19.0	16.7	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	21.4	20.3	18.5	16.8	15.1	13.4	12.8	13.2	13.7	14.2	14.7
95°	25.7	24.5	22.6	20.7	18.7	16.8	19.4	26.6	33.8	41.0	48.2
97.5°	26.9	25.4	38.1	50.8	63.5	76.0	84.0	87.2	90.5	93.7	97.0
100°	27.5	26.1	53.5	80.9	108.3	135.7	147.7	144.2	140.7	137.1	133.6
102.5°	47.7	52.0	82.0	111.9	141.9	171.8	185.5	183.0	180.5	177.9	175.4
105°	142.0	173.2	189.0	204.8	220.6	236.4	243.4	241.5	239.5	237.6	235.6
107.5°	294.6	317.4	314.9	312.4	309.9	307.4	305.4	303.9	302.3	300.8	299.2
110°	350.8	356.6	354.7	352.8	350.8	348.9	347.2	345.8	344.4	343.0	341.6



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	396.6	396.5	394.5	392.6	390.7	388.7	387.1	385.9	384.6	383.3	382.1
115°	455.7	453.8	452.3	450.7	449.1	447.6	446.2	445.2	444.1	443.1	442.0
117.5°	511.0	509.5	508.7	507.9	507.1	506.3	505.3	504.0	502.6	501.4	500.0
120°	547.0	545.6	545.1	544.5	544.0	543.5	542.4	540.8	539.2	537.7	536.1
122.5°	582.7	581.6	581.0	580.4	579.6	579.0	578.0	576.7	575.4	574.1	572.8
125°	633.0	632.6	631.8	631.1	630.5	629.8	628.7	627.3	625.9	624.5	623.1
127.5°	682.5	681.9	681.0	680.2	679.4	678.5	677.4	676.0	674.6	673.2	671.8
130°	712.3	711.6	710.9	710.3	709.6	708.8	707.8	706.4	705.0	703.5	702.2
132.5°	740.8	740.1	739.6	738.9	738.4	737.8	736.9	735.5	734.0	732.7	731.3
135°	784.1	783.6	782.9	782.2	781.5	780.8	779.9	778.9	777.8	776.7	775.7
137.5°	822.2	821.4	821.0	820.6	820.2	819.8	819.0	817.7	816.3	815.0	813.7
140°	846.8	846.1	845.6	845.0	844.5	844.0	843.2	842.1	841.1	840.0	838.9
142.5°	870.1	869.5	868.9	868.4	867.9	867.4	866.6	865.5	864.4	863.4	862.4
145°	902.5	902.2	901.8	901.5	901.2	900.8	900.0	898.8	897.5	896.4	895.1
147.5°	931.5	931.1	930.8	930.4	930.1	929.7	929.2	928.4	927.6	926.8	925.9
150°	949.2	948.9	948.5	948.2	947.8	947.5	947.0	946.5	945.9	945.5	944.9
152.5°	964.6	964.0	963.8	963.6	963.4	963.2	963.0	962.7	962.5	962.3	961.9
155°	986.1	985.2	985.1	984.8	984.7	984.5	984.6	985.0	985.3	985.6	986.0
157.5°	1004.8	1003.7	1003.9	1004.1	1004.2	1004.4	1004.6	1004.6	1004.6	1004.6	1004.6
160°	1015.6	1014.5	1014.6	1014.9	1015.0	1015.2	1015.3	1015.6	1015.7	1015.9	1016.1
162.5°	1025.2	1024.0	1024.1	1024.3	1024.5	1024.7	1025.0	1025.5	1025.9	1026.4	1026.8
165°	1038.0	1036.6	1036.8	1037.0	1037.1	1037.4	1037.7	1038.2	1038.7	1039.3	1039.8
167.5°	1048.1	1046.7	1046.7	1046.7	1046.7	1046.7	1047.1	1047.8	1048.5	1049.2	1049.9
170°	1053.8	1052.4	1052.4	1052.4	1052.4	1052.4	1052.8	1053.5	1054.2	1054.9	1055.6
172.5°	1057.6	1056.2	1056.1	1056.0	1055.8	1055.7	1056.1	1056.9	1057.7	1058.6	1059.4
175°	1062.4	1061.1	1061.0	1060.8	1060.6	1060.4	1060.8	1061.7	1062.6	1063.4	1064.3
177.5°	1064.1	1063.0	1062.9	1062.8	1062.6	1062.5	1062.8	1063.4	1064.1	1064.9	1065.6
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	712.6	715.3	718.7	723.8	727.7	731.1	731.8	732.8	735.2	739.3	742.5
5°	717.3	724.3	735.5	746.4	758.3	767.9	777.1	783.5	789.5	802.2	812.5
7.5°	715.8	731.3	748.9	768.6	788.4	807.6	825.5	841.5	857.4	875.9	897.1
10°	714.9	733.1	756.7	781.9	809.5	836.5	862.6	883.0	906.7	927.9	954.9
12.5°	710.3	736.5	764.8	796.9	830.9	862.1	896.4	924.5	951.5	982.2	1013.6
15°	704.3	736.1	771.9	814.7	866.3	903.9	939.1	987.9	1021.3	1054.7	1099.6
17.5°	693.2	732.1	776.9	832.4	875.5	926.1	979.0	1017.6	1062.6	1109.6	1150.2
20°	684.5	729.8	779.8	834.4	889.3	944.3	995.5	1041.6	1088.1	1142.4	1175.8
22.5°	675.8	720.5	772.5	830.5	889.5	947.4	1005.4	1059.6	1111.8	1166.6	1209.3
25°	657.2	710.3	766.8	825.9	884.2	947.8	1017.1	1077.4	1142.1	1198.5	1238.9
27.5°	638.4	687.1	743.2	803.3	868.0	943.3	1024.7	1093.4	1158.1	1198.5	1211.2
30°	621.4	673.0	724.5	785.5	855.6	939.7	1026.2	1104.8	1157.9	1175.4	1162.4
32.5°	604.2	650.9	702.0	764.5	838.9	930.7	1028.1	1098.0	1130.0	1116.5	1063.3
35°	573.8	615.9	665.4	727.9	813.5	925.7	1020.1	1067.5	1059.5	983.7	883.5
37.5°	541.2	575.6	621.4	686.7	787.1	906.0	985.6	992.6	924.3	807.9	692.2
40°	515.5	546.4	593.5	661.8	766.8	886.6	950.9	922.7	816.8	687.2	590.7
42.5°	490.5	516.6	561.9	635.6	747.3	860.2	899.2	837.7	715.6	593.0	505.3
45°	448.1	472.7	518.2	593.8	707.6	809.5	804.4	697.6	575.3	476.7	403.9
47.5°	408.0	429.4	472.2	549.3	660.9	733.6	685.4	571.8	468.0	389.0	337.0
50°	379.6	400.8	443.3	519.4	623.5	676.6	607.8	498.2	403.2	337.7	296.4
52.5°	352.4	373.1	412.0	486.2	578.4	610.1	536.1	434.6	355.5	298.9	263.4
55°	314.3	330.1	365.0	436.0	504.9	512.1	437.2	352.3	287.0	247.6	223.3
57.5°	275.6	289.1	323.6	380.2	428.5	424.7	353.6	280.2	236.2	206.9	189.3
60°	250.3	263.6	294.0	342.5	379.0	366.2	301.0	241.9	204.2	182.7	168.7
62.5°	226.8	237.2	265.6	301.0	327.3	312.8	257.3	208.3	178.5	160.3	149.2
65°	192.7	201.1	223.9	242.4	257.0	243.0	196.9	163.0	141.4	128.7	121.0
67.5°	160.3	165.6	180.1	186.7	197.0	181.7	148.1	125.3	113.0	102.3	97.0
70°	139.9	143.9	151.4	156.9	159.6	143.9	118.9	102.3	92.0	84.4	81.0
72.5°	119.5	122.9	124.5	129.0	127.5	112.7	95.6	82.4	74.9	69.8	65.5
75°	91.3	92.8	91.3	89.5	85.6	75.3	63.5	56.7	51.3	48.9	47.4
77.5°	66.5	66.1	64.0	61.2	54.4	47.9	41.6	39.3	37.0	35.6	35.2
80°	51.3	50.1	48.2	43.7	37.9	33.4	31.8	30.3	29.5	27.9	27.6
82.5°	38.2	37.5	34.4	30.6	26.5	24.4	23.1	22.6	21.6	20.9	20.8
85°	20.4	19.4	16.1	13.9	13.4	12.8	12.4	12.4	11.2	10.9	10.9
87.5°	7.1	5.9	6.1	5.7	6.1	6.1	6.7	6.7	7.0	7.4	7.0
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4
92.5°	14.2	13.7	13.2	12.8	13.4	15.1	16.8	18.5	20.3	21.4	22.5
95°	41.0	33.8	26.6	19.4	16.8	18.7	20.7	22.6	24.5	25.7	26.9
97.5°	93.7	90.5	87.2	84.0	76.0	63.5	50.8	38.1	25.4	26.9	28.3
100°	137.1	140.7	144.2	147.7	135.7	108.3	80.9	53.5	26.1	27.5	28.9
102.5°	177.9	180.5	183.0	185.5	171.8	141.9	111.9	82.0	52.0	47.7	43.3
105°	237.6	239.5	241.5	243.4	236.4	220.6	204.8	189.0	173.2	142.0	111.0
107.5°	300.8	302.3	303.9	305.4	307.4	309.9	312.4	314.9	317.4	294.6	271.8
110°	343.0	344.4	345.8	347.2	348.9	350.8	352.8	354.7	356.6	350.8	345.0



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.3	384.6	385.9	387.1	388.7	390.7	392.6	394.5	396.5	396.6	396.6
115°	443.1	444.1	445.2	446.2	447.6	449.1	450.7	452.3	453.8	455.7	457.4
117.5°	501.4	502.6	504.0	505.3	506.3	507.1	507.9	508.7	509.5	511.0	512.4
120°	537.7	539.2	540.8	542.4	543.5	544.0	544.5	545.1	545.6	547.0	548.4
122.5°	574.1	575.4	576.7	578.0	579.0	579.6	580.4	581.0	581.6	582.7	583.6
125°	624.5	625.9	627.3	628.7	629.8	630.5	631.1	631.8	632.6	633.0	633.3
127.5°	673.2	674.6	676.0	677.4	678.5	679.4	680.2	681.0	681.9	682.5	683.0
130°	703.5	705.0	706.4	707.8	708.8	709.6	710.3	710.9	711.6	712.3	713.0
132.5°	732.7	734.0	735.5	736.9	737.8	738.4	738.9	739.6	740.1	740.8	741.5
135°	776.7	777.8	778.9	779.9	780.8	781.5	782.2	782.9	783.6	784.1	784.7
137.5°	815.0	816.3	817.7	819.0	819.8	820.2	820.6	821.0	821.4	822.2	823.1
140°	840.0	841.1	842.1	843.2	844.0	844.5	845.0	845.6	846.1	846.8	847.5
142.5°	863.4	864.4	865.5	866.6	867.4	867.9	868.4	868.9	869.5	870.1	870.6
145°	896.4	897.5	898.8	900.0	900.8	901.2	901.5	901.8	902.2	902.5	902.9
147.5°	926.8	927.6	928.4	929.2	929.7	930.1	930.4	930.8	931.1	931.5	931.8
150°	945.5	945.9	946.5	947.0	947.5	947.8	948.2	948.5	948.9	949.2	949.6
152.5°	962.3	962.5	962.7	963.0	963.2	963.4	963.6	963.8	964.0	964.6	965.3
155°	985.6	985.3	985.0	984.6	984.5	984.7	984.8	985.1	985.2	986.1	987.0
157.5°	1004.6	1004.6	1004.6	1004.6	1004.4	1004.2	1004.1	1003.9	1003.7	1004.8	1005.8
160°	1015.9	1015.7	1015.6	1015.3	1015.2	1015.0	1014.9	1014.6	1014.5	1015.6	1016.6
162.5°	1026.4	1025.9	1025.5	1025.0	1024.7	1024.5	1024.3	1024.1	1024.0	1025.2	1026.4
165°	1039.3	1038.7	1038.2	1037.7	1037.4	1037.1	1037.0	1036.8	1036.6	1038.0	1039.4
167.5°	1049.2	1048.5	1047.8	1047.1	1046.7	1046.7	1046.7	1046.7	1046.7	1048.1	1049.6
170°	1054.9	1054.2	1053.5	1052.8	1052.4	1052.4	1052.4	1052.4	1052.4	1053.8	1055.3
172.5°	1058.6	1057.7	1056.9	1056.1	1055.7	1055.8	1056.0	1056.1	1056.2	1057.6	1059.1
175°	1063.4	1062.6	1061.7	1060.8	1060.4	1060.6	1060.8	1061.0	1061.1	1062.4	1063.6
177.5°	1064.9	1064.1	1063.4	1062.8	1062.5	1062.6	1062.8	1062.9	1063.0	1064.1	1065.2
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	747.7	747.7	748.6	752.3	752.7	755.9	754.9
5°	821.7	827.4	829.6	838.7	844.1	846.5	841.7
7.5°	912.2	928.4	936.2	945.7	954.1	956.7	950.1
10°	978.3	995.2	1009.5	1018.3	1026.5	1031.9	1038.9
12.5°	1042.0	1063.0	1076.5	1088.9	1097.3	1104.3	1105.4
15°	1111.4	1143.0	1167.0	1184.6	1193.3	1197.9	1196.1
17.5°	1181.4	1210.6	1227.7	1245.6	1257.8	1258.5	1258.9
20°	1221.0	1249.5	1269.2	1282.5	1296.2	1295.6	1298.6
22.5°	1247.4	1269.9	1285.0	1294.7	1299.3	1297.0	1297.7
25°	1259.8	1266.5	1263.8	1248.2	1244.4	1230.1	1232.5
27.5°	1196.0	1164.4	1131.8	1089.7	1056.6	1030.2	1031.5
30°	1109.3	1053.4	989.8	936.4	888.4	875.0	846.5
32.5°	988.2	904.4	829.8	780.1	738.9	727.7	702.8
35°	782.8	701.5	624.7	578.6	560.4	535.0	534.6
37.5°	608.5	536.9	496.3	461.7	443.5	428.1	426.6
40°	511.9	456.1	425.4	400.5	382.6	371.1	368.4
42.5°	444.4	399.3	370.5	355.1	341.4	335.4	331.0
45°	362.9	332.6	312.5	298.6	292.2	287.6	285.2
47.5°	303.6	283.2	269.6	260.3	255.1	250.3	251.6
50°	271.2	254.6	244.5	235.8	231.8	228.5	228.8
52.5°	245.3	230.3	222.2	215.9	211.0	208.6	207.4
55°	208.2	198.8	190.5	186.0	183.2	179.9	179.0
57.5°	177.5	170.2	163.6	158.4	157.8	154.6	155.0
60°	157.2	151.1	145.6	142.9	140.8	138.1	138.9
62.5°	140.5	135.3	130.3	128.1	126.0	124.0	124.4
65°	115.0	110.1	107.1	105.9	105.0	104.1	103.1
67.5°	91.7	88.6	86.7	84.1	82.3	82.0	81.0
70°	77.1	73.1	69.8	66.5	65.5	65.2	65.5
72.5°	61.8	59.3	58.4	56.7	56.6	55.8	56.3
75°	46.4	45.6	44.9	43.7	43.7	43.7	43.7
77.5°	34.2	33.7	33.4	33.0	32.8	32.3	32.3
80°	26.7	26.4	25.8	25.8	25.5	25.8	25.5
82.5°	20.1	20.1	19.5	19.5	19.2	19.0	19.2
85°	10.3	10.0	10.6	10.0	10.3	9.7	10.3
87.5°	7.1	7.3	7.1	7.2	7.1	7.6	7.2
90°	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	23.6	24.7	25.4	25.6	25.8	26.1	26.2
95°	28.2	29.5	30.0	30.0	30.0	30.0	30.0
97.5°	29.7	31.1	31.8	32.1	32.2	32.4	32.6
100°	30.3	31.7	32.5	32.7	32.9	33.0	33.2
102.5°	39.0	34.6	32.6	32.9	33.2	33.5	33.8
105°	79.9	48.8	33.4	33.7	34.1	34.5	34.8
107.5°	249.0	226.2	203.0	179.6	156.1	132.7	109.2
110°	339.2	333.4	318.0	292.8	267.7	242.6	217.5



TEST NUMBER: P332288-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	396.8	396.9	394.3	389.0	383.7	378.3	373.0
115°	459.1	460.9	462.2	462.8	463.5	464.2	464.9
117.5°	513.7	515.2	515.9	516.1	516.2	516.3	516.5
120°	549.8	551.2	551.9	551.9	551.9	551.9	551.9
122.5°	584.6	585.6	586.1	586.3	586.5	586.5	586.7
125°	633.6	634.0	634.3	634.7	635.0	635.4	635.7
127.5°	683.6	684.1	684.3	683.9	683.6	683.2	682.9
130°	713.8	714.5	714.6	714.3	713.9	713.6	713.2
132.5°	742.2	742.9	743.0	742.5	742.0	741.6	741.1
135°	785.2	785.7	785.7	785.2	784.7	784.1	783.6
137.5°	823.9	824.7	825.0	824.7	824.3	823.9	823.6
140°	848.2	848.9	849.1	848.7	848.3	848.0	847.6
142.5°	871.2	871.7	871.7	871.2	870.8	870.3	869.8
145°	903.2	903.6	903.8	903.8	903.8	903.8	903.8
147.5°	932.2	932.6	932.3	931.5	930.7	929.9	929.1
150°	949.9	950.3	950.1	949.7	949.1	948.6	948.1
152.5°	965.9	966.5	966.5	965.7	964.9	964.1	963.2
155°	987.9	988.7	988.6	987.6	986.6	985.5	984.4
157.5°	1006.9	1008.0	1007.8	1006.4	1005.0	1003.7	1002.3
160°	1017.6	1018.7	1018.6	1017.4	1016.1	1014.9	1013.7
162.5°	1027.5	1028.7	1028.8	1027.7	1026.6	1025.6	1024.5
165°	1040.8	1042.3	1042.4	1041.1	1039.9	1038.6	1037.4
167.5°	1051.0	1052.3	1052.3	1051.0	1049.6	1048.1	1046.7
170°	1056.7	1058.0	1058.0	1056.7	1055.3	1053.8	1052.4
172.5°	1060.4	1061.8	1061.8	1060.3	1058.7	1057.2	1055.6
175°	1064.9	1066.0	1066.0	1064.5	1063.2	1061.8	1060.3
177.5°	1066.4	1067.5	1067.4	1066.0	1064.6	1063.2	1061.8
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3

(END OF REPORT)