

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332291-927

Luminaire Tested: **S123RDIP-S560D1025U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332291-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D1025U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4938.9 lumens  
Efficiency: N/A  
Efficacy: 111.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332291-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332291-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	103	103	103	103	93	93	93	93	75	75	75		57	57	57		42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	62		51	49	48		37	36	36	29
2	86	79	73	68	78	72	67	62	58	54	51		45	43	41		33	32	30	25
3	79	70	63	57	71	63	57	52	51	47	43		40	37	34		29	28	26	21
4	72	62	54	48	65	56	50	44	45	41	37		36	32	30		26	24	23	18
5	66	55	47	41	60	50	43	38	41	36	32		32	28	26		24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28		29	25	23		22	19	17	14
7	56	44	37	31	51	41	34	29	33	28	24		26	23	20		20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22		24	20	18		18	16	14	11
9	49	37	29	25	44	34	27	23	28	23	19		22	19	16		17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17		20	17	14		16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332291-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	1.4
10°-20°	195.5	4.0
20°-30°	281.5	5.7
30°-40°	317.1	6.4
40°-50°	303.3	6.1
50°-60°	248.4	5.0
60°-70°	167.6	3.4
70°-80°	84.3	1.7
80°-90°	25.3	0.5
90°-100°	38.7	0.8
100°-110°	184.4	3.7
110°-120°	443.0	9.0
120°-130°	564.1	11.4
130°-140°	602.7	12.2
140°-150°	563.6	11.4
150°-160°	454.6	9.2
160°-170°	293.4	5.9
170°-180°	101.1	2.0
0°-30°	547.2	11.1
0°-40°	864.3	17.5
0°-60°	1416.1	28.7
0°-90°	1693.3	34.3
90°-120°	666.1	13.5
90°-150°	2396.5	48.5
90°-180°	3246.0	65.7
0°-180°	4938.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	9	19	22	24	4
95°	48	18	24	30	30	60
105°	236	240	173	41	35	250
115°	442	447	454	462	465	436
125°	623	629	633	634	636	556
135°	776	780	784	786	784	597
145°	895	900	902	904	904	560
155°	986	985	985	989	984	454
165°	1040	1038	1037	1042	1037	294
175°	1064	1061	1061	1066	1060	101
180°	1064	1064	1064	1064	1064	



TEST NUMBER: P332291-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.8	11.0	10.1	9.3	8.5	8.3	8.7	9.2	9.7	10.1	10.1
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6
92.5°	14.7	14.2	13.7	13.2	12.8	13.4	15.1	16.8	18.5	20.3	21.4
95°	48.2	41.0	33.8	26.6	19.4	16.8	18.7	20.7	22.6	24.5	25.7
97.5°	97.0	93.7	90.5	87.2	84.0	76.0	63.5	50.8	38.1	25.4	26.9
100°	133.6	137.1	140.7	144.2	147.7	135.7	108.3	80.9	53.5	26.1	27.5
102.5°	175.4	177.9	180.5	183.0	185.5	171.8	141.9	111.9	82.0	52.0	47.7
105°	235.6	237.6	239.5	241.5	243.4	236.4	220.6	204.8	189.0	173.2	142.0
107.5°	299.2	300.8	302.3	303.9	305.4	307.4	309.9	312.4	314.9	317.4	294.6
110°	341.6	343.0	344.4	345.8	347.2	348.9	350.8	352.8	354.7	356.6	350.8



TEST NUMBER: P332291-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.1	383.3	384.6	385.9	387.1	388.7	390.7	392.6	394.5	396.5	396.6
115°	442.0	443.1	444.1	445.2	446.2	447.6	449.1	450.7	452.3	453.8	455.7
117.5°	500.0	501.4	502.6	504.0	505.3	506.3	507.1	507.9	508.7	509.5	511.0
120°	536.1	537.7	539.2	540.8	542.4	543.5	544.0	544.5	545.1	545.6	547.0
122.5°	572.8	574.1	575.4	576.7	578.0	579.0	579.6	580.4	581.0	581.6	582.7
125°	623.1	624.5	625.9	627.3	628.7	629.8	630.5	631.1	631.8	632.6	633.0
127.5°	671.8	673.2	674.6	676.0	677.4	678.5	679.4	680.2	681.0	681.9	682.5
130°	702.2	703.5	705.0	706.4	707.8	708.8	709.6	710.3	710.9	711.6	712.3
132.5°	731.3	732.7	734.0	735.5	736.9	737.8	738.4	738.9	739.6	740.1	740.8
135°	775.7	776.7	777.8	778.9	779.9	780.8	781.5	782.2	782.9	783.6	784.1
137.5°	813.7	815.0	816.3	817.7	819.0	819.8	820.2	820.6	821.0	821.4	822.2
140°	838.9	840.0	841.1	842.1	843.2	844.0	844.5	845.0	845.6	846.1	846.8
142.5°	862.4	863.4	864.4	865.5	866.6	867.4	867.9	868.4	868.9	869.5	870.1
145°	895.1	896.4	897.5	898.8	900.0	900.8	901.2	901.5	901.8	902.2	902.5
147.5°	925.9	926.8	927.6	928.4	929.2	929.7	930.1	930.4	930.8	931.1	931.5
150°	944.9	945.5	945.9	946.5	947.0	947.5	947.8	948.2	948.5	948.9	949.2
152.5°	961.9	962.3	962.5	962.7	963.0	963.2	963.4	963.6	963.8	964.0	964.6
155°	986.0	985.6	985.3	985.0	984.6	984.5	984.7	984.8	985.1	985.2	986.1
157.5°	1004.6	1004.6	1004.6	1004.6	1004.6	1004.4	1004.2	1004.1	1003.9	1003.7	1004.8
160°	1016.1	1015.9	1015.7	1015.6	1015.3	1015.2	1015.0	1014.9	1014.6	1014.5	1015.6
162.5°	1026.8	1026.4	1025.9	1025.5	1025.0	1024.7	1024.5	1024.3	1024.1	1024.0	1025.2
165°	1039.8	1039.3	1038.7	1038.2	1037.7	1037.4	1037.1	1037.0	1036.8	1036.6	1038.0
167.5°	1049.9	1049.2	1048.5	1047.8	1047.1	1046.7	1046.7	1046.7	1046.7	1046.7	1048.1
170°	1055.6	1054.9	1054.2	1053.5	1052.8	1052.4	1052.4	1052.4	1052.4	1052.4	1053.8
172.5°	1059.4	1058.6	1057.7	1056.9	1056.1	1055.7	1055.8	1056.0	1056.1	1056.2	1057.6
175°	1064.3	1063.4	1062.6	1061.7	1060.8	1060.4	1060.6	1060.8	1061.0	1061.1	1062.4
177.5°	1065.6	1064.9	1064.1	1063.4	1062.8	1062.5	1062.6	1062.8	1062.9	1063.0	1064.1
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332291-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	10.1	10.2	10.2	10.2	10.2	10.1	10.1	10.1
90°	20.4	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	22.5	23.6	24.7	25.4	25.6	25.8	26.1	26.2
95°	26.9	28.2	29.5	30.0	30.0	30.0	30.0	30.0
97.5°	28.3	29.7	31.1	31.8	32.1	32.2	32.4	32.6
100°	28.9	30.3	31.7	32.5	32.7	32.9	33.0	33.2
102.5°	43.3	39.0	34.6	32.6	32.9	33.2	33.5	33.8
105°	111.0	79.9	48.8	33.4	33.7	34.1	34.5	34.8
107.5°	271.8	249.0	226.2	203.0	179.6	156.1	132.7	109.2
110°	345.0	339.2	333.4	318.0	292.8	267.7	242.6	217.5





TEST NUMBER: P332291-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	396.6	396.8	396.9	394.3	389.0	383.7	378.3	373.0
115°	457.4	459.1	460.9	462.2	462.8	463.5	464.2	464.9
117.5°	512.4	513.7	515.2	515.9	516.1	516.2	516.3	516.5
120°	548.4	549.8	551.2	551.9	551.9	551.9	551.9	551.9
122.5°	583.6	584.6	585.6	586.1	586.3	586.5	586.5	586.7
125°	633.3	633.6	634.0	634.3	634.7	635.0	635.4	635.7
127.5°	683.0	683.6	684.1	684.3	683.9	683.6	683.2	682.9
130°	713.0	713.8	714.5	714.6	714.3	713.9	713.6	713.2
132.5°	741.5	742.2	742.9	743.0	742.5	742.0	741.6	741.1
135°	784.7	785.2	785.7	785.7	785.2	784.7	784.1	783.6
137.5°	823.1	823.9	824.7	825.0	824.7	824.3	823.9	823.6
140°	847.5	848.2	848.9	849.1	848.7	848.3	848.0	847.6
142.5°	870.6	871.2	871.7	871.7	871.2	870.8	870.3	869.8
145°	902.9	903.2	903.6	903.8	903.8	903.8	903.8	903.8
147.5°	931.8	932.2	932.6	932.3	931.5	930.7	929.9	929.1
150°	949.6	949.9	950.3	950.1	949.7	949.1	948.6	948.1
152.5°	965.3	965.9	966.5	966.5	965.7	964.9	964.1	963.2
155°	987.0	987.9	988.7	988.6	987.6	986.6	985.5	984.4
157.5°	1005.8	1006.9	1008.0	1007.8	1006.4	1005.0	1003.7	1002.3
160°	1016.6	1017.6	1018.7	1018.6	1017.4	1016.1	1014.9	1013.7
162.5°	1026.4	1027.5	1028.7	1028.8	1027.7	1026.6	1025.6	1024.5
165°	1039.4	1040.8	1042.3	1042.4	1041.1	1039.9	1038.6	1037.4
167.5°	1049.6	1051.0	1052.3	1052.3	1051.0	1049.6	1048.1	1046.7
170°	1055.3	1056.7	1058.0	1058.0	1056.7	1055.3	1053.8	1052.4
172.5°	1059.1	1060.4	1061.8	1061.8	1060.3	1058.7	1057.2	1055.6
175°	1063.6	1064.9	1066.0	1066.0	1064.5	1063.2	1061.8	1060.3
177.5°	1065.2	1066.4	1067.5	1067.4	1066.0	1064.6	1063.2	1061.8
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3

(END OF REPORT)