

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331752-935

Luminaire Tested: **S122RDIP-S1005D725U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331752-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D725U935-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5437.4 lumens  
Efficiency: N/A  
Efficacy: 89.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331752-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331752-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	52	48
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	31
5	70	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23541	23541	23541
5°	23631	23246	23376
10°	23451	22866	22673
15°	23181	22188	21549
20°	22807	21220	20155
25°	22425	20122	18805
30°	21895	18990	17074
35°	21378	17763	15554
40°	20858	16493	13793
45°	20247	15066	12202
50°	19623	13622	10638
55°	18978	12073	9137
60°	18235	10440	7585
65°	17391	8772	6907
70°	16386	7227	6354
75°	15147	6588	5926
80°	13371	5895	5393
85°	10504	4650	4650



TEST NUMBER: P331752-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.5	2.5
10°-20°	374.7	6.9
20°-30°	526.2	9.7
30°-40°	573.8	10.6
40°-50°	527.6	9.7
50°-60°	414.4	7.6
60°-70°	270.2	5.0
70°-80°	139.3	2.6
80°-90°	39.3	0.7
90°-100°	139.9	2.6
100°-110°	474.9	8.7
110°-120°	504.5	9.3
120°-130°	415.3	7.6
130°-140°	333.5	6.1
140°-150°	252.0	4.6
150°-160°	177.1	3.3
160°-170°	104.3	1.9
170°-180°	33.9	0.6
0°-30°	1037.4	19.1
0°-40°	1611.3	29.6
0°-60°	2553.2	47.0
0°-90°	3002.0	55.2
90°-120°	1119.3	20.6
90°-150°	2120.1	39.0
90°-180°	2435.0	44.8
0°-180°	5437.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1445	1442	138
15°	1387	1371	1327	1303	1289	390
25°	1259	1214	1130	1077	1056	579
35°	1085	1015	901	821	789	678
45°	887	796	660	570	534	684
55°	674	569	429	353	325	602
65°	455	348	230	187	181	451
75°	243	153	106	97	95	257
85°	57	30	25	25	25	67
90°	1	9	23	22	22	4
95°	24	58	264	100	77	25
105°	82	124	499	892	758	87
115°	145	183	417	861	998	143
125°	202	239	401	698	810	179
135°	237	283	396	586	671	183
145°	270	311	394	490	536	170
155°	308	332	383	433	450	141
165°	335	345	367	389	395	94
175°	349	350	353	357	356	33
180°	350	350	350	350	350	



TEST NUMBER: P331752-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1463.4	1462.2	1460.9	1459.8	1458.6	1456.7	1454.1	1451.6	1449.1	1446.5	1448.8
5°	1458.0	1456.6	1455.1	1453.6	1452.2	1449.6	1445.7	1441.9	1438.1	1434.3	1436.9
7.5°	1443.0	1441.2	1439.4	1437.5	1435.7	1432.6	1428.1	1423.7	1419.3	1414.8	1415.6
10°	1430.4	1428.3	1426.2	1424.2	1422.1	1418.2	1412.3	1406.4	1400.6	1394.7	1393.9
12.5°	1414.5	1412.0	1409.5	1407.0	1404.5	1399.4	1391.9	1384.4	1376.9	1369.4	1367.8
15°	1386.8	1383.5	1380.4	1377.1	1373.9	1367.3	1357.4	1347.4	1337.4	1327.4	1321.9
17.5°	1352.7	1347.8	1342.9	1338.0	1333.1	1324.2	1311.4	1298.6	1285.8	1273.1	1266.4
20°	1327.4	1321.5	1315.7	1309.8	1304.0	1293.7	1279.0	1264.4	1249.7	1235.0	1227.7
22.5°	1299.9	1293.4	1286.9	1280.3	1273.7	1262.1	1245.6	1229.1	1212.5	1196.0	1186.5
25°	1258.8	1249.4	1240.0	1230.6	1221.2	1206.9	1187.6	1168.2	1148.8	1129.5	1117.5
27.5°	1209.2	1199.0	1188.8	1178.6	1168.4	1152.4	1130.6	1108.7	1086.9	1065.1	1051.1
30°	1174.4	1163.2	1152.1	1140.9	1129.8	1112.5	1089.0	1065.6	1042.2	1018.6	1003.7
32.5°	1140.6	1127.6	1114.6	1101.6	1088.5	1070.1	1046.1	1022.2	998.2	974.3	957.3
35°	1084.6	1069.7	1054.7	1039.7	1024.8	1004.4	978.6	952.9	927.0	901.2	882.8
37.5°	1028.7	1012.3	995.8	979.4	963.0	941.1	913.5	886.1	858.5	831.0	810.7
40°	989.6	972.1	954.4	936.9	919.3	896.2	867.8	839.4	810.9	782.5	761.6
42.5°	949.5	931.0	912.5	893.9	875.4	851.4	822.1	792.6	763.3	733.9	712.4
45°	886.7	867.0	847.4	827.8	808.1	782.9	752.1	721.3	690.5	659.8	638.9
47.5°	825.4	804.7	783.9	763.0	742.2	715.9	684.2	652.3	620.5	588.8	568.1
50°	781.2	760.3	739.5	718.7	697.8	671.3	639.1	606.8	574.5	542.3	522.1
52.5°	737.9	716.1	694.4	672.6	650.8	624.2	592.6	561.1	529.5	498.0	478.5
55°	674.2	651.4	628.5	605.6	582.8	555.5	523.8	492.1	460.5	428.9	411.2
57.5°	609.1	585.7	562.1	538.7	515.2	488.3	457.9	427.4	397.0	366.5	350.4
60°	564.7	541.3	517.8	494.4	470.9	444.1	413.9	383.7	353.4	323.3	308.3
62.5°	521.5	498.0	474.6	451.1	427.7	401.5	372.7	343.9	315.1	286.4	272.1
65°	455.2	431.4	407.8	384.0	360.2	335.2	308.8	282.4	256.0	229.6	219.6
67.5°	391.3	367.8	344.2	320.6	297.0	273.4	249.7	225.9	202.2	178.4	173.8
70°	347.1	324.2	301.3	278.4	255.5	234.0	213.8	193.6	173.3	153.1	150.2
72.5°	304.8	282.8	261.0	239.0	217.1	197.9	181.8	165.5	149.2	133.0	130.5
75°	242.8	222.2	201.7	181.2	160.7	145.4	135.4	125.5	115.5	105.6	103.5
77.5°	181.8	163.8	145.9	127.9	109.8	98.4	93.6	88.8	83.9	79.2	78.0
80°	143.8	128.9	113.9	98.9	84.0	75.1	72.2	69.2	66.3	63.4	62.2
82.5°	109.0	97.3	85.7	74.0	62.3	55.4	53.5	51.5	49.5	47.5	46.8
85°	56.7	50.5	44.4	38.2	32.1	28.6	27.7	26.9	25.9	25.1	25.1
87.5°	17.0	15.6	14.2	12.6	11.0	10.5	11.1	12.1	12.9	13.0	12.7
90°	0.7	2.7	5.4	6.7	8.1	10.1	13.4	18.2	22.2	22.9	22.2
92.5°	8.2	11.9	16.7	19.6	24.2	30.6	45.8	67.2	86.3	87.5	73.9
95°	23.6	26.3	33.0	39.0	49.8	66.0	96.9	155.5	233.6	263.8	230.8
97.5°	38.4	42.0	49.2	58.3	70.7	88.9	127.9	209.5	339.2	450.4	472.5
100°	51.8	53.8	59.9	70.7	84.1	103.0	138.6	220.8	366.1	531.7	628.6
102.5°	64.2	65.7	71.7	82.5	96.5	115.4	148.4	221.3	355.9	534.4	686.7
105°	82.1	84.8	89.5	99.6	114.4	133.3	164.9	224.8	335.9	498.7	677.8
107.5°	101.5	103.7	108.2	117.5	132.2	151.2	181.8	234.1	325.9	460.5	618.6
110°	114.4	117.1	121.1	129.9	144.0	163.6	193.1	241.6	323.7	442.2	581.5



TEST NUMBER: P331752-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.2	129.0	133.5	141.7	155.3	175.4	204.0	249.7	324.3	430.3	555.7
115°	144.7	148.1	152.1	160.1	173.7	191.8	220.8	261.8	327.1	417.3	523.7
117.5°	163.8	166.5	170.6	177.7	190.6	209.5	236.3	274.7	331.9	411.0	503.4
120°	175.6	178.4	182.4	188.5	201.9	220.8	247.0	283.4	335.2	407.2	492.7
122.5°	187.0	189.2	193.1	199.8	213.2	232.6	257.3	290.9	339.0	405.0	483.5
125°	201.9	204.0	207.9	216.0	229.5	248.3	272.6	302.9	344.6	401.1	470.5
127.5°	213.8	216.5	222.1	231.0	243.9	263.3	286.9	314.0	350.4	398.8	458.3
130°	220.8	223.4	230.1	239.6	253.0	271.9	295.5	321.1	354.7	397.8	450.3
132.5°	227.2	230.5	237.7	247.7	261.7	280.5	303.0	328.0	359.0	397.3	443.8
135°	236.9	239.6	247.7	257.8	273.3	292.1	313.7	337.2	364.1	396.4	434.8
137.5°	246.1	249.3	257.4	268.1	283.5	301.0	322.3	344.2	368.7	396.3	428.4
140°	253.0	255.7	263.8	274.6	289.4	306.9	327.1	347.9	370.8	395.7	424.7
142.5°	260.0	262.3	269.8	280.5	294.8	311.3	330.9	351.2	372.5	395.7	420.9
145°	270.5	273.3	280.0	290.1	303.5	318.3	336.6	355.3	374.2	394.4	415.9
147.5°	281.9	283.9	290.3	299.6	310.8	324.0	341.1	357.7	374.8	392.0	410.9
150°	289.4	291.4	296.8	305.6	315.6	327.8	343.3	358.7	374.2	390.4	406.5
152.5°	297.0	297.9	303.2	310.9	320.5	331.6	345.4	359.3	373.2	387.7	402.8
155°	307.5	308.2	312.3	319.7	327.1	337.2	348.6	360.1	371.5	383.0	395.7
157.5°	316.5	317.1	320.4	326.8	332.8	341.2	350.9	360.1	368.4	378.2	389.2
160°	322.4	323.0	325.7	331.1	336.6	343.9	352.0	360.1	366.8	374.9	384.4
162.5°	328.3	327.9	330.6	334.9	339.8	345.5	352.6	359.6	365.2	372.2	380.0
165°	335.2	334.5	335.9	339.9	343.3	347.3	353.4	358.1	362.1	366.8	372.9
167.5°	340.9	340.0	341.2	343.8	346.2	348.8	353.2	357.1	359.0	362.1	365.8
170°	344.6	343.3	343.9	345.9	347.3	349.3	352.7	356.0	357.4	359.4	362.1
172.5°	346.7	345.9	345.5	347.6	348.4	349.8	352.1	354.4	355.2	356.2	358.3
175°	349.3	348.6	347.9	349.3	349.3	350.0	351.3	352.7	352.0	352.7	353.4
177.5°	350.5	349.5	348.9	350.0	350.0	350.0	350.5	351.6	350.5	350.0	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331752-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1451.1	1453.5	1455.9	1456.7	1456.3	1455.9	1455.3	1454.9
5°	1439.6	1442.3	1444.8	1445.7	1444.8	1444.0	1443.1	1442.3
7.5°	1416.3	1417.0	1417.8	1417.5	1415.9	1414.4	1412.9	1411.4
10°	1392.9	1392.1	1391.2	1389.9	1388.1	1386.4	1384.6	1382.9
12.5°	1366.2	1364.6	1363.0	1360.8	1357.9	1355.0	1352.0	1349.1
15°	1316.3	1310.7	1305.1	1300.9	1298.0	1295.0	1292.1	1289.2
17.5°	1259.8	1253.2	1246.6	1240.7	1235.7	1230.6	1225.5	1220.6
20°	1220.4	1213.1	1205.7	1198.9	1192.4	1185.9	1179.5	1173.0
22.5°	1177.2	1167.7	1158.2	1151.1	1146.3	1141.5	1136.7	1131.9
25°	1105.4	1093.5	1081.4	1073.2	1068.8	1064.4	1060.0	1055.6
27.5°	1037.1	1023.0	1009.0	998.5	991.5	984.6	977.6	970.6
30°	988.8	973.8	958.8	947.4	939.5	931.6	923.7	915.8
32.5°	940.2	923.2	906.0	893.8	886.4	878.9	871.4	864.0
35°	864.3	845.8	827.3	814.9	808.4	801.9	795.5	789.1
37.5°	790.3	770.0	749.6	735.7	728.4	721.0	713.6	706.2
40°	740.8	720.0	699.2	685.0	677.3	669.7	662.1	654.4
42.5°	690.9	669.3	647.8	633.4	625.9	618.5	611.2	603.8
45°	618.1	597.3	576.4	562.6	555.5	548.5	541.4	534.4
47.5°	547.3	526.7	505.9	492.4	486.0	479.7	473.2	466.8
50°	501.9	481.6	461.4	448.2	442.0	435.8	429.7	423.5
52.5°	458.9	439.4	419.9	407.3	401.6	395.9	390.2	384.5
55°	393.6	376.1	358.4	346.9	341.3	335.7	330.2	324.6
57.5°	334.3	318.1	302.0	291.6	287.0	282.2	277.6	272.9
60°	293.3	278.4	263.5	253.7	248.9	244.3	239.5	234.9
62.5°	257.9	243.6	229.4	220.8	218.0	215.2	212.3	209.6
65°	209.7	199.7	189.7	184.3	183.4	182.5	181.7	180.8
67.5°	169.3	164.7	160.1	157.3	156.4	155.5	154.5	153.6
70°	147.2	144.3	141.4	139.3	138.1	136.9	135.8	134.6
72.5°	128.1	125.6	123.1	121.6	120.9	120.2	119.4	118.7
75°	101.4	99.4	97.4	96.2	95.9	95.6	95.3	95.0
77.5°	76.8	75.7	74.5	73.6	73.2	72.8	72.2	71.8
80°	61.0	59.8	58.6	58.0	58.0	58.0	58.0	58.0
82.5°	46.1	45.4	44.7	44.3	44.3	44.3	44.3	44.3
85°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
87.5°	12.3	11.8	11.8	11.8	11.8	11.8	11.8	11.8
90°	21.5	20.2	21.5	22.2	22.2	22.2	22.2	22.2
92.5°	58.7	50.4	44.7	40.6	40.0	37.8	38.4	37.3
95°	176.3	135.3	107.0	92.2	83.4	78.1	76.0	76.7
97.5°	411.5	336.7	263.8	215.2	183.0	166.5	156.7	151.0
100°	614.5	531.1	438.9	357.4	301.5	272.6	253.0	240.9
102.5°	747.5	728.7	661.2	574.9	514.2	464.8	440.4	424.0
105°	817.8	893.8	902.6	880.4	838.6	796.9	767.9	758.5
107.5°	767.2	881.7	951.7	984.3	989.5	987.2	981.5	968.9
110°	723.5	844.0	930.1	985.3	1014.3	1027.1	1033.1	1032.4





TEST NUMBER: P331752-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	683.7	799.3	891.4	954.7	994.9	1016.3	1027.8	1031.4
115°	634.6	738.3	826.5	895.8	943.6	974.6	992.0	998.2
117.5°	597.8	688.8	768.8	833.8	882.5	915.2	933.7	938.7
120°	579.5	663.0	734.3	795.6	842.7	874.3	893.8	900.5
122.5°	565.0	641.4	708.9	764.3	806.6	837.7	855.1	860.7
125°	543.8	613.1	672.4	722.8	761.9	787.5	804.3	809.7
127.5°	523.0	585.7	641.5	688.1	722.2	746.1	760.7	765.0
130°	509.5	567.4	620.5	665.0	697.9	720.8	734.3	739.7
132.5°	496.5	550.2	599.0	640.8	673.2	696.0	708.4	713.3
135°	478.5	523.0	567.4	605.0	634.0	656.3	668.3	671.1
137.5°	464.2	501.3	536.6	569.4	595.8	614.9	625.5	629.6
140°	455.0	487.3	518.2	547.9	569.4	586.9	597.0	601.1
142.5°	447.5	474.9	501.5	526.3	546.8	562.7	571.7	572.5
145°	436.8	459.0	479.9	499.4	515.6	527.0	533.7	535.7
147.5°	428.6	446.1	462.4	476.6	490.0	499.1	503.7	504.9
150°	422.7	437.5	451.6	463.7	473.8	481.9	485.9	486.6
152.5°	416.7	430.5	442.5	453.0	460.9	467.9	470.9	471.0
155°	408.5	419.3	429.4	436.8	444.2	448.9	451.6	450.3
157.5°	399.0	408.0	416.5	422.2	427.5	431.4	432.7	432.7
160°	393.0	400.5	407.9	412.6	417.3	420.7	421.3	421.3
162.5°	387.1	393.5	399.8	403.5	408.1	410.4	411.1	410.5
165°	378.2	383.0	387.7	390.4	393.0	395.7	395.7	395.1
167.5°	369.8	373.4	376.6	379.1	380.3	381.8	381.6	380.8
170°	365.5	367.5	370.1	371.5	372.2	374.2	373.5	372.2
172.5°	360.6	362.1	364.3	365.1	365.8	366.7	366.0	365.2
175°	355.3	356.0	356.7	357.4	357.4	358.1	357.4	356.0
177.5°	351.6	351.6	352.1	352.1	352.1	352.1	351.6	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0

(END OF REPORT)