

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832209

Luminaire Tested: S123RDIP-S560D1195U927-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832209
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U927-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5697.2 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22				
4	73	63	56	50	66	57	51	46	47	42	38	37	34	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	34	33	30	27	25	23	21	18				
6	62	51	43	38	56	46	40	35	38	33	30	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	36	31	35	30	26	28	24	22	21	19	17	14				
8	53	42	35	30	48	38	32	28	32	27	24	25	22	20	20	17	16	13				
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	15573	15573	15573	15573	15573
5°	18492	17902	15672	12669	11761
10°	16753	18183	15593	10151	8708
15°	11535	15591	15428	8296	6888
20°	8025	12003	15119	6995	6054
25°	6115	9149	14668	6217	5580
30°	5323	7315	14105	5773	5168
35°	4887	6169	13306	5398	4794
40°	4460	5510	12261	5030	4451
45°	4028	5039	11134	4682	4109
50°	3656	4649	9805	4340	3686
55°	3307	4269	8527	4008	3162
60°	2962	3881	7408	3640	2988
65°	2735	3443	6375	3270	2825
70°	2222	2977	5564	2958	2297
75°	1951	2366	4712	2454	2021
80°	1767	2002	3862	2058	1909
85°	1618	1754	2927	1865	1754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 11749 cd/sqm



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	2.3
10°-20°	305.2	5.4
20°-30°	350.1	6.1
30°-40°	345.1	6.1
40°-50°	304.3	5.3
50°-60°	234.1	4.1
60°-70°	153.9	2.7
70°-80°	74.8	1.3
80°-90°	21.3	0.4
90°-100°	43.7	0.8
100°-110°	211.1	3.7
110°-120°	517.5	9.1
120°-130°	657.0	11.5
130°-140°	701.9	12.3
140°-150°	656.4	11.5
150°-160°	529.4	9.3
160°-170°	341.7	6.0
170°-180°	117.7	2.1
0°-30°	787.2	13.8
0°-40°	1132.3	19.9
0°-60°	1670.7	29.3
0°-90°	1920.7	33.7
90°-120°	772.4	13.6
90°-150°	2787.7	48.9
90°-180°	3776.0	66.3
0°-180°	5697.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1447	1447	1447	1447	1447	
5°	1711	1657	1450	1172	1088	156
15°	1035	1399	1384	744	618	292
25°	515	770	1235	524	470	243
35°	372	470	1013	411	365	232
45°	265	331	731	308	270	205
55°	176	228	454	214	168	158
65°	107	135	250	128	111	105
75°	47	57	113	59	49	50
85°	13	14	24	15	14	14
90°	28	22	1	22	28	13
95°	35	28	56	28	35	29
105°	40	202	274	202	40	84
115°	541	528	514	528	541	509
125°	740	736	725	736	740	661
135°	912	912	903	912	912	704
145°	1052	1050	1042	1050	1052	657
155°	1146	1147	1148	1147	1146	529
165°	1208	1207	1210	1207	1208	341
175°	1234	1235	1239	1235	1234	117
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8
2.5°	1603.4	1598.4	1593.3	1591.8	1590.4	1585.6	1580.9	1570.2	1559.5	1548.5	1537.6
5°	1711.4	1712.0	1712.6	1711.1	1709.6	1703.4	1697.1	1684.1	1671.0	1656.8	1642.6
7.5°	1678.2	1687.7	1697.1	1698.9	1700.7	1705.4	1710.2	1707.2	1704.3	1698.9	1693.6
10°	1532.8	1532.2	1531.6	1542.3	1553.0	1584.7	1616.5	1632.8	1649.1	1663.6	1678.2
12.5°	1295.5	1296.4	1297.3	1332.3	1367.3	1397.3	1427.2	1468.8	1510.3	1555.1	1599.9
15°	1035.1	1049.7	1064.2	1095.3	1126.5	1171.6	1216.7	1272.4	1328.2	1399.1	1469.9
17.5°	850.1	856.3	862.5	892.5	922.4	965.1	1007.8	1071.0	1134.2	1225.5	1316.9
20°	700.6	706.2	711.8	733.5	755.1	796.1	837.0	897.2	957.4	1047.9	1138.3
22.5°	584.9	595.9	606.8	621.4	635.9	665.6	695.2	756.6	818.0	900.5	982.9
25°	514.9	519.9	525.0	537.4	549.9	578.4	606.8	647.5	688.1	770.3	852.4
27.5°	467.4	468.9	470.4	479.6	488.8	507.2	525.6	563.2	600.9	668.5	736.2
30°	428.3	431.0	433.6	440.7	447.9	461.2	474.6	501.3	527.9	588.5	649.0
32.5°	398.0	399.5	401.0	406.9	412.9	422.7	432.4	453.5	474.6	520.8	567.1
35°	371.9	372.2	372.5	377.0	381.4	390.9	400.4	417.9	435.4	469.5	503.6
37.5°	342.3	344.4	346.4	349.7	353.0	361.3	369.6	383.8	398.0	426.2	454.4
40°	317.4	319.1	320.9	324.8	328.6	335.2	341.7	354.7	367.8	392.1	416.4
42.5°	292.4	293.6	294.8	298.7	302.5	310.5	318.5	328.9	339.3	359.5	379.6
45°	264.6	267.5	270.5	274.7	278.8	285.6	292.4	303.1	313.8	331.0	348.2
47.5°	241.4	242.9	244.4	248.0	251.5	259.8	268.1	277.6	287.1	303.1	319.1
50°	218.3	218.9	219.5	222.7	226.0	233.4	240.8	251.8	262.8	277.6	292.4
52.5°	196.3	197.8	199.3	202.6	205.8	210.9	215.9	227.2	238.5	253.0	267.5
55°	176.2	177.1	178.0	180.3	182.7	188.6	194.6	204.4	214.1	227.5	240.8
57.5°	157.2	158.4	159.6	161.4	163.1	168.5	173.8	182.4	191.0	204.4	217.7
60°	137.6	139.1	140.6	142.7	144.7	148.9	153.0	160.8	168.5	180.3	192.2
62.5°	123.4	123.7	124.0	125.8	127.5	130.5	133.5	139.7	145.9	157.8	169.7
65°	107.4	108.3	109.1	110.0	110.9	113.3	115.7	121.0	126.4	135.2	144.1
67.5°	90.8	91.6	92.5	94.0	95.5	97.6	99.7	103.2	106.8	115.1	123.4
70°	70.6	70.6	70.6	73.0	75.3	78.9	82.5	85.1	87.8	94.6	101.4
72.5°	57.5	57.8	58.1	58.4	58.7	60.8	62.9	67.3	71.8	75.9	80.1
75°	46.9	47.2	47.5	47.8	48.0	48.6	49.2	50.7	52.2	56.9	61.7
77.5°	37.4	37.7	38.0	38.3	38.6	39.2	39.7	40.3	40.9	42.7	44.5
80°	28.5	28.8	29.1	29.4	29.7	30.0	30.3	30.8	31.4	32.3	33.2
82.5°	20.8	20.8	20.8	20.8	20.8	21.4	21.9	21.9	21.9	22.5	23.1
85°	13.1	13.1	13.1	13.3	13.6	13.6	13.6	13.9	14.2	14.2	14.2
87.5°	5.9	5.6	5.3	5.6	5.9	5.9	5.9	6.2	6.5	6.5	6.5
90°	27.6	27.2	26.8	26.4	26.0	25.4	24.5	23.7	22.9	22.1	19.4
92.5°	31.3	31.1	30.9	30.7	30.5	29.7	28.2	26.8	25.4	23.9	22.1
95°	35.0	35.0	35.0	35.0	35.0	34.3	32.8	31.4	30.0	28.5	26.3
97.5°	37.7	37.5	37.3	37.1	36.9	36.0	34.4	32.7	31.1	29.5	39.9
100°	38.7	38.5	38.2	38.0	37.8	36.9	35.3	33.6	32.0	30.4	62.3
102.5°	39.6	39.2	38.8	38.3	37.9	41.1	47.9	54.6	61.4	68.1	103.7
105°	40.5	40.1	39.7	39.3	38.9	56.8	93.0	129.2	165.4	201.6	220.0
107.5°	95.7	122.5	149.3	176.1	202.9	232.0	263.5	295.0	326.5	358.0	355.0
110°	253.1	282.3	311.6	340.8	370.1	388.1	394.8	401.6	408.3	415.1	412.8



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.5	479.9	480.3	480.7	481.1	480.4	478.6	476.7	474.9	473.1	470.8
115°	541.2	540.4	539.5	538.7	537.9	536.5	534.4	532.4	530.3	528.3	526.4
117.5°	590.9	590.7	590.5	590.3	590.1	589.1	587.5	585.9	584.2	582.6	581.6
120°	642.4	642.4	642.4	642.4	642.4	641.6	640.0	638.3	636.7	635.1	634.4
122.5°	693.0	692.8	692.6	692.4	692.2	691.6	690.6	689.6	688.5	687.5	686.7
125°	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1	736.7	736.3	735.5
127.5°	786.0	786.4	786.8	787.2	787.6	787.5	786.9	786.3	785.7	785.1	784.0
130°	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0	829.1	828.3	827.5
132.5°	870.7	871.3	871.9	872.5	873.1	873.0	872.2	871.4	870.6	869.7	869.1
135°	912.1	912.7	913.3	913.9	914.5	914.5	913.9	913.3	912.7	912.1	911.3
137.5°	951.7	952.1	952.5	952.9	953.3	953.0	952.0	950.9	949.9	948.9	948.5
140°	986.6	987.0	987.4	987.9	988.3	988.1	987.2	986.4	985.6	984.8	984.2
142.5°	1018.8	1019.5	1020.1	1020.7	1021.3	1021.3	1020.7	1020.1	1019.5	1018.8	1018.2
145°	1052.0	1052.0	1052.0	1052.0	1052.0	1051.8	1051.4	1051.0	1050.5	1050.1	1049.7
147.5°	1075.9	1076.9	1078.0	1079.0	1080.0	1080.3	1079.9	1079.5	1079.1	1078.7	1078.3
150°	1103.5	1104.1	1104.7	1105.4	1106.0	1106.1	1105.7	1105.3	1104.8	1104.4	1104.0
152.5°	1125.6	1126.6	1127.7	1128.7	1129.7	1129.8	1129.0	1128.2	1127.3	1126.5	1126.3
155°	1145.9	1147.1	1148.3	1149.5	1150.8	1150.9	1149.8	1148.8	1147.8	1146.8	1146.6
157.5°	1163.3	1165.0	1166.6	1168.2	1169.9	1170.1	1168.9	1167.6	1166.4	1165.2	1165.4
160°	1179.9	1181.3	1182.8	1184.2	1185.6	1185.7	1184.5	1183.3	1182.1	1180.8	1181.0
162.5°	1195.6	1196.8	1198.0	1199.2	1200.5	1200.4	1198.9	1197.5	1196.1	1194.6	1194.8
165°	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9	1208.2	1206.6	1206.8
167.5°	1216.7	1218.4	1220.0	1221.6	1223.3	1223.3	1221.6	1220.0	1218.4	1216.7	1216.7
170°	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0	1225.0
172.5°	1229.6	1231.4	1233.3	1235.1	1237.0	1237.1	1235.4	1233.8	1232.2	1230.5	1230.3
175°	1234.2	1235.8	1237.5	1239.1	1240.8	1240.9	1239.4	1238.0	1236.6	1235.1	1234.9
177.5°	1235.1	1237.2	1239.2	1241.3	1243.3	1243.5	1241.9	1240.2	1238.6	1237.0	1236.8
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8
2.5°	1536.1	1534.6	1520.4	1506.1	1492.2	1478.3	1467.9	1457.5	1440.0	1422.5	1411.5
5°	1631.3	1620.0	1597.5	1574.9	1541.1	1507.3	1478.8	1450.4	1414.2	1378.0	1347.7
7.5°	1684.4	1675.2	1647.9	1620.6	1575.8	1531.0	1486.6	1442.1	1388.7	1335.3	1289.6
10°	1685.9	1693.6	1671.0	1648.5	1598.1	1547.7	1487.1	1426.6	1354.9	1283.1	1224.1
12.5°	1633.1	1666.3	1661.6	1656.8	1605.5	1554.2	1480.6	1407.1	1319.0	1230.9	1157.0
15°	1534.3	1598.7	1617.7	1636.6	1594.2	1551.8	1468.2	1384.5	1281.0	1177.5	1092.7
17.5°	1407.1	1497.2	1547.4	1597.5	1566.6	1535.8	1444.1	1352.5	1235.9	1119.4	1027.1
20°	1256.4	1374.4	1453.0	1531.6	1520.4	1509.1	1414.5	1319.9	1194.1	1068.4	968.4
22.5°	1107.5	1232.1	1340.6	1449.2	1460.8	1472.3	1376.8	1281.3	1143.7	1006.1	904.3
25°	979.1	1105.7	1235.0	1364.4	1390.5	1416.6	1325.8	1235.0	1092.4	949.7	848.6
27.5°	856.6	977.0	1119.4	1261.7	1309.2	1356.6	1273.6	1190.6	1042.0	893.4	792.5
30°	756.6	864.3	1009.6	1155.0	1221.1	1287.2	1211.0	1134.8	987.4	840.0	741.2
32.5°	663.5	759.9	905.8	1051.7	1128.6	1205.4	1139.5	1073.7	931.9	790.1	692.6
35°	589.9	676.2	812.4	948.5	1034.5	1120.6	1066.6	1012.6	874.1	735.6	643.3
37.5°	526.8	599.1	727.0	854.8	946.2	1037.5	992.4	947.3	817.1	686.9	599.7
40°	474.6	532.7	651.6	770.6	860.1	949.7	911.2	872.6	756.0	639.5	557.9
42.5°	429.8	479.9	586.7	693.4	775.6	857.8	832.3	806.8	701.2	595.6	519.9
45°	390.3	432.4	526.5	620.5	696.1	771.8	751.6	731.4	640.4	549.3	479.9
47.5°	355.3	391.5	475.4	559.4	627.3	695.2	676.5	657.9	582.5	507.2	444.0
50°	323.3	354.1	424.1	494.1	555.2	616.3	600.9	585.5	523.2	460.9	406.3
52.5°	293.0	318.5	381.4	444.3	493.5	542.8	530.9	519.0	471.0	423.0	373.4
55°	264.3	287.7	340.8	393.9	436.0	478.1	466.3	454.4	417.0	379.6	336.0
57.5°	238.2	258.6	301.6	344.6	378.2	411.7	406.0	400.4	369.3	338.1	302.2
60°	210.6	229.0	266.0	303.1	330.1	357.1	350.6	344.1	321.8	299.6	268.7
62.5°	186.0	202.3	231.9	261.6	283.5	305.5	300.8	296.0	279.1	262.2	236.7
65°	160.2	176.2	200.2	224.2	241.4	258.6	254.5	250.3	237.6	224.8	204.4
67.5°	136.7	150.1	170.8	191.6	203.2	214.7	212.4	210.0	200.2	190.4	174.4
70°	113.0	124.6	141.8	159.0	167.0	175.0	175.9	176.8	167.9	159.0	147.1
72.5°	89.3	98.5	114.5	130.5	136.7	143.0	142.7	142.4	137.0	131.7	121.0
75°	68.5	75.3	87.8	100.3	105.6	110.9	112.1	113.3	108.3	103.2	97.3
77.5°	49.2	54.0	63.5	73.0	78.9	84.8	85.4	86.0	83.6	81.3	75.6
80°	34.7	36.2	42.1	48.0	54.3	60.5	61.4	62.3	59.9	57.5	54.0
82.5°	24.0	24.9	27.0	29.1	34.1	39.2	40.3	41.5	40.3	39.2	35.3
85°	14.5	14.8	15.7	16.6	19.0	21.4	22.5	23.7	23.1	22.5	20.5
87.5°	6.5	6.5	6.8	7.1	7.7	8.3	9.8	11.3	10.4	9.5	8.6
90°	16.8	14.1	11.5	9.1	7.1	5.0	3.0	0.9	3.0	5.0	7.1
92.5°	20.2	18.4	16.6	16.3	17.5	18.7	19.9	21.2	19.9	18.7	17.5
95°	24.0	21.8	19.5	22.6	31.0	39.4	47.8	56.1	47.8	39.4	31.0
97.5°	50.3	60.7	71.2	79.3	85.0	90.7	96.4	102.2	96.4	90.7	85.0
100°	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5	159.6	163.7	167.8
102.5°	139.3	174.9	210.5	226.9	224.3	221.6	218.9	216.3	218.9	221.6	224.3
105°	238.4	256.8	275.2	283.3	281.0	278.8	276.5	274.3	276.5	278.8	281.0
107.5°	351.9	348.8	345.8	343.3	341.5	339.6	337.8	335.9	337.8	339.6	341.5
110°	410.6	408.3	406.1	404.1	402.5	400.9	399.2	397.6	399.2	400.9	402.5



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	468.6	466.3	464.1	462.2	460.8	459.4	457.9	456.5	457.9	459.4	460.8
115°	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5	515.7	516.9	518.2
117.5°	580.5	579.5	578.5	577.3	575.8	574.4	573.0	571.5	573.0	574.4	575.8
120°	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0	625.8	627.7	629.5
122.5°	685.9	685.1	684.2	683.1	681.7	680.3	678.8	677.4	678.8	680.3	681.7
125°	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2	726.9	728.5	730.2
127.5°	783.0	782.0	781.0	779.7	778.0	776.4	774.7	773.1	774.7	776.4	778.0
130°	826.7	825.9	825.1	823.8	822.2	820.6	818.9	817.3	818.9	820.6	822.2
132.5°	868.5	867.9	867.3	866.2	864.5	862.9	861.3	859.6	861.3	862.9	864.5
135°	910.4	909.6	908.8	907.8	906.6	905.3	904.1	902.9	904.1	905.3	906.6
137.5°	948.1	947.7	947.3	946.2	944.6	943.0	941.3	939.7	941.3	943.0	944.6
140°	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5	977.7	979.0	980.2
142.5°	1017.6	1017.0	1016.4	1015.5	1014.2	1013.0	1011.8	1010.6	1011.8	1013.0	1014.2
145°	1049.3	1048.9	1048.5	1047.6	1046.1	1044.7	1043.3	1041.9	1043.3	1044.7	1046.1
147.5°	1077.8	1077.4	1077.0	1076.3	1075.3	1074.3	1073.2	1072.2	1073.2	1074.3	1075.3
150°	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.8	1100.4	1101.1	1101.7
152.5°	1126.1	1125.9	1125.7	1125.5	1125.3	1125.1	1124.9	1124.7	1124.9	1125.1	1125.3
155°	1146.4	1146.2	1146.0	1146.1	1146.5	1146.9	1147.3	1147.7	1147.3	1146.9	1146.5
157.5°	1165.6	1165.8	1166.0	1166.1	1166.1	1166.1	1166.1	1166.1	1166.1	1166.1	1166.1
160°	1181.2	1181.4	1181.6	1181.8	1182.1	1182.3	1182.5	1182.7	1182.5	1182.3	1182.1
162.5°	1195.0	1195.2	1195.5	1195.9	1196.5	1197.1	1197.7	1198.3	1197.7	1197.1	1196.5
165°	1207.0	1207.2	1207.4	1207.8	1208.4	1209.1	1209.7	1210.3	1209.7	1209.1	1208.4
167.5°	1216.7	1216.7	1216.7	1217.1	1217.9	1218.8	1219.6	1220.4	1219.6	1218.8	1217.9
170°	1225.0	1225.0	1225.0	1225.4	1226.2	1227.0	1227.9	1228.7	1227.9	1227.0	1226.2
172.5°	1230.1	1229.9	1229.7	1230.1	1231.1	1232.2	1233.2	1234.2	1233.2	1232.2	1231.1
175°	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8	1237.8	1236.8	1235.7
177.5°	1236.6	1236.4	1236.2	1236.6	1237.6	1238.6	1239.6	1240.7	1239.6	1238.6	1237.6
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8
2.5°	1400.5	1383.6	1366.7	1354.6	1342.4	1327.3	1312.2	1311.6	1311.0	1299.7	1288.4
5°	1317.5	1288.1	1258.8	1230.0	1201.2	1172.5	1143.7	1137.2	1130.6	1120.8	1111.1
7.5°	1243.9	1197.1	1150.2	1113.4	1076.7	1047.9	1019.1	999.5	980.0	964.8	949.7
10°	1165.0	1106.9	1048.8	1004.3	959.8	928.7	897.5	875.0	852.4	841.7	831.1
12.5°	1083.2	1020.0	956.8	913.2	869.6	832.3	794.9	774.4	754.0	739.1	724.3
15°	1007.8	939.9	872.0	825.7	779.5	744.5	709.5	689.0	668.5	653.7	638.9
17.5°	934.9	866.4	797.9	751.0	704.1	672.4	640.7	620.8	600.9	591.7	582.5
20°	868.4	799.3	730.2	686.0	641.8	610.7	579.6	568.9	558.2	549.6	541.0
22.5°	802.6	736.2	669.7	627.3	584.9	562.4	539.8	531.2	522.6	516.1	509.6
25°	747.4	681.3	615.1	578.1	541.0	523.5	506.0	500.4	494.7	488.2	481.7
27.5°	691.7	628.8	565.9	536.3	506.6	492.4	478.1	471.0	463.9	458.5	453.2
30°	642.4	584.3	526.2	501.5	476.9	464.5	452.0	444.3	436.6	431.6	426.5
32.5°	595.0	543.4	491.8	470.7	449.6	437.5	425.3	417.9	410.5	404.6	398.6
35°	551.1	506.3	461.5	442.2	423.0	410.8	398.6	391.2	383.8	377.9	371.9
37.5°	512.5	471.9	431.3	413.2	395.1	384.4	373.7	366.0	358.3	352.1	345.8
40°	476.3	440.5	404.6	387.1	369.6	358.0	346.4	339.6	332.8	327.1	321.5
42.5°	444.3	411.4	378.5	361.3	344.1	333.1	322.1	314.1	306.1	302.8	299.6
45°	410.5	381.4	352.4	335.8	319.1	307.6	296.0	289.2	282.4	279.4	276.4
47.5°	380.8	353.8	326.9	310.5	294.2	283.8	273.5	268.1	262.8	258.6	254.5
50°	351.8	325.7	299.6	283.8	268.1	259.2	250.3	243.8	237.3	234.3	231.3
52.5°	323.9	300.2	276.4	260.4	244.4	235.8	227.2	221.6	215.9	209.7	203.5
55°	292.4	271.7	250.9	236.7	222.4	213.6	204.7	198.1	191.6	185.1	178.6
57.5°	266.3	245.9	225.4	212.7	199.9	191.3	182.7	175.6	168.5	163.1	157.8
60°	237.9	220.1	202.3	189.8	177.4	169.1	160.8	153.9	147.1	144.4	141.8
62.5°	211.2	194.6	178.0	167.0	156.0	148.0	140.0	135.5	131.1	129.3	127.5
65°	183.9	169.7	155.4	145.3	135.2	128.4	121.6	119.5	117.5	116.0	114.5
67.5°	158.4	146.2	134.1	125.2	116.3	111.5	106.8	104.4	102.0	100.3	98.5
70°	135.2	124.6	113.9	106.2	98.5	94.0	89.6	87.5	85.4	82.2	78.9
72.5°	110.3	102.0	93.7	87.8	81.9	78.0	74.1	70.0	65.8	62.9	59.9
75°	91.4	83.0	74.7	69.1	63.5	59.0	54.6	53.1	51.6	50.7	49.8
77.5°	70.0	62.9	55.8	51.3	46.9	44.8	42.7	41.8	40.9	40.6	40.3
80°	50.4	44.5	38.6	36.2	33.8	33.2	32.6	32.0	31.4	31.1	30.8
82.5°	31.4	28.5	25.5	24.9	24.3	24.0	23.7	23.4	23.1	22.8	22.5
85°	18.4	17.2	16.0	15.7	15.4	15.1	14.8	14.8	14.8	14.8	14.8
87.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.4	7.1
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7	24.5	25.4	26.0
92.5°	16.3	16.6	18.4	20.2	22.1	23.9	25.4	26.8	28.2	29.7	30.5
95°	22.6	19.5	21.8	24.0	26.3	28.5	30.0	31.4	32.8	34.3	35.0
97.5°	79.3	71.2	60.7	50.3	39.9	29.5	31.1	32.7	34.4	36.0	36.9
100°	171.9	158.0	126.1	94.2	62.3	30.4	32.0	33.6	35.3	36.9	37.8
102.5°	226.9	210.5	174.9	139.3	103.7	68.1	61.4	54.6	47.9	41.1	37.9
105°	283.3	275.2	256.8	238.4	220.0	201.6	165.4	129.2	93.0	56.8	38.9
107.5°	343.3	345.8	348.8	351.9	355.0	358.0	326.5	295.0	263.5	232.0	202.9
110°	404.1	406.1	408.3	410.6	412.8	415.1	408.3	401.6	394.8	388.1	370.1



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	462.2	464.1	466.3	468.6	470.8	473.1	474.9	476.7	478.6	480.4	481.1
115°	519.4	520.9	522.8	524.6	526.4	528.3	530.3	532.4	534.4	536.5	537.9
117.5°	577.3	578.5	579.5	580.5	581.6	582.6	584.2	585.9	587.5	589.1	590.1
120°	631.4	632.6	633.2	633.8	634.4	635.1	636.7	638.3	640.0	641.6	642.4
122.5°	683.1	684.2	685.1	685.9	686.7	687.5	688.5	689.6	690.6	691.6	692.2
125°	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1	737.5	737.9	738.3
127.5°	779.7	781.0	782.0	783.0	784.0	785.1	785.7	786.3	786.9	787.5	787.6
130°	823.8	825.1	825.9	826.7	827.5	828.3	829.1	830.0	830.8	831.6	831.8
132.5°	866.2	867.3	867.9	868.5	869.1	869.7	870.6	871.4	872.2	873.0	873.1
135°	907.8	908.8	909.6	910.4	911.3	912.1	912.7	913.3	913.9	914.5	914.5
137.5°	946.2	947.3	947.7	948.1	948.5	948.9	949.9	950.9	952.0	953.0	953.3
140°	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4	987.2	988.1	988.3
142.5°	1015.5	1016.4	1017.0	1017.6	1018.2	1018.8	1019.5	1020.1	1020.7	1021.3	1021.3
145°	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0	1051.4	1051.8	1052.0
147.5°	1076.3	1077.0	1077.4	1077.8	1078.3	1078.7	1079.1	1079.5	1079.9	1080.3	1080.0
150°	1102.3	1102.8	1103.2	1103.6	1104.0	1104.4	1104.8	1105.3	1105.7	1106.1	1106.0
152.5°	1125.5	1125.7	1125.9	1126.1	1126.3	1126.5	1127.3	1128.2	1129.0	1129.8	1129.7
155°	1146.1	1146.0	1146.2	1146.4	1146.6	1146.8	1147.8	1148.8	1149.8	1150.9	1150.8
157.5°	1166.1	1166.0	1165.8	1165.6	1165.4	1165.2	1166.4	1167.6	1168.9	1170.1	1169.9
160°	1181.8	1181.6	1181.4	1181.2	1181.0	1180.8	1182.1	1183.3	1184.5	1185.7	1185.6
162.5°	1195.9	1195.5	1195.2	1195.0	1194.8	1194.6	1196.1	1197.5	1198.9	1200.4	1200.5
165°	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9	1211.5	1213.1	1213.2
167.5°	1217.1	1216.7	1216.7	1216.7	1216.7	1216.7	1218.4	1220.0	1221.6	1223.3	1223.3
170°	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5
172.5°	1230.1	1229.7	1229.9	1230.1	1230.3	1230.5	1232.2	1233.8	1235.4	1237.1	1237.0
175°	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0	1239.4	1240.9	1240.8
177.5°	1236.6	1236.2	1236.4	1236.6	1236.8	1237.0	1238.6	1240.2	1241.9	1243.5	1243.3
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1446.8	1446.8	1446.8	1446.8
2.5°	1285.5	1282.5	1281.3	1280.1
5°	1101.9	1092.7	1090.6	1088.5
7.5°	945.9	942.0	929.2	916.5
10°	819.2	807.3	802.0	796.7
12.5°	713.3	702.3	700.6	698.8
15°	631.2	623.5	620.8	618.1
17.5°	577.2	571.8	568.6	565.3
20°	537.1	533.3	530.9	528.5
22.5°	506.6	503.6	501.8	500.1
25°	477.2	472.8	471.3	469.8
27.5°	449.3	445.5	444.0	442.5
30°	423.2	420.0	417.9	415.8
32.5°	394.8	390.9	389.7	388.5
35°	369.6	367.2	366.0	364.8
37.5°	342.9	339.9	338.1	336.3
40°	320.0	318.5	317.7	316.8
42.5°	296.9	294.2	293.9	293.6
45°	273.8	271.1	270.5	269.9
47.5°	252.1	249.7	249.4	249.1
50°	228.1	224.8	222.4	220.1
52.5°	200.5	197.5	195.5	193.4
55°	175.3	172.0	170.2	168.5
57.5°	156.3	154.8	153.9	153.0
60°	140.9	140.0	139.4	138.8
62.5°	126.6	125.8	125.8	125.8
65°	113.6	112.7	111.8	110.9
67.5°	96.7	94.9	94.6	94.3
70°	76.2	73.6	73.3	73.0
72.5°	59.6	59.3	58.7	58.1
75°	49.2	48.6	48.6	48.6
77.5°	39.7	39.2	39.2	39.2
80°	30.5	30.3	30.5	30.8
82.5°	22.5	22.5	22.2	21.9
85°	14.5	14.2	14.2	14.2
87.5°	7.1	7.1	7.1	7.1
90°	26.4	26.8	27.2	27.6
92.5°	30.7	30.9	31.1	31.3
95°	35.0	35.0	35.0	35.0
97.5°	37.1	37.3	37.5	37.7
100°	38.0	38.2	38.5	38.7
102.5°	38.3	38.8	39.2	39.6
105°	39.3	39.7	40.1	40.5
107.5°	176.1	149.3	122.5	95.7
110°	340.8	311.6	282.3	253.1



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	480.7	480.3	479.9	479.5
115°	538.7	539.5	540.4	541.2
117.5°	590.3	590.5	590.7	590.9
120°	642.4	642.4	642.4	642.4
122.5°	692.4	692.6	692.8	693.0
125°	738.7	739.2	739.6	740.0
127.5°	787.2	786.8	786.4	786.0
130°	831.4	831.0	830.6	830.2
132.5°	872.5	871.9	871.3	870.7
135°	913.9	913.3	912.7	912.1
137.5°	952.9	952.5	952.1	951.7
140°	987.9	987.4	987.0	986.6
142.5°	1020.7	1020.1	1019.5	1018.8
145°	1052.0	1052.0	1052.0	1052.0
147.5°	1079.0	1078.0	1076.9	1075.9
150°	1105.4	1104.7	1104.1	1103.5
152.5°	1128.7	1127.7	1126.6	1125.6
155°	1149.5	1148.3	1147.1	1145.9
157.5°	1168.2	1166.6	1165.0	1163.3
160°	1184.2	1182.8	1181.3	1179.9
162.5°	1199.2	1198.0	1196.8	1195.6
165°	1211.8	1210.4	1208.9	1207.5
167.5°	1221.6	1220.0	1218.4	1216.7
170°	1229.9	1228.3	1226.6	1225.0
172.5°	1235.1	1233.3	1231.4	1229.6
175°	1239.1	1237.5	1235.8	1234.2
177.5°	1241.3	1239.2	1237.2	1235.1
180°	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P832209

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.53	9.23	9.62	10.31	11.80	13.19	13.89	14.29	14.98	16.47
	3H	9.74	10.36	10.84	11.46	12.97	14.68	15.31	15.78	16.40	17.91
	4H	10.12	10.71	11.23	11.81	13.32	15.17	15.76	16.28	16.85	18.37
	6H	10.39	10.94	11.51	12.04	13.56	15.47	16.02	16.59	17.11	18.64
	8H	10.48	10.99	11.60	12.11	13.63	15.55	16.06	16.67	17.18	18.70
	12H	10.52	11.02	11.65	12.12	13.66	15.57	16.07	16.70	17.17	18.71
4H	2H	9.23	9.83	10.36	10.92	12.44	13.17	13.76	14.29	14.86	16.37
	3H	10.59	11.09	11.72	12.21	13.73	14.82	15.31	15.94	16.43	17.96
	4H	11.04	11.50	12.17	12.61	14.15	15.42	15.87	16.55	16.98	18.53
	6H	11.41	11.79	12.54	12.93	14.47	15.85	16.24	16.99	17.37	18.91
	8H	11.53	11.89	12.66	13.02	14.57	15.98	16.34	17.12	17.47	19.02
	12H	11.60	11.93	12.75	13.07	14.62	16.04	16.36	17.19	17.50	19.06
8H	4H	11.35	11.71	12.48	12.84	14.39	15.38	15.74	16.51	16.87	18.42
	6H	11.81	12.11	12.97	13.28	14.83	15.87	16.17	17.03	17.34	18.89
	8H	12.00	12.26	13.16	13.41	14.98	16.06	16.32	17.22	17.46	19.03
	12H	12.14	12.37	13.30	13.51	15.12	16.17	16.39	17.33	17.54	19.15
12H	4H	11.35	11.68	12.51	12.82	14.38	15.32	15.65	16.47	16.79	18.35
	6H	11.87	12.13	13.03	13.28	14.85	15.84	16.10	17.01	17.25	18.82
	8H	12.08	12.31	13.25	13.45	15.06	16.03	16.26	17.20	17.41	19.01