

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332324-927

Luminaire Tested: **S123RDIP-S775D1195U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332324-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6193.5 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	40	40	34
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	1.5
10°-20°	297.7	4.8
20°-30°	467.6	7.6
30°-40°	487.9	7.9
40°-50°	417.5	6.7
50°-60°	318.2	5.1
60°-70°	204.0	3.3
70°-80°	98.1	1.6
80°-90°	29.4	0.5
90°-100°	45.0	0.7
100°-110°	214.7	3.5
110°-120°	515.6	8.3
120°-130°	656.6	10.6
130°-140°	701.5	11.3
140°-150°	656.0	10.6
150°-160°	529.2	8.5
160°-170°	341.5	5.5
170°-180°	117.7	1.9
0°-30°	860.6	13.9
0°-40°	1348.4	21.8
0°-60°	2084.2	33.7
0°-90°	2415.7	39.0
90°-120°	775.3	12.5
90°-150°	2789.4	45.0
90°-180°	3778.0	61.0
0°-180°	6193.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	28	1	28	1	28	13
95°	35	56	35	56	35	29
105°	40	274	40	274	40	93
115°	541	514	541	514	541	500
125°	740	725	740	725	740	661
135°	912	903	912	903	912	703
145°	1052	1042	1052	1042	1052	657
155°	1146	1148	1146	1148	1146	528
165°	1208	1210	1208	1210	1208	341
175°	1234	1239	1234	1239	1234	117
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	8.9	9.4	8.7	9.0	8.9	9.0	8.9	8.7	9.2	8.7	8.6
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7	22.9	22.1	19.4
92.5°	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1	24.9	23.5	21.5
95°	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4	29.9	28.5	26.3
97.5°	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9	31.3	29.6	44.4
100°	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7	32.0	30.3	62.3
102.5°	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4	55.5	60.5	95.4
105°	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1	165.3	201.5	220.0
107.5°	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3	342.9	369.5	366.5
110°	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6	408.4	415.1	412.8



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7	461.6	461.4	459.2
115°	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3	530.4	528.3	526.5
117.5°	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4	594.7	593.1	592.2
120°	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3	636.7	635.0	634.5
122.5°	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3	678.2	677.0	676.2
125°	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1	736.7	736.3	735.5
127.5°	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0	794.4	793.7	792.7
130°	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0	829.2	828.3	827.5
132.5°	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1	862.3	861.5	860.8
135°	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1	911.2
137.5°	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1	957.0	956.1	955.6
140°	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4	985.6	984.8	984.2
142.5°	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4	1012.7	1012.0	1011.5
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0	1050.5	1050.1	1049.7
147.5°	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7	1084.3	1083.8	1083.4
150°	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3	1104.9	1104.5	1104.1
152.5°	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6	1122.8	1122.1	1121.9
155°	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8	1147.8	1146.8	1146.6
157.5°	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8	1169.6	1168.3	1168.5
160°	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3	1182.1	1180.8	1181.1
162.5°	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7	1193.3	1191.8	1192.1
165°	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9	1208.2	1206.6	1206.8
167.5°	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4	1218.4
170°	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0	1225.0
172.5°	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7	1231.1	1229.4	1229.2
175°	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0	1236.6	1235.1	1234.9
177.5°	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9	1238.7	1237.3	1237.2
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	8.6	7.8	7.9	7.4	8.1	8.0	9.6	10.8	11.6	10.6	11.0
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1	16.6	16.0	15.4
95°	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2	47.8	39.4	31.0
97.5°	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8	109.1	105.3	101.6
100°	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5	159.6	163.7	167.8
102.5°	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1	207.1	210.0	212.9
105°	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3	276.6	278.8	281.0
107.5°	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2	350.1	351.9	353.6
110°	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6	399.3	400.8	402.5



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7	446.2	447.7	449.2
115°	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5	515.7	516.9	518.2
117.5°	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0	583.5	585.0	586.6
120°	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0	625.8	627.7	629.5
122.5°	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7	668.2	669.7	671.2
125°	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2	726.9	728.5	730.2
127.5°	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0	783.5	785.2	786.9
130°	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3	819.0	820.5	822.2
132.5°	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1	852.8	854.4	856.0
135°	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9	904.1	905.3	906.6
137.5°	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1	948.6	950.1	951.7
140°	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5	977.7	979.0	980.2
142.5°	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8	1005.0	1006.2	1007.4
145°	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9	1043.3	1044.7	1046.2
147.5°	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8	1078.7	1079.7	1080.5
150°	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9	1100.4	1101.1	1101.7
152.5°	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7	1120.0	1120.3	1120.5
155°	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7	1147.3	1146.8	1146.4
157.5°	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4	1169.3	1169.3	1169.3
160°	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6	1182.5	1182.3	1182.1
162.5°	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2	1194.7	1194.1	1193.6
165°	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3	1209.7	1209.0	1208.5
167.5°	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1	1221.2	1220.4	1219.6
170°	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7	1227.9	1227.1	1226.2
172.5°	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1	1232.2	1231.1	1230.2
175°	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8	1237.8	1236.8	1235.7
177.5°	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3	1239.4	1238.7	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	11.1	12.6	13.5	14.3	15.1	15.4	15.8	16.0	16.6	16.7	16.8
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7	24.6	25.3	26.0
92.5°	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1	27.5	28.8	29.5
95°	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4	32.8	34.2	34.9
97.5°	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9	34.5	36.2	37.1
100°	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7	35.3	36.9	37.9
102.5°	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4	45.3	40.2	37.9
105°	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1	92.9	56.7	38.9
107.5°	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3	289.8	263.2	236.3
110°	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6	394.8	388.1	370.1



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7	461.8	462.0	458.9
115°	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3	534.4	536.5	537.9
117.5°	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4	598.0	599.6	600.6
120°	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3	639.9	641.6	642.4
122.5°	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3	680.5	681.6	682.2
125°	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1	737.5	737.9	738.3
127.5°	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0	795.7	796.3	796.5
130°	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0	830.8	831.6	831.8
132.5°	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1	864.0	864.7	864.8
135°	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3	913.9	914.6	914.6
137.5°	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1	959.0	960.0	960.3
140°	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4	987.2	988.1	988.2
142.5°	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4	1014.0	1014.6	1014.7
145°	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0	1051.4	1051.8	1051.9
147.5°	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7	1085.1	1085.4	1085.2
150°	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3	1105.6	1106.0	1106.0
152.5°	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6	1124.3	1125.1	1125.0
155°	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8	1149.9	1150.9	1150.7
157.5°	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8	1172.0	1173.2	1173.1
160°	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3	1184.5	1185.7	1185.7
162.5°	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7	1196.0	1197.5	1197.5
165°	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9	1211.5	1213.1	1213.2
167.5°	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0
170°	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5
172.5°	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7	1234.3	1236.0	1235.9
175°	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0	1239.4	1240.9	1240.7
177.5°	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9	1241.3	1242.5	1242.4
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	17.6	17.0	17.0	17.4	17.0	17.0	17.6	16.8	16.7	16.6	16.0
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7
92.5°	29.8	30.1	30.3	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1
95°	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4
97.5°	37.3	37.5	37.7	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9
100°	38.0	38.3	38.4	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7
102.5°	38.3	38.7	39.1	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4
105°	39.3	39.7	40.1	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1
107.5°	209.1	181.7	154.5	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3
110°	340.9	311.6	282.3	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.7	446.6	440.4	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7
115°	538.7	539.6	540.3	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3
117.5°	600.7	600.9	601.0	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4
120°	642.4	642.4	642.4	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3
122.5°	682.4	682.5	682.8	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3
125°	738.7	739.2	739.6	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1
127.5°	796.1	795.7	795.3	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0
130°	831.4	831.0	830.6	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0
132.5°	864.3	863.7	863.2	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1
135°	913.9	913.3	912.7	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3
137.5°	959.9	959.5	959.1	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1
140°	987.9	987.5	987.1	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4
142.5°	1014.2	1013.5	1013.0	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0
147.5°	1084.3	1083.3	1082.4	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7
150°	1105.3	1104.8	1104.1	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3
152.5°	1124.0	1123.1	1122.1	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6
155°	1149.5	1148.3	1147.1	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8
157.5°	1171.5	1169.8	1168.2	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8
160°	1184.2	1182.8	1181.3	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3
162.5°	1196.2	1194.9	1193.7	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7
165°	1211.8	1210.4	1208.9	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9
167.5°	1223.3	1221.6	1220.0	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6
170°	1229.9	1228.3	1226.6	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3
172.5°	1234.1	1232.3	1230.5	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7
175°	1239.1	1237.5	1235.9	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0
177.5°	1240.8	1239.1	1237.5	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	15.8	15.4	15.1	14.3	13.5	12.6	11.1	11.0	10.6	11.6	10.8
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	24.9	23.5	21.5	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1
95°	29.9	28.5	26.3	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2
97.5°	31.3	29.6	44.4	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8
100°	32.0	30.3	62.3	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5
102.5°	55.5	60.5	95.4	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1
105°	165.3	201.5	220.0	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3
107.5°	342.9	369.5	366.5	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2
110°	408.4	415.1	412.8	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	461.6	461.4	459.2	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7
115°	530.4	528.3	526.5	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5
117.5°	594.7	593.1	592.2	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0
120°	636.7	635.0	634.5	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0
122.5°	678.2	677.0	676.2	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7
125°	736.7	736.3	735.5	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2
127.5°	794.4	793.7	792.7	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0
130°	829.2	828.3	827.5	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3
132.5°	862.3	861.5	860.8	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1
135°	912.7	912.1	911.2	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9
137.5°	957.0	956.1	955.6	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1
140°	985.6	984.8	984.2	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5
142.5°	1012.7	1012.0	1011.5	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8
145°	1050.5	1050.1	1049.7	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9
147.5°	1084.3	1083.8	1083.4	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8
150°	1104.9	1104.5	1104.1	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9
152.5°	1122.8	1122.1	1121.9	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7
155°	1147.8	1146.8	1146.6	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7
157.5°	1169.6	1168.3	1168.5	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4
160°	1182.1	1180.8	1181.1	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6
162.5°	1193.3	1191.8	1192.1	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2
165°	1208.2	1206.6	1206.8	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3
167.5°	1220.0	1218.4	1218.4	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1
170°	1226.6	1225.0	1225.0	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7
172.5°	1231.1	1229.4	1229.2	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1
175°	1236.6	1235.1	1234.9	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8
177.5°	1238.7	1237.3	1237.2	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.6	8.0	8.1	7.4	7.9	7.8	8.6	8.6	8.7	9.2	8.7
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7
92.5°	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1
95°	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4
97.5°	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9
100°	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7
102.5°	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4
105°	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1
107.5°	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3
110°	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7
115°	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3
117.5°	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4
120°	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3
122.5°	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3
125°	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1
127.5°	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0
130°	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0
132.5°	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1
135°	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3
137.5°	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1
140°	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4
142.5°	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4
145°	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0
147.5°	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7
150°	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3
152.5°	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6
155°	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8
157.5°	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8
160°	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3
162.5°	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7
165°	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9
167.5°	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6
170°	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3
172.5°	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7
175°	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0
177.5°	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	8.9	9.0	8.9	9.0	8.7	9.4	8.9
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	394.8	388.1	370.1	340.9	311.6	282.3	253.1



TEST NUMBER: P332324-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)