

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332329-927

Luminaire Tested: **S123RDIP-S775D1195U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332329-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5734.8 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332329-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332329-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																				
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34																				
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29																				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30	25																				
4	73	63	55	49	66	58	51	46	48	43	39	38	35	32	30	28	26	22																				
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	25	22	19																				
6	62	50	42	37	56	46	39	34	39	33	29	31	27	25	25	22	20	17																				
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13																				
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12																				
10	46	34	27	23	42	32	26	21	27	22	19	22	18	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11009	11009	11009
5°	11051	10899	10962
10°	10989	10762	10726
15°	10871	10510	10399
20°	10709	10195	9958
25°	10542	9841	9526
30°	10320	9434	8918
35°	10093	9025	8360
40°	9884	8543	7669
45°	9608	8068	7046
50°	9306	7529	6348
55°	8997	6912	5697
60°	8714	6250	4982
65°	8344	5535	4266
70°	7884	4648	3446
75°	7207	3656	3244
80°	6428	3242	2982
85°	5434	2865	2655



TEST NUMBER: P332329-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	1.7
10°-20°	267.2	4.7
20°-30°	384.8	6.7
30°-40°	433.4	7.6
40°-50°	414.6	7.2
50°-60°	339.6	5.9
60°-70°	229.1	4.0
70°-80°	115.3	2.0
80°-90°	34.0	0.6
90°-100°	253.0	4.4
100°-110°	716.5	12.5
110°-120°	704.8	12.3
120°-130°	562.2	9.8
130°-140°	443.3	7.7
140°-150°	330.8	5.8
150°-160°	230.6	4.0
160°-170°	135.5	2.4
170°-180°	44.1	0.8
0°-30°	748.0	13.0
0°-40°	1181.5	20.6
0°-60°	1935.6	33.8
0°-90°	2314.0	40.4
90°-120°	1674.3	29.2
90°-150°	3010.6	52.5
90°-180°	3421.0	59.7
0°-180°	5734.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1023	1023	1023	1023	1023	
5°	1023	1018	1009	1016	1014	97
15°	976	966	943	939	933	275
25°	888	866	829	812	802	408
35°	768	737	687	652	636	481
45°	631	592	530	484	463	487
55°	479	437	368	322	304	430
65°	328	281	217	178	168	324
75°	173	133	88	80	78	185
85°	44	27	23	22	22	49
90°	2	11	23	26	27	4
95°	31	102	546	159	107	34
105°	107	158	740	1294	1171	113
115°	189	235	566	1241	1424	187
125°	262	310	528	957	1123	233
135°	307	367	521	788	910	237
145°	351	402	514	647	712	220
155°	398	430	498	566	590	183
165°	435	448	477	506	514	123
175°	454	454	457	464	463	43
180°	455	455	455	455	455	



TEST NUMBER: P332329-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1026.0	1025.5	1024.8	1024.3	1023.7	1022.5	1020.7	1019.0	1017.2	1015.4	1017.1
5°	1022.8	1021.8	1020.9	1020.0	1019.1	1017.5	1015.3	1013.0	1010.8	1008.7	1010.3
7.5°	1013.3	1012.3	1011.3	1010.3	1009.3	1007.3	1004.5	1001.6	998.8	995.9	996.8
10°	1005.4	1004.0	1002.7	1001.5	1000.1	997.8	994.5	991.3	987.9	984.6	984.8
12.5°	994.0	992.6	991.2	989.8	988.3	985.6	981.5	977.5	973.4	969.3	969.2
15°	975.5	973.4	971.4	969.4	967.3	963.8	958.6	953.5	948.2	943.1	942.2
17.5°	952.0	949.7	947.4	945.0	942.6	938.2	931.6	925.0	918.5	912.0	910.0
20°	934.9	931.8	928.9	926.0	923.1	918.1	911.0	904.0	897.1	890.0	887.6
22.5°	915.6	912.2	908.8	905.4	902.0	896.6	889.1	881.7	874.3	866.8	863.8
25°	887.6	883.0	878.3	873.7	869.1	862.5	854.1	845.6	837.1	828.6	824.7
27.5°	853.5	848.4	843.4	838.3	833.2	825.9	816.5	807.1	797.6	788.1	782.8
30°	830.3	824.7	819.3	813.7	808.2	800.3	790.0	779.6	769.3	759.0	752.7
32.5°	807.1	800.8	794.6	788.3	782.0	773.4	762.5	751.6	740.7	729.8	722.9
35°	768.1	761.4	754.8	748.2	741.6	732.5	721.1	709.6	698.2	686.8	678.9
37.5°	728.6	721.2	713.8	706.5	699.1	689.4	677.2	665.0	652.8	640.6	631.5
40°	703.4	695.3	687.1	679.1	671.0	660.4	647.3	634.2	621.1	608.0	598.4
42.5°	674.9	666.8	658.6	650.5	642.5	631.6	618.1	604.5	591.0	577.5	567.0
45°	631.2	623.0	614.7	606.3	598.0	586.8	572.6	558.4	544.2	530.0	519.5
47.5°	587.6	578.5	569.4	560.3	551.2	539.6	525.4	511.1	496.9	482.8	471.3
50°	555.7	547.1	538.4	529.7	521.1	509.3	494.4	479.4	464.5	449.6	438.2
52.5°	527.2	517.8	508.4	499.0	489.6	477.5	462.7	448.0	433.2	418.4	406.5
55°	479.4	470.4	461.4	452.3	443.3	430.9	415.3	399.7	384.0	368.3	357.6
57.5°	435.3	425.5	415.7	405.8	395.9	383.2	367.4	351.6	335.9	320.2	310.1
60°	404.8	394.7	384.5	374.4	364.2	351.5	336.2	320.9	305.6	290.3	280.4
62.5°	374.2	364.1	353.9	343.8	333.7	321.0	305.7	290.4	275.1	259.8	250.4
65°	327.6	317.5	307.4	297.2	287.1	274.8	260.5	246.1	231.7	217.3	208.3
67.5°	281.1	270.8	260.5	250.3	240.0	228.0	214.2	200.4	186.6	172.9	166.1
70°	250.5	240.6	230.6	220.6	210.7	199.2	186.3	173.5	160.6	147.7	141.2
72.5°	220.0	210.2	200.3	190.5	180.8	170.0	158.3	146.6	134.8	123.1	117.8
75°	173.3	164.5	155.7	146.8	138.0	128.5	118.4	108.2	98.1	87.9	86.1
77.5°	130.9	122.9	114.9	106.9	98.9	91.7	85.1	78.6	72.1	65.5	64.6
80°	103.7	96.1	88.6	81.0	73.4	67.7	63.8	60.0	56.2	52.3	51.7
82.5°	77.8	71.3	64.7	58.2	51.7	47.5	45.7	43.9	42.1	40.3	39.8
85°	44.0	39.9	35.9	31.8	27.7	25.4	24.9	24.3	23.8	23.2	22.9
87.5°	16.3	15.1	13.8	12.8	11.5	11.0	11.6	12.1	12.7	13.2	12.9
90°	1.8	3.6	5.5	8.3	10.1	12.0	14.7	17.5	20.3	23.0	22.1
92.5°	11.4	17.0	24.6	31.8	39.6	53.2	77.3	116.9	155.7	141.6	106.8
95°	31.3	34.1	44.2	59.8	83.7	119.6	197.9	335.0	486.0	545.8	442.7
97.5°	53.4	54.3	62.2	75.8	99.4	138.2	213.0	367.6	619.2	845.8	904.9
100°	68.1	69.0	75.5	88.3	110.4	146.3	210.8	347.0	589.1	871.6	1053.0
102.5°	83.6	85.2	90.9	103.1	122.9	155.9	213.7	329.3	544.9	823.8	1060.3
105°	106.8	109.6	115.0	126.1	143.5	172.1	221.8	316.6	490.6	740.0	1004.2
107.5°	131.4	134.2	139.5	150.4	166.8	193.3	236.9	315.7	456.0	666.0	905.9
110°	149.1	151.9	156.5	166.6	182.2	208.0	249.5	319.4	442.7	624.0	844.0



TEST NUMBER: P332329-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.3	168.1	172.7	182.8	198.4	223.5	262.0	326.8	435.4	596.0	790.3
115°	188.7	192.3	197.9	207.1	222.8	247.6	282.6	338.7	432.6	566.0	725.2
117.5°	212.1	216.3	220.9	229.3	246.8	269.9	304.4	354.5	434.3	548.3	686.0
120°	228.2	231.0	235.6	244.9	262.3	285.3	318.5	366.3	437.2	540.3	665.4
122.5°	242.2	245.0	249.6	259.5	276.3	300.8	333.2	377.4	442.4	535.1	648.5
125°	262.3	264.2	269.7	279.8	297.3	322.1	354.3	394.8	450.0	528.3	626.8
127.5°	277.6	280.4	287.2	297.5	316.8	341.7	372.7	409.2	458.9	525.0	607.7
130°	287.2	289.9	298.2	309.3	328.6	353.4	383.8	418.7	464.8	522.8	597.3
132.5°	294.5	298.0	307.0	320.3	339.6	363.8	393.4	427.6	469.2	522.0	587.8
135°	307.4	311.1	321.2	335.0	354.3	379.2	407.7	439.0	475.9	520.9	575.3
137.5°	319.6	323.4	333.4	348.1	367.3	390.2	417.6	447.5	480.3	518.9	564.4
140°	327.6	332.2	341.4	356.2	374.6	397.6	424.3	451.9	483.2	518.2	557.8
142.5°	336.5	340.4	350.3	363.5	382.0	403.5	429.4	456.3	485.4	516.7	551.8
145°	350.7	353.4	361.7	375.5	391.2	412.3	436.3	461.1	486.9	514.5	544.0
147.5°	365.0	366.7	374.8	386.7	401.9	419.9	441.8	464.1	486.9	511.0	536.2
150°	374.6	375.5	382.9	394.8	407.7	424.3	445.4	464.8	486.9	508.0	531.1
152.5°	384.2	384.4	391.7	402.2	413.6	429.4	447.7	466.3	484.7	504.4	525.2
155°	398.5	398.5	404.1	413.3	423.3	436.3	451.9	466.7	482.3	498.0	516.3
157.5°	410.0	410.7	415.1	423.2	431.8	441.8	454.3	467.5	479.2	492.3	506.4
160°	418.7	418.7	422.5	429.8	436.3	445.4	456.5	467.5	477.7	487.8	499.8
162.5°	425.4	425.4	428.3	434.3	440.0	447.7	457.2	466.8	474.8	483.4	493.1
165°	435.4	434.4	436.3	440.8	444.6	451.0	458.4	464.8	470.3	476.7	484.1
167.5°	442.9	441.8	442.7	446.2	448.8	452.8	458.2	463.3	465.9	470.2	475.5
170°	447.3	445.4	446.4	449.2	451.0	452.8	457.4	461.1	463.0	465.7	470.3
172.5°	450.3	449.2	449.3	451.4	452.5	453.6	457.4	460.4	460.7	462.0	465.2
175°	453.8	452.8	451.9	453.8	453.8	454.7	456.5	458.4	457.4	457.4	459.3
177.5°	455.4	454.7	453.9	454.7	454.7	454.7	455.4	456.9	455.4	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332329-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1018.7	1020.3	1021.9	1022.6	1022.3	1022.0	1021.7	1021.4
5°	1011.9	1013.6	1015.3	1015.9	1015.6	1015.2	1014.8	1014.5
7.5°	997.8	998.6	999.6	999.7	999.1	998.5	997.8	997.2
10°	985.0	985.2	985.3	985.0	984.0	983.1	982.2	981.3
12.5°	969.1	969.0	968.9	968.3	967.3	966.1	965.1	964.0
15°	941.3	940.3	939.4	938.3	937.1	935.7	934.5	933.2
17.5°	908.0	906.1	904.1	902.2	900.2	898.3	896.4	894.5
20°	885.3	882.8	880.4	878.1	875.9	873.7	871.5	869.3
22.5°	860.9	857.9	854.8	852.3	850.2	848.2	846.1	844.1
25°	820.9	817.1	813.2	810.2	808.2	806.1	804.1	802.1
27.5°	777.4	772.1	766.7	762.4	759.3	756.2	753.1	750.0
30°	746.5	740.1	733.9	729.3	726.4	723.4	720.4	717.5
32.5°	716.1	709.2	702.3	697.4	694.3	691.2	688.1	685.0
35°	671.0	663.1	655.1	649.5	646.2	642.9	639.5	636.2
37.5°	622.5	613.5	604.5	598.0	593.9	589.8	585.7	581.6
40°	588.8	579.2	569.7	562.8	558.5	554.3	550.0	545.8
42.5°	556.5	546.1	535.6	528.5	524.7	520.9	517.1	513.3
45°	509.1	498.5	488.0	480.5	476.1	471.7	467.3	462.9
47.5°	459.9	448.5	437.0	429.4	425.4	421.4	417.6	413.6
50°	426.7	415.3	403.9	396.0	391.8	387.5	383.3	379.1
52.5°	394.7	382.8	370.9	363.1	359.3	355.5	351.6	347.8
55°	346.9	336.2	325.5	318.3	314.7	310.9	307.3	303.6
57.5°	300.0	289.9	279.8	273.1	270.1	266.9	263.7	260.6
60°	270.4	260.5	250.5	244.0	240.8	237.7	234.6	231.4
62.5°	241.1	231.7	222.4	216.0	212.7	209.5	206.2	202.9
65°	199.2	190.2	181.2	175.6	173.6	171.6	169.6	167.5
67.5°	159.4	152.7	145.8	141.4	139.3	137.0	134.9	132.7
70°	134.8	128.3	121.8	117.6	115.6	113.5	111.5	109.5
72.5°	112.6	107.3	102.0	98.9	98.1	97.3	96.4	95.5
75°	84.2	82.4	80.6	79.5	79.1	78.7	78.3	78.0
77.5°	63.5	62.5	61.6	60.8	60.5	60.1	59.7	59.4
80°	51.2	50.6	50.1	49.6	49.2	48.9	48.5	48.1
82.5°	39.2	38.7	38.1	37.8	37.7	37.6	37.5	37.5
85°	22.5	22.1	21.8	21.5	21.5	21.5	21.5	21.5
87.5°	12.9	13.0	13.0	13.2	12.9	12.9	13.0	12.7
90°	23.0	23.9	24.9	26.7	25.7	26.7	27.6	26.7
92.5°	77.5	61.5	54.3	49.5	47.8	45.1	46.0	44.4
95°	331.4	224.6	175.8	142.7	125.2	116.9	110.4	106.8
97.5°	825.9	661.6	542.9	432.8	364.9	323.4	298.6	290.7
100°	1085.1	1010.6	902.9	772.2	679.2	612.0	576.2	577.1
102.5°	1171.3	1168.9	1106.1	1023.3	950.9	897.8	867.8	846.6
105°	1196.5	1288.6	1306.1	1282.1	1239.8	1204.8	1175.4	1170.8
107.5°	1123.9	1273.4	1354.1	1386.9	1387.6	1375.8	1365.9	1357.4
110°	1054.8	1224.2	1340.1	1404.5	1430.3	1437.7	1435.8	1434.0



TEST NUMBER: P332329-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	986.3	1159.4	1289.3	1372.1	1419.3	1442.1	1449.1	1449.5
115°	895.6	1055.7	1191.0	1291.3	1360.3	1400.8	1419.3	1423.9
117.5°	829.8	968.0	1089.6	1191.4	1263.4	1309.7	1336.3	1342.5
120°	795.2	919.5	1029.9	1122.9	1195.6	1247.1	1269.2	1274.8
122.5°	767.9	880.4	982.8	1069.1	1133.8	1180.1	1204.4	1211.4
125°	731.7	832.0	920.4	994.0	1053.0	1093.4	1116.4	1122.9
127.5°	700.1	789.5	869.2	936.2	988.7	1023.3	1044.1	1050.0
130°	680.2	763.0	837.6	900.2	949.0	982.1	1001.4	1008.8
132.5°	661.8	738.0	807.4	867.0	912.8	945.9	963.1	968.3
135°	636.9	702.3	762.1	814.5	859.7	887.2	903.8	910.3
137.5°	614.3	667.8	719.4	764.9	802.8	830.8	844.7	849.0
140°	601.0	647.9	692.1	731.7	766.7	792.5	807.2	806.3
142.5°	588.5	628.8	667.1	701.6	731.3	754.2	767.4	766.5
145°	573.4	603.8	633.3	659.9	682.9	702.3	709.6	711.5
147.5°	561.1	585.2	609.0	627.9	645.4	658.5	665.4	666.1
150°	552.2	573.4	592.7	610.2	624.0	634.1	639.7	639.7
152.5°	544.2	562.4	579.5	594.1	604.9	614.3	617.6	617.6
155°	532.0	546.7	560.5	571.6	579.9	587.2	589.1	589.9
157.5°	519.1	531.5	542.1	550.7	557.9	563.5	564.9	564.7
160°	511.7	521.9	531.1	537.5	544.0	549.5	549.5	548.6
162.5°	502.9	511.6	520.0	525.7	530.0	534.7	534.7	533.9
165°	491.5	497.0	503.4	508.0	511.7	515.4	514.5	514.5
167.5°	481.6	485.8	489.5	492.8	494.4	497.0	496.1	496.1
170°	474.9	477.7	481.3	483.2	484.1	486.0	485.1	485.1
172.5°	469.1	471.0	474.0	475.1	475.3	477.1	475.5	474.8
175°	461.1	462.0	463.9	463.9	463.9	464.8	463.9	463.0
177.5°	456.1	456.9	457.6	457.6	456.9	457.6	456.1	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

(END OF REPORT)