

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331626-935

Luminaire Tested: **S122RDIP-S290D530U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331626-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D530U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2668.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331626-935

CATALOG NUMBER: S122RDIP-S290D530U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331626-935

CATALOG NUMBER: S122RDIP-S290D530U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331626-935

CATALOG NUMBER: S122RDIP-S290D530U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	1.5
10°-20°	111.1	4.2
20°-30°	156.0	5.8
30°-40°	170.1	6.4
40°-50°	156.4	5.9
50°-60°	122.8	4.6
60°-70°	80.1	3.0
70°-80°	41.3	1.5
80°-90°	13.0	0.5
90°-100°	102.1	3.8
100°-110°	346.4	13.0
110°-120°	368.0	13.8
120°-130°	303.0	11.4
130°-140°	243.3	9.1
140°-150°	183.9	6.9
150°-160°	129.2	4.8
160°-170°	76.1	2.9
170°-180°	24.8	0.9
0°-30°	307.5	11.5
0°-40°	477.6	17.9
0°-60°	756.8	28.4
0°-90°	891.2	33.4
90°-120°	816.6	30.6
90°-150°	1546.7	58.0
90°-180°	1777.0	66.6
0°-180°	2668.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	0	7	17	16	16	2
95°	17	42	192	73	56	18
105°	60	90	364	650	553	64
115°	106	133	304	628	728	105
125°	147	174	293	509	591	131
135°	173	206	289	428	490	133
145°	197	227	288	357	391	124
155°	224	242	279	316	328	103
165°	244	252	268	284	288	69
175°	255	255	257	260	260	24
180°	255	255	255	255	255	



TEST NUMBER: P331626-935

CATALOG NUMBER: S122RDIP-S290D530U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.1	4.8	4.6	4.3	4.0	4.0	4.5	5.2	5.8	5.9	5.7
90°	0.5	2.0	4.0	4.9	5.9	7.4	9.8	13.3	16.2	16.7	16.2
92.5°	6.0	8.6	12.1	14.4	17.7	22.3	33.4	49.0	62.9	63.8	53.9
95°	17.2	19.1	24.0	28.5	36.3	48.1	70.7	113.4	170.4	192.5	168.4
97.5°	28.0	30.7	35.8	42.5	51.6	64.9	93.3	152.8	247.5	328.6	344.7
100°	37.8	39.3	43.7	51.6	61.4	75.2	101.2	161.1	267.1	387.9	458.6
102.5°	46.8	48.0	52.3	60.2	70.4	84.1	108.2	161.4	259.7	389.9	501.0
105°	59.9	61.9	65.3	72.7	83.4	97.2	120.3	164.0	245.0	363.9	494.5
107.5°	74.0	75.6	79.0	85.8	96.4	110.3	132.7	170.7	237.7	336.0	451.3
110°	83.4	85.4	88.4	94.8	105.0	119.3	140.9	176.2	236.2	322.6	424.2



TEST NUMBER: P331626-935

CATALOG NUMBER: S122RDIP-S290D530U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	92.1	94.1	97.4	103.4	113.3	127.9	148.8	182.2	236.6	313.9	405.4
115°	105.6	108.1	111.0	116.8	126.7	139.9	161.1	191.0	238.7	304.4	382.0
117.5°	119.5	121.5	124.4	129.7	139.1	152.8	172.4	200.4	242.2	299.8	367.3
120°	128.1	130.1	133.0	137.5	147.3	161.1	180.2	206.7	244.5	297.0	359.5
122.5°	136.4	138.0	140.9	145.8	155.6	169.7	187.7	212.2	247.3	295.5	352.8
125°	147.3	148.8	151.7	157.6	167.5	181.2	198.9	220.9	251.4	292.7	343.2
127.5°	155.9	157.9	162.0	168.5	178.0	192.1	209.3	229.1	255.6	291.0	334.4
130°	161.1	163.0	167.9	174.8	184.6	198.4	215.6	234.2	258.7	290.2	328.5
132.5°	165.7	168.2	173.4	180.7	190.9	204.7	221.0	239.4	261.9	289.8	323.7
135°	172.8	174.8	180.7	188.0	199.3	213.1	228.9	246.0	265.6	289.2	317.2
137.5°	179.5	181.8	187.8	195.6	206.8	219.6	235.1	251.1	269.0	289.1	312.5
140°	184.6	186.6	192.5	200.4	211.1	223.9	238.7	253.8	270.5	288.7	309.9
142.5°	189.8	191.3	196.8	204.7	215.1	227.0	241.4	256.2	271.7	288.7	307.1
145°	197.4	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	303.4
147.5°	205.6	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.7
150°	211.1	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6
152.5°	216.6	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9
155°	224.4	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7
157.5°	230.8	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9
160°	235.2	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3
162.5°	239.5	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2
165°	244.5	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0
167.5°	248.7	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9
170°	251.4	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2
172.5°	253.0	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4
175°	254.9	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8
177.5°	255.7	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331626-935

CATALOG NUMBER: S122RDIP-S290D530U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	5.5	5.3	5.3	5.4	5.4	5.4	5.4	5.4
90°	15.7	14.7	15.7	16.2	16.2	16.2	16.2	16.2
92.5°	42.8	36.8	32.6	29.5	29.2	27.6	28.0	27.2
95°	128.6	98.7	78.1	67.2	60.9	57.0	55.4	56.0
97.5°	300.2	245.6	192.5	157.0	133.5	121.5	114.3	110.2
100°	448.3	387.4	320.1	260.7	220.0	198.9	184.6	175.8
102.5°	545.4	531.6	482.4	419.4	375.1	339.1	321.3	309.4
105°	596.6	652.0	658.5	642.2	611.8	581.3	560.3	553.4
107.5°	559.6	643.3	694.3	718.1	721.9	720.2	716.0	706.9
110°	527.9	615.7	678.6	718.8	739.9	749.3	753.7	753.2



TEST NUMBER: P331626-935

CATALOG NUMBER: S122RDIP-S290D530U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	498.8	583.2	650.3	696.5	725.8	741.4	749.8	752.4
115°	463.0	538.6	603.0	653.6	688.4	711.0	723.8	728.1
117.5°	436.1	502.5	560.9	608.3	643.9	667.7	681.1	684.8
120°	422.8	483.6	535.7	580.4	614.8	637.8	652.0	656.9
122.5°	412.2	468.0	517.2	557.6	588.4	611.1	623.8	627.9
125°	396.7	447.3	490.5	527.4	555.9	574.5	586.8	590.7
127.5°	381.5	427.3	468.0	502.0	526.8	544.3	554.9	558.1
130°	371.7	414.0	452.7	485.1	509.2	525.9	535.7	539.6
132.5°	362.3	401.4	437.0	467.4	491.1	507.8	516.9	520.4
135°	349.1	381.5	414.0	441.4	462.5	478.7	487.6	489.6
137.5°	338.6	365.8	391.4	415.4	434.6	448.6	456.3	459.3
140°	331.9	355.5	378.1	399.7	415.4	428.2	435.5	438.5
142.5°	326.4	346.5	365.9	384.0	398.9	410.5	417.1	417.7
145°	318.7	334.8	350.1	364.4	376.1	384.4	389.3	390.8
147.5°	312.7	325.5	337.3	347.8	357.5	364.1	367.5	368.3
150°	308.3	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	304.0	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	298.1	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	291.1	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	286.7	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	282.4	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	276.0	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	269.8	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	266.7	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	263.1	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.2	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)