

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331678-935

Luminaire Tested: **S122RDIP-S675D330U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331678-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D330U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3126.0 lumens  
Efficiency: N/A  
Efficacy: 89.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331678-935

CATALOG NUMBER: S122RDIP-S675D330U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331678-935

CATALOG NUMBER: S122RDIP-S675D330U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	49	47	44	41
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39	35
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	41	37	34	31
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30	28
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25	22
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15681	15681	15681
5°	15741	15486	15571
10°	15621	15231	15101
15°	15442	14780	14355
20°	15192	14136	13426
25°	14938	13402	12527
30°	14585	12652	11373
35°	14241	11832	10360
40°	13894	10985	9187
45°	13486	10035	8127
50°	13069	9075	7086
55°	12645	8042	6086
60°	12148	6952	5050
65°	11584	5841	4604
70°	10914	4810	4230
75°	10087	4386	3949
80°	8908	3924	3598
85°	7003	3094	3094



TEST NUMBER: P331678-935

CATALOG NUMBER: S122RDIP-S675D330U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.9	2.9
10°-20°	249.6	8.0
20°-30°	350.5	11.2
30°-40°	382.2	12.2
40°-50°	351.5	11.2
50°-60°	276.0	8.8
60°-70°	180.0	5.8
70°-80°	92.8	3.0
80°-90°	25.0	0.8
90°-100°	12.8	0.4
100°-110°	47.1	1.5
110°-120°	125.8	4.0
120°-130°	207.7	6.6
130°-140°	220.8	7.1
140°-150°	205.3	6.6
150°-160°	165.0	5.3
160°-170°	106.3	3.4
170°-180°	36.6	1.2
0°-30°	691.1	22.1
0°-40°	1073.3	34.3
0°-60°	1700.8	54.4
0°-90°	1998.6	63.9
90°-120°	185.7	5.9
90°-150°	819.5	26.2
90°-180°	1127.0	36.1
0°-180°	3126.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	971	966	956	963	961	92
15°	924	913	884	868	859	260
25°	838	809	752	718	703	385
35°	722	676	600	547	526	452
45°	591	530	440	379	356	456
55°	449	379	286	235	216	401
65°	303	232	153	125	120	300
75°	162	102	70	64	63	171
85°	38	20	17	17	17	45
90°	0	3	6	7	8	2
95°	18	10	11	12	12	22
105°	85	88	17	20	21	90
115°	160	165	172	49	23	158
125°	226	230	235	237	238	202
135°	280	284	287	290	289	216
145°	325	325	329	331	330	203
155°	358	356	358	360	358	165
165°	377	375	376	378	376	106
175°	386	384	384	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P331678-935

CATALOG NUMBER: S122RDIP-S675D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	974.7	974.0	973.2	972.4	971.6	970.3	968.6	966.9	965.3	963.5	965.1
5°	971.2	970.3	969.3	968.3	967.3	965.6	963.0	960.5	957.9	955.5	957.2
7.5°	961.2	960.0	958.8	957.6	956.4	954.2	951.3	948.4	945.4	942.5	942.9
10°	952.8	951.4	950.0	948.6	947.3	944.7	940.7	936.9	933.0	929.0	928.5
12.5°	942.2	940.6	938.8	937.2	935.5	932.2	927.2	922.2	917.1	912.1	911.1
15°	923.8	921.6	919.5	917.3	915.2	910.8	904.1	897.5	890.9	884.2	880.5
17.5°	901.1	897.9	894.6	891.2	887.9	882.1	873.6	865.0	856.5	848.0	843.6
20°	884.2	880.3	876.4	872.5	868.6	861.8	852.0	842.2	832.5	822.7	817.8
22.5°	865.9	861.6	857.2	852.8	848.4	840.8	829.7	818.7	807.7	796.7	790.4
25°	838.5	832.2	826.0	819.8	813.6	803.9	791.1	778.2	765.3	752.3	744.3
27.5°	805.5	798.7	791.9	785.1	778.3	767.6	753.1	738.6	724.0	709.5	700.2
30°	782.3	774.8	767.4	760.0	752.6	741.1	725.4	709.8	694.1	678.6	668.6
32.5°	759.7	751.1	742.4	733.7	725.0	712.7	696.8	680.9	665.0	649.0	637.7
35°	722.5	712.6	702.6	692.6	682.7	669.1	651.9	634.7	617.5	600.3	588.0
37.5°	685.3	674.2	663.3	652.4	641.4	626.8	608.6	590.2	571.9	553.5	540.0
40°	659.2	647.5	635.8	624.1	612.3	597.0	578.1	559.1	540.2	521.2	507.4
42.5°	632.5	620.2	607.8	595.5	583.2	567.1	547.6	528.1	508.4	488.9	474.5
45°	590.6	577.6	564.5	551.4	538.3	521.5	501.0	480.5	459.9	439.5	425.6
47.5°	549.8	536.0	522.1	508.2	494.4	476.9	455.7	434.5	413.4	392.2	378.4
50°	520.3	506.4	492.6	478.7	464.9	447.2	425.7	404.2	382.7	361.3	347.8
52.5°	491.5	477.0	462.5	448.1	433.5	415.8	394.8	373.8	352.8	331.7	318.7
55°	449.2	433.9	418.7	403.5	388.2	370.1	349.0	327.9	306.8	285.7	274.0
57.5°	405.7	390.1	374.4	358.9	343.2	325.3	305.0	284.7	264.4	244.2	233.4
60°	376.2	360.6	344.9	329.3	313.7	295.8	275.7	255.5	235.5	215.3	205.3
62.5°	347.3	331.7	316.1	300.5	284.8	267.4	248.3	229.1	209.9	190.7	181.2
65°	303.2	287.4	271.6	255.8	240.0	223.3	205.7	188.1	170.5	152.9	146.3
67.5°	260.7	245.0	229.3	213.6	197.9	182.1	166.3	150.5	134.7	118.8	115.8
70°	231.2	215.9	200.7	185.5	170.2	155.8	142.4	128.9	115.5	101.9	100.0
72.5°	203.0	188.4	173.8	159.2	144.6	131.9	121.1	110.2	99.4	88.6	87.0
75°	161.7	148.1	134.4	120.7	107.0	96.9	90.2	83.6	77.0	70.3	69.0
77.5°	121.1	109.1	97.1	85.2	73.2	65.5	62.3	59.2	56.0	52.8	51.9
80°	95.8	85.8	75.9	66.0	56.0	50.0	48.0	46.1	44.2	42.2	41.4
82.5°	72.6	64.8	57.1	49.2	41.5	36.9	35.6	34.3	33.0	31.7	31.2
85°	37.8	33.7	29.6	25.5	21.4	19.0	18.4	17.9	17.3	16.7	16.7
87.5°	11.3	10.2	9.0	8.0	6.9	6.4	6.5	6.5	6.6	6.7	6.6
90°	0.3	0.9	1.6	2.3	3.0	3.6	4.0	4.6	5.1	5.6	5.9
92.5°	5.6	5.6	5.5	5.4	5.3	5.5	5.7	5.9	6.2	6.5	6.6
95°	18.1	16.0	14.0	12.0	9.9	9.1	9.6	10.0	10.4	10.8	11.2
97.5°	35.9	30.1	24.4	18.7	12.9	10.5	11.5	12.5	13.5	14.6	14.8
100°	49.2	40.8	32.3	23.8	15.4	11.6	12.7	13.8	14.8	15.8	16.4
102.5°	64.0	62.2	60.4	58.6	56.8	51.5	42.7	33.9	25.1	16.3	17.0
105°	84.6	86.4	88.3	90.2	92.0	84.6	67.7	50.8	33.8	17.0	17.7
107.5°	108.1	109.7	111.2	112.7	114.2	104.8	84.6	64.3	44.0	23.8	23.1
110°	123.3	124.6	126.0	127.3	128.5	120.2	102.4	84.5	66.6	48.7	42.5



TEST NUMBER: P331678-935

CATALOG NUMBER: S122RDIP-S675D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	137.6	138.7	139.9	141.0	142.2	140.5	136.1	131.7	127.3	122.9	100.3
115°	160.1	161.1	162.2	163.2	164.3	165.6	167.1	168.7	170.2	171.8	143.1
117.5°	180.2	181.3	182.5	183.7	184.9	186.0	187.1	188.1	189.2	190.3	183.3
120°	194.8	195.8	196.7	197.7	198.5	199.6	200.7	201.8	202.9	204.1	204.8
122.5°	207.3	208.4	209.3	210.3	211.3	212.3	213.5	214.7	216.0	217.2	217.7
125°	226.4	227.1	227.9	228.8	229.5	230.6	231.7	232.9	234.0	235.2	235.7
127.5°	243.5	244.4	245.3	246.2	247.1	248.0	248.8	249.8	250.6	251.5	252.1
130°	254.4	255.5	256.4	257.4	258.4	259.2	259.9	260.6	261.3	262.0	262.6
132.5°	265.6	266.4	267.3	268.1	269.0	269.7	270.4	271.0	271.7	272.4	273.0
135°	280.1	281.0	282.1	283.0	284.0	284.8	285.3	285.9	286.5	287.1	287.7
137.5°	294.7	295.4	296.1	296.8	297.5	298.2	298.8	299.4	300.1	300.7	301.3
140°	304.3	304.8	305.2	305.7	306.3	306.9	307.5	308.2	308.9	309.5	310.1
142.5°	312.3	312.7	313.1	313.7	314.1	314.7	315.5	316.2	317.0	317.8	318.3
145°	324.9	324.9	324.8	324.7	324.6	325.1	326.1	327.3	328.3	329.3	329.8
147.5°	335.9	335.6	335.4	335.1	334.9	335.3	336.3	337.4	338.5	339.5	339.8
150°	342.9	342.5	342.1	341.6	341.2	341.6	342.5	343.5	344.5	345.5	345.9
152.5°	349.0	348.5	348.0	347.5	347.1	347.2	348.2	349.1	350.1	351.0	351.4
155°	357.7	357.1	356.6	356.0	355.5	355.6	356.4	357.1	357.8	358.5	359.0
157.5°	364.5	364.1	363.6	363.2	362.7	362.7	363.3	363.8	364.3	364.8	365.2
160°	368.6	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.9
162.5°	372.1	371.8	371.4	371.0	370.7	370.7	370.9	371.3	371.6	372.0	372.4
165°	376.9	376.6	376.2	375.8	375.5	375.4	375.6	375.7	375.9	376.1	376.5
167.5°	380.5	380.1	379.8	379.4	379.0	378.9	379.1	379.3	379.4	379.6	380.0
170°	382.5	382.1	381.8	381.4	381.0	380.9	381.0	381.2	381.3	381.4	381.9
172.5°	383.8	383.5	383.1	382.7	382.4	382.2	382.4	382.5	382.6	382.7	383.1
175°	385.6	385.1	384.7	384.3	383.8	383.7	383.8	383.9	384.1	384.2	384.6
177.5°	385.8	385.5	385.1	384.8	384.4	384.4	384.4	384.4	384.4	384.5	384.9
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331678-935

CATALOG NUMBER: S122RDIP-S675D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	966.6	968.2	969.7	970.3	970.1	969.7	969.5	969.1
5°	958.9	960.7	962.4	963.0	962.4	961.8	961.3	960.7
7.5°	943.4	943.9	944.4	944.2	943.1	942.2	941.2	940.1
10°	927.9	927.3	926.7	925.8	924.6	923.5	922.3	921.1
12.5°	910.1	909.0	907.9	906.5	904.5	902.6	900.6	898.6
15°	876.8	873.1	869.4	866.5	864.6	862.6	860.7	858.8
17.5°	839.2	834.7	830.3	826.5	823.1	819.8	816.4	813.0
20°	813.0	808.0	803.1	798.6	794.3	790.0	785.7	781.4
22.5°	784.1	777.8	771.5	766.8	763.5	760.3	757.2	754.0
25°	736.3	728.3	720.3	714.9	712.0	709.0	706.1	703.2
27.5°	690.8	681.5	672.2	665.1	660.5	655.8	651.2	646.5
30°	658.7	648.7	638.7	631.1	625.8	620.5	615.3	610.0
32.5°	626.3	614.9	603.6	595.4	590.4	585.5	580.5	575.6
35°	575.8	563.4	551.1	542.8	538.5	534.2	529.9	525.6
37.5°	526.4	512.9	499.4	490.1	485.2	480.3	475.4	470.5
40°	493.4	479.6	465.7	456.2	451.2	446.1	441.0	435.9
42.5°	460.2	445.8	431.5	421.9	417.0	412.1	407.2	402.2
45°	411.7	397.9	384.0	374.7	370.1	365.3	360.7	355.9
47.5°	364.6	350.9	337.0	328.0	323.7	319.5	315.2	311.0
50°	334.3	320.8	307.4	298.5	294.5	290.3	286.3	282.1
52.5°	305.7	292.7	279.7	271.3	267.5	263.7	259.9	256.1
55°	262.3	250.5	238.8	231.1	227.4	223.6	219.9	216.2
57.5°	222.7	212.0	201.2	194.2	191.1	188.0	184.9	181.8
60°	195.4	185.5	175.5	168.9	165.8	162.7	159.5	156.4
62.5°	171.8	162.2	152.7	147.1	145.2	143.4	141.5	139.6
65°	139.7	133.0	126.4	122.8	122.2	121.6	121.0	120.5
67.5°	112.7	109.7	106.7	104.8	104.2	103.6	103.0	102.3
70°	98.1	96.1	94.1	92.8	92.0	91.2	90.4	89.6
72.5°	85.3	83.7	82.1	81.0	80.5	80.1	79.6	79.1
75°	67.6	66.2	64.8	64.1	63.9	63.7	63.5	63.3
77.5°	51.1	50.4	49.6	49.1	48.7	48.5	48.1	47.8
80°	40.6	39.9	39.1	38.7	38.7	38.7	38.7	38.7
82.5°	30.7	30.2	29.8	29.5	29.5	29.5	29.5	29.5
85°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
87.5°	6.5	6.5	6.4	6.3	6.4	6.4	6.4	6.5
90°	6.2	6.5	6.8	7.1	7.1	7.2	7.4	7.5
92.5°	6.8	7.0	7.1	7.2	7.3	7.4	7.4	7.5
95°	11.5	11.8	12.1	12.2	12.1	12.1	12.1	12.0
97.5°	15.1	15.2	15.5	15.7	15.8	15.8	15.9	16.0
100°	16.9	17.4	17.8	18.2	18.3	18.4	18.5	18.7
102.5°	17.6	18.3	18.9	19.3	19.5	19.6	19.8	20.0
105°	18.3	19.0	19.7	20.1	20.4	20.7	20.9	21.2
107.5°	22.4	21.7	21.0	20.8	21.0	21.3	21.5	21.8
110°	36.3	30.1	23.9	21.0	21.3	21.5	21.8	22.0





TEST NUMBER: P331678-935

CATALOG NUMBER: S122RDIP-S675D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	77.7	55.2	32.6	21.4	21.6	21.8	22.0	22.2
115°	114.5	85.8	57.2	40.6	36.2	31.8	27.3	22.8
117.5°	176.4	169.4	162.6	151.8	137.2	122.5	107.9	93.2
120°	205.5	206.3	207.0	203.2	194.8	186.5	178.1	169.8
122.5°	218.1	218.5	219.0	218.3	216.8	215.2	213.5	211.9
125°	236.1	236.5	236.9	237.3	237.5	237.6	237.8	238.0
127.5°	252.8	253.4	254.0	254.3	254.4	254.4	254.4	254.5
130°	263.3	264.0	264.7	265.0	264.9	264.8	264.8	264.8
132.5°	273.6	274.1	274.7	275.0	274.9	274.9	274.8	274.7
135°	288.3	288.9	289.5	289.7	289.6	289.5	289.4	289.2
137.5°	301.9	302.5	303.1	303.2	303.1	302.9	302.6	302.5
140°	310.6	311.3	311.8	311.9	311.6	311.3	311.0	310.6
142.5°	318.8	319.3	319.9	319.9	319.6	319.3	319.0	318.7
145°	330.2	330.6	331.1	331.1	330.8	330.5	330.2	329.8
147.5°	340.1	340.4	340.8	340.8	340.5	340.3	340.0	339.8
150°	346.2	346.6	347.0	347.0	346.7	346.4	346.0	345.8
152.5°	351.8	352.1	352.5	352.5	352.1	351.7	351.3	350.9
155°	359.3	359.6	360.1	360.0	359.5	359.0	358.5	358.0
157.5°	365.7	366.1	366.4	366.4	365.9	365.5	365.0	364.5
160°	369.4	369.7	370.1	370.1	369.6	369.2	368.8	368.3
162.5°	372.7	373.2	373.6	373.6	373.0	372.5	372.0	371.4
165°	376.9	377.4	377.8	377.8	377.4	376.9	376.5	376.1
167.5°	380.5	380.9	381.3	381.3	380.7	380.1	379.6	379.0
170°	382.3	382.7	383.1	383.1	382.5	381.9	381.4	380.8
172.5°	383.6	384.0	384.4	384.4	383.8	383.3	382.7	382.2
175°	385.0	385.5	385.9	385.8	385.2	384.6	383.9	383.3
177.5°	385.2	385.6	385.9	385.8	385.4	385.0	384.5	384.1
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7

(END OF REPORT)