

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332033-830

Luminaire Tested: **S123DIP-S1000D1025U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332033-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7747.4 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332033-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332033-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29	26
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332033-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	1.8
10°-20°	396.8	5.1
20°-30°	586.2	7.6
30°-40°	684.7	8.8
40°-50°	688.4	8.9
50°-60°	604.7	7.8
60°-70°	450.5	5.8
70°-80°	256.7	3.3
80°-90°	77.2	1.0
90°-100°	46.0	0.6
100°-110°	219.4	2.8
110°-120°	527.0	6.8
120°-130°	671.1	8.7
130°-140°	717.1	9.3
140°-150°	670.6	8.7
150°-160°	540.9	7.0
160°-170°	349.1	4.5
170°-180°	120.3	1.6
0°-30°	1123.5	14.5
0°-40°	1808.2	23.3
0°-60°	3101.3	40.0
0°-90°	3885.7	50.2
90°-120°	792.5	10.2
90°-150°	2851.3	36.8
90°-180°	3862.0	49.8
0°-180°	7747.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	10	23	26	28	6
95°	57	22	29	35	36	71
105°	280	285	206	49	41	297
115°	526	532	540	549	553	519
125°	741	749	753	754	756	662
135°	923	928	932	935	932	710
145°	1065	1071	1074	1075	1075	666
155°	1173	1171	1172	1176	1171	540
165°	1237	1234	1233	1240	1234	349
175°	1266	1262	1262	1268	1262	120
180°	1266	1266	1266	1266	1266	



TEST NUMBER: P332033-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.9	26.6	26.3	26.1	25.8	25.8	26.1	26.5	26.8	27.1	27.1
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	17.5	16.9	16.3	15.7	15.2	15.9	17.9	20.0	22.1	24.1	25.4
95°	57.4	48.8	40.2	31.7	23.1	20.0	22.2	24.6	26.9	29.1	30.6
97.5°	115.4	111.5	107.6	103.8	99.9	90.5	75.5	60.4	45.3	30.3	32.0
100°	159.0	163.2	167.4	171.5	175.7	161.5	128.8	96.2	63.6	31.0	32.7
102.5°	208.7	211.7	214.7	217.7	220.7	204.4	168.8	133.2	97.6	61.9	56.7
105°	280.3	282.7	284.9	287.3	289.5	281.3	262.5	243.6	224.9	206.0	169.0
107.5°	356.0	357.9	359.7	361.6	363.4	365.8	368.7	371.7	374.7	377.7	350.5
110°	406.4	408.1	409.7	411.4	413.1	415.1	417.4	419.7	422.0	424.3	417.4



TEST NUMBER: P332033-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.6	456.1	457.6	459.1	460.6	462.5	464.9	467.1	469.4	471.7	471.8
115°	525.9	527.2	528.4	529.7	530.9	532.5	534.3	536.2	538.1	540.0	542.2
117.5°	594.9	596.5	598.0	599.6	601.2	602.4	603.3	604.4	605.3	606.2	607.9
120°	637.8	639.7	641.6	643.5	645.4	646.7	647.2	647.9	648.6	649.1	650.8
122.5°	681.6	683.1	684.6	686.2	687.7	688.9	689.7	690.5	691.3	692.0	693.2
125°	741.3	743.0	744.7	746.4	748.0	749.3	750.2	750.9	751.8	752.6	753.1
127.5°	799.3	801.0	802.7	804.3	806.0	807.3	808.3	809.4	810.3	811.3	812.0
130°	835.5	837.1	838.8	840.5	842.2	843.4	844.2	845.1	845.8	846.7	847.5
132.5°	870.1	871.8	873.4	875.1	876.8	877.9	878.5	879.2	880.0	880.6	881.5
135°	922.9	924.2	925.4	926.7	927.9	929.0	929.8	930.7	931.5	932.4	932.9
137.5°	968.1	969.7	971.3	972.9	974.4	975.4	975.9	976.4	976.9	977.3	978.3
140°	998.2	999.5	1000.7	1001.9	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5
142.5°	1026.1	1027.3	1028.5	1029.8	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2
145°	1065.0	1066.5	1067.9	1069.4	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8
147.5°	1101.6	1102.7	1103.6	1104.6	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3
150°	1124.3	1124.9	1125.5	1126.1	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4
152.5°	1144.5	1144.9	1145.2	1145.5	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7
155°	1173.2	1172.7	1172.3	1172.0	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3
157.5°	1195.3	1195.3	1195.3	1195.2	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5
160°	1208.9	1208.7	1208.5	1208.3	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3
162.5°	1221.7	1221.2	1220.6	1220.1	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7
165°	1237.2	1236.5	1235.9	1235.3	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0
167.5°	1249.2	1248.4	1247.5	1246.7	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1
170°	1255.9	1255.1	1254.3	1253.5	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9
172.5°	1260.5	1259.5	1258.5	1257.4	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4
175°	1266.3	1265.3	1264.2	1263.2	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0
177.5°	1267.8	1267.0	1266.1	1265.3	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332033-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	27.0	27.0	26.9	26.9	27.0	27.1	27.1	27.2
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	26.8	28.1	29.4	30.3	30.4	30.7	31.0	31.2
95°	32.0	33.6	35.1	35.7	35.7	35.7	35.7	35.7
97.5°	33.6	35.3	36.9	37.9	38.2	38.4	38.5	38.7
100°	34.4	36.1	37.7	38.6	38.9	39.1	39.3	39.5
102.5°	51.6	46.4	41.2	38.7	39.1	39.5	39.9	40.2
105°	132.1	95.0	58.1	39.7	40.2	40.5	41.0	41.4
107.5°	323.4	296.2	269.1	241.6	213.7	185.8	157.9	130.0
110°	410.5	403.6	396.7	378.3	348.4	318.5	288.6	258.7



TEST NUMBER: P332033-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	471.9	472.1	472.2	469.1	462.8	456.5	450.2	443.8
115°	544.2	546.3	548.4	549.9	550.6	551.5	552.3	553.2
117.5°	609.6	611.2	612.9	613.9	614.1	614.2	614.3	614.5
120°	652.5	654.1	655.8	656.7	656.7	656.7	656.7	656.7
122.5°	694.4	695.6	696.7	697.4	697.6	697.8	697.9	698.0
125°	753.5	753.8	754.3	754.7	755.2	755.5	756.0	756.4
127.5°	812.7	813.3	814.0	814.2	813.7	813.3	812.8	812.5
130°	848.4	849.2	850.1	850.3	849.9	849.4	849.0	848.6
132.5°	882.2	883.1	883.9	884.0	883.4	882.9	882.3	881.7
135°	933.6	934.2	934.8	934.8	934.2	933.6	932.9	932.4
137.5°	979.3	980.3	981.3	981.6	981.2	980.8	980.3	980.0
140°	1008.3	1009.2	1010.0	1010.2	1009.7	1009.4	1009.0	1008.5
142.5°	1035.9	1036.5	1037.2	1037.2	1036.6	1036.0	1035.5	1034.9
145°	1074.3	1074.7	1075.2	1075.3	1075.3	1075.3	1075.3	1075.3
147.5°	1108.7	1109.1	1109.6	1109.3	1108.3	1107.4	1106.4	1105.4
150°	1129.8	1130.2	1130.7	1130.5	1129.9	1129.3	1128.6	1128.0
152.5°	1148.5	1149.2	1150.0	1149.9	1149.0	1148.0	1147.1	1146.0
155°	1174.3	1175.4	1176.4	1176.3	1175.1	1173.8	1172.5	1171.3
157.5°	1196.7	1198.0	1199.3	1199.1	1197.4	1195.8	1194.2	1192.6
160°	1209.6	1210.8	1212.0	1211.9	1210.5	1209.0	1207.6	1206.1
162.5°	1221.2	1222.6	1224.0	1224.1	1222.8	1221.4	1220.2	1218.9
165°	1236.7	1238.4	1240.1	1240.2	1238.7	1237.3	1235.8	1234.4
167.5°	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4
170°	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2
172.5°	1260.1	1261.7	1263.4	1263.3	1261.5	1259.6	1257.8	1255.9
175°	1265.5	1267.0	1268.4	1268.3	1266.6	1265.0	1263.3	1261.6
177.5°	1267.4	1268.9	1270.2	1270.0	1268.3	1266.7	1265.0	1263.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3

(END OF REPORT)