

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331684-935

Luminaire Tested: **S122RDIP-S675D530U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331684-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D530U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3818.9 lumens  
Efficiency: N/A  
Efficacy: 94.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331684-935

CATALOG NUMBER: S122RDIP-S675D530U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331684-935

CATALOG NUMBER: S122RDIP-S675D530U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43	39
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	59	51	45	65	55	48	42	47	42	38	41	36	33	34	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	29	34	29	26	29	25	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	33	28	48	37	31	26	33	28	24	29	24	21	24	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15681	15681	15681
5°	15741	15486	15571
10°	15621	15231	15101
15°	15442	14780	14355
20°	15192	14136	13426
25°	14938	13402	12527
30°	14585	12652	11373
35°	14241	11832	10360
40°	13894	10985	9187
45°	13486	10035	8127
50°	13069	9075	7086
55°	12645	8042	6086
60°	12148	6952	5050
65°	11584	5841	4604
70°	10914	4810	4230
75°	10087	4386	3949
80°	8908	3924	3598
85°	7003	3094	3094



TEST NUMBER: P331684-935

CATALOG NUMBER: S122RDIP-S675D530U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.9	2.4
10°-20°	249.6	6.5
20°-30°	350.5	9.2
30°-40°	382.2	10.0
40°-50°	351.5	9.2
50°-60°	276.0	7.2
60°-70°	180.0	4.7
70°-80°	92.8	2.4
80°-90°	25.6	0.7
90°-100°	20.7	0.5
100°-110°	76.0	2.0
110°-120°	203.0	5.3
120°-130°	335.2	8.8
130°-140°	356.5	9.3
140°-150°	331.3	8.7
150°-160°	266.4	7.0
160°-170°	171.7	4.5
170°-180°	59.1	1.5
0°-30°	691.1	18.1
0°-40°	1073.3	28.1
0°-60°	1700.8	44.5
0°-90°	1999.1	52.3
90°-120°	299.7	7.8
90°-150°	1322.7	34.6
90°-180°	1820.0	47.7
0°-180°	3818.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	971	966	956	963	961	92
15°	924	913	884	868	859	260
25°	838	809	752	718	703	385
35°	722	676	600	547	526	452
45°	591	530	440	379	356	456
55°	449	379	286	235	216	401
65°	303	232	153	125	120	300
75°	162	102	70	64	63	171
85°	38	20	17	17	17	45
90°	0	5	9	11	12	3
95°	29	15	18	20	19	36
105°	137	143	27	32	34	146
115°	258	266	277	79	37	254
125°	365	371	380	383	384	326
135°	452	459	463	468	467	349
145°	524	524	532	534	532	328
155°	577	574	579	581	578	266
165°	608	606	607	610	607	172
175°	622	619	620	623	619	59
180°	621	621	621	621	621	



TEST NUMBER: P331684-935

CATALOG NUMBER: S122RDIP-S675D530U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	974.7	974.0	973.2	972.4	971.6	970.3	968.6	966.9	965.3	963.5	965.1
5°	971.2	970.3	969.3	968.3	967.3	965.6	963.0	960.5	957.9	955.5	957.2
7.5°	961.2	960.0	958.8	957.6	956.4	954.2	951.3	948.4	945.4	942.5	942.9
10°	952.8	951.4	950.0	948.6	947.3	944.7	940.7	936.9	933.0	929.0	928.5
12.5°	942.2	940.6	938.8	937.2	935.5	932.2	927.2	922.2	917.1	912.1	911.1
15°	923.8	921.6	919.5	917.3	915.2	910.8	904.1	897.5	890.9	884.2	880.5
17.5°	901.1	897.9	894.6	891.2	887.9	882.1	873.6	865.0	856.5	848.0	843.6
20°	884.2	880.3	876.4	872.5	868.6	861.8	852.0	842.2	832.5	822.7	817.8
22.5°	865.9	861.6	857.2	852.8	848.4	840.8	829.7	818.7	807.7	796.7	790.4
25°	838.5	832.2	826.0	819.8	813.6	803.9	791.1	778.2	765.3	752.3	744.3
27.5°	805.5	798.7	791.9	785.1	778.3	767.6	753.1	738.6	724.0	709.5	700.2
30°	782.3	774.8	767.4	760.0	752.6	741.1	725.4	709.8	694.1	678.6	668.6
32.5°	759.7	751.1	742.4	733.7	725.0	712.7	696.8	680.9	665.0	649.0	637.7
35°	722.5	712.6	702.6	692.6	682.7	669.1	651.9	634.7	617.5	600.3	588.0
37.5°	685.3	674.2	663.3	652.4	641.4	626.8	608.6	590.2	571.9	553.5	540.0
40°	659.2	647.5	635.8	624.1	612.3	597.0	578.1	559.1	540.2	521.2	507.4
42.5°	632.5	620.2	607.8	595.5	583.2	567.1	547.6	528.1	508.4	488.9	474.5
45°	590.6	577.6	564.5	551.4	538.3	521.5	501.0	480.5	459.9	439.5	425.6
47.5°	549.8	536.0	522.1	508.2	494.4	476.9	455.7	434.5	413.4	392.2	378.4
50°	520.3	506.4	492.6	478.7	464.9	447.2	425.7	404.2	382.7	361.3	347.8
52.5°	491.5	477.0	462.5	448.1	433.5	415.8	394.8	373.8	352.8	331.7	318.7
55°	449.2	433.9	418.7	403.5	388.2	370.1	349.0	327.9	306.8	285.7	274.0
57.5°	405.7	390.1	374.4	358.9	343.2	325.3	305.0	284.7	264.4	244.2	233.4
60°	376.2	360.6	344.9	329.3	313.7	295.8	275.7	255.5	235.5	215.3	205.3
62.5°	347.3	331.7	316.1	300.5	284.8	267.4	248.3	229.1	209.9	190.7	181.2
65°	303.2	287.4	271.6	255.8	240.0	223.3	205.7	188.1	170.5	152.9	146.3
67.5°	260.7	245.0	229.3	213.6	197.9	182.1	166.3	150.5	134.7	118.8	115.8
70°	231.2	215.9	200.7	185.5	170.2	155.8	142.4	128.9	115.5	101.9	100.0
72.5°	203.0	188.4	173.8	159.2	144.6	131.9	121.1	110.2	99.4	88.6	87.0
75°	161.7	148.1	134.4	120.7	107.0	96.9	90.2	83.6	77.0	70.3	69.0
77.5°	121.1	109.1	97.1	85.2	73.2	65.5	62.3	59.2	56.0	52.8	51.9
80°	95.8	85.8	75.9	66.0	56.0	50.0	48.0	46.1	44.2	42.2	41.4
82.5°	72.6	64.8	57.1	49.2	41.5	36.9	35.6	34.3	33.0	31.7	31.2
85°	37.8	33.7	29.6	25.5	21.4	19.0	18.4	17.9	17.3	16.7	16.7
87.5°	11.4	10.3	9.3	8.3	7.2	6.8	7.0	7.1	7.2	7.4	7.4
90°	0.4	1.5	2.7	3.7	4.8	5.8	6.6	7.4	8.2	9.0	9.5
92.5°	9.0	9.0	8.9	8.8	8.7	8.9	9.2	9.6	10.0	10.4	10.7
95°	29.2	25.9	22.6	19.3	16.0	14.7	15.4	16.1	16.8	17.6	18.0
97.5°	57.9	48.6	39.4	30.1	20.8	17.0	18.6	20.2	21.9	23.4	23.8
100°	79.6	65.9	52.2	38.5	24.8	18.9	20.5	22.2	23.9	25.6	26.4
102.5°	103.2	100.4	97.5	94.5	91.7	83.1	69.0	54.8	40.6	26.3	27.4
105°	136.6	139.6	142.6	145.6	148.6	136.5	109.2	82.0	54.7	27.4	28.5
107.5°	174.6	177.0	179.4	181.8	184.3	169.1	136.5	103.8	71.0	38.4	37.3
110°	199.1	201.1	203.3	205.3	207.4	194.1	165.2	136.4	107.5	78.6	68.6



TEST NUMBER: P331684-935

CATALOG NUMBER: S122RDIP-S675D530U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	222.1	223.9	225.8	227.6	229.5	226.9	219.7	212.6	205.4	198.4	161.9
115°	258.4	260.0	261.7	263.5	265.2	267.3	269.8	272.2	274.7	277.2	231.0
117.5°	290.8	292.7	294.6	296.5	298.4	300.2	302.0	303.7	305.4	307.0	295.9
120°	314.5	316.0	317.5	319.0	320.6	322.2	324.0	325.8	327.5	329.3	330.5
122.5°	334.7	336.2	337.9	339.4	341.0	342.8	344.7	346.6	348.6	350.6	351.3
125°	365.3	366.6	367.9	369.2	370.5	372.1	374.0	375.9	377.8	379.7	380.4
127.5°	393.0	394.5	396.0	397.4	398.8	400.3	401.7	403.1	404.5	406.0	406.9
130°	410.7	412.2	413.9	415.5	417.1	418.4	419.6	420.6	421.7	422.8	424.0
132.5°	428.7	430.0	431.4	432.7	434.1	435.3	436.4	437.6	438.6	439.7	440.7
135°	452.0	453.7	455.2	456.8	458.4	459.7	460.5	461.5	462.4	463.2	464.3
137.5°	475.7	476.7	477.9	479.0	480.1	481.2	482.2	483.3	484.2	485.3	486.3
140°	491.1	491.9	492.8	493.5	494.3	495.2	496.4	497.5	498.5	499.6	500.6
142.5°	504.0	504.8	505.5	506.2	507.0	507.9	509.2	510.4	511.7	513.0	513.8
145°	524.3	524.3	524.2	524.1	524.0	524.8	526.5	528.1	529.9	531.6	532.3
147.5°	542.1	541.7	541.3	541.0	540.5	541.2	542.9	544.6	546.2	547.9	548.5
150°	553.5	552.8	552.2	551.5	550.8	551.2	552.8	554.4	556.0	557.6	558.2
152.5°	563.3	562.5	561.7	560.9	560.2	560.5	562.1	563.6	565.1	566.6	567.2
155°	577.4	576.5	575.6	574.7	573.8	573.9	575.1	576.4	577.6	578.8	579.4
157.5°	588.4	587.7	586.9	586.2	585.4	585.5	586.3	587.1	588.0	588.8	589.4
160°	595.0	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	595.6
162.5°	600.6	600.0	599.4	598.8	598.3	598.2	598.7	599.3	599.8	600.3	601.0
165°	608.4	607.8	607.2	606.6	606.0	605.9	606.1	606.4	606.7	607.0	607.8
167.5°	614.2	613.5	612.9	612.3	611.7	611.6	611.8	612.2	612.4	612.7	613.4
170°	617.3	616.8	616.2	615.6	615.0	614.8	615.0	615.2	615.4	615.6	616.3
172.5°	619.6	619.0	618.4	617.8	617.2	616.9	617.2	617.3	617.5	617.8	618.5
175°	622.3	621.6	621.0	620.3	619.5	619.3	619.5	619.7	619.8	620.1	620.8
177.5°	622.8	622.2	621.6	621.1	620.5	620.3	620.4	620.4	620.5	620.6	621.2
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331684-935

CATALOG NUMBER: S122RDIP-S675D530U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	966.6	968.2	969.7	970.3	970.1	969.7	969.5	969.1
5°	958.9	960.7	962.4	963.0	962.4	961.8	961.3	960.7
7.5°	943.4	943.9	944.4	944.2	943.1	942.2	941.2	940.1
10°	927.9	927.3	926.7	925.8	924.6	923.5	922.3	921.1
12.5°	910.1	909.0	907.9	906.5	904.5	902.6	900.6	898.6
15°	876.8	873.1	869.4	866.5	864.6	862.6	860.7	858.8
17.5°	839.2	834.7	830.3	826.5	823.1	819.8	816.4	813.0
20°	813.0	808.0	803.1	798.6	794.3	790.0	785.7	781.4
22.5°	784.1	777.8	771.5	766.8	763.5	760.3	757.2	754.0
25°	736.3	728.3	720.3	714.9	712.0	709.0	706.1	703.2
27.5°	690.8	681.5	672.2	665.1	660.5	655.8	651.2	646.5
30°	658.7	648.7	638.7	631.1	625.8	620.5	615.3	610.0
32.5°	626.3	614.9	603.6	595.4	590.4	585.5	580.5	575.6
35°	575.8	563.4	551.1	542.8	538.5	534.2	529.9	525.6
37.5°	526.4	512.9	499.4	490.1	485.2	480.3	475.4	470.5
40°	493.4	479.6	465.7	456.2	451.2	446.1	441.0	435.9
42.5°	460.2	445.8	431.5	421.9	417.0	412.1	407.2	402.2
45°	411.7	397.9	384.0	374.7	370.1	365.3	360.7	355.9
47.5°	364.6	350.9	337.0	328.0	323.7	319.5	315.2	311.0
50°	334.3	320.8	307.4	298.5	294.5	290.3	286.3	282.1
52.5°	305.7	292.7	279.7	271.3	267.5	263.7	259.9	256.1
55°	262.3	250.5	238.8	231.1	227.4	223.6	219.9	216.2
57.5°	222.7	212.0	201.2	194.2	191.1	188.0	184.9	181.8
60°	195.4	185.5	175.5	168.9	165.8	162.7	159.5	156.4
62.5°	171.8	162.2	152.7	147.1	145.2	143.4	141.5	139.6
65°	139.7	133.0	126.4	122.8	122.2	121.6	121.0	120.5
67.5°	112.7	109.7	106.7	104.8	104.2	103.6	103.0	102.3
70°	98.1	96.1	94.1	92.8	92.0	91.2	90.4	89.6
72.5°	85.3	83.7	82.1	81.0	80.5	80.1	79.6	79.1
75°	67.6	66.2	64.8	64.1	63.9	63.7	63.5	63.3
77.5°	51.1	50.4	49.6	49.1	48.7	48.5	48.1	47.8
80°	40.6	39.9	39.1	38.7	38.7	38.7	38.7	38.7
82.5°	30.7	30.2	29.8	29.5	29.5	29.5	29.5	29.5
85°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
87.5°	7.3	7.2	7.2	7.1	7.2	7.2	7.3	7.3
90°	10.0	10.5	11.0	11.4	11.5	11.7	12.0	12.1
92.5°	10.9	11.2	11.5	11.6	11.8	11.9	12.1	12.1
95°	18.5	19.0	19.5	19.7	19.6	19.5	19.5	19.3
97.5°	24.3	24.6	25.1	25.3	25.4	25.6	25.7	25.8
100°	27.2	28.0	28.8	29.3	29.5	29.7	29.9	30.1
102.5°	28.4	29.4	30.5	31.2	31.4	31.7	31.9	32.3
105°	29.6	30.7	31.8	32.5	33.0	33.3	33.8	34.2
107.5°	36.2	35.0	33.9	33.6	33.9	34.4	34.7	35.1
110°	58.6	48.6	38.7	33.9	34.3	34.7	35.1	35.5





TEST NUMBER: P331684-935

CATALOG NUMBER: S122RDIP-S675D530U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.4	89.0	52.6	34.6	34.9	35.2	35.6	35.8
115°	184.8	138.5	92.3	65.6	58.4	51.2	44.0	36.9
117.5°	284.7	273.5	262.3	245.0	221.3	197.7	174.1	150.4
120°	331.7	332.9	334.2	328.0	314.5	301.1	287.6	274.1
122.5°	352.0	352.8	353.4	352.5	349.9	347.2	344.7	342.0
125°	381.1	381.8	382.5	383.0	383.3	383.6	383.9	384.2
127.5°	407.9	409.0	410.0	410.5	410.6	410.7	410.7	410.8
130°	425.0	426.1	427.2	427.7	427.6	427.5	427.4	427.3
132.5°	441.6	442.6	443.5	443.8	443.8	443.7	443.6	443.5
135°	465.3	466.2	467.3	467.7	467.4	467.3	467.1	466.8
137.5°	487.2	488.2	489.2	489.5	489.1	488.8	488.5	488.2
140°	501.4	502.3	503.3	503.4	502.9	502.5	502.0	501.4
142.5°	514.6	515.4	516.3	516.4	515.9	515.4	514.9	514.4
145°	533.0	533.6	534.3	534.4	534.0	533.5	533.0	532.4
147.5°	549.0	549.5	550.0	550.0	549.7	549.2	548.8	548.4
150°	558.8	559.4	560.0	560.1	559.6	559.0	558.5	558.1
152.5°	567.8	568.4	569.0	568.9	568.3	567.7	567.0	566.4
155°	580.0	580.6	581.2	581.0	580.2	579.5	578.7	577.8
157.5°	590.1	590.8	591.5	591.5	590.6	589.9	589.1	588.3
160°	596.1	596.7	597.3	597.3	596.6	595.9	595.1	594.4
162.5°	601.7	602.4	603.0	603.0	602.1	601.2	600.4	599.5
165°	608.5	609.2	609.8	609.8	609.2	608.5	607.8	607.0
167.5°	614.1	614.8	615.5	615.4	614.5	613.6	612.7	611.8
170°	617.0	617.7	618.4	618.3	617.3	616.5	615.6	614.7
172.5°	619.1	619.8	620.5	620.4	619.6	618.6	617.8	616.8
175°	621.5	622.2	622.8	622.8	621.7	620.7	619.7	618.7
177.5°	621.7	622.3	622.8	622.8	622.1	621.3	620.6	619.9
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

(END OF REPORT)