

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332011-830

Luminaire Tested: **S123DIP-S1000D585U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332011-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D585U830-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5995.7 lumens  
Efficiency: N/A  
Efficacy: 122.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57
2	93	86	80	74	87	81	76	71	72	68	64	64	61	58	57	54	52	48
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14249	14249	14249	14249
5°	16993	14311	12682	14311
10°	21270	14238	11455	14238
15°	26088	14123	10664	14123
20°	31078	13945	10153	13945
25°	32999	13726	10041	13726
30°	28285	13569	10092	13569
35°	19671	13341	10198	13341
40°	14816	13078	10166	13078
45°	12301	12683	10036	12683
50°	11020	11879	9945	11879
55°	10303	11012	9822	11012
60°	9664	10107	9722	10107
65°	9085	9212	9411	9212
70°	8519	8195	8960	8195
75°	7627	7178	8218	7178
80°	6676	5883	7073	5883
85°	5224	4273	4755	4273



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.4	2.2
10°-20°	418.2	7.0
20°-30°	701.8	11.7
30°-40°	794.6	13.3
40°-50°	712.6	11.9
50°-60°	575.1	9.6
60°-70°	400.7	6.7
70°-80°	210.6	3.5
80°-90°	53.6	0.9
90°-100°	147.8	2.5
100°-110°	418.5	7.0
110°-120°	411.7	6.9
120°-130°	328.4	5.5
130°-140°	258.9	4.3
140°-150°	193.2	3.2
150°-160°	134.7	2.2
160°-170°	79.1	1.3
170°-180°	25.7	0.4
0°-30°	1250.4	20.9
0°-40°	2045.0	34.1
0°-60°	3332.7	55.6
0°-90°	3997.6	66.7
90°-120°	978.0	16.3
90°-150°	1758.5	29.3
90°-180°	1998.0	33.3
0°-180°	5995.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1324	1324	1324	1324	1324	
5°	1573	1324	1174	1324	1573	163
15°	2341	1267	957	1267	2341	676
25°	2778	1156	845	1156	2778	1219
35°	1497	1015	776	1015	1497	973
45°	808	833	659	833	808	640
55°	549	587	523	587	549	493
65°	357	362	370	362	357	355
75°	183	173	198	173	183	196
85°	42	35	38	35	42	50
90°	16	1	16	1	16	10
95°	62	18	62	18	62	112
105°	684	62	684	62	684	675
115°	832	110	832	110	832	808
125°	656	153	656	153	656	594
135°	532	180	532	180	532	412
145°	416	205	416	205	416	264
155°	345	233	345	233	345	161
165°	300	254	300	254	300	86
175°	270	265	270	265	270	26
180°	266	266	266	266	266	



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1404.9	1403.9	1401.3	1403.4	1399.3	1393.6	1393.1	1388.0	1373.1	1372.1	1368.0
5°	1572.7	1567.5	1566.9	1566.3	1557.3	1545.1	1522.0	1520.1	1489.3	1473.9	1455.3
7.5°	1790.0	1792.7	1783.3	1775.1	1747.7	1729.6	1704.8	1673.1	1635.3	1596.9	1571.4
10°	1946.0	1967.2	1940.9	1922.9	1906.2	1874.8	1838.2	1792.7	1747.2	1693.9	1653.5
12.5°	2113.3	2123.6	2118.4	2101.5	2075.6	2027.7	1962.9	1912.8	1870.9	1782.2	1746.3
15°	2341.1	2380.2	2355.2	2297.4	2298.8	2253.2	2168.5	2075.6	2026.2	1948.5	1842.8
17.5°	2583.8	2588.7	2578.0	2529.9	2497.8	2435.2	2357.1	2267.9	2167.9	2074.0	1961.8
20°	2713.1	2709.2	2686.8	2661.7	2606.6	2557.9	2472.6	2373.1	2244.9	2152.5	2030.0
22.5°	2784.9	2778.5	2767.9	2746.9	2701.0	2648.7	2572.1	2463.4	2341.4	2214.1	2072.6
25°	2778.5	2786.8	2788.1	2782.4	2766.4	2734.9	2674.6	2588.0	2466.2	2302.6	2155.1
27.5°	2527.1	2538.9	2573.1	2603.6	2637.5	2672.2	2667.6	2624.6	2534.4	2393.1	2212.8
30°	2275.7	2250.0	2313.5	2393.7	2448.2	2544.4	2598.3	2601.5	2550.8	2429.6	2253.8
32.5°	1926.7	1954.9	1983.0	2081.7	2200.8	2308.9	2416.1	2502.5	2512.3	2431.7	2277.9
35°	1497.0	1532.3	1583.6	1634.9	1763.2	1873.5	2062.1	2226.3	2357.1	2374.5	2280.1
37.5°	1206.4	1223.8	1256.2	1307.7	1391.6	1522.4	1668.3	1875.8	2065.4	2206.4	2212.5
40°	1054.4	1059.6	1096.2	1135.3	1203.2	1311.0	1442.5	1625.9	1852.9	2049.9	2132.0
42.5°	940.6	951.8	967.3	1004.9	1059.0	1140.1	1262.3	1414.0	1622.1	1848.7	2009.3
45°	808.1	821.0	830.6	855.6	894.1	948.6	1034.0	1172.4	1330.9	1565.0	1781.1
47.5°	720.7	721.7	728.9	747.7	773.9	814.8	875.2	964.1	1109.6	1299.5	1521.4
50°	658.1	668.4	670.9	685.6	706.2	736.3	786.4	862.0	981.4	1148.1	1352.1
52.5°	614.0	617.0	624.2	634.9	652.8	676.3	719.6	778.9	872.5	1014.6	1202.2
55°	549.0	549.0	556.1	564.4	574.7	595.9	624.7	668.4	739.5	849.9	1005.0
57.5°	489.0	492.2	497.2	499.7	508.5	522.5	546.6	579.7	632.8	717.7	841.1
60°	448.9	454.8	454.1	459.2	466.9	477.9	498.3	525.3	572.8	640.7	744.7
62.5°	414.1	413.7	413.6	419.7	427.4	437.8	451.2	474.5	514.8	575.0	663.5
65°	356.7	355.3	359.9	363.6	366.3	373.9	384.2	404.7	431.7	476.5	545.2
67.5°	305.6	301.8	304.3	305.6	309.9	315.9	325.6	338.3	359.7	395.8	447.4
70°	270.7	267.5	266.8	268.1	271.9	276.4	283.5	295.7	315.6	344.4	382.3
72.5°	234.8	232.5	232.4	235.3	237.0	240.0	245.0	256.2	271.9	293.6	328.9
75°	183.4	183.4	183.4	184.1	186.0	188.6	192.4	198.2	210.4	225.7	249.5
77.5°	137.5	137.4	136.6	136.5	139.3	140.4	141.4	146.8	153.5	163.9	181.3
80°	107.7	104.5	105.8	107.7	109.1	109.7	111.6	112.9	118.7	124.4	136.6
82.5°	80.0	77.4	77.6	80.6	80.8	81.4	83.4	85.2	87.4	92.7	99.2
85°	42.3	42.3	43.0	43.0	43.6	43.0	44.9	45.5	45.5	48.7	52.6
87.5°	18.5	17.6	18.0	18.4	18.0	18.3	18.7	19.1	19.5	20.2	20.4
90°	15.6	16.1	15.6	15.1	15.6	14.5	13.9	13.5	12.9	13.5	11.8
92.5°	25.9	26.9	26.3	28.0	28.9	31.8	35.9	45.2	62.4	82.7	91.0
95°	62.4	64.5	68.2	73.1	83.3	102.6	131.2	193.5	258.5	318.8	283.9
97.5°	169.8	174.4	188.9	213.1	252.8	317.1	386.4	482.5	528.6	494.1	361.7
100°	337.1	336.6	357.5	396.7	451.0	527.4	590.3	633.9	615.0	509.1	344.0
102.5°	494.5	506.8	524.3	555.4	597.7	646.1	682.8	684.2	619.3	481.2	318.3
105°	683.8	686.5	703.7	724.2	748.9	762.9	752.6	698.9	586.5	432.3	286.5
107.5°	792.9	797.8	803.6	810.5	810.0	790.9	743.9	656.5	529.1	389.0	266.4
110°	837.5	838.7	839.7	835.5	820.4	782.8	715.0	616.0	492.9	364.5	258.5



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	846.6	846.4	842.4	829.0	801.4	753.1	677.1	576.1	461.6	348.2	254.3
115°	831.7	829.0	818.2	794.6	754.2	695.7	616.6	523.1	423.7	330.6	252.7
117.5°	784.1	780.5	765.0	737.9	695.9	636.4	565.4	484.7	400.8	320.3	253.6
120°	744.6	741.3	728.5	698.3	655.9	601.5	537.1	464.5	388.7	315.6	255.3
122.5°	707.6	703.5	689.3	662.2	624.4	574.0	514.3	448.6	378.8	312.5	258.4
125°	655.9	652.1	638.7	615.0	580.6	537.6	486.0	427.3	366.1	308.6	262.9
127.5°	613.3	609.8	597.7	577.5	546.9	507.7	461.2	408.9	355.0	306.6	268.1
130°	589.2	584.9	573.6	554.3	525.8	489.2	445.6	397.3	348.9	305.4	271.5
132.5°	565.5	562.5	552.5	533.2	506.4	471.6	431.0	386.5	343.3	304.9	274.1
135°	531.7	527.9	518.2	502.1	475.8	445.2	410.2	372.0	336.0	304.3	278.0
137.5°	495.9	493.4	485.2	468.9	446.8	420.2	390.1	358.8	329.7	303.1	280.5
140°	470.9	471.5	462.9	447.8	427.3	404.3	378.4	351.1	325.7	302.7	282.2
142.5°	447.7	448.3	440.5	427.2	409.7	389.6	367.3	343.7	322.3	301.8	283.5
145°	415.6	414.5	410.2	398.9	385.5	369.9	352.7	334.9	317.7	300.5	284.4
147.5°	389.1	388.7	384.6	376.9	366.7	355.7	341.8	327.7	313.2	298.5	284.4
150°	373.6	373.6	370.4	364.5	356.5	346.2	334.9	322.5	310.2	296.7	284.4
152.5°	360.7	360.7	358.8	353.3	346.9	338.5	328.5	317.8	306.8	294.6	283.1
155°	344.6	344.0	343.0	338.7	333.8	327.4	319.3	310.8	301.6	290.9	281.7
157.5°	329.9	330.0	329.1	325.9	321.7	316.7	310.4	303.2	295.8	287.5	279.8
160°	320.4	320.9	320.9	317.7	314.0	310.2	304.8	298.9	291.9	284.9	279.0
162.5°	311.8	312.4	312.4	309.5	307.1	303.8	298.8	293.8	288.0	282.4	277.3
165°	300.5	300.5	301.0	298.9	296.7	294.1	290.3	287.1	282.8	278.5	274.8
167.5°	289.7	289.7	290.3	288.8	287.9	285.9	283.7	281.3	277.8	274.6	272.1
170°	283.3	283.3	283.9	282.8	282.2	281.2	279.0	277.4	274.8	272.0	270.4
172.5°	277.3	277.8	278.7	277.6	277.5	276.8	275.1	274.0	271.7	269.8	269.1
175°	270.4	271.0	271.5	271.0	271.0	271.0	269.8	269.4	268.2	267.2	267.2
177.5°	266.5	266.5	267.3	266.8	267.3	267.3	266.8	266.5	266.0	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1364.9	1360.7	1356.7	1349.5	1343.3	1334.6	1332.0	1329.0	1319.7	1311.5	1305.3
5°	1448.2	1432.9	1410.4	1389.9	1373.2	1350.8	1337.9	1324.5	1305.2	1287.9	1273.8
7.5°	1535.5	1505.2	1470.4	1432.6	1397.5	1363.6	1336.2	1311.9	1285.0	1259.4	1239.5
10°	1604.8	1561.1	1512.4	1459.8	1414.9	1371.3	1334.7	1302.7	1268.0	1237.8	1212.9
12.5°	1683.8	1619.1	1551.9	1488.0	1434.9	1374.4	1330.1	1289.3	1250.1	1213.8	1185.7
15°	1777.3	1695.2	1615.7	1527.8	1447.0	1371.3	1318.7	1267.4	1221.8	1184.7	1148.8
17.5°	1862.5	1769.4	1664.6	1557.8	1460.3	1370.6	1296.9	1238.9	1181.9	1136.4	1100.6
20°	1910.7	1804.9	1686.2	1575.3	1467.5	1367.4	1286.7	1217.4	1155.7	1107.7	1067.2
22.5°	1952.3	1828.4	1705.7	1587.1	1467.0	1359.2	1267.6	1196.4	1129.6	1082.5	1039.5
25°	1995.4	1847.2	1724.1	1584.9	1450.9	1339.3	1236.6	1155.7	1089.1	1034.0	989.7
27.5°	2032.3	1846.0	1699.8	1550.1	1425.4	1313.5	1204.0	1117.3	1046.5	986.6	941.7
30°	2056.9	1848.5	1674.7	1526.5	1400.8	1285.3	1178.8	1091.7	1017.3	956.3	914.0
32.5°	2072.4	1846.9	1651.6	1493.6	1361.8	1259.7	1151.7	1061.4	985.0	925.0	884.2
35°	2081.3	1835.7	1611.8	1425.8	1298.8	1199.4	1109.0	1015.3	935.2	879.4	833.2
37.5°	2063.3	1811.9	1565.7	1360.4	1221.3	1123.4	1047.4	967.6	890.9	829.4	789.7
40°	2035.1	1796.6	1529.7	1314.2	1168.0	1073.7	1008.9	930.7	855.0	796.6	759.4
42.5°	1981.2	1765.2	1490.3	1262.9	1112.6	1018.2	958.7	893.2	821.6	766.9	729.6
45°	1849.7	1697.1	1431.0	1185.9	1030.7	933.2	880.6	833.2	768.4	715.1	683.1
47.5°	1667.4	1594.6	1345.3	1104.8	945.3	851.5	796.8	758.7	711.3	668.4	637.5
50°	1540.6	1510.5	1287.2	1049.3	888.3	796.6	744.0	709.4	675.4	632.4	604.2
52.5°	1394.4	1413.0	1219.6	991.8	830.4	740.2	690.7	663.2	632.3	597.0	572.4
55°	1188.5	1255.8	1102.6	895.4	744.0	658.1	611.2	586.8	568.9	542.6	521.4
57.5°	995.7	1081.4	976.1	796.0	659.2	585.0	540.2	513.6	502.1	488.3	471.6
60°	881.3	965.9	885.8	729.2	602.3	531.7	491.9	469.5	458.0	448.4	434.2
62.5°	779.2	864.9	797.5	661.6	546.3	480.9	446.3	424.3	415.4	410.4	398.3
65°	638.9	712.6	667.7	556.1	466.3	408.6	377.1	361.7	353.5	351.5	343.7
67.5°	519.9	576.1	543.4	461.3	390.6	340.7	314.1	301.0	294.5	293.9	288.1
70°	442.0	494.6	469.5	395.1	334.1	295.0	271.9	260.4	256.6	255.9	252.7
72.5°	381.4	418.0	398.1	336.1	289.0	253.4	236.6	224.5	220.1	221.0	218.9
75°	282.2	309.8	298.2	255.2	217.4	194.4	180.2	172.6	168.7	170.6	168.1
77.5°	203.0	220.6	210.1	180.4	157.0	140.3	130.0	125.2	121.8	121.6	120.5
80°	153.3	163.5	157.8	139.8	120.6	106.5	98.1	94.9	93.0	92.4	91.7
82.5°	109.1	117.9	111.1	98.8	85.7	77.2	72.5	68.2	66.8	67.2	66.5
85°	55.1	58.3	55.8	48.1	43.0	39.1	36.6	34.6	33.4	34.0	32.7
87.5°	21.0	21.2	19.3	17.1	15.8	13.9	13.8	12.5	11.7	12.0	11.8
90°	10.2	8.6	7.0	5.9	4.8	3.2	2.2	1.0	2.2	3.2	4.8
92.5°	68.2	45.1	31.1	23.1	18.6	14.4	9.9	6.7	9.9	14.4	18.6
95°	195.7	115.6	69.8	48.9	35.0	25.8	19.9	18.3	19.9	25.8	35.0
97.5°	214.7	124.4	80.8	58.1	44.3	36.4	31.8	31.2	31.8	36.4	44.3
100°	202.6	123.1	85.5	64.5	51.7	44.1	40.3	39.8	40.3	44.1	51.7
102.5°	192.4	124.8	91.0	71.8	60.2	53.2	49.8	48.8	49.8	53.2	60.2
105°	184.9	129.6	100.6	83.9	73.6	67.2	64.0	62.4	64.0	67.2	73.6
107.5°	184.4	138.4	112.9	97.5	87.8	81.5	78.4	76.7	78.4	81.5	87.8
110°	186.5	145.7	121.5	106.4	97.3	91.4	88.7	87.1	88.7	91.4	97.3





TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	190.9	153.0	130.5	115.9	106.8	100.9	98.2	96.5	98.2	100.9	106.8
115°	197.8	165.0	144.6	130.1	120.9	115.6	112.4	110.2	112.4	115.6	120.9
117.5°	207.1	177.9	157.6	144.2	133.9	129.0	126.3	123.9	126.3	129.0	133.9
120°	214.0	186.0	166.6	153.3	143.0	137.6	135.0	133.4	135.0	137.6	143.0
122.5°	220.5	194.6	175.7	161.4	151.6	145.8	143.1	141.5	143.1	145.8	151.6
125°	230.6	207.0	188.1	173.6	163.4	157.5	154.3	153.3	154.3	157.5	163.4
127.5°	239.0	217.7	199.5	185.0	173.7	167.8	163.7	162.1	163.7	167.8	173.7
130°	244.6	224.1	206.4	191.9	180.6	174.2	169.4	167.8	169.4	174.2	180.6
132.5°	249.8	229.8	212.4	198.4	187.1	179.4	174.1	172.0	174.1	179.4	187.1
135°	256.5	238.2	221.5	207.0	195.7	187.7	181.7	179.6	181.7	187.7	195.7
137.5°	261.4	243.9	227.9	214.5	203.3	194.7	188.9	186.6	188.9	194.7	203.3
140°	264.0	247.8	232.2	218.8	208.0	199.4	194.1	191.4	194.1	199.4	208.0
142.5°	266.6	250.8	235.7	223.1	212.4	204.6	198.8	196.5	198.8	204.6	212.4
145°	269.4	254.9	240.8	228.5	219.3	211.3	206.4	204.8	206.4	211.3	219.3
147.5°	271.1	258.1	245.2	234.7	225.9	219.0	214.1	213.2	214.1	219.0	225.9
150°	271.5	260.2	247.8	238.2	230.6	223.7	219.3	218.8	219.3	223.7	230.6
152.5°	272.4	261.5	250.8	241.6	235.0	228.8	224.5	224.4	224.5	228.8	235.0
155°	272.6	264.0	254.9	247.3	241.4	236.0	232.8	232.8	232.8	236.0	241.4
157.5°	273.1	265.3	258.1	252.2	247.2	242.4	239.9	239.4	239.9	242.4	247.2
160°	273.1	266.6	260.2	254.9	251.1	246.8	244.6	244.6	244.6	246.8	251.1
162.5°	272.7	267.1	261.5	256.9	253.6	250.2	248.5	248.5	248.5	250.2	253.6
165°	271.5	267.7	263.4	259.7	257.5	254.9	253.7	254.3	253.7	254.9	257.5
167.5°	270.6	267.6	264.5	262.1	260.6	258.5	258.1	258.7	258.1	258.5	260.6
170°	269.4	267.2	264.5	263.4	262.3	260.7	260.2	261.3	260.2	260.7	262.3
172.5°	268.9	267.2	264.9	264.3	263.6	262.5	262.3	263.0	262.3	262.5	263.6
175°	267.7	266.6	265.6	265.0	265.0	264.0	264.5	265.0	264.5	264.0	265.0
177.5°	266.8	266.0	265.6	265.6	265.6	265.1	265.6	266.0	265.6	265.1	265.6
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1301.7	1298.2	1293.1	1285.3	1279.2	1269.4	1269.4	1271.0	1271.0	1270.5	1269.4
5°	1262.3	1252.6	1241.1	1227.7	1213.5	1199.4	1196.8	1191.8	1187.9	1185.2	1182.0
7.5°	1220.6	1203.5	1186.7	1167.8	1150.7	1136.4	1126.5	1118.3	1113.0	1107.4	1103.3
10°	1192.3	1171.2	1151.3	1131.4	1109.6	1092.3	1081.4	1073.7	1067.9	1062.8	1060.3
12.5°	1159.0	1134.7	1112.9	1093.9	1070.1	1052.3	1041.9	1038.3	1031.5	1020.7	1015.0
15°	1110.2	1087.8	1061.5	1032.6	1021.1	999.3	987.1	981.4	977.5	969.1	966.6
17.5°	1068.6	1039.2	1009.7	988.2	966.7	949.0	942.2	935.0	929.9	923.1	921.1
20°	1035.2	1008.9	981.9	958.8	936.4	917.2	911.4	906.3	901.2	898.0	895.4
22.5°	1001.4	975.1	952.7	931.1	907.2	894.6	888.3	882.7	879.1	876.9	874.3
25°	953.8	930.7	905.7	886.4	867.1	858.8	855.0	851.8	849.2	846.0	845.4
27.5°	911.2	886.0	865.7	847.8	834.0	827.0	823.3	821.7	822.3	823.4	824.2
30°	879.4	856.3	839.6	824.2	811.3	804.9	804.3	804.3	806.9	807.5	808.8
32.5°	850.1	831.1	814.5	799.6	789.9	785.4	787.9	787.9	789.9	791.6	793.9
35°	807.5	790.8	778.0	765.2	756.9	758.7	760.1	761.3	764.5	768.4	771.0
37.5°	766.9	752.3	739.0	729.0	725.2	728.6	731.7	734.4	738.1	741.0	743.7
40°	737.6	726.7	713.9	704.9	706.2	708.1	710.7	713.9	717.1	719.0	721.6
42.5°	710.4	699.0	689.3	681.8	683.6	686.1	687.6	689.3	693.0	696.4	698.0
45°	669.0	660.0	651.0	646.5	647.8	649.1	650.4	652.3	655.5	658.1	658.7
47.5°	622.4	616.1	610.1	605.8	607.8	607.3	609.0	613.0	614.1	615.6	619.2
50°	592.7	586.8	579.9	578.5	578.5	578.5	579.2	584.3	584.3	586.8	589.5
52.5°	559.8	556.1	551.6	549.3	548.3	548.3	550.9	553.6	554.6	558.2	560.7
55°	511.2	507.4	503.5	501.5	500.3	501.5	506.7	507.9	511.2	513.1	515.0
57.5°	460.5	457.6	454.5	453.5	453.2	454.9	457.7	461.6	462.3	468.3	471.2
60°	427.2	422.6	420.1	420.1	418.9	424.6	423.3	429.7	431.0	434.9	439.3
62.5°	392.8	386.7	385.7	385.7	387.6	389.2	391.0	393.8	397.2	402.0	405.5
65°	337.3	334.1	338.7	338.0	336.8	340.5	340.5	343.7	347.6	352.1	359.2
67.5°	284.9	283.2	283.6	283.6	285.6	287.8	289.5	292.4	297.0	301.7	306.3
70°	249.5	251.5	248.3	250.8	252.7	253.4	254.7	258.4	263.6	266.8	271.9
72.5°	215.1	215.0	215.4	216.4	218.3	219.5	220.7	225.2	230.7	233.5	237.6
75°	165.5	164.9	166.7	166.7	169.9	171.3	172.6	174.5	179.6	183.4	186.6
77.5°	120.8	121.6	121.2	123.4	122.5	122.7	126.8	128.7	129.2	136.8	138.5
80°	91.0	92.4	93.0	93.7	94.3	93.0	97.5	99.4	99.4	103.9	107.1
82.5°	65.4	66.2	67.9	68.5	68.6	69.9	70.3	71.7	73.2	75.2	79.4
85°	32.7	34.6	35.3	34.6	35.3	34.0	35.9	36.6	37.2	37.2	37.2
87.5°	11.4	12.2	12.0	12.8	12.6	13.5	13.4	12.4	12.5	14.2	12.3
90°	5.9	7.0	8.6	10.2	11.8	13.5	12.9	13.5	13.9	14.5	15.6
92.5°	23.1	31.1	45.1	68.2	91.0	82.7	62.4	45.2	35.9	31.8	28.9
95°	48.9	69.8	115.6	195.7	283.9	318.8	258.5	193.5	131.2	102.6	83.3
97.5°	58.1	80.8	124.4	214.7	361.7	494.1	528.6	482.5	386.4	317.1	252.8
100°	64.5	85.5	123.1	202.6	344.0	509.1	615.0	633.9	590.3	527.4	451.0
102.5°	71.8	91.0	124.8	192.4	318.3	481.2	619.3	684.2	682.8	646.1	597.7
105°	83.9	100.6	129.6	184.9	286.5	432.3	586.5	698.9	752.6	762.9	748.9
107.5°	97.5	112.9	138.4	184.4	266.4	389.0	529.1	656.5	743.9	790.9	810.0
110°	106.4	121.5	145.7	186.5	258.5	364.5	492.9	616.0	715.0	782.8	820.4



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	115.9	130.5	153.0	190.9	254.3	348.2	461.6	576.1	677.1	753.1	801.4
115°	130.1	144.6	165.0	197.8	252.7	330.6	423.7	523.1	616.6	695.7	754.2
117.5°	144.2	157.6	177.9	207.1	253.6	320.3	400.8	484.7	565.4	636.4	695.9
120°	153.3	166.6	186.0	214.0	255.3	315.6	388.7	464.5	537.1	601.5	655.9
122.5°	161.4	175.7	194.6	220.5	258.4	312.5	378.8	448.6	514.3	574.0	624.4
125°	173.6	188.1	207.0	230.6	262.9	308.6	366.1	427.3	486.0	537.6	580.6
127.5°	185.0	199.5	217.7	239.0	268.1	306.6	355.0	408.9	461.2	507.7	546.9
130°	191.9	206.4	224.1	244.6	271.5	305.4	348.9	397.3	445.6	489.2	525.8
132.5°	198.4	212.4	229.8	249.8	274.1	304.9	343.3	386.5	431.0	471.6	506.4
135°	207.0	221.5	238.2	256.5	278.0	304.3	336.0	372.0	410.2	445.2	475.8
137.5°	214.5	227.9	243.9	261.4	280.5	303.1	329.7	358.8	390.1	420.2	446.8
140°	218.8	232.2	247.8	264.0	282.2	302.7	325.7	351.1	378.4	404.3	427.3
142.5°	223.1	235.7	250.8	266.6	283.5	301.8	322.3	343.7	367.3	389.6	409.7
145°	228.5	240.8	254.9	269.4	284.4	300.5	317.7	334.9	352.7	369.9	385.5
147.5°	234.7	245.2	258.1	271.1	284.4	298.5	313.2	327.7	341.8	355.7	366.7
150°	238.2	247.8	260.2	271.5	284.4	296.7	310.2	322.5	334.9	346.2	356.5
152.5°	241.6	250.8	261.5	272.4	283.1	294.6	306.8	317.8	328.5	338.5	346.9
155°	247.3	254.9	264.0	272.6	281.7	290.9	301.6	310.8	319.3	327.4	333.8
157.5°	252.2	258.1	265.3	273.1	279.8	287.5	295.8	303.2	310.4	316.7	321.7
160°	254.9	260.2	266.6	273.1	279.0	284.9	291.9	298.9	304.8	310.2	314.0
162.5°	256.9	261.5	267.1	272.7	277.3	282.4	288.0	293.8	298.8	303.8	307.1
165°	259.7	263.4	267.7	271.5	274.8	278.5	282.8	287.1	290.3	294.1	296.7
167.5°	262.1	264.5	267.6	270.6	272.1	274.6	277.8	281.3	283.7	285.9	287.9
170°	263.4	264.5	267.2	269.4	270.4	272.0	274.8	277.4	279.0	281.2	282.2
172.5°	264.3	264.9	267.2	268.9	269.1	269.8	271.7	274.0	275.1	276.8	277.5
175°	265.0	265.6	266.6	267.7	267.2	267.2	268.2	269.4	269.8	271.0	271.0
177.5°	265.6	265.6	266.0	266.8	266.0	265.6	266.0	266.5	266.8	267.3	267.3
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1265.8	1265.4	1268.9	1266.4	1268.9	1265.4	1265.8	1269.4	1270.5	1271.0	1271.0
5°	1178.3	1180.2	1173.7	1173.7	1173.7	1180.2	1178.3	1182.0	1185.2	1187.9	1191.8
7.5°	1100.2	1097.4	1097.7	1094.2	1097.7	1097.4	1100.2	1103.3	1107.4	1113.0	1118.3
10°	1052.5	1048.7	1047.4	1048.0	1047.4	1048.7	1052.5	1060.3	1062.8	1067.9	1073.7
12.5°	1013.0	1012.3	1003.8	1003.9	1003.8	1012.3	1013.0	1015.0	1020.7	1031.5	1038.3
15°	966.6	954.4	953.1	957.0	953.1	954.4	966.6	966.6	969.1	977.5	981.4
17.5°	920.0	913.6	914.0	912.1	914.0	913.6	920.0	921.1	923.1	929.9	935.0
20°	895.4	891.6	890.9	886.4	890.9	891.6	895.4	895.4	898.0	901.2	906.3
22.5°	872.8	871.6	871.9	867.0	871.9	871.6	872.8	874.3	876.9	879.1	882.7
25°	844.7	847.9	845.4	845.4	845.4	847.9	844.7	845.4	846.0	849.2	851.8
27.5°	825.8	825.6	824.3	824.3	824.3	825.6	825.8	824.2	823.4	822.3	821.7
30°	811.3	810.7	812.0	812.0	812.0	810.7	811.3	808.8	807.5	806.9	804.3
32.5°	797.0	797.9	798.1	798.6	798.1	797.9	797.0	793.9	791.6	789.9	787.9
35°	774.8	775.4	777.4	776.1	777.4	775.4	774.8	771.0	768.4	764.5	761.3
37.5°	744.8	747.7	747.1	748.1	747.1	747.7	744.8	743.7	741.0	738.1	734.4
40°	722.2	724.2	723.5	723.5	723.5	724.2	722.2	721.6	719.0	717.1	713.9
42.5°	699.1	700.5	698.9	697.9	698.9	700.5	699.1	698.0	696.4	693.0	689.3
45°	661.3	660.0	661.9	659.3	661.9	660.0	661.3	658.7	658.1	655.5	652.3
47.5°	619.0	620.2	620.8	622.6	620.8	620.2	619.0	619.2	615.6	614.1	613.0
50°	590.7	594.6	594.6	593.9	594.6	594.6	590.7	589.5	586.8	584.3	584.3
52.5°	563.0	564.8	567.4	567.2	567.4	564.8	563.0	560.7	558.2	554.6	553.6
55°	520.2	521.4	522.7	523.4	522.7	521.4	520.2	515.0	513.1	511.2	507.9
57.5°	475.8	475.2	478.3	479.3	478.3	475.2	475.8	471.2	468.3	462.3	461.6
60°	444.5	444.5	449.6	451.6	449.6	444.5	444.5	439.3	434.9	431.0	429.7
62.5°	411.1	413.2	418.3	415.7	418.3	413.2	411.1	405.5	402.0	397.2	393.8
65°	362.4	367.5	366.8	369.5	366.8	367.5	362.4	359.2	352.1	347.6	343.7
67.5°	311.4	314.6	319.2	319.7	319.2	314.6	311.4	306.3	301.7	297.0	292.4
70°	277.1	280.3	282.9	284.7	282.9	280.3	277.1	271.9	266.8	263.6	258.4
72.5°	243.7	245.4	251.6	248.8	251.6	245.4	243.7	237.6	233.5	230.7	225.2
75°	191.1	195.6	199.4	197.6	199.4	195.6	191.1	186.6	183.4	179.6	174.5
77.5°	141.4	145.8	147.6	146.0	147.6	145.8	141.4	138.5	136.8	129.2	128.7
80°	111.6	110.9	114.8	114.1	114.8	110.9	111.6	107.1	103.9	99.4	99.4
82.5°	81.8	81.2	83.0	83.4	83.0	81.2	81.8	79.4	75.2	73.2	71.7
85°	39.8	41.7	39.1	38.5	39.1	41.7	39.8	37.2	37.2	37.2	36.6
87.5°	12.3	12.3	12.0	11.3	12.0	12.3	12.3	12.3	14.2	12.5	12.4
90°	15.1	15.6	16.1	15.6	16.1	15.6	15.1	15.6	14.5	13.9	13.5
92.5°	28.0	26.3	26.9	25.9	26.9	26.3	28.0	28.9	31.8	35.9	45.2
95°	73.1	68.2	64.5	62.4	64.5	68.2	73.1	83.3	102.6	131.2	193.5
97.5°	213.1	188.9	174.4	169.8	174.4	188.9	213.1	252.8	317.1	386.4	482.5
100°	396.7	357.5	336.6	337.1	336.6	357.5	396.7	451.0	527.4	590.3	633.9
102.5°	555.4	524.3	506.8	494.5	506.8	524.3	555.4	597.7	646.1	682.8	684.2
105°	724.2	703.7	686.5	683.8	686.5	703.7	724.2	748.9	762.9	752.6	698.9
107.5°	810.5	803.6	797.8	792.9	797.8	803.6	810.5	810.0	790.9	743.9	656.5
110°	835.5	839.7	838.7	837.5	838.7	839.7	835.5	820.4	782.8	715.0	616.0



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	829.0	842.4	846.4	846.6	846.4	842.4	829.0	801.4	753.1	677.1	576.1
115°	794.6	818.2	829.0	831.7	829.0	818.2	794.6	754.2	695.7	616.6	523.1
117.5°	737.9	765.0	780.5	784.1	780.5	765.0	737.9	695.9	636.4	565.4	484.7
120°	698.3	728.5	741.3	744.6	741.3	728.5	698.3	655.9	601.5	537.1	464.5
122.5°	662.2	689.3	703.5	707.6	703.5	689.3	662.2	624.4	574.0	514.3	448.6
125°	615.0	638.7	652.1	655.9	652.1	638.7	615.0	580.6	537.6	486.0	427.3
127.5°	577.5	597.7	609.8	613.3	609.8	597.7	577.5	546.9	507.7	461.2	408.9
130°	554.3	573.6	584.9	589.2	584.9	573.6	554.3	525.8	489.2	445.6	397.3
132.5°	533.2	552.5	562.5	565.5	562.5	552.5	533.2	506.4	471.6	431.0	386.5
135°	502.1	518.2	527.9	531.7	527.9	518.2	502.1	475.8	445.2	410.2	372.0
137.5°	468.9	485.2	493.4	495.9	493.4	485.2	468.9	446.8	420.2	390.1	358.8
140°	447.8	462.9	471.5	470.9	471.5	462.9	447.8	427.3	404.3	378.4	351.1
142.5°	427.2	440.5	448.3	447.7	448.3	440.5	427.2	409.7	389.6	367.3	343.7
145°	398.9	410.2	414.5	415.6	414.5	410.2	398.9	385.5	369.9	352.7	334.9
147.5°	376.9	384.6	388.7	389.1	388.7	384.6	376.9	366.7	355.7	341.8	327.7
150°	364.5	370.4	373.6	373.6	373.6	370.4	364.5	356.5	346.2	334.9	322.5
152.5°	353.3	358.8	360.7	360.7	360.7	358.8	353.3	346.9	338.5	328.5	317.8
155°	338.7	343.0	344.0	344.6	344.0	343.0	338.7	333.8	327.4	319.3	310.8
157.5°	325.9	329.1	330.0	329.9	330.0	329.1	325.9	321.7	316.7	310.4	303.2
160°	317.7	320.9	320.9	320.4	320.9	320.9	317.7	314.0	310.2	304.8	298.9
162.5°	309.5	312.4	312.4	311.8	312.4	312.4	309.5	307.1	303.8	298.8	293.8
165°	298.9	301.0	300.5	300.5	300.5	301.0	298.9	296.7	294.1	290.3	287.1
167.5°	288.8	290.3	289.7	289.7	289.7	290.3	288.8	287.9	285.9	283.7	281.3
170°	282.8	283.9	283.3	283.3	283.3	283.9	282.8	282.2	281.2	279.0	277.4
172.5°	277.6	278.7	277.8	277.3	277.8	278.7	277.6	277.5	276.8	275.1	274.0
175°	271.0	271.5	271.0	270.4	271.0	271.5	271.0	271.0	271.0	269.8	269.4
177.5°	266.8	267.3	266.5	266.5	266.5	267.3	266.8	267.3	267.3	266.8	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1269.4	1269.4	1279.2	1285.3	1293.1	1298.2	1301.7	1305.3	1311.5	1319.7	1329.0
5°	1196.8	1199.4	1213.5	1227.7	1241.1	1252.6	1262.3	1273.8	1287.9	1305.2	1324.5
7.5°	1126.5	1136.4	1150.7	1167.8	1186.7	1203.5	1220.6	1239.5	1259.4	1285.0	1311.9
10°	1081.4	1092.3	1109.6	1131.4	1151.3	1171.2	1192.3	1212.9	1237.8	1268.0	1302.7
12.5°	1041.9	1052.3	1070.1	1093.9	1112.9	1134.7	1159.0	1185.7	1213.8	1250.1	1289.3
15°	987.1	999.3	1021.1	1032.6	1061.5	1087.8	1110.2	1148.8	1184.7	1221.8	1267.4
17.5°	942.2	949.0	966.7	988.2	1009.7	1039.2	1068.6	1100.6	1136.4	1181.9	1238.9
20°	911.4	917.2	936.4	958.8	981.9	1008.9	1035.2	1067.2	1107.7	1155.7	1217.4
22.5°	888.3	894.6	907.2	931.1	952.7	975.1	1001.4	1039.5	1082.5	1129.6	1196.4
25°	855.0	858.8	867.1	886.4	905.7	930.7	953.8	989.7	1034.0	1089.1	1155.7
27.5°	823.3	827.0	834.0	847.8	865.7	886.0	911.2	941.7	986.6	1046.5	1117.3
30°	804.3	804.9	811.3	824.2	839.6	856.3	879.4	914.0	956.3	1017.3	1091.7
32.5°	787.9	785.4	789.9	799.6	814.5	831.1	850.1	884.2	925.0	985.0	1061.4
35°	760.1	758.7	756.9	765.2	778.0	790.8	807.5	833.2	879.4	935.2	1015.3
37.5°	731.7	728.6	725.2	729.0	739.0	752.3	766.9	789.7	829.4	890.9	967.6
40°	710.7	708.1	706.2	704.9	713.9	726.7	737.6	759.4	796.6	855.0	930.7
42.5°	687.6	686.1	683.6	681.8	689.3	699.0	710.4	729.6	766.9	821.6	893.2
45°	650.4	649.1	647.8	646.5	651.0	660.0	669.0	683.1	715.1	768.4	833.2
47.5°	609.0	607.3	607.8	605.8	610.1	616.1	622.4	637.5	668.4	711.3	758.7
50°	579.2	578.5	578.5	578.5	579.9	586.8	592.7	604.2	632.4	675.4	709.4
52.5°	550.9	548.3	548.3	549.3	551.6	556.1	559.8	572.4	597.0	632.3	663.2
55°	506.7	501.5	500.3	501.5	503.5	507.4	511.2	521.4	542.6	568.9	586.8
57.5°	457.7	454.9	453.2	453.5	454.5	457.6	460.5	471.6	488.3	502.1	513.6
60°	423.3	424.6	418.9	420.1	420.1	422.6	427.2	434.2	448.4	458.0	469.5
62.5°	391.0	389.2	387.6	385.7	385.7	386.7	392.8	398.3	410.4	415.4	424.3
65°	340.5	340.5	336.8	338.0	338.7	334.1	337.3	343.7	351.5	353.5	361.7
67.5°	289.5	287.8	285.6	283.6	283.6	283.2	284.9	288.1	293.9	294.5	301.0
70°	254.7	253.4	252.7	250.8	248.3	251.5	249.5	252.7	255.9	256.6	260.4
72.5°	220.7	219.5	218.3	216.4	215.4	215.0	215.1	218.9	221.0	220.1	224.5
75°	172.6	171.3	169.9	166.7	166.7	164.9	165.5	168.1	170.6	168.7	172.6
77.5°	126.8	122.7	122.5	123.4	121.2	121.6	120.8	120.5	121.6	121.8	125.2
80°	97.5	93.0	94.3	93.7	93.0	92.4	91.0	91.7	92.4	93.0	94.9
82.5°	70.3	69.9	68.6	68.5	67.9	66.2	65.4	66.5	67.2	66.8	68.2
85°	35.9	34.0	35.3	34.6	35.3	34.6	32.7	32.7	34.0	33.4	34.6
87.5°	13.4	13.5	12.6	12.8	12.0	12.2	11.4	11.8	12.0	11.7	12.5
90°	12.9	13.5	11.8	10.2	8.6	7.0	5.9	4.8	3.2	2.2	1.0
92.5°	62.4	82.7	91.0	68.2	45.1	31.1	23.1	18.6	14.4	9.9	6.7
95°	258.5	318.8	283.9	195.7	115.6	69.8	48.9	35.0	25.8	19.9	18.3
97.5°	528.6	494.1	361.7	214.7	124.4	80.8	58.1	44.3	36.4	31.8	31.2
100°	615.0	509.1	344.0	202.6	123.1	85.5	64.5	51.7	44.1	40.3	39.8
102.5°	619.3	481.2	318.3	192.4	124.8	91.0	71.8	60.2	53.2	49.8	48.8
105°	586.5	432.3	286.5	184.9	129.6	100.6	83.9	73.6	67.2	64.0	62.4
107.5°	529.1	389.0	266.4	184.4	138.4	112.9	97.5	87.8	81.5	78.4	76.7
110°	492.9	364.5	258.5	186.5	145.7	121.5	106.4	97.3	91.4	88.7	87.1



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	461.6	348.2	254.3	190.9	153.0	130.5	115.9	106.8	100.9	98.2	96.5
115°	423.7	330.6	252.7	197.8	165.0	144.6	130.1	120.9	115.6	112.4	110.2
117.5°	400.8	320.3	253.6	207.1	177.9	157.6	144.2	133.9	129.0	126.3	123.9
120°	388.7	315.6	255.3	214.0	186.0	166.6	153.3	143.0	137.6	135.0	133.4
122.5°	378.8	312.5	258.4	220.5	194.6	175.7	161.4	151.6	145.8	143.1	141.5
125°	366.1	308.6	262.9	230.6	207.0	188.1	173.6	163.4	157.5	154.3	153.3
127.5°	355.0	306.6	268.1	239.0	217.7	199.5	185.0	173.7	167.8	163.7	162.1
130°	348.9	305.4	271.5	244.6	224.1	206.4	191.9	180.6	174.2	169.4	167.8
132.5°	343.3	304.9	274.1	249.8	229.8	212.4	198.4	187.1	179.4	174.1	172.0
135°	336.0	304.3	278.0	256.5	238.2	221.5	207.0	195.7	187.7	181.7	179.6
137.5°	329.7	303.1	280.5	261.4	243.9	227.9	214.5	203.3	194.7	188.9	186.6
140°	325.7	302.7	282.2	264.0	247.8	232.2	218.8	208.0	199.4	194.1	191.4
142.5°	322.3	301.8	283.5	266.6	250.8	235.7	223.1	212.4	204.6	198.8	196.5
145°	317.7	300.5	284.4	269.4	254.9	240.8	228.5	219.3	211.3	206.4	204.8
147.5°	313.2	298.5	284.4	271.1	258.1	245.2	234.7	225.9	219.0	214.1	213.2
150°	310.2	296.7	284.4	271.5	260.2	247.8	238.2	230.6	223.7	219.3	218.8
152.5°	306.8	294.6	283.1	272.4	261.5	250.8	241.6	235.0	228.8	224.5	224.4
155°	301.6	290.9	281.7	272.6	264.0	254.9	247.3	241.4	236.0	232.8	232.8
157.5°	295.8	287.5	279.8	273.1	265.3	258.1	252.2	247.2	242.4	239.9	239.4
160°	291.9	284.9	279.0	273.1	266.6	260.2	254.9	251.1	246.8	244.6	244.6
162.5°	288.0	282.4	277.3	272.7	267.1	261.5	256.9	253.6	250.2	248.5	248.5
165°	282.8	278.5	274.8	271.5	267.7	263.4	259.7	257.5	254.9	253.7	254.3
167.5°	277.8	274.6	272.1	270.6	267.6	264.5	262.1	260.6	258.5	258.1	258.7
170°	274.8	272.0	270.4	269.4	267.2	264.5	263.4	262.3	260.7	260.2	261.3
172.5°	271.7	269.8	269.1	268.9	267.2	264.9	264.3	263.6	262.5	262.3	263.0
175°	268.2	267.2	267.2	267.7	266.6	265.6	265.0	265.0	264.0	264.5	265.0
177.5°	266.0	265.6	266.0	266.8	266.0	265.6	265.6	265.6	265.1	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1332.0	1334.6	1343.3	1349.5	1356.7	1360.7	1364.9	1368.0	1372.1	1373.1	1388.0
5°	1337.9	1350.8	1373.2	1389.9	1410.4	1432.9	1448.2	1455.3	1473.9	1489.3	1520.1
7.5°	1336.2	1363.6	1397.5	1432.6	1470.4	1505.2	1535.5	1571.4	1596.9	1635.3	1673.1
10°	1334.7	1371.3	1414.9	1459.8	1512.4	1561.1	1604.8	1653.5	1693.9	1747.2	1792.7
12.5°	1330.1	1374.4	1434.9	1488.0	1551.9	1619.1	1683.8	1746.3	1782.2	1870.9	1912.8
15°	1318.7	1371.3	1447.0	1527.8	1615.7	1695.2	1777.3	1842.8	1948.5	2026.2	2075.6
17.5°	1296.9	1370.6	1460.3	1557.8	1664.6	1769.4	1862.5	1961.8	2074.0	2167.9	2267.9
20°	1286.7	1367.4	1467.5	1575.3	1686.2	1804.9	1910.7	2030.0	2152.5	2244.9	2373.1
22.5°	1267.6	1359.2	1467.0	1587.1	1705.7	1828.4	1952.3	2072.6	2214.1	2341.4	2463.4
25°	1236.6	1339.3	1450.9	1584.9	1724.1	1847.2	1995.4	2155.1	2302.6	2466.2	2588.0
27.5°	1204.0	1313.5	1425.4	1550.1	1699.8	1846.0	2032.3	2212.8	2393.1	2534.4	2624.6
30°	1178.8	1285.3	1400.8	1526.5	1674.7	1848.5	2056.9	2253.8	2429.6	2550.8	2601.5
32.5°	1151.7	1259.7	1361.8	1493.6	1651.6	1846.9	2072.4	2277.9	2431.7	2512.3	2502.5
35°	1109.0	1199.4	1298.8	1425.8	1611.8	1835.7	2081.3	2280.1	2374.5	2357.1	2226.3
37.5°	1047.4	1123.4	1221.3	1360.4	1565.7	1811.9	2063.3	2212.5	2206.4	2065.4	1875.8
40°	1008.9	1073.7	1168.0	1314.2	1529.7	1796.6	2035.1	2132.0	2049.9	1852.9	1625.9
42.5°	958.7	1018.2	1112.6	1262.9	1490.3	1765.2	1981.2	2009.3	1848.7	1622.1	1414.0
45°	880.6	933.2	1030.7	1185.9	1431.0	1697.1	1849.7	1781.1	1565.0	1330.9	1172.4
47.5°	796.8	851.5	945.3	1104.8	1345.3	1594.6	1667.4	1521.4	1299.5	1109.6	964.1
50°	744.0	796.6	888.3	1049.3	1287.2	1510.5	1540.6	1352.1	1148.1	981.4	862.0
52.5°	690.7	740.2	830.4	991.8	1219.6	1413.0	1394.4	1202.2	1014.6	872.5	778.9
55°	611.2	658.1	744.0	895.4	1102.6	1255.8	1188.5	1005.0	849.9	739.5	668.4
57.5°	540.2	585.0	659.2	796.0	976.1	1081.4	995.7	841.1	717.7	632.8	579.7
60°	491.9	531.7	602.3	729.2	885.8	965.9	881.3	744.7	640.7	572.8	525.3
62.5°	446.3	480.9	546.3	661.6	797.5	864.9	779.2	663.5	575.0	514.8	474.5
65°	377.1	408.6	466.3	556.1	667.7	712.6	638.9	545.2	476.5	431.7	404.7
67.5°	314.1	340.7	390.6	461.3	543.4	576.1	519.9	447.4	395.8	359.7	338.3
70°	271.9	295.0	334.1	395.1	469.5	494.6	442.0	382.3	344.4	315.6	295.7
72.5°	236.6	253.4	289.0	336.1	398.1	418.0	381.4	328.9	293.6	271.9	256.2
75°	180.2	194.4	217.4	255.2	298.2	309.8	282.2	249.5	225.7	210.4	198.2
77.5°	130.0	140.3	157.0	180.4	210.1	220.6	203.0	181.3	163.9	153.5	146.8
80°	98.1	106.5	120.6	139.8	157.8	163.5	153.3	136.6	124.4	118.7	112.9
82.5°	72.5	77.2	85.7	98.8	111.1	117.9	109.1	99.2	92.7	87.4	85.2
85°	36.6	39.1	43.0	48.1	55.8	58.3	55.1	52.6	48.7	45.5	45.5
87.5°	13.8	13.9	15.8	17.1	19.3	21.2	21.0	20.4	20.2	19.5	19.1
90°	2.2	3.2	4.8	5.9	7.0	8.6	10.2	11.8	13.5	12.9	13.5
92.5°	9.9	14.4	18.6	23.1	31.1	45.1	68.2	91.0	82.7	62.4	45.2
95°	19.9	25.8	35.0	48.9	69.8	115.6	195.7	283.9	318.8	258.5	193.5
97.5°	31.8	36.4	44.3	58.1	80.8	124.4	214.7	361.7	494.1	528.6	482.5
100°	40.3	44.1	51.7	64.5	85.5	123.1	202.6	344.0	509.1	615.0	633.9
102.5°	49.8	53.2	60.2	71.8	91.0	124.8	192.4	318.3	481.2	619.3	684.2
105°	64.0	67.2	73.6	83.9	100.6	129.6	184.9	286.5	432.3	586.5	698.9
107.5°	78.4	81.5	87.8	97.5	112.9	138.4	184.4	266.4	389.0	529.1	656.5
110°	88.7	91.4	97.3	106.4	121.5	145.7	186.5	258.5	364.5	492.9	616.0





TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	98.2	100.9	106.8	115.9	130.5	153.0	190.9	254.3	348.2	461.6	576.1
115°	112.4	115.6	120.9	130.1	144.6	165.0	197.8	252.7	330.6	423.7	523.1
117.5°	126.3	129.0	133.9	144.2	157.6	177.9	207.1	253.6	320.3	400.8	484.7
120°	135.0	137.6	143.0	153.3	166.6	186.0	214.0	255.3	315.6	388.7	464.5
122.5°	143.1	145.8	151.6	161.4	175.7	194.6	220.5	258.4	312.5	378.8	448.6
125°	154.3	157.5	163.4	173.6	188.1	207.0	230.6	262.9	308.6	366.1	427.3
127.5°	163.7	167.8	173.7	185.0	199.5	217.7	239.0	268.1	306.6	355.0	408.9
130°	169.4	174.2	180.6	191.9	206.4	224.1	244.6	271.5	305.4	348.9	397.3
132.5°	174.1	179.4	187.1	198.4	212.4	229.8	249.8	274.1	304.9	343.3	386.5
135°	181.7	187.7	195.7	207.0	221.5	238.2	256.5	278.0	304.3	336.0	372.0
137.5°	188.9	194.7	203.3	214.5	227.9	243.9	261.4	280.5	303.1	329.7	358.8
140°	194.1	199.4	208.0	218.8	232.2	247.8	264.0	282.2	302.7	325.7	351.1
142.5°	198.8	204.6	212.4	223.1	235.7	250.8	266.6	283.5	301.8	322.3	343.7
145°	206.4	211.3	219.3	228.5	240.8	254.9	269.4	284.4	300.5	317.7	334.9
147.5°	214.1	219.0	225.9	234.7	245.2	258.1	271.1	284.4	298.5	313.2	327.7
150°	219.3	223.7	230.6	238.2	247.8	260.2	271.5	284.4	296.7	310.2	322.5
152.5°	224.5	228.8	235.0	241.6	250.8	261.5	272.4	283.1	294.6	306.8	317.8
155°	232.8	236.0	241.4	247.3	254.9	264.0	272.6	281.7	290.9	301.6	310.8
157.5°	239.9	242.4	247.2	252.2	258.1	265.3	273.1	279.8	287.5	295.8	303.2
160°	244.6	246.8	251.1	254.9	260.2	266.6	273.1	279.0	284.9	291.9	298.9
162.5°	248.5	250.2	253.6	256.9	261.5	267.1	272.7	277.3	282.4	288.0	293.8
165°	253.7	254.9	257.5	259.7	263.4	267.7	271.5	274.8	278.5	282.8	287.1
167.5°	258.1	258.5	260.6	262.1	264.5	267.6	270.6	272.1	274.6	277.8	281.3
170°	260.2	260.7	262.3	263.4	264.5	267.2	269.4	270.4	272.0	274.8	277.4
172.5°	262.3	262.5	263.6	264.3	264.9	267.2	268.9	269.1	269.8	271.7	274.0
175°	264.5	264.0	265.0	265.0	265.6	266.6	267.7	267.2	267.2	268.2	269.4
177.5°	265.6	265.1	265.6	265.6	265.6	266.0	266.8	266.0	265.6	266.0	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1393.1	1393.6	1399.3	1403.4	1401.3	1403.9	1404.9
5°	1522.0	1545.1	1557.3	1566.3	1566.9	1567.5	1572.7
7.5°	1704.8	1729.6	1747.7	1775.1	1783.3	1792.7	1790.0
10°	1838.2	1874.8	1906.2	1922.9	1940.9	1967.2	1946.0
12.5°	1962.9	2027.7	2075.6	2101.5	2118.4	2123.6	2113.3
15°	2168.5	2253.2	2298.8	2297.4	2355.2	2380.2	2341.1
17.5°	2357.1	2435.2	2497.8	2529.9	2578.0	2588.7	2583.8
20°	2472.6	2557.9	2606.6	2661.7	2686.8	2709.2	2713.1
22.5°	2572.1	2648.7	2701.0	2746.9	2767.9	2778.5	2784.9
25°	2674.6	2734.9	2766.4	2782.4	2788.1	2786.8	2778.5
27.5°	2667.6	2672.2	2637.5	2603.6	2573.1	2538.9	2527.1
30°	2598.3	2544.4	2448.2	2393.7	2313.5	2250.0	2275.7
32.5°	2416.1	2308.9	2200.8	2081.7	1983.0	1954.9	1926.7
35°	2062.1	1873.5	1763.2	1634.9	1583.6	1532.3	1497.0
37.5°	1668.3	1522.4	1391.6	1307.7	1256.2	1223.8	1206.4
40°	1442.5	1311.0	1203.2	1135.3	1096.2	1059.6	1054.4
42.5°	1262.3	1140.1	1059.0	1004.9	967.3	951.8	940.6
45°	1034.0	948.6	894.1	855.6	830.6	821.0	808.1
47.5°	875.2	814.8	773.9	747.7	728.9	721.7	720.7
50°	786.4	736.3	706.2	685.6	670.9	668.4	658.1
52.5°	719.6	676.3	652.8	634.9	624.2	617.0	614.0
55°	624.7	595.9	574.7	564.4	556.1	549.0	549.0
57.5°	546.6	522.5	508.5	499.7	497.2	492.2	489.0
60°	498.3	477.9	466.9	459.2	454.1	454.8	448.9
62.5°	451.2	437.8	427.4	419.7	413.6	413.7	414.1
65°	384.2	373.9	366.3	363.6	359.9	355.3	356.7
67.5°	325.6	315.9	309.9	305.6	304.3	301.8	305.6
70°	283.5	276.4	271.9	268.1	266.8	267.5	270.7
72.5°	245.0	240.0	237.0	235.3	232.4	232.5	234.8
75°	192.4	188.6	186.0	184.1	183.4	183.4	183.4
77.5°	141.4	140.4	139.3	136.5	136.6	137.4	137.5
80°	111.6	109.7	109.1	107.7	105.8	104.5	107.7
82.5°	83.4	81.4	80.8	80.6	77.6	77.4	80.0
85°	44.9	43.0	43.6	43.0	43.0	42.3	42.3
87.5°	18.7	18.3	18.0	18.4	18.0	17.6	18.5
90°	13.9	14.5	15.6	15.1	15.6	16.1	15.6
92.5°	35.9	31.8	28.9	28.0	26.3	26.9	25.9
95°	131.2	102.6	83.3	73.1	68.2	64.5	62.4
97.5°	386.4	317.1	252.8	213.1	188.9	174.4	169.8
100°	590.3	527.4	451.0	396.7	357.5	336.6	337.1
102.5°	682.8	646.1	597.7	555.4	524.3	506.8	494.5
105°	752.6	762.9	748.9	724.2	703.7	686.5	683.8
107.5°	743.9	790.9	810.0	810.5	803.6	797.8	792.9
110°	715.0	782.8	820.4	835.5	839.7	838.7	837.5



TEST NUMBER: P332011-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	677.1	753.1	801.4	829.0	842.4	846.4	846.6
115°	616.6	695.7	754.2	794.6	818.2	829.0	831.7
117.5°	565.4	636.4	695.9	737.9	765.0	780.5	784.1
120°	537.1	601.5	655.9	698.3	728.5	741.3	744.6
122.5°	514.3	574.0	624.4	662.2	689.3	703.5	707.6
125°	486.0	537.6	580.6	615.0	638.7	652.1	655.9
127.5°	461.2	507.7	546.9	577.5	597.7	609.8	613.3
130°	445.6	489.2	525.8	554.3	573.6	584.9	589.2
132.5°	431.0	471.6	506.4	533.2	552.5	562.5	565.5
135°	410.2	445.2	475.8	502.1	518.2	527.9	531.7
137.5°	390.1	420.2	446.8	468.9	485.2	493.4	495.9
140°	378.4	404.3	427.3	447.8	462.9	471.5	470.9
142.5°	367.3	389.6	409.7	427.2	440.5	448.3	447.7
145°	352.7	369.9	385.5	398.9	410.2	414.5	415.6
147.5°	341.8	355.7	366.7	376.9	384.6	388.7	389.1
150°	334.9	346.2	356.5	364.5	370.4	373.6	373.6
152.5°	328.5	338.5	346.9	353.3	358.8	360.7	360.7
155°	319.3	327.4	333.8	338.7	343.0	344.0	344.6
157.5°	310.4	316.7	321.7	325.9	329.1	330.0	329.9
160°	304.8	310.2	314.0	317.7	320.9	320.9	320.4
162.5°	298.8	303.8	307.1	309.5	312.4	312.4	311.8
165°	290.3	294.1	296.7	298.9	301.0	300.5	300.5
167.5°	283.7	285.9	287.9	288.8	290.3	289.7	289.7
170°	279.0	281.2	282.2	282.8	283.9	283.3	283.3
172.5°	275.1	276.8	277.5	277.6	278.7	277.8	277.3
175°	269.8	271.0	271.0	271.0	271.5	271.0	270.4
177.5°	266.8	267.3	267.3	266.8	267.3	266.5	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6

(END OF REPORT)