

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332080-830

Luminaire Tested: **S123DIP-S1165D1025U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332080-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7983.9 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332080-830

CATALOG NUMBER: S123DIP-S1165D1025U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332080-830

CATALOG NUMBER: S123DIP-S1165D1025U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332080-830

CATALOG NUMBER: S123DIP-S1165D1025U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.0
10°-20°	458.3	5.7
20°-30°	677.0	8.5
30°-40°	790.8	9.9
40°-50°	795.1	10.0
50°-60°	698.4	8.7
60°-70°	520.3	6.5
70°-80°	296.4	3.7
80°-90°	88.7	1.1
90°-100°	258.6	3.2
100°-110°	732.4	9.2
110°-120°	720.5	9.0
120°-130°	574.7	7.2
130°-140°	453.1	5.7
140°-150°	338.2	4.2
150°-160°	235.7	3.0
160°-170°	138.5	1.7
170°-180°	45.1	0.6
0°-30°	1297.6	16.3
0°-40°	2088.4	26.2
0°-60°	3581.8	44.9
0°-90°	4487.2	56.2
90°-120°	1711.5	21.4
90°-150°	3077.4	38.5
90°-180°	3497.0	43.8
0°-180°	7983.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	2	11	24	26	27	6
95°	32	104	558	163	109	35
105°	109	161	756	1323	1197	116
115°	193	240	579	1269	1456	191
125°	268	317	540	978	1148	238
135°	314	375	532	806	930	243
145°	358	411	526	661	727	225
155°	407	439	509	579	603	187
165°	445	458	487	517	526	125
175°	464	464	468	474	473	44
180°	465	465	465	465	465	



TEST NUMBER: P332080-830

CATALOG NUMBER: S123DIP-S1165D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	31.2	30.8	30.3	30.2	29.7	29.6	29.9	30.2	30.4	30.8	30.3
90°	1.9	3.8	5.7	8.5	10.4	12.3	15.1	17.9	20.7	23.6	22.6
92.5°	11.7	17.3	25.3	32.5	40.4	54.4	79.0	119.5	159.2	144.7	109.1
95°	32.0	34.8	45.1	61.2	85.6	122.3	202.3	342.4	496.7	557.9	452.5
97.5°	54.6	55.5	63.6	77.5	101.6	141.3	217.7	375.8	633.0	864.6	925.0
100°	69.7	70.6	77.2	90.3	112.9	149.6	215.5	354.7	602.1	891.0	1076.3
102.5°	85.4	87.1	92.9	105.4	125.7	159.4	218.5	336.6	556.9	842.1	1083.8
105°	109.1	112.0	117.6	128.9	146.8	176.0	226.8	323.7	501.4	756.4	1026.4
107.5°	134.3	137.1	142.6	153.7	170.5	197.6	242.1	322.7	466.1	680.8	926.0
110°	152.4	155.2	159.9	170.3	186.2	212.6	255.0	326.5	452.5	637.9	862.7



TEST NUMBER: P332080-830

CATALOG NUMBER: S123DIP-S1165D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.0	171.8	176.5	186.8	202.8	228.5	267.8	334.0	445.0	609.3	807.8
115°	192.8	196.6	202.3	211.7	227.7	253.1	288.8	346.2	442.1	578.6	741.4
117.5°	216.8	221.1	225.8	234.4	252.3	275.9	311.2	362.4	443.8	560.5	701.3
120°	233.3	236.1	240.8	250.2	268.2	291.6	325.6	374.5	446.9	552.2	680.2
122.5°	247.6	250.4	255.1	265.3	282.5	307.5	340.5	385.8	452.1	547.0	662.9
125°	268.2	270.0	275.7	286.0	303.9	329.3	362.2	403.6	460.1	540.1	640.7
127.5°	283.8	286.5	293.5	304.1	323.9	349.2	381.1	418.3	469.1	536.7	621.1
130°	293.5	296.3	304.8	316.1	335.8	361.3	392.3	428.1	475.1	534.4	610.6
132.5°	301.0	304.6	313.9	327.4	347.1	371.8	402.1	437.2	479.7	533.7	600.8
135°	314.2	318.0	328.4	342.4	362.2	387.6	416.8	448.7	486.4	532.5	588.1
137.5°	326.7	330.6	340.7	355.8	375.4	398.9	427.0	457.4	490.9	530.5	576.9
140°	335.0	339.6	349.0	364.1	383.0	406.4	433.8	461.9	493.9	529.7	570.1
142.5°	343.9	347.9	358.1	371.6	390.4	412.5	439.0	466.5	496.2	528.2	564.1
145°	358.4	361.3	369.8	383.9	399.8	421.5	445.9	471.4	497.7	525.9	556.0
147.5°	373.2	374.8	383.1	395.3	410.8	429.2	451.6	474.4	497.7	522.4	548.1
150°	383.0	383.9	391.3	403.6	416.8	433.8	455.3	475.1	497.7	519.3	542.8
152.5°	392.7	392.9	400.4	411.1	422.8	439.0	457.6	476.6	495.4	515.6	536.9
155°	407.4	407.4	413.0	422.4	432.8	445.9	461.9	477.0	492.9	509.0	527.8
157.5°	419.1	419.8	424.3	432.6	441.4	451.6	464.4	478.0	489.8	503.1	517.6
160°	428.1	428.1	431.9	439.3	445.9	455.3	466.7	478.0	488.3	498.6	510.9
162.5°	434.9	434.9	437.9	443.8	449.7	457.6	467.4	477.2	485.3	494.1	504.1
165°	445.0	444.0	445.9	450.6	454.4	461.0	468.5	475.1	480.8	487.4	494.8
167.5°	452.7	451.6	452.5	456.1	458.7	462.9	468.3	473.6	476.3	480.6	486.1
170°	457.2	455.3	456.3	459.1	461.0	462.9	467.6	471.4	473.3	476.1	480.8
172.5°	460.2	459.1	459.3	461.4	462.5	463.6	467.6	470.6	471.0	472.3	475.5
175°	463.8	462.9	461.9	463.8	463.8	464.8	466.7	468.5	467.6	467.6	469.5
177.5°	465.5	464.8	464.0	464.8	464.8	464.8	465.5	467.0	465.5	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332080-830

CATALOG NUMBER: S123DIP-S1165D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	30.3	30.2	30.1	30.3	30.2	30.3	30.5	30.3
90°	23.6	24.5	25.4	27.2	26.3	27.2	28.2	27.2
92.5°	79.2	62.9	55.5	50.6	48.9	46.1	47.0	45.3
95°	338.7	229.6	179.7	145.8	128.0	119.5	112.9	109.1
97.5°	844.3	676.3	554.9	442.3	373.0	330.6	305.2	297.1
100°	1109.3	1033.0	922.9	789.4	694.4	625.7	589.0	589.9
102.5°	1197.3	1194.9	1130.7	1046.0	972.0	917.7	887.0	865.3
105°	1223.0	1317.2	1335.0	1310.6	1267.2	1231.5	1201.5	1196.7
107.5°	1149.0	1301.7	1384.1	1417.7	1418.4	1406.4	1396.2	1387.5
110°	1078.2	1251.3	1369.8	1435.7	1462.1	1469.6	1467.7	1465.8



TEST NUMBER: P332080-830

CATALOG NUMBER: S123DIP-S1165D1025U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1008.1	1185.1	1317.9	1402.6	1450.8	1474.0	1481.2	1481.6
115°	915.4	1079.1	1217.4	1319.9	1390.5	1431.9	1450.8	1455.5
117.5°	848.3	989.6	1113.7	1217.8	1291.4	1338.8	1365.9	1372.2
120°	812.8	939.9	1052.8	1147.8	1222.1	1274.8	1297.4	1303.1
122.5°	785.0	900.0	1004.7	1092.9	1159.0	1206.4	1231.1	1238.3
125°	748.0	850.6	940.8	1016.1	1076.3	1117.7	1141.2	1147.8
127.5°	715.6	807.0	888.5	957.0	1010.6	1046.0	1067.2	1073.3
130°	695.3	780.0	856.1	920.1	970.0	1003.9	1023.6	1031.1
132.5°	676.5	754.3	825.3	886.3	933.1	967.0	984.5	989.8
135°	651.0	717.8	779.0	832.6	878.7	906.9	923.9	930.5
137.5°	627.9	682.7	735.4	781.8	820.6	849.2	863.5	867.8
140°	614.3	662.3	707.5	748.0	783.7	810.0	825.1	824.2
142.5°	601.5	642.8	681.9	717.1	747.6	770.9	784.5	783.5
145°	586.2	617.2	647.2	674.6	698.0	717.8	725.4	727.3
147.5°	573.5	598.1	622.5	641.9	659.7	673.1	680.2	681.0
150°	564.5	586.2	605.9	623.8	637.9	648.2	653.8	653.8
152.5°	556.2	574.9	592.4	607.2	618.3	627.9	631.3	631.3
155°	543.8	558.8	573.0	584.3	592.8	600.2	602.1	603.0
157.5°	530.7	543.2	554.1	563.0	570.3	576.0	577.5	577.3
160°	523.1	533.5	542.8	549.4	556.0	561.7	561.7	560.7
162.5°	514.1	522.9	531.6	537.4	541.8	546.6	546.6	545.6
165°	502.4	508.0	514.6	519.3	523.1	526.9	525.9	525.9
167.5°	492.2	496.5	500.3	503.7	505.4	508.0	507.1	507.1
170°	485.5	488.3	492.0	493.9	494.8	496.7	495.8	495.8
172.5°	479.5	481.5	484.6	485.7	485.9	487.8	486.1	485.3
175°	471.4	472.3	474.2	474.2	474.2	475.1	474.2	473.3
177.5°	466.3	467.0	467.8	467.8	467.0	467.8	466.3	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

(END OF REPORT)