

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331722-935

Luminaire Tested: **S122RDIP-S865D725U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331722-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D725U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5035.1 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331722-935

CATALOG NUMBER: S122RDIP-S865D725U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331722-935

CATALOG NUMBER: S122RDIP-S865D725U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32	29
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	19	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331722-935

CATALOG NUMBER: S122RDIP-S865D725U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	2.3
10°-20°	324.5	6.4
20°-30°	455.6	9.0
30°-40°	496.8	9.9
40°-50°	456.8	9.1
50°-60°	358.8	7.1
60°-70°	233.9	4.6
70°-80°	120.6	2.4
80°-90°	34.4	0.7
90°-100°	139.9	2.8
100°-110°	474.9	9.4
110°-120°	504.5	10.0
120°-130°	415.3	8.2
130°-140°	333.5	6.6
140°-150°	252.0	5.0
150°-160°	177.1	3.5
160°-170°	104.3	2.1
170°-180°	33.9	0.7
0°-30°	898.3	17.8
0°-40°	1395.1	27.7
0°-60°	2210.7	43.9
0°-90°	2599.7	51.6
90°-120°	1119.3	22.2
90°-150°	2120.1	42.1
90°-180°	2435.0	48.4
0°-180°	5035.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	1	9	23	22	22	3
95°	24	58	264	100	77	25
105°	82	124	499	892	758	87
115°	145	183	417	861	998	143
125°	202	239	401	698	810	179
135°	237	283	396	586	671	183
145°	270	311	394	490	536	170
155°	308	332	383	433	450	141
165°	335	345	367	389	395	94
175°	349	350	353	357	356	33
180°	350	350	350	350	350	



TEST NUMBER: P331722-935

CATALOG NUMBER: S122RDIP-S865D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.7	13.5	12.5	11.1	9.7	9.3	10.0	10.9	11.8	11.9	11.5
90°	0.7	2.7	5.4	6.7	8.1	10.1	13.4	18.2	22.2	22.9	22.2
92.5°	8.2	11.9	16.7	19.6	24.2	30.6	45.8	67.2	86.3	87.5	73.9
95°	23.6	26.3	33.0	39.0	49.8	66.0	96.9	155.5	233.6	263.8	230.8
97.5°	38.4	42.0	49.2	58.3	70.7	88.9	127.9	209.5	339.2	450.4	472.5
100°	51.8	53.8	59.9	70.7	84.1	103.0	138.6	220.8	366.1	531.7	628.6
102.5°	64.2	65.7	71.7	82.5	96.5	115.4	148.4	221.3	355.9	534.4	686.7
105°	82.1	84.8	89.5	99.6	114.4	133.3	164.9	224.8	335.9	498.7	677.8
107.5°	101.5	103.7	108.2	117.5	132.2	151.2	181.8	234.1	325.9	460.5	618.6
110°	114.4	117.1	121.1	129.9	144.0	163.6	193.1	241.6	323.7	442.2	581.5



TEST NUMBER: P331722-935

CATALOG NUMBER: S122RDIP-S865D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.2	129.0	133.5	141.7	155.3	175.4	204.0	249.7	324.3	430.3	555.7
115°	144.7	148.1	152.1	160.1	173.7	191.8	220.8	261.8	327.1	417.3	523.7
117.5°	163.8	166.5	170.6	177.7	190.6	209.5	236.3	274.7	331.9	411.0	503.4
120°	175.6	178.4	182.4	188.5	201.9	220.8	247.0	283.4	335.2	407.2	492.7
122.5°	187.0	189.2	193.1	199.8	213.2	232.6	257.3	290.9	339.0	405.0	483.5
125°	201.9	204.0	207.9	216.0	229.5	248.3	272.6	302.9	344.6	401.1	470.5
127.5°	213.8	216.5	222.1	231.0	243.9	263.3	286.9	314.0	350.4	398.8	458.3
130°	220.8	223.4	230.1	239.6	253.0	271.9	295.5	321.1	354.7	397.8	450.3
132.5°	227.2	230.5	237.7	247.7	261.7	280.5	303.0	328.0	359.0	397.3	443.8
135°	236.9	239.6	247.7	257.8	273.3	292.1	313.7	337.2	364.1	396.4	434.8
137.5°	246.1	249.3	257.4	268.1	283.5	301.0	322.3	344.2	368.7	396.3	428.4
140°	253.0	255.7	263.8	274.6	289.4	306.9	327.1	347.9	370.8	395.7	424.7
142.5°	260.0	262.3	269.8	280.5	294.8	311.3	330.9	351.2	372.5	395.7	420.9
145°	270.5	273.3	280.0	290.1	303.5	318.3	336.6	355.3	374.2	394.4	415.9
147.5°	281.9	283.9	290.3	299.6	310.8	324.0	341.1	357.7	374.8	392.0	410.9
150°	289.4	291.4	296.8	305.6	315.6	327.8	343.3	358.7	374.2	390.4	406.5
152.5°	297.0	297.9	303.2	310.9	320.5	331.6	345.4	359.3	373.2	387.7	402.8
155°	307.5	308.2	312.3	319.7	327.1	337.2	348.6	360.1	371.5	383.0	395.7
157.5°	316.5	317.1	320.4	326.8	332.8	341.2	350.9	360.1	368.4	378.2	389.2
160°	322.4	323.0	325.7	331.1	336.6	343.9	352.0	360.1	366.8	374.9	384.4
162.5°	328.3	327.9	330.6	334.9	339.8	345.5	352.6	359.6	365.2	372.2	380.0
165°	335.2	334.5	335.9	339.9	343.3	347.3	353.4	358.1	362.1	366.8	372.9
167.5°	340.9	340.0	341.2	343.8	346.2	348.8	353.2	357.1	359.0	362.1	365.8
170°	344.6	343.3	343.9	345.9	347.3	349.3	352.7	356.0	357.4	359.4	362.1
172.5°	346.7	345.9	345.5	347.6	348.4	349.8	352.1	354.4	355.2	356.2	358.3
175°	349.3	348.6	347.9	349.3	349.3	350.0	351.3	352.7	352.0	352.7	353.4
177.5°	350.5	349.5	348.9	350.0	350.0	350.0	350.5	351.6	350.5	350.0	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331722-935

CATALOG NUMBER: S122RDIP-S865D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	11.2	10.8	10.8	10.8	10.8	10.8	10.8	10.8
90°	21.5	20.2	21.5	22.2	22.2	22.2	22.2	22.2
92.5°	58.7	50.4	44.7	40.6	40.0	37.8	38.4	37.3
95°	176.3	135.3	107.0	92.2	83.4	78.1	76.0	76.7
97.5°	411.5	336.7	263.8	215.2	183.0	166.5	156.7	151.0
100°	614.5	531.1	438.9	357.4	301.5	272.6	253.0	240.9
102.5°	747.5	728.7	661.2	574.9	514.2	464.8	440.4	424.0
105°	817.8	893.8	902.6	880.4	838.6	796.9	767.9	758.5
107.5°	767.2	881.7	951.7	984.3	989.5	987.2	981.5	968.9
110°	723.5	844.0	930.1	985.3	1014.3	1027.1	1033.1	1032.4



TEST NUMBER: P331722-935

CATALOG NUMBER: S122RDIP-S865D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	683.7	799.3	891.4	954.7	994.9	1016.3	1027.8	1031.4
115°	634.6	738.3	826.5	895.8	943.6	974.6	992.0	998.2
117.5°	597.8	688.8	768.8	833.8	882.5	915.2	933.7	938.7
120°	579.5	663.0	734.3	795.6	842.7	874.3	893.8	900.5
122.5°	565.0	641.4	708.9	764.3	806.6	837.7	855.1	860.7
125°	543.8	613.1	672.4	722.8	761.9	787.5	804.3	809.7
127.5°	523.0	585.7	641.5	688.1	722.2	746.1	760.7	765.0
130°	509.5	567.4	620.5	665.0	697.9	720.8	734.3	739.7
132.5°	496.5	550.2	599.0	640.8	673.2	696.0	708.4	713.3
135°	478.5	523.0	567.4	605.0	634.0	656.3	668.3	671.1
137.5°	464.2	501.3	536.6	569.4	595.8	614.9	625.5	629.6
140°	455.0	487.3	518.2	547.9	569.4	586.9	597.0	601.1
142.5°	447.5	474.9	501.5	526.3	546.8	562.7	571.7	572.5
145°	436.8	459.0	479.9	499.4	515.6	527.0	533.7	535.7
147.5°	428.6	446.1	462.4	476.6	490.0	499.1	503.7	504.9
150°	422.7	437.5	451.6	463.7	473.8	481.9	485.9	486.6
152.5°	416.7	430.5	442.5	453.0	460.9	467.9	470.9	471.0
155°	408.5	419.3	429.4	436.8	444.2	448.9	451.6	450.3
157.5°	399.0	408.0	416.5	422.2	427.5	431.4	432.7	432.7
160°	393.0	400.5	407.9	412.6	417.3	420.7	421.3	421.3
162.5°	387.1	393.5	399.8	403.5	408.1	410.4	411.1	410.5
165°	378.2	383.0	387.7	390.4	393.0	395.7	395.7	395.1
167.5°	369.8	373.4	376.6	379.1	380.3	381.8	381.6	380.8
170°	365.5	367.5	370.1	371.5	372.2	374.2	373.5	372.2
172.5°	360.6	362.1	364.3	365.1	365.8	366.7	366.0	365.2
175°	355.3	356.0	356.7	357.4	357.4	358.1	357.4	356.0
177.5°	351.6	351.6	352.1	352.1	352.1	352.1	351.6	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0

(END OF REPORT)