

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331460-840

Luminaire Tested: **S122DIP-S1005D1080U840-4F0-1E-UDD-D1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331460-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D1080U840-4F0-1E-UDD-D1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7966.4 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331460-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-D1

### Luminous Intensity Polar Plot





TEST NUMBER: P331460-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-D1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	95	91	86	82	87	83	79	76	69	66	63	56	54	52	44	42	41	35				
2	86	78	72	66	79	72	66	61	59	55	51	48	45	42	38	36	34	29				
3	78	68	61	54	71	63	56	50	52	47	43	42	38	35	33	30	28	24				
4	71	60	52	45	65	55	48	42	46	40	36	37	33	30	29	26	24	20				
5	65	53	45	39	60	49	42	36	41	35	31	33	29	25	26	23	20	17				
6	60	48	39	33	55	44	36	31	37	31	27	30	26	22	24	20	18	15				
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13				
8	51	39	31	25	47	36	29	24	30	24	20	25	20	17	20	16	14	12				
9	48	35	28	23	44	33	26	21	28	22	18	23	18	15	18	15	13	10				
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	14	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17241	17241	17241
5°	17327	16597	16534
10°	17217	16106	15925
15°	16980	15587	15284
20°	16681	15031	14669
25°	16384	14494	14107
30°	15966	13945	13546
35°	15544	13412	13150
40°	15099	12958	12754
45°	14678	12551	12415
50°	14226	12185	12082
55°	13750	11789	11742
60°	13168	11380	11382
65°	12566	10901	10957
70°	11886	10385	10497
75°	11021	9881	10071
80°	9646	9362	9643
85°	8334	8915	9308



TEST NUMBER: P331460-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-D1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.2	1.3
10°-20°	290.2	3.6
20°-30°	439.7	5.5
30°-40°	535.6	6.7
40°-50°	576.2	7.2
50°-60°	559.5	7.0
60°-70°	488.6	6.1
70°-80°	376.1	4.7
80°-90°	258.0	3.2
90°-100°	262.0	3.3
100°-110°	400.6	5.0
110°-120°	551.5	6.9
120°-130°	661.8	8.3
130°-140°	709.8	8.9
140°-150°	680.2	8.5
150°-160°	567.6	7.1
160°-170°	376.5	4.7
170°-180°	131.6	1.7
0°-30°	831.1	10.4
0°-40°	1366.6	17.2
0°-60°	2502.3	31.4
0°-90°	3625.0	45.5
90°-120°	1214.0	15.2
90°-150°	3265.8	41.0
90°-180°	4341.0	54.5
0°-180°	7966.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1071	1066	1057	1066	1065	102
15°	1022	1024	1024	1038	1037	288
25°	929	940	953	971	976	427
35°	800	827	856	889	901	500
45°	656	699	752	798	816	506
55°	503	560	639	693	715	450
65°	344	420	511	572	594	341
75°	190	278	376	440	463	201
85°	56	152	251	313	337	60
90°	17	122	245	303	325	14
95°	73	158	253	310	328	80
105°	260	310	391	446	465	275
115°	475	502	567	610	626	470
125°	686	698	742	779	793	613
135°	885	898	916	946	956	684
145°	1072	1080	1087	1097	1101	670
155°	1226	1229	1233	1238	1235	564
165°	1334	1333	1333	1340	1335	376
175°	1388	1384	1382	1389	1383	132
180°	1390	1390	1390	1390	1390	



TEST NUMBER: P331460-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8
2.5°	1074.1	1073.3	1072.4	1071.6	1070.8	1069.3	1067.4	1065.5	1063.6	1061.7	1063.1
5°	1071.0	1070.0	1068.9	1067.8	1066.8	1065.3	1063.3	1061.2	1059.1	1057.0	1059.1
7.5°	1061.4	1060.7	1060.0	1059.3	1058.6	1057.5	1055.9	1054.3	1052.8	1051.2	1053.6
10°	1054.0	1053.3	1052.6	1051.9	1051.2	1050.4	1049.4	1048.2	1047.2	1046.2	1048.9
12.5°	1041.6	1041.7	1041.9	1042.0	1042.1	1041.8	1041.1	1040.3	1039.6	1038.7	1041.6
15°	1021.5	1022.2	1022.8	1023.5	1024.2	1024.5	1024.5	1024.5	1024.5	1024.5	1027.6
17.5°	995.4	996.9	998.4	999.8	1001.2	1002.5	1003.6	1004.7	1005.8	1006.9	1010.2
20°	978.2	979.9	981.6	983.3	985.0	986.5	988.0	989.3	990.7	992.1	995.8
22.5°	959.6	961.5	963.5	965.5	967.6	969.5	971.4	973.3	975.2	977.1	981.0
25°	928.6	931.0	933.4	935.8	938.3	941.0	944.0	947.2	950.3	953.3	957.5
27.5°	891.4	895.3	899.3	903.2	907.2	910.9	914.5	918.2	921.8	925.5	930.7
30°	866.7	871.1	875.7	880.1	884.5	889.1	893.5	898.0	902.4	907.0	912.4
32.5°	839.4	844.4	849.5	854.5	859.5	864.6	870.0	875.3	880.6	885.9	892.2
35°	800.1	806.0	811.8	817.7	823.5	829.7	836.3	842.7	849.3	855.9	863.4
37.5°	757.4	764.2	770.9	777.6	784.4	791.9	800.4	808.9	817.4	825.9	834.2
40°	728.9	736.5	744.1	751.6	759.2	767.6	776.9	786.2	795.5	804.8	813.7
42.5°	701.8	709.2	716.8	724.4	732.0	741.0	751.7	762.4	773.1	783.8	793.5
45°	656.2	665.5	674.8	684.1	693.4	704.0	716.1	728.1	740.1	752.1	762.9
47.5°	611.4	621.5	631.6	641.7	651.8	663.9	678.0	692.1	706.2	720.2	731.4
50°	580.4	591.1	601.7	612.4	623.0	636.1	651.6	667.0	682.5	698.0	709.7
52.5°	550.7	561.9	573.1	584.3	595.5	609.3	625.5	641.9	658.1	674.5	686.4
55°	503.0	515.3	527.8	540.2	552.5	567.6	585.5	603.4	621.3	639.1	651.6
57.5°	456.0	469.9	483.8	497.9	511.8	527.9	546.1	564.3	582.6	600.8	614.1
60°	422.5	437.3	452.1	466.9	481.7	498.9	518.5	538.1	557.6	577.2	590.4
62.5°	392.8	408.1	423.4	438.8	454.1	471.6	491.2	510.8	530.5	550.1	563.9
65°	343.6	360.4	377.3	394.2	411.0	429.6	449.9	470.1	490.4	510.7	524.8
67.5°	298.4	316.0	333.6	351.2	368.8	388.0	408.8	429.6	450.3	471.1	485.3
70°	266.2	284.1	301.9	319.8	337.7	357.3	378.7	400.0	421.3	442.6	457.4
72.5°	236.5	254.9	273.4	291.8	310.2	330.2	351.8	373.4	395.1	416.7	431.1
75°	190.4	209.6	228.8	248.1	267.4	288.0	310.0	332.0	354.1	376.1	390.8
77.5°	145.8	165.9	186.1	206.2	226.4	247.6	270.0	292.4	314.7	337.1	351.8
80°	116.0	137.0	158.0	179.0	200.0	221.7	244.0	266.4	288.7	311.0	325.5
82.5°	91.3	112.0	132.7	153.4	174.1	195.8	218.4	241.1	263.7	286.3	300.7
85°	55.7	77.1	98.4	119.7	141.0	162.7	184.7	206.7	228.7	250.7	265.2
87.5°	30.6	51.7	72.8	93.9	115.0	137.2	160.4	183.5	206.7	229.8	243.8
90°	16.7	39.7	62.8	85.8	109.0	134.4	162.1	189.9	217.6	245.3	258.6
92.5°	35.1	55.9	76.9	97.8	118.6	140.3	162.8	185.4	207.9	230.5	244.1
95°	73.4	92.2	110.9	129.7	148.5	168.4	189.6	210.8	231.9	253.1	266.1
97.5°	122.3	139.0	155.6	172.3	188.9	207.7	228.5	249.3	270.1	290.8	303.6
100°	159.8	174.6	189.5	204.2	219.0	236.5	256.5	276.6	296.6	316.7	329.4
102.5°	198.0	211.3	224.6	237.8	251.2	267.6	287.3	307.1	326.8	346.5	359.1
105°	259.9	270.7	281.4	292.3	303.0	317.5	336.0	354.4	372.7	391.1	403.7
107.5°	324.0	333.1	342.1	351.3	360.4	373.5	390.7	407.8	425.0	442.0	453.8
110°	364.0	372.4	380.8	389.3	397.8	410.4	427.3	444.1	460.9	477.8	488.8



TEST NUMBER: P331460-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	409.0	416.4	423.7	431.0	438.4	450.0	465.7	481.6	497.5	513.2	523.6
115°	475.4	480.8	486.1	491.4	496.8	507.0	521.9	536.8	551.8	566.7	576.8
117.5°	540.0	544.6	549.2	553.7	558.3	566.9	579.9	592.7	605.5	618.3	627.9
120°	584.1	587.5	591.1	594.5	597.9	605.5	617.2	628.8	640.6	652.3	661.9
122.5°	624.5	627.5	630.6	633.6	636.7	644.0	655.4	666.9	678.3	689.8	698.5
125°	685.8	688.1	690.5	692.9	695.2	701.5	711.7	722.0	732.2	742.4	750.8
127.5°	747.0	749.6	752.2	754.9	757.5	762.9	770.7	778.7	786.7	794.6	802.1
130°	785.5	788.6	791.6	794.7	797.7	802.5	809.3	816.0	822.6	829.4	837.1
132.5°	828.7	831.1	833.5	836.0	838.4	842.4	848.1	853.7	859.4	865.2	871.9
135°	884.8	887.7	890.6	893.4	896.4	899.7	903.7	907.7	911.6	915.5	922.5
137.5°	945.6	947.9	950.2	952.4	954.7	956.9	959.2	961.3	963.5	965.7	971.8
140°	982.2	984.2	986.2	988.3	990.2	992.2	994.2	996.2	998.2	1000.2	1005.7
142.5°	1019.8	1021.8	1023.8	1025.7	1027.7	1029.3	1030.3	1031.3	1032.4	1033.4	1037.9
145°	1072.2	1074.0	1075.8	1077.6	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1089.7
147.5°	1120.2	1122.5	1124.6	1126.8	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.7
150°	1153.1	1154.7	1156.2	1157.8	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6
152.5°	1182.1	1183.8	1185.3	1186.9	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9
155°	1225.9	1226.6	1227.4	1228.2	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2
157.5°	1263.1	1263.6	1264.1	1264.7	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4
160°	1285.7	1286.2	1286.7	1287.2	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7
162.5°	1306.3	1306.4	1306.5	1306.6	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7
165°	1333.7	1333.5	1333.2	1332.9	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4
167.5°	1356.8	1355.9	1355.1	1354.4	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8
170°	1369.0	1368.2	1367.4	1366.5	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0
172.5°	1377.4	1376.6	1375.8	1375.0	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5
175°	1387.8	1386.9	1386.1	1385.3	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7
177.5°	1391.9	1391.3	1390.7	1390.1	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331460-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8
2.5°	1064.4	1065.8	1067.2	1067.6	1067.0	1066.5	1065.9	1065.4
5°	1061.2	1063.3	1065.3	1066.1	1065.8	1065.5	1065.1	1064.8
7.5°	1056.1	1058.6	1061.1	1062.2	1061.8	1061.5	1061.1	1060.8
10°	1051.7	1054.5	1057.2	1058.4	1058.0	1057.7	1057.4	1057.0
12.5°	1044.3	1047.0	1049.8	1051.0	1050.7	1050.3	1050.0	1049.7
15°	1030.8	1033.8	1036.9	1038.3	1037.9	1037.6	1037.2	1036.9
17.5°	1013.4	1016.6	1019.9	1021.5	1021.5	1021.5	1021.5	1021.5
20°	999.6	1003.4	1007.1	1009.1	1009.1	1009.1	1009.1	1009.1
22.5°	984.7	988.6	992.3	994.5	995.0	995.6	996.1	996.7
25°	961.6	965.7	969.9	972.4	973.5	974.5	975.5	976.5
27.5°	935.9	941.2	946.4	949.4	950.2	950.9	951.7	952.4
30°	918.0	923.4	929.0	932.2	933.2	934.2	935.3	936.3
32.5°	898.6	904.8	911.2	915.2	917.2	919.0	920.9	922.7
35°	871.0	878.6	886.2	891.1	893.5	896.0	898.4	900.7
37.5°	842.6	851.0	859.4	864.8	867.4	870.0	872.5	875.0
40°	822.6	831.6	840.5	846.6	849.7	852.7	855.9	859.0
42.5°	803.2	813.0	822.8	829.2	832.3	835.5	838.5	841.6
45°	773.5	784.2	794.8	801.8	805.3	808.7	812.1	815.6
47.5°	742.6	753.7	764.9	772.3	776.1	779.9	783.7	787.5
50°	721.3	733.1	744.8	752.6	756.3	760.0	763.9	767.6
52.5°	698.4	710.3	722.4	730.3	734.4	738.5	742.6	746.6
55°	664.0	676.3	688.7	697.1	701.6	706.1	710.5	715.0
57.5°	627.5	640.9	654.2	663.1	667.6	672.2	676.7	681.3
60°	603.4	616.5	629.5	638.5	643.3	648.1	653.0	657.7
62.5°	577.8	591.7	605.6	614.8	619.4	623.9	628.4	633.0
65°	539.0	553.0	567.1	576.4	580.9	585.3	589.9	594.3
67.5°	499.6	513.8	528.1	537.6	542.2	546.8	551.6	556.2
70°	472.2	487.0	501.8	511.2	515.3	519.5	523.6	527.8
72.5°	445.7	460.2	474.6	484.4	489.4	494.3	499.3	504.2
75°	405.7	420.4	435.3	444.8	449.3	453.8	458.3	462.7
77.5°	366.5	381.2	396.0	405.8	410.5	415.4	420.2	425.0
80°	339.9	354.5	368.9	378.5	383.3	388.1	392.9	397.8
82.5°	315.2	329.6	344.1	353.6	358.1	362.6	367.2	371.7
85°	279.6	294.1	308.5	318.1	323.0	327.8	332.5	337.4
87.5°	257.7	271.7	285.6	294.8	299.2	303.7	308.1	312.6
90°	271.9	285.1	298.3	307.1	311.4	315.9	320.2	324.7
92.5°	257.6	271.2	284.8	293.7	297.8	302.1	306.2	310.4
95°	279.2	292.3	305.3	313.7	317.3	320.8	324.5	328.1
97.5°	316.3	329.1	341.8	350.1	354.2	358.2	362.1	366.2
100°	342.1	354.9	367.6	375.7	379.2	382.7	386.3	389.8
102.5°	371.7	384.5	397.1	405.2	408.7	412.2	415.8	419.3
105°	416.3	428.9	441.4	449.6	453.3	457.2	460.9	464.7
107.5°	465.5	477.4	489.1	496.2	498.9	501.5	504.0	506.6
110°	499.8	510.8	521.8	528.9	531.8	534.8	537.9	540.8





TEST NUMBER: P331460-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	534.0	544.4	554.7	561.6	564.7	567.9	571.2	574.4
115°	586.8	596.9	607.0	613.5	616.5	619.6	622.5	625.5
117.5°	637.4	647.0	656.6	662.7	665.4	668.1	670.9	673.6
120°	671.5	681.2	690.7	697.0	700.0	703.1	706.1	709.0
122.5°	707.3	716.0	724.8	730.4	733.1	735.8	738.4	741.0
125°	759.4	767.9	776.4	782.0	784.9	787.7	790.5	793.3
127.5°	809.7	817.4	825.0	829.8	832.0	834.2	836.4	838.6
130°	844.9	852.5	860.3	865.1	866.8	868.5	870.1	871.8
132.5°	878.8	885.7	892.4	896.9	898.8	900.6	902.5	904.4
135°	929.5	936.4	943.4	947.9	949.9	951.8	953.8	955.7
137.5°	978.0	984.1	990.2	993.9	995.2	996.5	997.7	999.1
140°	1011.2	1016.7	1022.2	1025.4	1026.4	1027.5	1028.5	1029.6
142.5°	1042.6	1047.2	1051.8	1054.5	1055.2	1056.0	1056.7	1057.4
145°	1092.1	1094.4	1096.7	1098.2	1098.9	1099.5	1100.2	1101.0
147.5°	1136.5	1137.3	1138.2	1138.5	1138.4	1138.2	1138.0	1137.9
150°	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9
152.5°	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9
155°	1235.5	1236.8	1238.1	1238.3	1237.6	1236.8	1236.0	1235.2
157.5°	1271.1	1272.9	1274.7	1275.0	1273.6	1272.4	1271.2	1269.9
160°	1292.3	1293.8	1295.5	1295.7	1294.6	1293.6	1292.5	1291.5
162.5°	1311.5	1313.2	1315.0	1315.2	1314.0	1312.8	1311.5	1310.3
165°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1334.9
167.5°	1356.7	1358.5	1360.3	1360.5	1359.2	1357.8	1356.5	1355.1
170°	1367.9	1369.7	1371.5	1371.7	1370.1	1368.6	1367.0	1365.4
172.5°	1376.3	1378.2	1380.0	1380.1	1378.6	1377.0	1375.4	1373.8
175°	1385.5	1387.4	1389.2	1389.3	1387.8	1386.1	1384.6	1383.0
177.5°	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1

(END OF REPORT)