

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332053-830

Luminaire Tested: **S123DIP-S1165D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332053-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D365U830-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5722.8 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332053-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332053-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	73	71	69
2	95	87	80	75	90	83	77	72	76	72	67	70	66	63	64	61	58
3	86	76	69	62	82	73	66	61	67	61	57	62	57	53	57	53	50
4	79	68	59	53	75	65	57	51	60	53	48	55	50	46	51	46	43
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	46	41	37
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	37	33
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29
8	58	45	37	31	55	43	36	30	40	34	29	37	32	28	35	30	26
9	54	41	33	28	52	40	32	27	37	31	26	35	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332053-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.3	2.8
10°-20°	458.3	8.0
20°-30°	677.0	11.8
30°-40°	790.8	13.8
40°-50°	795.1	13.9
50°-60°	698.4	12.2
60°-70°	520.3	9.1
70°-80°	296.4	5.2
80°-90°	86.4	1.5
90°-100°	91.6	1.6
100°-110°	259.3	4.5
110°-120°	255.1	4.5
120°-130°	203.5	3.6
130°-140°	160.4	2.8
140°-150°	119.7	2.1
150°-160°	83.4	1.5
160°-170°	49.0	0.9
170°-180°	16.0	0.3
0°-30°	1297.6	22.7
0°-40°	2088.4	36.5
0°-60°	3581.8	62.6
0°-90°	4484.9	78.4
90°-120°	605.9	10.6
90°-150°	1089.5	19.0
90°-180°	1238.0	21.6
0°-180°	5722.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	1	4	8	9	10	5
95°	11	37	198	58	39	12
105°	39	57	268	468	424	41
115°	68	85	205	449	515	68
125°	95	112	191	346	406	84
135°	111	133	188	285	329	86
145°	127	145	186	234	258	80
155°	144	156	180	205	214	66
165°	158	162	173	183	186	44
175°	164	164	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P332053-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	30.9	30.3	29.6	29.0	28.4	28.0	27.9	27.9	27.8	27.7	27.4
90°	0.7	1.3	2.0	3.0	3.7	4.3	5.4	6.3	7.4	8.3	8.0
92.5°	4.1	6.1	9.0	11.5	14.3	19.2	28.0	42.3	56.4	51.2	38.6
95°	11.3	12.3	16.0	21.7	30.3	43.3	71.6	121.2	175.9	197.6	160.2
97.5°	19.3	19.6	22.5	27.4	36.0	50.0	77.1	133.0	224.1	306.1	327.4
100°	24.7	25.0	27.3	32.0	40.0	53.0	76.3	125.5	213.2	315.5	381.1
102.5°	30.3	30.8	32.9	37.3	44.5	56.5	77.4	119.1	197.2	298.1	383.7
105°	38.6	39.7	41.7	45.6	51.9	62.3	80.3	114.6	177.6	267.8	363.4
107.5°	47.6	48.5	50.5	54.4	60.3	69.9	85.8	114.2	165.0	241.0	327.8
110°	53.9	55.0	56.6	60.3	66.0	75.3	90.3	115.6	160.2	225.8	305.5



TEST NUMBER: P332053-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.9	60.8	62.5	66.2	71.8	80.9	94.8	118.3	157.5	215.7	286.0
115°	68.2	69.7	71.6	74.9	80.6	89.6	102.3	122.5	156.6	204.8	262.5
117.5°	76.7	78.2	79.9	83.0	89.4	97.6	110.2	128.3	157.1	198.4	248.3
120°	82.6	83.6	85.3	88.6	94.9	103.2	115.3	132.5	158.3	195.5	240.8
122.5°	87.7	88.7	90.3	94.0	100.0	108.9	120.6	136.6	160.0	193.7	234.7
125°	94.9	95.6	97.6	101.2	107.5	116.6	128.3	142.9	162.9	191.1	226.9
127.5°	100.5	101.4	104.0	107.6	114.6	123.7	134.9	148.1	166.1	190.0	219.9
130°	104.0	104.9	107.9	111.9	118.9	127.9	138.9	151.6	168.2	189.2	216.1
132.5°	106.6	107.8	111.1	115.9	122.9	131.7	142.3	154.8	169.8	188.9	212.7
135°	111.2	112.5	116.2	121.2	128.3	137.2	147.5	158.9	172.2	188.5	208.2
137.5°	115.6	117.1	120.6	125.9	132.9	141.2	151.2	161.9	173.8	187.8	204.2
140°	118.6	120.3	123.6	128.9	135.5	143.9	153.5	163.5	174.8	187.6	201.8
142.5°	121.8	123.2	126.8	131.6	138.3	146.0	155.4	165.1	175.7	187.0	199.7
145°	126.9	127.9	130.9	135.9	141.6	149.2	157.9	166.8	176.2	186.2	196.8
147.5°	132.1	132.7	135.6	140.0	145.4	151.9	159.9	168.0	176.2	184.9	194.1
150°	135.5	135.9	138.6	142.9	147.5	153.5	161.2	168.2	176.2	183.9	192.2
152.5°	139.0	139.1	141.8	145.5	149.7	155.4	162.0	168.7	175.4	182.6	190.0
155°	144.2	144.2	146.2	149.6	153.3	157.9	163.5	168.9	174.6	180.2	186.8
157.5°	148.4	148.6	150.2	153.2	156.3	159.9	164.4	169.2	173.4	178.1	183.2
160°	151.6	151.6	152.9	155.5	157.9	161.2	165.2	169.2	172.9	176.5	180.9
162.5°	153.9	153.9	155.0	157.1	159.2	162.0	165.5	168.9	171.8	174.9	178.4
165°	157.5	157.2	157.9	159.6	160.9	163.2	165.9	168.2	170.2	172.6	175.2
167.5°	160.2	159.9	160.2	161.5	162.4	163.9	165.8	167.7	168.6	170.1	172.1
170°	161.8	161.2	161.6	162.5	163.2	163.9	165.5	166.8	167.6	168.5	170.2
172.5°	163.0	162.5	162.6	163.3	163.7	164.1	165.5	166.6	166.7	167.2	168.3
175°	164.2	163.9	163.5	164.2	164.2	164.6	165.2	165.9	165.5	165.5	166.2
177.5°	164.9	164.6	164.3	164.6	164.6	164.6	164.9	165.3	164.9	164.6	164.9
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332053-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	27.2	27.1	26.9	26.9	26.8	26.9	26.9	26.9
90°	8.3	8.7	9.0	9.6	9.3	9.6	10.0	9.6
92.5°	28.1	22.2	19.6	17.9	17.3	16.3	16.7	16.0
95°	119.9	81.2	63.6	51.7	45.3	42.3	40.0	38.6
97.5°	298.9	239.4	196.4	156.7	132.1	117.1	108.0	105.2
100°	392.7	365.7	326.8	279.5	245.8	221.5	208.5	208.9
102.5°	423.9	423.0	400.3	370.3	344.1	324.9	314.1	306.3
105°	433.0	466.3	472.6	464.0	448.7	436.0	425.4	423.7
107.5°	406.7	460.8	490.0	501.9	502.2	497.9	494.3	491.3
110°	381.7	443.0	484.9	508.3	517.6	520.3	519.6	519.0





TEST NUMBER: P332053-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	356.9	419.5	466.6	496.5	513.6	521.9	524.4	524.5
115°	324.0	382.0	431.0	467.3	492.3	506.9	513.6	515.3
117.5°	300.3	350.3	394.3	431.1	457.2	474.0	483.5	485.8
120°	287.8	332.7	372.7	406.3	432.6	451.3	459.3	461.3
122.5°	278.0	318.6	355.6	386.9	410.3	427.1	435.8	438.4
125°	264.8	301.1	333.1	359.8	381.1	395.7	404.1	406.3
127.5°	253.4	285.7	314.5	338.8	357.8	370.3	377.9	379.9
130°	246.1	276.2	303.1	325.7	343.4	355.4	362.4	365.0
132.5°	239.5	267.0	292.2	313.8	330.4	342.3	348.6	350.4
135°	230.5	254.1	275.8	294.7	311.1	321.1	327.1	329.4
137.5°	222.3	241.7	260.3	276.8	290.5	300.7	305.7	307.3
140°	217.5	234.5	250.4	264.8	277.5	286.8	292.1	291.8
142.5°	213.0	227.5	241.4	253.8	264.7	273.0	277.7	277.4
145°	207.5	218.5	229.1	238.8	247.1	254.1	256.8	257.5
147.5°	203.0	211.8	220.4	227.2	233.6	238.3	240.8	241.1
150°	199.8	207.5	214.5	220.8	225.8	229.5	231.5	231.5
152.5°	196.9	203.5	209.7	215.0	218.9	222.3	223.5	223.5
155°	192.6	197.8	202.8	206.8	209.8	212.5	213.2	213.5
157.5°	187.8	192.3	196.1	199.3	201.9	203.9	204.4	204.3
160°	185.2	188.9	192.2	194.5	196.8	198.9	198.9	198.5
162.5°	182.0	185.1	188.2	190.3	191.8	193.5	193.5	193.2
165°	177.9	179.8	182.2	183.9	185.2	186.5	186.2	186.2
167.5°	174.3	175.8	177.1	178.3	178.9	179.8	179.6	179.6
170°	171.8	172.9	174.2	174.8	175.2	175.9	175.5	175.5
172.5°	169.8	170.5	171.5	171.9	172.0	172.7	172.1	171.8
175°	166.8	167.2	167.9	167.9	167.9	168.2	167.9	167.6
177.5°	165.0	165.3	165.6	165.6	165.3	165.6	165.0	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6

(END OF REPORT)