

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331447-840

Luminaire Tested: **S122DIP-S1005D925U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331447-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D925U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8181.1 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38	35
4	76	66	58	52	71	62	55	50	53	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	38	41	37	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	30	26	24	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	2.3
10°-20°	557.5	6.8
20°-30°	809.1	9.9
30°-40°	853.9	10.4
40°-50°	756.0	9.2
50°-60°	603.3	7.4
60°-70°	410.1	5.0
70°-80°	210.2	2.6
80°-90°	53.8	0.7
90°-100°	42.5	0.5
100°-110°	155.9	1.9
110°-120°	416.8	5.1
120°-130°	688.0	8.4
130°-140°	731.7	8.9
140°-150°	680.1	8.3
150°-160°	546.8	6.7
160°-170°	352.3	4.3
170°-180°	121.3	1.5
0°-30°	1558.5	19.0
0°-40°	2412.3	29.5
0°-60°	3771.7	46.1
0°-90°	4445.8	54.3
90°-120°	615.2	7.5
90°-150°	2714.9	33.2
90°-180°	3735.0	45.7
0°-180°	8181.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	46
90°	25	1	25	1	25	13
95°	40	60	40	60	40	37
105°	70	280	70	280	70	73
115°	76	530	76	530	76	189
125°	789	750	789	750	789	682
135°	958	928	958	928	958	739
145°	1093	1076	1093	1076	1093	683
155°	1186	1185	1186	1185	1186	547
165°	1246	1249	1246	1249	1246	352
175°	1270	1277	1270	1277	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	21.1	21.0	21.5	20.8	20.7	21.2	21.0	20.2	20.6	21.0	21.3
90°	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5	19.5	18.5	16.8
92.5°	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4	21.9	21.4	20.6
95°	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0	37.0	36.0	34.5
97.5°	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8	49.0	48.2	44.8
100°	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8	54.2	52.6	49.1
102.5°	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3	56.1	54.0	83.2
105°	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8	58.5	56.2	112.2
107.5°	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1	76.4	78.8	145.8
110°	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4	140.9	161.4	220.7



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6	332.3	407.1	421.7
115°	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3	474.1	569.1	563.9
117.5°	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4	607.3	630.3	626.8
120°	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0	678.5	676.0	672.4
122.5°	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6	721.0	719.6	715.6
125°	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2	780.8	779.3	775.5
127.5°	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4	835.3	833.2	830.3
130°	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4	870.1	867.9	865.7
132.5°	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5	904.5	902.5	900.3
135°	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0	952.9	950.9	949.1
137.5°	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1	998.0	996.1	994.0
140°	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3	1027.4	1025.6	1023.4
142.5°	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2	1054.6	1052.9	1050.4
145°	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0	1092.5	1091.1	1087.6
147.5°	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8	1125.7	1124.7	1121.3
150°	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0	1145.8	1144.6	1141.3
152.5°	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5	1164.3	1163.1	1159.9
155°	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4	1189.1	1187.9	1185.5
157.5°	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3	1210.0	1208.6	1206.9
160°	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6	1222.3	1221.1	1219.9
162.5°	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0	1233.6	1232.2	1231.1
165°	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1	1245.5
167.5°	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5	1259.1	1257.7	1257.1
170°	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5	1265.0	1263.5	1263.1
172.5°	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8	1269.4	1268.0	1267.6
175°	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7	1274.2	1272.7	1272.3
177.5°	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2	1275.1	1273.8	1273.7
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	21.6	21.3	20.9	21.8	19.5	19.1	16.2	13.8	13.6	13.4	12.7
90°	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9	3.1	5.5	7.7
92.5°	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6	18.4	18.2	18.0
95°	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0	53.2	46.5	39.7
97.5°	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0	99.9	80.9	61.8
100°	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3	135.1	107.0	79.0
102.5°	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0	206.0	200.1	194.1
105°	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3	286.5	292.7	298.8
107.5°	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4	363.3	368.3	373.2
110°	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6	412.9	417.2	421.5



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8	459.6	463.4	467.3
115°	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3	533.8	537.2	540.8
117.5°	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9	600.8	604.7	608.6
120°	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6	648.6	651.8	654.8
122.5°	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9	690.1	693.4	696.6
125°	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8	752.5	755.2	757.8
127.5°	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8	809.8	812.7	815.7
130°	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0	846.3	849.5	852.8
132.5°	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9	882.6	885.4	888.3
135°	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9	931.1	934.4	937.7
137.5°	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3	978.7	981.0	983.2
140°	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0	1009.8	1011.4	1013.0
142.5°	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6	1036.1	1037.6	1039.1
145°	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3	1076.1	1075.9	1075.7
147.5°	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7	1111.9	1111.2	1110.3
150°	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3	1134.9	1133.4	1132.0
152.5°	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2	1154.6	1153.0	1151.4
155°	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2	1183.4	1181.4	1179.6
157.5°	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8	1206.3	1204.8	1203.2
160°	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1219.9	1218.7	1217.4
162.5°	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9	1231.7	1230.5	1229.2
165°	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8	1247.6	1246.4	1245.1
167.5°	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6	1259.4	1258.2	1256.9
170°	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3	1266.0	1264.8	1263.5
172.5°	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6	1270.4	1269.2	1268.0
175°	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4	1276.0	1274.6	1273.0
177.5°	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3	1277.2	1276.1	1274.9
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	12.5	12.3	12.0	12.3	12.0	11.7	11.3	11.5	11.7	10.7	10.8
90°	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5	21.5	22.5	23.2
92.5°	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4	23.0	23.5	23.9
95°	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0	39.1	40.1	40.5
97.5°	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8	50.6	51.4	51.9
100°	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8	57.5	59.2	60.2
102.5°	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3	60.5	62.6	63.9
105°	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8	63.0	65.2	66.9
107.5°	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1	71.9	69.6	68.9
110°	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4	99.9	79.4	69.6



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6	182.8	108.1	71.0
115°	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3	284.4	189.5	134.6
117.5°	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4	561.5	538.5	502.7
120°	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0	683.5	685.9	673.3
122.5°	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6	724.0	725.5	723.6
125°	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2	783.7	785.1	786.1
127.5°	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4	839.5	841.6	842.6
130°	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4	874.6	876.9	878.0
132.5°	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5	908.4	910.3	911.1
135°	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0	957.0	959.1	959.9
137.5°	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1	1002.1	1004.1	1004.8
140°	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3	1031.2	1033.0	1033.4
142.5°	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2	1057.9	1059.7	1060.0
145°	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0	1095.4	1096.8	1097.0
147.5°	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8	1127.8	1128.9	1129.0
150°	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0	1148.3	1149.5	1149.6
152.5°	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5	1166.7	1167.9	1167.9
155°	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4	1191.6	1192.9	1192.7
157.5°	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3	1212.7	1214.2	1214.1
160°	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6	1224.9	1226.1	1226.0
162.5°	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0	1236.4	1237.8	1237.6
165°	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7
167.5°	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5	1261.9	1263.4	1263.1
170°	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5	1267.9	1269.3	1269.1
172.5°	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8	1272.3	1273.7	1273.5
175°	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7	1277.1	1278.5	1278.2
177.5°	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2	1277.4	1278.5	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	10.9	10.4	10.5	9.9	10.5	10.4	10.9	10.8	10.7	11.7	11.5
90°	23.6	24.0	24.5	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5
92.5°	24.1	24.4	24.6	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4
95°	40.3	40.1	39.9	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0
97.5°	52.2	52.4	52.7	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8
100°	60.6	61.0	61.4	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8
102.5°	64.5	65.0	65.6	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3
105°	67.7	68.5	69.3	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8
107.5°	69.7	70.5	71.3	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1
110°	70.4	71.2	72.0	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	71.6	72.3	72.9	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6
115°	119.9	105.1	90.4	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3
117.5°	454.2	405.8	357.3	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4
120°	645.6	617.9	590.3	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0
122.5°	718.2	712.8	707.4	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6
125°	786.7	787.3	788.0	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2
127.5°	842.8	842.9	843.0	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4
130°	877.8	877.5	877.3	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4
132.5°	910.9	910.7	910.5	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5
135°	959.5	959.1	958.7	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0
137.5°	1004.1	1003.4	1002.7	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1
140°	1032.4	1031.4	1030.4	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3
142.5°	1058.9	1057.9	1056.9	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2
145°	1096.0	1095.0	1094.0	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0
147.5°	1128.1	1127.3	1126.4	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8
150°	1148.6	1147.5	1146.5	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0
152.5°	1166.5	1165.2	1163.9	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5
155°	1191.0	1189.3	1187.7	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4
157.5°	1212.4	1210.8	1209.2	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3
160°	1224.5	1223.0	1221.6	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6
162.5°	1235.9	1234.1	1232.3	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0
165°	1250.3	1248.9	1247.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9
167.5°	1261.3	1259.5	1257.7	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5
170°	1267.3	1265.4	1263.5	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5
172.5°	1271.6	1269.8	1268.0	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8
175°	1276.2	1274.1	1272.0	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7
177.5°	1276.9	1275.4	1273.8	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	11.3	11.7	12.0	12.3	12.0	12.3	12.5	12.7	13.4	13.6	13.8
90°	19.5	18.5	16.8	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9
92.5°	21.9	21.4	20.6	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6
95°	37.0	36.0	34.5	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0
97.5°	49.0	48.2	44.8	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0
100°	54.2	52.6	49.1	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3
102.5°	56.1	54.0	83.2	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0
105°	58.5	56.2	112.2	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3
107.5°	76.4	78.8	145.8	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4
110°	140.9	161.4	220.7	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	332.3	407.1	421.7	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8
115°	474.1	569.1	563.9	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3
117.5°	607.3	630.3	626.8	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9
120°	678.5	676.0	672.4	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6
122.5°	721.0	719.6	715.6	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9
125°	780.8	779.3	775.5	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8
127.5°	835.3	833.2	830.3	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8
130°	870.1	867.9	865.7	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0
132.5°	904.5	902.5	900.3	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9
135°	952.9	950.9	949.1	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9
137.5°	998.0	996.1	994.0	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3
140°	1027.4	1025.6	1023.4	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0
142.5°	1054.6	1052.9	1050.4	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6
145°	1092.5	1091.1	1087.6	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3
147.5°	1125.7	1124.7	1121.3	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7
150°	1145.8	1144.6	1141.3	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3
152.5°	1164.3	1163.1	1159.9	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2
155°	1189.1	1187.9	1185.5	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2
157.5°	1210.0	1208.6	1206.9	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8
160°	1222.3	1221.1	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1
162.5°	1233.6	1232.2	1231.1	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9
165°	1247.5	1246.1	1245.5	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8
167.5°	1259.1	1257.7	1257.1	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6
170°	1265.0	1263.5	1263.1	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3
172.5°	1269.4	1268.0	1267.6	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6
175°	1274.2	1272.7	1272.3	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4
177.5°	1275.1	1273.8	1273.7	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	16.2	19.1	19.5	21.8	20.9	21.3	21.6	21.3	21.0	20.6	20.2
90°	3.1	5.5	7.7	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5
92.5°	18.4	18.2	18.0	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4
95°	53.2	46.5	39.7	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0
97.5°	99.9	80.9	61.8	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8
100°	135.1	107.0	79.0	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8
102.5°	206.0	200.1	194.1	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3
105°	286.5	292.7	298.8	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8
107.5°	363.3	368.3	373.2	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1
110°	412.9	417.2	421.5	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.6	463.4	467.3	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6
115°	533.8	537.2	540.8	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3
117.5°	600.8	604.7	608.6	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4
120°	648.6	651.8	654.8	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0
122.5°	690.1	693.4	696.6	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6
125°	752.5	755.2	757.8	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2
127.5°	809.8	812.7	815.7	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4
130°	846.3	849.5	852.8	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4
132.5°	882.6	885.4	888.3	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5
135°	931.1	934.4	937.7	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0
137.5°	978.7	981.0	983.2	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1
140°	1009.8	1011.4	1013.0	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3
142.5°	1036.1	1037.6	1039.1	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2
145°	1076.1	1075.9	1075.7	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0
147.5°	1111.9	1111.2	1110.3	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8
150°	1134.9	1133.4	1132.0	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0
152.5°	1154.6	1153.0	1151.4	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5
155°	1183.4	1181.4	1179.6	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4
157.5°	1206.3	1204.8	1203.2	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3
160°	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6
162.5°	1231.7	1230.5	1229.2	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0
165°	1247.6	1246.4	1245.1	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9
167.5°	1259.4	1258.2	1256.9	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5
170°	1266.0	1264.8	1263.5	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5
172.5°	1270.4	1269.2	1268.0	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8
175°	1276.0	1274.6	1273.0	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7
177.5°	1277.2	1276.1	1274.9	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	21.0	21.2	20.7	20.8	21.5	21.0	21.1
90°	21.5	22.5	23.2	23.6	24.0	24.5	24.9
92.5°	23.0	23.5	23.9	24.1	24.4	24.6	24.9
95°	39.1	40.1	40.5	40.3	40.1	39.9	39.7
97.5°	50.6	51.4	51.9	52.2	52.4	52.7	52.9
100°	57.5	59.2	60.2	60.6	61.0	61.4	61.8
102.5°	60.5	62.6	63.9	64.5	65.0	65.6	66.2
105°	63.0	65.2	66.9	67.7	68.5	69.3	70.1
107.5°	71.9	69.6	68.9	69.7	70.5	71.3	72.1
110°	99.9	79.4	69.6	70.4	71.2	72.0	72.9



TEST NUMBER: P331447-840

CATALOG NUMBER: S122DIP-S1005D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	182.8	108.1	71.0	71.6	72.3	72.9	73.6
115°	284.4	189.5	134.6	119.9	105.1	90.4	75.6
117.5°	561.5	538.5	502.7	454.2	405.8	357.3	308.8
120°	683.5	685.9	673.3	645.6	617.9	590.3	562.6
122.5°	724.0	725.5	723.6	718.2	712.8	707.4	702.1
125°	783.7	785.1	786.1	786.7	787.3	788.0	788.6
127.5°	839.5	841.6	842.6	842.8	842.9	843.0	843.1
130°	874.6	876.9	878.0	877.8	877.5	877.3	877.1
132.5°	908.4	910.3	911.1	910.9	910.7	910.5	910.3
135°	957.0	959.1	959.9	959.5	959.1	958.7	958.3
137.5°	1002.1	1004.1	1004.8	1004.1	1003.4	1002.7	1002.0
140°	1031.2	1033.0	1033.4	1032.4	1031.4	1030.4	1029.3
142.5°	1057.9	1059.7	1060.0	1058.9	1057.9	1056.9	1055.8
145°	1095.4	1096.8	1097.0	1096.0	1095.0	1094.0	1093.0
147.5°	1127.8	1128.9	1129.0	1128.1	1127.3	1126.4	1125.6
150°	1148.3	1149.5	1149.6	1148.6	1147.5	1146.5	1145.5
152.5°	1166.7	1167.9	1167.9	1166.5	1165.2	1163.9	1162.5
155°	1191.6	1192.9	1192.7	1191.0	1189.3	1187.7	1186.1
157.5°	1212.7	1214.2	1214.1	1212.4	1210.8	1209.2	1207.7
160°	1224.9	1226.1	1226.0	1224.5	1223.0	1221.6	1220.2
162.5°	1236.4	1237.8	1237.6	1235.9	1234.1	1232.3	1230.5
165°	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1
167.5°	1261.9	1263.4	1263.1	1261.3	1259.5	1257.7	1255.8
170°	1267.9	1269.3	1269.1	1267.3	1265.4	1263.5	1261.7
172.5°	1272.3	1273.7	1273.5	1271.6	1269.8	1268.0	1266.2
175°	1277.1	1278.5	1278.2	1276.2	1274.1	1272.0	1270.0
177.5°	1277.4	1278.5	1278.3	1276.9	1275.4	1273.8	1272.4
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7

(END OF REPORT)