

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332071-830

Luminaire Tested: **S123DIP-S1165D805U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332071-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7225.2 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332071-830

CATALOG NUMBER: S123DIP-S1165D805U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332071-830

CATALOG NUMBER: S123DIP-S1165D805U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20		
RC	80					70					50					30					10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																							
0	110	110	110	110		103	103	103	103		90	90	90		78	78	78		67	67	67	62	
1	100	96	92	88		94	90	87	83		79	76	74		69	67	65		59	58	57	52	
2	91	84	77	72		85	79	73	68		69	65	61		60	57	54		52	50	48	44	
3	83	74	66	60		78	69	63	57		61	56	51		53	49	46		46	43	41	37	
4	76	65	57	51		71	61	54	49		54	48	44		48	43	39		41	38	35	32	
5	70	58	50	44		65	55	47	42		49	42	38		43	38	34		37	33	30	27	
6	65	52	44	38		60	49	42	36		44	38	33		39	34	30		34	30	27	24	
7	60	47	39	33		56	45	37	32		40	34	29		35	30	26		31	27	24	21	
8	56	43	35	30		52	41	33	28		36	30	26		32	27	24		28	24	21	19	
9	52	39	32	26		48	37	30	25		33	27	23		30	25	21		26	22	19	17	
10	48	36	29	24		45	34	27	23		31	25	21		27	23	19		24	20	18	16	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332071-830

CATALOG NUMBER: S123DIP-S1165D805U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.2
10°-20°	458.3	6.3
20°-30°	677.0	9.4
30°-40°	790.8	10.9
40°-50°	795.1	11.0
50°-60°	698.4	9.7
60°-70°	520.3	7.2
70°-80°	296.4	4.1
80°-90°	87.9	1.2
90°-100°	202.6	2.8
100°-110°	573.6	7.9
110°-120°	564.3	7.8
120°-130°	450.1	6.2
130°-140°	354.9	4.9
140°-150°	264.9	3.7
150°-160°	184.6	2.6
160°-170°	108.5	1.5
170°-180°	35.3	0.5
0°-30°	1297.6	18.0
0°-40°	2088.4	28.9
0°-60°	3581.8	49.6
0°-90°	4486.4	62.1
90°-120°	1340.5	18.6
90°-150°	2410.4	33.4
90°-180°	2739.0	37.9
0°-180°	7225.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	2	9	18	21	21	6
95°	25	81	437	127	86	27
105°	86	126	592	1036	937	91
115°	151	188	453	994	1140	150
125°	210	248	423	766	899	186
135°	246	294	417	631	729	190
145°	281	322	412	518	570	176
155°	319	344	399	453	472	147
165°	349	358	382	405	412	98
175°	363	364	366	371	371	34
180°	364	364	364	364	364	



TEST NUMBER: P332071-830

CATALOG NUMBER: S123DIP-S1165D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	31.1	30.6	30.2	29.8	29.3	29.0	29.2	29.4	29.6	29.8	29.3
90°	1.5	2.9	4.4	6.6	8.1	9.6	11.8	14.0	16.2	18.4	17.7
92.5°	9.1	13.6	19.8	25.5	31.7	42.6	61.9	93.6	124.7	113.3	85.5
95°	25.1	27.2	35.3	47.9	67.0	95.8	158.4	268.2	389.1	437.0	354.5
97.5°	42.7	43.5	49.9	60.7	79.6	110.7	170.5	294.4	495.8	677.2	724.5
100°	54.6	55.2	60.4	70.8	88.4	117.2	168.7	277.8	471.6	697.9	843.0
102.5°	66.9	68.2	72.8	82.6	98.5	124.8	171.1	263.6	436.2	659.5	848.9
105°	85.5	87.7	92.1	100.9	115.0	137.8	177.6	253.4	392.8	592.5	804.0
107.5°	105.2	107.4	111.7	120.4	133.6	154.8	189.6	252.8	365.0	533.2	725.3
110°	119.4	121.6	125.3	133.4	145.9	166.5	199.7	255.7	354.5	499.6	675.7



TEST NUMBER: P332071-830

CATALOG NUMBER: S123DIP-S1165D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.3	134.6	138.3	146.4	158.9	178.9	209.7	261.6	348.6	477.2	632.7
115°	151.1	154.0	158.4	165.8	178.3	198.2	226.2	271.2	346.4	453.2	580.7
117.5°	169.8	173.1	176.8	183.6	197.7	216.0	243.7	283.9	347.7	439.0	549.3
120°	182.8	184.9	188.6	196.0	210.0	228.5	255.0	293.3	350.1	432.5	532.8
122.5°	194.0	196.1	199.8	207.8	221.2	240.8	266.7	302.1	354.1	428.5	519.2
125°	210.0	211.5	215.9	224.0	238.0	257.9	283.7	316.1	360.3	423.0	501.8
127.5°	222.3	224.4	229.9	238.2	253.6	273.5	298.4	327.6	367.4	420.4	486.5
130°	229.9	232.1	238.7	247.6	263.1	283.0	307.3	335.3	372.1	418.6	478.2
132.5°	235.8	238.7	245.8	256.5	271.9	291.2	314.9	342.3	375.7	417.9	470.6
135°	246.1	249.1	257.2	268.2	283.7	303.6	326.4	351.5	381.0	417.1	460.5
137.5°	255.8	258.9	266.9	278.7	294.0	312.5	334.4	358.3	384.6	415.5	451.9
140°	262.3	266.0	273.4	285.2	299.9	318.3	339.7	361.8	386.9	414.9	446.6
142.5°	269.4	272.5	280.5	291.1	305.9	323.0	343.8	365.3	388.6	413.7	441.9
145°	280.8	283.0	289.6	300.7	313.2	330.2	349.3	369.2	389.8	411.9	435.5
147.5°	292.3	293.6	300.1	309.6	321.7	336.2	353.7	371.6	389.8	409.2	429.3
150°	299.9	300.7	306.5	316.1	326.4	339.7	356.7	372.1	389.8	406.8	425.2
152.5°	307.6	307.7	313.6	322.1	331.1	343.8	358.4	373.3	388.0	403.8	420.5
155°	319.1	319.1	323.5	330.8	338.9	349.3	361.8	373.6	386.2	398.7	413.4
157.5°	328.2	328.8	332.3	338.8	345.7	353.7	363.7	374.4	383.6	394.1	405.5
160°	335.3	335.3	338.3	344.1	349.3	356.7	365.5	374.4	382.5	390.6	400.1
162.5°	340.6	340.6	343.0	347.7	352.2	358.4	366.1	373.7	380.1	387.0	394.8
165°	348.6	347.8	349.3	353.0	355.9	361.1	366.9	372.1	376.5	381.7	387.6
167.5°	354.6	353.7	354.5	357.2	359.3	362.6	366.8	371.0	373.1	376.5	380.7
170°	358.2	356.7	357.4	359.6	361.1	362.6	366.3	369.2	370.7	372.9	376.5
172.5°	360.5	359.6	359.8	361.4	362.2	363.2	366.3	368.6	368.9	369.9	372.4
175°	363.3	362.6	361.8	363.3	363.3	364.0	365.5	366.9	366.3	366.3	367.7
177.5°	364.6	364.0	363.4	364.0	364.0	364.0	364.6	365.8	364.6	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332071-830

CATALOG NUMBER: S123DIP-S1165D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	29.2	29.1	29.0	29.1	29.0	29.1	29.3	29.1
90°	18.4	19.1	19.9	21.4	20.6	21.4	22.1	21.4
92.5°	62.0	49.2	43.5	39.7	38.4	36.1	36.9	35.5
95°	265.3	179.8	140.7	114.2	100.2	93.6	88.4	85.5
97.5°	661.3	529.7	434.6	346.5	292.1	258.9	239.0	232.7
100°	868.8	809.1	722.9	618.2	543.8	490.0	461.3	462.0
102.5°	937.7	935.9	885.6	819.3	761.4	718.8	694.7	677.8
105°	958.0	1031.6	1045.7	1026.5	992.6	964.6	941.0	937.4
107.5°	899.9	1019.5	1084.1	1110.3	1111.0	1101.5	1093.5	1086.8
110°	844.5	980.1	1072.9	1124.5	1145.1	1151.0	1149.5	1148.1



TEST NUMBER: P332071-830

CATALOG NUMBER: S123DIP-S1165D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	789.7	928.2	1032.3	1098.5	1136.3	1154.6	1160.2	1160.5
115°	717.0	845.2	953.6	1033.9	1089.1	1121.5	1136.3	1140.0
117.5°	664.4	775.1	872.3	953.9	1011.4	1048.6	1069.8	1074.9
120°	636.7	736.1	824.6	899.0	957.2	998.5	1016.2	1020.6
122.5°	614.9	704.9	786.8	856.0	907.7	944.8	964.3	969.9
125°	585.8	666.2	736.9	795.9	843.0	875.4	893.8	899.0
127.5°	560.5	632.1	696.0	749.6	791.5	819.3	835.9	840.7
130°	544.6	610.9	670.6	720.7	759.8	786.3	801.7	807.7
132.5°	529.8	590.9	646.4	694.2	730.8	757.4	771.1	775.2
135°	509.9	562.2	610.1	652.1	688.2	710.4	723.6	728.8
137.5°	491.8	534.7	576.0	612.4	642.7	665.2	676.4	679.8
140°	481.2	518.8	554.1	585.8	613.9	634.4	646.3	645.5
142.5°	471.2	503.4	534.1	561.7	585.5	603.8	614.4	613.7
145°	459.1	483.4	507.0	528.4	546.8	562.2	568.2	569.6
147.5°	449.2	468.5	487.6	502.8	516.7	527.2	532.8	533.4
150°	442.1	459.1	474.6	488.5	499.6	507.7	512.2	512.2
152.5°	435.6	450.3	463.9	475.6	484.3	491.8	494.5	494.5
155°	425.9	437.7	448.7	457.6	464.2	470.1	471.6	472.3
157.5°	415.6	425.5	434.0	440.9	446.7	451.1	452.3	452.1
160°	409.7	417.8	425.2	430.4	435.5	439.9	439.9	439.2
162.5°	402.7	409.5	416.3	420.9	424.3	428.1	428.1	427.4
165°	393.5	397.9	403.1	406.8	409.7	412.6	411.9	411.9
167.5°	385.5	388.9	391.9	394.5	395.9	397.9	397.2	397.2
170°	380.2	382.5	385.4	386.9	387.6	389.1	388.3	388.3
172.5°	375.5	377.1	379.5	380.4	380.5	382.0	380.7	380.1
175°	369.2	369.9	371.4	371.4	371.4	372.1	371.4	370.7
177.5°	365.2	365.8	366.4	366.4	365.8	366.4	365.2	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0

(END OF REPORT)