

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331865-830

Luminaire Tested: **S123DIP-S340D365U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331865-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D365U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2736.2 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50																												
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43																												
2	89	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41	36																												
3	82	72	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31																												
4	75	64	56	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27																												
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23																												
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21																												
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18																												
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16																												
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15																												
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4878	4878	4878	4878
5°	5817	4900	4341	4900
10°	7282	4875	3922	4875
15°	8931	4835	3651	4835
20°	10639	4774	3477	4774
25°	11297	4700	3437	4700
30°	9684	4645	3455	4645
35°	6734	4568	3491	4568
40°	5073	4477	3481	4477
45°	4211	4341	3436	4341
50°	3773	4068	3404	4068
55°	3526	3772	3363	3772
60°	3309	3460	3328	3460
65°	3110	3156	3222	3156
70°	2917	2807	3068	2807
75°	2612	2458	2816	2458
80°	2287	2015	2424	2015
85°	1791	1470	1630	1470



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	1.6
10°-20°	143.2	5.2
20°-30°	240.3	8.8
30°-40°	272.0	9.9
40°-50°	244.0	8.9
50°-60°	196.9	7.2
60°-70°	137.2	5.0
70°-80°	72.1	2.6
80°-90°	18.9	0.7
90°-100°	16.3	0.6
100°-110°	77.7	2.8
110°-120°	186.6	6.8
120°-130°	237.6	8.7
130°-140°	253.9	9.3
140°-150°	237.4	8.7
150°-160°	191.5	7.0
160°-170°	123.6	4.5
170°-180°	42.6	1.6
0°-30°	428.1	15.6
0°-40°	700.1	25.6
0°-60°	1140.9	41.7
0°-90°	1369.1	50.0
90°-120°	280.6	10.3
90°-150°	1009.4	36.9
90°-180°	1367.0	50.0
0°-180°	2736.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	538	454	402	454	538	56
15°	801	434	328	434	801	231
25°	951	396	289	396	951	417
35°	512	348	266	348	512	333
45°	277	285	226	285	277	219
55°	188	201	179	201	188	169
65°	122	124	126	124	122	122
75°	63	59	68	59	63	67
85°	14	12	13	12	14	17
90°	10	0	10	0	10	5
95°	13	20	13	20	13	11
105°	15	99	15	99	15	33
115°	196	186	196	186	196	181
125°	268	262	268	262	268	239
135°	330	327	330	327	330	255
145°	381	377	381	377	381	238
155°	415	415	415	415	415	191
165°	437	438	437	438	437	123
175°	447	448	447	448	447	43
180°	448	448	448	448	448	



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	481.0	480.6	479.8	480.4	479.0	477.1	476.9	475.1	470.0	469.8	468.3
5°	538.4	536.7	536.4	536.2	533.1	529.0	521.0	520.4	509.8	504.6	498.2
7.5°	612.8	613.7	610.5	607.8	598.3	592.1	583.6	572.8	559.9	546.7	538.0
10°	666.2	673.4	664.5	658.3	652.6	641.9	629.3	613.7	598.1	579.9	566.1
12.5°	723.5	727.0	725.2	719.4	710.6	694.2	672.0	654.8	640.5	610.1	597.9
15°	801.4	814.8	806.3	786.6	786.9	771.4	742.4	710.6	693.6	667.0	630.8
17.5°	884.6	886.2	882.6	866.1	855.2	833.7	806.9	776.5	742.2	710.0	671.6
20°	928.8	927.5	919.8	911.3	892.4	875.7	846.5	812.5	768.5	736.9	694.9
22.5°	953.4	951.2	947.5	940.4	924.7	906.8	880.5	843.4	801.5	758.0	709.5
25°	951.2	954.0	954.5	952.5	947.1	936.3	915.7	886.0	844.3	788.2	737.8
27.5°	865.2	869.2	880.9	891.4	903.0	914.8	913.2	898.5	867.6	819.3	757.5
30°	779.1	770.2	792.0	819.4	838.1	871.1	889.5	890.6	873.3	831.8	771.6
32.5°	659.6	669.3	678.9	712.7	753.5	790.4	827.2	856.7	860.1	832.5	779.9
35°	512.5	524.6	542.2	559.7	603.6	641.4	706.0	762.1	806.9	812.8	780.6
37.5°	413.0	419.0	430.1	447.7	476.4	521.2	571.1	642.2	707.1	755.4	757.4
40°	361.0	362.8	375.2	388.6	411.9	448.8	493.8	556.7	634.3	701.8	729.9
42.5°	322.0	325.8	331.2	344.0	362.6	390.3	432.2	484.1	555.3	632.9	687.9
45°	276.6	281.1	284.4	292.9	306.1	324.8	353.9	401.4	455.6	535.7	609.7
47.5°	246.8	247.0	249.5	256.0	264.9	279.0	299.6	330.1	379.8	444.9	520.8
50°	225.3	228.8	229.7	234.7	241.8	252.0	269.2	295.1	335.9	393.0	462.9
52.5°	210.2	211.2	213.7	217.4	223.5	231.5	246.4	266.6	298.7	347.4	411.6
55°	187.9	187.9	190.4	193.2	196.7	204.0	213.9	228.8	253.2	291.0	344.1
57.5°	167.4	168.5	170.2	171.1	174.1	178.9	187.1	198.5	216.6	245.7	287.9
60°	153.7	155.7	155.4	157.2	159.9	163.6	170.6	179.8	196.0	219.3	255.0
62.5°	141.8	141.7	141.6	143.7	146.3	149.9	154.5	162.4	176.3	196.9	227.2
65°	122.1	121.7	123.2	124.5	125.4	128.0	131.5	138.6	147.8	163.2	186.6
67.5°	104.6	103.3	104.2	104.6	106.1	108.2	111.5	115.8	123.1	135.4	153.2
70°	92.7	91.5	91.3	91.8	93.1	94.6	97.1	101.2	108.0	117.9	130.8
72.5°	80.4	79.6	79.6	80.6	81.2	82.2	83.9	87.7	93.1	100.6	112.6
75°	62.8	62.8	62.8	63.1	63.7	64.6	65.9	67.9	72.0	77.3	85.4
77.5°	47.0	47.0	46.8	46.8	47.7	48.1	48.4	50.2	52.6	56.1	62.0
80°	36.9	35.8	36.2	36.9	37.3	37.5	38.2	38.6	40.6	42.6	46.8
82.5°	27.4	26.5	26.6	27.6	27.7	27.9	28.6	29.1	29.9	31.7	33.9
85°	14.5	14.5	14.7	14.7	14.9	14.7	15.4	15.6	15.6	16.7	18.0
87.5°	7.3	6.9	7.1	7.2	7.0	7.1	7.3	7.4	7.4	7.5	7.5
90°	10.0	9.8	9.7	9.5	9.4	9.1	8.9	8.6	8.3	8.0	7.1
92.5°	11.0	10.9	10.8	10.7	10.7	10.5	10.0	9.5	9.0	8.5	7.8
95°	12.6	12.6	12.6	12.6	12.6	12.4	11.9	11.4	10.8	10.4	9.5
97.5°	13.8	13.7	13.6	13.5	13.4	13.1	12.5	11.9	11.3	10.7	16.0
100°	13.9	13.9	13.9	13.8	13.7	13.4	12.7	12.2	11.6	11.0	22.5
102.5°	14.2	14.1	13.9	13.9	13.8	14.6	16.4	18.3	20.1	22.0	34.5
105°	14.6	14.5	14.3	14.2	14.0	20.5	33.6	46.8	59.9	73.0	79.6
107.5°	46.0	55.9	65.8	75.7	85.5	95.3	104.9	114.5	124.0	133.7	132.6
110°	91.6	102.2	112.7	123.4	133.9	140.4	142.9	145.3	147.8	150.2	149.4



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.1	159.4	161.6	163.8	166.1	167.2	167.1	167.1	167.0	167.0	166.2
115°	195.9	195.6	195.3	194.9	194.6	194.2	193.4	192.7	191.9	191.1	190.5
117.5°	217.5	217.5	217.4	217.4	217.4	217.0	216.4	215.8	215.2	214.6	214.3
120°	232.5	232.5	232.5	232.5	232.5	232.1	231.6	231.0	230.5	229.8	229.6
122.5°	247.1	247.0	247.0	246.9	246.9	246.7	246.3	245.8	245.4	245.0	244.7
125°	267.8	267.7	267.5	267.3	267.2	267.0	266.9	266.7	266.6	266.5	266.2
127.5°	287.7	287.8	287.9	288.0	288.2	288.2	287.9	287.7	287.5	287.2	286.9
130°	300.4	300.6	300.8	300.9	301.0	301.0	300.7	300.4	300.0	299.7	299.4
132.5°	312.2	312.4	312.5	312.7	313.0	312.9	312.6	312.4	312.1	311.8	311.5
135°	330.1	330.3	330.5	330.7	330.9	330.9	330.7	330.5	330.3	330.1	329.8
137.5°	346.9	347.0	347.2	347.3	347.5	347.4	347.0	346.7	346.4	346.0	345.8
140°	357.0	357.2	357.3	357.5	357.6	357.6	357.2	356.9	356.7	356.4	356.2
142.5°	366.4	366.6	366.7	367.0	367.2	367.2	366.9	366.7	366.5	366.3	366.0
145°	380.7	380.7	380.7	380.7	380.7	380.6	380.5	380.3	380.2	380.0	379.8
147.5°	391.3	391.7	392.0	392.4	392.8	392.9	392.7	392.5	392.4	392.2	392.1
150°	399.4	399.5	399.8	400.0	400.2	400.3	400.1	400.0	399.8	399.6	399.5
152.5°	405.8	406.0	406.4	406.8	407.1	407.2	406.9	406.6	406.3	406.0	406.0
155°	414.6	415.1	415.6	416.0	416.4	416.5	416.1	415.8	415.4	415.0	414.9
157.5°	422.2	422.7	423.4	424.0	424.5	424.6	424.1	423.7	423.2	422.8	422.8
160°	427.0	427.5	428.0	428.6	429.0	429.1	428.7	428.2	427.7	427.3	427.4
162.5°	431.5	432.0	432.4	432.9	433.4	433.3	432.8	432.3	431.8	431.3	431.4
165°	437.0	437.5	438.0	438.6	439.0	439.0	438.5	437.8	437.2	436.7	436.7
167.5°	440.9	441.5	442.1	442.7	443.3	443.3	442.7	442.1	441.5	440.9	440.9
170°	443.3	443.9	444.5	445.1	445.6	445.6	445.1	444.5	443.9	443.3	443.3
172.5°	444.6	445.3	445.9	446.6	447.2	447.2	446.7	446.1	445.5	444.9	444.9
175°	446.7	447.2	447.8	448.5	449.0	449.0	448.6	448.0	447.5	447.0	446.9
177.5°	447.2	447.8	448.5	449.0	449.6	449.7	449.2	448.7	448.3	447.8	447.7
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	467.2	465.9	464.5	462.0	459.9	456.9	456.0	455.0	451.8	449.0	446.9
5°	495.8	490.5	482.9	475.8	470.1	462.4	458.1	453.5	446.9	440.9	436.1
7.5°	525.7	515.3	503.3	490.5	478.4	466.8	457.5	449.1	439.9	431.2	424.3
10°	549.4	534.4	517.7	499.7	484.4	469.5	456.9	446.0	434.1	423.8	415.2
12.5°	576.5	554.3	531.3	509.4	491.3	470.5	455.3	441.4	427.9	415.6	406.0
15°	608.4	580.3	553.1	523.0	495.4	469.5	451.5	433.9	418.3	405.6	393.2
17.5°	637.6	605.8	569.9	533.3	499.9	469.2	444.0	424.1	404.6	389.1	376.8
20°	654.1	617.9	577.3	539.3	502.4	468.2	440.5	416.8	395.7	379.2	365.4
22.5°	668.4	625.9	583.9	543.3	502.2	465.3	433.9	409.5	386.7	370.6	355.9
25°	683.2	632.4	590.2	542.6	496.7	458.5	423.4	395.7	372.9	353.9	338.8
27.5°	695.8	632.0	581.9	530.7	488.0	449.7	412.2	382.5	358.3	337.7	322.3
30°	704.2	632.8	573.3	522.6	479.6	440.1	403.6	373.7	348.3	327.4	312.9
32.5°	709.5	632.3	565.4	511.3	466.2	431.2	394.3	363.4	337.1	316.7	302.7
35°	712.6	628.4	551.8	488.1	444.7	410.6	379.7	347.6	320.2	301.0	285.2
37.5°	706.3	620.3	536.0	465.7	418.1	384.7	358.5	331.3	305.0	284.0	270.3
40°	696.7	615.0	523.7	449.9	399.8	367.6	345.4	318.6	292.7	272.7	260.0
42.5°	678.3	604.4	510.2	432.3	380.9	348.6	328.2	305.8	281.3	262.5	249.8
45°	633.3	581.0	489.8	406.0	352.9	319.5	301.5	285.2	263.1	244.9	233.8
47.5°	570.8	545.9	460.5	378.2	323.6	291.5	272.8	259.8	243.6	228.8	218.3
50°	527.4	517.1	440.7	359.2	304.2	272.7	254.7	242.9	231.2	216.5	206.9
52.5°	477.4	483.7	417.5	339.6	284.3	253.4	236.5	227.1	216.5	204.3	196.0
55°	406.9	429.9	377.5	306.5	254.7	225.3	209.2	201.0	194.7	185.8	178.5
57.5°	340.9	370.2	334.1	272.5	225.6	200.3	184.9	175.9	171.9	167.2	161.5
60°	301.7	330.6	303.2	249.7	206.2	182.0	168.4	160.7	156.7	153.4	148.6
62.5°	266.7	296.1	273.1	226.5	187.0	164.7	152.8	145.2	142.2	140.5	136.4
65°	218.7	243.9	228.6	190.4	159.7	139.9	129.1	123.9	121.0	120.4	117.7
67.5°	178.0	197.2	186.1	157.9	133.7	116.7	107.5	103.0	100.9	100.6	98.6
70°	151.3	169.3	160.7	135.3	114.4	101.0	93.1	89.2	87.8	87.7	86.5
72.5°	130.5	143.1	136.3	115.1	99.0	86.8	81.0	76.8	75.4	75.7	74.9
75°	96.6	106.0	102.1	87.4	74.5	66.5	61.7	59.1	57.8	58.4	57.5
77.5°	69.6	75.5	71.9	61.7	53.7	48.1	44.5	42.9	41.7	41.7	41.3
80°	52.5	56.0	54.0	47.9	41.3	36.5	33.6	32.5	31.9	31.6	31.4
82.5°	37.4	40.3	38.0	33.8	29.3	26.4	24.8	23.4	22.9	23.0	22.8
85°	18.9	20.0	19.1	16.5	14.7	13.4	12.5	11.9	11.4	11.6	11.2
87.5°	7.7	7.7	7.0	6.1	5.6	4.9	4.8	4.2	4.1	4.2	4.2
90°	6.0	5.1	4.1	3.3	2.5	1.8	1.0	0.4	1.0	1.8	2.5
92.5°	7.1	6.3	5.7	5.4	5.6	5.7	6.0	6.2	6.0	5.7	5.6
95°	8.7	7.9	7.1	8.2	11.2	14.2	17.2	20.4	17.2	14.2	11.2
97.5°	21.4	26.7	32.0	35.3	36.8	38.1	39.5	40.8	39.5	38.1	36.8
100°	34.1	45.6	57.2	62.2	60.7	59.3	57.8	56.3	57.8	59.3	60.7
102.5°	47.1	59.8	72.4	78.1	77.1	76.0	74.9	73.9	74.9	76.0	77.1
105°	86.2	92.9	99.6	102.5	101.7	100.9	100.1	99.2	100.1	100.9	101.7
107.5°	131.6	130.5	129.5	128.7	128.0	127.3	126.7	126.0	126.7	127.3	128.0
110°	148.5	147.8	146.9	146.3	145.6	145.1	144.5	143.9	144.5	145.1	145.6



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	165.4	164.6	163.7	163.1	162.5	162.0	161.5	160.9	161.5	162.0	162.5
115°	189.8	189.2	188.5	187.9	187.5	187.1	186.6	186.2	186.6	187.1	187.5
117.5°	214.0	213.6	213.3	212.8	212.3	211.7	211.2	210.7	211.2	211.7	212.3
120°	229.4	229.1	228.9	228.5	227.8	227.2	226.5	225.8	226.5	227.2	227.8
122.5°	244.4	244.1	243.8	243.5	242.9	242.3	241.9	241.3	241.9	242.3	242.9
125°	265.9	265.6	265.2	264.9	264.2	263.6	263.1	262.5	263.1	263.6	264.2
127.5°	286.5	286.2	285.8	285.3	284.7	284.2	283.6	283.0	283.6	284.2	284.7
130°	299.2	298.9	298.6	298.1	297.6	296.9	296.3	295.8	296.3	296.9	297.6
132.5°	311.3	311.0	310.8	310.4	309.8	309.2	308.6	308.0	308.6	309.2	309.8
135°	329.5	329.1	328.9	328.5	328.1	327.6	327.2	326.8	327.2	327.6	328.1
137.5°	345.6	345.5	345.3	345.0	344.4	343.8	343.3	342.7	343.3	343.8	344.4
140°	355.9	355.7	355.5	355.2	354.7	354.3	353.8	353.4	353.8	354.3	354.7
142.5°	365.8	365.6	365.3	365.0	364.6	364.1	363.7	363.3	363.7	364.1	364.6
145°	379.8	379.6	379.5	379.1	378.6	378.1	377.6	377.0	377.6	378.1	378.6
147.5°	391.9	391.8	391.6	391.3	391.1	390.7	390.4	390.0	390.4	390.7	391.1
150°	399.4	399.3	399.1	398.9	398.7	398.4	398.2	398.0	398.2	398.4	398.7
152.5°	405.9	405.8	405.8	405.6	405.5	405.4	405.3	405.2	405.3	405.4	405.5
155°	414.8	414.8	414.7	414.7	414.9	415.0	415.2	415.4	415.2	415.0	414.9
157.5°	422.9	423.0	423.1	423.1	423.1	423.2	423.2	423.2	423.2	423.2	423.1
160°	427.4	427.5	427.6	427.7	427.7	427.8	427.9	428.0	427.9	427.8	427.7
162.5°	431.5	431.5	431.6	431.8	432.0	432.2	432.3	432.5	432.3	432.2	432.0
165°	436.8	436.9	437.0	437.1	437.3	437.5	437.7	438.0	437.7	437.5	437.3
167.5°	440.9	440.9	440.9	441.0	441.4	441.7	442.0	442.2	442.0	441.7	441.4
170°	443.3	443.3	443.3	443.5	443.7	444.0	444.3	444.6	444.3	444.0	443.7
172.5°	444.8	444.7	444.7	444.8	445.2	445.5	445.9	446.2	445.9	445.5	445.2
175°	446.9	446.8	446.7	446.9	447.2	447.5	447.9	448.3	447.9	447.5	447.2
177.5°	447.6	447.6	447.5	447.6	448.0	448.3	448.6	448.8	448.6	448.3	448.0
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	445.6	444.4	442.7	440.1	437.9	434.6	434.6	435.1	435.1	435.0	434.6
5°	432.2	428.9	424.9	420.3	415.5	410.6	409.7	407.9	406.7	405.8	404.7
7.5°	417.8	412.0	406.2	399.8	393.9	389.1	385.7	382.9	381.1	379.1	377.7
10°	408.2	401.0	394.2	387.4	379.8	373.9	370.2	367.6	365.6	363.8	363.0
12.5°	396.8	388.5	381.0	374.5	366.4	360.2	356.7	355.4	353.2	349.4	347.5
15°	380.1	372.4	363.4	353.5	349.6	342.1	337.9	335.9	334.6	331.8	330.9
17.5°	365.8	355.8	345.6	338.3	330.9	324.9	322.5	320.1	318.4	316.0	315.3
20°	354.4	345.4	336.2	328.3	320.6	314.0	312.0	310.3	308.5	307.5	306.5
22.5°	342.8	333.8	326.1	318.8	310.6	306.2	304.2	302.2	301.0	300.2	299.4
25°	326.5	318.6	310.0	303.5	296.9	294.0	292.7	291.6	290.7	289.6	289.4
27.5°	312.0	303.3	296.4	290.2	285.5	283.1	281.8	281.3	281.5	281.9	282.2
30°	301.0	293.1	287.5	282.2	277.8	275.6	275.3	275.3	276.3	276.4	276.9
32.5°	291.1	284.6	278.8	273.7	270.4	268.9	269.8	269.8	270.4	271.0	271.8
35°	276.4	270.7	266.4	261.9	259.1	259.8	260.2	260.6	261.7	263.1	263.9
37.5°	262.5	257.6	253.0	249.6	248.3	249.4	250.5	251.4	252.7	253.7	254.6
40°	252.5	248.7	244.4	241.3	241.8	242.4	243.3	244.4	245.5	246.2	247.0
42.5°	243.2	239.3	235.9	233.4	234.0	234.9	235.4	235.9	237.2	238.5	238.9
45°	229.0	225.9	222.9	221.3	221.8	222.3	222.6	223.3	224.4	225.3	225.6
47.5°	213.1	210.9	208.9	207.4	208.1	207.9	208.5	209.9	210.2	210.8	212.0
50°	202.9	201.0	198.5	198.0	198.0	198.0	198.3	200.0	200.0	201.0	201.8
52.5°	191.6	190.4	188.9	188.0	187.7	187.7	188.6	189.5	189.8	191.1	192.0
55°	175.0	173.7	172.4	171.7	171.3	171.7	173.4	173.9	175.0	175.7	176.3
57.5°	157.7	156.7	155.6	155.2	155.1	155.7	156.7	158.0	158.3	160.3	161.3
60°	146.3	144.7	143.8	143.8	143.4	145.3	145.0	147.1	147.6	148.9	150.4
62.5°	134.5	132.4	132.1	132.1	132.7	133.3	133.8	134.8	136.0	137.6	138.8
65°	115.5	114.4	115.9	115.7	115.3	116.6	116.6	117.7	119.0	120.6	123.0
67.5°	97.6	97.0	97.1	97.1	97.7	98.5	99.2	100.1	101.7	103.3	104.9
70°	85.4	86.1	85.0	85.9	86.5	86.7	87.2	88.5	90.2	91.3	93.1
72.5°	73.6	73.6	73.7	74.1	74.7	75.1	75.6	77.1	79.0	79.9	81.3
75°	56.6	56.5	57.1	57.1	58.2	58.6	59.1	59.8	61.5	62.8	63.9
77.5°	41.4	41.7	41.5	42.2	41.9	42.0	43.4	44.0	44.2	46.8	47.4
80°	31.2	31.6	31.9	32.0	32.2	31.9	33.4	34.0	34.0	35.5	36.7
82.5°	22.4	22.6	23.2	23.5	23.5	23.9	24.0	24.5	25.1	25.7	27.1
85°	11.2	11.9	12.1	11.9	12.1	11.6	12.3	12.5	12.7	12.7	12.7
87.5°	4.1	4.5	4.5	4.9	4.9	5.3	5.4	5.1	5.1	5.7	5.0
90°	3.3	4.1	5.1	6.0	7.1	8.0	8.3	8.6	8.9	9.1	9.4
92.5°	5.4	5.7	6.3	7.1	7.8	8.5	9.0	9.5	10.0	10.5	10.7
95°	8.2	7.1	7.9	8.7	9.5	10.4	10.8	11.4	11.9	12.4	12.6
97.5°	35.3	32.0	26.7	21.4	16.0	10.7	11.3	11.9	12.5	13.1	13.4
100°	62.2	57.2	45.6	34.1	22.5	11.0	11.6	12.2	12.7	13.4	13.7
102.5°	78.1	72.4	59.8	47.1	34.5	22.0	20.1	18.3	16.4	14.6	13.8
105°	102.5	99.6	92.9	86.2	79.6	73.0	59.9	46.8	33.6	20.5	14.0
107.5°	128.7	129.5	130.5	131.6	132.6	133.7	124.0	114.5	104.9	95.3	85.5
110°	146.3	146.9	147.8	148.5	149.4	150.2	147.8	145.3	142.9	140.4	133.9



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	163.1	163.7	164.6	165.4	166.2	167.0	167.0	167.1	167.1	167.2	166.1
115°	187.9	188.5	189.2	189.8	190.5	191.1	191.9	192.7	193.4	194.2	194.6
117.5°	212.8	213.3	213.6	214.0	214.3	214.6	215.2	215.8	216.4	217.0	217.4
120°	228.5	228.9	229.1	229.4	229.6	229.8	230.5	231.0	231.6	232.1	232.5
122.5°	243.5	243.8	244.1	244.4	244.7	245.0	245.4	245.8	246.3	246.7	246.9
125°	264.9	265.2	265.6	265.9	266.2	266.5	266.6	266.7	266.9	267.0	267.2
127.5°	285.3	285.8	286.2	286.5	286.9	287.2	287.5	287.7	287.9	288.2	288.2
130°	298.1	298.6	298.9	299.2	299.4	299.7	300.0	300.4	300.7	301.0	301.0
132.5°	310.4	310.8	311.0	311.3	311.5	311.8	312.1	312.4	312.6	312.9	313.0
135°	328.5	328.9	329.1	329.5	329.8	330.1	330.3	330.5	330.7	330.9	330.9
137.5°	345.0	345.3	345.5	345.6	345.8	346.0	346.4	346.7	347.0	347.4	347.5
140°	355.2	355.5	355.7	355.9	356.2	356.4	356.7	356.9	357.2	357.6	357.6
142.5°	365.0	365.3	365.6	365.8	366.0	366.3	366.5	366.7	366.9	367.2	367.2
145°	379.1	379.5	379.6	379.8	379.8	380.0	380.2	380.3	380.5	380.6	380.7
147.5°	391.3	391.6	391.8	391.9	392.1	392.2	392.4	392.5	392.7	392.9	392.8
150°	398.9	399.1	399.3	399.4	399.5	399.6	399.8	400.0	400.1	400.3	400.2
152.5°	405.6	405.8	405.8	405.9	406.0	406.0	406.3	406.6	406.9	407.2	407.1
155°	414.7	414.7	414.8	414.8	414.9	415.0	415.4	415.8	416.1	416.5	416.4
157.5°	423.1	423.1	423.0	422.9	422.8	422.8	423.2	423.7	424.1	424.6	424.5
160°	427.7	427.6	427.5	427.4	427.4	427.3	427.7	428.2	428.7	429.1	429.0
162.5°	431.8	431.6	431.5	431.5	431.4	431.3	431.8	432.3	432.8	433.3	433.4
165°	437.1	437.0	436.9	436.8	436.7	436.7	437.2	437.8	438.5	439.0	439.0
167.5°	441.0	440.9	440.9	440.9	440.9	440.9	441.5	442.1	442.7	443.3	443.3
170°	443.5	443.3	443.3	443.3	443.3	443.3	443.9	444.5	445.1	445.6	445.6
172.5°	444.8	444.7	444.7	444.8	444.9	444.9	445.5	446.1	446.7	447.2	447.2
175°	446.9	446.7	446.8	446.9	446.9	447.0	447.5	448.0	448.6	449.0	449.0
177.5°	447.6	447.5	447.6	447.6	447.7	447.8	448.3	448.7	449.2	449.7	449.6
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	433.4	433.2	434.4	433.6	434.4	433.2	433.4	434.6	435.0	435.1	435.1
5°	403.4	404.1	401.8	401.8	401.8	404.1	403.4	404.7	405.8	406.7	407.9
7.5°	376.6	375.7	375.8	374.6	375.8	375.7	376.6	377.7	379.1	381.1	382.9
10°	360.3	359.0	358.5	358.8	358.5	359.0	360.3	363.0	363.8	365.6	367.6
12.5°	346.8	346.6	343.7	343.7	343.7	346.6	346.8	347.5	349.4	353.2	355.4
15°	330.9	326.8	326.3	327.6	326.3	326.8	330.9	330.9	331.8	334.6	335.9
17.5°	315.0	312.7	312.9	312.3	312.9	312.7	315.0	315.3	316.0	318.4	320.1
20°	306.5	305.2	305.0	303.5	305.0	305.2	306.5	306.5	307.5	308.5	310.3
22.5°	298.8	298.4	298.5	296.8	298.5	298.4	298.8	299.4	300.2	301.0	302.2
25°	289.2	290.3	289.4	289.4	289.4	290.3	289.2	289.4	289.6	290.7	291.6
27.5°	282.7	282.7	282.2	282.2	282.2	282.7	282.7	282.2	281.9	281.5	281.3
30°	277.8	277.6	278.0	278.0	278.0	277.6	277.8	276.9	276.4	276.3	275.3
32.5°	272.9	273.1	273.2	273.4	273.2	273.1	272.9	271.8	271.0	270.4	269.8
35°	265.2	265.5	266.2	265.7	266.2	265.5	265.2	263.9	263.1	261.7	260.6
37.5°	255.0	256.0	255.8	256.1	255.8	256.0	255.0	254.6	253.7	252.7	251.4
40°	247.2	247.9	247.7	247.7	247.7	247.9	247.2	247.0	246.2	245.5	244.4
42.5°	239.3	239.8	239.2	238.9	239.2	239.8	239.3	238.9	238.5	237.2	235.9
45°	226.4	225.9	226.6	225.7	226.6	225.9	226.4	225.6	225.3	224.4	223.3
47.5°	211.9	212.4	212.5	213.2	212.5	212.4	211.9	212.0	210.8	210.2	209.9
50°	202.3	203.6	203.6	203.3	203.6	203.6	202.3	201.8	201.0	200.0	200.0
52.5°	192.7	193.3	194.3	194.2	194.3	193.3	192.7	192.0	191.1	189.8	189.5
55°	178.0	178.5	179.0	179.2	179.0	178.5	178.0	176.3	175.7	175.0	173.9
57.5°	162.9	162.7	163.7	164.1	163.7	162.7	162.9	161.3	160.3	158.3	158.0
60°	152.1	152.1	153.9	154.6	153.9	152.1	152.1	150.4	148.9	147.6	147.1
62.5°	140.7	141.5	143.2	142.3	143.2	141.5	140.7	138.8	137.6	136.0	134.8
65°	124.0	125.8	125.6	126.5	125.6	125.8	124.0	123.0	120.6	119.0	117.7
67.5°	106.6	107.7	109.3	109.4	109.3	107.7	106.6	104.9	103.3	101.7	100.1
70°	94.8	96.0	96.8	97.5	96.8	96.0	94.8	93.1	91.3	90.2	88.5
72.5°	83.4	84.0	86.1	85.2	86.1	84.0	83.4	81.3	79.9	79.0	77.1
75°	65.4	67.0	68.3	67.7	68.3	67.0	65.4	63.9	62.8	61.5	59.8
77.5°	48.4	50.0	50.5	50.0	50.5	50.0	48.4	47.4	46.8	44.2	44.0
80°	38.2	38.0	39.3	39.1	39.3	38.0	38.2	36.7	35.5	34.0	34.0
82.5°	28.0	27.8	28.4	28.6	28.4	27.8	28.0	27.1	25.7	25.1	24.5
85°	13.6	14.2	13.4	13.2	13.4	14.2	13.6	12.7	12.7	12.7	12.5
87.5°	5.1	5.1	5.0	4.8	5.0	5.1	5.1	5.0	5.7	5.1	5.1
90°	9.5	9.7	9.8	10.0	9.8	9.7	9.5	9.4	9.1	8.9	8.6
92.5°	10.7	10.8	10.9	11.0	10.9	10.8	10.7	10.7	10.5	10.0	9.5
95°	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.4	11.9	11.4
97.5°	13.5	13.6	13.7	13.8	13.7	13.6	13.5	13.4	13.1	12.5	11.9
100°	13.8	13.9	13.9	13.9	13.9	13.9	13.8	13.7	13.4	12.7	12.2
102.5°	13.9	13.9	14.1	14.2	14.1	13.9	13.9	13.8	14.6	16.4	18.3
105°	14.2	14.3	14.5	14.6	14.5	14.3	14.2	14.0	20.5	33.6	46.8
107.5°	75.7	65.8	55.9	46.0	55.9	65.8	75.7	85.5	95.3	104.9	114.5
110°	123.4	112.7	102.2	91.6	102.2	112.7	123.4	133.9	140.4	142.9	145.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	163.8	161.6	159.4	157.1	159.4	161.6	163.8	166.1	167.2	167.1	167.1
115°	194.9	195.3	195.6	195.9	195.6	195.3	194.9	194.6	194.2	193.4	192.7
117.5°	217.4	217.4	217.5	217.5	217.5	217.4	217.4	217.4	217.0	216.4	215.8
120°	232.5	232.5	232.5	232.5	232.5	232.5	232.5	232.5	232.1	231.6	231.0
122.5°	246.9	247.0	247.0	247.1	247.0	247.0	246.9	246.9	246.7	246.3	245.8
125°	267.3	267.5	267.7	267.8	267.7	267.5	267.3	267.2	267.0	266.9	266.7
127.5°	288.0	287.9	287.8	287.7	287.8	287.9	288.0	288.2	288.2	287.9	287.7
130°	300.9	300.8	300.6	300.4	300.6	300.8	300.9	301.0	301.0	300.7	300.4
132.5°	312.7	312.5	312.4	312.2	312.4	312.5	312.7	313.0	312.9	312.6	312.4
135°	330.7	330.5	330.3	330.1	330.3	330.5	330.7	330.9	330.9	330.7	330.5
137.5°	347.3	347.2	347.0	346.9	347.0	347.2	347.3	347.5	347.4	347.0	346.7
140°	357.5	357.3	357.2	357.0	357.2	357.3	357.5	357.6	357.6	357.2	356.9
142.5°	367.0	366.7	366.6	366.4	366.6	366.7	367.0	367.2	367.2	366.9	366.7
145°	380.7	380.7	380.7	380.7	380.7	380.7	380.7	380.7	380.6	380.5	380.3
147.5°	392.4	392.0	391.7	391.3	391.7	392.0	392.4	392.8	392.9	392.7	392.5
150°	400.0	399.8	399.5	399.4	399.5	399.8	400.0	400.2	400.3	400.1	400.0
152.5°	406.8	406.4	406.0	405.8	406.0	406.4	406.8	407.1	407.2	406.9	406.6
155°	416.0	415.6	415.1	414.6	415.1	415.6	416.0	416.4	416.5	416.1	415.8
157.5°	424.0	423.4	422.7	422.2	422.7	423.4	424.0	424.5	424.6	424.1	423.7
160°	428.6	428.0	427.5	427.0	427.5	428.0	428.6	429.0	429.1	428.7	428.2
162.5°	432.9	432.4	432.0	431.5	432.0	432.4	432.9	433.4	433.3	432.8	432.3
165°	438.6	438.0	437.5	437.0	437.5	438.0	438.6	439.0	439.0	438.5	437.8
167.5°	442.7	442.1	441.5	440.9	441.5	442.1	442.7	443.3	443.3	442.7	442.1
170°	445.1	444.5	443.9	443.3	443.9	444.5	445.1	445.6	445.6	445.1	444.5
172.5°	446.6	445.9	445.3	444.6	445.3	445.9	446.6	447.2	447.2	446.7	446.1
175°	448.5	447.8	447.2	446.7	447.2	447.8	448.5	449.0	449.0	448.6	448.0
177.5°	449.0	448.5	447.8	447.2	447.8	448.5	449.0	449.6	449.7	449.2	448.7
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	434.6	434.6	437.9	440.1	442.7	444.4	445.6	446.9	449.0	451.8	455.0
5°	409.7	410.6	415.5	420.3	424.9	428.9	432.2	436.1	440.9	446.9	453.5
7.5°	385.7	389.1	393.9	399.8	406.2	412.0	417.8	424.3	431.2	439.9	449.1
10°	370.2	373.9	379.8	387.4	394.2	401.0	408.2	415.2	423.8	434.1	446.0
12.5°	356.7	360.2	366.4	374.5	381.0	388.5	396.8	406.0	415.6	427.9	441.4
15°	337.9	342.1	349.6	353.5	363.4	372.4	380.1	393.2	405.6	418.3	433.9
17.5°	322.5	324.9	330.9	338.3	345.6	355.8	365.8	376.8	389.1	404.6	424.1
20°	312.0	314.0	320.6	328.3	336.2	345.4	354.4	365.4	379.2	395.7	416.8
22.5°	304.2	306.2	310.6	318.8	326.1	333.8	342.8	355.9	370.6	386.7	409.5
25°	292.7	294.0	296.9	303.5	310.0	318.6	326.5	338.8	353.9	372.9	395.7
27.5°	281.8	283.1	285.5	290.2	296.4	303.3	312.0	322.3	337.7	358.3	382.5
30°	275.3	275.6	277.8	282.2	287.5	293.1	301.0	312.9	327.4	348.3	373.7
32.5°	269.8	268.9	270.4	273.7	278.8	284.6	291.1	302.7	316.7	337.1	363.4
35°	260.2	259.8	259.1	261.9	266.4	270.7	276.4	285.2	301.0	320.2	347.6
37.5°	250.5	249.4	248.3	249.6	253.0	257.6	262.5	270.3	284.0	305.0	331.3
40°	243.3	242.4	241.8	241.3	244.4	248.7	252.5	260.0	272.7	292.7	318.6
42.5°	235.4	234.9	234.0	233.4	235.9	239.3	243.2	249.8	262.5	281.3	305.8
45°	222.6	222.3	221.8	221.3	222.9	225.9	229.0	233.8	244.9	263.1	285.2
47.5°	208.5	207.9	208.1	207.4	208.9	210.9	213.1	218.3	228.8	243.6	259.8
50°	198.3	198.0	198.0	198.0	198.5	201.0	202.9	206.9	216.5	231.2	242.9
52.5°	188.6	187.7	187.7	188.0	188.9	190.4	191.6	196.0	204.3	216.5	227.1
55°	173.4	171.7	171.3	171.7	172.4	173.7	175.0	178.5	185.8	194.7	201.0
57.5°	156.7	155.7	155.1	155.2	155.6	156.7	157.7	161.5	167.2	171.9	175.9
60°	145.0	145.3	143.4	143.8	143.8	144.7	146.3	148.6	153.4	156.7	160.7
62.5°	133.8	133.3	132.7	132.1	132.1	132.4	134.5	136.4	140.5	142.2	145.2
65°	116.6	116.6	115.3	115.7	115.9	114.4	115.5	117.7	120.4	121.0	123.9
67.5°	99.2	98.5	97.7	97.1	97.1	97.0	97.6	98.6	100.6	100.9	103.0
70°	87.2	86.7	86.5	85.9	85.0	86.1	85.4	86.5	87.7	87.8	89.2
72.5°	75.6	75.1	74.7	74.1	73.7	73.6	73.6	74.9	75.7	75.4	76.8
75°	59.1	58.6	58.2	57.1	57.1	56.5	56.6	57.5	58.4	57.8	59.1
77.5°	43.4	42.0	41.9	42.2	41.5	41.7	41.4	41.3	41.7	41.7	42.9
80°	33.4	31.9	32.2	32.0	31.9	31.6	31.2	31.4	31.6	31.9	32.5
82.5°	24.0	23.9	23.5	23.5	23.2	22.6	22.4	22.8	23.0	22.9	23.4
85°	12.3	11.6	12.1	11.9	12.1	11.9	11.2	11.2	11.6	11.4	11.9
87.5°	5.4	5.3	4.9	4.9	4.5	4.5	4.1	4.2	4.2	4.1	4.2
90°	8.3	8.0	7.1	6.0	5.1	4.1	3.3	2.5	1.8	1.0	0.4
92.5°	9.0	8.5	7.8	7.1	6.3	5.7	5.4	5.6	5.7	6.0	6.2
95°	10.8	10.4	9.5	8.7	7.9	7.1	8.2	11.2	14.2	17.2	20.4
97.5°	11.3	10.7	16.0	21.4	26.7	32.0	35.3	36.8	38.1	39.5	40.8
100°	11.6	11.0	22.5	34.1	45.6	57.2	62.2	60.7	59.3	57.8	56.3
102.5°	20.1	22.0	34.5	47.1	59.8	72.4	78.1	77.1	76.0	74.9	73.9
105°	59.9	73.0	79.6	86.2	92.9	99.6	102.5	101.7	100.9	100.1	99.2
107.5°	124.0	133.7	132.6	131.6	130.5	129.5	128.7	128.0	127.3	126.7	126.0
110°	147.8	150.2	149.4	148.5	147.8	146.9	146.3	145.6	145.1	144.5	143.9



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	167.0	167.0	166.2	165.4	164.6	163.7	163.1	162.5	162.0	161.5	160.9
115°	191.9	191.1	190.5	189.8	189.2	188.5	187.9	187.5	187.1	186.6	186.2
117.5°	215.2	214.6	214.3	214.0	213.6	213.3	212.8	212.3	211.7	211.2	210.7
120°	230.5	229.8	229.6	229.4	229.1	228.9	228.5	227.8	227.2	226.5	225.8
122.5°	245.4	245.0	244.7	244.4	244.1	243.8	243.5	242.9	242.3	241.9	241.3
125°	266.6	266.5	266.2	265.9	265.6	265.2	264.9	264.2	263.6	263.1	262.5
127.5°	287.5	287.2	286.9	286.5	286.2	285.8	285.3	284.7	284.2	283.6	283.0
130°	300.0	299.7	299.4	299.2	298.9	298.6	298.1	297.6	296.9	296.3	295.8
132.5°	312.1	311.8	311.5	311.3	311.0	310.8	310.4	309.8	309.2	308.6	308.0
135°	330.3	330.1	329.8	329.5	329.1	328.9	328.5	328.1	327.6	327.2	326.8
137.5°	346.4	346.0	345.8	345.6	345.5	345.3	345.0	344.4	343.8	343.3	342.7
140°	356.7	356.4	356.2	355.9	355.7	355.5	355.2	354.7	354.3	353.8	353.4
142.5°	366.5	366.3	366.0	365.8	365.6	365.3	365.0	364.6	364.1	363.7	363.3
145°	380.2	380.0	379.8	379.8	379.6	379.5	379.1	378.6	378.1	377.6	377.0
147.5°	392.4	392.2	392.1	391.9	391.8	391.6	391.3	391.1	390.7	390.4	390.0
150°	399.8	399.6	399.5	399.4	399.3	399.1	398.9	398.7	398.4	398.2	398.0
152.5°	406.3	406.0	406.0	405.9	405.8	405.8	405.6	405.5	405.4	405.3	405.2
155°	415.4	415.0	414.9	414.8	414.8	414.7	414.7	414.9	415.0	415.2	415.4
157.5°	423.2	422.8	422.8	422.9	423.0	423.1	423.1	423.1	423.2	423.2	423.2
160°	427.7	427.3	427.4	427.4	427.5	427.6	427.7	427.7	427.8	427.9	428.0
162.5°	431.8	431.3	431.4	431.5	431.5	431.6	431.8	432.0	432.2	432.3	432.5
165°	437.2	436.7	436.7	436.8	436.9	437.0	437.1	437.3	437.5	437.7	438.0
167.5°	441.5	440.9	440.9	440.9	440.9	440.9	441.0	441.4	441.7	442.0	442.2
170°	443.9	443.3	443.3	443.3	443.3	443.3	443.5	443.7	444.0	444.3	444.6
172.5°	445.5	444.9	444.9	444.8	444.7	444.7	444.8	445.2	445.5	445.9	446.2
175°	447.5	447.0	446.9	446.9	446.8	446.7	446.9	447.2	447.5	447.9	448.3
177.5°	448.3	447.8	447.7	447.6	447.6	447.5	447.6	448.0	448.3	448.6	448.8
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	456.0	456.9	459.9	462.0	464.5	465.9	467.2	468.3	469.8	470.0	475.1
5°	458.1	462.4	470.1	475.8	482.9	490.5	495.8	498.2	504.6	509.8	520.4
7.5°	457.5	466.8	478.4	490.5	503.3	515.3	525.7	538.0	546.7	559.9	572.8
10°	456.9	469.5	484.4	499.7	517.7	534.4	549.4	566.1	579.9	598.1	613.7
12.5°	455.3	470.5	491.3	509.4	531.3	554.3	576.5	597.9	610.1	640.5	654.8
15°	451.5	469.5	495.4	523.0	553.1	580.3	608.4	630.8	667.0	693.6	710.6
17.5°	444.0	469.2	499.9	533.3	569.9	605.8	637.6	671.6	710.0	742.2	776.5
20°	440.5	468.2	502.4	539.3	577.3	617.9	654.1	694.9	736.9	768.5	812.5
22.5°	433.9	465.3	502.2	543.3	583.9	625.9	668.4	709.5	758.0	801.5	843.4
25°	423.4	458.5	496.7	542.6	590.2	632.4	683.2	737.8	788.2	844.3	886.0
27.5°	412.2	449.7	488.0	530.7	581.9	632.0	695.8	757.5	819.3	867.6	898.5
30°	403.6	440.1	479.6	522.6	573.3	632.8	704.2	771.6	831.8	873.3	890.6
32.5°	394.3	431.2	466.2	511.3	565.4	632.3	709.5	779.9	832.5	860.1	856.7
35°	379.7	410.6	444.7	488.1	551.8	628.4	712.6	780.6	812.8	806.9	762.1
37.5°	358.5	384.7	418.1	465.7	536.0	620.3	706.3	757.4	755.4	707.1	642.2
40°	345.4	367.6	399.8	449.9	523.7	615.0	696.7	729.9	701.8	634.3	556.7
42.5°	328.2	348.6	380.9	432.3	510.2	604.4	678.3	687.9	632.9	555.3	484.1
45°	301.5	319.5	352.9	406.0	489.8	581.0	633.3	609.7	535.7	455.6	401.4
47.5°	272.8	291.5	323.6	378.2	460.5	545.9	570.8	520.8	444.9	379.8	330.1
50°	254.7	272.7	304.2	359.2	440.7	517.1	527.4	462.9	393.0	335.9	295.1
52.5°	236.5	253.4	284.3	339.6	417.5	483.7	477.4	411.6	347.4	298.7	266.6
55°	209.2	225.3	254.7	306.5	377.5	429.9	406.9	344.1	291.0	253.2	228.8
57.5°	184.9	200.3	225.6	272.5	334.1	370.2	340.9	287.9	245.7	216.6	198.5
60°	168.4	182.0	206.2	249.7	303.2	330.6	301.7	255.0	219.3	196.0	179.8
62.5°	152.8	164.7	187.0	226.5	273.1	296.1	266.7	227.2	196.9	176.3	162.4
65°	129.1	139.9	159.7	190.4	228.6	243.9	218.7	186.6	163.2	147.8	138.6
67.5°	107.5	116.7	133.7	157.9	186.1	197.2	178.0	153.2	135.4	123.1	115.8
70°	93.1	101.0	114.4	135.3	160.7	169.3	151.3	130.8	117.9	108.0	101.2
72.5°	81.0	86.8	99.0	115.1	136.3	143.1	130.5	112.6	100.6	93.1	87.7
75°	61.7	66.5	74.5	87.4	102.1	106.0	96.6	85.4	77.3	72.0	67.9
77.5°	44.5	48.1	53.7	61.7	71.9	75.5	69.6	62.0	56.1	52.6	50.2
80°	33.6	36.5	41.3	47.9	54.0	56.0	52.5	46.8	42.6	40.6	38.6
82.5°	24.8	26.4	29.3	33.8	38.0	40.3	37.4	33.9	31.7	29.9	29.1
85°	12.5	13.4	14.7	16.5	19.1	20.0	18.9	18.0	16.7	15.6	15.6
87.5°	4.8	4.9	5.6	6.1	7.0	7.7	7.7	7.5	7.5	7.4	7.4
90°	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3	8.6
92.5°	6.0	5.7	5.6	5.4	5.7	6.3	7.1	7.8	8.5	9.0	9.5
95°	17.2	14.2	11.2	8.2	7.1	7.9	8.7	9.5	10.4	10.8	11.4
97.5°	39.5	38.1	36.8	35.3	32.0	26.7	21.4	16.0	10.7	11.3	11.9
100°	57.8	59.3	60.7	62.2	57.2	45.6	34.1	22.5	11.0	11.6	12.2
102.5°	74.9	76.0	77.1	78.1	72.4	59.8	47.1	34.5	22.0	20.1	18.3
105°	100.1	100.9	101.7	102.5	99.6	92.9	86.2	79.6	73.0	59.9	46.8
107.5°	126.7	127.3	128.0	128.7	129.5	130.5	131.6	132.6	133.7	124.0	114.5
110°	144.5	145.1	145.6	146.3	146.9	147.8	148.5	149.4	150.2	147.8	145.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.5	162.0	162.5	163.1	163.7	164.6	165.4	166.2	167.0	167.0	167.1
115°	186.6	187.1	187.5	187.9	188.5	189.2	189.8	190.5	191.1	191.9	192.7
117.5°	211.2	211.7	212.3	212.8	213.3	213.6	214.0	214.3	214.6	215.2	215.8
120°	226.5	227.2	227.8	228.5	228.9	229.1	229.4	229.6	229.8	230.5	231.0
122.5°	241.9	242.3	242.9	243.5	243.8	244.1	244.4	244.7	245.0	245.4	245.8
125°	263.1	263.6	264.2	264.9	265.2	265.6	265.9	266.2	266.5	266.6	266.7
127.5°	283.6	284.2	284.7	285.3	285.8	286.2	286.5	286.9	287.2	287.5	287.7
130°	296.3	296.9	297.6	298.1	298.6	298.9	299.2	299.4	299.7	300.0	300.4
132.5°	308.6	309.2	309.8	310.4	310.8	311.0	311.3	311.5	311.8	312.1	312.4
135°	327.2	327.6	328.1	328.5	328.9	329.1	329.5	329.8	330.1	330.3	330.5
137.5°	343.3	343.8	344.4	345.0	345.3	345.5	345.6	345.8	346.0	346.4	346.7
140°	353.8	354.3	354.7	355.2	355.5	355.7	355.9	356.2	356.4	356.7	356.9
142.5°	363.7	364.1	364.6	365.0	365.3	365.6	365.8	366.0	366.3	366.5	366.7
145°	377.6	378.1	378.6	379.1	379.5	379.6	379.8	379.8	380.0	380.2	380.3
147.5°	390.4	390.7	391.1	391.3	391.6	391.8	391.9	392.1	392.2	392.4	392.5
150°	398.2	398.4	398.7	398.9	399.1	399.3	399.4	399.5	399.6	399.8	400.0
152.5°	405.3	405.4	405.5	405.6	405.8	405.8	405.9	406.0	406.0	406.3	406.6
155°	415.2	415.0	414.9	414.7	414.7	414.8	414.8	414.9	415.0	415.4	415.8
157.5°	423.2	423.2	423.1	423.1	423.1	423.0	422.9	422.8	422.8	423.2	423.7
160°	427.9	427.8	427.7	427.7	427.6	427.5	427.4	427.4	427.3	427.7	428.2
162.5°	432.3	432.2	432.0	431.8	431.6	431.5	431.5	431.4	431.3	431.8	432.3
165°	437.7	437.5	437.3	437.1	437.0	436.9	436.8	436.7	436.7	437.2	437.8
167.5°	442.0	441.7	441.4	441.0	440.9	440.9	440.9	440.9	440.9	441.5	442.1
170°	444.3	444.0	443.7	443.5	443.3	443.3	443.3	443.3	443.3	443.9	444.5
172.5°	445.9	445.5	445.2	444.8	444.7	444.7	444.8	444.9	444.9	445.5	446.1
175°	447.9	447.5	447.2	446.9	446.7	446.8	446.9	446.9	447.0	447.5	448.0
177.5°	448.6	448.3	448.0	447.6	447.5	447.6	447.6	447.7	447.8	448.3	448.7
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	476.9	477.1	479.0	480.4	479.8	480.6	481.0
5°	521.0	529.0	533.1	536.2	536.4	536.7	538.4
7.5°	583.6	592.1	598.3	607.8	610.5	613.7	612.8
10°	629.3	641.9	652.6	658.3	664.5	673.4	666.2
12.5°	672.0	694.2	710.6	719.4	725.2	727.0	723.5
15°	742.4	771.4	786.9	786.6	806.3	814.8	801.4
17.5°	806.9	833.7	855.2	866.1	882.6	886.2	884.6
20°	846.5	875.7	892.4	911.3	919.8	927.5	928.8
22.5°	880.5	906.8	924.7	940.4	947.5	951.2	953.4
25°	915.7	936.3	947.1	952.5	954.5	954.0	951.2
27.5°	913.2	914.8	903.0	891.4	880.9	869.2	865.2
30°	889.5	871.1	838.1	819.4	792.0	770.2	779.1
32.5°	827.2	790.4	753.5	712.7	678.9	669.3	659.6
35°	706.0	641.4	603.6	559.7	542.2	524.6	512.5
37.5°	571.1	521.2	476.4	447.7	430.1	419.0	413.0
40°	493.8	448.8	411.9	388.6	375.2	362.8	361.0
42.5°	432.2	390.3	362.6	344.0	331.2	325.8	322.0
45°	353.9	324.8	306.1	292.9	284.4	281.1	276.6
47.5°	299.6	279.0	264.9	256.0	249.5	247.0	246.8
50°	269.2	252.0	241.8	234.7	229.7	228.8	225.3
52.5°	246.4	231.5	223.5	217.4	213.7	211.2	210.2
55°	213.9	204.0	196.7	193.2	190.4	187.9	187.9
57.5°	187.1	178.9	174.1	171.1	170.2	168.5	167.4
60°	170.6	163.6	159.9	157.2	155.4	155.7	153.7
62.5°	154.5	149.9	146.3	143.7	141.6	141.7	141.8
65°	131.5	128.0	125.4	124.5	123.2	121.7	122.1
67.5°	111.5	108.2	106.1	104.6	104.2	103.3	104.6
70°	97.1	94.6	93.1	91.8	91.3	91.5	92.7
72.5°	83.9	82.2	81.2	80.6	79.6	79.6	80.4
75°	65.9	64.6	63.7	63.1	62.8	62.8	62.8
77.5°	48.4	48.1	47.7	46.8	46.8	47.0	47.0
80°	38.2	37.5	37.3	36.9	36.2	35.8	36.9
82.5°	28.6	27.9	27.7	27.6	26.6	26.5	27.4
85°	15.4	14.7	14.9	14.7	14.7	14.5	14.5
87.5°	7.3	7.1	7.0	7.2	7.1	6.9	7.3
90°	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	10.0	10.5	10.7	10.7	10.8	10.9	11.0
95°	11.9	12.4	12.6	12.6	12.6	12.6	12.6
97.5°	12.5	13.1	13.4	13.5	13.6	13.7	13.8
100°	12.7	13.4	13.7	13.8	13.9	13.9	13.9
102.5°	16.4	14.6	13.8	13.9	13.9	14.1	14.2
105°	33.6	20.5	14.0	14.2	14.3	14.5	14.6
107.5°	104.9	95.3	85.5	75.7	65.8	55.9	46.0
110°	142.9	140.4	133.9	123.4	112.7	102.2	91.6



TEST NUMBER: P331865-830

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	167.1	167.2	166.1	163.8	161.6	159.4	157.1
115°	193.4	194.2	194.6	194.9	195.3	195.6	195.9
117.5°	216.4	217.0	217.4	217.4	217.4	217.5	217.5
120°	231.6	232.1	232.5	232.5	232.5	232.5	232.5
122.5°	246.3	246.7	246.9	246.9	247.0	247.0	247.1
125°	266.9	267.0	267.2	267.3	267.5	267.7	267.8
127.5°	287.9	288.2	288.2	288.0	287.9	287.8	287.7
130°	300.7	301.0	301.0	300.9	300.8	300.6	300.4
132.5°	312.6	312.9	313.0	312.7	312.5	312.4	312.2
135°	330.7	330.9	330.9	330.7	330.5	330.3	330.1
137.5°	347.0	347.4	347.5	347.3	347.2	347.0	346.9
140°	357.2	357.6	357.6	357.5	357.3	357.2	357.0
142.5°	366.9	367.2	367.2	367.0	366.7	366.6	366.4
145°	380.5	380.6	380.7	380.7	380.7	380.7	380.7
147.5°	392.7	392.9	392.8	392.4	392.0	391.7	391.3
150°	400.1	400.3	400.2	400.0	399.8	399.5	399.4
152.5°	406.9	407.2	407.1	406.8	406.4	406.0	405.8
155°	416.1	416.5	416.4	416.0	415.6	415.1	414.6
157.5°	424.1	424.6	424.5	424.0	423.4	422.7	422.2
160°	428.7	429.1	429.0	428.6	428.0	427.5	427.0
162.5°	432.8	433.3	433.4	432.9	432.4	432.0	431.5
165°	438.5	439.0	439.0	438.6	438.0	437.5	437.0
167.5°	442.7	443.3	443.3	442.7	442.1	441.5	440.9
170°	445.1	445.6	445.6	445.1	444.5	443.9	443.3
172.5°	446.7	447.2	447.2	446.6	445.9	445.3	444.6
175°	448.6	449.0	449.0	448.5	447.8	447.2	446.7
177.5°	449.2	449.7	449.6	449.0	448.5	447.8	447.2
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3

(END OF REPORT)