

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831370

Luminaire Tested: S123DIP-S340D365U830-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831370
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D365U830-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2663.4 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 22.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831370
CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	100	96	92	88	93	89	86	83	77	74	72	66	64	62	55	54	53	48				
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41				
3	84	75	68	62	78	70	64	59	61	56	52	52	49	46	44	42	40	36				
4	77	67	59	53	71	62	56	50	54	49	45	47	43	40	40	37	35	31				
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	33	31	28				
6	66	54	46	41	61	51	44	39	45	39	35	39	35	31	34	30	28	25				
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	28	25	23				
8	57	45	37	32	53	42	36	31	38	32	28	33	29	25	29	25	23	21				
9	53	41	34	29	50	39	32	28	35	29	26	31	26	23	27	23	21	19				
10	50	38	31	26	47	36	30	25	32	27	23	29	24	21	25	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	9961	9961	9961	9961	9961
5°	12598	11890	10050	8099	7443
10°	12719	13105	9983	6456	5642
15°	9580	12167	9916	5467	4771
20°	6675	9845	9789	4781	4333
25°	5090	7571	9573	4399	4065
30°	4404	6016	9229	4129	3848
35°	4085	5079	8832	3933	3696
40°	3868	4555	8272	3747	3645
45°	3739	4217	7563	3602	3621
50°	3674	3949	6723	3470	3602
55°	3537	3751	5898	3344	3618
60°	3412	3541	5085	3227	3559
65°	3204	3342	4386	3100	3489
70°	2958	3087	3729	2892	3286
75°	2678	2770	3198	2687	2999
80°	2207	2424	2529	2343	2529
85°	1754	1964	1853	1988	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8636 cd/sqm



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	3.3
10°-20°	217.7	8.2
20°-30°	257.7	9.7
30°-40°	259.1	9.7
40°-50°	237.7	8.9
50°-60°	196.2	7.4
60°-70°	138.8	5.2
70°-80°	74.1	2.8
80°-90°	19.7	0.7
90°-100°	27.3	1.0
100°-110°	82.6	3.1
110°-120°	140.6	5.3
120°-130°	185.0	6.9
130°-140°	208.0	7.8
140°-150°	204.5	7.7
150°-160°	172.1	6.5
160°-170°	114.6	4.3
170°-180°	40.1	1.5
0°-30°	562.9	21.1
0°-40°	822.0	30.9
0°-60°	1255.9	47.2
0°-90°	1488.5	55.9
90°-120°	250.5	9.4
90°-150°	848.0	31.8
90°-180°	1175.0	44.1
0°-180°	2663.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	925	925	925	925	925	
5°	1166	1100	930	750	689	111
15°	860	1092	890	491	428	237
25°	429	638	806	370	342	202
35°	311	386	672	299	281	195
45°	246	277	497	237	238	190
55°	188	200	314	178	193	169
65°	126	131	172	122	137	125
75°	64	67	77	65	72	68
85°	14	16	15	16	16	16
90°	10	8	0	8	10	6
95°	26	25	20	25	26	26
105°	79	79	75	79	79	84
115°	142	142	142	142	142	141
125°	205	208	207	208	205	183
135°	268	270	269	270	268	207
145°	326	328	326	328	326	204
155°	373	374	373	374	373	172
165°	405	406	407	406	405	114
175°	421	422	423	422	421	40
180°	424	424	424	424	424	



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	1043.1	1042.0	1040.9	1035.6	1030.2	1027.6	1025.0	1017.3	1009.6	1001.0	992.4
5°	1165.9	1168.9	1171.9	1168.5	1165.0	1154.5	1144.0	1130.0	1116.1	1100.4	1084.7
7.5°	1222.6	1224.3	1226.0	1223.9	1221.7	1218.9	1216.1	1203.7	1191.2	1175.1	1159.0
10°	1163.7	1167.6	1171.5	1179.8	1188.2	1197.7	1207.1	1205.4	1203.7	1199.0	1194.2
12.5°	1034.5	1039.2	1043.9	1060.7	1077.4	1098.9	1120.4	1138.8	1157.3	1170.2	1183.1
15°	859.7	872.8	885.9	901.1	916.4	948.0	979.5	1018.4	1057.2	1091.8	1126.4
17.5°	708.1	713.1	718.0	734.3	750.6	790.4	830.1	875.0	919.8	977.2	1034.5
20°	582.7	587.2	591.7	613.2	634.7	665.8	697.0	747.4	797.9	859.5	921.1
22.5°	489.5	496.6	503.7	515.7	527.8	557.6	587.5	632.3	677.2	745.3	813.3
25°	428.6	433.7	438.9	446.2	453.5	477.3	501.1	538.1	575.0	637.5	700.0
27.5°	386.9	389.1	391.2	398.5	405.8	421.3	436.7	468.5	500.3	553.3	606.3
30°	354.3	355.8	357.3	363.7	370.2	380.7	391.2	414.2	437.2	484.0	530.8
32.5°	331.5	332.6	333.7	338.6	343.5	351.1	358.6	375.3	392.1	430.7	469.4
35°	310.9	311.5	312.2	315.8	319.5	325.1	330.7	343.3	356.0	386.5	417.0
37.5°	292.9	293.7	294.6	296.7	298.9	303.8	308.8	318.8	328.9	352.3	375.7
40°	275.3	276.8	278.3	279.8	281.3	285.4	289.4	297.2	304.9	324.2	343.5
42.5°	260.2	261.7	263.2	263.9	264.5	266.9	269.2	276.3	283.4	297.8	312.2
45°	245.6	246.3	246.9	247.6	248.2	250.1	252.1	258.3	264.5	277.0	289.4
47.5°	232.3	232.3	232.3	232.7	233.2	234.9	236.6	241.1	245.6	255.3	265.0
50°	219.4	219.4	219.4	218.8	218.1	219.2	220.3	223.7	227.2	235.8	244.3
52.5°	204.0	204.0	204.0	204.2	204.4	204.4	204.4	207.4	210.4	218.1	225.9
55°	188.5	189.4	190.2	189.6	188.9	189.4	189.8	191.7	193.7	199.9	206.1
57.5°	173.1	173.5	173.9	173.7	173.5	173.7	173.9	175.6	177.4	182.1	186.8
60°	158.5	158.5	158.5	158.0	157.6	158.0	158.5	159.3	160.2	164.5	168.8
62.5°	142.1	142.4	142.6	142.8	143.0	142.6	142.1	143.2	144.3	147.5	150.7
65°	125.8	126.0	126.3	126.9	127.5	127.1	126.7	127.8	128.8	131.2	133.6
67.5°	111.2	110.8	110.4	110.6	110.8	111.4	112.1	112.3	112.5	115.1	117.7
70°	94.0	94.5	94.9	94.7	94.5	94.7	94.9	95.5	96.2	98.1	100.1
72.5°	78.6	78.8	79.0	79.0	79.0	79.4	79.9	80.5	81.2	82.2	83.3
75°	64.4	64.4	64.4	64.8	65.3	65.5	65.7	65.7	65.7	66.6	67.4
77.5°	49.0	50.0	51.1	50.9	50.7	51.1	51.5	52.2	52.8	53.2	53.7
80°	35.6	35.6	35.6	35.9	36.1	36.7	37.4	37.8	38.2	39.1	39.9
82.5°	22.8	23.0	23.2	23.8	24.5	24.9	25.3	26.0	26.6	26.6	26.6
85°	14.2	13.7	13.3	13.7	14.2	14.6	15.0	15.2	15.5	15.9	16.3
87.5°	6.9	6.9	6.9	6.9	6.9	7.1	7.3	7.3	7.3	7.3	7.3
90°	10.0	9.8	9.7	9.5	9.4	9.2	8.9	8.6	8.3	8.0	7.0
92.5°	14.3	14.5	14.6	14.8	14.9	14.9	14.7	14.4	14.2	14.0	13.5
95°	26.0	26.0	26.0	26.0	26.0	25.8	25.5	25.2	24.9	24.6	24.1
97.5°	37.3	37.4	37.5	37.5	37.6	37.5	37.1	36.7	36.3	36.0	35.5
100°	50.6	50.5	50.3	50.2	50.0	49.9	49.6	49.4	49.2	49.0	48.6
102.5°	64.3	64.4	64.4	64.5	64.6	64.5	64.3	64.1	63.8	63.6	63.1
105°	79.3	79.1	79.0	78.8	78.7	78.6	78.6	78.6	78.6	78.6	77.9
107.5°	94.6	94.7	94.7	94.8	94.9	94.8	94.6	94.4	94.2	93.9	93.6
110°	110.3	110.4	110.5	110.7	110.8	110.8	110.5	110.2	109.9	109.6	109.4



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.9	126.9	126.9	126.9	126.9	126.7	126.4	126.0	125.6	125.2	125.2
115°	141.9	142.0	142.0	142.1	142.2	142.2	142.1	142.0	142.0	141.9	142.0
117.5°	157.2	157.4	157.7	157.9	158.1	158.2	158.2	158.2	158.2	158.2	158.4
120°	173.5	173.7	173.8	174.0	174.1	174.2	174.3	174.4	174.5	174.5	174.9
122.5°	189.2	189.4	189.6	189.9	190.1	190.3	190.5	190.7	191.0	191.2	191.3
125°	204.8	205.1	205.4	205.7	206.0	206.3	206.6	206.9	207.2	207.5	207.7
127.5°	220.5	220.8	221.1	221.4	221.7	222.1	222.5	222.9	223.4	223.8	224.0
130°	235.8	236.3	236.9	237.4	237.9	238.3	238.6	238.9	239.2	239.5	239.7
132.5°	251.8	252.2	252.6	252.9	253.3	253.7	254.0	254.4	254.8	255.1	255.3
135°	268.5	268.6	268.8	268.9	269.1	269.3	269.6	269.9	270.2	270.5	270.5
137.5°	283.1	283.3	283.6	283.8	284.0	284.3	284.7	285.0	285.4	285.8	285.6
140°	297.4	298.0	298.5	299.0	299.5	299.8	299.9	300.0	300.0	300.1	300.0
142.5°	312.1	312.5	312.8	313.2	313.6	313.8	313.9	314.0	314.0	314.1	314.0
145°	326.1	326.4	326.7	327.0	327.3	327.5	327.5	327.6	327.7	327.8	327.5
147.5°	338.7	339.2	339.6	340.1	340.5	340.7	340.7	340.7	340.7	340.7	340.5
150°	350.7	351.2	351.6	352.1	352.5	352.7	352.7	352.7	352.7	352.7	352.6
152.5°	362.4	362.8	363.1	363.5	363.9	364.0	363.8	363.7	363.5	363.4	363.3
155°	372.7	373.2	373.8	374.3	374.8	374.9	374.6	374.3	374.0	373.7	373.6
157.5°	382.4	382.8	383.3	383.7	384.2	384.2	383.9	383.6	383.3	383.0	383.0
160°	391.7	392.0	392.3	392.6	392.9	392.9	392.5	392.1	391.7	391.4	391.4
162.5°	398.7	399.2	399.7	400.3	400.8	400.9	400.5	400.1	399.7	399.4	399.3
165°	405.4	405.9	406.4	406.9	407.4	407.5	407.0	406.6	406.1	405.7	405.7
167.5°	411.4	411.8	412.2	412.7	413.1	413.1	412.7	412.2	411.8	411.4	411.3
170°	415.7	416.2	416.7	417.2	417.8	417.8	417.2	416.7	416.2	415.7	415.7
172.5°	419.0	419.5	420.1	420.6	421.1	421.1	420.7	420.2	419.8	419.4	419.4
175°	421.4	421.9	422.4	422.9	423.4	423.5	423.0	422.6	422.1	421.7	421.7
177.5°	422.7	423.2	423.7	424.2	424.8	424.8	424.4	423.9	423.5	423.0	423.0
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	989.8	987.2	977.8	968.4	957.6	946.9	938.9	931.0	919.2	907.4	897.7
5°	1072.7	1060.7	1040.7	1020.7	993.7	966.6	948.4	930.1	905.7	881.2	861.6
7.5°	1138.4	1117.8	1089.9	1062.0	1026.5	991.1	957.6	924.1	886.8	849.4	818.9
10°	1180.3	1166.3	1134.1	1101.9	1054.5	1007.0	960.2	913.4	865.3	817.2	776.8
12.5°	1184.4	1185.6	1156.0	1126.4	1072.7	1019.0	962.1	905.2	844.7	784.1	737.1
15°	1148.5	1170.6	1154.3	1138.0	1083.9	1029.8	959.8	889.8	820.0	750.2	695.9
17.5°	1081.9	1129.4	1131.8	1134.1	1080.0	1025.9	948.4	870.9	791.9	712.8	655.7
20°	991.1	1061.1	1085.2	1109.2	1065.2	1021.2	937.9	854.6	766.1	677.6	617.7
22.5°	898.4	983.4	1027.4	1071.4	1038.8	1006.1	917.5	828.8	735.4	642.0	581.2
25°	792.7	885.5	953.1	1020.7	1000.8	980.8	893.4	806.0	706.6	607.2	545.2
27.5°	700.6	794.9	876.5	958.0	953.8	949.5	862.7	776.0	674.2	572.4	512.5
30°	618.6	706.4	797.7	888.9	899.4	910.0	826.2	742.5	640.5	538.5	480.7
32.5°	546.0	622.7	720.6	818.5	839.1	859.7	784.1	708.6	607.6	506.7	451.1
35°	486.5	556.1	654.0	751.9	777.7	803.5	737.8	672.1	573.7	475.4	422.3
37.5°	433.9	492.1	587.7	683.2	714.8	746.3	687.5	628.7	536.6	444.5	395.7
40°	390.3	437.2	525.0	612.8	649.3	685.8	637.3	588.7	501.4	414.0	369.1
42.5°	353.8	395.5	475.2	554.8	589.8	624.8	583.8	542.8	465.1	387.3	346.3
45°	322.7	356.0	428.4	500.7	534.0	567.3	532.1	496.8	428.4	359.9	321.6
47.5°	293.5	322.1	383.9	445.7	475.4	505.0	477.5	450.0	392.1	334.1	299.5
50°	267.3	290.3	344.4	398.5	424.3	450.0	425.8	401.5	353.8	306.2	276.1
52.5°	244.6	263.2	308.5	353.8	376.0	398.1	377.3	356.4	318.6	280.8	254.6
55°	222.0	237.9	277.2	316.5	331.5	346.5	330.4	314.3	283.9	253.4	231.2
57.5°	201.0	215.1	247.3	279.6	291.2	302.7	288.1	273.5	250.6	227.6	209.1
60°	180.4	192.0	218.8	245.6	252.7	259.8	248.0	236.2	220.1	204.0	187.4
62.5°	161.2	171.8	191.7	211.7	216.4	221.2	212.1	203.1	190.9	178.6	165.8
65°	141.5	149.4	165.8	182.1	185.1	188.1	180.1	172.2	163.0	153.7	144.3
67.5°	123.2	128.8	142.1	155.5	155.7	155.9	149.4	143.0	137.8	132.7	125.2
70°	105.4	110.8	119.6	128.4	128.6	128.8	123.7	118.5	114.7	110.8	105.2
72.5°	87.2	91.0	97.7	104.4	103.9	103.5	100.3	97.1	94.0	91.0	87.0
75°	70.6	73.9	78.4	82.9	81.6	80.3	78.6	76.9	74.3	71.7	69.1
77.5°	55.6	57.5	60.1	62.7	61.8	61.0	59.5	58.0	56.0	54.1	53.0
80°	40.8	41.7	43.4	45.1	44.7	44.2	42.5	40.8	40.4	39.9	38.4
82.5°	27.7	28.8	29.2	29.6	29.4	29.2	27.9	26.6	26.2	25.8	25.6
85°	16.5	16.7	17.0	17.2	16.5	15.9	15.5	15.0	15.0	15.0	14.8
87.5°	7.5	7.7	7.7	7.7	7.5	7.3	6.9	6.4	6.7	6.9	6.9
90°	6.1	5.1	4.1	3.3	2.6	1.8	1.1	0.3	1.1	1.8	2.6
92.5°	13.1	12.7	12.2	11.8	11.3	10.9	10.4	10.0	10.4	10.9	11.3
95°	23.5	22.9	22.3	21.7	21.2	20.7	20.2	19.7	20.2	20.7	21.2
97.5°	35.1	34.6	34.2	33.8	33.4	33.0	32.7	32.3	32.7	33.0	33.4
100°	48.2	47.9	47.5	47.1	46.6	46.2	45.7	45.3	45.7	46.2	46.6
102.5°	62.6	62.1	61.5	61.2	61.0	60.7	60.5	60.3	60.5	60.7	61.0
105°	77.3	76.6	75.9	75.5	75.4	75.2	75.1	74.9	75.1	75.2	75.4
107.5°	93.3	93.0	92.7	92.6	92.5	92.4	92.3	92.3	92.3	92.4	92.5
110°	109.3	109.1	109.0	108.8	108.7	108.5	108.4	108.3	108.4	108.5	108.7



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	125.2	125.2	125.2	125.2	125.1	125.1	125.0	124.9	125.0	125.1	125.1
115°	142.2	142.3	142.5	142.4	142.2	142.0	141.8	141.6	141.8	142.0	142.2
117.5°	158.5	158.7	158.8	158.8	158.8	158.7	158.6	158.5	158.6	158.7	158.8
120°	175.3	175.6	176.0	176.0	175.5	175.1	174.6	174.2	174.6	175.1	175.5
122.5°	191.5	191.6	191.8	191.7	191.4	191.1	190.8	190.5	190.8	191.1	191.4
125°	207.8	208.0	208.1	208.1	207.8	207.6	207.4	207.2	207.4	207.6	207.8
127.5°	224.1	224.3	224.4	224.3	223.8	223.4	222.9	222.5	222.9	223.4	223.8
130°	239.9	240.2	240.4	240.2	239.6	239.0	238.4	237.8	238.4	239.0	239.6
132.5°	255.4	255.6	255.7	255.5	254.9	254.3	253.7	253.1	253.7	254.3	254.9
135°	270.6	270.7	270.8	270.6	270.1	269.7	269.2	268.8	269.2	269.7	270.1
137.5°	285.3	285.1	284.9	284.6	284.2	283.9	283.5	283.1	283.5	283.9	284.2
140°	300.0	299.9	299.8	299.6	299.2	298.9	298.5	298.1	298.5	298.9	299.2
142.5°	313.8	313.7	313.5	313.2	312.9	312.5	312.1	311.8	312.1	312.5	312.9
145°	327.3	327.1	326.9	326.7	326.5	326.4	326.2	326.1	326.2	326.4	326.5
147.5°	340.3	340.1	339.9	339.6	339.3	339.0	338.7	338.4	338.7	339.0	339.3
150°	352.4	352.3	352.1	352.0	351.8	351.7	351.6	351.4	351.6	351.7	351.8
152.5°	363.2	363.2	363.1	363.0	362.7	362.5	362.3	362.1	362.3	362.5	362.7
155°	373.6	373.5	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4
157.5°	382.9	382.8	382.8	382.8	382.8	382.9	383.0	383.0	383.0	382.9	382.8
160°	391.4	391.4	391.4	391.5	391.6	391.7	391.9	392.0	391.9	391.7	391.6
162.5°	399.2	399.1	399.1	399.1	399.4	399.6	399.8	400.0	399.8	399.6	399.4
165°	405.7	405.7	405.7	405.8	406.0	406.3	406.5	406.7	406.5	406.3	406.0
167.5°	411.2	411.1	411.1	411.2	411.5	411.8	412.1	412.4	412.1	411.8	411.5
170°	415.7	415.7	415.7	415.8	416.1	416.4	416.7	417.0	416.7	416.4	416.1
172.5°	419.4	419.4	419.4	419.5	419.8	420.1	420.4	420.7	420.4	420.1	419.8
175°	421.7	421.7	421.7	421.8	422.1	422.4	422.7	423.0	422.7	422.4	422.1
177.5°	423.0	423.0	423.0	423.2	423.5	423.8	424.1	424.4	424.1	423.8	423.5
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.1	879.7	871.3	864.9	858.4	847.5	836.5	833.9	831.4	827.7	824.1
5°	842.1	821.5	800.9	782.4	763.9	749.6	735.2	725.7	716.3	709.4	702.5
7.5°	788.4	757.5	726.6	704.7	682.8	662.0	641.1	634.5	627.8	618.8	609.8
10°	736.5	702.3	668.2	639.6	611.1	590.7	570.3	562.1	554.0	542.6	531.2
12.5°	690.1	652.7	615.4	586.6	557.8	538.1	518.3	506.5	494.7	488.3	481.8
15°	641.6	601.6	561.7	535.1	508.4	490.6	472.8	462.5	452.2	446.0	439.7
17.5°	598.6	559.1	519.6	494.1	468.5	452.2	435.9	426.8	417.8	413.1	408.4
20°	557.8	519.2	480.5	455.6	430.7	417.4	404.1	398.3	392.5	388.6	384.8
22.5°	520.5	482.5	444.5	423.2	401.9	391.2	380.5	376.4	372.3	369.1	365.9
25°	483.1	449.2	415.3	397.2	379.2	370.4	361.6	357.5	353.4	350.2	347.0
27.5°	452.6	420.2	387.8	372.3	356.9	350.0	343.1	339.9	336.7	333.7	330.7
30°	423.0	394.0	365.0	351.7	338.4	332.2	325.9	322.7	319.5	316.7	313.9
32.5°	395.5	370.6	345.7	333.4	321.2	316.1	310.9	307.0	303.2	301.0	298.9
35°	369.3	347.0	324.6	314.6	304.5	299.3	294.2	290.9	287.7	286.0	284.3
37.5°	347.0	327.0	307.0	297.4	287.7	282.8	277.8	275.0	272.3	271.6	271.0
40°	324.2	307.0	289.9	280.4	271.0	266.7	262.4	260.7	258.9	258.5	258.1
42.5°	305.3	288.6	271.8	263.2	254.6	251.0	247.3	246.5	245.6	246.3	246.9
45°	283.4	269.5	255.5	247.6	239.6	236.6	233.6	233.0	232.3	233.6	234.9
47.5°	265.0	252.1	239.2	231.7	224.2	222.0	219.9	219.7	219.4	221.2	222.9
50°	246.1	233.6	221.2	215.1	209.1	207.2	205.3	205.9	206.6	209.3	212.1
52.5°	228.5	216.9	205.3	199.7	194.1	192.8	191.5	193.0	194.5	197.5	200.5
55°	209.1	198.6	188.1	183.8	179.5	178.2	176.9	179.9	182.9	185.7	188.5
57.5°	190.7	181.4	172.2	168.3	164.5	164.3	164.0	166.8	169.6	172.6	175.6
60°	170.9	163.2	155.5	152.4	149.4	149.9	150.3	153.5	156.7	159.1	161.5
62.5°	152.9	146.4	140.0	137.2	134.4	135.5	136.6	139.8	143.0	145.8	148.6
65°	134.8	129.5	124.1	122.2	120.2	121.7	123.2	126.0	128.8	130.8	132.7
67.5°	117.7	113.2	108.6	107.1	105.6	107.1	108.6	111.4	114.2	116.2	118.1
70°	99.6	96.0	92.3	91.3	90.2	91.9	93.6	96.0	98.3	100.3	102.2
72.5°	82.9	80.1	77.3	77.1	76.9	78.4	79.9	82.2	84.6	85.9	87.2
75°	66.6	65.1	63.6	63.3	63.1	64.6	66.1	67.4	68.7	69.8	70.9
77.5°	52.0	50.7	49.4	49.6	49.8	50.9	52.0	53.2	54.5	55.2	55.8
80°	36.9	36.5	36.1	36.5	36.9	37.8	38.6	39.5	40.4	40.8	41.2
82.5°	25.3	24.9	24.5	25.1	25.8	26.4	27.1	27.7	28.3	28.6	28.8
85°	14.6	15.2	15.9	15.9	15.9	16.1	16.3	16.5	16.7	16.5	16.3
87.5°	6.9	7.1	7.3	7.3	7.3	7.5	7.7	7.7	7.7	7.5	7.3
90°	3.3	4.1	5.1	6.1	7.0	8.0	8.3	8.6	8.9	9.2	9.4
92.5°	11.8	12.2	12.7	13.1	13.5	14.0	14.2	14.4	14.7	14.9	14.9
95°	21.7	22.3	22.9	23.5	24.1	24.6	24.9	25.2	25.5	25.8	26.0
97.5°	33.8	34.2	34.6	35.1	35.5	36.0	36.3	36.7	37.1	37.5	37.6
100°	47.1	47.5	47.9	48.2	48.6	49.0	49.2	49.4	49.6	49.9	50.0
102.5°	61.2	61.5	62.1	62.6	63.1	63.6	63.8	64.1	64.3	64.5	64.6
105°	75.5	75.9	76.6	77.3	77.9	78.6	78.6	78.6	78.6	78.6	78.7
107.5°	92.6	92.7	93.0	93.3	93.6	93.9	94.2	94.4	94.6	94.8	94.9
110°	108.8	109.0	109.1	109.3	109.4	109.6	109.9	110.2	110.5	110.8	110.8



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	125.2	125.2	125.2	125.2	125.2	125.2	125.6	126.0	126.4	126.7	126.9
115°	142.4	142.5	142.3	142.2	142.0	141.9	142.0	142.0	142.1	142.2	142.2
117.5°	158.8	158.8	158.7	158.5	158.4	158.2	158.2	158.2	158.2	158.2	158.1
120°	176.0	176.0	175.6	175.3	174.9	174.5	174.5	174.4	174.3	174.2	174.1
122.5°	191.7	191.8	191.6	191.5	191.3	191.2	191.0	190.7	190.5	190.3	190.1
125°	208.1	208.1	208.0	207.8	207.7	207.5	207.2	206.9	206.6	206.3	206.0
127.5°	224.3	224.4	224.3	224.1	224.0	223.8	223.4	222.9	222.5	222.1	221.7
130°	240.2	240.4	240.2	239.9	239.7	239.5	239.2	238.9	238.6	238.3	237.9
132.5°	255.5	255.7	255.6	255.4	255.3	255.1	254.8	254.4	254.0	253.7	253.3
135°	270.6	270.8	270.7	270.6	270.5	270.5	270.2	269.9	269.6	269.3	269.1
137.5°	284.6	284.9	285.1	285.3	285.6	285.8	285.4	285.0	284.7	284.3	284.0
140°	299.6	299.8	299.9	300.0	300.0	300.1	300.0	300.0	299.9	299.8	299.5
142.5°	313.2	313.5	313.7	313.8	314.0	314.1	314.0	314.0	313.9	313.8	313.6
145°	326.7	326.9	327.1	327.3	327.5	327.8	327.7	327.6	327.5	327.5	327.3
147.5°	339.6	339.9	340.1	340.3	340.5	340.7	340.7	340.7	340.7	340.7	340.5
150°	352.0	352.1	352.3	352.4	352.6	352.7	352.7	352.7	352.7	352.7	352.5
152.5°	363.0	363.1	363.2	363.2	363.3	363.4	363.5	363.7	363.8	364.0	363.9
155°	373.4	373.4	373.5	373.6	373.6	373.7	374.0	374.3	374.6	374.9	374.8
157.5°	382.8	382.8	382.8	382.9	383.0	383.0	383.3	383.6	383.9	384.2	384.2
160°	391.5	391.4	391.4	391.4	391.4	391.4	391.7	392.1	392.5	392.9	392.9
162.5°	399.1	399.1	399.1	399.2	399.3	399.4	399.7	400.1	400.5	400.9	400.8
165°	405.8	405.7	405.7	405.7	405.7	405.7	406.1	406.6	407.0	407.5	407.4
167.5°	411.2	411.1	411.1	411.2	411.3	411.4	411.8	412.2	412.7	413.1	413.1
170°	415.8	415.7	415.7	415.7	415.7	415.7	416.2	416.7	417.2	417.8	417.8
172.5°	419.5	419.4	419.4	419.4	419.4	419.4	419.8	420.2	420.7	421.1	421.1
175°	421.8	421.7	421.7	421.7	421.7	421.7	422.1	422.6	423.0	423.5	423.4
177.5°	423.2	423.0	423.0	423.0	423.0	423.0	423.5	423.9	424.4	424.8	424.8
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	925.4	925.4	925.4	925.4
2.5°	822.6	821.1	815.0	809.0
5°	697.4	692.2	690.5	688.8
7.5°	609.4	608.9	599.9	590.9
10°	531.8	532.5	524.3	516.2
12.5°	476.4	471.1	470.4	469.8
15°	434.8	429.9	429.0	428.1
17.5°	405.4	402.4	401.5	400.7
20°	383.0	381.3	379.8	378.3
22.5°	363.7	361.6	360.3	359.0
25°	345.0	343.1	342.7	342.3
27.5°	328.3	325.9	325.9	325.9
30°	312.4	310.9	310.3	309.6
32.5°	297.6	296.3	296.3	296.3
35°	283.6	283.0	282.1	281.3
37.5°	271.0	271.0	270.5	270.1
40°	258.7	259.4	259.4	259.4
42.5°	247.6	248.2	248.2	248.2
45°	236.0	237.0	237.5	237.9
47.5°	224.6	226.3	226.7	227.2
50°	213.4	214.7	214.9	215.1
52.5°	202.0	203.5	204.6	205.7
55°	190.0	191.5	192.2	192.8
57.5°	177.1	178.6	178.9	179.1
60°	163.0	164.5	164.9	165.3
62.5°	149.4	150.3	150.7	151.2
65°	134.0	135.3	136.1	137.0
67.5°	119.2	120.2	120.2	120.2
70°	102.6	103.1	103.7	104.4
72.5°	87.4	87.6	87.6	87.6
75°	71.3	71.7	71.9	72.1
77.5°	56.0	56.3	56.3	56.3
80°	41.0	40.8	40.8	40.8
82.5°	28.1	27.5	27.5	27.5
85°	16.1	15.9	16.1	16.3
87.5°	7.3	7.3	7.3	7.3
90°	9.5	9.7	9.8	10.0
92.5°	14.8	14.6	14.5	14.3
95°	26.0	26.0	26.0	26.0
97.5°	37.5	37.5	37.4	37.3
100°	50.2	50.3	50.5	50.6
102.5°	64.5	64.4	64.4	64.3
105°	78.8	79.0	79.1	79.3
107.5°	94.8	94.7	94.7	94.6
110°	110.7	110.5	110.4	110.3



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	126.9	126.9	126.9	126.9
115°	142.1	142.0	142.0	141.9
117.5°	157.9	157.7	157.4	157.2
120°	174.0	173.8	173.7	173.5
122.5°	189.9	189.6	189.4	189.2
125°	205.7	205.4	205.1	204.8
127.5°	221.4	221.1	220.8	220.5
130°	237.4	236.9	236.3	235.8
132.5°	252.9	252.6	252.2	251.8
135°	268.9	268.8	268.6	268.5
137.5°	283.8	283.6	283.3	283.1
140°	299.0	298.5	298.0	297.4
142.5°	313.2	312.8	312.5	312.1
145°	327.0	326.7	326.4	326.1
147.5°	340.1	339.6	339.2	338.7
150°	352.1	351.6	351.2	350.7
152.5°	363.5	363.1	362.8	362.4
155°	374.3	373.8	373.2	372.7
157.5°	383.7	383.3	382.8	382.4
160°	392.6	392.3	392.0	391.7
162.5°	400.3	399.7	399.2	398.7
165°	406.9	406.4	405.9	405.4
167.5°	412.7	412.2	411.8	411.4
170°	417.2	416.7	416.2	415.7
172.5°	420.6	420.1	419.5	419.0
175°	422.9	422.4	421.9	421.4
177.5°	424.2	423.7	423.2	422.7
180°	424.0	424.0	424.0	424.0



TEST NUMBER: P831370

CATALOG NUMBER: S123DIP-S340D365U830-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.09	12.96	13.00	13.89	15.08	14.32	15.20	15.24	16.13	17.31
	3H	13.74	14.52	14.66	15.46	16.67	15.75	16.53	16.67	17.47	18.68
	4H	14.31	15.05	15.25	15.99	17.22	16.20	16.94	17.14	17.88	19.10
	6H	14.68	15.37	15.64	16.31	17.55	16.48	17.16	17.43	18.11	19.34
	8H	14.78	15.43	15.74	16.39	17.63	16.54	17.19	17.50	18.15	19.38
	12H	14.83	15.44	15.79	16.40	17.66	16.56	17.18	17.52	18.13	19.39
4H	2H	12.66	13.40	13.61	14.35	15.57	14.49	15.23	15.43	16.17	17.39
	3H	14.49	15.11	15.45	16.08	17.32	16.11	16.73	17.06	17.70	18.93
	4H	15.19	15.76	16.16	16.72	17.98	16.69	17.26	17.66	18.22	19.48
	6H	15.67	16.15	16.65	17.14	18.40	17.10	17.58	18.08	18.57	19.83
	8H	15.81	16.26	16.78	17.24	18.51	17.21	17.66	18.19	18.65	19.92
	12H	15.87	16.28	16.87	17.28	18.56	17.26	17.66	18.25	18.66	19.94
8H	4H	15.46	15.91	16.44	16.89	18.17	16.80	17.25	17.78	18.23	19.51
	6H	16.05	16.42	17.05	17.45	18.72	17.30	17.68	18.31	18.70	19.97
	8H	16.26	16.59	17.27	17.60	18.89	17.48	17.81	18.50	18.82	20.11
	12H	16.38	16.67	17.40	17.68	19.01	17.59	17.87	18.60	18.88	20.22
12H	4H	15.46	15.87	16.46	16.87	18.15	16.78	17.18	17.77	18.18	19.46
	6H	16.10	16.43	17.11	17.44	18.73	17.32	17.65	18.33	18.66	19.95
	8H	16.34	16.62	17.35	17.63	18.97	17.52	17.81	18.53	18.81	20.15