

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331880-830

Luminaire Tested: **S123DIP-S340D585U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331880-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3537.7 lumens
Efficiency: N/A
Efficacy: 138.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331880-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331880-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32
2	86	79	73	68	78	72	67	62	59	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P331880-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.4
10°-20°	135.9	3.8
20°-30°	200.7	5.7
30°-40°	234.4	6.6
40°-50°	235.7	6.7
50°-60°	207.0	5.9
60°-70°	154.2	4.4
70°-80°	87.9	2.5
80°-90°	27.2	0.8
90°-100°	26.3	0.7
100°-110°	125.4	3.5
110°-120°	301.2	8.5
120°-130°	383.5	10.8
130°-140°	409.8	11.6
140°-150°	383.2	10.8
150°-160°	309.1	8.7
160°-170°	199.5	5.6
170°-180°	68.7	1.9
0°-30°	384.6	10.9
0°-40°	619.1	17.5
0°-60°	1061.7	30.0
0°-90°	1331.1	37.6
90°-120°	452.8	12.8
90°-150°	1629.3	46.1
90°-180°	2207.0	62.4
0°-180°	3537.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	6	13	15	16	3
95°	33	12	17	20	20	41
105°	160	163	118	28	24	170
115°	300	304	309	314	316	297
125°	424	428	430	431	432	378
135°	527	531	533	534	533	406
145°	608	612	613	614	614	381
155°	670	669	670	672	669	309
165°	707	705	705	709	705	200
175°	724	721	721	725	721	69
180°	724	724	724	724	724	



TEST NUMBER: P331880-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.2	9.2	9.2	9.2	9.2	9.4	9.6	9.8	10.1	10.3	10.4
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	10.0	9.7	9.3	9.0	8.7	9.0	10.3	11.4	12.6	13.8	14.5
95°	32.8	27.9	23.0	18.1	13.2	11.4	12.7	14.0	15.4	16.7	17.5
97.5°	65.9	63.7	61.5	59.3	57.1	51.7	43.1	34.5	25.9	17.3	18.3
100°	90.9	93.2	95.7	98.0	100.4	92.3	73.6	55.0	36.4	17.7	18.7
102.5°	119.2	120.9	122.7	124.4	126.1	116.8	96.4	76.1	55.7	35.3	32.4
105°	160.2	161.6	162.9	164.1	165.4	160.7	150.0	139.2	128.5	117.7	96.6
107.5°	203.4	204.4	205.6	206.6	207.6	209.0	210.7	212.4	214.1	215.7	200.3
110°	232.2	233.2	234.1	235.1	236.0	237.2	238.5	239.8	241.1	242.4	238.5



TEST NUMBER: P331880-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.8	260.6	261.5	262.3	263.2	264.3	265.6	266.9	268.2	269.6	269.7
115°	300.5	301.2	301.9	302.7	303.4	304.3	305.4	306.4	307.5	308.6	309.8
117.5°	340.0	340.8	341.8	342.6	343.5	344.2	344.8	345.3	345.9	346.4	347.4
120°	364.5	365.5	366.6	367.7	368.8	369.5	369.9	370.2	370.6	370.9	371.9
122.5°	389.5	390.3	391.2	392.1	392.9	393.6	394.1	394.5	395.0	395.5	396.2
125°	423.6	424.6	425.6	426.5	427.4	428.2	428.7	429.1	429.6	430.1	430.3
127.5°	456.8	457.7	458.6	459.6	460.5	461.3	461.8	462.5	463.1	463.6	464.0
130°	477.4	478.3	479.3	480.2	481.2	481.9	482.4	482.9	483.3	483.8	484.3
132.5°	497.2	498.1	499.1	500.0	501.0	501.6	502.0	502.4	502.8	503.2	503.7
135°	527.4	528.1	528.8	529.5	530.3	530.8	531.3	531.8	532.3	532.7	533.1
137.5°	553.2	554.1	555.0	555.9	556.8	557.4	557.6	557.9	558.2	558.5	559.0
140°	570.3	571.1	571.8	572.5	573.3	573.8	574.1	574.5	574.9	575.2	575.7
142.5°	586.3	587.0	587.8	588.4	589.2	589.7	590.0	590.4	590.8	591.2	591.5
145°	608.5	609.4	610.2	611.1	611.9	612.5	612.7	612.9	613.1	613.4	613.6
147.5°	629.5	630.1	630.7	631.1	631.7	632.1	632.4	632.5	632.8	633.1	633.3
150°	642.4	642.8	643.1	643.5	643.9	644.1	644.4	644.6	644.9	645.1	645.4
152.5°	654.0	654.2	654.3	654.5	654.7	654.9	655.0	655.2	655.3	655.4	655.8
155°	670.3	670.1	669.9	669.7	669.4	669.4	669.5	669.6	669.7	669.9	670.4
157.5°	683.1	683.1	683.0	683.0	683.0	682.9	682.8	682.7	682.5	682.4	683.2
160°	690.8	690.7	690.6	690.4	690.3	690.2	690.0	689.9	689.8	689.8	690.4
162.5°	698.1	697.8	697.5	697.2	696.8	696.6	696.5	696.4	696.3	696.2	697.0
165°	706.9	706.5	706.2	705.9	705.5	705.2	705.1	705.0	704.9	704.7	705.8
167.5°	713.8	713.3	712.8	712.4	711.9	711.6	711.6	711.6	711.6	711.6	712.7
170°	717.7	717.2	716.7	716.2	715.8	715.5	715.5	715.5	715.5	715.5	716.5
172.5°	720.3	719.7	719.1	718.5	717.9	717.7	717.8	717.9	718.0	718.1	719.1
175°	723.6	723.0	722.4	721.8	721.2	721.0	721.0	721.2	721.3	721.4	722.3
177.5°	724.4	724.0	723.5	723.0	722.6	722.4	722.5	722.6	722.6	722.7	723.5
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P331880-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	10.4	10.4	10.4	10.4	10.5	10.5	10.6	10.7
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	15.3	16.0	16.8	17.2	17.4	17.5	17.7	17.8
95°	18.4	19.1	20.0	20.5	20.5	20.5	20.5	20.5
97.5°	19.2	20.2	21.1	21.7	21.8	21.9	22.1	22.1
100°	19.6	20.6	21.6	22.1	22.2	22.3	22.4	22.6
102.5°	29.4	26.5	23.6	22.1	22.3	22.6	22.8	23.0
105°	75.4	54.3	33.2	22.7	22.9	23.2	23.4	23.7
107.5°	184.7	169.3	153.7	138.1	122.1	106.1	90.2	74.3
110°	234.6	230.6	226.7	216.1	199.1	182.0	164.9	147.8



TEST NUMBER: P331880-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	269.7	269.8	269.8	268.1	264.5	260.8	257.2	253.6
115°	310.9	312.2	313.4	314.1	314.6	315.2	315.7	316.1
117.5°	348.4	349.3	350.2	350.8	350.9	351.0	351.1	351.2
120°	372.9	373.8	374.8	375.2	375.2	375.2	375.2	375.2
122.5°	396.8	397.5	398.1	398.5	398.6	398.7	398.8	398.9
125°	430.6	430.7	431.0	431.3	431.5	431.8	432.0	432.3
127.5°	464.4	464.8	465.1	465.2	465.0	464.8	464.5	464.3
130°	484.7	485.2	485.7	485.9	485.6	485.4	485.1	484.9
132.5°	504.2	504.6	505.1	505.2	504.8	504.4	504.2	503.8
135°	533.5	533.9	534.1	534.1	533.9	533.5	533.1	532.7
137.5°	559.6	560.2	560.7	560.9	560.6	560.4	560.2	560.0
140°	576.2	576.6	577.1	577.2	577.0	576.7	576.6	576.3
142.5°	591.9	592.3	592.7	592.7	592.4	592.0	591.6	591.4
145°	613.9	614.1	614.3	614.4	614.4	614.4	614.4	614.4
147.5°	633.6	633.8	634.0	633.9	633.3	632.7	632.3	631.7
150°	645.5	645.8	646.0	646.0	645.6	645.3	644.9	644.6
152.5°	656.3	656.7	657.1	657.0	656.6	656.0	655.4	654.9
155°	671.0	671.7	672.2	672.1	671.5	670.7	670.1	669.3
157.5°	683.8	684.6	685.3	685.1	684.2	683.3	682.4	681.5
160°	691.2	691.8	692.6	692.5	691.7	690.9	690.0	689.2
162.5°	697.8	698.6	699.5	699.5	698.7	698.0	697.2	696.5
165°	706.7	707.7	708.6	708.7	707.8	707.0	706.2	705.3
167.5°	713.6	714.5	715.5	715.5	714.5	713.6	712.7	711.6
170°	717.5	718.4	719.3	719.3	718.4	717.5	716.5	715.5
172.5°	720.0	721.0	721.9	721.9	720.9	719.8	718.7	717.7
175°	723.1	724.0	724.8	724.7	723.8	722.8	721.9	720.9
177.5°	724.2	725.0	725.8	725.7	724.7	723.8	722.8	721.9
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

(END OF REPORT)