

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331881-830

Luminaire Tested: **S123DIP-S340D585U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331881-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3227.3 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331881-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331881-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	79	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	23	19	17	19	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P331881-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.5
10°-20°	135.9	4.2
20°-30°	200.7	6.2
30°-40°	234.4	7.3
40°-50°	235.7	7.3
50°-60°	207.0	6.4
60°-70°	154.2	4.8
70°-80°	87.9	2.7
80°-90°	27.2	0.8
90°-100°	44.6	1.4
100°-110°	133.4	4.1
110°-120°	227.0	7.0
120°-130°	298.5	9.3
130°-140°	335.6	10.4
140°-150°	329.8	10.2
150°-160°	277.7	8.6
160°-170°	184.8	5.7
170°-180°	64.7	2.0
0°-30°	384.6	11.9
0°-40°	619.1	19.2
0°-60°	1061.7	32.9
0°-90°	1331.1	41.2
90°-120°	405.0	12.5
90°-150°	1368.9	42.4
90°-180°	1896.0	58.7
0°-180°	3227.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	6	13	15	16	3
95°	32	36	40	42	42	36
105°	121	122	127	127	128	130
115°	228	230	229	230	229	226
125°	334	336	335	333	331	298
135°	434	437	437	434	433	334
145°	526	527	529	528	526	329
155°	603	603	603	605	602	277
165°	656	655	655	658	654	185
175°	683	681	681	683	680	65
180°	684	684	684	684	684	



TEST NUMBER: P331881-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.2	9.2	9.2	9.2	9.2	9.4	9.6	9.8	10.1	10.3	10.4
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	13.0	13.9	14.6	15.5	16.3	17.2	18.0	18.9	19.8	20.6	21.0
95°	31.8	32.5	33.4	34.2	35.1	36.0	36.9	37.9	38.8	39.8	40.2
97.5°	56.4	56.9	57.6	58.2	58.8	59.5	60.1	60.9	61.5	62.3	62.8
100°	73.1	73.8	74.6	75.3	76.0	76.6	77.2	77.9	78.4	79.0	79.4
102.5°	92.5	92.9	93.3	93.8	94.2	94.8	95.6	96.4	97.2	97.9	98.3
105°	120.9	121.2	121.4	121.7	122.0	122.5	123.7	124.7	125.8	126.9	126.9
107.5°	154.1	154.2	154.4	154.5	154.7	155.0	155.3	155.8	156.3	156.7	157.0
110°	174.7	174.9	175.2	175.4	175.7	175.9	176.2	176.4	176.6	176.9	177.4



TEST NUMBER: P331881-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.3	196.5	196.6	196.8	196.9	197.0	197.0	197.1	197.1	197.7
115°	228.5	228.8	229.2	229.6	229.9	230.0	229.7	229.5	229.2	229.0	229.1
117.5°	261.0	261.2	261.5	261.6	261.9	261.8	261.6	261.3	261.0	260.6	260.6
120°	281.2	281.9	282.6	283.3	284.1	284.1	283.5	283.0	282.3	281.7	281.6
122.5°	302.3	302.7	303.3	303.8	304.3	304.4	304.2	303.9	303.5	303.2	302.9
125°	334.4	334.8	335.1	335.5	335.8	335.9	335.6	335.5	335.2	335.0	334.4
127.5°	364.1	364.9	365.6	366.4	367.1	367.4	367.1	366.8	366.6	366.4	365.7
130°	383.9	384.8	385.8	386.7	387.7	388.0	387.7	387.3	386.9	386.5	386.1
132.5°	403.6	404.6	405.6	406.5	407.5	407.8	407.6	407.3	407.0	406.8	406.1
135°	433.9	434.6	435.3	436.0	436.7	437.1	436.9	436.8	436.7	436.6	436.1
137.5°	461.8	462.4	463.0	463.6	464.2	464.7	465.0	465.2	465.6	465.9	465.4
140°	481.2	481.7	482.4	483.0	483.5	483.9	484.0	484.2	484.3	484.4	484.3
142.5°	498.8	499.4	500.0	500.6	501.1	501.6	501.8	502.0	502.3	502.5	502.4
145°	526.3	526.6	526.8	527.1	527.3	527.5	527.9	528.3	528.7	529.0	528.9
147.5°	550.4	550.8	551.3	551.7	552.1	552.5	552.9	553.2	553.6	553.8	553.8
150°	567.2	567.4	567.7	567.9	568.2	568.4	568.6	568.8	569.1	569.3	569.3
152.5°	581.0	581.3	581.6	581.9	582.3	582.5	582.7	582.8	583.0	583.1	583.2
155°	602.7	602.7	602.7	602.7	602.7	602.8	602.9	602.9	603.1	603.2	603.7
157.5°	621.1	621.0	620.9	620.8	620.6	620.6	620.7	620.8	620.9	620.9	621.4
160°	632.7	632.5	632.3	632.1	631.8	631.7	631.7	631.7	631.7	631.7	632.3
162.5°	643.1	642.7	642.4	642.1	641.8	641.7	641.8	641.9	642.0	642.1	642.6
165°	656.4	656.1	655.7	655.3	655.0	654.8	654.8	654.8	654.8	654.8	655.5
167.5°	667.0	666.6	666.1	665.6	665.2	665.0	665.1	665.2	665.2	665.3	666.1
170°	673.1	672.6	672.1	671.7	671.2	670.9	670.9	670.9	670.9	670.9	671.8
172.5°	677.8	677.3	676.8	676.4	675.9	675.7	675.7	675.7	675.7	675.7	676.5
175°	682.8	682.3	681.8	681.4	680.9	680.6	680.6	680.6	680.6	680.6	681.4
177.5°	684.9	684.5	684.1	683.6	683.2	683.1	683.1	683.1	683.1	683.1	683.6
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331881-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	10.4	10.4	10.4	10.4	10.5	10.5	10.6	10.7
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	21.4	21.8	22.1	22.3	22.1	22.0	21.9	21.7
95°	40.7	41.2	41.7	41.9	41.9	41.9	41.9	41.9
97.5°	63.3	63.9	64.5	64.7	64.7	64.6	64.6	64.5
100°	79.7	80.1	80.5	80.8	81.0	81.2	81.4	81.7
102.5°	98.7	99.1	99.3	99.5	99.5	99.4	99.4	99.3
105°	126.9	126.9	126.9	127.0	127.2	127.4	127.7	128.0
107.5°	157.4	157.8	158.2	158.3	158.2	158.1	157.9	157.8
110°	177.9	178.3	178.8	178.9	178.7	178.4	178.2	178.0



TEST NUMBER: P331881-830

CATALOG NUMBER: S123DIP-S340D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	198.8	199.3	199.6	199.6	199.5	199.5	199.4
115°	229.2	229.4	229.5	229.5	229.4	229.2	229.1	229.0
117.5°	260.6	260.5	260.5	260.3	260.0	259.7	259.4	259.0
120°	281.4	281.3	281.3	281.1	280.8	280.6	280.3	280.1
122.5°	302.6	302.3	302.0	301.6	301.3	301.0	300.7	300.3
125°	333.9	333.5	333.0	332.5	332.1	331.6	331.1	330.6
127.5°	365.0	364.3	363.6	363.1	362.5	361.9	361.4	360.8
130°	385.6	385.1	384.7	384.0	383.1	382.3	381.4	380.6
132.5°	405.6	405.0	404.4	403.9	403.2	402.6	401.9	401.2
135°	435.5	435.1	434.6	434.2	434.0	433.8	433.6	433.3
137.5°	464.9	464.4	463.9	463.4	463.0	462.5	462.0	461.6
140°	484.2	484.0	483.9	483.4	482.6	481.7	480.9	480.1
142.5°	502.2	502.1	502.0	501.6	501.0	500.3	499.6	499.0
145°	528.8	528.7	528.6	528.2	527.7	527.3	526.8	526.3
147.5°	553.8	553.8	553.8	553.5	552.8	552.0	551.4	550.6
150°	569.3	569.3	569.3	569.0	568.3	567.5	566.8	566.1
152.5°	583.5	583.7	583.9	583.6	583.1	582.4	581.8	581.2
155°	604.2	604.6	605.1	604.9	604.1	603.2	602.5	601.6
157.5°	622.0	622.5	622.9	622.8	622.2	621.5	620.9	620.2
160°	632.9	633.5	634.0	634.1	633.7	633.2	632.7	632.3
162.5°	643.2	643.9	644.4	644.3	643.6	642.8	642.1	641.3
165°	656.3	657.0	657.7	657.6	656.8	655.9	655.2	654.3
167.5°	666.8	667.6	668.4	668.4	667.6	666.8	666.1	665.3
170°	672.6	673.4	674.3	674.3	673.4	672.6	671.8	670.9
172.5°	677.1	677.9	678.6	678.6	677.8	676.9	676.1	675.2
175°	682.0	682.8	683.5	683.4	682.6	681.7	680.9	680.0
177.5°	684.3	684.9	685.4	685.3	684.7	684.0	683.3	682.7
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4

(END OF REPORT)