

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331302-840

Luminaire Tested: **S122DIP-S485D530U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331302-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D530U840-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4082.2 lumens  
Efficiency: N/A  
Efficacy: 124.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331302-840

CATALOG NUMBER: S122DIP-S485D530U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331302-840

CATALOG NUMBER: S122DIP-S485D530U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	73	70	68	60	58	57	49	48	47	41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331302-840

CATALOG NUMBER: S122DIP-S485D530U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	1.8
10°-20°	207.5	5.1
20°-30°	305.0	7.5
30°-40°	354.3	8.7
40°-50°	354.0	8.7
50°-60°	308.7	7.6
60°-70°	228.2	5.6
70°-80°	129.3	3.2
80°-90°	37.4	0.9
90°-100°	119.7	2.9
100°-110°	406.3	10.0
110°-120°	431.7	10.6
120°-130°	355.4	8.7
130°-140°	285.4	7.0
140°-150°	215.7	5.3
150°-160°	151.6	3.7
160°-170°	89.2	2.2
170°-180°	29.0	0.7
0°-30°	586.3	14.4
0°-40°	940.7	23.0
0°-60°	1603.3	39.3
0°-90°	1998.2	48.9
90°-120°	957.8	23.5
90°-150°	1814.1	44.4
90°-180°	2084.0	51.1
0°-180°	4082.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	8	20	19	19	3
95°	20	50	226	85	66	21
105°	70	106	427	763	649	75
115°	124	156	357	737	854	123
125°	173	204	343	597	693	153
135°	203	242	339	502	574	157
145°	232	266	338	419	458	145
155°	263	284	328	371	385	121
165°	287	295	314	333	338	81
175°	299	299	302	306	305	28
180°	299	299	299	299	299	



TEST NUMBER: P331302-840

CATALOG NUMBER: S122DIP-S485D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.0	11.0	11.2	11.2	11.2	11.2	11.5	12.1	12.5	12.3	11.8
90°	0.6	2.3	4.6	5.8	6.9	8.7	11.5	15.6	19.0	19.6	19.0
92.5°	7.1	10.1	14.2	16.9	20.7	26.2	39.2	57.5	73.8	74.8	63.2
95°	20.2	22.4	28.2	33.4	42.6	56.5	82.9	133.0	199.9	225.8	197.5
97.5°	32.8	36.0	42.0	49.9	60.5	76.1	109.5	179.3	290.2	385.4	404.2
100°	44.3	46.0	51.3	60.5	72.0	88.2	118.7	188.9	313.3	454.9	537.9
102.5°	54.9	56.2	61.4	70.6	82.6	98.7	126.9	189.3	304.6	457.3	587.6
105°	70.3	72.6	76.5	85.2	97.9	114.0	141.1	192.4	287.4	426.8	580.0
107.5°	86.8	88.7	92.6	100.6	113.1	129.4	155.6	200.3	278.8	394.0	529.4
110°	97.9	100.2	103.7	111.2	123.2	140.0	165.3	206.7	277.0	378.4	497.6



TEST NUMBER: P331302-840

CATALOG NUMBER: S122DIP-S485D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.1	110.4	114.2	121.3	132.9	150.1	174.5	213.7	277.5	368.2	475.4
115°	123.8	126.7	130.2	137.0	148.6	164.1	188.9	224.0	279.9	357.1	448.1
117.5°	140.2	142.5	145.9	152.1	163.1	179.3	202.2	235.1	284.1	351.6	430.8
120°	150.3	152.6	156.0	161.3	172.8	188.9	211.4	242.5	286.8	348.4	421.6
122.5°	160.0	161.9	165.3	171.0	182.5	199.0	220.2	248.9	290.0	346.6	413.7
125°	172.8	174.5	177.9	184.9	196.4	212.5	233.3	259.1	294.9	343.3	402.5
127.5°	182.9	185.2	190.1	197.6	208.7	225.3	245.5	268.7	299.8	341.3	392.2
130°	188.9	191.2	196.9	205.0	216.5	232.7	252.9	274.7	303.5	340.3	385.3
132.5°	194.4	197.2	203.4	212.0	223.9	240.0	259.2	280.7	307.2	339.9	379.7
135°	202.7	205.0	212.0	220.6	233.8	249.9	268.4	288.5	311.5	339.2	372.0
137.5°	210.6	213.3	220.3	229.4	242.6	257.5	275.8	294.5	315.5	339.1	366.6
140°	216.5	218.8	225.8	235.0	247.6	262.7	279.9	297.7	317.3	338.6	363.5
142.5°	222.6	224.4	230.9	240.0	252.3	266.3	283.2	300.5	318.7	338.6	360.2
145°	231.6	233.8	239.5	248.2	259.7	272.4	287.9	304.1	320.2	337.5	355.9
147.5°	241.2	242.9	248.4	256.4	266.0	277.2	291.9	306.1	320.6	335.4	351.5
150°	247.6	249.3	254.0	261.5	270.1	280.4	293.7	307.0	320.2	334.1	347.9
152.5°	254.1	254.9	259.5	266.1	274.3	283.7	295.6	307.4	319.3	331.7	344.7
155°	263.2	263.8	267.2	273.6	279.9	288.5	298.3	308.1	317.9	327.7	338.6
157.5°	270.7	271.4	274.2	279.6	284.8	292.0	300.2	308.1	315.3	323.6	333.0
160°	275.9	276.4	278.7	283.4	287.9	294.3	301.2	308.1	313.9	320.8	328.8
162.5°	280.9	280.5	282.9	286.6	290.7	295.7	301.6	307.6	312.5	318.5	325.2
165°	286.8	286.2	287.4	290.8	293.7	297.2	302.4	306.4	309.8	313.9	319.0
167.5°	291.6	290.9	292.0	294.2	296.3	298.4	302.3	305.6	307.2	309.8	313.1
170°	294.9	293.7	294.3	296.0	297.2	298.9	301.7	304.7	305.8	307.5	309.8
172.5°	296.7	296.0	295.7	297.4	298.1	299.3	301.3	303.3	304.0	304.8	306.6
175°	298.9	298.3	297.7	298.9	298.9	299.4	300.6	301.7	301.2	301.7	302.4
177.5°	299.9	299.0	298.5	299.4	299.4	299.4	299.9	300.8	299.9	299.4	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331302-840

CATALOG NUMBER: S122DIP-S485D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	11.3	10.7	10.5	10.4	10.2	10.1	10.0	9.8
90°	18.4	17.3	18.4	19.0	19.0	19.0	19.0	19.0
92.5°	50.2	43.1	38.3	34.6	34.2	32.4	32.8	31.9
95°	150.9	115.7	91.6	78.9	71.4	66.9	65.0	65.6
97.5°	352.1	288.1	225.8	184.2	156.6	142.5	134.1	129.3
100°	525.8	454.4	375.5	305.8	258.0	233.3	216.5	206.2
102.5°	639.6	623.5	565.8	491.9	440.0	397.7	376.9	362.8
105°	699.7	764.8	772.3	753.3	717.6	681.9	657.1	649.0
107.5°	656.4	754.5	814.4	842.2	846.7	844.8	839.8	829.1
110°	619.1	722.2	795.9	843.1	867.9	878.9	884.0	883.4





TEST NUMBER: P331302-840

CATALOG NUMBER: S122DIP-S485D530U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	585.0	684.0	762.8	816.9	851.3	869.6	879.4	882.5
115°	543.1	631.8	707.2	766.6	807.4	833.9	848.9	854.0
117.5°	511.5	589.4	657.8	713.5	755.2	783.2	798.9	803.2
120°	495.8	567.2	628.3	680.8	721.0	748.1	764.8	770.5
122.5°	483.4	548.9	606.6	654.0	690.1	716.8	731.6	736.5
125°	465.3	524.6	575.3	618.5	652.0	673.8	688.2	692.9
127.5°	447.5	501.2	549.0	588.9	617.9	638.4	650.9	654.6
130°	436.0	485.5	531.0	569.0	597.2	616.8	628.3	632.9
132.5°	425.0	470.8	512.6	548.3	576.0	595.6	606.2	610.4
135°	409.5	447.5	485.5	517.8	542.5	561.5	571.9	574.2
137.5°	397.2	429.0	459.1	487.3	509.8	526.1	535.2	538.7
140°	389.3	417.0	443.4	468.8	487.3	502.2	510.8	514.3
142.5°	382.8	406.4	429.2	450.4	467.9	481.5	489.2	489.9
145°	373.8	392.7	410.6	427.4	441.1	450.9	456.7	458.4
147.5°	366.8	381.7	395.7	407.9	419.3	427.1	431.0	432.0
150°	361.6	374.4	386.5	396.8	405.5	412.3	415.8	416.4
152.5°	356.6	368.4	378.6	387.6	394.4	400.4	402.9	403.0
155°	349.6	358.8	367.4	373.8	380.1	384.2	386.5	385.3
157.5°	341.4	349.1	356.4	361.3	365.8	369.2	370.2	370.2
160°	336.3	342.6	349.0	353.0	357.1	359.9	360.5	360.5
162.5°	331.2	336.7	342.1	345.2	349.2	351.2	351.7	351.3
165°	323.7	327.7	331.7	334.1	336.3	338.6	338.6	338.1
167.5°	316.4	319.5	322.2	324.4	325.4	326.7	326.6	325.9
170°	312.8	314.5	316.8	317.9	318.5	320.2	319.6	318.5
172.5°	308.6	309.8	311.6	312.4	313.0	313.8	313.2	312.5
175°	304.1	304.7	305.3	305.8	305.8	306.4	305.8	304.7
177.5°	300.8	300.8	301.3	301.3	301.3	301.3	300.8	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4

(END OF REPORT)